

SULLINS 2mm Connectors (Cont.)

| Fig. | Circuits | Dimensions - mm | | Digi-Key Part No. | Price Each | | | Sullins Part No. | |
|--|--|-----------------|-------------|-------------------|-------------|------|-----------------|------------------|----------------|
| | | A | B | | 1 | 10 | 100 | | |
| 8 | 50 | 48.00 | 50.00 | S5803-25-ND | 2.84 | 2.47 | 2.09 | PRPN252PARN-RC | |
| | 60 | 58.00 | 60.00 | S5803-30-ND | 3.18 | 2.76 | 2.33 | PRPN302PARN-RC | |
| | 80 | 78.00 | 80.00 | S5803-40-ND | 5.12 | 4.44 | 3.76 | PRPN402PARN-RC | |
| Dual Row Receptacles, Straight | | | | | | | | | |
| 9 | 12 | 10.00 | 12.50 | S2201-06-ND | 1.41 | 1.18 | .75 | PPPN062AFNCN | |
| Dual Row Receptacles, Straight — RoHS Compliant | | | | | | | | | |
| 9 | 4 | 2.00 | 4.50 | S5750-02-ND | .86 | .72 | .46 | PPPN022AFNCN-RC | |
| | 6 | 4.00 | 6.50 | S5750-03-ND | .94 | .79 | .50 | PPPN032AFNCN-RC | |
| | 8 | 6.00 | 8.50 | S5750-04-ND | 1.22 | 1.01 | .65 | PPPN042AFNCN-RC | |
| | 10 | 8.00 | 10.50 | S5750-05-ND | 1.41 | 1.18 | .75 | PPPN052AFNCN-RC | |
| | 12 | 10.00 | 12.50 | S5750-06-ND | 1.57 | 1.31 | .84 | PPPN062AFNCN-RC | |
| | 14 | 12.00 | 14.50 | S5750-07-ND | 1.69 | 1.40 | .90 | PPPN072AFNCN-RC | |
| | 16 | 14.00 | 16.50 | S5750-08-ND | 1.96 | 1.63 | 1.04 | PPPN082AFNCN-RC | |
| | 18 | 16.00 | 18.50 | S5750-09-ND | 2.01 | 1.66 | 1.06 | PPPN092AFNCN-RC | |
| | 20 | 18.00 | 20.50 | S5750-10-ND | 2.04 | 1.70 | 1.08 | PPPN102AFNCN-RC | |
| | 22 | 20.00 | 22.50 | S5750-11-ND | 2.12 | 1.76 | 1.13 | PPPN112AFNCN-RC | |
| | 24 | 22.00 | 24.50 | S5750-12-ND | 2.17 | 1.79 | 1.15 | PPPN122AFNCN-RC | |
| | 26 | 24.00 | 26.50 | S5750-13-ND | 2.24 | 1.86 | 1.19 | PPPN132AFNCN-RC | |
| | 30 | 28.00 | 30.50 | S5750-15-ND | 2.56 | 2.12 | 1.35 | PPPN152AFNCN-RC | |
| | 34 | 32.00 | 34.50 | S5750-17-ND | 2.91 | 2.41 | 1.54 | PPPN172AFNCN-RC | |
| | 40 | 38.00 | 40.50 | S5750-20-ND | 3.42 | 2.84 | 1.81 | PPPN202AFNCN-RC | |
| | 44 | 42.00 | 44.50 | S5750-22-ND | 3.58 | 2.97 | 1.89 | PPPN222AFNCN-RC | |
| | 50 | 48.00 | 50.50 | S5750-25-ND | 4.08 | 3.39 | 2.16 | PPPN252AFNCN-RC | |
| | 60 | 58.00 | 60.50 | S5750-30-ND | 4.87 | 4.04 | 2.58 | PPPN302AFNCN-RC | |
| 80 | 78.00 | 80.50 | S5750-40-ND | 6.36 | 5.28 | 3.37 | PPPN402AFNCN-RC | | |
| Dual Row Receptacles, SMT, without Locating Peg — RoHS Compliant | | | | | | | | | |
| 10 | 4 | 2.00 | 4.00 | S6010-02-ND | 1.07 | .88 | .57 | NPPN022FFKS-RC | |
| | 6 | 4.00 | 6.00 | S6010-03-ND | 1.10 | .92 | .59 | NPPN032FFKS-RC | |
| | 8 | 6.00 | 8.00 | S6010-04-ND | 1.26 | 1.05 | .67 | NPPN042FFKS-RC | |
| | 10 | 8.00 | 10.00 | S6010-05-ND | 1.41 | 1.18 | .75 | NPPN052FFKS-RC | |
| | 12 | 10.00 | 12.00 | S6010-06-ND | 1.69 | 1.40 | .90 | NPPN062FFKS-RC | |
| | 14 | 12.00 | 14.00 | S6010-07-ND | 1.96 | 1.63 | 1.04 | NPPN072FFKS-RC | |
| | 16 | 14.00 | 16.00 | S6010-08-ND | 2.12 | 1.76 | 1.13 | NPPN082FFKS-RC | |
| | 18 | 16.00 | 18.00 | S6010-09-ND | 2.40 | 1.99 | 1.27 | NPPN092FFKS-RC | |
| | 20 | 18.00 | 20.00 | S6010-10-ND | 2.67 | 2.22 | 1.42 | NPPN102FFKS-RC | |
| | 24 | 22.00 | 24.00 | S6010-12-ND | 2.98 | 2.48 | 1.58 | NPPN122FFKS-RC | |
| | 26 | 24.00 | 26.00 | S6010-13-ND | 3.22 | 2.67 | 1.71 | NPPN132FFKS-RC | |
| | 30 | 28.00 | 30.00 | S6010-15-ND | 3.74 | 3.10 | 1.98 | NPPN152FFKS-RC | |
| | 40 | 38.00 | 40.00 | S6010-20-ND | 4.79 | 3.97 | 2.54 | NPPN202FFKS-RC | |
| | 44 | 42.00 | 44.00 | S6010-22-ND | 5.07 | 4.20 | 2.68 | NPPN222FFKS-RC | |
| | 50 | 48.00 | 50.00 | S6010-25-ND | 5.78 | 4.79 | 3.06 | NPPN252FFKS-RC | |
| | 60 | 58.00 | 60.00 | S6010-30-ND | 6.68 | 5.54 | 3.53 | NPPN302FFKS-RC | |
| | Dual Row Receptacles, SMT, with Locating Peg — RoHS Compliant | | | | | | | | |
| | 10 | 4 | 2.00 | 4.00 | S6011-02-ND | 1.07 | .88 | .57 | NPPN022FFKP-RC |
| 6 | | 4.00 | 6.00 | S6011-03-ND | 1.10 | .92 | .59 | NPPN032FFKP-RC | |
| 8 | | 6.00 | 8.00 | S6011-04-ND | 1.26 | 1.05 | .67 | NPPN042FFKP-RC | |
| 10 | | 8.00 | 10.00 | S6011-05-ND | 1.41 | 1.18 | .75 | NPPN052FFKP-RC | |
| 12 | | 10.00 | 12.00 | S6011-06-ND | 1.69 | 1.40 | .90 | NPPN062FFKP-RC | |
| 14 | | 12.00 | 14.00 | S6011-07-ND | 1.96 | 1.63 | 1.04 | NPPN072FFKP-RC | |
| 16 | | 14.00 | 16.00 | S6011-08-ND | 2.12 | 1.76 | 1.13 | NPPN082FFKP-RC | |
| 18 | | 16.00 | 18.00 | S6011-09-ND | 2.40 | 1.99 | 1.27 | NPPN092FFKP-RC | |
| 24 | | 22.00 | 24.00 | S6011-12-ND | 2.98 | 2.48 | 1.58 | NPPN122FFKP-RC | |
| 30 | | 28.00 | 30.00 | S6011-15-ND | 3.74 | 3.10 | 1.98 | NPPN152FFKP-RC | |
| 44 | | 42.00 | 44.00 | S6011-22-ND | 5.07 | 4.20 | 2.68 | NPPN222FFKP-RC | |
| 50 | | 48.00 | 50.00 | S6011-25-ND | 5.78 | 4.79 | 3.06 | NPPN252FFKP-RC | |
| 60 | 58.00 | 60.00 | S6011-30-ND | 6.68 | 5.54 | 3.53 | NPPN302FFKP-RC | | |
| Dual Row Receptacles (Bottom Entry), SMT, with Locating Peg | | | | | | | | | |
| 11 | 18 | 16.00 | 18.00 | S2205-09-ND | 2.87 | 2.38 | 1.52 | PPPN092GHNP | |
| | 56 | 54.00 | 56.00 | S2205-28-ND | 7.98 | 6.61 | 4.22 | PPPN282GHNP | |
| | 60 | 58.00 | 60.00 | S2205-30-ND | 8.56 | 7.10 | 4.53 | PPPN302GHNP | |
| Dual Row Receptacles (Top Entry Low Profile), SMT, with Locating Peg | | | | | | | | | |
| 12 | 18 | 16.00 | 18.00 | S2206-09-ND | 2.87 | 2.38 | 1.52 | PPPN092GFNP | |
| | 56 | 54.00 | 56.00 | S2206-28-ND | 7.98 | 6.61 | 4.22 | PPPN282GFNP | |
| | 80 | 78.00 | 80.00 | S2206-40-ND | 11.39 | 9.44 | 6.03 | PPPN402GFNP | |
| Dual Row Receptacles (Top Entry Low Profile), SMT, with Locating Peg — RoHS Compliant | | | | | | | | | |
| 12 | 10 | 8.00 | 10.00 | S6013-05-ND | 1.73 | 1.44 | .92 | NPPN052GFNP-RC | |
| | 12 | 10.00 | 12.00 | S6013-06-ND | 1.73 | 1.44 | .92 | NPPN062GFNP-RC | |
| | 14 | 12.00 | 14.00 | S6013-07-ND | 1.93 | 1.60 | 1.02 | NPPN072GFNP-RC | |
| | 16 | 14.00 | 16.00 | S6013-08-ND | 2.17 | 1.79 | 1.15 | NPPN082GFNP-RC | |
| | 18 | 16.00 | 18.00 | S6013-09-ND | 2.36 | 1.96 | 1.25 | NPPN092GFNP-RC | |
| | 20 | 18.00 | 20.00 | S6013-10-ND | 2.48 | 2.05 | 1.31 | NPPN102GFNP-RC | |
| | 24 | 22.00 | 24.00 | S6013-12-ND | 2.83 | 2.35 | 1.50 | NPPN122GFNP-RC | |
| | 30 | 28.00 | 30.00 | S6013-15-ND | 3.53 | 2.93 | 1.87 | NPPN152GFNP-RC | |
| | 36 | 34.00 | 36.00 | S6013-18-ND | 4.08 | 3.39 | 2.16 | NPPN182GFNP-RC | |
| | 44 | 42.00 | 44.00 | S6013-22-ND | 4.99 | 4.14 | 2.64 | NPPN222GFNP-RC | |
| | 56 | 54.00 | 56.00 | S6013-28-ND | 6.36 | 5.28 | 3.37 | NPPN282GFNP-RC | |
| | 60 | 58.00 | 60.00 | S6013-30-ND | 6.83 | 5.67 | 3.62 | NPPN302GFNP-RC | |
| 70 | 68.00 | 70.00 | S6013-35-ND | 7.66 | 6.35 | 4.05 | NPPN352GFNP-RC | | |
| 80 | 78.00 | 80.00 | S6013-40-ND | 8.76 | 7.26 | 4.63 | NPPN402GFNP-RC | | |
| Dual Row Receptacles (Top Entry Low Profile), SMT, without Locating Peg | | | | | | | | | |
| 12 | 18 | 16.00 | 18.00 | S2207-09-ND | 2.87 | 2.38 | 1.52 | PPPN092GFNS | |
| | 30 | 28.00 | 30.00 | S2207-15-ND | 4.37 | 3.62 | 2.31 | PPPN152GFNS | |
| | 44 | 42.00 | 44.00 | S2207-22-ND | 6.41 | 5.31 | 3.39 | PPPN222GFNS | |
| | 56 | 54.00 | 56.00 | S2207-28-ND | 7.98 | 6.61 | 4.22 | PPPN282GFNS | |
| 60 | 58.00 | 60.00 | S2207-30-ND | 8.56 | 7.10 | 4.53 | PPPN302GFNS | | |

A

| Fig. | Circuits | Dimensions - mm | | Digi-Key Part No. | Price Each | | | Sullins Part No. | |
|--|--|-----------------|-------|-------------------|-------------|------|------|------------------|----------------|
| | | A | B | | 1 | 10 | 100 | | |
| Dual Row Receptacles (Top Entry Low Profile), SMT, without Locating Peg | | | | | | | | | |
| RoHS Compliant | | | | | | | | | |
| 8 | 10 | 8.00 | 10.00 | S6014-04-ND | 1.41 | 1.18 | .75 | NPPN042GFNS-RC | |
| | 8 | 8.00 | 10.00 | S6014-05-ND | 1.73 | 1.44 | .92 | NPPN052GFNS-RC | |
| | 12 | 10.00 | 12.00 | S6014-06-ND | 1.73 | 1.44 | .92 | NPPN062GFNS-RC | |
| | 14 | 12.00 | 14.00 | S6014-07-ND | 1.93 | 1.60 | 1.02 | NPPN072GFNS-RC | |
| | 16 | 14.00 | 16.00 | S6014-08-ND | 2.17 | 1.79 | 1.15 | NPPN082GFNS-RC | |
| | 12 | 18 | 16.00 | 18.00 | S6014-09-ND | 2.36 | 1.96 | 1.25 | NPPN092GFNS-RC |
| | | 20 | 18.00 | 20.00 | S6014-10-ND | 2.48 | 2.05 | 1.31 | NPPN102GFNS-RC |
| | | 24 | 22.00 | 24.00 | S6014-12-ND | 2.83 | 2.35 | 1.50 | NPPN122GFNS-RC |
| | | 30 | 28.00 | 30.00 | S6014-15-ND | 3.53 | 2.93 | 1.87 | NPPN152GFNS-RC |
| | | 36 | 34.00 | 36.00 | S6014-18-ND | 4.08 | 3.39 | 2.16 | NPPN182GFNS-RC |
| | | 44 | 42.00 | 44.00 | S6014-22-ND | 4.99 | 4.14 | 2.64 | NPPN222GFNS-RC |
| | 8 | 56 | 54.00 | 56.00 | S6014-28-ND | 6.36 | 5.28 | 3.37 | NPPN282GFNS-RC |
| 60 | | 58.00 | 60.00 | S6014-30-ND | 6.83 | 5.67 | 3.62 | NPPN302GFNS-RC | |
| 80 | | 78.00 | 80.00 | S6014-40-ND | 8.76 | 7.26 | 4.63 | NPPN402GFNS-RC | |
| Dual Row Receptacles, Right Angle | | | | | | | | | |
| 13 | 22 | 20.00 | 22.50 | S2204-11-ND | 2.01 | 1.66 | 1.06 | PPPN112FJFN | |
| | 26 | 24.00 | 26.50 | S2204-13-ND | 2.36 | 1.96 | 1.25 | PPPN132FJFN | |
| | 28 | 26.00 | 28.50 | S2204-14-ND | 2.56 | 2.12 | 1.35 | PPPN142FJFN | |
| | 34 | 32.00 | 34.50 | S2204-17-ND | 2.87 | 2.38 | 1.52 | PPPN172FJFN | |
| | 38 | 36.00 | 38.50 | S2204-19-ND | 3.19 | 2.64 | 1.69 | PPPN192FJFN | |
| Dual Row Receptacles, Right Angle — RoHS Compliant | | | | | | | | | |
| 13 | 6 | 4.00 | 6.50 | S5753-03-ND | 1.54 | 1.27 | .81 | PPPN032FJFN-RC | |
| | 8 | 6.00 | 8.50 | S5753-04-ND | 1.96 | 1.63 | 1.04 | PPPN042FJFN-RC | |
| | 10 | 8.00 | 10.50 | S5753-05-ND | 2.24 | 1.86 | 1.19 | PPPN052FJFN-RC | |
| | 12 | 10.00 | 12.50 | S5753-06-ND | 2.67 | 2.22 | 1.42 | PPPN062FJFN-RC | |
| | 14 | 12.00 | 14.50 | S5753-07-ND | 2.67 | 2.22 | 1.42 | PPPN072FJFN-RC | |
| | 16 | 14.00 | 16.50 | S5753-08-ND | 2.91 | 2.41 | 1.54 | PPPN082FJFN-RC | |
| | 18 | 16.00 | 18.50 | S5753-09-ND | 3.06 | 2.54 | 1.62 | PPPN092FJFN-RC | |
| | 20 | 18.00 | 20.50 | S5753-10-ND | 3.46 | 2.87 | 1.83 | PPPN102FJFN-RC | |
| | 22 | 20.00 | 22.50 | S5753-11-ND | 3.77 | 3.13 | 2.00 | PPPN112FJFN-RC | |
| | 24 | 22.00 | 24.50 | S5753-12-ND | 3.93 | 3.26 | 2.08 | PPPN122FJFN-RC | |
| | 26 | 24.00 | 26.50 | S5753-13-ND | 4.37 | 3.62 | 2.31 | PPPN132FJFN-RC | |
| | 28 | 26.00 | 28.50 | S5753-14-ND | 4.68 | 3.88 | 2.48 | PPPN142FJFN-RC | |
| | 30 | 28.00 | 30.50 | S5753-15-ND | 4.76 | 3.94 | 2.52 | PPPN152FJFN-RC | |
| | 32 | 30.00 | 32.50 | S5753-16-ND | 5.26 | 4.37 | 2.79 | PPPN162FJFN-RC | |
| | 34 | 32.00 | 34.50 | S5753-17-ND | 5.54 | 4.59 | 2.93 | PPPN172FJFN-RC | |
| | 36 | 34.00 | 36.50 | S5753-18-ND | 5.89 | 4.89 | 3.12 | PPPN182FJFN-RC | |
| | 38 | 36.00 | 38.50 | S5753-19-ND | 6.25 | 5.18 | 3.31 | PPPN192FJFN-RC | |
| | Quad Row Headers, Straight — RoHS Compliant | | | | | | | | |
| 14 | 24 | 10.00 | 12.00 | S5804-06-ND | 9.13 | 7.92 | 6.70 | PRPN064RCCN-RC | |
| | 40 | 18.00 | 20.00 | S5804-10-ND | 10.39 | 9.01 | 7.63 | PRPN104RCCN-RC | |
| | 48 | 22.00 | 24.00 | S5804-12-ND | 11.02 | 9.56 | 8.09 | PRPN124RCCN-RC | |
| | 60 | | | | | | | | |