


AMP PIDG Spade Terminals



PIDG (Pre-Insulated Diamond Grip) Terminals: Meet or exceed the requirements of MIL-T-7928, Type II, Class 1 and 2. Product Facts: Temperature Rating: 105°C maximum. AMP Wire: Solid or Stranded. Terminal Material: The basic terminal is conducted of fine grade high conductivity copper per ASTM B-152 and tin-plated per MIL-T-10727. Basic material for Spring Spade Tongue Terminals is phosphor bronze per ASTM B-139 and tin-plated per MIL-T-10727. AMP's special plating process creates durable corrosion resistance to salt spray and most chemical fumes. Copper Sleeve: The specially designed copper sleeve, fitted over the terminal barrel, provides circumferential insulation support to the wire and allows the wire to be bent in any direction, without fraying the wire's insulation or breaking the conductor. Nylon Insulation (unless otherwise noted): Nylon sleeve assures high dielectric strength.



A

PIDG Spade Tongue

Table with columns: Fig., AWG, Stud Size, Dim. - Inch W x L, Ins. Dia. Inch, Digi-Key Part No., Price Each 10 100, AMP Part No., Digi-Key Part No., Cut Tape Pricing 500 1,000, Digi-Key Part No., Tape and Reel Qty. Pricing, AMP Part No.

PIDG Spring Spade Tongue

Table with columns: Fig., AWG, Stud Size, Dim. - Inch W x L, Ins. Dia. Inch, Digi-Key Part No., Price Each 10 100, AMP Part No., Digi-Key Part No., Cut Tape Pricing 500 1,000, Digi-Key Part No., Tape and Reel Qty. Pricing, AMP Part No. Includes sub-sections for Short and Long.

PIDG Flanged Spade Tongue

Table with columns: Fig., AWG, Stud Size, Dim. - Inch W x L, Ins. Dia. Inch, Digi-Key Part No., Price Each 10 100, AMP Part No., Digi-Key Part No., Cut Tape Pricing 500 1,000, Digi-Key Part No., Tape and Reel Qty. Pricing, AMP Part No.

Tools

Table listing tools: A9996-ND PRO-CRIMPER II™ Hand Tool without Dies \$50.90, A9991-ND Die Set for Insulated Terminals, use with A9996 \$55.75, A9811-ND Crimp Tool, Insulated Terminals with Die Set \$101.80

Table listing terminal kits: A9821-ND PIDG and PLASTI-GRIP™ Connector Kit (includes hand tool A9811-ND, 225 insulated ring and spade terminals in 12-10, 16-14 and 22-16 AWG wire sizes) \$173.51, A30572-ND Universal Crimp Tool, 22-10 AWG, Insulated/Non-Insulated Terminals and Splices \$46.12, A30573-ND Universal Crimp Tool, 22-10 AWG, Insulated Terminals and Splices \$43.80, A30574-ND Universal Crimp Tool, 22-10 AWG, Insulated/Non-Insulated Terminals, Splices, and Tab-Lok FASTON Flag Terminals \$102.85

Free shipping on orders over \$200 CAD! All prices in Canadian dollars and include duty and brokerage fees.

1-800-344-4539 • www.digikey.ca • 218-681-6674 • Fax: 218-681-3380

(CA2011) 389