



Fig.	Color	Digi-Key Part No.	Pricing					Johnson Part No.	
Tip Jacks - for Standard Tip Plug: 2.03mm									
1	White	J330-ND	1.43	12.71	100.64	211.86	397.24	688.56	105-1041-001
	Red	J124-ND	1.43	12.71	100.64	211.86	397.24	688.56	105-1042-001
	Black	J125-ND	1.43	12.71	100.64	211.86	397.24	688.56	105-1043-001
	Green	J331-ND	1.43	12.71	100.64	211.86	397.24	741.52	105-1044-001
	Yellow	J333-ND	1.43	12.71	100.64	211.86	397.24	688.56	105-1047-001
Horizontal Test Jacks - for Standard Tip Plug: 2.03mm									
2	White	J108-ND	.52	4.56	36.03	75.86	142.23	246.54	105-0751-001
	Red	J109-ND*	.52	4.56	36.03	75.86	142.23	246.54	105-0752-001
	Black	J110-ND*	.52	4.56	36.03	75.86	142.23	246.54	105-0753-001
	Green	J111-ND	.52	4.56	36.03	75.86	142.23	246.54	105-0754-001
	Orange	J112-ND	.52	4.56	36.03	75.86	142.23	246.54	105-0756-001
	Yellow	J113-ND	.52	4.56	36.03	75.86	142.23	246.54	105-0757-001
	Brown	J114-ND	.52	4.56	36.03	75.86	142.23	246.54	105-0758-001
	Blue	J115-ND	.52	4.56	36.03	75.86	142.23	246.54	105-0760-001
	White	J116-ND	.52	4.56	36.03	75.86	142.23	246.54	105-0762-001
	Horizontal Insulated Miniature Test Jacks - for Standard Tip Plug: 2.03mm								
	3	White	J575-ND	.50	4.44	35.18	74.06	138.87	240.70
Red		J576-ND	.50	4.44	35.18	74.06	138.87	240.70	105-1102-001
Black		J577-ND	.50	4.44	35.18	74.06	138.87	240.70	105-1103-001
Green		J578-ND	.50	4.44	35.18	74.06	138.87	240.70	105-1104-001
Yellow		J579-ND	.50	4.44	35.18	74.06	138.87	240.70	105-1107-001
Blue	J580-ND	.50	4.44	35.18	74.06	138.87	240.70	105-1110-001	
Vertical Test Jacks - for Standard Tip Plug: 2.03mm									
4	White	J119-ND	.77	6.89	54.58	114.91	215.45	373.45	105-0851-001
	Red	J120-ND	.77	6.89	54.58	114.91	215.45	373.45	105-0852-001
	Black	J121-ND	.77	6.89	54.58	114.91	215.45	373.45	105-0853-001
	Green	J122-ND	.77	6.89	54.58	114.91	215.45	373.45	105-0854-001
	Yellow	J123-ND	.77	6.89	54.58	114.91	215.45	373.45	105-0857-001
	Blue	J312-ND	.77	6.89	54.58	114.91	215.45	373.45	105-0860-001
	Vertical Insulated Formed Contact Test Jacks - for Standard Tip Plug: 2.03mm								
5	White	J581-ND	.70	6.22	49.25	103.69	194.41	336.98	105-2201-201
	Red	J582-ND	.70	6.22	49.25	103.69	194.41	336.98	105-2202-201
	Black	J583-ND	.70	6.22	49.25	103.69	194.41	336.98	105-2203-201
	Green	J584-ND	.70	6.22	49.25	103.69	194.41	336.98	105-2204-201
	Yellow	J585-ND	.70	6.22	49.25	103.69	194.41	336.98	105-2207-201
Shielded Test Jack - Horizontal									
6	Tin	J463-ND	5.58	49.53	392.09	825.46	1547.74	2682.75	129-0701-301
	Gold	J571-ND	6.65	59.12	468.00	985.26	1847.36	3202.08	129-0701-302
Shielded Test Jack - Vertical									
7	Tin	J462-ND	6.05	53.75	425.57	895.93	1679.87	2911.78	129-0701-201
	Gold	J570-ND	5.32	47.27	374.18	787.76	1477.04	2560.21	129-0701-202

Fig.	Color	Digi-Key Part No.	Pricing					Johnson Part No.	
Tip Jacks - Insulated Deluxe: 2.00mm									
8	White	J105-ND	1.49	13.31	105.33	221.74	415.76	720.65	105-0601-001
	Red	J106-ND	1.49	13.31	105.33	221.74	415.76	720.65	105-0602-001
	Black	J107-ND	1.49	13.31	105.33	221.74	415.76	720.65	105-0603-001
	Green	J337-ND	1.49	13.31	105.33	221.74	415.76	720.65	105-0604-001
	Yellow	J338-ND	1.49	13.31	105.33	221.74	415.76	720.65	105-0607-001
Blue	J339-ND	1.49	13.31	105.33	221.74	415.76	720.65	105-0610-001	
Tip Jacks - Insulated Standard Type: 2.00mm									
9	White	J320-ND	.86	7.68	60.76	127.93	239.86	415.76	105-0801-001
	Red	J117-ND*	.86	7.68	60.76	127.93	239.86	415.76	105-0802-001
	Black	J118-ND*	.86	7.68	60.76	127.93	239.86	415.76	105-0803-001
	Green	J321-ND	.86	7.68	60.76	127.93	239.86	415.76	105-0804-001
	Yellow	J323-ND	.86	7.68	60.76	127.93	239.86	415.76	105-0807-001
Blue	J325-ND	.86	7.68	60.76	127.93	239.86	415.76	105-0810-001	
Tip Jacks with Sleeve Assembly: 2.00mm									
10	Red	J451-ND	1.78	15.83	125.37	263.93	494.87	857.78	105-0702-001
	Black	J452-ND	1.78	15.83	125.37	263.93	494.87	857.78	105-0703-001
Tip Plugs - Insulated Solderless Type: 2.00mm									
11	White	J300-ND	1.04	9.24	73.13	153.96	288.68	500.37	105-0301-001
	Red	J103-ND*	1.04	9.24	73.13	153.96	288.68	500.37	105-0302-001
	Black	J104-ND*	1.04	9.24	73.13	153.96	288.68	500.37	105-0303-001
	Green	J301-ND	1.04	9.24	73.13	153.96	288.68	500.37	105-0304-001
	Blue	J305-ND	1.04	9.24	73.13	153.96	288.68	500.37	105-0310-001
Miniature Banana Plugs - Insulated Solder Type: 2.64mm									
12	Red	J457-ND	2.06	18.34	145.20	305.68	573.14	993.45	108-1002-001
	Black	J458-ND	2.06	18.34	145.20	305.68	573.14	993.45	108-1003-001
13	—	J147-ND*	1.66	14.73	116.63	245.53	460.37	797.97	108-0740-001
Uninsulated w/Knurled Thumb Nut for Standard Banana Plug 4.44mm Across Flats									
14	—	J587-ND	3.20	28.41	224.94	473.55	887.91	1539.04	111-2223-001
Binding Posts - Insulated Standard: 4.44mm									
15	White	J370-ND	2.69	23.91	189.33	398.59	747.36	1295.42	111-0101-001
	Red	J164-ND*	2.69	23.91	189.33	398.59	747.36	1295.42	111-0102-001
	Black	J165-ND*	2.69	23.91	189.33	398.59	747.36	1295.42	111-0103-001
	Green	J371-ND	2.91	25.80	204.26	430.01	806.27	1397.54	111-0104-001
	Yellow	J372-ND	2.69	23.91	189.33	398.59	747.36	1295.42	111-0107-001
Banana Jacks - Insulated Solder Terminal: 4.44mm									
16	White	J150-ND*	.66	5.90	46.69	98.30	184.31	319.48	108-0901-001
	Red	J151-ND*	.66	5.90	46.69	98.30	184.31	319.48	108-0902-001
	Black	J152-ND*	.66	5.90	46.69	98.30	184.31	319.48	108-0903-001
	Green	J153-ND	.74	6.54	51.81	109.07	204.51	354.49	108-0904-001
	Orange	J356-ND	.66	5.90	46.69	98.30	184.31	319.48	108-0906-001
	Yellow	J154-ND	.66	5.90	46.69	98.30	184.31	319.48	108-0907-001
	Brown	J357-ND	.74	6.54	51.81	109.07	204.51	354.49	108-0908-001
	Blue	J155-ND	.66	5.90	46.69	98.30	184.31	319.48	108-0910-001
	Violet	J358-ND	.74	6.54	51.81	109.07	204.51	354.49	108-0912-001
	Gray	J359-ND	.66	5.90	46.69	98.30	184.31	319.48	108-0913-001
	Banana Plug - Uninsulated Panel Mount Threaded Stud: 4.23mm								
17	—	J148-ND	1.75	15.60	123.45	259.89	487.30	844.65	108-0750-001
Banana Plug - Uninsulated Panel Mount Screw Type: 4.23mm									
18	—	J149-ND	1.50	13.41	106.18	223.53	419.13	726.49	108-0753-001
Banana Plugs - Insulated Solderless Tapered Handle: 4.23mm									
19	White	J144-ND*	1.40	12.47	98.72	207.82	389.67	675.43	108-0301-001
	Red	J145-ND*	1.40	12.47	98.72	207.82	389.67	675.43	108-0302-001
	Black	J146-ND*	1.40	12.47	98.72	207.82	389.67	675.43	108-0303-001
	Green	J340-ND	1.40	12.47	98.72	207.82	389.67	675.43	108-0304-001
	Orange	J341-ND	1.40	12.47	98.72	207.82	389.67	675.43	108-0306-001
	Yellow	J342-ND	1.40	12.47	98.72	207.82	389.67	675.43	108-0307-001
	Brown	J343-ND	1.40	12.47	98.72	207.82	389.67	675.43	108-0308-001
	Blue	J344-ND	1.40	12.47	98.72	207.82	389.67	675.43	108-0310-001
	Violet	J345-ND	1.40	12.47	98.72	207.82	389.67	675.43	108-0312-001
	Gray	J346-ND	1.40	12.47	98.72	207.82	389.67	675.43	108-0313-001
Banana Plugs - Insulated Round Body Solder Stud: 4.23mm									
20	Red	J156-ND	2.82	25.05	198.29	417.44	782.71	1356.69	108-1722-101
	Black	J157-ND	2.82	25.05	198.29	417.44	782.71	1356.69	108-1723-101
Banana Plugs - Insulated Round Body Solderless: 4.23mm									
20	Red	J158-ND	2.14	19.04	150.74	317.35	595.03	1031.38	108-1722-103
	Black	J159-ND	2.14	19.04	150.74	317.35	595.03	1031.38	108-1723-103
Banana Plugs - Insulated Stacking Single Type: 4.23mm									
21	White	J459-ND	2.33	20.74	164.17	345.63	648.05	1123.28	108-1081-001
	Red	J460-ND	2.33	20.74	164.17	345.63	648.05	1123.28	108-1082-001
	Black	J461-ND	2.33	20.74	164.17	345.63	648.05	1123.28	108-1083-001

J100-KIT-ND Digi-Key® Plug & Jack Kit Contains 10 each of the plugs or jacks as denoted (*) on chart. Price includes compartment divided plastic box for easy storage and quick access.....\$78.50



Free shipping on orders over \$200 CAD! All prices in Canadian dollars and include duty and brokerage fees.

1-800-344-4539 • www.digikey.ca • 218-681-6674 • Fax: 218-681-3380

(CA2011) 437