



Fig.	Mates With	Dia. (mm)	Digi-Key Part No.	Price Each			CUI Part No.
				1	10	100	
65B	SP-3501	3.5	CP-3524SJCT-ND- <b>✦</b>	1.01	.88	.68	SJ-3524-SMT
	SP-3501	3.5	CP-3524SJTR-ND- <b>✦</b>	503.29	1,000		SJ-3524-SMT
65C	SP-3501	3.5	CP-3524SJBCET-ND- <b>✦</b> <b>NEW!</b>	1.27	1.23	1.11	SJ-3524-SMT-BE
	SP-3501	3.5	CP-3524SJBETR-ND- <b>✦</b> <b>NEW!</b>	636.26	1,000		SJ-3524-SMT-BE
	SP-3501	3.5	CP-3524SJGRCT-ND- <b>✦</b> <b>NEW!</b>	1.27	1.23	1.11	SJ-3524-SMT-GR
	SP-3501	3.5	CP-3524SJGRTR-ND- <b>✦</b> <b>NEW!</b>	636.26	1,000		SJ-3524-SMT-GR
	SP-3501	3.5	CP-3524SJPICCT-ND- <b>✦</b> <b>NEW!</b>	1.27	1.23	1.11	SJ-3524-SMT-PI
66A	SP-3501	3.5	CP-3524SJPITR-ND- <b>✦</b> <b>NEW!</b>	636.26	1,000		SJ-3524-SMT-PI
	SP-3501	3.5	CP1-3533N-ND- <b>✦</b>	.89	.77	.59	SJ1-3533N
66B	SP-3501	3.5	CP1-3533NG-ND- <b>✦</b>	.66	.58	.45	SJ1-3533NG
	SP-3501	3.5	CP1-3533NS-ND- <b>✦</b>	.86	.75	.58	SJ1-3533NS
	SP-3501	3.5	CP1-3534NG-ND- <b>✦</b>	.70	.60	.47	SJ1-3534NG
66C	SP-3501	3.5	CP1-3534NS-ND- <b>✦</b>	1.26	1.09	.84	SJ1-3534NS
	SP-3501	3.5	CP1-3534NS-ND- <b>✦</b>	.88	.76	.59	SJ1-3534NS
66D	SP-3501	3.5	CP1-3535N-ND- <b>✦</b>	.90	.78	.60	SJ1-3535N
	SP-3501	3.5	CP1-3535NG-ND- <b>✦</b>	.71	.61	.47	SJ1-3535NG
	SP-3501	3.5	CP1-3535NS-ND- <b>✦</b>	.70	.61	.47	SJ1-3535NS
67	SP-3501	3.5	CP1-3535NG-BE-ND- <b>✦</b> <b>NEW!</b>	.88	.76	.59	SJ1-3535NG-BE
	SP-3501	3.5	CP1-3535NG-GR-ND- <b>✦</b> <b>NEW!</b>	.88	.76	.59	SJ1-3535NG-GR
68A	SP-3501	3.5	CP1-3535NG-PI-ND- <b>✦</b> <b>NEW!</b>	.88	.76	.59	SJ1-3535NG-PI
	SP-3501	3.5	CP-351133-ND- <b>✦</b>	1.87	1.63	1.26	SJD-3511-33
68B	SP-3501	3.5	CP-351145-ND- <b>✦</b>	1.77	1.54	1.18	SJD-3511-45
	SP-3501	3.5	CP-351033-ND- <b>✦</b>	1.60	1.39	1.07	SJD-3510-33
69A	SP-3501	3.5	CP-351233-ND- <b>✦</b>	1.87	1.63	1.26	SJD-3512-33
	SP-3501	3.5	CP-351045-ND- <b>✦</b>	1.67	1.45	1.12	SJD-3510-45
69B	SP-3501	3.5	CP-351245-ND- <b>✦</b>	2.04	1.77	1.37	SJD-3512-45
	SP-3501	3.5	CP1-3543N-ND- <b>✦</b>	1.12	.97	.75	SJ1-3543N
70A	SP-3501	3.5	CP1-3543N-ND- <b>✦</b>	.92	.80	.62	SJ1-3543N
	SP-3501	3.5	CP1-3544N-ND- <b>✦</b>	1.12	.98	.75	SJ1-3544N
70B	SP-3501	3.5	CP1-3544N-ND- <b>✦</b>	.92	.80	.62	SJ1-3544N
	SP-3501	3.5	CP1-3545N-ND- <b>✦</b>	.93	.81	.62	SJ1-3545N
70C	SP-3501	3.5	CP1-3545N-ND- <b>✦</b>	.56	.49	.38	SJ1-3545N
	SP-3501	3.5	CP1-3546N-ND- <b>✦</b>	.58	.51	.39	SJ1-3546N
71A	SP-3501	3.5	CP1-3546N-ND- <b>✦</b>	.59	.52	.40	SJ1-3546N
	SP-3501	3.5	CP1-3555NG-BE-ND- <b>✦</b> <b>NEW!</b>	.80	.69	.53	SJ1-3555NG-BE
71C	SP-3501	3.5	CP1-3555NG-GR-ND- <b>✦</b> <b>NEW!</b>	.80	.69	.53	SJ1-3555NG-GR
	SP-3501	3.5	CP1-3555NG-PI-ND- <b>✦</b> <b>NEW!</b>	.80	.69	.53	SJ1-3555NG-PI
72A	CA-254S or CA-254S-M/M	2.5	CP1-42514-ND	.80	.70	.54	SJ1-42514
	CA-254S or CA-254S-M/M	2.5	CP-42515RS-ND	1.18	1.03	.79	SJ-42515RS
72B	CA-254S or CA-254S-M/M	2.5	CP1-42515RS-ND	.83	.72	.55	SJ1-42515RS
	CA-254S or CA-254S-M/M	2.5	CP-42515TS-ND	1.18	1.03	.79	SJ-42515TS
72C	CA-254S or CA-254S-M/M	2.5	CP1-42515TS-ND	.83	.72	.55	SJ1-42515TS
	CA-254S or CA-254S-M/M	2.5	CP1-42516-ND- <b>✦</b>	.85	.74	.57	SJ1-42516

Fig.	Mates With	Dia. (mm)	Digi-Key Part No.	Price Each			CUI Part No.
				1	10	100	
73A	CA-254S or CA-254S-M/M	2.5	CP1-42514SJCT-ND- <b>✦</b>	.90	.78	.60	SJ1-42514-SMT
	CA-254S or CA-254S-M/M	2.5	CP1-42514SJTR-ND- <b>✦</b>	449.43	1,000		SJ1-42514-SMT
73B	CA-254S or CA-254S-M/M	2.5	CP-42515RSSJTR-ND- <b>✦</b>	589.13	1,000		SJ-42515RS-SMT
	CA-254S or CA-254S-M/M	2.5	CP-42515RSSJCT-ND- <b>✦</b>	1.18	1.03	.79	SJ-42515RS-SMT-1
	CA-254S or CA-254S-M/M	2.5	CP1-42515RSSJTR-ND- <b>✦</b>	.93	.81	.62	SJ1-42515RS-SMT
73C	CA-254S or CA-254S-M/M	2.5	CP-42515RSSJCT-ND- <b>✦</b>	462.89	1,000		SJ-42515RS-SMT
	CA-254S or CA-254S-M/M	2.5	CP-42515TSSJTR-ND- <b>✦</b>	589.13	1,000		SJ-42515TS-SMT
73D	CA-254S or CA-254S-M/M	2.5	CP1-42515TSSJCT-ND- <b>✦</b>	1.18	1.03	.79	SJ-42515TS-SMT-1
	CA-254S or CA-254S-M/M	2.5	CP1-42515TSSJTR-ND- <b>✦</b>	.93	.81	.62	SJ1-42515TS-SMT
	CA-254S or CA-254S-M/M	2.5	CP1-42516SJTCT-ND- <b>✦</b>	462.89	1,000		SJ1-42516-SMT
74A	CA-254S or CA-254S-M/M	2.5	CP1-42534SJTCT-ND- <b>✦</b>	97	.84	.64	SJ1-42534-SMT
	CA-254S or CA-254S-M/M	2.5	CP1-42534SJTR-ND- <b>✦</b>	479.72	1,000		SJ1-42534-SMT
74B	CA-254S or CA-254S-M/M	2.5	CP1-42535RSSJCT-ND- <b>✦</b>	.99	.86	.66	SJ1-42535RS-SMT
	CA-254S or CA-254S-M/M	2.5	CP-42535TSSJTR-ND- <b>✦</b>	656.46	1,000		SJ-42535TS-SMT
	CA-254S or CA-254S-M/M	2.5	CP-42535TSSJCT-ND- <b>✦</b>	1.18	1.14	.88	SJ-42535TS-SMT-1
74C	CA-254S or CA-254S-M/M	2.5	CP1-42535TSSJCT-ND- <b>✦</b>	.99	.86	.66	SJ1-42535TS-SMT
	CA-254S or CA-254S-M/M	2.5	CP1-42535TSSJTR-ND- <b>✦</b>	493.19	1,000		SJ1-42535TS-SMT
	CA-254S or CA-254S-M/M	2.5	CP-42536SJ-ND	1.35	1.17	.90	SJ-42536-SMT-1
74D	CA-254S or CA-254S-M/M	2.5	CP1-42536SJTCT-ND- <b>✦</b>	1.01	.88	.68	SJ1-42536-SMT
	CA-254S or CA-254S-M/M	2.5	CP1-42536SJTR-ND- <b>✦</b>	504.97	1,000		SJ1-42536-SMT
75	CA-354S or CA-354S-M/M	3.5	CP5-43502PM-ND- <b>✦</b>	2.46	2.18	1.64	SJ5-43502PM
76A	CA-354S or CA-354S-M/M	3.5	CP-43514-ND- <b>✦</b>	1.01	.88	.68	SJ-43514
	CA-354S or CA-354S-M/M	3.5	CP-43515TS-ND- <b>✦</b>	1.04	.91	.70	SJ-43515TS
77A	CA-354S or CA-354S-M/M	3.5	CP-43514SJCT-ND- <b>✦</b>	.77	.68	.52	SJ-43514-SMT
	CA-354S or CA-354S-M/M	3.5	CP-43514SJTR-ND- <b>✦</b>	387.15	1,000		SJ-43514-SMT
77B	CA-354S or CA-354S-M/M	3.5	CP-43515RSSJCT-ND- <b>✦</b>	80	.69	.53	SJ-43515RS-SMT
	CA-354S or CA-354S-M/M	3.5	CP-43515RSSJTR-ND- <b>✦</b>	395.56	1,000		SJ-43515RS-SMT
77C	CA-354S or CA-354S-M/M	3.5	CP-43515TSSJCT-ND- <b>✦</b>	80	.69	.53	SJ-43515TS-SMT
	CA-354S or CA-354S-M/M	3.5	CP-43515TSSJTR-ND- <b>✦</b>	395.56	1,000		SJ-43515TS-SMT
77D	CA-354S or CA-354S-M/M	3.5	CP-43516SJTCT-ND- <b>✦</b>	.81	.70	.54	SJ-43516-SMT
	CA-354S or CA-354S-M/M	3.5	CP-43516SJTR-ND- <b>✦</b>	403.98	1,000		SJ-43516-SMT
78	CA-354S or CA-354S-M/M	3.5	CP-43516SJBCT-ND- <b>✦</b> <b>NEW!</b>	1.02	.99	.89	SJ-43516-SMT-BE
	CA-354S or CA-354S-M/M	3.5	CP-43516SJBETR-ND- <b>✦</b> <b>NEW!</b>	508.34	1,000		SJ-43516-SMT-BE
	CA-354S or CA-354S-M/M	3.5	CP-43516SJGRCT-ND- <b>✦</b> <b>NEW!</b>	1.02	.99	.89	SJ-43516-SMT-GR
	CA-354S or CA-354S-M/M	3.5	CP-43516SJGRTR-ND- <b>✦</b> <b>NEW!</b>	508.34	1,000		SJ-43516-SMT-GR
	CA-354S or CA-354S-M/M	3.5	CP-43516SJPICCT-ND- <b>✦</b> <b>NEW!</b>	1.02	.99	.89	SJ-43516-SMT-PI
79	CA-356CS or CA-356CS-M/M	3.5	CP-43516SJPITR-ND- <b>✦</b> <b>NEW!</b>	508.34	1,000		SJ-43516-SMT-PI
	CA-356CS or CA-356CS-M/M	3.5	CP-63516-ND- <b>✦</b>	1.41	1.23	.95	SJ-63516
80	CA-356CS or CA-356CS-M/M	2.5	CP-2501SP-ND- <b>✦</b>	1.08	.94	.72	SP-2501

▲ Threaded with nut ★ Non-threaded ▼ Shielded version ✦ Cut Tape ☆ Tape and Reel ◆ RoHS Compliant (Continued)

Digi-Reel® Most SMT cutdown parts are available on a Digi-Reel®. For Digi-Reel part number, change 1-ND to 6-ND or CT-ND to DKR-ND. See Digi-Key® Services on page 2 for additional information.

Free shipping on orders over \$200 CAD! All prices in Canadian dollars and include duty and brokerage fees.

1-800-344-4539 • www.digikey.ca • 218-681-6674 • Fax: 218-681-3380 (CA2011) 501