

ANALOG DEVICES		DigiKey Reel® (Cont.)		POWER MANAGEMENT			
Digi-Key Part No.	Description	Pkg.	Price Each*				
			1	25	100		
ADR443BRZ-ND	3V, LDO XFET® Voltage Reference*	8-SOIC	7.86	6.29	5.31		
ADR444ARMZ-ND	4.096V, LDO XFET® Voltage Reference*	8-MSOP	6.01	4.82	4.06		
ADR444ARZ-ND	4.096V, LDO XFET® Reference*	8-SOIC	5.68	4.55	3.84		
ADR444BRZ-ND	4.096V, LDO XFET® Voltage Reference*	8-SOIC	7.86	6.29	5.31		
ADR445ARMZ-ND	5V, LDO XFET® Voltage Reference*	8-MSOP	6.01	4.82	4.06		
ADR445ARZ-ND	5V, LDO XFET® Voltage Reference*	8-SOIC	5.68	4.55	3.84		
ADR445BRZ-ND	5V, LDO XFET® Voltage Reference*	8-SOIC	7.86	6.29	5.31		
ADR5044ARTZ-REEL7CT-ND	4.096V Precision Reference Shunt*	SOT-23-3	1.01	.85	.68		
ADR5044ARTZ-REEL7TR-ND	4.096V Precision Reference Shunt*	SOT-23-3	1312.93/3,000				
ADR510ARTZ-REEL7CT-ND	1V, Precision Reference Shunt*	SOT-23-3	1.72	1.37	1.03		
ADR510ARTZ-REEL7TR-ND	1V, Precision Reference Shunt*	SOT-23-3	2628.55/3,000				
ADR512ARTZ-REEL7CT-ND	1.2V, Precision Reference Shunt*	SOT-23-3	1.49	1.19	.90		
ADR512ARTZ-REEL7TR-ND	1.2V, Precision Reference Shunt*	SOT-23-3	2283.82/3,000				
ADR520ARTZ-REEL7CT-ND	Voltage Reference Shunt 2.048V*	SOT-23	1.41	1.18	.95		
ADR520ARTZ-REEL7TR-ND	Voltage Reference Shunt 2.048V*	SOT-23	1838.10/3,000				
ADR525ARTZ-REEL7CT-ND	Voltage Reference Shunt 2.5V	SOT-23	2.22	1.78	1.33		
ADR525ARTZ-REEL7TR-ND	Voltage Reference Shunt 2.5V	SOT-23	162.17/3,000				
ADR525ARTZ-REEL7CT-ND	Voltage Reference Shunt 2.5V*	SOT-23-3	1.45	1.21	.97		
ADR525ARTZ-REEL7TR-ND	Voltage Reference Shunt 2.5V*	SOT-23-3	1881.86/3,000				
ADR525BKSZ-REEL7CT-ND	Voltage Reference Shunt 2.5V*	SC-70-3	2.47	1.98	1.49		
ADR525BKSZ-REEL7TR-ND	Voltage Reference Shunt 2.5V*	SC-70-3	1881.86/3,000				
ADR525BRTZ-REEL7CT-ND	Voltage Reference Shunt 2.5V*	SOT-23	2.28	1.82	1.37		
ADR525BRTZ-REEL7TR-ND	Voltage Reference Shunt 2.5V*	SOT-23	3490.37/3,000				
ADR530BKSZ-REEL7CT-ND	Voltage Reference Shunt 3.0V*	SC-70-3	2.47	1.98	1.49		
ADR530BKSZ-REEL7TR-ND	Voltage Reference Shunt 3.0V*	SC-70-3	3792.00/3,000				
ADR530BRTZ-REEL7CT-ND	Voltage Reference Shunt 3.0V*	SOT-23	2.28	1.82	1.37		
ADR530BRTZ-REEL7TR-ND	Voltage Reference Shunt 3.0V*	SOT-23	3490.37/3,000				
ADR550BRTZ-REEL7CT-ND	Voltage Reference Shunt 5.0V*	SOT-23	2.28	1.82	1.37		
ADR550BRTZ-REEL7TR-ND	Voltage Reference Shunt 5.0V*	SOT-23	3490.37/3,000				
ADR821ARMZ-REEL7CT-ND	2.5V, LP, Precision Reference and Op Amp*	10-MSOP	3.12	2.50	1.87		
ADR821BRMZ-REEL7CT-ND	2.5V, LP, Precision Reference and Op Amp*	10-MSOP	3.66	2.93	2.28		
ADR827ARMZ-REEL7CT-ND	1.25V, LP, Precision Reference and Op Amp*	10-MSOP	3.12	2.50	1.87		
ADR827BRMZ-REEL7CT-ND	1.25V, LP, Precision Reference and Op Amp*	10-MSOP	3.66	2.93	2.28		
ADR1581ARTZ-REEL7CT-ND	Voltage Reference Shunt 1.25V*	SOT-23-3	1.72	1.37	1.03		
ADR1581ARTZ-REEL7TR-ND	Voltage Reference Shunt 1.25V*	SOT-23-3	2628.55/3,000				
ADR5040ARTZ-REEL7CT-ND	Voltage Reference Shunt 2.048V*	SOT-23	1.01	.85	.68		
ADR5040ARTZ-REEL7TR-ND	Voltage Reference Shunt 2.048V*	SOT-23	1312.93/3,000				
ADR5041ARTZ-REEL7CT-ND	Voltage Reference Shunt 2.5V*	SOT-23	1.01	.85	.68		
ADR5041ARTZ-REEL7TR-ND	Voltage Reference Shunt 2.5V*	SOT-23	1312.93/3,000				
ADR5041BKSZ-REEL7CT-ND	Voltage Reference Shunt 2.5V*	SC70	1.62	1.35	1.08		
ADR5041BKSZ-REEL7TR-ND	Voltage Reference Shunt 2.5V*	SC70	2100.68/3,000				
REF01CPZ-ND	Precision Voltage Reference 10V*	8-Dip	2.83	2.27	1.76		
REF01CSZ-ND	Precision Voltage Reference 10V*	8-SOIC	2.73	2.19	1.70		
REF01EZ-ND	Precision Voltage Reference 10V*	8-CDIP	11.28	10.15	9.00		
REF01HFZ-ND	Precision Voltage Reference 10V*	8-Dip	4.32	3.48	2.83		
REF02AZ-ND	Prac. Voltage Reference/Temp. 5V Transducer*	8-CDIP	35.55	33.18	30.81		
REF02CPZ-ND	Precision Voltage Reference 5V*	8-Dip	2.83	2.27	1.76		
REF02CSZ-ND	Precision Voltage Reference 5V*	8-SOIC	2.73	2.19	1.70		
REF02EZAD1-ND	Precision Voltage Reference 5V*	8-CDIP	11.28	10.15	9.00		
REF02HFZ-ND	Precision Voltage Reference 5V*	8-Dip	4.32	3.48	2.89		
REF02HSZ-ND	Precision Voltage Reference 5V*	8-SOIC	4.80	3.84	2.99		
REF03GPZ-ND	Precision Voltage Reference 2.5V*	8-Dip	2.91	2.33	1.81		
REF03GSZ-ND	Precision Voltage Reference 2.5V*	8-SOIC	2.73	2.19	1.70		
REF43GPZ-ND	Precision Voltage Reference Low Power 2.5V*	8-Dip	8.64	6.92	5.84		
REF43GSZ-ND	Precision Voltage Reference Low Power 2.5V*	8-SOIC	8.64	6.92	5.84		
REF191ESZ-ND	Voltage Reference LDO 2.048V*	8-SOIC	5.63	4.51	3.51		
REF191GSZ-ND	Voltage Reference LDO 2.048V*	8-SOIC	5.13	2.51	1.95		
REF192ESZ-ND	Voltage Reference LDO 2.5V*	8-SOIC	5.63	4.51	3.51		
REF192FSZ-ND	Voltage Reference LDO 2.5V*	8-SOIC	4.37	3.50	2.72		
REF192GSZ-ND	Voltage Reference LDO 2.5V*	8-Dip	3.13	2.51	1.95		
REF192GRUZ-ND	Voltage Reference LDO 2.5V*	8-TSSOP	4.95	3.96	3.08		
REF192GRUZREEL7CT-ND	Voltage Reference LDO 2.5V*	8-TSSOP	4.95	3.96	3.08		
REF192GSZ-ND	Voltage Reference LDO 2.5V*	8-SOIC	3.13	2.51	1.95		
REF193GSZ-ND	Voltage Reference LDO 3V*	8-SOIC	3.13	2.51	1.95		
REF194ESZ-ND	Voltage Reference LDO 4.5V*	8-SOIC	5.13	4.11	3.19		
REF194GSZ-ND	Voltage Reference LDO 4.5V*	8-SOIC	3.13	2.51	1.95		
REF195ESZ-ND	Voltage Reference LDO 5V*	8-SOIC	5.13	4.11	3.19		
REF195FSZ-ND	Voltage Reference LDO 5V*	8-SOIC	3.96	3.18	2.47		
REF195FS-REELCT-ND	Voltage Reference LDO 5V*	8-SOIC	4.72	3.78	2.94		
REF195GPZ-ND	Voltage Reference LDO 5V*	8-Dip	2.85	2.29	1.78		
REF195GSZ-ND	Voltage Reference LDO 5V*	8-SOIC	3.13	2.51	1.95		
REF196GSZ-ND	Voltage Reference LDO 3.3V*	8-SOIC	3.13	2.51	1.95		
REF198ESZ-ND	Voltage Reference LDO 4.096V*	8-SOIC	5.63	4.51	3.51		
REF198FSZ-ND	Voltage Reference LDO 4.096V*	8-SOIC	4.37	3.50	2.72		
REF198GRUZ-ND	Voltage Reference LDO 4.096V*	8-TSSOP	4.95	3.96	3.08		
REF198GSZ-ND	Voltage Reference LDO 4.096V*	8-SOIC	3.13	2.51	1.95		

ANALOG DEVICES		DigiKey Reel® (Cont.)		SENSOR/SIGNAL CONDITIONING			
Digi-Key Part No.	Description	Pkg.	Price Each*				
			1	25	100		
ADE7758ARWZ-ND	Energy Metering*	24-SOIC	13.41	12.07	10.71		
ADE7759ARSZ-ND	Energy Meter with Sensor Interface*	20-SSOP	5.05	4.04	3.15		
ADE7763ARSZ-ND	Energy Meter Single Phase Active and Apparent*	24-SSOP	4.06	3.26	2.53		
ADE7763ARSZRLCT-ND	Energy Meter Single Phase Active and Apparent*	20-SSOP	4.06	3.26	2.53		
ADE7763ARSZRLTR-ND	Energy Meter Single Phase Active and Apparent*	20-SSOP	3455.28/1,500				
Temperature							
AD5900JF-ND	Temperature Transducer 2-Terminal*	2-COFF	17.34	16.19	15.03		
AD5900JH-ND	Temperature Transducer 2-Terminal*	TO-52-3	9.52	7.62	6.43		
AD5900JL-ND	Temperature Transducer 2-Terminal*	8-SOIC	6.13	4.91	4.14		
AD5900KF-ND	Temperature Transducer 2-Terminal*	2-COFF	18.95	17.69	16.43		
AD5900KH-ND	Temperature Transducer 2-Terminal*	TO-52-3	11.96	10.78	9.56		
AD5900KRZ-ND	Temperature Transducer 2-Terminal*	8-SOIC	10.14	8.12	6.85		
AD5900LF-ND	Temperature Transducer 2-Terminal*	2-COFF	47.15	44.01	40.87		
AD5900LH-ND	Temperature Transducer 2-Terminal*	TO-52-3	24.00	22.41	20.81		
AD5900MF-ND	Temperature Transducer 2-Terminal*	2-COFF	86.61	80.83	75.06		
AD5900MH-ND	Temperature Transducer 2-Terminal*	TO-52-3	57.15	53.34	49.53		
AD592ANZ-ND	Temperature Transducer 2-Terminal*	TO-92	5.41	4.33	3.37		
AD592BNZ-ND	Temperature Transducer 2-Terminal*	TO-92	12.46	11.22	9.94		
AD592CNZ-ND	Temperature Transducer 2-Terminal*	TO-92	16.59	14.94	13.24		
AD594AQ-ND	Thermocouple Amp with Compensator	14-Dip	13.86	12.48	11.06		
AD594CQ-ND	Thermocouple Amp with Compensator	14-Dip	22.52	21.03	19.52		
AD595AQ-ND	Thermocouple Amp with Compensator	14-Dip	13.86	12.48	11.06		
AD595CQ-ND	Thermocouple Amp with Compensator	14-Dip	22.52	21.03	19.52		
AD596AHZ-ND	Thermocouple Conditioning*	TO-100	14.96	13.47	11.94		
AD597AHZ-ND	Thermocouple Conditioning*	TO-100	16.11	14.51	12.87		
AD597ARZ-ND	Thermocouple Conditioning*	8-SOIC	6.67	5.34	4.50		
AD22100ARZ-ND	Temperature Sensor Voltage Out*	8-SOIC	6.28	5.03	4.25		
AD22100ATZ-ND	Temperature Sensor Voltage Out*	TO-92-3	5.70	4.57	3.85		
AD22100KTZ-ND	Temperature Sensor Voltage Out*	TO-92-3	3.82	3.05	2.38		
AD22100SRZ-ND	Temperature Sensor Voltage Out*	8-SOIC	6.91	5.53	4.67		
AD22100STZ-ND	Temperature Sensor Voltage Out*	TO-92-3	6.28	5.03	4.25		
AD22103KRZ-ND	Temperature Sensor Voltage Out*	8-SOIC	3.82	3.05	2.38		
AD22105ARZ-ND	Thermostatic Switch Solid State*	8-SOIC	3.36	2.69	2.09		
AD7314ARMZ-ND	Temperature Sensor 10-Bit Digital*	8-MSOP	1.85	1.49	1.12		
AD7414ARMOREEL7CT-ND	Temperature Sensor 10-Bit Digital*	8-MSOP	3.36	2.69	2.09		
AD7414ARMZ-ND	Temperature Sensor 10-Bit Digital*	8-MSOP	2.83	2.27	1.76		
AD7414ARTZ0500RCT-ND	Temperature Sensor 10-Bit*	SOT-23-6	2.63	2.11	1.64		
AD7414ARTZ0500RTR-ND	Temperature Sensor 10-Bit*	SOT-23-6	758.58/500				
AD7414ARTZ-1REEL7CT-ND	Temperature Sensor 10-Bit*	SOT-23-6	2.92	2.34	1.76		
AD7414ARTZ-1REEL7TR-ND	Temperature Sensor 10-Bit*	SOT-23-6	4411.44/3,000				
AD7415ARTZ-0500RL7CT-ND	Temperature Sensor 10-Bit*	SOT-23-6	2.63	2.11	1.64		
AD7415ARTZ-0500RL7TR-ND	Temperature Sensor 10-Bit*	SOT-23-6	758.58/500				
AD7415ARTZ-1500RL7CT-ND	Temperature Sensor 10-Bit*	SOT-23-5	2.63	2.11	1.64		
AD7415ARTZ-1500RL7TR-ND	Temperature Sensor 10-Bit*	SOT-23-5	758.58/500				
AD7416ARMZ-ND	Temperature Sensor 10-Bit*	8-MSOP	2.81	2.25	1.69		
AD7417ARZ-ND	Temperature Sensor 10-Bit/Four 1-Channel ADCs*	16-SOIC	6.85	5.48	4.63		
AD7417ARUZ-ND	Temperature Sensor 10-Bit/Four 1-Ch. ADCs*	16-TSSOP	6.85	5.48	4.63		
AD7418ARMZ-ND	Temperature Sensor 10-Bit/Four 1-Channel ADCs*	8-MSOP	5.79	4.64	3.91		
AD7418ARZ-ND	Temperature Sensor 10-Bit/Four 1-Channel ADCs*	8-SOIC	5.79	4.64	3.91		
AD7814ARMZ-ND	Digital Temperature Sensor 10-Bit*	8-MSOP	2.78	2.23	1.73		
AD7814ARTZ-REEL7CT-ND	Digital Temperature Sensor 10-Bit*	SOT-23-6	2.81	2.25	1.69		
AD7814ARTZ-REEL7TR-ND	Digital Temperature Sensor 10-Bit*	SOT-23-6	4309.09/3,000				
AD22103KTZ-ND	Temperature Sensor 3.3V Signal Condition*	TO-92	3.64	2.91	2.27		
AD22151VYZ-ND	Magnetic Field Sensor Linear*	8-SOIC	6.18	4.95	3.85		
AD17310TRZ-ND	Digital SPI Temperature Sensor 16-Bit* NEW!	8-SOIC	3.53	2.83	2.20		
AD17410TRZ-ND	IG Temperature Sensor* NEW!	8-SOIC	3.53	2.83	2.20		
EVAL-AD17X10EBZ-ND	Evaluation Board for AD17410* NEW!		163.32				
AD175ARZ-ND	Digital Temperature Sensor 12-Bit*	8-MSOP	1.94	1.55	1.17		
AD175BRZ-ND	Digital Temperature Sensor 12-Bit*	8-SOIC	1.94	1.55	1.17		
AD175BRMZ-ND	Digital Temperature Sensor 12-Bit*	8-MSOP	2.73	2.18	1.64		
AD16401SRJZ-RL7CT-ND	Temperature Switch 2.7V-5.5V*	SOT-23-6	1.68	1.35	1.01		
AD16401SRJZ-RL7TR-ND	Temperature Switch 2.7V-5.5V*	SOT-23-6	2585.46/3,000				
AD16402SRJZ-RL7CT-ND	Temperature Switch 2.7V-5.5V*	SOT-23-6	1.68	1.35	1.01		
AD16402SRJZ-RL7TR-ND	Temperature Switch 2.7V-5.5V*	SOT-23-6	2585.46/3,000				
AD16501SRJZ-P06SR7CT-ND	Temperature Switch 2.7V-5.5V*	SOT-23-5	1.68	1.41	1.13		
AD16501SRJZ-P06SR7TR-ND	Temperature Switch 2.7V-5.5V*	SOT-23-5	1.68	1.41	1.13		
AD16503SRJZ-02SR7CT-ND	Temperature Switch 2.7V-5.5V*	SOT-23-5	1.68				