

AUTOMOTIVE STANDARD BOOT BLOCK				
Numonyx Part No.	Digi-Key Part No.	Description	Pkg.	Price Each★
				1 10 100
M29W160EB70N6E	M29W160EB70N6E-ND	16Mb (2Mbx8 or 1Mbx16, Boot Block) 3V Supply Flash*	48-TSOP	3.31 2.99 2.40
M29W160EB70ZA6E	M29W160EB70ZA6E-ND	16Mb (2Mbx8 or 1Mbx16, Boot Block) 3V Supply Flash*	48-TFBGA	3.31 2.99 2.40
M29W160ET70N6F	M29W160ET70N6FCT-ND	16Mb (2Mbx8 or 1Mbx16, Boot Block) 3V Supply Flash*	48-TSOP	3.74 3.20 2.62
M29W160ET70N6F	M29W160ET70N6FTR-ND	16Mb (2Mbx8 or 1Mbx16, Boot Block) 3V Supply Flash*	48-TSOP	2319.50/1,500
M29W160EB70ZS6E	M29W160EB70ZS6E-ND	16Mb (2Mbx8 or 1Mbx16, Boot Block) 3V Supply Flash* NEW!	64-FBGA	3.31 2.99 2.40
M29W160ET70ZS6E	M29W160ET70ZS6E-ND	16Mb (2Mbx8 or 1Mbx16, Boot Block) 3V Supply Flash* NEW!	64-FBGA	3.31 2.99 2.40
M29W256GH70N6E	M29W256GH70N6E-ND	256Mb (32Mbx8 or 16Mbx16 Page, Uniform Block) 3V Supply Flash* NEW!	56-TSOP	11.17 9.16 8.27
M29W256GH70N6F	M29W256GH70N6FCT-ND	256Mb (32Mbx8 or 16Mbx16, Uniform Block) 3V Supply Flash* NEW!	56-TSOP	11.84 9.83 8.94
M29W256GH70N6F	M29W256GH70N6FTR-ND	256Mb (32Mbx8 or 16Mbx16, Uniform Block) 3V Supply Flash* NEW!	56-TSOP	7235.24/1,200
M29W256GH70ZA6F	M29W256GH70ZA6FCT-ND	256Mb (32Mbx8 or 16Mbx16, Uniform Block) 3V Supply Flash* NEW!	64-TBGA	11.84 9.83 8.94
M29W256GH70ZA6F	M29W256GH70ZA6FTR-ND	256Mb (32Mbx8 or 16Mbx16, Uniform Block) 3V Supply Flash* NEW!	64-TBGA	14515.14/2,500
M29W256GH70ZS6E	M29W256GH70ZS6E-ND	256Mb (32Mbx8 or 16Mbx16 Page, Uniform Block) 3V Supply Flash* NEW!	64-LBGA	11.17 9.16 8.27
M29W256GH70ZS6F	M29W256GH70ZS6F-ND	256Mb (32Mbx8 or 16Mbx16 Page, Uniform Block) 3V Supply Flash* NEW!	64-LBGA	10450.90/1,800
M29W256GL70N6E	M29W256GL70N6E-ND	256Mb (32Mbx8 or 16Mbx16 Page, Uniform Block) 3V Supply Flash* NEW!	56-TSOP	11.17 9.16 8.27
M29W256GL70N6F	M29W256GL70N6FCT-ND	256Mb (32Mbx8 or 16Mbx16, Uniform Block) 3V Supply Flash* NEW!	56-TSOP	11.84 9.83 8.94
M29W256GL70N6F	M29W256GL70N6FTR-ND	256Mb (32Mbx8 or 16Mbx16, Uniform Block) 3V Supply Flash* NEW!	56-TSOP	7235.24/1,200
M29W256GL70ZA6E	M29W256GL70ZA6E-ND	256Mb (32Mbx8 or 16Mbx16 Page, Uniform Block) 3V Supply Flash* NEW!	64-TBGA	11.17 9.16 8.27
M29W256GL70ZA6F	M29W256GL70ZA6FCT-ND	256Mb (32Mbx8 or 16Mbx16, Uniform Block) 3V Supply Flash* NEW!	64-TBGA	11.84 9.83 8.94
M29W256GL70ZA6F	M29W256GL70ZA6FTR-ND	256Mb (32Mbx8 or 16Mbx16, Uniform Block) 3V Supply Flash* NEW!	64-TBGA	14515.14/2,500
M29W256GL70ZS6E	M29W256GL70ZS6E-ND	256Mb (32Mbx8 or 16Mbx16 Page, Uniform Block) 3V Supply Flash* NEW!	64-LBGA	11.17 9.16 8.27
M29W256GL70ZS6F	M29W256GL70ZS6F-ND	256Mb (32Mbx8 or 16Mbx16 Page, Uniform Block) 3V Supply Flash* NEW!	64-LBGA	11.17 10.05 7.82
M29W256GSH70ZS6E	M29W256GSH70ZS6E-ND	256Mb (32Mbx8 or 16Mbx16 Page, Uniform Block) 3V Supply Flash* NEW!	64-LBGA	11.17 9.16 8.27
M29W256GSH70ZS6F	M29W256GSH70ZS6F-ND	256Mb (32Mbx8 or 16Mbx16 Page, Uniform Block) 3V Supply Flash* NEW!	64-LBGA	11.17 9.16 8.27
M29W256GSL70ZS6E	M29W256GSL70ZS6E-ND	256Mb (32Mbx8 or 16Mbx16 Page, Uniform Block) 3V Supply Flash* NEW!	64-LBGA	11.17 9.16 8.27
M29W256GSL70ZS6F	M29W256GSL70ZS6F-ND	256Mb (32Mbx8 or 16Mbx16 Page, Uniform Block) 3V Supply Flash* NEW!	64-LBGA	11.17 9.16 8.27
M29W320EB70N6E	M29W320EB70N6E-ND	32Mb (4Mbx8 or 2Mbx16, Uniform Parameter Blocks, Boot Block)*	48-TSOP	4.12 3.68 3.02
M29W320EB70ZS6E	M29W320EB70ZS6E-ND	32Mb (4Mbx8 or 2Mbx16, Uniform Parameter Blocks, Boot Block) 3V Supply Flash* NEW!	64-FBGA	4.12 3.68 3.02
M29W320ET70ZS6E	M29W320ET70ZS6E-ND	32Mb (4Mbx8 or 2Mbx16, Uniform Parameter Blocks, Boot Block) 3V Supply Flash* NEW!	64-FBGA	4.12 3.68 3.02
M29W320ET70N6E	M29W320ET70N6E-ND	32Mb (4Mbx8 or 2Mbx16, Uniform Parameter Blocks, Boot Block)*	48-TSOP	4.12 3.68 3.02
M29W320ET70ZE6E	M29W320ET70ZE6E-ND	32Mb (4Mbx8 or 2Mbx16, Uniform Parameter Blocks, Boot Block)*	48-TFBGA	4.12 3.68 3.02
M29W400DB55ZE6E	M29W400DB55ZE6E-ND	4Mb (512Kbx8 or 256Kbx16, Boot Block) 3V Supply Flash*	48-TFBGA	2.72 2.46 1.97
M29W400DB70N6E	M29W400DB70N6E-ND	4Mb (512Kbx8 or 256Kbx16, Boot Block) 3V Supply Flash*	48-TSOP	2.72 2.46 1.97
M29W400DT55N6E	M29W400DT55N6E-ND	4Mb (512Kbx8 or 256Kbx16, Boot Block) 3V Supply Flash*	48-TSOP	2.72 2.46 1.97
M29W400DT55ZE6E	M29W400DT55ZE6E-ND	4Mb (512Kbx8 or 256Kbx16, Boot Block) 3V Supply Flash*	48-TFBGA	2.72 2.46 1.97
M29W400DT70ZE6E	M29W400DT70ZE6E-ND	4Mb (512Kbx8 or 256Kbx16, Boot Block) 3V Supply Flash*	48-TFBGA	2.72 2.46 1.97
M29W640FB70ZA6E	M29W640FB70ZA6E-ND	64Mb (8Mbx8 or 4Mbx16, Page, Boot Block) 3V Supply Flash*	48-TFBGA	5.94 5.31 4.35
M29W640GB70NA6E	M29W640GB70NA6E-ND	64Mb (8Mbx8 or 4Mbx16, Bottom Boot Block) 3V Supply Flash*	48-TSOP	5.94 5.31 4.35
M29W640GB70ZA6E	M29W640GB70ZA6E-ND	64Mb (8Mbx8 or 4Mbx16, Bottom Boot Block) 3V Supply Flash*	48-TFBGA	5.94 5.31 4.35
M29W640GH70NB6E	M29W640GH70NB6E-ND	64Mb (8Mbx8 or 4Mbx16, Uniform, LBP) 3V Supply Flash*	56-TSOP	5.94 5.31 4.35
M29W640GL70NB6E	M29W640GL70NB6E-ND	64Mb (8Mbx8 or 4Mbx16, Uniform, FBP) 3V Supply Flash*	56-TSOP	5.94 5.31 4.35
M29W640GSL70ZF6E	M29W640GSL70ZF6E-ND	64Mb (8Mbx8 or 4Mbx16, Page, Uniform Block) 3V Supply Flash* NEW!	64-TBGA	5.94 5.31 4.35

AUTOMOTIVE STANDARD BOOT BLOCK				
Numonyx Part No.	Digi-Key Part No.	Description	Pkg.	Price Each★
				1 10 100
M29W640GSL70ZF6E	M29W640GSL70ZF6E-ND	64Mb (8Mbx8 or 4Mbx16, Page, Uniform Block) 3V Supply Flash* NEW!	64-TBGA	6.36 5.73 4.67
M29W640GSL70ZF6F	M29W640GSL70ZF6FTR-ND	64Mb (8Mbx8 or 4Mbx16, Page, Uniform Block) 3V Supply Flash* NEW!	64-TBGA	5969.89/2,500
M29W640GST70ZF6E	M29W640GST70ZF6E-ND	64Mb (8Mbx8 or 4Mbx16, Page, Uniform Block) 3V Supply Flash* NEW!	64-TBGA	5.94 5.31 4.35
M29W640GT70NA6E	M29W640GT70NA6E-ND	64Mb (8Mbx8 or 4Mbx16, Top Boot Block) 3V Supply Flash*	48-TSOP	5.94 5.31 4.35
M29W800DB70N6E	M29W800DB70N6E-ND	8Mb (1Mbx8 or 512Kbx16, Boot Block) 3V Supply Flash*	48-TSOP	2.92 2.64 2.13
M29W800DB70ZE6E	M29W800DB70ZE6E-ND	8Mb (1Mbx8 or 512Kbx16, Boot Block) 3V Supply Flash*	48-TFBGA	2.92 2.64 2.13
M29W800DT45N6E	M29W800DT45N6E-ND	8Mb (1Mbx8 or 512Kbx16, Boot Block) 3V Supply Flash*	48-TSOP	2.92 2.64 2.13
M29W800DT70N6E	M29W800DT70N6E-ND	8Mb (1Mbx8 or 512Kbx16, Boot Block) 3V Supply Flash*	48-TSOP	2.92 2.64 2.13
M29W800DT70ZE6E	M29W800DT70ZE6E-ND	8Mb (1Mbx8 or 512Kbx16, Boot Block) 3V Supply Flash*	48-TFBGA	2.92 2.64 2.13

M45P Series — RoHS Compliant				
M45PE10-VMN6TP	M45PE10-VMN6TPCT-ND	1Mb, Page-Erasable Serial Flash	SO-8	1.80 1.61 1.28
M45PE10-VMN6TP	M45PE10-VMN6TPTR-ND	1Mb, Page-Erasable Serial Flash	SO-8	1649.58/2,500
M45PE20-VMN6P	M45PE20-VMN6P-ND	2Mb, Page-Erasable Serial Flash	SO-8	1.81 1.64 1.32
M45PE20-VMN6TP	M45PE20-VMN6TPCT-ND	2Mb, Page-Erasable Serial Flash	SO-8	2.20 1.89 1.55
M45PE20-VMN6TP	M45PE20-VMN6TPTR-ND	2Mb, Page-Erasable Serial Flash	SO-8	2123.69/2,500
M45PE20-VMP6TG	M45PE20-VMP6TGCT-ND	2Mb, Page-Erasable Serial Flash	8-VDFPN	2.20 1.89 1.55
M45PE20-VMP6TG	M45PE20-VMP6TGTR-ND	2Mb, Page-Erasable Serial Flash	8-VDFPN	3397.90/4,000
M45PE40-VMP6G	M45PE40-VMP6G-ND	4Mb, Page-Erasable Serial Flash	8-VDFPN	2.09 1.89 1.52
M45PE80-VMP6TG	M45PE80-VMP6TGCT-ND	8Mb, LV, Page-Erasable, Serial Flash	8-VDFPN	2.83 2.43 1.98
M45PE80-VMP6TG	M45PE80-VMP6TGTR-ND	8Mb, LV, Page-Erasable, Serial Flash	8-VDFPN	4362.96/4,000

NEW! M58L Series — RoHS Compliant NEW!				
M58LR128KB85ZB5E	M58LR128KB85ZB5E-ND	128Mb, (Multiple Bank, Multilevel Interface, Burst) 1.8V Supply Flash	56-VFBGA	4.71 3.79 3.46
M58LR128KT85ZB5E	M58LR128KT85ZB5E-ND	128Mb, (Multiple Bank, Multilevel Interface, Burst) 1.8V Supply Flash	56-VFBGA	4.77 4.30 3.34
M58LR256KT70ZC5E	M58LR256KT70ZC5E-ND	128Mb, (Multiple Bank, Multilevel Interface, Burst) 1.8V Supply Flash	79-VFBGA	7.86 6.45 5.82

INTEGRATED CIRCUITS				
Digi-Key Part No.	Description	Pkg.	Price Each★	
				1 10 100
LED Ballasts — RoHS Compliant				
BCR401RE6327INCT-ND	18V, 60mA LED Driver	SOT-143R	61	48 33
BCR401RE6327INTR-ND	18V, 60mA LED Driver	SOT-143R	414.08/3,000	
BCR401UE6327INCT-ND	12V, 65mA LED Driver NEW!	SC-74-6	63	51 38
BCR401UE6327INTR-ND	12V, 65mA LED Driver NEW!	SC-74-6	531.90/3,000	
BCR401WE6327INCT-ND	18V, 60mA LED Driver	SOT-343	61	48 33
BCR402RE6327INCT-ND	18V, 60mA LED Driver	SOT-143R	61	48 33
BCR402RE6327INTR-ND	18V, 60mA LED Driver	SOT-143R	414.08/3,000	
BCR402UE6327INCT-ND	40V, 65mA LED Driver	SC-74-6	63	51 38
BCR402UE6327INTR-ND	40V, 65mA LED Driver	SC-74-6	531.90/3,000	
BCR402WE6327INCT-ND	18V, 60mA LED Driver	SOT-343	61	48 33
BCR402WE6327INTR-ND	18V, 60mA LED Driver	SOT-343	414.08/3,000	
BCR405UE6327INCT-ND	40V, 50mA LED Driver NEW!	SC-74-6	63	51 38
BCR405UE6327INTR-ND	40V, 50mA LED Driver NEW!	SC-74-6	532.24/3,000	
BCR405I0INCT-ND	40V, 100mA LED Driver	SC-74-6	1.14	1.03 82
BCR405I0INTR-ND	40V, 100mA LED Driver	SC-74-6	1269.16/3,000	
BT55576GCT-ND	54V, 25mA LED Driver NEW!	DSO-36	8.40	7.62 6.35
BT55576GTR-ND	54V, 25mA LED Driver NEW!	DSO-36	4282.16/1,000	
BT55590GCT-ND	54V, 25mA LED Driver NEW!	DSO-36	9.31	8.44 7.03
BT55590GTR-ND	54V, 25mA LED Driver NEW!	DSO-36	4744.49/1,000	
TLE4240-2MCT-ND	45V, 58mA LDO Linear LED Driver NEW!	SCTS95-5	1.58	1.42 1.13
TLE4240-2MTR-ND	45V, 58mA LDO Linear LED Driver NEW!	SCTS95-5	1605.81/3,000	
TLE4240-3MCT-ND	45V, 58mA LDO Linear LED Driver NEW!	SCTS95-5	1.78	1.60 1.27
TLE4240-3MTR-ND	45V, 58mA LDO Linear LED Driver NEW!	SCTS95-5	1794.33/3,000	
TLE4242INCT-ND	42V, 500mA Adj. LED Driver	D2PAK	3.71	3.35 2.73
TLE4242INTR-ND	42V, 500mA Adj. LED Driver	D2PAK	1596.83/1,000	
TLE4309GCT-ND	45V, 500mA Adj. LDO Linear LED Driver NEW!	TO-263-7	2.96	2.54 2.08
TLE4309GTR-ND	45V, 500mA Adj. LDO Linear LED Driver NEW!	TO-263-7	1225.40/1,000	
Power Management				
ADM6996LX-AA-T11N-ND	6-Port, 10/100Mbps TX/FX Switch	128-QFP	6.01	5.41 4.45
BSP75N CT-ND	Smart Low-Side Power Switch* NEW!	SOT-223-4	1.03	92 74
BSP75N TR-ND	Smart Low-Side Power Switch* NEW!	SOT-223-4	1624.89/4,000	
BSP76 E6433CT-ND	Smart Low-Side Power Switch* NEW!	SOT-223-4	1.13	1.01 81
BSP76 E6433TR-ND	Smart Low-Side Power Switch* NEW!	SOT-223-4	1665.29/4,000	
BSP77 E6433CT-ND	Smart Low-Side Power Switch* NEW!	SOT-223-4	1.45	1.30 1.03
BSP77 E6433TR-ND	Smart Low-Side Power Switch* NEW!	SOT-223-4	1939.09/4,000	
BSP78CT-ND	Smart Low-Side Power Switch* NEW!	SOT-223-4	1.99	1.71 1.40
BSP78TR-ND	Smart Low-Side Power Switch* NEW!	SOT-223-4	2818.87/4,000	
BSP452CT-ND	Smart High-Side Power Switch* NEW!	SOT-223-4	2.29	1.97 1.61
BSP452TR-ND	Smart High-Side Power Switch* NEW!	SOT-223-4	3532.56/4,000	
BSP742RCT-ND	Smart Power High-Side Switch* NEW!	DSO-8	2.04	1.75 1.43
BSP742RTR-ND	Smart Power High-Side Switch* NEW!	DSO-8	1966.59/2,500	
BSP742RICT-ND	Smart Power High-Side Switch* NEW!	DSO-8	2.04	1.75 1.43
BSP742RITR-ND	Smart Power High-Side Switch* NEW!	DSO-8	1966.59/2,500	
BSP742TINCT-ND	Smart Power High-Side Switch	DSO-8	3.13	2.81 2.23
BSP742TINTR-ND	Smart Power High-Side Switch	DSO-8	2883.95/2,500	
BSP752RINCT-ND	Smart Power High-Side Switch	DSO-8	3.59	3.08 2.52
BSP752RINTR-ND	Smart Power High-Side Switch	DSO-8	3459.06/2,500	
BSP752TCT-ND	Smart Power High-Side Switch* NEW!	DSO-8	2.26	1.94 1.59
BSP752TTR-ND	Smart Power High-Side Switch* NEW!	DSO-8	2176.99/2,500	
BSP762TINCT-ND	Smart Power High-Side Switch*	DSO-8	2.69	2.32 1.89
BSP762TINTR-ND	Smart Power High-Side Switch*	DSO-8	2600.61/2,500	
BSP772TINCT-ND	Smart Power High-Side Switch*	DSO-8	3.01	2.59 2.11
BSP772TINTR-ND	Smart Power High-Side Switch*	DSO-8	2903.59/2,500	
BTM7700GCT-ND	High Current Motor Driver* NEW!	DSO-28	4.94	4.45 3.62
BTM7700GTR-ND	High Current Motor Driver* NEW!	DSO-28	2096.19/1,000	

* RoHS Compliant

★ CALL FOR LOWER PRICING ON LARGER QUANTITIES! ★

(Continued)

Free shipping on orders over \$200 CAD! All prices in Canadian dollars and include duty and brokerage fees.

862 (CA2011)

1-800-344-4539 • www.digikey.ca • 218-681-6674 • Fax: 218-681-3380