

TEXAS INSTRUMENTS		DigiKey (Cont.)		AMPLIFIERS			RoHS Compliant Parts Available		
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*					
				1	25	100			
ONE9901PARGP	296-17055-5-ND	10.7Gbps Limiting Amp	20-VQFN	23.82	20.04	18.41			
OP07CD	296-12852-5-ND	Low Offset Voltage Precision Op Amp	8-SOIC	1.65	1.32	1.16			
OP07CDR	296-14626-1-ND	Low Offset Voltage Precision Op Amp	8-SOIC	1.49	1.18	1.07			
OP07CDR	296-14626-2-ND	Low Offset Voltage Precision Op Amp	8-SOIC	1374.65/2,500					
OP07CP	296-12853-5-ND	Low Offset Voltage Precision Op Amp	8-Dip	1.78	1.43	1.26			
OP07DD	296-9621-5-ND	Low Offset Voltage Precision Op Amp	8-SOIC	1.41	1.14	99			
OP07DP	296-9622-5-ND	Low Offset Voltage Precision Op Amp	8-Dip	1.30	1.04	91			
OPA276P	OPA276P-ND	Compensated, LNI, Precision Op Amp	8-Dip	3.42	2.76	2.51			
OPA276U	OPA276U-ND	Compensated, LNI, Precision Op Amp	8-SOIC	4.02	3.24	2.95			
OPA376P	OPA376P-ND	Uncompensated, LNI, Prec. Op Amp	8-Dip	3.58	2.88	2.63			
OPA376U	OPA376U-ND	Uncompensated, LNI, Prec. Op Amp	8-SOIC	4.17	3.36	3.06			
OPA111AM	OPA111AM-ND	Low Noise, Precision Op Amp (500µV Out)	TO-99	36.54	31.06	28.78			
OPA111BM	OPA111BM-ND	Low Noise, Precision Op Amp (250µV Out)	TO-99	54.97	47.55	44.58			
OPA121KU	OPA121KU-ND	Low Cost, Precision DIFET Op Amp	8-SOIC	15.06	12.67	11.64			
OPA124U	OPA124U-ND	Low Noise, Precision DIFET Op Amp	8-SOIC	13.33	10.93	9.87			
OPA124UA	OPA124UA-ND	Low Noise, Precision DIFET Op Amp	8-SOIC	13.70	11.53	10.59			
OPA128JM	OPA128JM-ND	DIFET Electrometer-Grade Op Amp	TO-99-8	63.74	56.24	53.43			
OPA128KM	OPA128KM-ND	DIFET Electrometer-Grade Op Amp	TO-99-8	71.02	62.67	59.54			
OPA128LM	OPA128LM-ND	DIFET Electrometer-Grade Op Amp	TO-99-8	75.71	67.69	64.24			
OPA128SM	OPA128SM-ND	DIFET Electrometer-Grade Op Amp	TO-99-8	88.84	79.42	75.38			
OPA129U	OPA129U-ND	Ultra-Low Bias Current DIFET Op Amp	8-SOIC	8.98	7.37	6.65			
OPA129UB	OPA129UB-ND	Ultra-Low Bias Current DIFET Op Amp	8-SOIC	15.06	12.67	11.64			
OPA130UA	OPA130UA-ND	Low Power, Precision, FET-In Op Amp	8-SOIC	5.34	4.30	3.92			
OPA131U	OPA131U-ND	General Purpose FET-In Op Amp	8-SOIC	7.07	5.69	5.18			
OPA131UA	OPA131UA-ND	General Purpose FET-In Op Amp	8-SOIC	4.08	3.29	3.00			
OPA131UJ	OPA131UJ-ND	General Purpose FET-In Op Amp	8-SOIC	3.13	2.53	2.28			
OPA132U	OPA132U-ND	High Speed FET-In Op Amp	8-SOIC	8.84	7.25	6.54			
OPA132UA	OPA132UA-ND	High Speed FET-In Op Amp	8-SOIC	5.50	4.42	4.03			
OPA134PA	OPA134PA-ND	High Performance Audio Op Amp	8-Dip	3.20	2.59	2.33			
OPA134UA	OPA134UA-ND	High Performance Audio Op Amp	8-SOIC	3.42	2.76	2.51			
OPA137N/250	OPA137NCT-ND	Low Cost FET-In Op Amp	SOT-23-5	3.53	2.89	2.60			
OPA137N/250	OPA137NTR-ND	Low Cost FET-In Op Amp	SOT-23-5	545.09/250					
OPA137NA/250	OPA137NACT-ND	Low Cost FET-In Op Amp	SOT-23-5	2.75	2.13	1.93			
OPA137NA/250	OPA137NATR-ND	Low Cost FET-In Op Amp	SOT-23-5	392.76/250					
OPA137P	OPA137P-ND	Low Cost FET-In Op Amp	8-Dip	3.31	2.67	2.40			
OPA137PA	OPA137PA-ND	Low Cost FET-In Op Amp	8-Dip	2.09	1.69	1.52			
OPA137U	OPA137U-ND	Low Cost FET-In Op Amp	8-SOIC	3.31	2.67	2.40			
OPA137UA	OPA137UA-ND	Low Cost FET-In Op Amp	8-SOIC	2.44	1.97	1.77			
OPA177FP	OPA177FP-ND	Precision Op Amp	8-Dip	2.92	2.36	2.13			
OPA177GP	OPA177GP-ND	Precision Op Amp	8-Dip	2.92	2.36	2.13			
OPA177GS	OPA177GS-ND	Precision Op Amp	8-SOIC	3.38	2.73	2.45			
OPA211ADR	296-22634-1-ND	Low Power, Precision Op Amp	8-SOIC	10.26	8.52	7.75			
OPA211ADR	296-22634-2-ND	Low Power, Precision Op Amp	8-SOIC	12582.22/2,500					
OPA211ADRGT	296-23412-1-ND	Low Power, Precision Op Amp	8-SOIC	11.89	9.88	8.98			
OPA211ADRGT	296-23412-2-ND	Low Power, Precision Op Amp	8-SOIC	1907.67/250					
OPA211ID	296-23958-5-ND	Low Power Precision Op Amp	8-SOIC	14.44	12.15	11.16			
OPA211IDGKT	296-23959-1-ND	Low Power Precision Op Amp	8-MSOP	14.71	12.48	11.52			
OPA2227P	296-23959-2-ND	Low Power Precision Op Amp	8-MSOP	2478.57/250					
OPA2227P	296-23959-3-ND	Low Power Precision Op Amp	8-Dip	7.16	5.76	5.25			
OPA2227U	296-23959-4-ND	High Precision, Low Noise Op Amp	8-Dip	3.20	2.66	2.42			
OPA2227U	296-23959-5-ND	High Precision, Low Noise Op Amp	8-SOIC	3.77	3.24	2.92			
OPA227U	296-22819-1-ND	High Precision, Low Noise Op Amp	8-SOIC	3.89	3.14	2.86			
OPA227U/2K5	296-25819-1-ND	High Precision, Low Noise Op Amp	8-SOIC	7.68 6.27 5.63					
OPA227U/2K5	296-25819-2-ND	High Precision, Low Noise Op Amp	8-SOIC	8505.97/2,500					
OPA228P	OPA228P-ND	Low Noise Precision Op Amp	8-Dip	7.16	5.76	5.25			
OPA228PA	OPA228PA-ND	Low Noise Precision Op Amp	8-Dip	3.20	2.66	2.42			
OPA228U	OPA228U-ND	High Precision Op Amp	8-SOIC	7.77	6.24	5.69			
OPA228UA	OPA228UA-ND	High Precision Op Amp	8-SOIC	3.89	3.14	2.86			
OPA234E/250	OPA234EACT-ND	Low Power Single-Supply Op Amp	8-MSOP	5.29	4.32	3.86			
OPA234E/250	OPA234EATR-ND	Low Power Single-Supply Op Amp	8-MSOP	814.97/250					
OPA234EA/250	OPA234EA-ND	Low Power Single-Supply Op Amp	8-MSOP	3.84	3.14	2.82			
OPA234EA/250	OPA234EA-ND	Low Power Single-Supply Op Amp	8-MSOP	591.66/250					
OPA234U	OPA234U-ND	Low Power Single-Supply Op Amp	8-SOIC	5.09	4.10	3.73			
OPA234UA	OPA234UA-ND	Low Power Single-Supply Op Amp	8-SOIC	3.74	3.01	2.74			
OPA237NA/250	OPA237NACT-ND	Single-Supply Op Amp	SOT-23-5	2.36	1.82	1.65			
OPA237NA/250	OPA237NATR-ND	Single-Supply Op Amp	SOT-23-5	336.65/250					
OPA237NA/3K	296-26265-1-ND	Single-Supply Op Amp	SOT-23-5	2.17	1.67	1.52			
OPA237NA/3K	296-26265-2-ND	Single-Supply Op Amp	SOT-23-5	2501.29/3,000					
OPA237UA	OPA237UA-ND	Single-Supply Op Amp	8-SOIC	2.27	1.83	1.65			
OPA241PA	OPA241PA-ND	Single-Supply, Micropower, Low Voltage Op Amp	8-Dip	3.61	2.91	2.65			
OPA241UA	OPA241UA-ND	Single-Supply, Micropower, Low Voltage Op Amp	8-SOIC	4.24	3.41	3.11			
OPA244NA/250	OPA244NACT-ND	Single-Supply, Micropower Op Amp	SOT-23-5	2.24	1.73	1.57			
OPA244NA/250	OPA244NATR-ND	Single-Supply, Micropower Op Amp	SOT-23-5	319.82/250					
OPA244PA	OPA244PA-ND	Single-Supply, Micropower Op Amp	8-Dip	1.81	1.46	1.32			
OPA244UA	OPA244UA-ND	Single-Supply, Micropower Op Amp	8-SOIC	2.15	1.74	1.57			
OPA251PA	OPA251PA-ND	Single-Supply, Micropower Op Amp	8-Dip	3.61	2.91	2.65			
OPA251UA	OPA251UA-ND	Single-Supply, Micropower Op Amp	8-SOIC	4.24	3.41	3.11			
OPA277P	OPA277P-ND	High Precision Op Amp	8-Dip	6.28	5.05	4.61			
OPA277PA	OPA277PA-ND	High Precision Op Amp	8-Dip	2.82	2.28	2.05			
OPA277U	OPA277U-ND	High Precision Op Amp	8-SOIC	6.88	5.53	5.04			
OPA277UA	OPA277UA-ND	High Precision Op Amp	8-SOIC	3.14	2.53	2.31			
OPA300AID	296-15087-5-ND	Low Noise, HS, 16-Bit CMOS Op Amp	8-SOIC	3.13	2.53	2.28			
OPA301AID	296-17236-5-ND	Low Noise, High Speed CMOS Op Amp	8-SOIC	3.13	2.53	2.28			
OPA330AID	296-25305-5-ND	350kHz, R/R CMOS Op Amp	8-SOIC	1.92	1.55	1.39			
OPA330AIDBVT	296-25307-1-ND	350kHz, R/R CMOS Op Amp	SOT-23-5	2.17	1.67	1.52			
OPA330AIDBVT	296-25307-2-ND	350kHz, R/R CMOS Op Amp	NEW! SOT-23-5	308.59/250					
OPA330AIDCKR	296-25615-1-ND	350kHz, R/R CMOS Op Amp	NEW! SC70-5	1.92	1.52	1.37			
OPA330AIDCKR	296-25615-2-ND	350kHz, R/R CMOS Op Amp	NEW! SC70-5	2120.88/3,000					
OPA330AIDCKT	296-25308-1-ND	350kHz, R/R CMOS Op Amp	NEW! SC70-5	2.17	1.67	1.52			
OPA330AIDCKT	296-25308-2-ND	350kHz, R/R CMOS Op Amp	NEW! SC70-5	308.59/250					
OPA330AIDR	296-25309-1-ND	350kHz, R/R CMOS Op Amp	NEW! 8-SOIC	1.92	1.52	1.37			
OPA330AIDR	296-25309-2-ND	350kHz, R/R CMOS Op Amp	NEW! 8-SOIC	1767.40/2,500					
OPA333AID	296-19545-5-ND	1.8V Micropower CMOS Op Amp	8-SOIC	3.61	2.91	2.65			
OPA333AIDBVT	296-19546-1-ND	1.8V Micropower CMOS Op Amp	SOT-23-5	3.70	3.03	2.72			
OPA333AIDBVT	296-19546-2-ND	1.8V Micropower CMOS Op Amp	SOT-23-5	570.90/250					
OPA333AIDCKR	296-19547-1-ND	1.8V Micropower CMOS Op Amp	SC70-5	3.74	2.88	2.62			
OPA333AIDCKR	296-19547-2-ND	1.8V Micropower CMOS Op Amp	SC70-5	4319.19/3,000					
OPA333AMDBVREP	296-22187-1-ND	1.8V Micropower CMOS Op Amp	SOT-23-5	8.47	7.04	6.40			
OPA333AMDCREP	296-22188-1-ND	1.8V Micropower CMOS Op Amp	SC70-5	8.47	7.04	6.40			

TEXAS INSTRUMENTS		DigiKey (Cont.)		AMPLIFIERS			RoHS Compliant Parts Available		
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*					
				1	25	100			
OPA335AID	296-13467-5-ND	Single-Supply CMOS Zero Drift Op Amp	8-SOIC	3.58	2.88	2.63			
OPA335AIDBVR	296-26271-1-ND	Single-Supply CMOS Zero Drift Op Amp	SOT-23-5	3.74	2.88	2.62			
OPA335AIDBVR	296-26271-2-ND	Single-Supply CMOS Zero Drift Op Amp	SOT-23-5	4319.19/3,000					
OPA335AIDBVT	296-13468-1-ND	Single-Supply CMOS Zero Drift Op Amp	SOT-23-5	3.67	3.00	2.70			
OPA335AIDBVT	296-13468-2-ND	Single-Supply CMOS Zero Drift Op Amp	SOT-23-5	565.85/250					
OPA336N/250	OPA336NCT-ND	Single-Supply, Micropower Op Amp	SOT-23-5	3.53	2.89	2.60			
OPA336N/250	OPA336NTR-ND	Single-Supply, Micropower Op Amp	SOT-23-5	545.09/250					
OPA336NA/250	OPA336NACT-ND	Single-Supply, Micropower Op Amp	SOT-23-5	2.95	2.28	2.07			
OPA336NA/250	OPA336NATR-ND	Single-Supply, Micropower Op Amp	SOT-23-5	420.81/250					
OPA336NU/250	296-26273-1-ND	Single-Supply, Micropower Op Amp	SOT-23-5	1.96	1.55	1.40			
OPA336NU/250	296-26273-2-ND	Single-Supply, Micropower Op Amp	SOT-23-5	277.45/250					
OPA336U	OPA336U-ND	Single-Supply, Micropower Op Amp	8-SOIC	3.20	2.66	2.42			
OPA336UA	OPA336UA-ND	Single-Supply, Micropower Op Amp	8-SOIC	2.61	2.11	1.90			
OPA337EA/250	OPA337EACT-ND	Single-Supply, CMOS Op Amp	8-MSOP	2.11	1.67	1.50			
OPA337EA/250	OPA337EATR-ND	Single-Supply, CMOS Op Amp	8-MSOP	298.49/250					
OPA337NA/250	OPA337NACT-ND	Single-Supply, CMOS Op Amp	SOT-23-5	2.11	1.67	1.50			
OPA337NA/250	OPA337NATR-ND	Single-Supply, CMOS Op Amp	SOT-23-5	298.49/250					
OPA337UA/2K5	OPA337UACT-ND	Single-Supply, CMOS Op Amp	8-Dip	1.69	1.36	1.19			
OPA337UA/2K5	OPA337UATR-ND	Single-Supply, CMOS Op Amp	8-SOIC	1.83	1.45	1.31			
OPA337UA/2K5	OPA337UA-ND	Single-Supply, CMOS Op Amp	8-SOIC	2.92	1.55	1.39			
OPA337UA/2K5	OPA337UA-ND	Single-Supply, CMOS Op Amp	8-SOIC	1688.85/2,500					
OPA338NA/250	OPA338NACT-ND	Decompensated Single-Supply CMOS Op Amp	SOT-23-5	2.56	1.97	1.79			
OPA338NA/250	OPA338NATR-ND	Decompensated Single-Supply CMOS Op Amp	SOT-23-5	364.70/250					
OPA338UA	OPA338UA-ND	Decompensated Single-Supply CMOS Op Amp	8-SOIC	1.92	1.55	1.39			
OPA340NA/250	OPA340NACT-ND	Single-Supply, R/R Op Amp	SOT-23-5	3.61	2.79	2.53			
OPA340NA/250	OPA340NATR-ND	Single-Supply, R/R Op Amp	SOT						