

TEXAS INSTRUMENTS		DigiKey® (Cont.)		AMPLIFIERS			
RoHS Compliant Parts Available							
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*			
				1	25	100	
TL072ACD	296-7189-5-ND	Dual Low Noise JFET Op Amp	8-SOIC	1.03	.83	.73	
TL072ACP	296-7190-5-ND	Dual Low Noise JFET Op Amp	8-Dip	1.12	.90	.79	
TL072BCD	296-7191-5-ND	Dual Low Noise JFET Op Amp	8-SOIC	1.46	1.17	1.03	
TL072BCDR	296-14996-1-ND	Dual Low Noise JFET Op Amp	8-SOIC	1.32	1.05	.94	
TL072BCDR	296-14996-2-ND	Dual Low Noise JFET Op Amp	8-SOIC	1217.54/2,500			
TL072BCP	296-7192-5-ND	Low Noise JFET Op Amp	8-Dip	1.58	1.27	1.11	
TL072CD	296-1282-5-ND	Dual JFET-Input Op Amp	8-SOIC	.79	.62	.54	
TL072CDR	296-1282-1-ND	Dual JFET-Input Op Amp	8-SOIC	520.68/2,000			
TL072CDR	296-1282-2-ND	Dual JFET-Input Op Amp	8-SOIC	.86	.67	.59	
TL072CP	296-1775-5-ND	Dual JFET-Input Op Amp	8-Dip	.93	.73	.64	
TL072CPSR	296-26695-1-ND	Dual Low Noise JFET Op Amp * NEW!	8-SOIC	.86	.68	.60	
TL072CPSR	296-26695-2-ND	Dual Low Noise JFET Op Amp * NEW!	8-SOIC	572.30/2,000			
TL072CPWR	296-7193-1-ND	Dual Low Noise JFET Op Amp	8-TSSOP	.79	.62	.54	
TL072CPWR	296-7193-2-ND	Dual Low Noise JFET Op Amp	8-TSSOP	520.68/2,000			
TL072ID	296-7194-5-ND	Dual Low Noise JFET Op Amp	8-SOIC	.86	.67	.59	
TL072IDR	296-7194-1-ND	Dual Low Noise JFET Op Amp	8-SOIC	.79	.62	.54	
TL072IDR	296-7194-2-ND	Dual Low Noise JFET Op Amp	8-SOIC	650.85/2,500			
TL072IP	296-14997-5-ND	Dual Low Noise JFET Op Amp	8-Dip	.79	.62	.54	
TL074ACD	296-7195-5-ND	Quad Low Noise JFET Op Amp	14-SOIC	1.13	.91	.80	
TL074ACN	296-12948-5-ND	Quad Low Noise JFET Op Amp	14-Dip	1.03	.83	.73	
TL074BCD	296-7196-5-ND	Quad Low Noise JFET Op Amp	14-SOIC	1.32	1.06	.93	
TL074BCDR	296-14999-1-ND	Quad Low Noise JFET Op Amp	14-SOIC	1.19	.95	.85	
TL074BCDR	296-14999-2-ND	Quad Low Noise JFET Op Amp	14-SOIC	1099.72/2,500			
TL074BCN	296-7197-5-ND	Quad Low Noise JFET Op Amp	14-Dip	1.21	.97	.85	
TL074CD	296-1283-5-ND	Quad Low Noise JFET Op Amp	14-SOIC	.76	.57	.49	
TL074CDR	296-1283-1-ND	Quad Low Noise JFET Op Amp	14-SOIC	.75	.53	.45	
TL074CDR	296-1283-2-ND	Quad Low Noise JFET Op Amp	14-SOIC	527.42/2,500			
TL074CN	296-1777-5-ND	Quad Low Noise JFET Op Amp	14-Dip	.70	.54	.47	
TL074CNSR	296-26696-1-ND	Quad LN JFET Op Amp * NEW!	14-SOP	.82	.58	.49	
TL074CNSR	296-26696-2-ND	Quad LN JFET Op Amp * NEW!	14-SOP	460.09/2,000			
TL074CPWR	296-7198-1-ND	Quad Low Noise JFET Op Amp	14-TSSOP	.75	.53	.45	
TL074CPWR	296-7198-2-ND	Quad Low Noise JFET Op Amp	14-TSSOP	421.93/2,000			
TL074ID	296-7199-5-ND	Quad Low Noise JFET Op Amp	14-SOIC	1.03	.83	.73	
TL074IDR	296-15000-1-ND	Quad Low Noise JFET Op Amp	14-SOIC	1.09	.84	.75	
TL074IDR	296-15000-2-ND	Quad Low Noise JFET Op Amp	14-SOIC	894.92/2,500			
TL074IN	296-7200-5-ND	Quad Low Noise JFET Op Amp	14-Dip	1.12	.90	.79	
TL080CP	296-10127-5-ND	JFET Op Amp	8-Dip	1.67	1.34	1.17	
TL081ACD	296-7201-5-ND	JFET Op Amp	8-SOIC	1.03	.83	.73	
TL081ACP	296-7202-5-ND	JFET Op Amp	8-Dip	1.12	.90	.79	
TL081CD	296-12949-5-ND	JFET Op Amp	8-SOIC	.64	.48	.41	
TL081CDR	296-15001-1-ND	JFET Op Amp	8-SOIC	.62	.44	.38	
TL081CDR	296-15001-2-ND	JFET Op Amp	8-SOIC	434.84/2,500			
TL081CP	296-7203-5-ND	JFET Op Amp	8-Dip	.58	.44	.38	
TL081ID	296-7204-5-ND	JFET Op Amp	8-SOIC	.70	.52	.44	
TL081IDR	296-15002-1-ND	JFET Op Amp	8-SOIC	.68	.48	.41	
TL081IDR	296-15002-2-ND	JFET Op Amp	8-SOIC	479.72/2,500			
TL082ACD	296-7205-5-ND	Dual JFET-Input Op Amp	8-SOIC	1.08	.84	.73	
TL082ACP	296-1778-5-ND	Dual JFET-Input Op Amp	8-Dip	.99	.77	.67	
TL082BCD	296-7206-5-ND	Dual JFET-Input Op Amp	8-SOIC	1.46	1.17	1.03	
TL082BCDR	296-15004-1-ND	Dual JFET-Input Op Amp	8-SOIC	1.32	1.05	.94	
TL082BCDR	296-15004-2-ND	Dual JFET-Input Op Amp	8-SOIC	1217.54/2,500			
TL082BCP	296-7207-5-ND	Dual JFET-Input Op Amp	8-Dip	1.58	1.27	1.11	
TL082CD	296-1284-5-ND	Dual JFET-Input Op Amp	8-SOIC	.86	.67	.59	
TL082CDR	296-1284-1-ND	Dual JFET-Input Op Amp	8-SOIC	.79	.62	.54	
TL082CP	296-1780-5-ND	Dual JFET-Input Op Amp	8-Dip	.93	.73	.64	
TL082CPSR	296-26698-1-ND	Dual JFET-Input Op Amp * NEW!	8-SOIC	.86	.68	.60	
TL082CPSR	296-26698-2-ND	Dual JFET-Input Op Amp * NEW!	8-SOIC	572.30/2,000			
TL082CPWR	296-26699-1-ND	Dual JFET-Input Op Amp * NEW!	8-TSSOP	.86	.67	.59	
TL082CPWR	296-26699-2-ND	Dual JFET-Input Op Amp * NEW!	8-TSSOP	.79	.62	.54	
TL082CPWR	296-7208-2-ND	Dual JFET-Input Op Amp	8-TSSOP	520.68/2,000			
TL082ID	296-7209-5-ND	Dual JFET-Input Op Amp	8-SOIC	.93	.73	.64	
TL082IDR	296-15005-1-ND	Dual JFET-Input Op Amp	8-SOIC	.86	.68	.60	
TL082IDR	296-15005-2-ND	Dual JFET-Input Op Amp	8-SOIC	715.38/2,500			
TL082IP	296-1781-5-ND	Dual JFET-Input Op Amp	8-Dip	.86	.67	.59	
TL084ACD	296-7210-5-ND	Quad JFET-Input Op Amp	14-SOIC	1.03	.83	.73	
TL084ACN	296-1782-5-ND	Quad JFET-Input Op Amp	14-Dip	1.09	.85	.74	
TL084BCD	296-12950-5-ND	Quad JFET-Input Op Amp	14-SOIC	1.50	1.21	1.06	
TL084BCDR	296-15007-1-ND	Quad JFET-Input Op Amp	14-SOIC	1.37	1.08	.97	
TL084BCDR	296-15007-2-ND	Quad JFET-Input Op Amp	14-SOIC	1256.82/2,500			
TL084BCN	296-12951-5-ND	Quad JFET-Input Op Amp	14-Dip	1.64	1.31	1.15	
TL084CD	296-1285-5-ND	Quad JFET-Input Op Amp	14-SOIC	.76	.57	.49	
TL084CDR	296-1285-1-ND	Quad JFET-Input Op Amp	14-SOIC	.68	.48	.41	
TL084CDR	296-1285-2-ND	Quad JFET-Input Op Amp	14-SOIC	479.72/2,500			
TL084CN	296-1784-5-ND	Quad JFET-Input Op Amp	14-Dip	.76	.57	.49	
TL084CNSR	296-7211-1-ND	Quad JFET-Input Op Amp	14-SOP	.75	.53	.45	
TL084CNSR	296-7211-2-ND	Quad JFET-Input Op Amp	14-SOP	421.93/2,000			
TL084CPWR	296-26700-5-ND	Quad JFET-Input Op Amp * NEW!	14-TSSOP	.71	.52	.45	
TL084ID	296-1785-5-ND	Quad JFET-Input Op Amp	14-SOIC	.76	.57	.49	
TL084IDR	296-1785-1-ND	Quad JFET-Input Op Amp	14-SOIC	.75	.53	.45	
TL084IDR	296-1785-2-ND	Quad JFET-Input Op Amp	14-SOIC	527.42/2,500			
TL084IN	296-7213-5-ND	Quad JFET-Input Op Amp	14-Dip	.71	.52	.45	
TL084OD	296-7214-5-ND	Quad JFET-Input Op Amp	14-SOIC	1.04	.84	.73	
TL103WIDR	296-18862-1-ND	Dual Op Amp with Internal Reference	8-SOIC	.89	.69	.61	
TL103WIDR	296-18862-2-ND	Dual Op Amp with Internal Reference	8-SOIC	732.21/2,500			
TL343IDBVR	296-12496-1-ND	Single, Low Power Op Amp	SOT-23-5	1.49	1.18	1.07	
TL343IDBVR	296-12496-2-ND	Single, Low Power Op Amp	SOT-23-5	1649.58/3,000			
TL347ACDR	296-24386-1-ND	Single Op Amp * NEW!	14-SOIC	1.58	1.25	1.13	
TL347ACDR	296-24386-2-ND	Single Op Amp * NEW!	14-SOIC	1453.20/2,500			
TL592B-8D	296-10218-5-ND	Differential Video Amplifier	8-SOIC	1.92	1.55	1.39	
TL592BP	296-10219-5-ND	Differential Video Amplifier	8-Dip	1.92	1.55	1.39	
TL971ODRQ1	296-24878-1-ND	Single, Output R/R, Very Low Noise Op Amp * NEW!	8-SOIC	.97	.75	.66	
TL971ODRQ1	296-24878-2-ND	Single, Output R/R, Very Low Noise Op Amp * NEW!	8-SOIC	797.29/2,500			

TEXAS INSTRUMENTS		DigiKey® (Cont.)		AMPLIFIERS			
RoHS Compliant Parts Available							
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*			
				1	25	100	
TL972ODRQ1	296-24869-1-ND	Dual, Output R/R, Very Low Noise Op Amp * NEW!	8-SOIC	1.08	.86	.77	
TL972ODRQ1	296-24869-2-ND	Dual, Output R/R, Very Low Noise Op Amp * NEW!	8-SOIC	993.67/2,500			
TL972QPWRQ1	296-25175-1-ND	Dual, Output R/R, Very Low Noise Op Amp * NEW!	8-TSSOP	1.08	.86	.77	
TL972QPWRQ1	296-25175-2-ND	Dual, Output R/R, Very Low Noise Op Amp * NEW!	8-TSSOP	794.94/2,000			
TL974IPWR	296-21861-1-ND	Quad, Output R/R, Very Low Noise Op Amp	14-TSSOP	1.11	.88	.79	
TL974IPWR	296-21861-2-ND	Quad, Output R/R, Very Low Noise Op Amp	14-TSSOP	816.93/2,000			
TL974QPWRQ1	296-24891-1-ND	Quad, Output R/R, Very Low Noise Op Amp * NEW!	14-TSSOP	1.28	1.01	.91	
TL974QPWRQ1	296-24891-2-ND	Quad, Output R/R, Very Low Noise Op Amp * NEW!	14-TSSOP	939.47/2,000			
TL3414AIP	296-17553-5-ND	Dual High Output Current Op Amp	8-Dip	1.12	.90	.79	
TL3472CD	296-10169-5-ND	High Slew Rate, Single Supply Op Amp	8-SOIC	.92	.71	.62	
TL3472CP	296-10170-5-ND	High Slew Rate, Single Supply Op Amp	8-Dip	.99	.77	.67	
TL3474ACDR	296-15623-1-ND	Quad, High Slew Rate, Single Supply Op Amp	14-SOIC	1.92	1.52	1.37	
TL3474ACN	296-15624-5-ND	Quad, High Slew Rate, Single Supply Op Amp	14-Dip	1.94	1.56	1.37	
TL3474ACPWR	296-15116-1-ND	Quad, High Slew Rate, Single Supply Op Amp	14-TSSOP	1.92	1.52	1.37	
TL3474ACPWR	296-15116-2-ND	Quad, High Slew Rate, Single Supply Op Amp	14-TSSOP	1413.92/2,000			
TL3474AIN	296-15626-5-ND	Quad, High Slew Rate, Single Supply Op Amp	14-Dip	1.94	1.56	1.37	
TL3474CD	296-14405-5-ND	Quad, High Slew Rate, Single Supply Op Amp	14-SOIC	1.74	1.40	1.23	
TL3474CN	296-14406-5-ND	Quad, High Slew Rate, Single Supply Op Amp	14-Dip	1.59	1.28	1.12	
TL3474ID	296-14407-5-ND	Quad, High Slew Rate, Single Supply Op Amp	14-SOIC	1.74	1.40	1.23	
TL3474IN	296-14408-5-ND	Quad, High Slew Rate, Single Supply Op Amp	14-Dip	1.59	1.28	1.12	
TL3474IPWR	296-15119-1-ND	Quad, High Slew Rate, Single Supply Op Amp	14-TSSOP	1.58	1.25	1.13	
TL3474IPWR	296-15119-2-ND	Quad, High Slew Rate, Single Supply Op Amp	14-TSSOP	1162.56/2,000			
TL4581P	296-15628-5-ND	Dual Low Noise High Drive Op Amp	8-Dip	1.30	1.04	.91	
TL5580AIP	296-21098-5-ND	Dual Low Noise Wide Bandwidth Precision Amp	8-Dip	2.96	2.39	2.15	
TL5580AIPWR	296-21099-1-ND	Dual Low Noise Wide Bandwidth Precision Amp	8-TSSOP	3.34	2.58	2.34	
TL5580IP	296-21101-5-ND	Dual Low Noise Wide Bandwidth Precision Amp	8-Dip	2.27	1.83	1.65	
TL25L2ACD	296-7297-5-ND	Dual Op Amp	8-SOIC	5.03	4.04	3.69	
TL25L2BCD	296-7298-5-ND	Dual Op Amp	8-SOIC	5.18	4.17	3.80	
TL25L2BCP	296-7299-5-ND	Dual Op Amp	8-Dip	5.18	4.17	3.80	
TL25L2CD	296-7300-5-ND	Dual Low Volt. Micropower Op Amp	8-SOIC	5.66	4.55	4.15	
TL25L2CPC	296-7301-5-ND	Dual Low Volt. Micropower Op Amp	8-Dip	4.71	3.79	3.46	
TL25L2ACN	296-7303-5-ND	Quad Op Amp	14-Dip	6.91	5.56	5.07	
TL25L2ABCD	296-7304-5-ND	Quad Op Amp	14-SOIC	7.23	5.81	5.30	
TL							