

Texas INSTRUMENTS		DigiKey Reel®	AMPLIFIERS			
(Cont.)			RoHS Compliant Parts Available			
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*		
				1	25	100
TLC271CD	296-1308-5-ND	LP Programmable Op Amp	8-SOIC	.99	.80	.70
TLC271CP	296-1820-5-ND	LP Programmable Op Amp	8-Dip	.94	.74	.64
TLC271CPS	296-26741-5-ND	LP Programmable Op Amp * <b>NEW!</b>	8-SO	.99	.80	.70
TLC271ID	296-1821-5-ND	LP Programmable Op Amp	8-SOIC	1.03	.83	.73
TLC271IP	296-1822-5-ND	LP Programmable Op Amp	8-Dip	.99	.77	.67
TLC272ACD	296-1309-5-ND	Dual Precision Op Amp	8-SOIC	1.11	.89	.78
TLC272ACDR	296-1309-1-ND	Dual Precision Op Amp	8-SOIC	1.16	.90	.80
TLC272ACDR	296-1309-2-ND	Dual Precision Op Amp	8-SOIC	956.64/2,500		
TLC272ACP	296-7346-5-ND	Dual Precision Op Amp	8-Dip	1.05	.82	.72
TLC272AD	296-7347-5-ND	Dual Precision Op Amp	8-SOIC	1.16	.93	.81
TLC272AIP	296-7348-5-ND	Dual Precision Op Amp	8-Dip	1.11	.86	.75
TLC272B	296-7349-5-ND	Dual Precision Op Amp	8-SOIC	1.14	.92	.81
TLC272BCDR	296-26742-1-ND	Dual Precision Op Amp * <b>NEW!</b>	8-SOIC	1.20	.94	.83
TLC272BCDR	296-26742-2-ND	Dual Precision Op Amp * <b>NEW!</b>	8-SOIC	993.11/2,500		
TLC272BCP	296-7350-5-ND	Dual Precision Op Amp	8-Dip	1.14	.92	.81
TLC272BD	296-7351-5-ND	Dual Precision Op Amp	8-SOIC	1.20	.96	.84
TLC272BDR	296-26743-1-ND	Dual Precision Op Amp * <b>NEW!</b>	8-SOIC	1.09	.87	.78
TLC272BDR	296-26743-2-ND	Dual Precision Op Amp * <b>NEW!</b>	8-SOIC	1004.33/2,500		
TLC272BIP	296-7352-5-ND	Dual Precision Op Amp	8-Dip	1.01	.81	.71
TLC272CD	296-1310-5-ND	Dual Precision Op Amp	8-SOIC	1.04	.81	.71
TLC272CDR	296-1310-1-ND	Dual Precision Op Amp	8-SOIC	.95	.74	.65
TLC272CDR	296-1310-2-ND	Dual Precision Op Amp	8-SOIC	785.10/2,500		
TLC272CP	296-1824-5-ND	Dual Precision Op Amp	8-Dip	.86	.68	.59
TLC272CPSR	296-7353-1-ND	Dual Single-Supply Op Amp	8-SOP	.95	.74	.65
TLC272CPSR	296-7353-2-ND	Dual Single-Supply Op Amp	8-SOP	628.41/2,000		
TLC272CPW	296-7354-5-ND	Dual Single-Supply Op Amp	8-TSSOP	1.04	.81	.71
TLC272CPWR	296-7354-1-ND	Dual Single-Supply Op Amp	8-TSSOP	.95	.74	.65
TLC272CPWR	296-7354-2-ND	Dual Single-Supply Op Amp	8-TSSOP	628.41/2,000		
TLC272ID	296-1311-5-ND	Dual Precision Single-Supply Op Amp	8-SOIC	1.09	.85	.74
TLC272IDR	296-1311-1-ND	Dual Precision Single-Supply Op Amp	8-SOIC	1.00	.78	.69
TLC272IDR	296-1311-2-ND	Dual Precision Single-Supply Op Amp	8-SOIC	825.78/2,500		
TLC272IP	296-7355-5-ND	Dual Single-Supply Op Amp	8-Dip	.91	.71	.62
TLC274ACD	296-1825-5-ND	Quad Precision Op Amp	14-SOIC	1.43	1.15	1.00
TLC274ACN	296-7356-5-ND	Quad Precision Op Amp	14-Dip	1.19	.95	.84
TLC274AID	296-7357-5-ND	Quad Precision Op Amp	14-SOIC	1.43	1.15	1.00
TLC274AIDR	296-26744-1-ND	Quad Precision Op Amp * <b>NEW!</b>	14-SOIC	1.29	1.02	.92
TLC274AIDR	296-26744-2-ND	Quad Precision Op Amp * <b>NEW!</b>	14-SOIC	1186.68/2,500		
TLC274AIND	296-7358-5-ND	Quad Precision Op Amp	14-Dip	1.19	.95	.84
TLC274BCD	296-7359-5-ND	Quad Precision Op Amp	14-SOIC	1.58	1.27	1.11
TLC274BCN	296-7360-5-ND	Quad Precision Op Amp	14-Dip	1.32	1.06	.93
TLC274BD	296-1312-5-ND	Quad Precision Op Amp	14-SOIC	1.58	1.27	1.11
TLC274BDR	296-1312-1-ND	Quad Precision Op Amp	14-SOIC	1.44	1.14	1.02
TLC274BDR	296-1312-2-ND	Quad Precision Op Amp	14-SOIC	1319.66/2,500		
TLC274BIN	296-7361-5-ND	Quad Precision Op Amp	14-Dip	1.32	1.06	.93
TLC274CD	296-1313-5-ND	Quad Single-Supply Op Amp	14-SOIC	1.31	1.05	.92
TLC274CDR	296-1313-1-ND	Quad Precision Op Amp	14-SOIC	1.18	.94	.84
TLC274CDR	296-1313-2-ND	Quad Precision Op Amp	14-SOIC	1087.93/2,500		
TLC274CN	296-1826-5-ND	Quad Precision Op Amp	14-Dip	1.09	.88	.77
TLC274CPWR	296-26745-1-ND	Quad Precision Op Amp * <b>NEW!</b>	14-TSSOP	1.18	.94	.84
TLC274CPWR	296-26745-2-ND	Quad Precision Op Amp * <b>NEW!</b>	14-TSSOP	870.80/2,000		
TLC274ID	296-1314-5-ND	Quad Precision Op Amp	14-SOIC	1.31	1.05	.92
TLC274IDR	296-1314-1-ND	Quad Precision Op Amp	14-SOIC	1.18	.94	.84
TLC274IDR	296-1314-2-ND	Quad Precision Op Amp	14-SOIC	1087.93/2,500		
TLC274IN	296-7362-5-ND	Quad Single-Supply Op Amp	14-Dip	1.31	1.05	.92
TLC274IPW	296-14197-5-ND	Quad Single-Supply Op Amp	14-TSSOP	1.31	1.05	.92
TLC274MD	296-7363-5-ND	Quad Single-Supply Op Amp	14-SOIC	1.39	1.12	.98
TLC277CD	296-7364-5-ND	Dual Precision Single-Supply Op Amp	8-SOIC	3.00	2.42	2.18
TLC277CDR	296-26747-1-ND	Dual Precision Op Amp * <b>NEW!</b>	8-SOIC	2.79	2.16	1.96
TLC277CDR	296-26747-2-ND	Dual Precision Op Amp * <b>NEW!</b>	8-SOIC	2690.38/2,500		
TLC277CP	296-1828-5-ND	Dual Precision Op Amp	8-Dip	2.47	2.00	1.80
TLC277ID	296-1829-5-ND	Dual Precision Op Amp	8-SOIC	3.13	2.53	2.28
TLC277IP	296-7365-5-ND	Dual Precision Single-Supply Op Amp	8-Dip	2.65	2.14	1.92
TLC279CD	296-7366-5-ND	Quad Prec. Single-Supply Op Amp	14-SOIC	3.74	3.01	2.74
TLC279CN	296-7367-5-ND	Quad Prec. Single-Supply Op Amp	14-Dip	3.14	2.53	2.31
TLC279ID	296-1315-5-ND	Quad Prec. Single-Supply Op Amp	14-SOIC	3.89	3.14	2.86
TLC279IDR	296-1315-1-ND	Quad Prec. Single-Supply Op Amp	14-SOIC	3.53	2.89	2.60
TLC279IDR	296-1315-2-ND	Quad Prec. Single-Supply Op Amp	14-SOIC	3917.74/2,500		
TLC279IN	296-7368-5-ND	Quad Prec. Single-Supply Op Amp	14-Dip	3.30	2.66	2.42
TLC393QDR	296-15027-1-ND	Dual Micropower LinCMOS Voltage Comparator	8-SOIC	1.32	1.05	.94
TLC1078CD	296-10231-5-ND	Dual Micropower Low Voltage Op Amp	8-SOIC	7.33	6.01	5.42
TLC1078CP	296-10232-5-ND	Dual Micropower Low Voltage Op Amp	8-Dip	6.88	5.53	5.04
TLC1078ID	296-10233-5-ND	Dual Micropower Low Voltage Op Amp	8-SOIC	7.61	6.24	5.63
TLC1078IP	296-10234-5-ND	Dual Micropower Low Voltage Op Amp	8-Dip	7.16	5.76	5.25
TLC1079CD	296-10235-5-ND	Quad Micropower Low Volt. Op Amp	14-SOIC	10.27	8.42	7.60
TLC1079CN	296-10236-5-ND	Quad Micropower Low Volt. Op Amp	14-Dip	8.53	7.00	6.32
TLC1079ID	296-10237-5-ND	Quad Micropower Low Volt. Op Amp	14-SOIC	10.66	8.75	7.89
TLC1079IN	296-10238-5-ND	Quad Micropower Low Volt. Op Amp	14-Dip	8.92	7.32	6.61
TLC2201ACD	296-7050-5-ND	Low Noise Precision Op Amp	8-SOIC	6.13	4.93	4.49
TLC2201AID	296-7052-5-ND	Low Noise Precision Op Amp	8-SOIC	6.41	5.16	4.70
TLC2201AMD	296-7054-5-ND	Low Noise Precision Op Amp	8-SOIC	6.56	5.28	4.81
TLC2201CD	296-2425-5-ND	Low Noise Precision R/R Op Amp	8-SOIC	5.97	4.80	4.38
TLC2201CP	296-10241-5-ND	Low Noise Precision R/R Op Amp	8-Dip	4.94	3.97	3.62
TLC2201IDR	296-7061-1-ND	Low Noise Precision R/R Op Amp	8-SOIC	5.59	4.57	4.10
TLC2201IDR	296-7061-2-ND	Low Noise Precision R/R Op Amp	8-SOIC	6194.32/2,500		
TLC2201ID	296-10242-5-ND	Low Noise Precision R/R Op Amp	8-SOIC	6.13	4.93	4.49
TLC2201IP	296-7062-5-ND	Low Noise Precision R/R Op Amp	8-Dip	5.22	4.20	3.82
TLC2202ACD	296-7063-5-ND	Dual Low Noise Precision Op Amp	14-SOIC	10.25	8.40	7.58
TLC2202AID	296-7065-5-ND	Dual Low Noise Precision Op Amp	14-SOIC	8.98	7.37	6.65
TLC2202CD	296-1807-5-ND	Dual Low Noise Precision Op Amp	14-SOIC	7.46	6.12	5.53
TLC2202CP	296-7071-5-ND	Dual Low Noise Precision Op Amp	8-Dip	7.00	5.64	5.13
TLC2202IP	296-7073-5-ND	Dual Low Noise Precision R/R Op Amp	8-Dip	7.32	5.89	5.36
TLC2252AID	296-7074-5-ND	Dual Rail-to-Rail Op Amp	8-SOIC	2.47	2.00	1.80
TLC2252AIDR	296-26729-1-ND	Dual Rail-to-Rail Op Amp * <b>NEW!</b>	8-SOIC	2.32	1.79	1.63

Texas INSTRUMENTS		DigiKey Reel®	AMPLIFIERS			
(Cont.)			RoHS Compliant Parts Available			
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*		
				1	25	100
TLC2252AIDR	296-26729-2-ND	Dual Rail-to-Rail Op Amp * <b>NEW!</b>	8-SOIC	2235.90/2,500		
TLC2252AIP	296-7075-5-ND	Dual Rail-to-Rail Op Amp	8-Dip	2.05	1.66	1.49
TLC2252AIPWR	296-7076-1-ND	Dual Rail-to-Rail Op Amp	8-TSSOP	2.32	1.79	1.63
TLC2252AIPWR	296-7076-2-ND	Dual Rail-to-Rail Op Amp	8-TSSOP	1788.72/2,000		
TLC2252AQD	296-7077-5-ND	Dual Rail-to-Rail Op Amp	8-SOIC	2.19	1.77	1.60
TLC2252AODRG401	296-24514-1-ND	Dual Rail-to-Rail Op Amp * <b>NEW!</b>	8-SOIC	2.48	1.91	1.74
TLC2252AODRG401	296-24514-2-ND	Dual Rail-to-Rail Op Amp * <b>NEW!</b>	8-SOIC	2387.40/2,500		
TLC2252CD	296-7078-5-ND	Dual R/R Micropower Op Amp	8-SOIC	2.33	1.88	1.70
TLC2252CDR	296-26730-1-ND	Dual R/R Micropower Op Amp * <b>NEW!</b>	8-SOIC	2.17	1.67	1.52
TLC2252CDR	296-26730-2-ND	Dual R/R Micropower Op Amp * <b>NEW!</b>	8-SOIC	2084.41/2,500		
TLC2252CP	296-7079-5-ND	Dual R/R Micropower Op Amp	8-Dip	1.92	1.55	1.39
TLC2252ID	296-7080-5-ND	Dual R/R Micropower Op Amp	8-SOIC	2.33	1.88	1.70
TLC2252IP	296-7081-5-ND	Dual R/R Micropower Op Amp	8-Dip	2.05	1.66	1.49
TLC2252QD	296-7082-5-ND	Dual R/R Micropower Op Amp	8-SOIC	2.05	1.66	1.49
TLC2254AID	296-7083-5-ND	Quad Rail-to-Rail Op Amp	14-SOIC	3.13	2.53	2.28
TLC2254AIDR	296-26731-1-ND	Quad Rail-to-Rail Op Amp * <b>NEW!</b>	14-SOIC	2.98	2.31	2.09
TLC2254AIDR	296-26731-2-ND	Quad Rail-to-Rail Op Amp * <b>NEW!</b>	14-SOIC	2878.34/2,500		
TLC2254AIN	296-7084-5-ND	Quad Rail-to-Rail Op Amp	14-Dip	2.65	2.14	1.92
TLC2254AIPWR	296-7085-1-ND	Quad Rail-to-Rail Op Amp	14-TSSOP	2.98	2.31	2.09
TLC2254AIPWR	296-7085-2-ND	Quad Rail-to-Rail Op Amp	14-TSSOP	2302.67/2,000		
TLC2254AQD	296-7086-5-ND	Quad Rail-to-Rail Op Amp	14-SOIC	2.82	2.28	2.05
TLC2254CD	296-1300-5-ND	Quad R/R Micropower Op Amp	14-SOIC	2.82	2.28	2.05
TLC2254CDR	296-1300-1-ND	Quad R/R Micropower Op Amp	14-SOIC	2.79	2.16	1.96
TLC2254CDR	296-1300-2-ND	Quad R/R Micropower Op Amp	14-SOIC	2688.98/2,500		
TLC2254CN	296-7088-5-ND	Quad R/R Micropower Op Amp	14-Dip	2.47	2.00	1.80
TLC2254CPWR	296-7089-1-ND	Quad R/R Micropower Op Amp	14-TSSOP	2.79	2.16	1.96
TLC2254CPWR	296-7089-2-ND	Quad R/R Micropower Op Amp	14-TSSOP	2152.30/2,000		
TLC2254ID	296-1301-5-ND	Quad Low Power Op Amp	14-SOIC	3.00	2.42	2.18
TLC2254IDR	296-1301-1-ND	Quad Low Power Op Amp	14-SOIC	2.79	2.16	1.96
TLC2254IDR	296-1301-2-ND	Quad Low Power Op Amp	14-SOIC	2688.98/2,500		
TLC2254IN	296-7090-5-ND	Quad R/R Micropower Op Amp	14-Dip	2.47	2.00	1.80
TLC2254QD	296-7091-5-ND	Quad R/R Micropower Op Amp	14-SOIC	2.65	2.14	1.92
TLC2262AID	296-7092-5-ND	Dual Rail-to-Rail Op Amp	8-SOIC	2.65	2.14	1.92
TLC2262AIDR	296-26732-1-ND	Dual Rail-to-Rail Op Amp * <b>NEW!</b>	8-SOIC	2.44	1.88	1.71
TLC2262AIDR	296-26732-2-ND	Dual Rail-to-Rail Op Amp * <b>NEW!</b>	8-SOIC	2348.12/2,500		
TLC2262AIP	296-7093-5-ND	Dual Rail-to-Rail Op Amp	8-Dip	2.15	1.74	1.57
TLC2262AQD	296-7094-5-ND	Dual Rail-to-Rail Op Amp	8-SOIC	2.33	1.88	1.70
TLC2262CD	296-1302-5-ND	Dual Rail-to-Rail Op Amp	8-SOIC	2.47	2.00	1.80
TLC2262CDR	296-1302-1-ND	Dual Rail-to-Rail Op Amp	8-SOIC	2.24	1.73	1.57
TLC2262CDR	296-1302-2-ND	Dual Rail-to-Rail Op Amp	8-SOIC	2158.76/2,500		
TLC2262CP	296-7095-5-ND	Dual Rail-to-Rail Op Amp	8-Dip	1.99	1.60	1.44
TLC2262CPWR	296-7096-1-ND	Dual Rail-to-Rail Op Amp	8-TSSOP			