

TEXAS INSTRUMENTS		DigiKey Real (Cont.)		AMPLIFIERS			RoHS Compliant Parts Available		
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*					
				1	25	100			
TPA2037D1YFFR	296-25337-2-ND	3.2W Mono Class-D Audio Amp* NEW!	9-DSBGA	2955.77	3,000				
TPA2037D1YFFT	296-25343-1-ND	3.2W Mono Class-D Audio Amp* NEW!	9-DSBGA	2.95	2.28	2.07			
TPA2037D1YFFT	296-25343-2-ND	3.2W Mono Class-D Audio Amp* NEW!	9-DSBGA	420.81	250				
TPA2039D1YFFR	296-25571-1-ND	3.2W Mono Class-D Audio Amp* NEW!	9-DSBGA	2.56	1.97	1.79			
TPA2039D1YFFR	296-25571-2-ND	3.2W Mono Class-D Audio Amp* NEW!	9-DSBGA	2955.77	3,000				
TPA2051D3YFFR	296-24832-1-ND	2.9W/Ch. Mono Class-D Audio Subsystem* NEW!	25-DSBGA	2.95	2.28	2.07			
TPA2051D3YFFR	296-24832-2-ND	2.9W/Ch. Mono Class-D Audio Subsystem* NEW!	25-DSBGA	3408.56	3,000				
TPA2054D4YZKR	296-24453-1-ND	1.4W/Ch. Stereo Class-D Audio Subsystem* NEW!	25-DSBGA	4.38	3.58	3.21			
TPA2054D4YZKR	296-24453-2-ND	1.4W/Ch. Stereo Class-D Audio Subsystem* NEW!	25-DSBGA	5820.64	3,000				
TPA2054D4YZKT	296-24516-1-ND	1.4W/Ch. Stereo Class-D Audio Subsystem* NEW!	25-DSBGA	.79	5.55	48			
TPA2054D4YZKT	296-24516-2-ND	1.4W/Ch. Stereo Class-D Audio Subsystem* NEW!	25-DSBGA	778.50	250				
TPA3001D1PWPR	296-14200-1-ND	20W Mono Class-D Audio Amp	24-HTSSOP	8.03	6.67	6.06			
TPA3001D1PWPR	296-14200-2-ND	20W Mono Class-D Audio Amp	24-HTSSOP	7877.56	2,000				
TPA3002D2EVM	296-20583-ND	Evaluation Module for TPA3002D2	—	56.11	—	—			
TPA3002D2PHPR	296-14201-1-ND	9W Class-D Audio Amp with DC Volume Control	48-HTQFP	9.82	8.15	7.41			
TPA3002D2PHPR	296-14201-2-ND	9W Class-D Audio Amp with DC Volume Control	48-HTQFP	4999.22	1,000				
TPA3003D2PFB	296-15037-ND	3.75W Class-D Audio Amp with DC Volume Control	48-TQFP	10.10	8.29	7.48			
TPA3004D2PHPR	296-15038-1-ND	12W Class-D Audio Amp with DC Volume Control	48-HTQFP	9.66	8.03	7.30			
TPA3004D2PHPR	296-15038-2-ND	12W Class-D Audio Amp with DC Volume Control	48-HTQFP	4924.04	1,000				
TPA3005D2EVM	296-18924-ND	Evaluation Module for TPA3005D2	—	56.11	—	—			
TPA3005D2PHPR	296-17058-1-ND	6W Class-D Stereo Audio Power Amp	48-HTQFP	8.78	7.29	6.63			
TPA3007D1EVM	296-18925-ND	Evaluation Module for TPA3007D1	—	56.11	—	—			
TPA3007D1PW	296-15792-5-ND	15W Audio Power Amp	24-TSSOP	7.38	5.94	5.41			
TPA3007D1PWR	296-26880-1-ND	6.5W Mono Class-D Audio Power Amp* NEW!	24-TSSOP	6.56	5.37	4.82			
TPA3007D1PWR	296-26880-2-ND	6.5W Mono Class-D Audio Power Amp* NEW!	24-TSSOP	5821.77	2,000				
TPA3008D2EVM	296-18926-ND	Evaluation Module for TPA3008D2	—	56.11	—	—			
TPA3008D2PHPR	296-17210-ND	10W Stereo Class-D Audio Power Amp	48-HTQFP	10.53	8.63	7.79			
TPA3100D2EVM	296-21138-ND	Evaluation Module for TPA3100D2	—	170.57	—	—			
TPA3100D2PHPR	296-19603-1-ND	21.8W Stereo Class-D Audio Pwr. Amp	48-HTQFP	10.41	8.65	7.86			
TPA3100D2PHPR	296-19603-2-ND	21.8W Stereo Class-D Audio Pwr. Amp	48-HTQFP	5302.21	1,000				
TPA3100D2RGR	296-19423-1-ND	21.8W Stereo Class-D Audio Pwr. Amp	48-VQFN	10.41	8.65	7.86			
TPA3101D2EVM	296-21139-ND	Evaluation Module for TPA3101D2	—	170.57	—	—			
TPA3101D2PHPR	296-19554-ND	10W Stereo Class-D Audio Power Amp	48-HTQFP	10.53	8.63	7.79			
TPA3106D1VFP	296-26884-ND	40W Mono Class-D Audio Power Amp* NEW!	32-LQFP	7.57	6.22	5.61			
TPA3106D1VFP	296-22976-1-ND	40W Mono Class-D Audio Power Amp	32-HLQFP	7.57	6.19	5.6			
TPA3110D2PWP	296-24968-5-ND	15W Stereo Class-D Audio Power Amp* NEW!	28-HTSSOP	5.50	4.42	4.03			
TPA3110D2PWP	296-24926-1-ND	15W Stereo Class-D Audio Power Amp* NEW!	28-HTSSOP	4.88	3.99	3.58			
TPA3110D2PWP	296-24926-2-ND	15W Stereo Class-D Audio Power Amp* NEW!	28-HTSSOP	4329.29	2,000				
TPA3111D1PWP	296-25128-5-ND	10W Mono Class-D Audio Power Amp* NEW!	28-HTSSOP	3.46	2.78	2.54			
TPA3111D1PWP	296-25121-1-ND	10W Mono Class-D Audio Power Amp* NEW!	28-HTSSOP	3.53	2.73	2.48			
TPA3111D1PWP	296-25121-2-ND	10W Mono Class-D Audio Power Amp* NEW!	28-HTSSOP	2726.85	2,000				
TPA3112D1PWP	296-25242-5-ND	25W Mono Class-D Audio Power Amp* NEW!	28-HTSSOP	4.40	3.54	3.23			
TPA3112D1PWP	296-25158-1-ND	25W Mono Class-D Audio Power Amp* NEW!	28-HTSSOP	4.52	3.49	3.17			
TPA3112D1PWP	296-25158-2-ND	25W Mono Class-D Audio Power Amp* NEW!	28-HTSSOP	3433.81	2,000				
TPA3113D2PWP	296-25127-5-ND	6W Stereo Class-D Audio Power Amp* NEW!	28-HTSSOP	3.30	2.66	2.42			
TPA3113D2PWP	296-25122-1-ND	6W Stereo Class-D Audio Power Amp* NEW!	28-HTSSOP	3.34	2.58	2.34			
TPA3113D2PWP	296-25122-2-ND	6W Stereo Class-D Audio Power Amp* NEW!	28-HTSSOP	2575.36	2,000				
TPA3120D2PWP	296-21673-5-ND	25W Stereo Class-D Audio Power Amp	24-HTSSOP	10.81	8.86	8.00			
TPA3121D2PWP	296-23477-1-ND	15W Stereo Class-D Audio Power Amp	24-HTSSOP	4.88	3.99	3.58			
TPA3121D2PWP	296-23477-2-ND	15W Stereo Class-D Audio Power Amp	24-HTSSOP	4329.29	2,000				
TPA3121D2PWP	296-23375-5-ND	15W Stereo Class-D Audio Power Amp	20-Dip	3.45	2.78	2.50			
TPA3123D2PWP	296-22008-1-ND	25W Stereo Class-D Audio Power Amp	24-HTSSOP	5.89	4.82	4.33			
TPA3123D2PWP	296-22008-2-ND	25W Stereo Class-D Audio Power Amp	24-HTSSOP	5224.78	2,000				
TPA3125D2N	296-24090-5-ND	10W Stereo Class-D Audio Power Amp	20-DIP	2.96	2.39	2.15			
TPA3200D1DCP	296-18302-5-ND	20W Mono Digital Input Audio Amp	44-HTSSOP	12.49	10.24	9.24			
TPA4411EVM	296-17385-ND	Evaluation Module for TPA4411	—	56.11	—	—			
TPA4411MRTJR	296-26885-1-ND	80mW DIRECTPATH™ Stereo Headphone Driver* NEW!	20-WQFN	2.79	2.16	1.96			
TPA4411MRTJR	296-26885-2-ND	80mW DIRECTPATH™ Stereo Headphone Driver* NEW!	20-WQFN	3228.45	3,000				
TPA4411RTJT	296-17312-1-ND	0.1W Capless Stereo Headphone Dvr.	20-WQFN	3.46	2.67	2.42			
TPA4860D	296-7013-5-ND	1.1W Mono Audio Power Amp	16-SOIC	2.33	1.88	1.70			
TPA4861D	296-7014-5-ND	1.1W Mono Audio Power Amp	8-SOIC	2.33	1.88	1.70			
TPA4861DR	296-7014-1-ND	1.1W Mono Audio Power Amp	8-SOIC	2.17	1.67	1.52			
TPA4861DR	296-7014-2-ND	1.1W Mono Audio Power Amp	8-SOIC	2084.41	2,500				
TPA4860EVM	296-10838-ND	Evaluation Module for TPA4860	—	56.11	—	—			
TPA5050RSAR	296-19884-1-ND	Stereo Digital Audio Lip-Sync Delay	16-VQFN	9.52	7.90	7.19			
TPA5050RSAR	296-19884-2-ND	Stereo Digital Audio Lip-Sync Delay	16-VQFN	14004.56	3,000				
TPA5051RSAR	296-20711-1-ND	4-Ch. Digital Audio Lip-Sync Delay	16-VQFN	9.52	7.90	7.19			
TPA5052RSAR	296-20712-1-ND	Stereo Digital Audio Lip-Sync Delay	16-VQFN	8.78	7.29	6.63			
TPA6010A4EVM	296-10840-ND	Evaluation Module for TPA6010A4	—	56.11	—	—			

TEXAS INSTRUMENTS		DigiKey Real (Cont.)		AMPLIFIERS			RoHS Compliant Parts Available		
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*					
				1	25	100			
TPA6010A4PWPR	296-7015-1-ND	2.7W Stereo Audio Power Amp w/Bass Boost/DC Volume Control	28-HTSSOP	7.57	6.19	5.56			
TPA6010A4PWPR	296-7015-2-ND	2.7W Stereo Audio Power Amp w/Bass Boost/DC Volume Control	28-HTSSOP	6716.13	2,000				
TPA6011A4EVM	296-13568-ND	Evaluation Module for TPA6011A4	—	56.11	—	—			
TPA6011A4PWPR	296-16919-5-ND	2W Stereo Audio Power Amp	24-HTSSOP	4.33	3.49	3.18			
TPA6011A4PWPR	296-12678-1-ND	2W Stereo Audio Power Amp	24-HTSSOP	3.84	3.14	2.82			
TPA6011A4PWPR	296-12678-2-ND	2W Stereo Audio Power Amp	24-HTSSOP	3402.84	2,000				
TPA6012A4PWPR	296-25462-1-ND	3W Stereo Audio Power Amp* NEW!	24-HTSSOP	4.04	3.30	2.97			
TPA6012A4PWPR	296-25462-2-ND	3W Stereo Audio Power Amp* NEW!	24-HTSSOP	3581.93	2,000				
TPA6013A4PWPR	296-25463-1-ND	3W Stereo Audio Power Amp* NEW!	24-HTSSOP	4.17	3.41	3.07			
TPA6013A4PWPR	296-25463-2-ND	3W Stereo Audio Power Amp* NEW!	24-HTSSOP	3700.88	2,000				
TPA6017A2EVM	296-20586-ND	Evaluation Module for TPA6017A2	—	56.11	—	—			
TPA6017A2PWPR	296-12506-1-ND	2W Stereo Audio Power Amp	20-HTSSOP	1.98	1.56	1.40			
TPA6020A2EVM	296-21141-ND	Evaluation Module for TPA6020A2	—	56.11	—	—			
TPA6021A4EVM	296-21142-ND	Evaluation Module for TPA6021A4	—	56.11	—	—			
TPA6021A4N	296-18249-5-ND	2W Stereo Audio Power Amp	20-Dip	3.20	2.59	2.33			
TPA6030A4EVM	296-20587-ND	Evaluation Module for TPA6030A4	—	56.11	—	—			
TPA6030A4PWPR	296-13866-5-ND	5W Stereo Audio Power Amp	28-HTSSOP	5.34	4.30	3.92			
TPA6047A4RHR	296-23843-1-ND	2W Stereo Audio Power Amp	32-QFN	3.89	3.00	2.73			
TPA6100A2DR	296-7017-1-ND	0.05W Ultra-LV Audio Power Amp	8-SOIC	1.49	1.18	1.07			
TPA6100A2DR	296-7017-2-ND	0.05W Ultra-LV Audio Power Amp	8-SOIC	1374.65	2,500				
TPA6100A2EVM	296-10841-ND	Evaluation Module for TPA6100A2	—	56.11	—	—			
TPA6101A2D	296-7018-5-ND	0.05W Ultra-LV Fixed Gain Stereo Headphone Audio Power Amp	8-SOIC	1.65	1.32	1.16			
TPA6101A2EVM	296-10842-ND	Evaluation Module for TPA6101A2	—	56.11	—	—			
TPA6102A2D	296-7020-5-ND	0.05W Ultra-LV Audio Power Amp	8-SOIC	1.89	1.51	1.32			
TPA6102A2EVM	296-11637-ND	Evaluation Module for TPA6102A2	—	56.11	—	—			
TPA610A2DGN	296-10843-5-ND	0.15W Stereo Power Amp	8-MSOP	1.40	1.13	.99			
TPA6110A2EVM	296-10844-ND	Evaluation Module for TPA6110A2	—	56.11	—	—			
TPA611A2DGN	296-10845-5-ND	0.15W Stereo Power Amp	8-MSOP	1.64	1.32	1.15			
TPA611A2DR	296-10846-1-ND	0.15W Stereo Power Amp	8-SOIC	1.18	.94	.84			
TPA611A2DR	296-10846-2-ND	0.15W Stereo Power Amp	8-SOIC	1088.50	2,500				
TPA611A2EVM	296-10847-ND	Evaluation Module for TPA611A2	—	56.11	—	—			
TPA6112A2DGNR	296-10848-1-ND	0.15W Stereo Power Amp	10-MSOP	1.76	1.39	1.25			
TPA6112A2DGNR	296-10848-2-ND	0.15W Stereo Power Amp	10-HMSOP	1618.72	2,500				
TPA6112A2EVM	296-10849-ND	Evaluation Module for TPA6112A2	—	56.11	—	—			
TPA6120A2DWP	296-16920-5-ND	High Fidelity Headphone Amp	20-HSOIC	7.23	5.81	5.30			
TPA6120A2EVM	296-18927-ND	Evaluation Module for TPA6120A2	—	113.34	—	—			
TPA6130A2RTRJ	296-21656-1-ND	0.29W DirectPath Stereo Headphone Amplifier	20-WQFN	3.14	2.43	2.20			
TPA6130A2RTRJ	296-21656-2-ND	0.29W DirectPath™ Stereo Headphone Amplifier	20-WQFN	3635.80	3,000				
TPA6132A2RTER	296-24053-1-ND	25mW DirectPath™ Stereo Headphone Amplifier* NEW!	16-TQFN	2.17	1.67	1.52			
TPA6135A2RTER	296-24218-1-ND	25mW DirectPath™ Stereo Headphone Amplifier* NEW!	16-WQFN	2.36	1.82	1.65			
TPA6135A2RTER	296-24218-2-ND	25mW DirectPath™ Stereo Headphone Amplifier* NEW!	16-WQFN	2726.85	3,000				
TPA6136A2YFFR	296-24962-1-ND	25mW DirectPath™ Stereo Headphone Amplifier* NEW!	16-DSBGA	2.75	2.13	1.93			
TPA6136A2YFFR	296-24962-2-ND	25mW DirectPath™ Stereo Headphone Amplifier* NEW!	16-DSBGA	3181.32	3,000				