

TEXAS INSTRUMENTS DigiKey Reel (Cont.)		DIGITAL LOGIC			
		RoHS Compliant Parts Available			
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*	
				1	25 100
CD4047BPWR	296-13642-2-ND	CMOS LP Monostable/Astable Multivibrator	14-TSSOP	365.82/2,000	
CD4048BE	296-2054-5-ND	Expandable 8-Input Gate	16-Dip	.66 .49 .42	
CD4049UBD	296-25945-5-ND	CMOS Hex Buffer/Converter* <b>NEW!</b>	16-SOIC	.63 .47 .40	
CD4049UBE	296-2055-5-ND	Hex Inverting Buffer/Converter	16-Dip	.62 .46 .39	
CD4049UBNSR	296-14112-1-ND	Hex Inverting Buffer/Converter	16-SOP	.66 .47 .40	
CD4049UBNSR	296-14112-2-ND	Hex Inverting Buffer/Converter	16-SOP	374.80/2,000	
CD4049UBPWR	296-25946-1-ND	CMOS Hex Buffer/Converter* <b>NEW!</b>	16-TSSOP	.61 .43 .37	
CD4049UBPWR	296-25946-2-ND	CMOS Hex Buffer/Converter* <b>NEW!</b>	16-TSSOP	341.14/2,000	
CD4050BE	296-2056-5-ND	Hex Non-Inverting Buffer/Converter	16-Dip	.62 .46 .39	
CD4050BDWR	296-14270-1-ND	Hex Non-Inverting Buffer/Converter	16-SOIC	.61 .43 .37	
CD4050BDWR	296-14270-2-ND	Hex Non-Inverting Buffer/Converter	16-SOIC	341.14/2,000	
CD4050BNSR	296-14113-1-ND	Hex Non-Inverting Buffer/Converter	16-SOP	.66 .47 .40	
CD4050BNSR	296-14113-2-ND	Hex Non-Inverting Buffer/Converter	16-SOP	374.80/2,000	
CD4051BE	296-2057-5-ND	8-Channel Analog Mux/Demux	16-Dip	.62 .46 .39	
CD4051BM	296-25947-5-ND	8-Channel Analog Mux/Demux* <b>NEW!</b>	16-SOIC	.63 .47 .40	
CD4051BM96	296-14271-1-ND	8-Channel Analog Mux/Demux	16-SOIC	.61 .43 .37	
CD4051BM96	296-14271-2-ND	8-Channel Analog Mux/Demux	16-SOIC	426.42/2,500	
CD4051BNSR	296-14115-1-ND	8-Channel Analog Mux/Demux	16-SOP	.66 .47 .40	
CD4051BNSR	296-14115-2-ND	8-Channel Analog Mux/Demux	16-SOP	374.80/2,000	
CD4051BPWR	296-11993-1-ND	8-Channel Analog Mux/Demux	16-TSSOP	.61 .43 .37	
CD4051BPWR	296-11993-2-ND	8-Channel Analog Mux/Demux	16-TSSOP	341.14/2,000	
CD4052BE	296-2058-5-ND	4-Channel Analog Mux/Demux	16-Dip	.62 .46 .39	
CD4052BM	296-25949-5-ND	4-Ch. Analog Mux/Demux* <b>NEW!</b>	16-SOIC	.63 .47 .40	
CD4052BM96	296-14272-1-ND	4-Channel Analog Mux/Demux	16-SOIC	.61 .43 .37	
CD4052BM96	296-14272-2-ND	4-Channel Analog Mux/Demux	16-SOIC	426.42/2,500	
CD4052BPWR	296-14273-1-ND	4-Channel Analog Mux/Demux	16-TSSOP	.61 .43 .37	
CD4052BPWR	296-14273-2-ND	4-Channel Analog Mux/Demux	16-TSSOP	341.14/2,000	
CD4053BE	296-2059-5-ND	Triple 2-Channel Analog Mux/Demux	16-Dip	.62 .46 .39	
CD4053BM	296-25950-5-ND	Triple 2-Channel Analog Mux/Demux* <b>NEW!</b>	16-SOIC	.63 .47 .40	
CD4053BM96	296-14274-1-ND	Triple 2-Channel Analog Mux/Demux	16-SOIC	.61 .43 .37	
CD4053BM96	296-14274-2-ND	Triple 2-Channel Analog Mux/Demux	16-SOIC	426.42/2,500	
CD4053BPWR	296-14117-1-ND	Triple 2-Channel Analog Mux/Demux	16-TSSOP	.61 .43 .37	
CD4053BPWR	296-14117-2-ND	Triple 2-Channel Analog Mux/Demux	16-TSSOP	341.14/2,000	
CD4054BE	296-3514-5-ND	CMOS 4-Segment LCD Driver	16-Dip	.62 .46 .39	
CD4055BE	296-14275-5-ND	BCD to 7-Segment Decoder/Driver	16-Dip	.66 .49 .42	
CD4056BE	296-14118-5-ND	BCD to 7-Segment Decoder/Driver	16-Dip	.66 .49 .42	
CD4059AE	296-3515-5-ND	CMOS Prog. Divide-by-N Counter	24-Dip	4.08 3.29 3.00	
CD4060BE	296-2060-5-ND	14-Stage Ripple Counter/Divider and Oscillator	16-Dip	.62 .46 .39	
CD4060BPWR	296-14119-1-ND	14-Stage Ripple Counter/Divider and Oscillator	16-TSSOP	.61 .43 .37	
CD4060BPWR	296-14119-2-ND	14-Stage Ripple Counter/Divider and Oscillator	16-TSSOP	341.14/2,000	
CD4063BE	296-14120-5-ND	8-Bit Magnitude Comparator	16-Dip	.62 .46 .39	
CD4066BE	296-2061-5-ND	Quad Bilateral Switch	14-Dip	.57 .42 .37	
CD4066BM	296-3516-5-ND	Quad Bilateral Switch	14-SOIC	.61 .45 .39	
CD4066BM96	296-14475-1-ND	Quad Bilateral Switch	14-SOIC	.58 .42 .36	
CD4066BM96	296-14475-2-ND	Quad Bilateral Switch	14-SOIC	412.39/2,500	
CD4066BNSR	296-14122-1-ND	Quad Bilateral Switch	14-SOP	.65 .46 .39	
CD4066BNSR	296-14122-2-ND	Quad Bilateral Switch	14-SOP	365.82/2,000	
CD4066BPWR	296-25952-5-ND	Quad Bilateral Switch* <b>NEW!</b>	14-TSSOP	.61 .45 .39	
CD4066BPWR	296-14123-1-ND	Quad Bilateral Switch	14-TSSOP	.58 .42 .36	
CD4066BPWR	296-14123-2-ND	Quad Bilateral Switch	14-TSSOP	329.92/2,000	
CD4067BE	296-3517-5-ND	Single 16-Channel Analog Mux/Demux	24-Dip	1.56 1.25 1.09	
CD4068BE	296-14124-5-ND	8-Input NAND/AND Gate	14-Dip	.57 .42 .37	
CD4068BM96	296-15355-1-ND	8-Input NAND/AND Gate	14-SOIC	.58 .42 .36	
CD4068BM96	296-15355-2-ND	8-Input NAND/AND Gate	14-SOIC	412.39/2,500	
CD4068BNSR	296-14125-1-ND	8-Input NAND/AND Gate	14-SOP	.65 .46 .39	
CD4068BNSR	296-14125-2-ND	8-Input NAND/AND Gate	14-SOP	365.82/2,000	
CD4069UBE	296-3518-5-ND	Hex Inverter	14-Dip	.57 .42 .37	
CD4069UBM	296-3519-5-ND	Hex Inverter	14-SOIC	.61 .45 .39	
CD4069UBM96	296-14476-1-ND	Hex Inverter	14-SOIC	.58 .42 .36	
CD4070BE	296-14128-5-ND	Quad Exclusive OR Gate	14-Dip	.57 .42 .37	
CD4070BM	296-14276-5-ND	Quad Exclusive OR Gate	14-SOIC	.61 .45 .39	
CD4071BE	296-2062-5-ND	Quad 2-Input OR Gate	14-Dip	.57 .42 .37	
CD4071BM	296-14278-5-ND	Quad 2-Input OR Gate	14-SOIC	.61 .45 .39	
CD4071BM96	296-25953-1-ND	Quad 2-Input OR Gate* <b>NEW!</b>	14-SOIC	.58 .42 .36	
CD4071BM96	296-25953-2-ND	Quad 2-Input OR Gate* <b>NEW!</b>	14-SOIC	412.39/2,500	
CD4071BNSR	296-14130-1-ND	Quad 2-Input OR Gate	14-SOP	.65 .46 .39	
CD4071BNSR	296-14130-2-ND	Quad 2-Input OR Gate	14-SOP	365.82/2,000	
CD4071BPWR	296-14131-5-ND	Quad 2-Input OR Gate	14-TSSOP	.61 .45 .39	
CD4071BPWR	296-24349-1-ND	Quad 2-Input OR Gate* <b>NEW!</b>	14-TSSOP	.58 .42 .36	
CD4071BPWR	296-24349-2-ND	Quad 2-Input OR Gate* <b>NEW!</b>	14-TSSOP	329.92/2,000	
CD4072BE	296-2063-5-ND	Dual 4-Input OR Gate	14-Dip	.57 .42 .37	
CD4072BM	296-25954-5-ND	Dual 4-Input OR Gate* <b>NEW!</b>	14-SOIC	.61 .45 .39	
CD4072BNSR	296-14132-1-ND	Dual 4-Input OR Gate	14-SOP	.65 .46 .39	
CD4072BNSR	296-14132-2-ND	Dual 4-Input OR Gate	14-SOP	365.82/2,000	
CD4073BE	296-2064-5-ND	Triple 3-Input AND Gate	14-Dip	.57 .42 .37	
CD4073BM	296-3520-5-ND	Triple 3-Input AND Gate	14-SOIC	.61 .45 .39	
CD4073BPWR	296-14134-1-ND	Triple 3-Input AND Gate	14-TSSOP	.58 .42 .36	
CD4075BE	296-2065-5-ND	Triple 3-Input OR Gate	14-Dip	.57 .42 .37	
CD4075BM	296-14279-5-ND	Triple 3-Input OR Gate	14-SOIC	.61 .45 .39	
CD4075BNSR	296-14136-1-ND	Triple 3-Input OR Gate	14-SOP	.65 .46 .39	
CD4075BNSR	296-14136-2-ND	Triple 3-Input OR Gate	14-SOP	365.82/2,000	
CD4076BE	296-14137-5-ND	4-Bit D-Type Register	16-Dip	.62 .46 .39	
CD4077BE	296-13771-5-ND	CMOS Quad Exclusive NOR Gate	14-Dip	.57 .42 .37	
CD4077BM	296-9406-5-ND	CMOS Quad Exclusive NOR Gate	14-SOIC	.61 .45 .39	
CD4078BE	296-3521-5-ND	8-Input NOR/OR Gate	14-Dip	.57 .42 .37	
CD4078BM	296-14138-5-ND	8-Input NOR/OR Gate	14-SOIC	.61 .45 .39	
CD4078BNSR	296-14139-1-ND	8-Input NOR/OR Gate	14-SOP	.65 .46 .39	
CD4081BE	296-2066-5-ND	Quad 2-Input AND Gate	14-Dip	.57 .42 .37	
CD4081BM	296-14280-5-ND	Quad 2-Input AND Gate	14-SOIC	.61 .45 .39	
CD4081BM96	296-25955-1-ND	Quad 2-Input AND Gate* <b>NEW!</b>	14-SOIC	.58 .42 .36	
CD4081BM96	296-25955-2-ND	Quad 2-Input AND Gate* <b>NEW!</b>	14-SOIC	412.39/2,500	
CD4081BNSR	296-14140-1-ND	Quad 2-Input AND Gate	14-SOP	.65 .46 .39	
CD4081BNSR	296-14140-2-ND	Quad 2-Input AND Gate	14-SOP	365.82/2,000	
CD4081BPWR	296-14141-1-ND	Quad 2-Input AND Gate	14-TSSOP	.58 .42 .36	
CD4081BPWR	296-14141-2-ND	Quad 2-Input AND Gate	14-TSSOP	329.92/2,000	
CD4082BE	296-2067-5-ND	Dual 4-Input AND Gate	14-Dip	.57 .42 .37	
CD4085BE	296-3522-5-ND	Dual 2-Wide/2-In AND/OR Invert Gate	14-Dip	.57 .42 .37	
CD4085BPWR	296-14143-1-ND	Dual 2-Wide/2-In AND/OR Invert Gate	14-TSSOP	1.62 1.28 1.16	

TEXAS INSTRUMENTS DigiKey Reel (Cont.)		DIGITAL LOGIC			
		RoHS Compliant Parts Available			
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*	
				1	25 100
CD4086BE	296-14281-5-ND	Expandable 4-Wide/2-Input AND/OR Invert Gate	14-Dip	1.54 1.24 1.08	
CD4089BE	296-2165-5-ND	Binary Rate Multiplier	16-Dip	.62 .46 .39	
CD4089BPWR	296-3523-1-ND	Binary Rate Multiplier	16-TSSOP	.61 .43 .37	
CD4093BE	296-2088-5-ND	Quad 2-Input NAND Schmitt Trigger	14-Dip	.57 .42 .37	
CD4093BM96	296-3524-5-ND	Quad 2-Input NAND Schmitt Trigger	14-SOIC	.61 .45 .39	
CD4093BM96	296-25956-1-ND	Quad 2-Input NAND Schmitt Trigger* <b>NEW!</b>	14-SOIC	.58 .42 .36	
CD4093BM96	296-25956-2-ND	Quad 2-Input NAND Schmitt Trigger* <b>NEW!</b>	14-SOIC	412.39/2,500	
CD4093BNSR	296-14145-1-ND	Quad 2-Input NAND Schmitt Trigger	14-SOP	.65 .46 .39	
CD4093BNSR	296-14145-2-ND	Quad 2-Input NAND Schmitt Trigger	14-SOP	365.82/2,000	
CD4093BPWR	296-14146-5-ND	Quad 2-Input NAND Schmitt Trigger	14-TSSOP	.61 .45 .39	
CD4093BPWR	296-13873-1-ND	Quad 2-Input NAND Schmitt Trigger	14-TSSOP	.58 .42 .36	
CD4093BPWR	296-13873-2-ND	Quad 2-Input NAND Schmitt Trigger	14-TSSOP	329.92/2,000	
CD4093BPM96G401	296-24699-1-ND	Quad 2-Input NAND Schmitt Trigger* <b>NEW!</b>	14-SOIC	.64 .45 .39	
CD4093BPM96G401	296-24699-2-ND	Quad 2-Input NAND Schmitt Trigger* <b>NEW!</b>	14-SOIC	451.67/2,500	
CD4094BE	296-2069-5-ND	8-Bit Shift Register with Latch	16-Dip	.62 .46 .39	
CD4094BPWR	296-13860-1-ND	8-Bit Shift Register with Latch	16-TSSOP	.61 .43 .37	
CD4094BPWR	296-13860-2-ND	8-Bit Shift Register with Latch	16-TSSOP	341.14/2,000	
CD4097BE	296-3525-5-ND	Diff. 8-Channel Analog Mux/Demux	24-Dip	1.56 1.25 1.09	
CD4098BE	296-3526-5-ND	Dual Monostable Multivibrator	16-Dip	.66 .49 .42	
CD4098BM	296-16736-5-ND	Dual Monostable Multivibrator	16-SOIC	.67 .50 .43	
CD4098BE	296-2070-5-ND	8-Bit Addressable Latch	16-Dip	.66 .49 .42	
CD4098BPWR	296-9407-1-ND	8-Bit Addressable Latch	16-TSSOP	.66 .47 .40	
CD4502BE	296-2166-5-ND	CMOS Strobed Hex Inverter/Buffer	16-Dip	.66 .49 .42	
CD4502BM	296-25958-5-ND	CMOS Strobed Hex Inverter/Buffer* <b>NEW!</b>	16-SOIC	.67 .50 .43	
CD4503BE	296-2071-5-ND	Tri-State Hex Buffer	16-Dip	.66 .49 .42	
CD4504BE	296-3527-5-ND	Hex Voltage-Level Shifter	16-Dip	.66 .49 .42	
CD4504BM	296-25959-5-ND	Hex Voltage-Level Shifter* <b>NEW!</b>	16-SOIC	.67 .50 .43	
CD4504BM96	296-14150-1-ND	Hex Voltage-Level Shifter	16-SOIC	.66 .47 .40	
CD4504BM96	296-14150-2-ND	Hex Voltage-Level Shifter	16-SOIC	468.50/2,500	
CD4504BPW	296-23203-5-ND	Hex Voltage-Level Shifter	16-TSSOP	.67 .50 .43	
CD4508BE	296-14151-5-ND	Dual 4-Bit Latch	24-Dip	1.60 1.29 1.13	
CD4510BPWR	296-14153-1-ND	BCD Presettable Up/Down Counter	16-TSSOP	.66 .47 .40	
CD4510BPWR	296-14153-2-ND	BCD Presettable Up/Down Counter	16-TSSOP	374.80/2,000	
CD4511BE	296-2072-5-ND	BCD-to-7 Segment LED Latch/Decoder/Driver	16-Dip	.66 .49 .42	
CD4511BNSR	296-3528-1-ND	BCD-to-7 Segment LED Latch/Decoder/Driver	16-SOP	.73 .51 .44	
CD4511BNSR	296-3528-2-ND	BCD-to-7 Segment LED Latch/Decoder/Driver	16-SOP	410.71/2,000	
CD4512BE	296-2073-5-ND	8-Channel Data Selector	16-Dip	.66 .49 .42	
CD4512BM96	296-16676-1-ND	8-Channel Data Selector	16-SOIC	.66 .47 .40	
CD4512BM96	296-16676-2-ND	8-Channel Data Selector	16-SOIC	468.50/2,500	
CD4514BE	296-2074-5-ND	4-Bit Latch/Line Decoder	24-Dip	1.40 1.13 .99	
CD4514BM	296-14282-5-ND	4-Bit Latch/Line Decoder	24-SOIC	.67 .50 .43	
CD4515BE	296-2168-5-ND	4-Bit Latch/Line Decoder	24-Dip	1.40 1.13 .99	
CD4515BM	296-14284-5-ND	4-Bit Latch/Line Decoder	24-SOIC	.67 .50 .43	
CD4516BE	296-2075-5-				