

TEXAS INSTRUMENTS		DIGI [®] Key [®] (Cont.)		DIGITAL LOGIC		RoHS Compliant Parts Available	
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*			
				1	25	100	
CD74AC244M96	296-14479-2-ND	Tri-State Non-Inverting Octal Buffer/Line Driver	20-SOIC	650.85/2,000			
CD74AC245M96	296-14480-1-ND	Tri-State Non-Inverting Octal Bus Transceiver	20-SOIC	1.13	.88	.78	
CD74AC245M96	296-14480-2-ND	Tri-State Non-Inverting Octal Bus Transceiver	20-SOIC	748.48/2,000			
CD74AC253M	296-4242-5-ND	Tri-State Dual 4-Input Mux	16-SOIC	1.02	.80	.70	
CD74AC257M	296-4243-5-ND	Tri-State Quad 2-Input Mux	16-SOIC	1.22	.99	.86	
CD74AC273E	296-1378-5-ND	Octal D-Type Flip-Flop with Reset	20-Dip	1.08	.87	.76	
CD74AC273M	296-25963-5-ND	Octal D-Type F/F with Reset NEW!	20-SOIC	1.18	.95	.83	
CD74AC280E	296-4245-5-ND	9-Bit Odd/Even Parity-Generator/Checker	14-Dip	1.09	.85	.74	
CD74AC373M96	296-14482-1-ND	Tri-State Octal Transparent Latch	20-SOIC	1.13	.88	.78	
CD74AC374M	296-9411-5-ND	Tri-State Octal D-Type Flip-Flop	20-SOIC	1.09	.87	.76	
CD74AC541E	296-4248-5-ND	Tri-State Octal Buffer/Line Driver	20-Dip	.99	.77	.67	
CD74AC541M	296-25965-5-ND	Tri-St. Octal Buffer/Line Dvr. NEW!	20-SOIC	1.08	.84	.73	
CD74AC541M96	296-16677-1-ND	Tri-State Octal Buffer/Line Driver	20-SOIC	.99	.77	.68	
CD74AC541M96	296-16677-2-ND	Tri-State Octal Buffer/Line Driver	20-SOIC	650.85/2,000			
CD74AC573E	296-1379-5-ND	Octal Transparent Latch	20-Dip	1.00	.80	.70	
CD74AC573M96	296-14483-1-ND	Octal Transparent Latch	20-SOIC	1.13	.88	.78	
SN74AC00D	296-1052-5-ND	Quad 2-Input NAND Gate	14-SOIC	1.64	.48	.41	
SN74AC00DR	296-1052-1-ND	Quad 2-Input NAND Gate	14-SOIC	.62	.44	.38	
SN74AC00D	296-1052-2-ND	Quad 2-Input NAND Gate	14-SOIC	434.84/2,500			
SN74AC00N	296-4287-5-ND	Quad 2-Input NAND Gate	14-Dip	.58	.44	.38	
SN74AC00PWR	296-4288-1-ND	Quad 2-Input NAND Gate	14-TSSOP	.62	.44	.38	
SN74AC00PWR	296-4288-2-ND	Quad 2-Input NAND Gate	14-TSSOP	347.87/2,000			
SN74AC04D	296-1053-5-ND	Hex Inverter	14-SOIC	1.64	.48	.41	
SN74AC04DR	296-1053-1-ND	Hex Inverter	14-SOIC	.62	.44	.38	
SN74AC04D	296-1053-2-ND	Hex Inverter	14-SOIC	434.84/2,500			
SN74AC04DBR	296-4289-1-ND	Hex Inverter	14-TSSOP	.68	.48	.41	
SN74AC04MDREP	296-18122-1-ND	Hex Inverter	14-SOIC	1.96	1.52	1.38	
SN74AC04N	296-4290-5-ND	Hex Inverter	14-Dip	.58	.44	.38	
SN74AC04PWR	296-1054-1-ND	Hex Inverter	14-TSSOP	.62	.44	.38	
SN74AC04PWR	296-1054-2-ND	Hex Inverter	14-TSSOP	347.87/2,000			
SN74AC08DR	296-1055-1-ND	Quad 2-Input AND Gate	14-SOIC	.56	.39	.34	
SN74AC08DR	296-1055-2-ND	Quad 2-Input AND Gate	14-SOIC	392.76/2,500			
SN74AC08MDREP	296-22248-1-ND	Quad 2-Input AND Gate	14-SOIC	2.04	1.62	1.46	
SN74AC08PWR	296-4292-1-ND	Quad 2-Input AND Gate	14-TSSOP	.56	.39	.34	
SN74AC08PWR	296-4292-2-ND	Quad 2-Input AND Gate	14-TSSOP	314.20/2,000			
SN74AC10DR	296-4294-1-ND	Triple 3-Input NAND Gate	14-SOIC	.62	.44	.38	
SN74AC11D	296-4297-5-ND	Triple 3-Input AND Gate	14-SOIC	.71	.52	.45	
SN74AC11DR	296-4297-1-ND	Triple 3-Input AND Gate	14-SOIC	.68	.48	.41	
SN74AC11PWR	296-4298-1-ND	Triple 3-Input AND Gate	14-TSSOP	.68	.48	.41	
SN74AC11PWR	296-4298-2-ND	Triple 3-Input AND Gate	14-TSSOP	383.78/2,000			
SN74AC14D	296-4300-5-ND	Hex Schmitt-Trigger Inverter	14-SOIC	.57	.43	.37	
SN74AC14DR	296-4300-1-ND	Hex Schmitt-Trigger Inverter	14-SOIC	.56	.39	.34	
SN74AC14DR	296-4300-2-ND	Hex Schmitt-Trigger Inverter	14-SOIC	392.76/2,500			
SN74AC14N	296-4301-5-ND	Hex Schmitt-Trigger Inverter	14-Dip	.53	.39	.34	
SN74AC14PWR	296-4302-1-ND	Hex Schmitt-Trigger Inverter	14-TSSOP	.56	.39	.34	
SN74AC14PWR	296-4302-2-ND	Hex Schmitt-Trigger Inverter	14-TSSOP	314.20/2,000			
SN74AC32D	296-1059-5-ND	Quad 2-Input OR Gate	14-SOIC	1.64	.48	.41	
SN74AC32DR	296-4317-1-ND	Quad 2-Input OR Gate	14-TSSOP	.68	.48	.41	
SN74AC32MDREP	296-22252-1-ND	Quad 2-Input OR Gate	14-SOIC	1.96	1.52	1.38	
SN74AC32N	296-4318-5-ND	Quad 2-Input OR Gate	14-Dip	.58	.44	.38	
SN74AC32PWR	296-4319-1-ND	Quad 2-Input OR Gate	14-TSSOP	.62	.44	.38	
SN74AC32PWR	296-4319-2-ND	Quad 2-Input OR Gate	14-TSSOP	347.87/2,000			
SN74AC74D	296-1063-5-ND	Dual Positive-Edge-Triggered D-Type Flip-Flop with Clear and Preset	14-SOIC	.64	.48	.41	
SN74AC74DR	296-1063-1-ND	Dual Positive-Edge-Triggered D-Type Flip-Flop with Clear and Preset	14-SOIC	.62	.44	.38	
SN74AC74DR	296-1063-2-ND	Dual Positive-Edge-Triggered D-Type Flip-Flop with Clear and Preset	14-SOIC	434.84/2,500			
SN74AC74MDREP	296-18123-1-ND	Dual Positive-Edge-Triggered D-Type Flip-Flop with Clear and Preset	14-SOIC	2.20	1.70	1.54	
SN74AC74N	296-4342-5-ND	Dual Positive-Edge-Triggered D-Type Flip-Flop with Clear and Preset	14-Dip	.58	.44	.38	
SN74AC74PWR	296-1064-1-ND	Dual Positive-Edge-Triggered D-Type Flip-Flop with Clear and Preset	14-TSSOP	.62	.44	.38	
SN74AC74PWR	296-1064-2-ND	Dual Positive-Edge-Triggered D-Type Flip-Flop with Clear and Preset	14-TSSOP	347.87/2,000			
SN74AC86D	296-4343-5-ND	Quad 2-Input Exclusive OR Gate	14-SOIC	1.64	.48	.41	
SN74AC86DBR	296-4344-1-ND	Quad 2-Input Exclusive OR Gate	14-TSSOP	.68	.48	.41	
SN74AC86N	296-4345-5-ND	Quad 2-Input Exclusive OR Gate	14-Dip	.58	.44	.38	
SN74AC86PWR	296-4346-1-ND	Quad 2-Input Exclusive OR Gate	14-TSSOP	.62	.44	.38	
SN74AC86PWR	296-4346-2-ND	Quad 2-Input Exclusive OR Gate	14-TSSOP	347.87/2,000			
SN74AC240DBR	296-4306-1-ND	Tri-State Octal Buffer/Line Driver	20-TSSOP	.98	.76	.67	
SN74AC240DWR	296-4304-5-ND	Tri-State Octal Buffer/Line Driver	20-SOIC	.97	.76	.66	
SN74AC240DWR	296-14686-1-ND	Tri-State Octal Buffer/Line Driver	20-SOIC	.89	.69	.61	
SN74AC240DWR	296-14686-2-ND	Tri-State Octal Buffer/Line Driver	20-SOIC	585.77/2,000			
SN74AC240N	296-4305-5-ND	Tri-State Octal Buffer/Line Driver	20-Dip	.89	.69	.60	
SN74AC240PWR	296-4306-1-ND	Tri-State Octal Buffer/Line Driver	20-TSSOP	.89	.69	.61	
SN74AC240PWR	296-4306-2-ND	Tri-State Octal Buffer/Line Driver	20-TSSOP	585.77/2,000			
SN74AC241DWR	296-4307-1-ND	Tri-State Octal Buffer/Line Driver	20-TSSOP	.92	.72	.63	
SN74AC241DWR	296-1056-5-ND	Tri-State Octal Buffer/Line Driver	20-SOIC	.92	.71	.62	
SN74AC241DWR	296-1056-1-ND	Tri-State Octal Buffer/Line Driver	20-SOIC	.84	.65	.58	
SN74AC241DWR	296-1056-2-ND	Tri-State Octal Buffer/Line Driver	20-SOIC	553.22/2,000			
SN74AC241N	296-4308-5-ND	Tri-State Octal Buffer/Line Driver	20-Dip	.84	.66	.57	
SN74AC241PWR	296-4309-1-ND	Tri-State Octal Buffer/Line Driver	20-TSSOP	.84	.65	.58	
SN74AC244DBR	296-4310-1-ND	Tri-State Octal Buffer/Line Driver	20-TSSOP	1.19	.93	.82	
SN74AC244DWR	296-1057-1-ND	Tri-State Octal Buffer/Line Driver	20-SOIC	1.09	.84	.75	
SN74AC244PWR	296-1057-2-ND	Tri-State Octal Buffer/Line Driver	20-SOIC	715.94/2,000			
SN74AC244MDWREP	296-22250-1-ND	Tri-State Octal Buffer/Line Driver	20-SOIC	3.77	3.08	2.77	
SN74AC244N	296-4311-5-ND	Tri-State Octal Buffer/Line Driver	20-Dip	1.09	.85	.74	
SN74AC244NSR	296-4312-1-ND	Tri-State Octal Buffer/Line Driver	20-Dip	1.19	.93	.82	
SN74AC244NSR	296-4312-2-ND	Tri-State Octal Buffer/Line Driver	20-SOP	787.76/2,000			
SN74AC245DBR	296-4314-1-ND	Tri-State Octal Bus Transceiver	20-TSSOP	1.19	.93	.82	
SN74AC245DWR	296-1058-5-ND	Tri-State Octal Bus Transceiver	20-SOIC	1.03	.83	.73	
SN74AC245DWR	296-1058-1-ND	Tri-State Octal Bus Transceiver	20-SOIC	1.09	.84	.75	
SN74AC245DWR	296-1058-2-ND	Tri-State Octal Bus Transceiver	20-SOIC	715.94/2,000			
SN74AC245N	296-4315-5-ND	Tri-State Octal Bus Transceiver	20-Dip	1.09	.85	.74	
SN74AC245PWR	296-4316-1-ND	Tri-State Octal Bus Transceiver	20-TSSOP	1.09	.84	.75	
SN74AC245PWR	296-4316-2-ND	Tri-State Octal Bus Transceiver	20-TSSOP	715.94/2,000			
SN74AC373DBR	296-4320-1-ND	Tri-St. Octal D-Type Transparent Latch	20-TSSOP	1.19	.93	.82	

TEXAS INSTRUMENTS		DIGI [®] Key [®] (Cont.)		DIGITAL LOGIC		RoHS Compliant Parts Available	
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*			
				1	25	100	
SN74AC373DWR	296-4321-1-ND	Tri-St. Octal D-Type Transparent Latch	20-SOIC	1.09	.84	.75	
SN74AC373DWR	296-4321-2-ND	Tri-St. Octal D-Type Transparent Latch	20-SOIC	715.94/2,000			
SN74AC373MDWREP	296-22253-1-ND	Tri-St. Octal D-Type Transparent Latch	20-SOIC	3.77	3.08	2.77	
SN74AC373N	296-26376-5-ND	Tri-St. Octal D-Type Transparent Latch	20-Dip	1.09	.85	.74	
SN74AC373MSR	296-4322-1-ND	Tri-St. Octal D-Type Transparent Latch	20-SOP	1.19	.93	.82	
SN74AC374DWR	296-1060-1-ND	Tri-State Octal D-Type Flip-Flop	20-SOIC	.99	.77	.68	
SN74AC374DWR	296-1060-2-ND	Tri-State Octal D-Type Flip-Flop	20-SOIC	650.85/2,000			
SN74AC374DWR	296-4327-5-ND	Tri-St. Octal D-Type Transparent Latch	20-SOIC	2.09	1.69	1.52	
SN74AC374DBR	296-4329-1-ND	Tri-State Octal D-Type Flip-Flop	20-TSSOP	.98	.76	.67	
SN74AC374DWR	296-4330-5-ND	Tri-State Octal D-Type Flip-Flop	20-SOIC	.97	.76	.66	
SN74AC374N	296-4331-5-ND	Tri-State Octal D-Type Flip-Flop	20-Dip	.89	.69	.60	
SN74AC374DWR	296-4334-5-ND	Tri-St. Octal D-Type Transparent Latch	20-SOIC	1.89	1.51	1.32	
SN74AC374DWR	296-4336-5-ND	Tri-State Octal D-Type Flip-Flop	20-SOIC	2.44	1.97	1.77	
SN74AC373DBR	296-4337-1-ND	Tri-St. Octal D-Type Transparent Latch	20-TSSOP	1.09	.84	.75	
SN74AC373DBR	296-4337-2-ND	Tri-St. Octal D-Type Transparent Latch	20-TSSOP	715.94/2,000			
SN74AC373DWR	296-1061-5-ND	Tri-St. Octal D-Type Transparent Latch	20-SOIC	1.08	.84	.73	
SN74AC373DWR	296-1061-1-ND	Tri-St. Octal D-Type Transparent Latch	20-SOIC	.99	.77	.68	
SN74AC373DWR	296-1061-2-ND	Tri-St. Octal D-Type Transparent Latch	20-SOIC	650.85/2,000			
SN74AC373PWR	296-4338-1-ND	Tri-State Octal D-Type Transp. Latch	20-TSSOP	.99	.77	.68	
SN74AC373PWR	296-4338-2-ND	Tri-State Octal D-Type Transp. Latch	20-TSSOP	650.85/2,000			
SN74AC374DBR	296-4339-1-ND	Tri-State Octal D-Type Flip-Flop	20-TSSOP	1.09	.84	.75	
SN74AC374DWR	296-1062-5-ND	Tri-State Octal D-Type Flip-Flop	20-SOIC	1.08	.84	.73	
SN74AC374DWR	296-1062-1-ND	Tri-State Octal D-Type Flip-Flop	20-SOIC	.99	.77	.68	
SN74AC374DWR	296-1062-2-ND	Tri-State Octal D-Type Flip-Flop	20-SOIC	650.85/2,000			
SN74AC374PWR	296-4340-1-ND	Tri-State Octal D-Type Flip-Flop	20-TSSOP	.99	.77	.68	
SN74AC374PWR	296-4340-2-ND	Tri-State Octal D-Type Flip-Flop	20-TSSOP	650.85/2,000			
ACT Family							
74ACT11000DR	296-14295-1-ND	Quad 2-Input NAND Gate	16-SOIC	2.95	2.28	2.07	
74ACT11000DR	296-14295-2-ND	Quad 2-Input NAND Gate	16-SOIC	2841.87/2,500			
74ACT11004DWR	296-4177-5-ND	Hex Inverter	20-SOIC	3.13	2.53	2.28	
74ACT11008D	296-4178-5-ND	Quad 2-Input AND Gate	16-SOIC	3.13	2.53	2.28	
74ACT11008N	296-4179-5-ND	Quad 2-Input AND Gate	16-Dip	2.78	2.25	2.02	
74ACT11030DR	296-4180-1-ND	8-Input NAND Gate	14-SOIC	2.95	2.28	2	