

Texas Instruments Digi+Reel® (Cont.)			DIGITAL LOGIC			
RoHS Compliant Parts Available			RoHS Compliant Parts Available			
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each★		
				1	25	100
SN74HC368N	296-8308-5-ND	Tri-State Hex Buffer/Line Driver	16-Dip	.76	.57	.49
SN74HC368PWR	296-25440-1-ND	Tri-St. Hex Buffer/Line Driver * NEW!	16-TSSOP	.81	.57	.49
SN74HC368PWR	296-25440-2-ND	Tri-St. Hex Buffer/Line Driver * NEW!	16-TSSOP	453.35/2,000		
SN74HC373DBR	296-8309-1-ND	Tri-St. Octal Transparent D-Type Latch	20-SSOP	.72	.51	.43
SN74HC373DBR	296-8309-2-ND	Tri-St. Octal Transparent D-Type Latch	20-SSOP	403.98/2,000		
SN74HC373DWR	296-1200-5-ND	Tri-St. Octal Transparent D-Type Latch	20-SOIC	.67	.50	.43
SN74HC373DWR	296-1200-1-ND	Tri-St. Octal Transparent D-Type Latch	20-SOIC	.65	.46	.39
SN74HC373DWR	296-1200-2-ND	Tri-St. Octal Transparent D-Type Latch	20-SOIC	365.82/2,000		
SN74HC373N	296-8310-5-ND	Tri-St. Octal Transparent D-Type Latch	20-Dip	.62	.46	.40
SN74HC373NSR	296-8310-1-ND	Tri-St. Octal Transparent D-Type Latch	20-SOP	.72	.51	.43
SN74HC373NSR	296-8310-2-ND	Tri-St. Octal Transparent D-Type Latch	20-SOP	403.98/2,000		
SN74HC373PWR	296-8311-1-ND	Tri-St. Octal Transparent D-Type Latch	20-TSSOP	.65	.46	.39
SN74HC373PWR	296-8311-2-ND	Tri-St. Octal Transparent D-Type Latch	20-TSSOP	365.82/2,000		
SN74HC374DBR	296-8312-1-ND	Tri-State Octal D-Type Flip-Flop	20-SSOP	.72	.51	.43
SN74HC374DBR	296-8312-2-ND	Tri-State Octal D-Type Flip-Flop	20-SSOP	403.98/2,000		
SN74HC374DWR	296-1201-5-ND	Tri-State Octal D-Type Flip-Flop	20-SOIC	.67	.50	.43
SN74HC374DWR	296-1201-1-ND	Tri-State Octal D-Type Flip-Flop	20-SOIC	.65	.46	.39
SN74HC374DWR	296-1201-2-ND	Tri-State Octal D-Type Flip-Flop	20-SOIC	365.82/2,000		
SN74HC374N	296-1592-5-ND	Tri-State Octal D-Type Flip-Flop	20-Dip	.62	.46	.40
SN74HC374NSR	296-8313-1-ND	Tri-State Octal D-Type Flip-Flop	20-SOP	.72	.51	.43
SN74HC374NSR	296-8313-2-ND	Tri-State Octal D-Type Flip-Flop	20-SOP	403.98/2,000		
SN74HC374PWR	296-8314-1-ND	Tri-State Octal D-Type Flip-Flop	20-TSSOP	.65	.46	.39
SN74HC374PWR	296-8314-2-ND	Tri-State Octal D-Type Flip-Flop	20-TSSOP	365.82/2,000		
SN74HC377DWR	296-9818-5-ND	Octal D-Type Flip-Flop w/ Clock Enable	20-SOIC	.76	.57	.49
SN74HC377DWR	296-9818-1-ND	Octal D-Type Flip-Flop w/ Clock Enable	20-SOIC	.74	.52	.45
SN74HC377DWR	296-9818-2-ND	Octal D-Type Flip-Flop w/ Clock Enable	20-SOIC	417.44/2,000		
SN74HC377N	296-8316-5-ND	Octal D-Type Flip-Flop w/ Clock Enable	20-Dip	.71	.52	.45
SN74HC393D	296-8317-5-ND	Dual 4-Bit Binary Counter	14-SOIC	.64	.48	.41
SN74HC393DBR	296-8318-1-ND	Dual 4-Bit Binary Counter	14-SSOP	.68	.48	.41
SN74HC393DBR	296-8318-2-ND	Dual 4-Bit Binary Counter	14-SSOP	383.78/2,000		
SN74HC393DWR	296-14851-1-ND	Dual 4-Bit Binary Counter	14-SOIC	.62	.44	.38
SN74HC393DWR	296-14851-2-ND	Dual 4-Bit Binary Counter	14-SOIC	434.84/2,500		
SN74HC393N	296-8319-5-ND	Dual 4-Bit Binary Counter	14-Dip	.58	.44	.38
SN74HC504DWR	296-8333-1-ND	Tri-State Octal Buffer/Line Driver	20-SOIC	.81	.57	.49
SN74HC504DWR	296-8333-2-ND	Tri-State Octal Buffer/Line Driver	20-SOIC	453.35/2,000		
SN74HC504N	296-8334-5-ND	Tri-State Octal Buffer/Line Driver	20-Dip	.76	.57	.49
SN74HC510DBR	296-14855-1-ND	Tri-State Octal Buffer/Line Driver	20-SSOP	.89	.62	.53
SN74HC510DBR	296-14855-2-ND	Tri-State Octal Buffer/Line Driver	20-SSOP	498.24/2,000		
SN74HC510DWR	296-1202-5-ND	Tri-State Octal Buffer/Line Driver	20-SOIC	.70	.55	.48
SN74HC510DWR	296-1202-1-ND	Tri-State Octal Buffer/Line Driver	20-SOIC	.81	.57	.49
SN74HC510DWR	296-1202-2-ND	Tri-State Octal Buffer/Line Driver	20-SOIC	453.35/2,000		
SN74HC514N	296-1594-5-ND	Tri-State Octal Buffer/Line Driver	20-Dip	.76	.57	.49
SN74HC514NSR	296-13218-1-ND	Tri-State Octal Buffer/Line Driver	20-SOP	.89	.62	.53
SN74HC514NSR	296-13218-2-ND	Tri-State Octal Buffer/Line Driver	20-SOP	498.24/2,000		
SN74HC514PWR	296-8335-1-ND	Tri-State Octal Buffer/Line Driver	20-TSSOP	.81	.57	.49
SN74HC514PWR	296-8335-2-ND	Tri-State Octal Buffer/Line Driver	20-TSSOP	453.35/2,000		
SN74HC563DWR	296-11838-5-ND	Tri-St. Octal Transparent D-Type Latch * NEW!	20-SOIC	1.65	1.32	1.16
SN74HC573ADB	296-23257-1-ND	Tri-St. Octal Transparent D-Type Latch	20-SSOP	.77	.55	.47
SN74HC573ADBR	296-23257-2-ND	Tri-St. Octal Transparent D-Type Latch	20-SSOP	447.64/2,000		
SN74HC573ADWR	296-1203-5-ND	Tri-St. Octal Transparent D-Type Latch	20-SOIC	.73	.54	.47
SN74HC573ADWR	296-1203-1-ND	Tri-St. Octal Transparent D-Type Latch	20-SOIC	.72	.51	.43
SN74HC573ADWR	296-1203-2-ND	Tri-St. Octal Transparent D-Type Latch	20-SOIC	403.98/2,000		
SN74HC573AN	296-1596-5-ND	Tri-St. Octal Transparent D-Type Latch	20-Dip	.67	.50	.43
SN74HC573APWR	296-8338-1-ND	Tri-St. Octal Transparent D-Type Latch	20-TSSOP	.72	.51	.43
SN74HC573APWR	296-8338-2-ND	Tri-St. Octal Transparent D-Type Latch	20-TSSOP	403.98/2,000		
SN74HC574DWR	296-1597-5-ND	Tri-State Octal D-Type Flip-Flop	20-SOIC	.67	.50	.43
SN74HC574DWR	296-1597-1-ND	Tri-State Octal D-Type Flip-Flop	20-SOIC	.65	.46	.39
SN74HC574DWR	296-1597-2-ND	Tri-State Octal D-Type Flip-Flop	20-SOIC	365.82/2,000		
SN74HC574N	296-1598-5-ND	Tri-State Octal D-Type Flip-Flop	20-Dip	.62	.46	.40
SN74HC574PWR	296-8339-1-ND	Tri-State Octal D-Type Flip-Flop	20-TSSOP	.65	.46	.39
SN74HC574PWR	296-8339-2-ND	Tri-State Octal D-Type Flip-Flop	20-TSSOP	365.82/2,000		
SN74HC590AD	296-8340-5-ND	Tri-State 8-Bit Binary Counter	16-SOIC	.81	.63	.55
SN74HC590ADR	296-17132-1-ND	Tri-State 8-Bit Binary Counter	16-SOIC	.74	.58	.51
SN74HC590ADR	296-17132-2-ND	Tri-State 8-Bit Binary Counter	16-SOIC	610.17/2,500		
SN74HC590ADWR	296-8341-5-ND	Tri-State 8-Bit Binary Counter	16-SOIC	.81	.63	.55
SN74HC594D	296-1599-5-ND	8-Bit Shift Register w/ Output Register * NEW!	16-Dip	.74	.58	.50
SN74HC594D	296-26484-5-ND	8-Bit Shift Register w/ Output Register * NEW!	16-SOIC	.86	.67	.59
SN74HC594DWR	296-8342-5-ND	8-Bit Shift Register w/ Output Register	16-SOIC	.86	.67	.59
SN74HC594N	296-8343-5-ND	8-Bit Shift Register w/ Output Register	16-Dip	.79	.62	.54
SN74HC595D	296-8344-5-ND	Tri-State 8-Bit Shift Register	16-SOIC	.76	.57	.49
SN74HC595DR	296-14857-1-ND	Tri-State 8-Bit Shift Register	16-SOIC	.74	.52	.45
SN74HC595DWR	296-14857-2-ND	Tri-State 8-Bit Shift Register	16-SOIC	521.80/2,500		
SN74HC595DWR	296-8345-5-ND	Tri-State 8-Bit Shift Register	16-SOIC	.76	.57	.49
SN74HC595DWR	296-14858-1-ND	Tri-State 8-Bit Shift Register	16-SOIC	.74	.52	.45
SN74HC595DWR	296-14858-2-ND	Tri-State 8-Bit Shift Register	16-SOIC	417.44/2,000		
SN74HC595N	296-1600-5-ND	Tri-State 8-Bit Shift Register	16-Dip	.71	.52	.45
SN74HC595NSR	296-26485-1-ND	Tri-State 8-Bit Shift Register * NEW!	16-SOP	.82	.58	.49
SN74HC595NSR	296-26485-2-ND	Tri-State 8-Bit Shift Register * NEW!	16-SOP	469.09/2,000		
SN74HC595PWR	296-23258-1-ND	Tri-State 8-Bit Shift Register	16-TSSOP	.74	.52	.45
SN74HC595PWR	296-23258-2-ND	Tri-State 8-Bit Shift Register	16-TSSOP	417.44/2,000		
SN74HC623DWR	296-8346-5-ND	Tri-State Octal Bus Transceiver	20-SOIC	8.84	7.25	6.54
SN74HC623N	296-8347-5-ND	Tri-State Octal Bus Transceiver	20-Dip	8.14	6.68	6.03
SN74HC640DWR	296-8348-5-ND	Tri-State Octal Bus Transceiver	20-SOIC	1.92	1.55	1.39
SN74HC640N	296-8349-5-ND	Tri-State Octal Bus Transceiver	20-Dip	1.94	1.56	1.37
SN74HC645DWR	296-8350-5-ND	Tri-State Octal Bus Transceiver	20-SOIC	1.89	1.51	1.32
SN74HC645N	296-8351-5-ND	Tri-State Octal Bus Transceiver	20-Dip	1.73	1.39	1.21
SN74HC646DWR	296-8352-5-ND	Tri-State Octal Bus Transcvr/Register	24-SOIC	1.89	1.51	1.32
SN74HC646N	296-8353-5-ND	Tri-State Octal Bus Transcvr/Register	24-Dip	1.92	1.55	1.39
SN74HC652DWR	296-8354-5-ND	Tri-State Octal Bus Transcvr/Register	24-SOIC	2.61	2.11	1.90
SN74HC652N	296-8355-5-ND	Tri-State Octal Bus Transcvr/Register	24-Dip	2.96	2.39	2.15
SN74HC682DWR	296-8356-1-ND	8-Bit Magnitude Comparator	20-SOIC	5.05	4.13	3.71
SN74HC682DWR	296-8356-2-ND	8-Bit Magnitude Comparator	20-SOIC	4477.42/2,000		
SN74HC682N	296-8357-5-ND	8-Bit Magnitude Comparator	20-Dip	5.18	4.17	3.80
SN74HC684DWR	296-8358-5-ND	8-Bit Magnitude Comparator	20-SOIC	9.82	8.06	7.27
SN74HC684N	296-8359-5-ND	8-Bit Magnitude Comparator	20-Dip	9.98	7.37	6.65
SN74HC688DWR	296-8360-5-ND	8-Bit Identity Comparator	20-SOIC	1.27	1.02	.90
SN74HC688N	296-8361-5-ND	8-Bit Identity Comparator	20-Dip	1.17	.94	.82
SN74HC688PWR	296-8362-1-ND	8-Bit Identity Comparator	20-TSSOP	1.16	.91	.82
SN74HC688PWR	296-8362-2-ND	8-Bit Identity Comparator	20-TSSOP	848.35/2,000		
SN74HC4020D	296-8320-5-ND	14-Bit Asynchronous Binary Counter	16-SOIC	.73	.57	.50

* RoHS Compliant

★ CALL FOR LOWER PRICING ON LARGER QUANTITIES! ★

(Continued)

Free shipping on orders over \$200 CAD! All prices in Canadian dollars and include duty and brokerage fees.

958 (CA2011) 1-800-344-4539 • www.digikey.ca • 218-681-6674 • Fax: 218-681-3380

Texas Instruments Digi+Reel® (Cont.)			DIGITAL LOGIC			
RoHS Compliant Parts Available			RoHS Compliant Parts Available			
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each★		
				1	25	100
SN74HC4020N	296-8321-5-ND	14-Bit Asynchronous Binary Counter	16-Dip	.80	.59	.51
SN74HC4040D	296-8322-5-ND	12-Bit Asynchronous Binary Counter	16-SOIC	.73	.57	.50
SN74HC4040DBR	296-8323-1-ND	12-Bit Asynchronous Binary Counter	16-SSOP	.92	.65	.56
SN74HC4040DBR	296-8323-2-ND	12-Bit Asynchronous Binary Counter	16-SSOP	518.44/2,000		
SN74HC4040DR	296-14852-1-ND	12-Bit Asynchronous Binary Counter	16-SOIC	.83	.59	.50
SN74HC4040DR	296-14852-2-ND	12-Bit Asynchronous Binary Counter	16-SOIC	587.04/2,500		
SN74HC4040N	296-8324-5-ND	12-Bit Asynchronous Binary Counter	16-Dip	.80	.59	.51
SN74HC4040PWR	296-26480-5-ND	12-Bit Async. Binary Counter * NEW!	16-TSSOP	.73	.57	.50
SN74HC4040PWR	296-8325-1-ND	12-Bit Asynchronous Binary Counter	16-TSSOP	.83	.59	.50
SN74HC4040PWR	296-8325-2-ND	12-Bit Asynchronous Binary Counter	16-TSSOP	469.62/2,000		
SN74HC4060D	296-8326-5-ND	14-Stage Asynchronous Binary Counter and Oscillator	16-SOIC	.75	.59	.51
SN74HC4060DR	296-14853-1-ND	14-Stage Asynchronous Binary Counter and Oscillator	16-SOIC	.86	.61	.52
SN74HC4060DR	296-14853-2-ND	14-Stage Asynchronous Binary Counter and Oscillator	16-SOIC	608.77/2,500		
SN74HC4060N	296-8209-5-ND	14-Stage Asynchronous Binary Counter and Oscillator	16-Dip	.70	.54	.47
SN74HC4066D	296-8327-5-ND	Quad Bilateral Analog Switch	14-SOIC	.64	.48	.41
SN74HC4066DR	296-14854-1-ND	Quad Bilateral Analog Switch	14-SOIC	.62	.44	.38
SN74HC4066DR	296-14854-2-ND	Quad Bilateral Analog Switch	14-SOIC	434.84/2,500		
SN74HC4066N	296-8329-5-ND	Quad Bilateral Analog Switch	14-Dip	.58	.44	.38
SN74HC4066PWR	296-26481-5-ND	Quad Bilateral Analog Switch * NEW!	14-TSSOP	.64	.48	.41
SN74HC4066PWR	296-8330-1-ND	Quad Bilateral Analog Switch	14-TSSOP	.62	.44	.38
SN74HC4066PWR	296-8330-2-ND	Quad Bilateral Analog Switch	14-TSSOP	347.87/2,000		
SN74HC4851DGV	296-19251-1-ND	8-Channel Analog Mux/Demux	16-TVOP	.79	.62	.54
SN74HC4851DGV	296-19251-2-ND	8-Channel Analog Mux/Demux	16-TVOP	520.68/2,000		
SN74HC4851N	296-15741-5-ND	8-Channel Analog Mux/Demux	16-Dip	.79	.62	.54
SN74HC4851PWR	296-16983-1-ND	8-Channel Analog Mux/Demux	16-TSSOP	.79	.62	.54
SN74HC4851PWR	296-169					