

TEXAS INSTRUMENTS		DigiKey (Cont.)		DIGITAL LOGIC		RoHS Compliant Parts Available	
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*	1	25	100
SN74LV245ATDBR	296-17767-1-ND	Tri-State Octal Bus Transceiver	20-SSOP	.68	48	.41	
SN74LV245ATDGR	296-17767-2-ND	Tri-State Octal Bus Transceiver	20-SSOP	383.78/2,000			
SN74LV245ATDWR	296-17768-1-ND	Tri-State Octal Bus Transceiver	20-TSSOP	.62	44	.38	
SN74LV245ATDWR	296-17768-2-ND	Tri-State Octal Bus Transceiver	20-TSSOP	347.87/2,000			
SN74LV245ATDWR	296-17769-1-ND	Tri-State Octal Bus Transceiver	20-TSSOP	.62	44	.38	
SN74LV245ATNSR	296-17770-1-ND	Tri-State Octal Bus Transceiver	20-SOP	68	48	.41	
SN74LV245ATNSR	296-17770-2-ND	Tri-State Octal Bus Transceiver	20-SOP	383.78/2,000			
SN74LV245ATNSR	296-17771-1-ND	Tri-State Octal Bus Transceiver	20-TSSOP	.62	44	.38	
SN74LV245ATNSR	296-17771-2-ND	Tri-State Octal Bus Transceiver	20-TSSOP	347.87/2,000			
SN74LV245ATNSR	296-17772-1-ND	Tri-State Octal Bus Transceiver	20-DFN	68	48	.41	
SN74LV245ATNSR	296-17772-2-ND	Tri-State Octal Bus Transceiver	20-DFN	575.67/3,000			
SN74LV245AZQNR	296-23384-1-ND	Tri-State Octal Bus Transceiver	20-BGA	.74	58	.51	
SN74LV245AZQNR	296-23384-2-ND	Tri-State Octal Bus Transceiver	20-BGA	269.32/1,000			
SN74LV273ADBR	296-12349-1-ND	Octal D-Type Flip-Flop with Clear	20-SSOP	.75	53	.45	
SN74LV273ADBR	296-12349-2-ND	Octal D-Type Flip-Flop with Clear	20-SSOP	421.93/2,000			
SN74LV273ADWR	296-3811-5-ND	Octal D-Type Flip-Flop with Clear	20-SOIC	.71	52	.45	
SN74LV273ADWR	296-14904-1-ND	Octal D-Type Flip-Flop with Clear	20-SOIC	68	48	.41	
SN74LV273ADWR	296-14904-2-ND	Octal D-Type Flip-Flop with Clear	20-SOIC	383.78/2,000			
SN74LV273APWR	296-26550-5-ND	Octal D-Type Flip-Flop with Clear	20-TSSOP	.71	52	.45	
SN74LV273APWR	296-3812-1-ND	Octal D-Type Flip-Flop with Clear	20-TSSOP	68	48	.41	
SN74LV273APWR	296-3812-2-ND	Octal D-Type Flip-Flop with Clear	20-TSSOP	383.78/2,000			
SN74LV273ARGYR	296-13940-1-ND	Octal D-Type Flip-Flop with Clear	20-VQFN	.75	53	.45	
SN74LV273ARGYR	296-13940-2-ND	Octal D-Type Flip-Flop with Clear	20-VQFN	632.90/3,000			
SN74LV367ADGVR	296-13491-1-ND	Tri-State Hex Buffer/Line Driver	16-TVSOIP	1.66	1.32	1.19	
SN74LV367ADGVR	296-13491-2-ND	Tri-State Hex Buffer/Line Driver	16-TVSOIP	1225.40/2,000			
SN74LV367APWR	296-12350-1-ND	Tri-State Hex Buffer/Line Driver	16-TSSOP	1.66	1.32	1.19	
SN74LV367APWR	296-12350-2-ND	Tri-State Hex Buffer/Line Driver	16-TSSOP	1225.40/2,000			
SN74LV373ADGVR	296-23671-1-ND	Tri-St. Octal D-Type Transparent Latch	20-TVSOIP	.68	48	.41	
SN74LV373ADGVR	296-23671-2-ND	Tri-St. Octal D-Type Transparent Latch	20-TVSOIP	383.78/2,000			
SN74LV373ADWR	296-16657-1-ND	Tri-St. Octal D-Type Transparent Latch	20-SOIC	.68	48	.41	
SN74LV373ADWR	296-16657-2-ND	Tri-St. Octal D-Type Transparent Latch	20-SOIC	383.78/2,000			
SN74LV373AGQNR	296-1687-5-ND	Tri-St. Octal D-Type Transparent Latch	20-BGA	.71	52	.45	
SN74LV373AGQNR	296-1688-5-ND	Tri-St. Octal D-Type Transparent Latch	20-BGA	82	63	.56	
SN74LV373APWR	296-14318-1-ND	Tri-St. Octal D-Type Transparent Latch	20-TSSOP	68	48	.41	
SN74LV373APWR	296-14318-2-ND	Tri-St. Octal D-Type Transparent Latch	20-TSSOP	383.78/2,000			
SN74LV373ARGYR	296-13942-1-ND	Tri-St. Octal D-Type Transparent Latch	20-VQFN	.75	53	.45	
SN74LV373ARGYR	296-13942-2-ND	Tri-St. Octal D-Type Transparent Latch	20-VQFN	632.90/3,000			
SN74LV373ATDWR	296-21039-1-ND	Tri-St. Octal D-Type Transparent Latch	20-SOIC	.68	48	.41	
SN74LV373ATDWR	296-21039-2-ND	Tri-St. Octal D-Type Transparent Latch	20-SOIC	383.78/2,000			
SN74LV373ATNSR	296-21040-1-ND	Tri-St. Octal D-Type Transparent Latch	20-SOP	.68	48	.41	
SN74LV373ATNSR	296-21040-2-ND	Tri-St. Octal D-Type Transparent Latch	20-SOP	383.78/2,000			
SN74LV373ATPWR	296-21041-1-ND	Tri-St. Octal D-Type Transparent Latch	20-TSSOP	.68	48	.41	
SN74LV373ATPWR	296-21041-2-ND	Tri-St. Octal D-Type Transparent Latch	20-TSSOP	383.78/2,000			
SN74LV373ATRGYR	296-21042-1-ND	Tri-St. Octal D-Type Transparent Latch	20-VQFN	.68	48	.41	
SN74LV373ATRGYR	296-21042-2-ND	Tri-St. Octal D-Type Transparent Latch	20-VQFN	575.67/3,000			
SN74LV373ADBR	296-12553-1-ND	Tri-St. Octal Edge-Triggered D-Type F/F	20-SSOP	.75	53	.45	
SN74LV373ADBR	296-12553-2-ND	Tri-St. Octal Edge-Triggered D-Type F/F	20-SSOP	421.93/2,000			
SN74LV373ADWR	296-1688-5-ND	Tri-St. Octal Edge-Triggered D-Type F/F	20-TSSOP	.71	52	.45	
SN74LV373AGQNR	296-12093-1-ND	Tri-St. Octal Edge-Triggered D-Type F/F	20-BGA	.82	63	.56	
SN74LV373AGQNR	296-12093-2-ND	Tri-St. Octal Edge-Triggered D-Type F/F	20-BGA	296.25/1,000			
SN74LV3734APW	296-26552-5-ND	Tri-St. Octal Edge-Triggered D-Type F/F	20-TSSOP	.71	52	.45	
SN74LV3734APWR	296-3820-1-ND	Tri-St. Octal Edge-Triggered D-Type F/F	20-TSSOP	.68	48	.41	
SN74LV3734APWR	296-3820-2-ND	Tri-St. Octal Edge-Triggered D-Type F/F	20-TSSOP	383.78/2,000			
SN74LV3734ARGYR	296-13943-1-ND	Tri-St. Octal Edge-Triggered D-Type F/F	20-VQFN	.75	53	.45	
SN74LV3734ARGYR	296-13943-2-ND	Tri-St. Octal Edge-Triggered D-Type F/F	20-VQFN	632.90/3,000			
SN74LV3734ATDBR	296-21043-1-ND	Tri-St. Octal Edge-Triggered D-Type F/F	20-SSOP	.68	48	.41	
SN74LV3734ATDBR	296-21043-2-ND	Tri-St. Octal Edge-Triggered D-Type F/F	20-SSOP	383.78/2,000			
SN74LV3734ATDWR	296-21044-1-ND	Tri-St. Octal Edge-Triggered D-Type F/F	20-SOIC	.68	48	.41	
SN74LV3734ATDWR	296-21044-2-ND	Tri-St. Octal Edge-Triggered D-Type F/F	20-SOIC	383.78/2,000			
SN74LV3734ATNSR	296-21045-1-ND	Tri-St. Octal Edge-Triggered D-Type F/F	20-SOP	.68	48	.41	
SN74LV3734ATNSR	296-21045-2-ND	Tri-St. Octal Edge-Triggered D-Type F/F	20-SOP	383.78/2,000			
SN74LV3734ATPWR	296-21046-1-ND	Tri-St. Octal Edge-Triggered D-Type F/F	20-TSSOP	.68	48	.41	
SN74LV3734ATPWR	296-21046-2-ND	Tri-St. Octal Edge-Triggered D-Type F/F	20-TSSOP	383.78/2,000			
SN74LV3734ATPWREP	296-22312-1-ND	Tri-St. Octal Edge-Triggered D-Type F/F	20-TSSOP	2.04	1.62	1.46	
SN74LV3734ATPWREP	296-22312-2-ND	Tri-St. Octal Edge-Triggered D-Type F/F	20-TSSOP	1508.18/2,000			
SN74LV3734ATPWREP	296-24751-1-ND	Tri-St. Octal Edge-Triggered D-Type F/F	20-TSSOP	.76	54	.46	
SN74LV3734ATPWREP	296-24751-2-ND	Tri-St. Octal Edge-Triggered D-Type F/F	20-TSSOP	428.67/2,000			
SN74LV393ADBR	296-12351-1-ND	Dual 4-Bit Binary Counter	14-SSOP	1.31	1.04	.94	
SN74LV393ADBR	296-12351-2-ND	Dual 4-Bit Binary Counter	14-SSOP	967.30/2,000			
SN74LV393ADGVR	296-13233-1-ND	Dual 4-Bit Binary Counter	14-TVSOIP	1.19	95	.85	
SN74LV393ADGVR	296-13233-2-ND	Dual 4-Bit Binary Counter	14-TVSOIP	879.77/2,000			
SN74LV393ADR	296-11664-1-ND	Dual 4-Bit Binary Counter	14-SOIC	1.19	95	.85	
SN74LV393ADR	296-11664-2-ND	Dual 4-Bit Binary Counter	14-SOIC	1099.72/2,500			
SN74LV393ANSR	296-14192-1-ND	Dual 4-Bit Binary Counter	14-SOIC	1.31	1.04	.94	
SN74LV393ANSR	296-14192-2-ND	Dual 4-Bit Binary Counter	14-SOIC	967.30/2,000			
SN74LV393APWR	296-26553-5-ND	Dual 4-Bit Binary Counter	14-TSSOP	1.32	1.06	.93	
SN74LV393APWR	296-22313-1-ND	Dual 4-Bit Binary Counter	14-TSSOP	2.95	2.28	2.07	
SN74LV393ATPWREP	296-22313-2-ND	Dual 4-Bit Binary Counter	14-TSSOP	2273.50/2,000			
SN74LV393ATPWREP	296-24752-1-ND	Dual 4-Bit Binary Counter	14-TSSOP	1.34	1.06	.96	
SN74LV393ATPWREP	296-24752-2-ND	Dual 4-Bit Binary Counter	14-TSSOP	987.50/2,000			
SN74LV504ADGVR	296-14319-1-ND	Tri-State Octal Buffer/Driver	20-TVSOIP	1.19	92	.81	
SN74LV504ADGVR	296-14319-2-ND	Tri-State Octal Buffer/Driver	20-TVSOIP	781.02/2,000			
SN74LV504ADWR	296-3837-1-ND	Tri-State Octal Buffer/Driver	20-SOIC	1.19	92	.81	
SN74LV504ADWR	296-3837-2-ND	Tri-State Octal Buffer/Driver	20-SOIC	781.02/2,000			
SN74LV504APWR	296-26559-9-ND	Tri-State Octal Buffer/Driver	20-TSSOP	1.19	92	.81	
SN74LV504APWR	296-26559-2-ND	Tri-State Octal Buffer/Driver	20-TSSOP	781.02/2,000			
SN74LV504ARGYR	296-25821-1-ND	Tri-State Octal Buffer/Driver	20-DFN	1.19	95	.85	
SN74LV504ARGYR	296-25821-2-ND	Tri-State Octal Buffer/Driver	20-DFN	131.69/3,000			
SN74LV541ADBR	296-3838-1-ND	Tri-State Octal Buffer/Driver	20-SSOP	1.22	97	.87	
SN74LV541ADBR	296-3838-2-ND	Tri-State Octal Buffer/Driver	20-SSOP	897.73/2,000			
SN74LV541ADWR	296-1688-5-ND	Tri-State Octal Buffer/Driver	20-SOIC	1.22	99	.86	
SN74LV541ANSR	296-26560-5-ND	Tri-State Octal Buffer/Driver	20-SOP	1.22	97	.87	
SN74LV541ANSR	296-26560-2-ND	Tri-State Octal Buffer/Driver	20-SOP	897.73/2,000			
SN74LV541APWR	296-26561-5-ND	Tri-State Octal Buffer/Driver	20-TSSOP	1.22	99	.86	
SN74LV541APWR	296-13700-1-ND	Tri-State Octal Buffer/Driver	20-TSSOP	1.11	88	.79	
SN74LV541APWR	296-13700-2-ND	Tri-State Octal Buffer/Driver	20-TSSOP	816.93/2,000			
SN74LV541ARGYR	296-13949-1-ND	Tri-State Octal Buffer/Driver	20-VQFN	1.22	97	.87	
SN74LV541ARGYR	296-13949-2-ND	Tri-State Octal Buffer/Driver	20-VQFN	1346.59/3,000			
SN74LV541ATDGR	296-19261-1-ND	Tri-State Octal Buffer/Driver	20-TVSOIP	1.19	92	.81	
SN74LV541ATDGR	296-19261-2-ND	Tri-State Octal Buffer/Driver	20-TVSOIP	781.02/2,000			
SN74LV541ATDWR	296-18662-1-ND	Tri-State Octal Buffer/Driver	20-SOIC	1.19	92	.81	

TEXAS INSTRUMENTS		DigiKey (Cont.)		DIGITAL LOGIC		RoHS Compliant Parts Available	
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*	1	25	100
SN74LV541ATDWR	296-18662-2-ND	Tri-State Octal Buffer/Driver	20-SOIC	781.02/2,000			
SN74LV541ATPWR	296-18698-1-ND	Tri-State Octal Buffer/Driver	20-TSSOP	1.19	92	.81	
SN74LV541ATPWR	296-18698-2-ND	Tri-State Octal Buffer/Driver	20-TSSOP	781.02/2,000			
SN74LV541ATRGYR	296-18725-1-ND	Tri-State Octal Buffer/Driver	20-DFN	1.12	89	.80	
SN74LV541ATRGYR	296-18725-2-ND	Tri-State Octal Buffer/Driver	20-DFN	1245.60/3,000			
SN74LV573ADBR	296-3839-1-ND	Tri-State Octal D-Type Latch	20-SSOP	.75	53	.45	
SN74LV573ADBR	296-3839-2-ND	Tri-State Octal D-Type Latch	20-SSOP	421.93/2,000			
SN74LV573ADWR	296-1690-5-ND	Tri-State Octal D-Type Latch	20-SOIC	.71	52	.45	
SN74LV573ADWR	296-1690-1-ND	Tri-State Octal D-Type Latch	20-SOIC	68	48	.41	
SN74LV573ADWR	296-1690-2-ND	Tri-State Octal D-Type Latch	20-SOIC	383.78/2,000			
SN74LV573AGQNR	296-12094-1-ND	Tri-St. Octal Transparent D-Type Latch	20-BGA	.82	63	.56	
SN74LV573AGQNR	296-12094-2-ND	Tri-St. Octal Transparent D-Type Latch	20-BGA	296.25/1,000			
SN74LV573APWR	296-26562-5-ND	Tri-St. Octal Transparent D-Type Latch	20-TSSOP	.71	52	.45	
SN74LV573APWR	296-3840-1-ND	Tri-State Octal D-Type Latch	20-TSSOP	68	48	.41	
SN74LV573APWR	296-3840-2-ND	Tri-State Octal D-Type Latch	20-TSSOP	383.78/2,000			
SN74LV573ARGYR	296-13950-1-ND	Tri-State Octal D-Type Latch	20-VQFN	.75	53	.45	
SN74LV573ARGYR	296-13950-2-ND	Tri-State Octal D-Type Latch	20-VQFN	632.90/3,000			
SN74LV573ATDWR	296-18743-1-ND	Tri-State Octal D-Type Latch	20-SOIC	.68	48	.41	
SN74LV573ATDWR	296-18743-2-ND	Tri-State Octal D-Type Latch	20-SOIC	383.78/2,000			
SN74LV573ATPWR	296-18745-1-ND	Tri-State Octal D-Type Latch	20-TSSOP	.68			