

TEXAS INSTRUMENTS		DigiKey Real (Cont.)		DIGITAL LOGIC		
		RoHS Compliant Parts Available		Pkg.	Price Each*	100
T.I. Part No.	Digi-Key Part No.	Description		1	25	100
SN74LVC1G86MCKREP	296-22351-2-ND	2-Input Exclusive OR Gate	5-DSBGA	1743.84/3,000		
SN74LVC1G86YEAR	296-15580-1-ND	2-Input Exclusive OR Gate	5-DSBGA	.94 .73	.64	
SN74LVC1G86YEAR	296-15580-2-ND	2-Input Exclusive OR Gate	5-DSBGA	927.47/3,000		
SN74LVC1G86YEP	296-18791-1-ND	2-Input Exclusive OR Gate	5-DSBGA	.94 .73	.64	
SN74LVC1G86YZAR	296-18791-2-ND	2-Input Exclusive OR Gate	5-DSBGA	927.47/3,000		
SN74LVC1G86YZAR	296-14032-2-ND	2-Input Exclusive OR Gate	5-DSBGA	.94 .73	.64	
SN74LVC1G86YZAR	296-14032-2-ND	2-Input Exclusive OR Gate	5-DSBGA	927.47/3,000		
SN74LVC1G86YZPR	296-18792-2-ND	2-Input Exclusive OR Gate	5-DSBGA	.64 .45	.39	
SN74LVC1G86YZPR	296-18792-2-ND	2-Input Exclusive OR Gate	5-DSBGA	538.64/3,000		
SN74LVC1G97DBVR	296-15581-1-ND	Configurable Multiple Function Gate	SOT-23-6	.49 .32	.27	
SN74LVC1G97DBVR	296-15581-2-ND	Configurable Multiple Function Gate	SOT-23-6	332.28/3,000		
SN74LVC1G97DCKR	296-15582-1-ND	Configurable Multiple Function Gate	SC70-6	.49 .32	.27	
SN74LVC1G97DCKR	296-15582-2-ND	Configurable Multiple Function Gate	SC70-6	332.28/3,000		
SN74LVC1G97DRLR	296-18655-1-ND	Configurable Multiple Function Gate	SOT-6	.65 .43	.36	
SN74LVC1G97DRLR	296-18655-2-ND	Configurable Multiple Function Gate	SOT-6	592.50/4,000		
SN74LVC1G97IDCKREP	296-22352-1-ND	Configurable Multiple Function Gate	SC70-6	.74 .58	.51	
SN74LVC1G97IDCKREP	296-22352-2-ND	Configurable Multiple Function Gate	SC70-6	732.21/3,000		
SN74LVC1G97ODCKRQ1	296-17671-1-ND	Configurable Multiple Function Gate	SC70-6	.56 .37	.31	
SN74LVC1G97ODCKRQ1	296-17671-2-ND	Configurable Multiple Function Gate	SC70-6	383.78/3,000		
SN74LVC1G97YAR	296-14366-1-ND	Configurable Multiple Function Gate	6-DSBGA	.94 .73	.64	
SN74LVC1G97YAR	296-14366-2-ND	Configurable Multiple Function Gate	6-DSBGA	927.47/3,000		
SN74LVC1G97YEP	296-16851-1-ND	Configurable Multiple Function Gate	6-DSBGA	.94 .73	.64	
SN74LVC1G97YEP	296-16851-2-ND	Configurable Multiple Function Gate	6-DSBGA	927.47/3,000		
SN74LVC1G97YZAR	296-14367-1-ND	Configurable Multiple Function Gate	6-DSBGA	.94 .73	.64	
SN74LVC1G97YZAR	296-14367-2-ND	Configurable Multiple Function Gate	6-DSBGA	927.47/3,000		
SN74LVC1G97YZPR	296-16852-1-ND	Configurable Multiple Function Gate	6-DSBGA	.64 .45	.39	
SN74LVC1G97YZPR	296-16852-2-ND	Configurable Multiple Function Gate	6-DSBGA	538.64/3,000		
SN74LVC1G98DBVR	296-15583-1-ND	Configurable Multiple Function Gate	SOT-23-6	.49 .32	.27	
SN74LVC1G98DBVR	296-15583-2-ND	Configurable Multiple Function Gate	SOT-23-6	332.28/3,000		
SN74LVC1G98DCKR	296-15584-1-ND	Configurable Multiple Function Gate	SC70-6	.49 .32	.27	
SN74LVC1G98DCKR	296-15584-2-ND	Configurable Multiple Function Gate	SC70-6	332.28/3,000		
SN74LVC1G98DRLR	296-18656-1-ND	Configurable Multiple Function Gate	SOT-6	.65 .43	.36	
SN74LVC1G98DRLR	296-18656-2-ND	Configurable Multiple Function Gate	SOT-6	592.50/4,000		
SN74LVC1G98IDCKREP	296-22353-1-ND	Configurable Multiple Function Gate	SC70-6	.74 .58	.51	
SN74LVC1G98IDCKREP	296-22353-2-ND	Configurable Multiple Function Gate	SC70-6	732.21/3,000		
SN74LVC1G98ODCKRQ1	296-17672-1-ND	Configurable Multiple Function Gate	SC70-6	.56 .37	.31	
SN74LVC1G98ODCKRQ1	296-17672-2-ND	Configurable Multiple Function Gate	SC70-6	383.78/3,000		
SN74LVC1G98YAR	296-14368-1-ND	Configurable Multiple Function Gate	6-DSBGA	.94 .73	.64	
SN74LVC1G98YAR	296-14368-2-ND	Configurable Multiple Function Gate	6-DSBGA	927.47/3,000		
SN74LVC1G98YEP	296-18793-1-ND	Configurable Multiple Function Gate	6-DSBGA	.94 .73	.64	
SN74LVC1G98YEP	296-18793-2-ND	Configurable Multiple Function Gate	6-DSBGA	927.47/3,000		
SN74LVC1G98YZAR	296-14369-1-ND	Configurable Multiple Function Gate	6-DSBGA	.94 .73	.64	
SN74LVC1G98YZAR	296-14369-2-ND	Configurable Multiple Function Gate	6-DSBGA	927.47/3,000		
SN74LVC1G98YZPR	296-23274-1-ND	Configurable Multiple Function Gate	6-DSBGA	.64 .45	.39	
SN74LVC1G98YZPR	296-23274-2-ND	Configurable Multiple Function Gate	6-DSBGA	538.64/3,000		
SN74LVC1G99DCTR	296-18590-1-ND	Tri-State Ultra Configurable Multiple Function Gate	SM8	.77 .54	.47	
SN74LVC1G99DCTR	296-18590-2-ND	Tri-State Ultra Configurable Multiple Function Gate	SM8	653.10/3,000		
SN74LVC1G99DCUR	296-18795-1-ND	Tri-State Ultra Configurable Multiple Function Gate	US8	.77 .54	.47	
SN74LVC1G99DCUR	296-18795-2-ND	Tri-State Ultra Configurable Multiple Function Gate	US8	653.10/3,000		
SN74LVC1G99YZPR	296-17900-1-ND	Tri-State Ultra Configurable Multiple Function Gate	8-DSBGA	.83 .65	.57	
SN74LVC1G99YZPR	296-17900-2-ND	Tri-State Ultra Configurable Multiple Function Gate	8-DSBGA	821.42/3,000		
SN74LVC1G123DCTR	296-18758-1-ND	Single Retriggerable Mono Multivibrator	SM8	.77 .54	.47	
SN74LVC1G123DCTR	296-18758-2-ND	Single Retriggerable Mono Multivibrator	SM8	653.10/3,000		
SN74LVC1G123YZPR	296-21058-1-ND	Single Retriggerable Mono Multivibrator	8-DSBGA	.86 .67	.59	
SN74LVC1G123YZPR	296-21058-2-ND	Single Retriggerable Mono Multivibrator	8-DSBGA	855.09/3,000		
SN74LVC1G125DRLR	296-18012-1-ND	Tri-State Single Bus Buffer Gate	SOT-5	.65 .43	.36	
SN74LVC1G125DRLR	296-18012-2-ND	Tri-State Single Bus Buffer Gate	SOT-5	592.50/4,000		
SN74LVC1G125YAR	296-14359-1-ND	Tri-State Single Bus Buffer Gate	5-DSBGA	.94 .73	.64	
SN74LVC1G125YAR	296-14359-2-ND	Tri-State Single Bus Buffer Gate	5-DSBGA	927.47/3,000		
SN74LVC1G125YZPR	296-18759-1-ND	Tri-State Single Bus Buffer Gate	5-DSBGA	.64 .45	.39	
SN74LVC1G125YZPR	296-18759-2-ND	Tri-State Single Bus Buffer Gate	5-DSBGA	538.64/3,000		
SN74LVC1G126DRLR	296-18013-1-ND	Tri-State Single Bus Buffer Gate	SOT-5	.65 .43	.36	
SN74LVC1G126DRLR	296-18013-2-ND	Tri-State Single Bus Buffer Gate	SOT-5	592.50/4,000		
SN74LVC1G126DRLR	296-18013-2-ND	Tri-State Single Bus Buffer Gate	6-SO8	.65 .43	.36	
SN74LVC1G126DRLR	296-18013-2-ND	Tri-State Single Bus Buffer Gate	6-SO8	695.74/5,000		
SN74LVC1G126YAR	296-15564-1-ND	Tri-State Single Bus Buffer Gate	5-DSBGA	.94 .73	.64	
SN74LVC1G126YAR	296-15564-2-ND	Tri-State Single Bus Buffer Gate	5-DSBGA	927.47/3,000		
SN74LVC1G126YEP	296-15565-1-ND	Tri-State Single Bus Buffer Gate	5-DSBGA	.94 .73	.64	
SN74LVC1G126YEP	296-15565-2-ND	Tri-State Single Bus Buffer Gate	5-DSBGA	927.47/3,000		
SN74LVC1G126YZAR	296-14027-1-ND	Tri-State Single Bus Buffer Gate	5-DSBGA	.83 .65	.57	
SN74LVC1G126YZAR	296-14027-2-ND	Tri-State Single Bus Buffer Gate	5-DSBGA	927.47/3,000		
SN74LVC1G126YZPR	296-14361-1-ND	Tri-State Single Bus Buffer Gate	5-DSBGA	.64 .45	.39	
SN74LVC1G126YZPR	296-14361-2-ND	Tri-State Single Bus Buffer Gate	5-DSBGA	538.64/3,000		
SN74LVC1G132DBVR	296-17888-1-ND	Single 2-Input NAND Gate	SOT-23-5	1.03 .81	.71	
SN74LVC1G132DBVR	296-17888-2-ND	Single 2-Input NAND Gate	SOT-23-5	1026.78/3,000		
SN74LVC1G132DCKR	296-18760-1-ND	Single 2-Input NAND Gate	SC70-5	.49 .32	.27	
SN74LVC1G132DCKR	296-18760-2-ND	Single 2-Input NAND Gate	SC70-5	332.28/3,000		
SN74LVC1G132ZEPR	296-17473-1-ND	Single 2-Input NAND Gate	5-DSBGA	.94 .73	.64	
SN74LVC1G132ZEPR	296-17473-2-ND	Single 2-Input NAND Gate	5-DSBGA	927.47/3,000		
SN74LVC1G132YZPR	296-17622-1-ND	Single 2-Input NAND Gate	5-DSBGA	.64 .45	.39	
SN74LVC1G132YZPR	296-17622-2-ND	Single 2-Input NAND Gate	5-DSBGA	538.64/3,000		
SN74LVC1G139DCTR	296-18235-1-ND	2-to-4 Line Decoder	SM8	.77 .54	.47	
SN74LVC1G139DCTR	296-18235-2-ND	2-to-4 Line Decoder	SM8	653.10/3,000		
SN74LVC1G139DCTR	296-18203-1-ND	2-to-4 Line Decoder	US8	.77 .54	.47	
SN74LVC1G139DCTR	296-18203-2-ND	2-to-4 Line Decoder	US8	653.10/3,000		
SN74LVC1G139YZPR	296-21059-1-ND	2-to-4 Line Decoder	8-DSBGA	.83 .65	.57	
SN74LVC1G139YZPR	296-21059-2-ND	2-to-4 Line Decoder	8-DSBGA	821.42/3,000		
SN74LVC1G175DBVR	296-17617-1-ND	Single D-Type F/F with Async. Clear	SOT-23-6	.49 .32	.27	
SN74LVC1G175DBVR	296-17617-2-ND	Single D-Type F/F with Async. Clear	SOT-23-6	332.28/3,000		
SN74LVC1G175DCKR	296-16998-1-ND	Single D-Type F/F with Async. Clear	SC70-6	.49 .32	.27	
SN74LVC1G175DCKR	296-16998-2-ND	Single D-Type F/F with Async. Clear	SC70-6	332.28/3,000		
SN74LVC1G175DRLR	296-24753-1-ND	Single D-Type F/F with Asynchronous Clear * NEW!	6-SO8	.65 .43	.36	
SN74LVC1G175DRLR	296-24753-2-ND	Single D-Type F/F with Asynchronous Clear * NEW!	6-SO8	695.74/5,000		
SN74LVC1G175YZPR	296-17373-1-ND	Single D-Type F/F with Async. Clear	6-DSBGA	.64 .45	.39	
SN74LVC1G175YZPR	296-17373-2-ND	Single D-Type F/F with Async. Clear	6-DSBGA	538.64/3,000		

TEXAS INSTRUMENTS		DigiKey Real (Cont.)		DIGITAL LOGIC		
		RoHS Compliant Parts Available		Pkg.	Price Each*	100
T.I. Part No.	Digi-Key Part No.	Description		1	25	100
SN74LVC1G240YEAR	296-14364-1-ND	Tri-State Single Buffer/Driver	5-DSBGA	.94 .73	.64	
SN74LVC1G240YEAR	296-14364-2-ND	Tri-State Single Buffer/Driver	5-DSBGA	927.47/3,000		
SN74LVC1G240YEP	296-15850-1-ND	Tri-State Single Buffer/Driver	5-DSBGA	.94 .73	.64	
SN74LVC1G240YEP	296-15850-2-ND	Tri-State Single Buffer/Driver	5-DSBGA	927.47/3,000		
SN74LVC1G240YZPR	296-15874-1-ND	Tri-State Single Buffer/Driver	5-DSBGA	.64 .45	.39	
SN74LVC1G240YZPR	296-15874-2-ND	Tri-State Single Buffer/Driver	5-DSBGA	538.64/3,000		
SN74LVC1G332DBVR	296-18587-1-ND	3-Input Positive OR Gate	SOT-23-6	.49 .32	.27	
SN74LVC1G332DBVR	296-18587-2-ND	3-Input Positive OR Gate	SOT-23-6	332.28/3,000		
SN74LVC1G332DCKR	296-15943-1-ND	3-Input Positive OR Gate	SC70-6	.49 .32	.27	
SN74LVC1G332DCKR	296-15943-2-ND	3-Input Positive OR Gate	SC70-6	332.28/3,000		
SN74LVC1G332DRLR	296-18652-1-ND	3-Input Positive OR Gate	SOT-563	.65 .43	.36	
SN74LVC1G332DRLR	296-18652-2-ND	3-Input Positive OR Gate	SOT-563	592.50/4,000		
SN74LVC1G332ZEPR	296-15875-1-ND	3-Input Positive OR Gate	5-DSBGA	.94 .73	.64	
SN74LVC1G332ZEPR	296-15875-2-ND	3-Input Positive OR Gate	5-DSBGA	927.47/3,000		
SN74LVC1G332YZPR	296-15853-1-ND	3-Input Positive OR Gate	6-DSBGA	.74 .52	.45	
SN74LVC1G332YZPR	296-15853-2-ND	3-Input Positive OR Gate	6-DSBGA	626.17/3,000		
SN74LVC1G373DBVR	296-18588-1-ND	Tri-State Single D-Type Latch	SOT-23-6	.49 .32	.27	
SN74LVC1G373DBVR	296-18588-2-ND	Tri-State Single D-Type Latch	SOT-23-6	332.28/3,000		
SN74LVC1G373DCKR	296-18775-1-ND	Tri-State Single D-Type Latch	SC70-6	.49 .32	.27	
SN74LVC1G373DCKR	296-18775-2-ND	Tri-State Single D-Type Latch	SC70-6	332.28/3,000		
SN74LVC1G373YZPR	296-17100-1-ND	Tri-State Single D-Type Latch	6-DSBGA	.77 .54	.47	
SN74LVC1G373YZPR	296-17100-2-ND	Tri-State Single D-Type Latch	6-DSBGA	626.26/3,000		
SN74LVC1G374DBVR	296-18776-1-ND	Tri-State Single D-Type Latch	SOT-23-6	.49 .32	.27	
SN74LVC1G374DBVR	296-18776-2-ND	Tri-State Single D-Type Latch	SOT-23-6	332.28/3,000		
SN74LVC1G374DCKR	296-18777-1-ND	Tri-State Single D-Type Latch	SC70-6	.72 .42	.34	
SN74LVC1G374DCKR	296-18777-2-ND	Tri-State Single D-Type Latch	SC70-6	332.28/3,000		
SN74LVC1G374YZPR	296-18778-1-ND	Tri-State Single D-Type Latch	6-DSBGA	.74 .52	.45	
SN74LVC1G374YZPR	296-18778-2-ND	Tri-State Single D-Type Latch	6-DSBGA	626.17/3,000		
SN74LVC1G386DBVR	296-18779-1-ND	Single 3-Input Positive XOR Gate	SOT-23-6	.49 .32	.27	
SN74LVC1G386DBVR	296-18779-2-ND	Single 3-Input Positive XOR Gate	SOT-23-6	332.28/3,000		
SN74LVC1G386DCKR	296-18780-1-ND	Single 3-Input Positive XOR Gate	SC70-6	.49 .32	.27	
SN74LVC1G386DCKR	296-18780-2-ND	Single 3-Input Positive XOR Gate	SC70-6	332.28/3,000		
SN74LVC1G386YEP	296-18781-1-ND	Single 3-Input Positive XOR Gate	6-DS			