

TEXAS INSTRUMENTS		DigiKey Reel (Cont.)		POWER SUPPLY PRODUCTS			RoHS Compliant Parts Available		
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*					
				1	25	100			
TLC7733QP	296-3287-5-ND	2.93V Micropower Supply Voltage Supervisor	8-Dip	2.65	2.14	1.92			
TLC7733QPWR	296-3288-1-ND	2.93V Micropower Supply Voltage Supervisor	8-TSSOP	2.98	2.31	2.09			
TLC7733QPWR	296-3288-2-ND	2.93V Micropower Supply Voltage Supervisor	8-TSSOP	2302.672,000					
TLC7733QPWR	296-3288-2-ND	2.93V Micropower Supply Voltage Supervisor	8-TSSOP	2302.672,000					
TPS3103E12DBVT	296-18143-1-ND	2.93V Micropower Volt. Supervisor	8-TSSOP	4.11	3.36	3.02			
TPS3103E12DBVT	296-13393-1-ND	1.14V, Ultralow Supply-Current/ Supply-Voltage Supervisor Circuit	SOT-23-6	3.53	2.73	2.48			
TPS3103E12DBVT	296-26930-1-ND	1.142V, Ultralow Supply-Current/ Supply-Voltage Supervisor Circuit	SOT-23-6	3.53	2.89	2.60			
TPS3103E12DBVT	296-26930-2-ND	1.142V, Ultralow Supply-Current/ Supply-Voltage Supervisor Circuit	SOT-23-6	545.09/250					
TPS3103E15DBVR	296-13394-1-ND	1.43V, Ultralow Supply-Current/ Supply-Voltage Supervisor Circuit	SOT-23-6	3.53	2.73	2.48			
TPS3103E15DBVR	296-13394-2-ND	1.43V, Ultralow Supply-Current/ Supply-Voltage Supervisor Circuit	SOT-23-6	4090.27/3,000					
TPS3103H20DBVR	296-13395-1-ND	1.84V, Ultralow Supply-Current/ Supply-Voltage Supervisor Circuit	SOT-23-6	3.53	2.73	2.48			
TPS3103H20DBVR	296-13395-2-ND	1.84V, Ultralow Supply-Current/ Supply-Voltage Supervisor Circuit	SOT-23-6	4090.27/3,000					
TPS3103K33DBVR	296-13396-1-ND	2.94V, Ultralow Supply-Current/ Supply-Voltage Supervisor Circuit	SOT-23-6	3.53	2.73	2.48			
TPS3103K33DBVR	296-13396-2-ND	2.94V, Ultralow Supply-Current/ Supply-Voltage Supervisor Circuit	SOT-23-6	4090.27/3,000					
TPS3106K33DBVR	296-13399-1-ND	2.94V, Ultralow Supply-Current/ Supply-Voltage Supervisor Circuit	SOT-23-6	3.53	2.73	2.48			
TPS3106K33DBVR	296-13399-2-ND	2.94V, Ultralow Supply-Current/ Supply-Voltage Supervisor Circuit	SOT-23-6	4090.27/3,000					
TPS3123G15DBVT	296-3289-1-ND	1.40V, Ultralow Voltage Processor Supervisor Circuit	SOT-23-5	3.74	2.88	2.62			
TPS3123G15DBVT	296-3289-2-ND	1.40V, Ultralow Voltage Processor Supervisor Circuit	SOT-23-5	533.03/250					
TPS3123J12DBVT	296-3290-1-ND	1.08V, Ultralow Voltage Processor Supervisor Circuit	SOT-23-5	3.74	2.88	2.62			
TPS3123J12DBVT	296-3290-2-ND	1.08V, Ultralow Voltage Processor Supervisor Circuit	SOT-23-5	533.03/250					
TPS3123J18DBVT	296-3291-1-ND	1.62V, Ultralow Voltage Processor Supervisor Circuit	SOT-23-5	3.74	2.88	2.62			
TPS3123J18DBVT	296-3291-2-ND	1.62V, Ultralow Voltage Processor Supervisor Circuit	SOT-23-5	533.03/250					
TPS3124G15DBVT	296-3292-1-ND	1.40V, Ultralow Voltage Processor Supervisor Circuit	SOT-23-5	3.74	2.88	2.62			
TPS3124G15DBVT	296-3292-2-ND	1.40V, Ultralow Voltage Processor Supervisor Circuit	SOT-23-5	533.03/250					
TPS3124J12DBVT	296-3293-1-ND	1.08V, Ultralow Voltage Processor Supervisor Circuit	SOT-23-5	3.74	2.88	2.62			
TPS3124J12DBVT	296-3293-2-ND	1.08V, Ultralow Voltage Processor Supervisor Circuit	SOT-23-5	533.03/250					
TPS3124J18DBVT	296-3294-1-ND	1.62V, Ultralow Voltage Processor Supervisor Circuit	SOT-23-5	3.74	2.88	2.62			
TPS3124J18DBVT	296-3294-2-ND	1.62V, Ultralow Voltage Processor Supervisor Circuit	SOT-23-5	533.03/250					
TPS3125G15DBVT	296-2613-1-ND	1.40V, Ultralow Voltage Processor Supervisor Circuit	SOT-23-5	3.38	2.61	2.37			
TPS3125G15DBVT	296-2613-2-ND	1.40V, Ultralow Voltage Processor Supervisor Circuit	SOT-23-5	482.53/250					
TPS3125J12DBVT	296-2614-1-ND	1.08V, Ultralow Voltage Processor Supervisor Circuit	SOT-23-5	3.38	2.61	2.37			
TPS3125J12DBVT	296-2614-2-ND	1.08V, Ultralow Voltage Processor Supervisor Circuit	SOT-23-5	482.53/250					
TPS3125J18DBVR	296-10898-1-ND	1.62V, Ultralow Voltage Processor Supervisor Circuit	SOT-23-5	2.98	2.31	2.09			
TPS3125J18DBVT	296-2615-1-ND	1.62V, Ultralow Voltage Processor Supervisor Circuit	SOT-23-5	3.38	2.61	2.37			
TPS3125J18DBVT	296-2615-2-ND	1.62V, Ultralow Voltage Processor Supervisor Circuit	SOT-23-5	482.53/250					
TPS3125L300BVR	296-10899-1-ND	2.64V, Ultralow Voltage Processor Supervisor Circuit	SOT-23-5	2.98	2.31	2.09			
TPS3125L300BVT	296-2616-1-ND	2.64V, Ultralow Voltage Processor Supervisor Circuit	SOT-23-5	3.38	2.61	2.37			
TPS3125L300BVT	296-2616-2-ND	2.64V, Ultralow Voltage Processor Supervisor Circuit	SOT-23-5	482.53/250					
TPS3128E12DBVT	296-10903-1-ND	1.14V, Ultralow Voltage Processor Supervisor Circuit	SOT-23-5	3.74	2.88	2.62			
TPS3128E15DBVT	296-10904-1-ND	1.43V, Ultralow Voltage Processor Supervisor Circuit	SOT-23-5	3.74	2.88	2.62			
TPS3305-18D	296-2617-5-ND	Dual 2.93/1.68 Voltage Monitor	8-SOIC	3.61	2.91	2.65			
TPS3305-18DGN	296-26932-5-ND	Dual Processor Supervisory Circuit*	8-MSOP	3.61	2.91	2.65			
TPS3305-18DGNR	296-3299-1-ND	Dual 3.3/1.8 Voltage Monitor	8-MSOP	3.37	2.75	2.47			
TPS3305-18DGNR	296-3299-2-ND	Dual 3.3/1.8 Voltage Monitor	8-MSOP	3731.18/2,500					
TPS3305-25D	296-2618-5-ND	Dual 2.93/2.25 Voltage Monitor	8-SOIC	3.61	2.91	2.65			
TPS3305-25DGNR	296-3300-1-ND	Dual 3.3/2.5 Voltage Monitor	8-MSOP	3.37	2.75	2.47			
TPS3305-25DGNR	296-3300-2-ND	Dual 3.3/2.5 Voltage Monitor	8-MSOP	3731.18/2,500					
TPS3305-33D	296-2619-5-ND	Dual 4.55/2.93 Voltage Monitor	8-SOIC	3.61	2.91	2.65			
TPS3305-33DGNR	296-3301-1-ND	Dual 5/3.3 Voltage Monitor	8-MSOP	3.37	2.75	2.47			
TPS3305-33DGNR	296-3301-2-ND	Dual 5/3.3 Voltage Monitor	8-MSOP	3731.18/2,500					
TPS3306-15D	296-3302-5-ND	Dual 3.3/1.5 Voltage Monitor	8-SOIC	3.93	3.16	2.88			
TPS3306-15D	296-3302-5-ND	Dual 3.3/1.5 Voltage Monitor	8-SOP	3.93	3.16	2.88			
TPS3306-15DRG401	296-24774-1-ND	Dual Processor Supervisory Circuit with Power Fail*	8-SOIC	4.21	3.44	3.09			
TPS3306-15DRG401	296-24774-2-ND	Dual Processor Supervisory Circuit with Power Fail*	8-SOIC	4663.98/2,500					
TPS3306-18D	296-3304-5-ND	Dual 3.3/1.8 Voltage Monitor	8-SOIC	3.93	3.16	2.88			
TPS3306-18DGN	296-3305-5-ND	Dual 3.3/1.8 Voltage Monitor	8-SOP	3.93	3.16	2.88			
TPS3306-20D	296-3306-5-ND	Dual 3.3/2 Voltage Monitor	8-SOIC	3.30	2.66	2.42			
TPS3306-20DGN	296-3307-5-ND	Dual 3.3/2 Voltage Monitor	8-SOP	3.30	2.66	2.42			
TPS3306-25D	296-3308-5-ND	Dual 3.3/2.5 Voltage Monitor	8-SOIC	3.93	3.16	2.88			
TPS3306-25DGN	296-3309-5-ND	Dual 3.3/2.5 Voltage Monitor	8-SOP	3.93	3.16	2.88			
TPS3306-33D	296-3310-5-ND	Dual 5/3.3 Voltage Monitor	8-SOIC	3.93	3.16	2.88			
TPS3306-33DGN	296-3311-5-ND	Dual 5/3.3 Voltage Monitor	8-SOP	3.93	3.16	2.88			
TPS3306-33DRG401	296-24181-1-ND	Dual Processor Supervisory Circuit with Power Fail*	8-SOIC	4.21	3.44	3.09			
TPS3306-33DRG401	296-24181-2-ND	Dual Processor Supervisory Circuit with Power Fail*	8-SOIC	4663.98/2,500					

TEXAS INSTRUMENTS		DigiKey Reel (Cont.)		POWER SUPPLY PRODUCTS			RoHS Compliant Parts Available		
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*					
				1	25	100			
TPS3306-33DRQ1	296-18948-1-ND	Dual Processor Supervisory Circuit with Power Fail	8-SOIC	4.21	3.44	3.09			
TPS3307-18D	296-2620-5-ND	Triple 2.93/1.68/1.25 Voltage Monitor	8-SOIC	3.93	3.16	2.88			
TPS3307-18DGNR	296-3312-1-ND	Triple 3.3/1.8/Adj. Voltage Monitor	8-MSOP	3.53	2.89	2.60			
TPS3307-18DGNR	296-3312-2-ND	Triple 3.3/1.8/Adj. Voltage Monitor	8-MSOP	3919.14/2,500					
TPS3307-18MDREP	296-18150-1-ND	Triple 3.3/1.8/Adj. Voltage Monitor	8-SOIC	7.97	6.62	6.02			
TPS3307-18DRQ1	296-15641-1-ND	Triple 3.3/1.8/Adj. Voltage Monitor	8-SOIC	4.21	3.44	3.09			
TPS3307-18DRQ1	296-15641-2-ND	Triple 3.3/1.8/Adj. Voltage Monitor	8-SOIC	4663.98/2,500					
TPS3307-25D	296-2621-5-ND	Triple 2.93/2.25/1.25 Voltage Monitor	8-SOIC	3.93	3.16	2.88			
TPS3307-25DGN	296-26936-5-ND	Triple 2.93/2.25/1.25 Processor Supervisor*	8-MSOP	3.93	3.16	2.88			
TPS3307-25DGNR	296-3313-1-ND	Triple 3.3/2.5/Adj. Voltage Monitor	8-MSOP	3.53	2.89	2.60			
TPS3307-25DGNR	296-3313-2-ND	Triple 3.3/2.5/Adj. Voltage Monitor	8-MSOP	3919.14/2,500					
TPS3307-33D	296-3314-5-ND	Triple 5/3.3/Adj. Voltage Monitor	8-SOIC	3.93	3.16	2.88			
TPS3307-33DR	296-3314-1-ND	Triple 5/3.3/Adj. Voltage Monitor	8-SOIC	3.53	2.89	2.60			
TPS3307-33DVR	296-3314-2-ND	Triple 5/3.3/Adj. Voltage Monitor	8-SOIC	3919.14/2,500					
TPS3307-33DGNR	296-3315-5-ND	Triple 5/3.3/Adj. Voltage Monitor	8-MSOP	3.93	3.16	2.88			
TPS3307-33DGNR	296-3315-2-ND	Triple 5/3.3/Adj. Voltage Monitor	8-MSOP	3919.14/2,500					
TPS3307-33DGNR	296-3315-1-ND	Triple 5/3.3/Adj. Voltage Monitor	8-MSOP	3.53	2.89	2.60			
TPS3310P	296-3318-5-ND	3.5V Power Supply Monitor	8-Dip	1.35	0.88	0.93			
TPS3311D	296-15041-5-ND	PC Power Supply Supervisor	8-SOIC	1.92	1.55	1.39			
TPS33513D	296-13404-5-ND	PC Power Supply Supervisor	14-SOIC	2.92	2.36	2.13			
TPS33513N	296-17024-ND	PC Power Supply Supervisor	14-Dip	2.47	2.00	1.80			
TPS33514D	296-13513-5-ND	PC Power Supply Supervisor	14-SOIC	2.33	1.88	1.70			
TPS33705-30D	296-2622-5-ND	2.63V Supply Monitor	8-SOIC	2.47	2.00	1.80			
TPS33705-30DGN	296-3316-5-ND	2.63V Supply Monitor	8-MSOP	2.05	1.66	1.49			
TPS33705-33D	296-2623-5-ND	2.93V Supply Monitor	8-SOIC	3.06	2.47	2.23			
TPS33705-33DGNR	296-3319-1-ND	2.93V Supply Monitor	8-MSOP	2.79	2.16	1.96			
TPS33705-33DGNR	296-3319-2-ND	2.93V Supply Monitor	8-MSOP	2690.38/2,500					
TPS33705-50D	296-2624-5-ND	4.55V Supply Monitor	8-SOIC	3.20	2.59	2.33			
TPS33705-50D	296-2625-5-ND	2.25V Supply Monitor	8-SOIC	2.92	2.36	2.13			
TPS33707-30D	296-2626-5-ND	2.63V Supply Monitor	8-SOIC	2.78	2.25	2.02			
TPS33707-30DGN	296-3322-5-ND	2.63V Supply Monitor	8-MSOP	2.78	2.25	2.02			
TPS33707-33DGN	296-3323-5-ND	2.93V Supply Monitor	8-MSOP	2.78	2.25	2.02			
TPS33707-50D	296-2628-5-ND	4.55V Supply Monitor	8-SOIC	2.78	2.25	2.02			
TPS33707-50DGNR	296-3324-1-ND	4.55V Supply Monitor	8-MSOP	2.64	2.04	1.85			
TPS3801-01DCCR	296-12383-1-ND	Ultra-Small Supply Voltage Supervisor	SC70-5	1.71	1.35	1.22			
TPS3801-01DCCR	296-12383-2-ND	Ultra-Small Supply Voltage Supervisor	SC70-5	1885.23/3,000					
TPS3801E18DCCR	296-12384-1-ND	Ultra-Small Supply Voltage Supervisor	SC70-5	1.71	1.35	1.22			
TPS3801E18DCCR	296-12384-2-ND	Ultra-Small Supply Voltage Supervisor	SC70-5	1885.23/3,000					
TPS3801J25DCCR	296-3326-1-ND	2.25V Supply Monitor	SC70-5	1.71	1.35	1.22			
TPS3801J25DCCR	296-3326-2-ND	2.25V Supply Monitor	SC70-5	1885.23/3,000					
TPS3801K33DCCR	296-3327-1-ND	2.93V Supply Monitor	SC70-5	1.71	1.35	1.22			
TPS3801K33DCCR	296-3327-2-ND	2.93V Supply Monitor	SC70-5</						