

TEXAS INSTRUMENTS		DigiKey® (Cont.)		POWER SUPPLY PRODUCTS			
		RoHS Compliant Parts Available					
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*			
				1	25	100	
TPS3809J25DBVT	296-2630-2-ND	2.25V Supply Voltage Supervisor	SOT-23-3	159.63/250			
TPS3809K33DBVBR	296-10916-1-ND	2.93V Supply Voltage Supervisor	SOT-23-3	.95	.74	.65	
TPS3809K33DBVBR	296-10916-2-ND	2.93V Supply Voltage Supervisor	SOT-23-3	942.61/3,000			
TPS3809K33DBVBT	296-2631-1-ND	2.93V Supply Voltage Supervisor	SOT-23-3	.95	.74	.65	
TPS3809K33DBVBT	296-2631-2-ND	2.93V Supply Voltage Supervisor	SOT-23-3	127.37/250			
TPS3809K33QDBVBRQ1	296-15644-1-ND	2.93V Supply Voltage Supervisor	SOT-23-3	1.11	.87	.77	
TPS3809K33QDBVBRQ1	296-15644-2-ND	2.93V Supply Voltage Supervisor	SOT-23-3	1104.21/3,000			
TPS3809K33QDBVREP	296-22439-1-ND	3.3V Supply Voltage Supervisor	SOT-23-3	2.51	1.94	1.76	
TPS3809K33QDBVREP	296-22439-2-ND	3.3V Supply Voltage Supervisor	SOT-23-3	2908.64/3,000			
TPS3809L30DBVBR	296-10917-1-ND	2.64V Supply Voltage Supervisor	SOT-23-3	1.16	.90	.80	
TPS3809L30DBVBR	296-10917-2-ND	2.64V Supply Voltage Supervisor	SOT-23-3	1147.97/3,000			
TPS3809L30DBVT	296-2632-1-ND	2.64V Supply Voltage Supervisor	SOT-23-3	1.16	.91	.82	
TPS3809L30DBVT	296-2632-2-ND	2.64V Supply Voltage Supervisor	SOT-23-3	162.99/250			
TPS3809L30QDBVBRQ1	296-22440-1-ND	3V Supply Voltage Supervisor	SOT-23-3	2.51	1.94	1.76	
TPS3809L30QDBVBRQ1	296-22440-2-ND	3V Supply Voltage Supervisor	SOT-23-3	2908.64/3,000			
TPS3809L30QDBVREP	296-15645-1-ND	2.64V Supply Voltage Supervisor	SOT-23-3	1.18	.93	.84	
TPS38131500DBVBRQ1	296-24776-1-ND	4.55V Supervisor with Programmable Watchdog Window* <b>NEW!</b>	SOT-23-6	3.53	2.89	2.60	
TPS38131500DBVBRQ1	296-24776-2-ND	4.55V Supervisor with Programmable Watchdog Window* <b>NEW!</b>	SOT-23-6	4701.29/3,000			
TPS3813K33MDBVREP	296-22441-1-ND	3.3V Processor Supervisory Circuit	SOT-23-6	7.74	6.33	5.68	
TPS3813K33MDBVREP	296-22441-2-ND	3.3V Processor Supervisory Circuit	SOT-23-6	1298.06/3,000			
TPS3820-33DBVT	296-2633-1-ND	2.93V Supply Monitor	SOT-23-5	2.17	1.67	1.52	
TPS3820-33DBVT	296-2633-2-ND	2.93V Supply Monitor	SOT-23-5	308.59/250			
TPS3820-33QDBVBRQ1	296-15646-1-ND	2.93V Supply Monitor	SOT-23-5	2.17	1.67	1.52	
TPS3820-33QDBVBRQ1	296-15646-2-ND	2.93V Supply Monitor	SOT-23-5	2501.29/3,000			
TPS3820-50DBVT	296-2635-1-ND	4.55V Supply Monitor	SOT-23-5	2.17	1.67	1.52	
TPS3820-50DBVT	296-2635-2-ND	4.55V Supply Monitor	SOT-23-5	308.59/250			
TPS3823-25DBVBR	296-3333-1-ND	2.25V Supply Monitor	SOT-23-5	2.32	1.79	1.63	
TPS3823-25DBVBR	296-3333-2-ND	2.25V Supply Monitor	SOT-23-5	2683.08/3,000			
TPS3823-25QDBVBRQ1	296-15648-1-ND	2.25V Supply Monitor	SOT-23-5	2.64	2.04	1.85	
TPS3823-30DBVBR	296-3334-1-ND	2.63V Supply Monitor	SOT-23-5	1.98	1.56	1.40	
TPS3823-30DBVBR	296-3334-2-ND	2.63V Supply Monitor	SOT-23-5	2178.11/3,000			
TPS3823-30QDBVBRQ1	296-15649-1-ND	2.63V Supply Monitor	SOT-23-5	2.17	1.67	1.52	
TPS3823-33DBVBR	296-1357-1-ND	2.93V Supply Monitor	SOT-23-5	1.80	1.42	1.28	
TPS3823-33DBVBR	296-1357-2-ND	2.93V Supply Monitor	SOT-23-5	1979.49/3,000			
TPS3823-50DBVBR	296-3335-1-ND	4.55V Supply Monitor	SOT-23-5	1.98	1.56	1.40	
TPS3823-50DBVBR	296-3335-2-ND	4.55V Supply Monitor	SOT-23-5	2178.11/3,000			
TPS3823-50DBVT	296-10922-1-ND	4.55V Supply Monitor	SOT-23-5	2.17	1.67	1.52	
TPS3823-50DBVT	296-10922-2-ND	4.55V Supply Monitor	SOT-23-5	308.59/250			
TPS3824-30DBVBR	296-3337-1-ND	2.63V Supply Monitor	SOT-23-5	1.96	1.52	1.38	
TPS3824-30DBVBR	296-3337-2-ND	2.63V Supply Monitor	SOT-23-5	2272.37/3,000			
TPS3824-33DBVBR	296-3338-1-ND	2.93V Supply Monitor	SOT-23-5	1.98	1.56	1.40	
TPS3824-33DBVBR	296-3338-2-ND	2.93V Supply Monitor	SOT-23-5	2178.11/3,000			
TPS3824-33DBVT	296-26951-1-ND	2.93V Supply Monitor* <b>NEW!</b>	SOT-23-5	2.17	1.67	1.52	
TPS3824-33DBVT	296-26951-2-ND	2.93V Supply Monitor* <b>NEW!</b>	SOT-23-5	308.59/250			
TPS3824-50DBVBR	296-1358-1-ND	4.55V Supply Monitor	SOT-23-5	1.96	1.52	1.38	
TPS3824-50DBVBR	296-1358-2-ND	4.55V Supply Monitor	SOT-23-5	2272.37/3,000			
TPS3825-33DBVT	296-2636-1-ND	2.93V Supply Monitor	SOT-23-5	2.32	1.79	1.63	
TPS3825-33DBVT	296-2636-2-ND	2.93V Supply Monitor	SOT-23-5	331.04/250			
TPS3825-50DBVT	296-2637-1-ND	4.55V Supply Monitor	SOT-23-5	1.96	1.52	1.38	
TPS3825-50DBVT	296-2637-2-ND	4.55V Supply Monitor	SOT-23-5	280.54/250			
TPS3825-50QDBVBRQ1	296-15657-1-ND	4.55V Supply Monitor	SOT-23-5	1.96	1.52	1.38	
TPS3828-33DBVT	296-2638-1-ND	2.93V Supply Monitor	SOT-23-5	2.17	1.67	1.52	
TPS3828-33DBVT	296-2638-2-ND	2.93V Supply Monitor	SOT-23-5	308.59/250			
TPS3828-50DBVT	296-2639-1-ND	4.55V Supply Monitor	SOT-23-5	2.32	1.79	1.63	
TPS3828-50DBVT	296-2639-2-ND	4.55V Supply Monitor	SOT-23-5	331.04/250			
TPS3828-50QDBVBRG40	296-24436-1-ND	5V Supply Monitor* <b>NEW!</b>	SOT-23-5	2.48	1.91	1.74	
TPS3828-50QDBVBRG40	296-24436-2-ND	5V Supply Monitor* <b>NEW!</b>	SOT-23-5	2863.19/3,000			
TPS3828-50QDBVBRQ1	296-15659-1-ND	4.55V Supply Monitor	SOT-23-5	2.48	1.91	1.74	
TPS3836E180DBVBRQ1	296-15660-1-ND	1.71V Low Current Monitor	SOT-23-5	3.37	2.75	2.47	
TPS3836E180DBVBRQ1	296-15660-2-ND	1.71V Low Current Monitor	SOT-23-5	4477.42/3,000			
TPS3836H300DBVBRQ1	296-15661-1-ND	2.79V Low Current Monitor	SOT-23-5	3.37	2.75	2.47	
TPS3836J25DBVT	296-3340-1-ND	2.25V Low Current Monitor	SOT-23-5	3.37	2.75	2.47	
TPS3836J25DBVT	296-3340-2-ND	2.25V Low Current Monitor	SOT-23-5	519.00/250			
TPS3836J25QDBVBRQ1	296-15662-1-ND	2.25V Low Current Monitor	SOT-23-5	3.37	2.75	2.47	
TPS3836K33DBVT	296-3341-1-ND	2.93V Low Current Monitor	SOT-23-5	3.37	2.75	2.47	
TPS3836K33DBVT	296-3341-2-ND	2.93V Low Current Monitor	SOT-23-5	519.00/250			
TPS3836K33QDBVBRQ1	296-15663-1-ND	2.93V Low Current Monitor	SOT-23-5	3.37	2.75	2.47	
TPS3836K33QDBVBRQ1	296-15663-2-ND	2.93V Low Current Monitor	SOT-23-5	4477.42/3,000			
TPS3836L300DBVBRQ1	296-15664-1-ND	2.64V Low Current Monitor	SOT-23-5	3.37	2.75	2.47	
TPS3836L300DBVBRQ1	296-15664-2-ND	2.64V Low Current Monitor	SOT-23-5	4477.42/3,000			
TPS3837E180DBVT	296-3343-1-ND	1.71V Low Current Monitor	SOT-23-5	3.37	2.75	2.47	
TPS3837E180DBVBRQ1	296-15665-1-ND	1.71V Low Current Monitor	SOT-23-5	3.37	2.75	2.47	
TPS3837E180DBVBRQ1	296-15665-2-ND	1.71V Low Current Monitor	SOT-23-5	4477.42/3,000			
TPS3837J25DBVT	296-3344-1-ND	2.25V Low Current Monitor	SOT-23-5	3.37	2.75	2.47	
TPS3837K33DBVT	296-3345-1-ND	2.93V Low Current Monitor	SOT-23-5	3.37	2.75	2.47	
TPS3837K33DBVT	296-3345-2-ND	2.93V Low Current Monitor	SOT-23-5	519.00/250			
TPS3837K33QDBVREP	296-20786-1-ND	2.93V Low Current Monitor	SOT-23-5	3.91	3.19	2.87	
TPS3838E180DBVREP	296-22442-1-ND	1.8V Nanopower Supervisory Circuit	SOT-23-5	3.37	2.75	2.47	
TPS3838E180DBVREP	296-22442-2-ND	1.8V Nanopower Supervisory Circuit	SOT-23-5	4477.42/3,000			
TPS3838E180DBVBRQ1	296-15669-1-ND	1.71V Low Current Monitor	SOT-23-5	3.37	2.75	2.47	
TPS3838E180DBVBRQ1	296-15669-2-ND	1.71V Low Current Monitor	SOT-23-5	4477.42/3,000			
TPS3838K33DBVT	296-3349-1-ND	2.93V Low Current Monitor	SOT-23-5	3.37	2.75	2.47	
TPS3838K33DBVT	296-3349-2-ND	2.93V Low Current Monitor	SOT-23-5	519.00/250			
TPS3838K33DBVRR	296-22631-1-ND	2.93V Low Current Monitor	6-SOIC	3.74	2.88	2.62	
TPS3838K33DBVRR	296-22631-2-ND	2.93V Low Current Monitor	6-SOIC	4319.19/3,000			
TPS3838K33QDBVREP	296-22444-1-ND	3.3V Nanopower Supervisory Circuit	SOT-23-5	3.37	2.75	2.47	
TPS3838K33QDBVREP	296-22444-2-ND	3.3V Nanopower Supervisory Circuit	SOT-23-5	4477.42/3,000			
TPS3838K33QDBVBRQ1	296-15670-1-ND	2.93V Low Current Monitor	SOT-23-5	3.37	2.75	2.47	
TPS3838K33QDBVBRQ1	296-15670-2-ND	2.93V Low Current Monitor	SOT-23-5	4477.42/3,000			
TPS3838L30DBVT	296-3350-1-ND	2.64V Low Current Monitor	SOT-23-5	3.37	2.75	2.47	
TPS3838L30DBVT	296-3350-2-ND	2.64V Low Current Monitor	SOT-23-5	519.00/250			
TPS3838L30QDBVBRQ1	296-15671-1-ND	2.64V Low Current Monitor	SOT-23-5	3.37	2.75	2.47	
TPS386000RGPT	296-25181-1-ND	Programmable Quad Supply Voltage Monitor* <b>NEW!</b>	20-QFN	7.59	6.30	5.73	
TPS386000RGPT	296-25181-2-ND	Programmable Quad Supply Voltage Monitor* <b>NEW!</b>	20-QFN	1216.14/250			
TPS386040RGPT	296-25182-1-ND	Programmable Quad Supply Voltage Monitor* <b>NEW!</b>	20-QFN	7.59	6.30	5.73	
TPS386040RGPT	296-25182-2-ND	Programmable Quad Supply Voltage Monitor* <b>NEW!</b>	20-QFN	1216.14/250			

\* RoHS Compliant

★ CALL FOR LOWER PRICING ON LARGER QUANTITIES! ★

(Continued)

Free shipping on orders over \$200 CAD! All prices in Canadian dollars and include duty and brokerage fees.

1-800-344-4539 • www.digikey.ca • 218-681-6674 • Fax: 218-681-3380

(CA2011) 1001

