

TEXAS INSTRUMENTS		DigiKey® (Cont.)		POWER SUPPLY PRODUCTS			RoHS Compliant Parts Available		
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*					
				1	25	100			
TPS79425DGDR	296-13527-1-ND	2.5V, Ultra Low Noise, High PSRR, Fast RF 250mA, LDO Linear Reg.	8-MSOP	2.56	1.97	1.79			
TPS79425DGDR	296-13527-2-ND	2.5V, Ultra Low Noise, High PSRR, Fast RF 250mA, LDO Linear Reg.	8-MSOP	2463.14/2,500					
TPS79425DGNT	296-14432-1-ND	2.5V, Ultra Low Noise, High PSRR, Fast RF 250mA, LDO Linear Reg.	8-MSOP	2.95	2.28	2.07			
TPS79425DGNT	296-14432-2-ND	2.5V, Ultra Low Noise, High PSRR, Fast RF 250mA, LDO Linear Reg.	8-MSOP	420.81/250					
TPS79428DCQR	296-14433-1-ND	2.8V, Ultra Low Noise, High PSRR, Fast RF 250mA, LDO Linear Reg.	SOT-223-6	2.56	1.97	1.79			
TPS79430DCQR	296-14433-1-ND	3V, Ultra Low Noise, High PSRR, Fast RF 250mA, LDO Linear Reg.	SOT-223-6	2.56	1.97	1.79			
TPS79430DGDR	296-13529-1-ND	3V, Ultra Low Noise, High PSRR, Fast RF 250mA, LDO Linear Reg.	8-MSOP	2.56	1.97	1.79			
TPS79433DCQR	296-14437-1-ND	3.3V, Ultra Low Noise, High PSRR, Fast RF 250mA, LDO Linear Reg.	SOT-223-6	2.56	1.97	1.79			
TPS79433DCQR	296-14437-2-ND	3.3V, Ultra Low Noise, High PSRR, Fast RF 250mA, LDO Linear Reg.	SOT-223-6	2461.74/2,500					
TPS79433DGDR	296-13530-1-ND	3.3V, Ultra Low Noise, High PSRR, Fast RF 250mA, LDO Linear Reg.	8-MSOP	2.56	1.97	1.79			
TPS79433DGDR	296-13530-2-ND	3.3V, Ultra Low Noise, High PSRR, Fast RF 250mA, LDO Linear Reg.	8-MSOP	2463.14/2,500					
TPS79433DGNT	296-14438-1-ND	3.3V, Ultra Low Noise, High PSRR, Fast RF 250mA, LDO Linear Reg.	8-MSOP	2.95	2.28	2.07			
TPS79433DGNT	296-14438-2-ND	3.3V, Ultra Low Noise, High PSRR, Fast RF 250mA, LDO Linear Reg.	8-MSOP	420.81/250					
TPS79501DCQR	296-13806-1-ND	1.2V to 5.5V, Ultra Low Noise, High PSRR, Fast RF LDO Linear Reg.	SOT-223-5	3.37	2.75	2.47			
TPS79501DCQR	296-13806-2-ND	1.2V to 5.5V, Ultra Low Noise, High PSRR, Fast RF LDO Linear Reg.	SOT-223-5	3731.18/2,500					
TPS79501DRBR	296-20792-1-ND	1.2V to 5.5V, Ultra Low Noise, High PSRR, Fast RF LDO Linear Reg.	8-SOP	3.70	3.03	2.72			
TPS79501DRBR	296-20792-2-ND	1.2V to 5.5V, Ultra Low Noise, High PSRR, Fast RF LDO Linear Reg.	8-SOP	4925.16/3,000					
TPS79501DRBT	296-27103-1-ND	1.2V to 5.5V, Ultra Low Noise, High PSRR, Fast RF LDO Linear Reg. *NEW!	8-SOP	4.21	3.44	3.09			
TPS79501DRBT	296-27103-2-ND	1.2V to 5.5V, Ultra Low Noise, High PSRR, Fast RF LDO Linear Reg. *NEW!	8-SOP	648.89/250					
TPS79518DCQR	296-13808-1-ND	1.8V, Ultra Low Noise, High PSRR, Fast RF LDO Linear Regulator	SOT-223-6	3.37	2.75	2.47			
TPS79518DCQR	296-13808-2-ND	1.8V, Ultra Low Noise, High PSRR, Fast RF LDO Linear Regulator	SOT-223-6	3731.18/2,500					
TPS79525DCQ	296-14753-5-ND	2.5V, Ultra Low Noise, High PSRR, Fast RF LDO Linear Regulator	SOT-223-6	3.77	3.03	2.77			
TPS79530DCQR	296-13809-1-ND	3V, Ultra Low Noise, High PSRR, Fast RF LDO Linear Regulator	SOT-223-6	3.37	2.75	2.47			
TPS79530DCQR	296-13809-2-ND	3V, Ultra Low Noise, High PSRR, Fast RF LDO Linear Regulator	SOT-223-6	3731.18/2,500					
TPS79533DCQR	296-13810-1-ND	3.3V, Ultra Low Noise, High PSRR, Fast RF LDO Linear Regulator	SOT-223-6	3.37	2.75	2.47			
TPS79533DCQR	296-13810-2-ND	3.3V, Ultra Low Noise, High PSRR, Fast RF LDO Linear Regulator	SOT-223-6	3731.18/2,500					
TPS79601DCQR	296-13761-1-ND	1.2V to 5.5V, Ultra Low Noise, High PSRR, Fast RF 1A LDO Regulator	SOT-223-6	3.70	3.03	2.72			
TPS79601DCQR	296-13761-2-ND	1.2V to 5.5V, Ultra Low Noise, High PSRR, Fast RF 1A LDO Regulator	SOT-223-6	4104.30/2,500					
TPS79601DRBR	296-23107-1-ND	1.2V to 5.5V, Ultra Low Noise, High PSRR, Fast RF 1A LDO Regulator	8-SOP	4.04	3.30	2.97			
TPS79601KTTT	296-14439-1-ND	1.2V to 5.5V, Ultra Low Noise, High PSRR, Fast RF 1A LDO Regulator	5-DPAK	5.05	4.13	—			
TPS79601KTTT	296-14439-2-ND	1.2V to 5.5V, Ultra Low Noise, High PSRR, Fast RF 1A LDO Regulator	5-DPAK	189.36/50					
TPS79618DCQR	296-13762-1-ND	1.8V, Ultra Low Noise, High PSRR, Fast RF 1A LDO Regulator	SOT-223-6	3.70	3.03	2.72			
TPS79618DCQR	296-13762-2-ND	1.8V, Ultra Low Noise, High PSRR, Fast RF 1A LDO Regulator	SOT-223-6	4104.30/2,500					
TPS79625DCQR	296-13763-1-ND	2.5V, Ultra Low Noise, High PSRR, Fast RF 1A LDO Regulator	SOT-223-6	3.70	3.03	2.72			
TPS79625DCQR	296-13763-2-ND	2.5V, Ultra Low Noise, High PSRR, Fast RF 1A LDO Regulator	SOT-223-6	4104.30/2,500					
TPS79625KTTT	296-14441-1-ND	2.5V, Ultra Low Noise, High PSRR, Fast RF 1A LDO Regulator	5-DPAK	5.05	4.13	—			
TPS79625KTTT	296-14441-2-ND	2.5V, Ultra Low Noise, High PSRR, Fast RF 1A LDO Regulator	5-DPAK	189.36/50					
TPS79628KTTT	296-14442-5-ND	2.8V, Ultra Low Noise, High PSRR, Fast RF 1A LDO Regulator	5-DPAK	3.70	2.98	2.72			
TPS79628KTTT	296-16737-1-ND	2.8V, Ultra Low Noise, High PSRR, Fast RF 1A LDO Regulator	5-DPAK	5.05 4.13 —					
TPS79630DCQR	296-13765-1-ND	3V, Ultra Low Noise, High PSRR, Fast RF 1A LDO Regulator	SOT-223-6	3.70	3.03	2.72			
TPS79630KTTT	296-14443-1-ND	3V, Ultra Low Noise, High PSRR, Fast RF 1A LDO Regulator	5-DPAK	5.05	4.13	—			
TPS79630KTTT	296-14443-2-ND	3V, Ultra Low Noise, High PSRR, Fast RF 1A LDO Regulator	5-DPAK	189.36/50					
TPS79633DCQ	296-27109-5-ND	3.3V, Ultra Low Noise, High PSRR, Fast RF 1A LDO Regulator *NEW!	SOT-223-6	4.24	3.41	3.11			
TPS79633DCQR	296-13766-1-ND	3.3V, Ultra Low Noise, High PSRR, Fast RF 1A LDO Regulator	SOT-223-6	3.70	3.03	2.72			
TPS79633DCQR	296-13766-2-ND	3.3V, Ultra Low Noise, High PSRR, Fast RF 1A LDO Regulator	SOT-223-6	4104.30/2,500					
TPS79633KTTT	296-14444-1-ND	3.3V, Ultra Low Noise, High PSRR, Fast RF 1A LDO Regulator	5-DPAK	5.05	4.13	—			
TPS79650DCQR	296-19746-1-ND	5V, Ultra Low Noise, High PSRR, Fast RF 1A LDO Regulator	SOT-223-6	3.70	3.03	2.72			
TPS79650DCQR	296-19746-2-ND	5V, Ultra Low Noise, High PSRR, Fast RF 1A LDO Regulator	SOT-223-6	4104.30/2,500					
TPS79650DRBR	296-21352-1-ND	5V, Ultra Low Noise, High PSRR, Fast RF 1A LDO Regulator	8-SOP	3.70	3.03	2.72			
TPS79650DRBR	296-21352-2-ND	5V, Ultra Low Noise, High PSRR, Fast RF 1A LDO Regulator	8-SOP	4925.16/3,000					
TPS79718DCR	296-11988-1-ND	1.8V, 10mA Micropower LDO Voltage Regulator	SC70-5	1.45	1.15	1.04			
TPS79718DCR	296-11988-2-ND	1.8V, 10mA Micropower LDO Voltage Regulator	SC70-5	1602.44/3,000					
TPS79718DCRKR1	296-23648-1-ND	1.8V, 10mA LDO Linear Voltage Reg.	SC70-5	1.69	1.34	1.21			
TPS79718DCRKR1	296-23648-2-ND	1.8V, 10mA LDO Linear Voltage Reg.	SC70-5	1875.80/3,000					

TEXAS INSTRUMENTS		DigiKey® (Cont.)		POWER SUPPLY PRODUCTS			RoHS Compliant Parts Available		
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*					
				1	25	100			
TPS79730DCR	296-11989-1-ND	3V, 10mA Micropower LDO Volt. Reg.	SC70-5	1.45	1.15	1.04			
TPS79730DCR	296-11989-2-ND	3V, 10mA Micropower LDO Volt. Reg.	SC70-5	1602.44/3,000					
TPS79730MDCRREP	296-22527-1-ND	3V, 10mA LDO Linear Voltage Reg.	SC70-5	3.42	2.64	2.40			
TPS79730DCR	296-11990-1-ND	3.3V, 10mA Micro LDO Voltage Reg.	SC70-5	1.45	1.15	1.04			
TPS79733DCR	296-11990-2-ND	3.3V, 10mA Micro LDO Voltage Reg.	SC70-5	1602.44/3,000					
TPS79733EVM	296-13595-ND	Evaluation Module for TPS79733	—	56.11					
TPS79801ODGNR01	296-24322-1-ND	Adj., 50mA LDO Linear Reg. *NEW!	8-MSOP	5.72	4.68	4.20			
TPS79801ODGNR01	296-24322-2-ND	Adj., 50mA LDO Linear Reg. *NEW!	8-MSOP	6343.01/2,500					
TPS79801ODGNR01	296-24323-1-ND	Adj., 50mA LDO Linear Reg. *NEW!	8-MSOP	5.72	4.68	4.20			
TPS79801ODGNR01	296-24323-2-ND	Adj., 50mA LDO Linear Reg. *NEW!	8-MSOP	6343.01/2,500					
TPS79901DDCR	296-17776-1-ND	Adj., 200mA LDO Linear Regulator	TSOT-23-5	1.21	96	87			
TPS79901DDCR	296-17776-2-ND	Adj., 200mA LDO Linear Regulator	TSOT-23-5	1343.23/3,000					
TPS79901DRVR	296-27114-1-ND	Adj., 200mA LDO Linear Reg. *NEW!	6-SOP	1.58	1.25	1.13			
TPS79901DRVR	296-27114-2-ND	Adj., 200mA LDO Linear Reg. *NEW!	6-SOP	1747.20/3,000					
TPS79901DRVT	296-19299-1-ND	Adj., 200mA LDO Linear Regulator	6-SOP	1.76	1.40	1.26			
TPS79901DRVT	296-19299-2-ND	Adj., 200mA LDO Linear Regulator	6-SOP	249.12/250					
TPS79901ZDTCR	296-18343-1-ND	Adj., 200mA LDO Linear Regulator	5-DSBGA	1.60	1.27	1.14			
TPS79912DDCR	296-21939-1-ND	1.2V, 200mA LDO Linear Regulator	TSOT-23-5	1.21	96	87			
TPS79912DDCR	296-21939-2-ND	1.2V, 200mA LDO Linear Regulator	TSOT-23-5	1343.23/3,000					
TPS79912DDCT	296-27115-1-ND	1.2V, 200mA LDO Linear Regulator *NEW!	TSOT-23-5	1.40	1.11	1.00			
TPS79912DDCT	296-27115-2-ND	1.2V, 200mA LDO Linear Regulator *NEW!	TSOT-23-5	197.78/250					
TPS79912DRVT	296-22870-1-ND	1.2V, 200mA LDO Linear Regulator	6-SOP	1.76	1.40	1.26			
TPS79912DRVT	296-22870-2-ND	1.2V, 200mA LDO Linear Regulator	6-SOP	249.12/250					
TPS79912DRVR01	296-25739-1-ND	1.2V, 200mA LDO Linear Regulator *NEW!	6-SOP	1.43	1.13	1.01			
TPS79912DRVR01	296-25739-2-ND	1.2V, 200mA LDO Linear Regulator *NEW!	6-SOP	1568.78/3,000					
TPS79913DDCR	296-21287-1-ND	1.3V, 200mA LDO Linear Regulator	TSOT-23-5	1.21	96	87			
TPS79913DDCR	296-21287-2-ND	1.3V, 200mA LDO Linear Regulator	TSOT-23-5	1343.23/3,000					
TPS79915DDCR	296-17777-1-ND	1.5V, 200mA LDO Linear Regulator	TSOT-23-5	1.21	96	87			
TPS79915DDCR	296-17777-2-ND	1.5V, 200mA LDO Linear Regulator	TSOT-23-5	1343.23/3,000					
TPS79915DDCT	296-27116-1-ND	1.5V, 200mA LDO Linear Regulator *NEW!	TSOT-23-5	1.40	1.11	1.00			
TPS79915DDCT	296-27116-2-ND	1.5V, 200mA LDO Linear Regulator *NEW!	TSOT-23-5	197.78/250					
TPS79915DDCR01	296-25740-1-ND	1.5V, 200mA LDO Linear Regulator *NEW!	SOT-5	1.43	1.13	1.01			
TPS79915DDCR01	296-25740-2-ND	1.5V, 200mA LDO Linear Regulator *NEW!	SOT-5	1568.78/3,000					
TPS79915YZUR	296-20715-1-ND	1.5V, 200mA LDO Linear Regulator	5-DSBGA	1.43	1.13	1.01			
TPS79915YZUR	296-20715-2-ND	1.5V, 200mA LDO Linear Regulator	5-DSBGA	1568.45/3,000					
TPS79918DDCR	296-17778-1-ND	1.8V, 200mA LDO Linear Regulator	TSOT-23-5	1.21	96	87			
TPS79918DDCR	296-17778-2-ND	1.8V, 200mA LDO Linear Regulator	TSOT-23-5	1343.23/3,000					
TPS79918DRVT	296-19367-1-ND	1.8V, 200mA, Ultra Low Noise, High PSRR, LDO Linear Regulator	6-SOP	1.76	1.40	1.26			
TPS79918DRVT	296-19367-2-ND	1.8V, 200mA, Ultra Low Noise, High PSRR, LDO Linear Regulator	6-SOP	249.12/250					
TPS79918DDCR01	296-24781-1-ND	1.8V, 200mA, Ultra Low Noise, High PSRR, LDO Linear Reg. *NEW!	SOT-5	1.43	1.13	1.01			
TPS79918DDCR01	296-24781-2-ND	1.8V, 200mA, Ultra Low Noise, High PSRR, LDO Linear Reg. *NEW!	SOT-5	1569.45/3,000					
TPS79918YZUR	296-19482-1-ND	1.8V, 200mA, Ultra Low Noise, High PSRR, LDO Linear Regulator	5-DSBGA	1.43	1.13	1.01			
TPS79918YZUR	296-19482-2-ND	1.8V, 200mA, Ultra Low Noise, High PSRR, LDO Linear Regulator	5-DSBGA	1569.45/3,000					
TPS79920YZUT	296-21564-1-ND	2V, 200mA LDO Linear Regulator	5-DSBGA	1.60	1.27	1.14			
TPS79925DDCR01	296-25741-1-ND	2.5V, 200mA LDO Linear Regulator *NEW!	SOT-5	1.43	1.13	1.01			
TPS79925DDCR01	296-25741-2-ND	2.5V, 200mA LDO Linear Regulator *NEW!	SOT-5	1568.78/3,000					
TPS79925YZUT	296-18345-1-ND	2.5V, 200mA LDO Linear Regulator	5-DSBGA	1.60	1.27	1.14			
TPS79925YZUT	296-18345-2-ND	2.5V, 200mA LDO Linear Regulator	5-DSBGA	226.12/250					
TPS79927DDCR	296-20730-1-ND	2.7V, 200mA LDO Linear Regulator	TSOT-23-5	1.21	96	87			
TPS79927DDCR	296-20730-2-ND	2.7V, 200mA LDO Linear Regulator	TSOT-23-5	1343.23/3,000					
TPS79927DDCR01	296-25742-1-ND	2.7V, 200mA LDO Linear Regulator *NEW!	SOT-5	1.43	1.13	1.01			
TPS79927DDCR01	296-25742-2-ND	2.7V, 200mA LDO Linear Regulator *NEW!	SOT-5	1568.78/3,000					
TPS79927DRVR01	296-25743-1-ND	2.7V, 200mA LDO Linear Regulator *NEW!	6-SOP	1.43</					