

TEXAS INSTRUMENTS		DigiKey® (Cont.)		POWER SUPPLY PRODUCTS			
				RoHS Compliant Parts Available			
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*			
				1	25	100	
TPS720105Y2UT	296-24627-2-ND	1.05V, 350mA LDO Reg. * NEW!	5-D8BGA	291	76/250		
TPS726126DCR	296-18257-ND	1.26V, 1A, LDO Regulator	SOT-223-6	4.24	—	—	
TPS731125DBVR	296-12176-1-ND	1.25V, 150mA LDO Regulator	SOT-23-5	8.33	1.45	1.31	
TPS736125DBRT	296-18252-1-ND	1.25V, 400mA LDO Regulator	8-SOIC	3.37	2.75	2.47	
TPS736125DBR	296-18252-2-ND	1.25V, 400mA LDO Regulator	8-SOIC	—	519.00/250		
TPS793285DBVR	296-12157-1-ND	2.85V, 200mA, High PSRR, RF LDO Regulator	SOT-23-5	1.08	.84	.74	
TPS793285DBVR	296-12157-2-ND	2.85V, 200mA, High PSRR, RF LDO Regulator	SOT-23-5	1.069	0.3/3,000		
TPS793285DBVT	296-27100-1-ND	2.85V, 200mA, High PSRR, RF LDO Regulator * NEW!	SOT-23-5	1.07	.85	.77	
TPS793285DBVT	296-27100-2-ND	2.85V, 200mA, High PSRR, RF LDO Regulator * NEW!	SOT-23-5	—	151.49/250		
TPS793285YEQVM	296-19007-ND	Evaluation Module for TPS793285YEQ	—	11.45	—	—	
TPS7934750DBVR	296-12160-1-ND	4.75V, 200mA, High PSRR, RF LDO Regulator	SOT-23-5	1.08	.84	.74	
TPS7934750DBVR	296-12160-2-ND	4.75V, 200mA, High PSRR, RF LDO Regulator	SOT-23-5	—	1070.54/3,000		
TPS797285DCR	296-25465-1-ND	2.85V, 50mA LDO Regulator * NEW!	SC70-5	1.45	1.15	1.04	
TPS797285DCR	296-25465-2-ND	2.85V, 50mA LDO Regulator * NEW!	SC70-5	—	1602.44/3,000		
TPS799285DBVR	296-19747-1-ND	2.85V, 200mA LDO Regulator	6-SOIC	1.58	1.25	1.13	
TPS799285DBVR	296-19747-2-ND	2.85V, 200mA LDO Regulator	6-SOIC	—	1747.20/3,000		
TPS728120150DRVT	296-25585-1-ND	1.2V/1.5V, 200mA LDO Reg. * NEW!	6-SOIC	1.92	1.52	1.37	
TPS728120150DRVT	296-25585-2-ND	1.2V/1.5V, 200mA LDO Reg. * NEW!	6-SOIC	—	270.72/250		
TPS780230300DRVT	296-24206-1-ND	150mA, Ultralow Power, LDO Regulator * NEW!	6-SOIC	1.86	1.48	1.33	
TPS780230300DRVT	296-24206-2-ND	150mA, Ultralow Power, LDO Regulator * NEW!	6-SOIC	—	263.71/250		
TPS780300250DRVR	296-24057-1-ND	2.5V or 3V Dual Level Output, 150mA LDO Regulator	6-SOIC	1.64	1.30	1.17	
TPS780300250DRVR	296-24057-2-ND	2.5V or 3V Dual Level Output, 150mA LDO Regulator	6-SOIC	—	1814.53/3,000		
TPS780330220DCR	296-23332-1-ND	3.3V or 2.2V Dual Level Output, 150mA LDO Regulator	TSOT-23	1.47	1.17	1.05	
TPS780330220DCR	296-23332-2-ND	3.3V or 2.2V Dual Level Output, 150mA LDO Regulator	TSOT-23	—	1626.01/3,000		
TPS780330220DRVR	296-23439-1-ND	3.3V or 2.2V Dual Level Output, 150mA LDO Regulator	6-SOIC	1.64	1.30	1.17	
TPS780330220DRVR	296-23439-2-ND	3.3V or 2.2V Dual Level Output, 150mA LDO Regulator	6-SOIC	—	1814.53/3,000		
UA7815ACDR	296-27137-1-ND	15V, 100mA, Pos. Volt. Reg. * NEW!	8-SOIC	.65	.43	.36	
UA7815ACDR	296-27137-2-ND	15V, 100mA, Pos. Volt. Reg. * NEW!	8-SOIC	—	370.31/2,500		
UC282T-1	296-15146-5-ND	1.5V, Fast LDO Regulator	TO-220-5	10.53	8.63	7.79	
UC282T-2	296-15147-5-ND	2.1V, Fast LDO Regulator	TO-220-5	10.53	8.63	7.79	
UC282T-3	296-15148-5-ND	2.5V, Fast LDO Regulator	TO-220-5	10.53	8.63	7.79	
UC282T-ADJ	296-15149-5-ND	Adj., Fast LDO Regulator	TO-220-5	10.53	8.63	7.79	
UC282T-D	296-2795-5-ND	2.5V, Fast LDO Regulator	TO-263-5	6.90	5.58	5.03	
UC282TDKTTT-3	296-16013-5-ND	2.5V, Fast LDO Regulator	TO-263-5	8.70	7.14	6.44	
UC282TDKTTT-ADJ	296-16014-1-ND	1.2V/Adj., Fast LDO Regulator	TO-263-5	9.22	7.66	6.96	
UC282TDTR-ADJ	296-18067-1-ND	1.2V/Adj., Fast LDO Regulator	TO-263-5	9.22	7.66	6.96	
UC282TDTR-3	296-19031-1-ND	2.5V, Fast LDO Regulator	TO-263-5	9.22	7.66	6.96	
UC282T-1	296-15153-5-ND	1.5V, Fast LDO Regulator	TO-220-5	12.21	10.01	9.04	
UC282T-2	296-15154-5-ND	2.1V, Fast LDO Regulator	TO-220-5	10.25	8.40	7.58	
UC282T-3	296-15155-5-ND	2.5V, Fast LDO Regulator	TO-220-5	12.21	10.01	9.04	
UC282T-ADJ	296-15156-5-ND	1.2V/Adj., Fast LDO Regulator	TO-220-5	12.21	10.01	9.04	
UC282TDKTTT-1	296-16015-1-ND	1.5V, Fast LDO Regulator	TO-263-5	10.85	9.02	—	
UC282TDKTTT-2	296-16015-2-ND	1.5V, Fast LDO Regulator	TO-263-5	—	419.86/50		
UC282TDKTTT-ADJ	296-16016-1-ND	1.2V/Adj., Fast LDO Regulator	TO-263-5	10.85	9.02	—	
UC282TDKTTT-ADJ	296-16016-2-ND	1.2V/Adj., Fast LDO Regulator	TO-263-5	—	419.86/50		
UC382T-1	296-2801-5-ND	1.5V, Fast Transient Response LDO Regulator	TO-220-5	9.12	7.48	6.75	
UC382T-2	296-2802-5-ND	2.1V, Fast Transient Response LDO Regulator	TO-220-5	9.12	7.48	6.75	
UC382T-3	296-2803-5-ND	2.5V, Fast Transient Response LDO Regulator	TO-220-5	9.12	7.48	6.75	
UC382T-ADJ	296-2804-5-ND	Adjustable Fast Transient Response LDO Regulator	TO-220-5	9.12	7.48	6.75	
UC385EVM-207	296-20626-ND	Evaluation Module for UC385	—	56.11	—	—	
UC385T-1	296-2809-5-ND	1.5V, 5A LDO Regulator	TO-220-5	10.66	8.75	7.89	
UC385T-2	296-2810-5-ND	2.1V, 5A LDO Regulator	TO-220-5	10.66	8.75	7.89	
UC385T-3	296-2811-5-ND	2.5V, 5A LDO Regulator	TO-220-5	10.66	8.75	7.89	
UC385T-ADJ	296-2812-5-ND	1.2V/Adj., 5A LDO Regulator	TO-220-5	10.66	8.75	7.89	
UC2573D	296-2814-5-ND	2.1V, 5A LDO Regulator	TO-263-5	6.91	5.68	5.12	
UC2578DP	296-2793-5-ND	Buck Pulse PWM Voltage Regulator	8-SOIC	4.40	3.54	3.23	
UC2832DWEV	296-19029-5-ND	Buck PWM Step-Down Voltage Reg. 2V Precision LDO Linear Controller	16-SOIC	11.37	9.32	8.41	
UC2834DW	296-2797-5-ND	High-Efficiency Linear Regulator	16-SOIC	12.21	10.01	9.04	
UC2835D	296-2798-5-ND	High-Efficiency Linear Regulator	16-SOIC	20.37	17.13	15.74	
UC3832N	296-2799-5-ND	High-Efficiency Regulator Controller Adjustable, 100mA LDO Regulator	14-Dip	12.06	9.90	8.93	
UC3833N	296-11274-5-ND	Adjustable, 100mA LDO Regulator	8-Dip	7.50	7.14	6.44	
UC3834DW	296-2808-5-ND	High-Efficiency Linear Regulator	16-SOIC	13.95	11.73	10.78	
UC281DP-5	296-2817-5-ND	5V, 1A LDO Regulator	8-SOIC	7.29	5.99	5.40	
UC281DP-ADJ	296-2818-5-ND	Adjustable, 1A LDO Regulator	8-SOIC	7.29	5.99	5.40	
UC283T-3	296-11413-5-ND	3.3V, 3A LDO Regulator	TO-220-3	10.53	8.63	7.79	
UC283T-5	296-11414-5-ND	5V, 3A LDO Regulator	TO-220-3	10.53	8.63	7.79	
UC283T-ADJ	296-11417-5-ND	Adjustable, 3A LDO Regulator	TO-220	10.53	8.63	7.79	
UC283TKTTT-5	296-19039-1-ND	5V, 3A LDO Regulator	3-D2PAK	9.22	7.66	—	
UC283TKTTT-5	296-19039-2-ND	5V, 3A LDO Regulator	3-D2PAK	—	356.57/50		
UC284DP-12	296-11415-5-ND	12V, 500mA Negative LDO Regulator	8-SOIC	7.86	6.45	5.82	
UC284DP-5	296-11416-5-ND	5V, 500mA Negative LDO Regulator	8-SOIC	8.98	7.37	6.65	
UC284DP-ADJ	296-11417-5-ND	Adj., 500mA Negative LDO Regulator	8-SOIC	8.98	7.37	6.65	
UC381DP-3	296-2819-5-ND	3.3V, 1A LDO Regulator	8-SOIC	7.23	5.81	5.30	
UC381DP-5	296-2820-5-ND	5V, 1A LDO Regulator	8-SOIC	7.23	5.81	5.30	
UC381DP-ADJ	296-2821-5-ND	Adjustable, 1A LDO Regulator	8-SOIC	7.23	5.81	5.30	
UC383T-3	296-8156-5-ND	3.3V, 3A LDO Linear Regulator	TO-220-3	9.12	7.48	6.75	
UC383T-5	296-8157-5-ND	5V, 3A LDO Linear Regulator	TO-220-3	9.12	7.48	6.75	
UC383T-ADJ	296-8158-5-ND	Adjustable, 3A LDO Linear Regulator	TO-220	9.12	7.48	6.75	
UC383TDKTTT-3	296-8161-5-ND	Adjustable, 3A LDO Linear Regulator	TO-263-5	6.62	5.32	4.85	
UC383TKTTT-ADJ	296-16028-1-ND	3.3V, 3A LDO Linear Regulator	3-D2PAK	8.03	6.67	—	
UC383TKTTT-3	296-16028-2-ND	3.3V, 3A LDO Linear Regulator	3-D2PAK	—	310.56/50		
UC383TKTTT-5	296-16029-1-ND	5V, 3A LDO Linear Regulator	3-D2PAK	8.03	6.67	—	
UC383TKTTT-5	296-16029-2-ND	5V, 3A LDO Linear Regulator	3-D2PAK	—	310.56/50		
UC384DP-12	296-8163-5-ND	-12V, 0.5A LDO Linear Regulator	8-SOIC	7.38	5.94	5.41	
UC384DP-5	296-8163-5-ND	-5V, 0.5A LDO Linear Regulator	8-SOIC	7.38	5.94	5.41	
UC384DP-ADJ	296-8164-5-ND	Neg. Adj. 0.5A LDO Linear Regulator	8-SOIC	7.38	5.94	5.41	
UC3833DWR	296-13767-1-ND	Precision LDO Linear Controller	16-SOIC	8.08	6.60	5.93	

TEXAS INSTRUMENTS		DigiKey® (Cont.)		POWER SUPPLY PRODUCTS			
				RoHS Compliant Parts Available			
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*			
				1	25	100	
Voltage Regulators							
LMF789D25CPWR	296-17215-1-ND	Dual Linear FET Controller	8-TSSOP	1.23	.98	.88	
LM237KCS5E	296-21574-5-ND	Adj., 1.5A 3-Terminal Regulator	TO-220-3	9.99	7.77	6.7	
LM317DCY	296-23224-5-ND	3-Terminal Adjustable Regulator	SOT-223	1.08	.84	.73	
LM317DCYR	296-12602-1-ND	3-Terminal Adjustable Regulator	SOT-223	—	99	77	
LM317DCYR	296-12602-2-ND	3-Terminal Adjustable Regulator	SOT-223	—	913.57/2,500		
LM317KCS	296-13869-5-ND	3-Terminal Adjustable Regulator	TO-220	90	70	61	
LM317KCS5E	296-21576-5-ND	3-Terminal Adjustable Regulator	TO-220	90	70	61	
LM317KTR	296-21390-1-ND	3-Terminal Adjustable Regulator	D2PAK-3	1.19	92	81	
LM317KTR	296-21390-2-ND	3-Terminal Adjustable Regulator	D2PAK-3	—	269.32/500		
LM317LDCR	296-17220-1-ND	3-Terminal Adjustable Regulator	8-SOIC	.65	.43	.36	
LM317LDCR	296-17220-2-ND	3-Terminal Adjustable Regulator	8-SOIC	—	370.31/2,500		
LM317LCPK	296-26093-1-ND	100mA Adjustable Pos. Reg. * NEW!	SOT-89-3	.86	.68	.60	
LM317LCPK	296-26093-2-ND	100mA Adjustable Pos. Reg. * NEW!	SOT-89-3	—	316.45/1,000		
LM317LCPWR	296-17222-1-ND	3-Terminal Adjustable Regulator	8-TSSOP	.65	.43	.36	
LM317LCPWR	296-17222-2-ND	3-Terminal Adjustable Regulator	8-TSSOP	—	296.25/2,000		
LM317LDR	296-20678-1-ND	3-Terminal Adjustable Regulator	8-SOIC	.72	.47	.39	
LM317LDR	296-20678-2-ND	3-Terminal Adjustable Regulator	8-SOIC	—	406.78/2,500		
LM317LILPR	296-20679-1-ND	3-Terminal Adjustable Regulator	TO-92	.72	.47	.39	
LM317LILPR	296-20679-2-ND	3-Terminal Adjustable Regulator	TO-92	—	325.88/2,000		
LM317LILPK	296-21742-1-ND	3-Terminal Adjustable Regulator	SOT-89	.91	.71	.62	
LM317LILPK	296-21742-2-ND	3-Terminal Adjustable Regulator	SOT-89	—	329.92/1,000		
LM317LIPWR	296-20680-1-ND	3-Terminal Adjustable Regulator	8-TSSOP	.72	.47	.39	
LM317LIPWR	296-20680-2-ND	3-Terminal Adjustable Regulator	8-TSSOP	—	325.88/2,000		
LM317MDCY	296-26095-5-ND	3-Terminal Adjustable Reg. * NEW!	SOT-223-4	1.03	83	73	
LM317MDCYR	296-23127-1-ND	3-Terminal Adjustable Regulator	SOT-223-4	1.19	93	82	
LM317MODCYRG4	296-23127-2-ND	3-Terminal Adjustable Regulator	SOT-223-4	—	984.70/2,500		
LM337K	296-9550-5-ND	Adj., 1.5A Negative Voltage Regulator	TO-220-3	1.04			