













ON Semiconductor   (Cont.)			SIGNAL/INTERFACE		
Digi-Key Part No.	Description	Pkg.	Price Each*		
			1	25	100
MC3302PGOS-ND	Single Supply Quad Comparators*	14-Dip	.86	.67	.58
MC3303PGOS-ND	Single Supply Quad Op Amp*	14-Dip	.86	.67	.58
MC3403DR2GOSCT-ND	Single Supply Quad Op Amp*	14-SOIC	.92	.65	.56
MC3403DR2GOSTR-ND	Single Supply Quad Op Amp*	14-SOIC	648.05/2,500		
MC3403PGOS-ND	Single Supply Quad Op Amp*	14-Dip	.86	.67	.58
MC14553BCPGOS-ND	3-Digit BCD Counter*	16-Dip	2.81	2.27	2.04
MC33035DRWR2GOSCT-ND	Brushless DC Motor Controller*	24-SOIC	5.29	4.32	3.88
MC33035DRWR2GOSTR-ND	Brushless DC Motor Controller*	24-SOIC	2466.51/1,000		
MC33071ADGOS-ND	Single Supply Op Amp*	8-SOIC	1.26	1.01	.88
MC33072ADGOS-ND	Single Supply Dual Op Amp*	8-SOIC	1.14	.92	.80
MC33072ADR2GOSCT-ND	Single Supply Dual Op Amp*	8-SOIC	1.23	.98	.88
MC33072ADR2GOSTR-ND	Single Supply Dual Op Amp*	8-SOIC	1138.99/2,500		
MC33072APGOS-ND	Single Supply Dual Op Amp*	8-Dip	1.26	1.01	.88
MC33072DGO-ND	Single Supply Dual Op Amp*	8-SOIC	1.10	.88	.77
MC33072DR2GOSCT-ND	Single Supply Dual Op Amp*	8-SOIC	1.19	.95	.85
MC33072DR2GOSTR-ND	Single Supply Dual Op Amp*	8-SOIC	1099.72/2,500		
MC33072PGOS-ND	Single Supply Dual Op Amp*	8-Dip	1.22	.98	.86
MC33074ADGOS-ND	Single Supply Quad Op Amp*	14-SOIC	1.77	1.42	1.24
MC33074ADR2GOSCT-ND	Single Supply Quad Op Amp*	14-SOIC	1.92	1.52	1.37
MC33074ADR2GOSTR-ND	Single Supply Quad Op Amp*	14-SOIC	1767.40/2,500		
MC33074APGOS-ND	Single Supply Quad Op Amp*	14-Dip	1.77	1.42	1.24
MC33074DGO-ND	Single Supply Quad Op Amp*	14-SOIC	1.73	1.39	1.21
MC33074DR2GOSCT-ND	Single Supply Quad Op Amp*	14-SOIC	1.87	1.49	1.34
MC33074DR2GOSTR-ND	Single Supply Quad Op Amp*	14-SOIC	1728.13/2,500		
MC33074PGOS-ND	Single Supply Quad Op Amp*	14-Dip	1.73	1.39	1.21
MC33078DGO-ND	Low Noise Dual Op Amp*	8-SOIC	1.07	.85	.75
MC33078PGOS-ND	Low Noise Dual Op Amp*	8-Dip	1.46	1.17	1.02
MC33078DR2GOSCT-ND	Low Noise Dual Op Amp*	8-SOIC	1.16	.91	.82
MC33078DR2GOSTR-ND	Low Noise Dual Op Amp*	8-SOIC	1060.44/2,500		
MC33079DGO-ND	Low Noise Quad Op Amp*	14-SOIC	1.18	.95	.83
MC33079DR2GOSCT-ND	Low Noise Quad Op Amp*	14-SOIC	1.28	1.01	.91
MC33079DR2GOSTR-ND	Low Noise Quad Op Amp*	14-SOIC	1178.27/2,500		
MC33079PGOS-ND	Low Noise Quad Op Amp*	14-Dip	1.62	1.29	1.13
MC33171DGO-ND	Single Supply Low Power Op Amp*	8-SOIC	1.22	.98	.86
MC33171DR2GOSCT-ND	Single Supply Low Power Op Amp*	8-SOIC	1.32	1.05	.94
MC33171DR2GOSTR-ND	Single Supply Low Power Op Amp*	8-SOIC	1217.54/2,500		
MC33171PGOS-ND	Single Supply Low Power Op Amp*	8-Dip	1.22	.98	.86
MC33172DGO-ND	Single Supply Low Power Dual Op Amp*	8-SOIC	1.18	.95	.83
MC33172DR2GOSCT-ND	Single Supply, Low Power Dual Op Amp*	8-SOIC	1.28	1.01	.91
MC33172DR2GOSTR-ND	Single Supply, Low Power Dual Op Amp*	8-SOIC	1178.27/2,500		
MC33172PGOS-ND	Single Supply Low Power Dual Op Amp*	8-Dip	1.54	1.23	1.08
MC33174DGO-ND	Single Supply Low Power Quad Op Amp*	14-SOIC	1.77	1.42	1.24
MC33174DR2GOSCT-ND	Single Supply Low Power Quad Op Amp*	14-SOIC	1.92	1.52	1.37
MC33174DR2GOSTR-ND	Single Supply Low Power Quad Op Amp*	14-SOIC	1767.40/2,500		
MC33174PGOS-ND	Single Supply Low Power Quad Op Amp*	14-Dip	1.77	1.42	1.24
MC33178DGO-ND	Dual Low Power, Low Noise Op Amp*	8-SOIC	1.22	.98	.86
MC33178DR2GOSCT-ND	Dual Low Power, Low Noise Op Amp*	8-SOIC	1.32	1.05	.94
MC33178DR2GOSTR-ND	Dual Low Power, Low Noise Op Amp*	8-SOIC	1217.54/2,500		
MC33178PGOS-ND	Dual Low Power, Low Noise Op Amp*	8-Dip	1.65	1.32	1.16
MC33179DGO-ND	Quad Low Power, Low Noise Op Amp*	14-SOIC	1.77	1.42	1.24
MC33179DR2GOSCT-ND	Quad Low Power, Low Noise Op Amp*	14-SOIC	1.92	1.52	1.37
MC33179DR2GOSTR-ND	Quad Low Power, Low Noise Op Amp*	14-SOIC	1767.40/2,500		
MC33179PGOS-ND	Quad Low Power, Low Noise Op Amp*	14-Dip	1.77	1.42	1.24
MC33201DGO-ND	Low Voltage, Rail-to-Rail Op Amp*	8-SOIC	1.57	1.26	1.10
MC33201PGOS-ND	Low Voltage, Rail-to-Rail Op Amp*	8-Dip	1.57	1.26	1.10
MC33202DGO-ND	Dual Low Voltage, Rail-to-Rail Op Amp*	8-SOIC	1.38	1.10	.97
MC33202MR2GOSCT-ND	Dual Low Volt., Rail-to-Rail Op Amp*	8-Micro	1.54	1.22	1.10
MC33202MR2GOSTR-ND	Dual Low Volt., Rail-to-Rail Op Amp*	8-Micro	2262.27/4,000		
MC33202DR2GOSCT-ND	Dual Low Voltage Rail-to-Rail Op Amp*	8-SOIC	1.49	1.18	1.07
MC33202DR2GOSTR-ND	Dual Low Voltage Rail-to-Rail Op Amp*	8-SOIC	1374.65/2,500		
MC33202PGOS-ND	Dual Low Voltage, Rail-to-Rail Op Amp*	8-Dip	1.38	1.10	.97
MC33204DGO-ND	Quad Low Voltage Rail-to-Rail Op Amp*	14-SOIC	1.81	1.46	1.32
MC33204DR2GOSCT-ND	Quad Low Voltage Rail-to-Rail Op Amp*	14-SOIC	2.04	1.58	1.43
MC33204DR2GOSTR-ND	Quad Low Voltage Rail-to-Rail Op Amp*	14-SOIC	1969.39/2,500		
MC33204TBGO-ND	Quad Low Volt., Rail-to-Rail Op Amp*	14-TSSOP	1.87	1.52	1.37
MC33204PGOS-ND	Quad Low Voltage Rail-to-Rail Op Amp*	14-Dip	1.81	1.46	1.32
MC33227ADGOS-ND	Dual High Slew Rate Op Amp*	8-SOIC	1.74	1.41	1.27
MC33227ADR2GOSCT-ND	Dual Single Supply, High Slew Rate Op Amp*	8-SOIC	1.96	1.52	1.38
MC33227ADR2GOSTR-ND	Dual Single Supply, High Slew Rate Op Amp*	8-SOIC	1893.65/2,500		
MC33274ADGOS-ND	Quad High Slew Rate Op Amp*	14-SOIC	2.15	1.74	1.57
MC33274ADR2GOSCT-ND	Quad High Slew Rate Op Amp*	14-SOIC	2.44	1.88	1.71
MC33274ADR2GOSTR-ND	Quad High Slew Rate Op Amp*	14-SOIC	2348.12/2,500		
MC33274APGOS-ND	Quad High Slew Rate Op Amp*	14-Dip	2.15	1.74	1.57
MC33502DGO-ND	1.0V, Rail-to-Rail, Dual Op Amp*	8-SOIC	2.27	1.83	1.65
MC34071ADGOS-ND	Single Supply Op Amp*	8-SOIC	1.18	.95	.83
MC34071APGOS-ND	Single Supply Op Amp*	8-Dip	1.18	.95	.83
MC34071DGO-ND	Single Supply Op Amp*	8-SOIC	1.14	.92	.80
MC34071PGOS-ND	Single Supply Op Amp*	8-Dip	1.14	.92	.80
MC34072ADGOS-ND	Single Supply Dual Op Amp*	8-SOIC	1.22	.98	.86
MC34072APGOS-ND	Single Supply Dual Op Amp*	8-Dip	1.22	.98	.86
MC34072DGO-ND	Single Supply Dual Op Amp*	8-SOIC	1.14	.92	.80
MC34072DR2GOSCT-ND	Single Supply Dual Op Amp*	8-SOIC	1.23	.98	.88
MC34072DR2GOSTR-ND	Single Supply Dual Op Amp*	8-SOIC	1138.99/2,500		
MC34072PGOS-ND	Single Supply Dual Op Amp*	8-Dip	1.18	.95	.83
MC34074ADGOS-ND	Single Supply Quad Op Amp*	14-SOIC	1.73	1.39	1.21
MC34074ADR2GOSCT-ND	Single Supply Quad Op Amp*	14-SOIC	1.87	1.49	1.34
MC34074ADR2GOSTR-ND	Single Supply Quad Op Amp*	14-SOIC	1728.13/2,500		
MC34074APGOS-ND	Single Supply Quad Op Amp*	14-Dip	1.73	1.39	1.21
MC34074DGO-ND	Single Supply Quad Op Amp*	14-SOIC	1.69	1.36	1.19
MC34074DR2GOSCT-ND	Single Supply Quad Op Amp*	14-SOIC	1.83	1.45	1.31
MC34074DR2GOSTR-ND	Single Supply Quad Op Amp*	14-SOIC	1688.85/2,500		
MC34074PGOS-ND	Single Supply Quad Op Amp*	14-Dip	1.69	1.36	1.19
NC60000DTR2OSCT-ND	Compact Smart Card Interface IC	20-TSSOP	4.15	3.40	3.05
NCP100SNT1GOSCT-ND	Sub TV Precision Adj. Shunt Regulator*	SOT23-5	1.16	.91	.82
NCP100SNT1GOSTR-ND	Sub TV Precision Adj. Shunt Regulator*	SOT23-5	1272.53/3,000		
NCP120060R2GOSCT-ND	60kHz PWM Current Mode Controller*	8-SOIC	1.31	1.04	.94
NCP120060R2GOSTR-ND	60kHz PWM Current Mode Controller*	8-SOIC	1206.32/2,500		
NCV1124DGO-ND	Dual Variable-Reluctance Sensor Interface*	8-SOIC	2.68	2.17	1.95
NE521NGOS-ND	Dual Differential Comparator/Sense Amp*	14-Dip	4.76	3.83	3.49
NE5517ANGOS-ND	Dual Operational Transconductance Amp*	16-Dip	2.44	1.97	1.77



ON Semiconductor   (Cont.)			SIGNAL/INTERFACE		
Digi-Key Part No.	Description	Pkg.	Price Each*		
			1	25	100
NE5517DGO-ND	Dual Op Transconductance Amp*	16-SOIC	2.33	1.88	1.70
NE5532ANGOS-ND	Dual Low Noise Op Amp*	8-Dip	1.57	1.26	1.10
NE5532DGO-ND	Dual Low Noise Op Amp*	16-SOIC	1.57	1.26	1.10
NE5532NGOS-ND	Dual Low Noise Op Amp*	8-Dip	1.49	1.20	1.05
SA571DGO-ND	Dual Gain Compandor*	16-SOIC	6.28	5.05	4.61
SA571NGOS-ND	Dual Gain Compandor*	16-Dip	6.44	5.18	4.72
SA572NGOS-ND	Dual Gain Compandor, Programmable*	16-Dip	7.10	5.71	5.20
SA575DGO-ND	Dual Gain Compandor, Low Voltage*	20-SOIC	7.55	6.19	5.59
SE5532ADGOS-ND	Dual Low Noise Op Amp*	8-SOIC	1.85	1.48	1.30
TC40372DP1GOS-ND	Dual 1A Output Current Op Amp*	8-Dip	1.55	1.24	1.09
TC40372DP2GOS-ND	1A Dual Power Op Amp*	16-Dip	1.50	1.21	1.06
TC40372DR2GOSCT-ND	Dual 1A Output Current Op Amp*	16-SOIC	1.48	1.18	1.06
TC40372DR2GOSTR-ND	Dual 1A Output Current Op Amp*	16-SOIC	585.77/1,000		

ON Semiconductor   (Cont.)			SMALL SIGNAL		
Digi-Key Part No.	Description	Pkg.	Price Each*		
			1	25	100
MMBV609L1T1GOSCT-ND	20V, Silicon Tuning Diode*	SOT-23	.50	.33	.27
MMBV609L1T1GOSTR-ND	20V, Silicon Tuning Diode*	SOT-23	340.01/3,000		
MMBV2109L1T1GOSCT-ND	30V, Silicon Tuning Diode	SOT-23	.58	.35	.28
MMBV3401L1T1GOSCT-ND	35V, Silicon Pin Diode*	SOT-23	.50	.33	.27
MMBV3401L1T1GOSTR-ND	35V, Silicon Pin Diode*	SOT-23	340.01/3,000		

ON Semiconductor   (Cont.)			SUPERVISORY CIRCUITS/RESET GENERATORS		
Digi-Key Part No.	Description	Pkg.	Price Each*		
			1	25	100
ADM1026JSTZ-ND	Control System Reference/EEPROM*	48-LQFP	12.34	10.38	9.54
ADM1026JSTZ-R7CT-ND	Control System Reference/EEPROM*	48-LQFP	12.90	10.95	10.10
ADM1026JSTZ-R7TR-ND	Control System Reference/EEPROM*	48-LQFP	4067.83/500		

ON Semiconductor   (Cont.)			SRAM RoHS Compliant			
On Semiconductor Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*		
				1	25	100
N645830HAS22I	766-1045-ND	8K x 8 Bit 64Kb Low Power Serial SRAMs	8-SOIC	3.37	2.71	2.47
N645830HAT22I	766-1046-5-ND	8K x 8 Bit 64Kb Low Power Serial SRAMs	8-TSSOP	3.37	2.71	2.47
N25S18HAS21I	766-1041-ND	32K x 8 Bit 256Kb Low Power Serial SRAMs	8-SOIC	3.89	3.14	2.86
N25S18HAT21I	766-1042-5-ND	32K x 8 Bit 256Kb Low Pwr Serial SRAMs	8-TSSOP	3.89	3.14	2.86
N25S30HAS22I	766-1043-ND	32K x 8 Bit 256Kb Low Power Serial SRAMs	8-SOIC	3.89	3.14	2.86
N25S30HAT22I	766-1044-ND	32K x 8 Bit 256Kb Low Pwr Serial SRAMs	8-TSSOP	3.89	3.14	2.86

ON Semiconductor   (Cont.)			SWITCHING		
Digi-Key Part No.	Description	Pkg.	Price Each*		
			1	25	100
LM2574N-3.3GOS-ND	0.5A, 3.3V Step-Down Switching Reg.*	8-Dip	2.00	1.61	1.45
LM2575D2T-5GOS-ND	1A, 5V Step-Down Switching Regulator*	D2PAK-5	2.86	2.31	2.08
LM2576D2T-ADJGOS-ND	3A, Adj. Step-Down Switching Regulator*	D2PAK-5	2.98	2.41	2.17
LM2576T-005GOS-ND	3A, 5V Step-Down Switching Reg.*	TO-220-5	2.81	2.27	2.04
LM2576T-1V1ADJGOS-ND	3A, Adj. Step-Down Switching Reg.*	TO-220-5	2.81	2.27	2.04
NLAS323USGOSCT-ND	Dual SPST Analog Switch*	USB-8	99.77	.68	
NLAS323USGOSTR-ND	Dual SPST Analog Switch*	USB-8	97.28/3,000		
NLAS1053USGOSCT-ND	2:1 Mux/Demux Analog Switch	USB-8	1.10	.87	.79
NLAS1053USGOSCT-ND	2:1 Mux/Demux Analog Switch*	USB-8	1.07	.85	.76
NLAS1053USGOSTR-ND	2:1 Mux/Demux Analog Switch*	USB-8	1178.27/3,000		
NLAS8252MUTAGOSCT-ND	DP3T Switch for USB/UART Data Mux*	12-UQFN	95.76	.68	

ON Semiconductor   (Cont.)			TVS		
Digi-Key Part No.	Description	Pkg.	Price Each*		
			1	25	100
NUF2221W1T2OSCT-ND	USB Upstream Terminator with ESD Protection	SOT-363	.92	.73	.66
NUF2221W1T2OSTR-ND	USB Upstream Terminator with ESD Protection	SOT-363	1121.04/3,000		
NUF2221W1T2GOSCT-ND	USB Upstream Terminator w/ESD Protection*	SOT-363	.76	.54	