

AMPLIFIERS AND COMPARATORS						
STMicroelectronics		DigiKey Reel		RoHS Compliant Parts Available		
Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*		
				1	10	100
TSV612AIDT	497-10457-2-ND	I/O, R/R, 120kHz Op Amp * NEW!	8-SOIC	1989.03/2,500		
TSV622AIDT	497-8986-1-ND	I/O, R/R, 420kHz Op Amp * NEW!	8-SOIC	1.89 1.69 1.34		
TSV622AIST	497-8986-2-ND	I/O, R/R, 420kHz Op Amp * NEW!	8-SOIC	1730.93/2,500		
TSV623AIST	497-8987-1-ND	I/O, R/R, 420kHz Op Amp * NEW!	8-MSOP	1.93 1.73 1.37		
TSV622AIST	497-8987-2-ND	I/O, R/R, 420kHz Op Amp * NEW!	8-MSOP	2841.31/4,000		
TSV622IDT	497-8988-1-ND	I/O, R/R, 420kHz Op Amp * NEW!	8-SOIC	1.35 1.21 96		
TSV622IDT	497-8988-2-ND	I/O, R/R, 420kHz Op Amp * NEW!	8-SOIC	1237.18/2,500		
TSV622IST	497-8989-1-ND	I/O, R/R, 420kHz Op Amp * NEW!	8-MSOP	1.39 1.25 99		
TSV622IST	497-8989-2-ND	I/O, R/R, 420kHz Op Amp * NEW!	8-MSOP	2046.82/4,000		
TSV623AIST	497-8990-1-ND	I/O, R/R, 420kHz Op Amp * NEW!	10-MSOP	1.93 1.73 1.37		
TSV623AIST	497-8990-2-ND	I/O, R/R, 420kHz Op Amp * NEW!	10-MSOP	2841.31/4,000		
TSV623IST	497-8991-1-ND	I/O, R/R, 420kHz Op Amp * NEW!	10-MSOP	1.53 1.37 1.09		
TSV623IST	497-8991-2-ND	I/O, R/R, 420kHz Op Amp * NEW!	10-MSOP	2244.32/4,000		
TSV624AIPD	497-8992-1-ND	I/O, R/R, 420kHz Op Amp * NEW!	14-TSSOP	2.73 2.34 1.91		
TSV624AIPD	497-8992-2-ND	I/O, R/R, 420kHz Op Amp * NEW!	14-TSSOP	2625.85/2,500		
TSV624IPT	497-8993-1-ND	I/O, R/R, 420kHz Op Amp * NEW!	14-TSSOP	2.11 1.89 1.50		
TSV624IPT	497-8993-2-ND	I/O, R/R, 420kHz Op Amp * NEW!	14-TSSOP	1941.34/2,500		
TSV630ICT	497-8539-1-ND	Single, I/O, R/R, 880kHz Op Amp *	SC70-6	1.17 1.05 83		
TSV630ICT	497-8539-2-ND	Single, I/O, R/R, 880kHz Op Amp *	SC70-6	1286.00/3,000		
TSV630ILT	497-8540-1-ND	Single, I/O, R/R, 880kHz Op Amp *	SOT-23-6	1.26 1.13 90		
TSV630ILT	497-8540-2-ND	Single, I/O, R/R, 880kHz Op Amp *	SOT-23-6	1386.99/3,000		
TSV631AICT	497-8541-1-ND	Single, I/O, R/R, 880kHz Op Amp *	SC70-5	1.66 1.49 1.18		
TSV631AICT	497-8541-2-ND	Single, I/O, R/R, 880kHz Op Amp *	SC70-5	1834.73/3,000		
TSV631AILT	497-8542-1-ND	Single, I/O, R/R, 880kHz Op Amp *	SOT-23-5	1.66 1.49 1.18		
TSV631AILT	497-8542-2-ND	Single, I/O, R/R, 880kHz Op Amp *	SOT-23-5	1834.73/3,000		
TSV631ICT	497-8543-1-ND	Single, I/O, R/R, 880kHz Op Amp *	SC70-5	1.08 97 77		
TSV631ICT	497-8543-2-ND	Single, I/O, R/R, 880kHz Op Amp *	SC70-5	1188.37/3,000		
TSV632AIDT	497-8994-1-ND	I/O, R/R, 880kHz Op Amp * NEW!	8-SOIC	1.89 1.69 1.34		
TSV632AIDT	497-8994-2-ND	I/O, R/R, 880kHz Op Amp * NEW!	8-SOIC	1730.93/2,500		
TSV632AIST	497-8995-1-ND	I/O, R/R, 880kHz Op Amp * NEW!	8-MSOP	1.93 1.73 1.37		
TSV632AIST	497-8995-2-ND	I/O, R/R, 880kHz Op Amp * NEW!	8-MSOP	2841.31/4,000		
TSV632IDT	497-8996-1-ND	I/O, R/R, 880kHz Op Amp * NEW!	8-SOIC	1.35 1.21 96		
TSV632IDT	497-8996-2-ND	I/O, R/R, 880kHz Op Amp * NEW!	8-SOIC	1237.18/2,500		
TSV632IST	497-8997-1-ND	I/O, R/R, 880kHz Op Amp * NEW!	8-MSOP	1.39 1.25 99		
TSV632IST	497-8997-2-ND	I/O, R/R, 880kHz Op Amp * NEW!	8-MSOP	2046.82/4,000		
TSV633AIST	497-8998-1-ND	I/O, R/R, 880kHz Op Amp * NEW!	10-MSOP	1.93 1.73 1.37		
TSV633AIST	497-8998-2-ND	I/O, R/R, 880kHz Op Amp * NEW!	10-MSOP	2841.31/4,000		
TSV633IST	497-8999-1-ND	I/O, R/R, 880kHz Op Amp * NEW!	10-MSOP	1.53 1.37 1.09		
TSV633IST	497-8999-2-ND	I/O, R/R, 880kHz Op Amp * NEW!	10-MSOP	2244.32/4,000		
TSV634AIPD	497-9000-1-ND	I/O, R/R, 880kHz Op Amp * NEW!	14-TSSOP	2.73 2.34 1.91		
TSV634AIPD	497-9000-2-ND	I/O, R/R, 880kHz Op Amp * NEW!	14-TSSOP	2625.85/2,500		
TSV634IPT	497-9001-1-ND	I/O, R/R, 880kHz Op Amp * NEW!	14-TSSOP	2.11 1.89 1.50		
TSV634IPT	497-9001-2-ND	I/O, R/R, 880kHz Op Amp * NEW!	14-TSSOP	1941.34/2,500		
TSV635AIPD	497-9002-1-ND	I/O, R/R, 880kHz Op Amp * NEW!	16-TSSOP	2.85 2.45 2.00		
TSV635AIPD	497-9002-2-ND	I/O, R/R, 880kHz Op Amp * NEW!	16-TSSOP	2746.49/2,500		
TSV635IPT	497-9003-1-ND	I/O, R/R, 880kHz Op Amp * NEW!	16-TSSOP	2.02 1.74 1.42		
TSV635IPT	497-9003-2-ND	I/O, R/R, 880kHz Op Amp * NEW!	16-TSSOP	1949.75/2,500		
TSV911AIDYT	497-10466-1-ND	I/O, R/R, 8mHz Op Amp * NEW!	8-SOIC	1.30 1.17 93		
TSV911AIDYT	497-10466-2-ND	I/O, R/R, 8mHz Op Amp * NEW!	8-SOIC	1197.91/2,500		
TSV911AILT	497-10467-1-ND	I/O, R/R, 8mHz Op Amp * NEW!	SOT-23-5	1.62 1.45 1.15		
TSV911AILT	497-10467-2-ND	I/O, R/R, 8mHz Op Amp * NEW!	SOT-23-5	1780.87/3,000		
TSV911YDT	497-10468-1-ND	I/O, R/R, 8mHz Op Amp * NEW!	8-SOIC	1.03 90 71		
TSV911YDT	497-10468-2-ND	I/O, R/R, 8mHz Op Amp * NEW!	8-SOIC	856.65/2,500		
TSV911YLT	497-10469-1-ND	I/O, R/R, 8mHz Op Amp * NEW!	SOT-23-5	1.08 97 77		
TSV911YLT	497-10469-2-ND	I/O, R/R, 8mHz Op Amp * NEW!	SOT-23-5	1188.37/3,000		
TSV912AIDYT	497-10470-1-ND	I/O, R/R, 8mHz Op Amp * NEW!	8-SOIC	1.62 1.45 1.15		
TSV912AIDYT	497-10470-2-ND	I/O, R/R, 8mHz Op Amp * NEW!	8-SOIC	1484.06/2,500		
TSV912AYST	497-10471-1-ND	I/O, R/R, 8mHz Op Amp * NEW!	8-MSOP	1.62 1.45 1.15		
TSV912AYST	497-10471-2-ND	I/O, R/R, 8mHz Op Amp * NEW!	8-MSOP	2374.49/4,000		
TSV912YDT	497-10472-1-ND	I/O, R/R, 8mHz Op Amp * NEW!	8-SOIC	1.44 1.29 1.02		
TSV912YDT	497-10472-2-ND	I/O, R/R, 8mHz Op Amp * NEW!	8-SOIC	1318.54/2,500		
TSV914IDYT	497-10473-1-ND	I/O, R/R, 8mHz Op Amp * NEW!	14-SOIC	2.02 1.74 1.42		
TSV914IDYT	497-10473-2-ND	I/O, R/R, 8mHz Op Amp * NEW!	14-SOIC	1949.75/2,500		
TSV6294AIPD	497-10458-2-ND	Micropower, Wide CMOS Op Amp * NEW!	14-TSSOP	1941.34/2,500		
TSV6294IPT	497-10459-1-ND	Micropower, Wide CMOS Op Amp * NEW!	14-TSSOP	1.66 1.49 1.18		
TSV6294IPT	497-10459-2-ND	Micropower, Wide CMOS Op Amp * NEW!	14-TSSOP	1528.94/2,500		
TSV6295AIPD	497-10460-1-ND	Micropower, Wide CMOS Op Amp * NEW!	16-TSSOP	1941.34/2,500		
TSV6295IPT	497-10461-1-ND	Micropower, Wide CMOS Op Amp * NEW!	16-TSSOP	1.66 1.49 1.18		
TSV6295IPT	497-10461-2-ND	Micropower, Wide CMOS Op Amp * NEW!	16-TSSOP	1528.94/2,500		
TSV6394AIPD	497-10462-1-ND	Micropower, Wide CMOS Op Amp * NEW!	14-TSSOP	2.11 1.89 1.50		
TSV6394AIPD	497-10462-2-ND	Micropower, Wide CMOS Op Amp * NEW!	14-TSSOP	1941.34/2,500		
TSV6394IPT	497-10463-1-ND	Micropower, Wide CMOS Op Amp * NEW!	14-TSSOP	1.66 1.49 1.18		
TSV6394IPT	497-10463-2-ND	Micropower, Wide CMOS Op Amp * NEW!	14-TSSOP	1528.94/2,500		
TSV6395AIPD	497-10464-1-ND	Micropower, Wide CMOS Op Amp * NEW!	16-TSSOP	2.11 1.89 1.50		
TSV6395AIPD	497-10464-2-ND	Micropower, Wide CMOS Op Amp * NEW!	16-TSSOP	1941.34/2,500		
TSV6395IPT	497-10465-1-ND	Micropower, Wide CMOS Op Amp * NEW!	16-TSSOP	1.66 1.49 1.18		
TSV6395IPT	497-10465-2-ND	Micropower, Wide CMOS Op Amp * NEW!	16-TSSOP	1528.94/2,500		

AMPLIFIERS AND LINEAR						
STMicroelectronics		DigiKey Reel		RoHS Compliant Parts Available		
Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*		
				1	10	100
L272D013TR	497-8854-1-ND	Dual Power Op Amp * NEW!	16-SOIC	2.59 2.23 1.82		
L272D013TR	497-8854-2-ND	Dual Power Op Amp * NEW!	16-SOIC	2499.61/2,500		
LF253DST	497-7801-1-ND	Wide Bandwidth Dual JFET Op Amp *	8-SOIC	1.66 1.49 1.18		
LF253DST	497-7801-2-ND	Wide Bandwidth Dual JFET Op Amp *	8-SOIC	1528.94/2,500		
LF347D	497-2963-1-ND	Wide Bandwidth Quad JFET Op Amp	14-SOIC	1.09 98 78		

AMPLIFIERS AND LINEAR						
STMicroelectronics		DigiKey Reel		RoHS Compliant Parts Available		
Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*		
				1	10	100
LF347D	497-2963-2-ND	Wide Bandwidth Quad JFET Op Amp	14-SOIC	1001.53/2,500		
LF347N	497-2964-5-ND	Wide Bandwidth Quad JFET Op Amp	14-Dip	1.04 93 73		
LF351D	497-4041-1-ND	Wide Bandwidth Single JFET Op Amp	8-SOIC	1.02 88 70		
LF351D	497-4041-2-ND	Wide Bandwidth Single JFET Op Amp	8-SOIC	838.81/2,500		
LF351N	497-2965-5-ND	Wide Bandwidth Single JFET Op Amp	8-Dip	1.03 91 70		
LF353D	497-2967-1-ND	Wide Bandwidth Dual JFET Op Amp	8-SOIC	1.02 88 70		
LF353D	497-2967-2-ND	Wide Bandwidth Dual JFET Op Amp	8-SOIC	838.81/2,500		
LF353N	497-2968-5-ND	Wide Bandwidth Dual JFET Op Amp	8-Dip	82 72 56		
LM124D	497-2969-5-ND	Low Power Quad Op Amp *	14-SOIC	2.67 2.41 1.94		
LM124D	497-6884-5-ND	Low Power Quad Op Amp *	14-Dip	2.01 1.82 1.46		
LM139ADT	497-6986-1-ND	Low Power Quad Voltage Comparator *	14-SOIC	3.10 2.66 2.17		
LM139ADT	497-6986-2-ND	Low Power Quad Voltage Comparator *	14-SOIC	2984.95/2,500		
LM139D	497-6987-1-ND	Low Power Quad Voltage Comparator *	14-SOIC	2.98 2.63 2.24		
LM139D	497-6987-2-ND	Low Power Quad Voltage Comparator *	14-SOIC	2589.38/2,500		
LM139N	497-6988-5-ND	Low Power Quad Voltage Comparator *	14-Dip	2.59 2.35 1.89		
LM158APT	497-6989-1-ND	Low Power Dual Op Amp *	8-TSSOP	1.26 1.13 90		
LM158APT	497-6989-2-ND	Low Power Dual Op Amp *	8-TSSOP	1849.32/4,000		
LM158D	497-6990-1-ND	Low Power Dual Op Amp *	8-SOIC	2.06 1.77 1.45		
LM158D	497-6990-2-ND	Low Power Dual Op Amp *	8-SOIC	1989.03/2,500		
LM158N	497-6991-5-ND	Low Power Dual Op Amp *	8-Dip	2.38 2.15 1.73		
LM158YDT	497-10204-1-ND	Low Power Dual Op Amp * NEW!	8-SOIC	2.48 2.13 1.74		
LM158YDT	497-10204-2-ND	Low Power Dual Op Amp * NEW!	8-SOIC	2387.40/2,500		
LM193D	497-6992-1-ND	Low Power Dual Voltage Comparator *	8-SOIC	3.89 3.50 2.86		
LM193D	497-6992-2-ND	Low Power Dual Voltage Comparator *	8-SOIC	4309.09/2,500		
LM193N	497-6993-5-ND	Low Power Dual Voltage Comparator *	8-Dip	3.61 3.37 2.62		
LM201AD	497-4042-5-ND	Single Op Amp	8-SOIC	1.73 1.54 1.22		
LM201AN	497-2970-5-ND	Single Op Amp	8-Dip	1.69 1.50 1.19		
LM211D	497-1542-1-ND	Voltage Comparator	8-SOIC	84 68 51		
LM211D	497-1542-2-ND	Voltage Comparator	8-SOIC	594.74/2,500		
LM211N	497-7319-5-ND	Voltage Comparator *	8-Dip	68 60 47		
LM219D	497-1544-1-ND	High Speed Dual Comparator	14-SOIC	1.55 1.39 1.10		
LM219D	497-1544-2-ND	High Speed Dual Comparator	14-SOIC	1425.14/2,500		
LM219N	497-7323-5-ND	High Speed Dual Comparator *	14-Dip	1.62 1.43 1.03		
LM224AD	497-1545-1-ND	Low Power Quad Op Amp	14-SOIC	95 83 66		
LM224AD	497-1545-2-ND	Low Power Quad Op Amp	14-SOIC	788.32/2,500		
LM224AN	497-1546-5-ND	Low Power Quad Op Amp	14-Dip	98 86 67		
LM224APT	497-4043-1-ND	Low Power Quad Op Amp	14-TSSOP	99 86 68		
LM224APT	497-4043-2-ND	Low Power Quad Op Amp	14-TSSOP	813.57/2,500		
LM224D	497-2972-1-ND	Low Power Quad Op Amp	14-SOIC			