

STMicroelectronics		DigiKey (Cont.)		AMPLIFIERS AND LINEAR RoHS Compliant Parts Available		
STMicroelectronics Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*		
				1	10	100
LM339AN	497-1587-5-ND	Low Power Quad Voltage Comparator	14-Dip	.56	.48	.36
LM339APT	497-8346-1-ND	Low Power Quad Voltage Comparator*	14-TSSOP	.90	.72	.54
LM339BPT	497-8346-2-ND	Low Power Quad Voltage Comparator*	14-TSSOP	631.22/2,500		
LM339DPT	497-1588-1-ND	Low Power Quad Voltage Comparator	14-SOIC	.57	.46	.32
LM339DT	497-1588-2-ND	Low Power Quad Voltage Comparator	14-SOIC	328.23/2,500		
LM339T	497-1589-5-ND	Low Power Quad Voltage Comparator	14-Dip	.48	.41	.31
LM339PT	497-4048-1-ND	Low Power Quad Voltage Comparator	14-TSSOP	.83	.67	.50
LM339T	497-4048-2-ND	Low Power Quad Voltage Comparator	14-TSSOP	583.52/2,500		
LM346N	497-2980-5-ND	Programmable Quad Bipolar Op Amp	16-Dip	1.76	1.56	1.24
LM348DT	497-4049-1-ND	Four UA741 Quad Bipolar Op Amp	14-SOIC	1.17	1.02	.80
LM348N	497-2981-5-ND	Four UA741 Quad Bipolar Op Amp	14-Dip	.99	.88	.70
LM358ADT	497-1590-1-ND	Low Power Dual Op Amp	8-SOIC	.62	.50	.38
LM358ADT	497-1590-2-ND	Low Power Dual Op Amp	8-SOIC	434.84/2,500		
LM358AN	497-2983-5-ND	Low Power Dual Op Amp	8-Dip	.54	.45	.34
LM358APT	497-5367-1-ND	Low Power Dual Op Amp*	8-TSSOP	.75	.60	.45
LM358BPT	497-5367-2-ND	Low Power Dual Op Amp*	8-TSSOP	843.86/4,000		
LM358AST	497-7332-1-ND	Low Power Dual Op Amp*	8-Mini SOIC	.65	.52	.39
LM358AST	497-7332-2-ND	Low Power Dual Op Amp*	8-Mini SOIC	731.65/4,000		
LM358DPT	497-1591-1-ND	Low Power Dual Op Amp	8-SOIC	.58	.46	.32
LM358DT	497-1591-2-ND	Low Power Dual Op Amp	8-SOIC	333.84/2,500		
LM358N	497-1592-5-ND	Low Power Dual Op Amp	8-Dip	.48	.41	.31
LM358PT	497-8455-1-ND	Low Power Dual Op Amp*	8-TSSOP	.58	.47	.36
LM358PT	497-8455-2-ND	Low Power Dual Op Amp*	8-TSSOP	659.83/4,000		
LM358ST	497-6456-1-ND	Low Power Dual Op Amp*	8-Mini SOIC	.65	.52	.39
LM358ST	497-6456-2-ND	Low Power Dual Op Amp*	8-Mini SOIC	731.65/4,000		
LM358YDT	497-10177-1-ND	Low Power Dual Op Amp* NEW!	8-SOIC	.65	.52	.39
LM358YDT	497-10177-2-ND	Low Power Dual Op Amp* NEW!	8-SOIC	457.28/2,500		
LM393ADT	497-4267-1-ND	Low Power Dual Voltage Comparator	8-SOIC	.71	.57	.43
LM393ADT	497-4267-2-ND	Low Power Dual Voltage Comparator	8-SOIC	499.36/2,500		
LM393AN	497-6881-5-ND	Low Power Dual Voltage Comparator*	8-Dip	.73	.62	.47
LM393DT	497-1593-1-ND	Low Power Dual Voltage Comparator	8-SOIC	.58	.46	.32
LM393DT	497-1593-2-ND	Low Power Dual Voltage Comparator	8-SOIC	333.84/2,500		
LM393N	497-1594-5-ND	Low Power Dual Voltage Comparator*	8-Dip	.48	.41	.31
LM393PT	497-7333-1-ND	Low Power Dual Voltage Comparator*	8-TSSOP	.68	.55	.41
LM393PT	497-7333-2-ND	Low Power Dual Voltage Comparator*	8-TSSOP	767.56/4,000		
LM393ST	497-7334-1-ND	Low Power Dual Voltage Comparator*	8-Mini SOIC	.68	.55	.41
LM393ST	497-7334-2-ND	Low Power Dual Voltage Comparator*	8-Mini SOIC	767.56/4,000		
LM833DPT	497-1597-2-ND	Low Noise Dual Op Amp	8-SOIC	740.63/2,500		
LM833N	497-1598-5-ND	Low Noise Dual Op Amp	8-Dip	.88	.77	.60
LM833YDT	497-10220-1-ND	Low Noise Dual Op Amp* NEW!	8-SOIC	.99	.86	.68
LM2901DT	497-1555-1-ND	Low Power Quad Voltage Comparator	14-SOIC	.72	.58	.43
LM2901DT	497-1555-2-ND	Low Power Quad Voltage Comparator	14-SOIC	504.97/2,500		
LM2901PT	497-1556-1-ND	Low Power Quad Voltage Comparator*	14-Dip	.62	.53	.40
LM2901PT	497-8454-1-ND	Low Power Quad Voltage Comparator*	14-TSSOP	.83	.67	.50
LM2901PT	497-8454-2-ND	Low Power Quad Voltage Comparator*	14-TSSOP	583.52/2,500		
LM2901YDT	497-10211-1-ND	Low Power Quad Voltage Comparator* NEW!	14-SOIC	1.03	.90	.71
LM2901YDT	497-10211-2-ND	Low Power Quad Voltage Comparator* NEW!	14-SOIC	855.65/2,500		
LM2901YPT	497-10212-1-ND	Low Power Quad Voltage Comparator* NEW!	14-TSSOP	1.03	.90	.71
LM2901YPT	497-10212-2-ND	Low Power Quad Voltage Comparator* NEW!	14-TSSOP	855.65/2,500		
LM2902AWYDT	497-10426-1-ND	Low Power Quad Op Amp* NEW!	14-SOIC	.65	.52	.39
LM2902AWYDT	497-10426-2-ND	Low Power Quad Op Amp* NEW!	14-SOIC	457.28/2,500		
LM2902AWYPT	497-10427-1-ND	Low Power Quad Op Amp* NEW!	14-TSSOP	.65	.52	.39
LM2902AWYPT	497-10427-2-ND	Low Power Quad Op Amp* NEW!	14-TSSOP	457.28/2,500		
LM2902DT	497-1557-1-ND	Low Power Quad Op Amp	14-SOIC	.72	.58	.43
LM2902DT	497-1557-2-ND	Low Power Quad Op Amp	14-SOIC	504.97/2,500		
LM2902N	497-1558-5-ND	Low Power Quad Op Amp	14-Dip	.62	.53	.40
LM2902PT	497-4045-1-ND	Low Power Quad Op Amp	14-TSSOP	.90	.72	.54
LM2902PT	497-4045-2-ND	Low Power Quad Op Amp	14-TSSOP	631.22/2,500		
LM2902WYDT	497-10428-1-ND	Low Power Quad Op Amp* NEW!	14-SOIC	.65	.52	.39
LM2902WYDT	497-10428-2-ND	Low Power Quad Op Amp* NEW!	14-SOIC	457.28/2,500		
LM2902WYPT	497-10429-1-ND	Low Power Quad Op Amp* NEW!	14-TSSOP	.65	.52	.39
LM2902WYPT	497-10429-2-ND	Low Power Quad Op Amp* NEW!	14-TSSOP	457.28/2,500		
LM2902YDT	497-10213-1-ND	Low Power Quad Op Amp* NEW!	14-SOIC	1.03	.90	.71
LM2902YDT	497-10213-2-ND	Low Power Quad Op Amp* NEW!	14-SOIC	855.65/2,500		
LM2902YPT	497-10214-1-ND	Low Power Quad Op Amp* NEW!	14-TSSOP	1.03	.90	.71
LM2902YPT	497-10214-2-ND	Low Power Quad Op Amp* NEW!	14-TSSOP	855.65/2,500		
LM2903DT	497-1559-1-ND	Low Power Dual Voltage Comparator	8-SOIC	.72	.58	.43
LM2903DT	497-1559-2-ND	Low Power Dual Voltage Comparator	8-SOIC	504.97/2,500		
LM2903HDT	497-4260-1-ND	Low Power Dual Voltage Comparator	8-SOIC	1.48	1.33	1.06
LM2903HDT	497-4260-2-ND	Low Power Dual Voltage Comparator	8-SOIC	1363.42/2,500		
LM2903N	497-1560-5-ND	Low Power Dual Voltage Comparator	8-Dip	.62	.53	.40
LM2903PT	497-7328-2-ND	Low Power Dual Voltage Comparator*	8-TSSOP	875.28/4,000		
LM2903YDT	497-10215-1-ND	Low Power Dual Voltage Comparator* NEW!	8-SOIC	1.03	.90	.71
LM2903YDT	497-10215-2-ND	Low Power Dual Voltage Comparator* NEW!	8-SOIC	855.65/2,500		
LM2903YPT	497-10216-1-ND	Low Power Dual Voltage Comparator* NEW!	8-TSSOP	1.03	.90	.71
LM2903YPT	497-10216-2-ND	Low Power Dual Voltage Comparator* NEW!	8-TSSOP	1369.04/4,000		
LM2904DT	497-1561-1-ND	Low Power Dual Op Amp	8-SOIC	.72	.58	.43
LM2904DT	497-1561-2-ND	Low Power Dual Op Amp	8-SOIC	504.97/2,500		
LM2904N	497-1562-5-ND	Low Power Dual Op Amp	8-Dip	.62	.53	.40
LM2904PT	497-4046-1-ND	Low Power Dual Op Amp	8-TSSOP	.68	.55	.41
LM2904PT	497-4046-2-ND	Low Power Dual Op Amp	8-TSSOP	767.56/4,000		
LM2904ST	497-7816-1-ND	Low Power Dual Op Amp*	8-Mini SOIC	.93	.81	.64
LM2904ST	497-7816-2-ND	Low Power Dual Op Amp*	8-Mini SOIC	1229.89/4,000		
LM2904WHD	497-4261-1-ND	Low Power Dual Op Amp	8-SOIC	1.62	1.45	1.15
LM2904WHD	497-4261-2-ND	Low Power Dual Op Amp	8-SOIC	1484.06/2,500		
LM2904YDT	497-10217-1-ND	Low Power Dual Op Amp* NEW!	8-SOIC	1.03	.90	.71
LM2904YDT	497-10217-2-ND	Low Power Dual Op Amp* NEW!	8-SOIC	855.65/2,500		
LM2904YPT	497-10218-1-ND	Low Power Dual Op Amp* NEW!	8-TSSOP	1.03	.90	.71
LM2904YPT	497-10218-2-ND	Low Power Dual Op Amp* NEW!	8-TSSOP	1369.04/4,000		
LM2904YST	497-10219-1-ND	Low Power Dual Op Amp* NEW!	8-MSOP	1.03	.90	.71
LM2904YST	497-10219-2-ND	Low Power Dual Op Amp* NEW!	8-MSOP	1369.04/4,000		
LMV3211LT	497-4941-1-ND	Low Power In/Out R/R Op Amp	SOT-23-5	1.19	1.04	.82
LMV3211LT	497-4941-2-ND	Low Power In/Out R/R Op Amp	SOT-23-5	1181.63/3,000		
LMV3211YLT	497-10221-1-ND	Low Power In/Out R/R Op Amp* NEW!	SOT-23-5	1.14	.99	.78
LMV3211YLT	497-10221-2-ND	Low Power In/Out R/R Op Amp* NEW!	SOT-23-5	1127.77/3,000		
LMV3211RLT	497-4942-1-ND	Low Power In/Out R/R Op Amp	SOT-23-5	1.19	1.04	.82
LMV3211RLT	497-4942-2-ND	Low Power In/Out R/R Op Amp	SOT-23-5	1181.63/3,000		
LMV3241DT	497-4943-1-ND	Low Power Quad In/Out R/R Op Amp	14-SOIC	1.23	1.11	.88

STMicroelectronics		DigiKey (Cont.)		AMPLIFIERS AND LINEAR RoHS Compliant Parts Available		
STMicroelectronics Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*		
				1	10	100
LMV3241DT	497-4943-2-ND	Low Power Quad In/Out R/R Op Amp	14-SOIC	1138.99/2,500		
LMV3241PT	497-4944-1-ND	Low Power Quad In/Out R/R Op Amp	14-TSSOP	1.23	1.11	.88
LMV3241PT	497-4944-2-ND	Low Power Quad In/Out R/R Op Amp	14-TSSOP	1138.99/2,500		
LMV3241YDT	497-10222-1-ND	Low Power Quad In/Out R/R Op Amp* NEW!	14-SOIC	1.19	1.07	.85
LMV3241YDT	497-10222-2-ND	Low Power Quad In/Out R/R Op Amp* NEW!	14-SOIC	1096.91/2,500		
LMV3241YPT	497-10356-1-ND	Low Power Quad In/Out R/R Op Amp* NEW!	14-TSSOP	1.14	.99	.78
LMV3241YPT	497-10356-2-ND	Low Power Quad In/Out R/R Op Amp* NEW!	14-TSSOP	939.81/2,500		
LMV3311CT	497-10355-1-ND	Low Voltage Comparator* NEW!	SC70-5	.93	.81	.64
LMV3311CT	497-10355-2-ND	Low Voltage Comparator* NEW!	SC70-5	922.42/3,000		
LMV3311LT	497-10433-1-ND	Low Voltage Comparator* NEW!	SOT-23-5	.93	.81	.64
LMV3311LT	497-10433-2-ND	Low Voltage Comparator* NEW!	SOT-23-5	922.42/3,000		
LMV3581DT	497-4945-1-ND	Low Power Dual In/Out R/R Op Amp	8-SOIC	1.19	1.04	.82
LMV3581DT	497-4945-2-ND	Low Power Dual In/Out R/R Op Amp	8-SOIC	984.70/2,500		
LMV3581PT	497-4946-1-ND	Low Power Dual In/Out R/R Op Amp	8-TSSOP	.95	.83	.66
LMV3581PT	497-4946-2-ND	Low Power Dual In/Out R/R Op Amp	8-TSSOP	1261.31/4,000		
LS204CDDT	497-7823-1-ND	High Performance Dual Op Amp*	8-SOIC	2.27	1.95	1.59
LS204CDDT	497-7823-2-ND	High Performance Dual Op Amp*	8-SOIC	2188.21/2,500		
LS204CNDT	497-7335-5-ND	High Performance Dual Op Amp*	8-Dip	2.01	1.82	1.46
LS204YDT	497-7824-1-ND	High Performance Dual Op Amp*	8-SOIC	2.27	1.95	1.59
LS204YDT	497-7824-2-ND	High Performance Dual Op Amp*	8-SOIC	2188.21/2,500		
LS204YDPT	497-10223-1-ND	High Performance Dual Op Amp* NEW!	8-SOIC	2.73	2.34	1.91
LS204YDPT	497-10223-2-ND	High Performance Dual Op Amp* NEW!	8-SOIC	2625.85/2,500		
LS404CDDT	497-7825-1-ND	High Performance Quad Op Amp*	14-SOIC	3.22	2.76	2.26
LS404CDDT	497-7825-2-ND	High Performance Quad Op Amp*	14-SOIC	3102.77/2,500		
LS404CNDT	497-7336-5-ND	High Performance Quad Op Amp*	14-Dip	2.85	2.58	2.07
LS404DPT	497-7826-1-ND	High Performance Quad Op Amp*	14-SOIC	3.51	3.01	2.46
LS404DPT	497-7826-2-ND	High Performance Quad Op Amp*	14-SOIC	3383.31/2,500		
LS404IDT	497-7337-5-ND	High Performance Quad Op Amp*	14-Dip	1.82	1.61	1.28
MC1458DT	497-1948-1-ND	High Performance Dual Op Amp	8-SOIC	.91	.73	.55
MC1458DT	497-1948-2-ND	High Performance Dual Op Amp	8-SOIC	639.63/2,500		
MC1458IDT	497-7405-5-ND	High Performance Dual Op Amp*	8-SOIC	.81	.71	.55
MC1458IN	497-1949-5-ND	High Performance Dual Op Amp	8-Dip	.75	.66	.51
MC1458N	497-7406-5-ND	High Performance Dual Op Amp*	8-Dip	.73	.62	.47
MC1558N	497-7407-5-ND	High Performance Dual Op Amp*	8-Dip	.75	.66	.51
MC3303DT	497-4050-1-ND	Low Power Quad Bipolar Op Amp	14-SOIC	1.29	1.16	.92
MC3303DT	497-4050-2-ND	Low Power Quad Bipolar Op Amp	14-SOIC	1189.49/2,500		
MC3303PT	497-7					