

STMicroelectronics		DigiKey (Cont.)		AMPLIFIERS AND LINEAR		
		RoHS Compliant Parts Available		Price Each*		
Part No.	Digi-Key Part No.	Description	Pkg.	1	10	100
TS393IPT	497-8098-1-ND	Micropower Dual CMOS Voltage Comparator*	8-TSSOP	1.08	.97	.77
TS393IPT	497-8098-2-ND	Micropower Dual CMOS Voltage Comparator*	8-TSSOP	1584.49/4,000		
TS393IYDT	497-10246-1-ND	Micropower Dual CMOS Voltage Comparator* NEW!	8-SOIC	1.07	.93	.73
TS393IYDT	497-10246-2-ND	Micropower Dual CMOS Voltage Comparator* NEW!	8-SOIC	878.09/2,500		
TS461CD	497-3039-5-ND	Output Rail-to-Rail Op Amp	8-SOIC	1.09	.95	.74
TS461CDT	497-2281-1-ND	Output Rail-to-Rail Op Amp	8-SOIC	1.19	1.04	.82
TS461CDT	497-2281-2-ND	Output Rail-to-Rail Op Amp	8-SOIC	984.70/2,500		
TS461CLT	497-2282-1-ND	Output Rail-to-Rail Op Amp	SOT-23-5	1.08	.97	.77
TS461CLT	497-2282-2-ND	Output Rail-to-Rail Op Amp	SOT-23-5	1188.37/3,000		
TS462CD	497-5431-5-ND	Output Rail-to-Rail Op Amp*	8-SOIC	.99	.88	.70
TS462CDT	497-2283-1-ND	Output Rail-to-Rail Op Amp	8-SOIC	1.08	.97	.77
TS462CDT	497-2283-2-ND	Output Rail-to-Rail Op Amp	8-SOIC	990.31/2,500		
TS462CPT	497-4067-1-ND	Output Rail-to-Rail Op Amp	8-TSSOP	1.12	1.01	.80
TS462CPT	497-4067-2-ND	Output Rail-to-Rail Op Amp	8-TSSOP	1651.82/4,000		
TS462CST	497-8109-1-ND	Output R/R Op Amp*	8-Mini SOIC	1.30	1.17	.93
TS462CST	497-8109-2-ND	Output R/R Op Amp*	8-Mini SOIC	1916.65/4,000		
TS464CD	497-3040-5-ND	Output Rail-to-Rail Op Amp	14-SOIC	1.16	1.03	.81
TS464CDT	497-2285-1-ND	Output Rail-to-Rail Op Amp	14-SOIC	1.26	1.13	.90
TS464CDT	497-2285-2-ND	Output Rail-to-Rail Op Amp	14-SOIC	1155.82/2,500		
TS464CPT	497-5432-1-ND	Output Rail-to-Rail Op Amp*	14-TSSOP	1.26	1.13	.90
TS507CDT	497-5996-1-ND	High Precision R/R Op Amp*	8-SOIC	2.72	2.33	1.90
TS507CDT	497-5996-2-ND	High Precision R/R Op Amp*	8-SOIC	2617.44/2,500		
TS507CLT	497-6944-1-ND	High Precision R/R Op Amp*	SOT-23-5	2.85	2.45	2.00
TS507CLT	497-6944-2-ND	High Precision R/R Op Amp*	SOT-23-5	3295.78/3,000		
TS507IDT	497-5997-1-ND	High Precision R/R Op Amp*	8-SOIC	2.78	2.45	2.08
TS507ILT	497-8118-1-ND	High Precision R/R Op Amp*	SOT-23-5	2.85	2.45	2.00
TS507ILT	497-8118-2-ND	High Precision R/R Op Amp*	SOT-23-5	3295.78/3,000		
TS507LYLT	497-10249-1-ND	High Precision R/R Op Amp* NEW!	SOT-23-5	2.06	1.77	1.45
TS507LYLT	497-10249-2-ND	High Precision R/R Op Amp* NEW!	SOT-23-5	2386.83/3,000		
TS512AIDT	497-2295-1-ND	Precision Dual Op Amp	8-SOIC	1.80	1.61	1.28
TS512AIDT	497-2295-2-ND	Precision Dual Op Amp	8-SOIC	1649.58/2,500		
TS512AIYDT	497-10250-1-ND	Precision Dual Op Amp* NEW!	8-SOIC	2.36	2.02	1.65
TS512AIYDT	497-10250-2-ND	Precision Dual Op Amp* NEW!	8-SOIC	2269.57/2,500		
TS512IDT	497-2296-1-ND	Precision Dual Op Amp	8-SOIC	1.75	1.51	1.25
TS512IDT	497-2296-2-ND	Precision Dual Op Amp	8-SOIC	1610.30/2,500		
TS512IYDT	497-10251-1-ND	Precision Dual Op Amp* NEW!	8-SOIC	1.80	1.61	1.28
TS512IYDT	497-10251-2-ND	Precision Dual Op Amp* NEW!	8-SOIC	1649.58/2,500		
TS514AIDT	497-4453-1-ND	Precision Quad Op Amp	14-SOIC	2.60	2.23	1.82
TS514AIDT	497-4453-2-ND	Precision Quad Op Amp	14-SOIC	2508.03/2,500		
TS514IDT	497-8119-1-ND	Precision Quad Op Amp*	14-SOIC	2.31	1.98	1.62
TS514IDT	497-8119-2-ND	Precision Quad Op Amp*	14-SOIC	2227.49/2,500		
TS522ID	497-3042-5-ND	Low Noise, Dual Op Amp	8-SOIC	1.57	1.39	1.10
TS522IDT	497-2297-1-ND	Low Noise, Dual Op Amp	8-SOIC	1.71	1.53	1.21
TS522IDT	497-2297-2-ND	Low Noise, Dual Op Amp	8-SOIC	1568.22/2,500		
TS524IDT	497-8120-1-ND	Precision LN Quad Op Amp*	14-SOIC	2.06	1.85	1.47
TS524IDT	497-8120-2-ND	Precision LN Quad Op Amp*	14-SOIC	1896.45/2,500		
TS613ID	497-5434-5-ND	Dual Wide Band Op Amp*	8-SOIC	5.94	5.31	4.35
TS616IDW	497-4454-5-ND	Dual Wide Band Op Amp	8-TSSOP	3.21	2.91	2.34
TS616IDWT	497-4455-1-ND	Dual Wide Band Op Amp	8-TSSOP	3.62	3.12	2.55
TS616IDWT	497-4455-2-ND	Dual Wide Band Op Amp	8-TSSOP	3498.33/2,500		
TS617IDT	497-8529-1-ND	Dual Wide Band Op Amp*	14-SOIC	3.71	3.19	2.60
TS617IDT	497-8529-2-ND	Dual Wide Band Op Amp*	14-SOIC	3579.69/2,500		
TS681AIDT	497-8130-1-ND	R/R, Micropower BiCMOS Comparator*	8-SOIC	1.57	1.41	1.12
TS681AIDT	497-8130-2-ND	R/R, Micropower BiCMOS Comparator*	8-SOIC	1444.78/2,500		
TS681AILT	497-2308-1-ND	R/R, Micropower BiCMOS Comparator	SOT-23-5	2.64	2.27	1.85
TS681AILT	497-2308-2-ND	R/R, Micropower BiCMOS Comparator	SOT-23-5	3053.40/3,000		
TS681IDT	497-4072-1-ND	R/R, Micropower BiCMOS Comparator	8-SOIC	2.00	1.71	1.40
TS681IDT	497-4072-2-ND	R/R, Micropower BiCMOS Comparator	8-SOIC	1924.50/2,500		
TS681ILT	497-6777-1-ND	R/R, Micropower BiCMOS Comparator*	SOT-23-5	2.56	2.20	1.79
TS681ILT	497-6777-2-ND	R/R, Micropower BiCMOS Comparator*	SOT-23-5	2959.14/3,000		
TS682IDT	497-8131-1-ND	R/R, Micropower BiCMOS Comparator*	8-SOIC	2.56	2.20	1.79
TS682IDT	497-8131-2-ND	R/R, Micropower BiCMOS Comparator*	8-SOIC	2465.95/2,500		
TS682IPT	497-8132-1-ND	R/R, Micropower BiCMOS Comparator*	8-TSSOP	2.56	2.20	1.79
TS682IPT	497-8132-2-ND	R/R, Micropower BiCMOS Comparator*	8-TSSOP	3945.51/4,000		
TS684AIDT	497-4073-1-ND	R/R, Micropower BiCMOS Comparator	14-SOIC	2.97	2.55	2.08
TS684AIDT	497-4073-2-ND	R/R, Micropower BiCMOS Comparator	14-SOIC	2864.31/2,500		
TS684IDT	497-8133-1-ND	R/R, Micropower BiCMOS Comparator*	14-SOIC	3.30	2.83	2.31
TS684IDT	497-8133-2-ND	R/R, Micropower BiCMOS Comparator*	14-SOIC	3181.32/2,500		
TS684IPT	497-8134-1-ND	R/R, Micropower BiCMOS Comparator*	14-TSSOP	3.30	2.83	2.31
TS684IPT	497-8134-2-ND	R/R, Micropower BiCMOS Comparator*	14-TSSOP	3181.32/2,500		
TS902IDT	497-8135-1-ND	R/R, CMOS Dual Op Amp*	14-SOIC	1.67	1.43	1.17
TS912AIDT	497-2310-1-ND	R/R, CMOS Dual Op Amp	8-SOIC	2.27	1.95	1.59
TS912AIDT	497-2310-2-ND	R/R, CMOS Dual Op Amp	8-SOIC	2188.21/2,500		
TS912AIDT	497-7682-5-ND	R/R, CMOS Dual Op Amp*	8-Dip	2.01	1.82	1.46
TS912BIDT	497-6617-1-ND	R/R, CMOS Dual Op Amp*	8-SOIC	3.01	2.59	2.11
TS912BIDT	497-6617-2-ND	R/R, CMOS Dual Op Amp*	8-SOIC	2903.59/2,500		
TS912IDT	497-6618-1-ND	R/R, CMOS Dual Op Amp*	8-SOIC	1.62	1.45	1.15
TS912IDT	497-6618-2-ND	R/R, CMOS Dual Op Amp*	8-SOIC	1484.06/2,500		
TS912IN	497-7683-5-ND	R/R, CMOS Dual Op Amp*	8-Dip	1.94	1.76	1.41
TS912YDT	497-10252-1-ND	R/R, CMOS Dual Op Amp* NEW!	8-SOIC	1.93	1.73	1.37
TS912YDT	497-10252-2-ND	R/R, CMOS Dual Op Amp* NEW!	8-SOIC	1775.82/2,500		
TS914AIDT	497-2311-1-ND	R/R, CMOS Quad Op Amp	14-SOIC	2.85	2.45	2.00
TS914AIDT	497-2311-2-ND	R/R, CMOS Quad Op Amp	14-SOIC	2746.49/2,500		
TS914AIYDT	497-10253-1-ND	R/R, CMOS Quad Op Amp* NEW!	14-SOIC	3.30	2.83	2.31
TS914AIYDT	497-10253-2-ND	R/R, CMOS Quad Op Amp* NEW!	14-SOIC	3181.32/2,500		
TS914IDT	497-6042-1-ND	R/R, CMOS Quad Op Amp*	14-SOIC	2.81	2.41	1.97
TS914IDT	497-6042-2-ND	R/R, CMOS Quad Op Amp*	14-SOIC	2704.41/2,500		
TS914IYDT	497-10254-1-ND	R/R, CMOS Quad Op Amp* NEW!	14-SOIC	2.60	2.23	1.82
TS914IYDT	497-10254-2-ND	R/R, CMOS Quad Op Amp* NEW!	14-SOIC	2508.03/2,500		
TS921IDT	497-4074-1-ND	R/R, High Output Current Single Op Amp	8-SOIC	1.84	1.65	1.31
TS921IDT	497-4074-2-ND	R/R, High Output Current Single Op Amp	8-SOIC	1691.66/2,500		
TS921IN	497-4075-5-ND	R/R, High Output Current Single Op Amp	8-Dip	1.69	1.50	1.19
TS921IPT	497-8136-1-ND	R/R, High Output Curr. Single Op Amp*	8-TSSOP	1.71	1.53	1.21
TS921IPT	497-8136-2-ND	R/R, High Output Curr. Single Op Amp*	8-TSSOP	2509.15/4,000		
TS922AIDT	497-6221-1-ND	R/R, High Output Current Dual Op Amp*	8-SOIC	2.44	2.09	1.71
TS922AIDT	497-6221-2-ND	R/R, High Output Current Dual Op Amp*	8-SOIC	2348.12/2,500		
TS922AIPT	497-8137-1-ND	R/R, High Output Current Dual Op Amp*	8-TSSOP	2.64	2.27	1.85
TS922AIPT	497-8137-2-ND	R/R, High Output Current Dual Op Amp*	8-TSSOP	4071.20/4,000		
TS922AIYDT	497-10255-1-ND	R/R, High Output Current Dual Op Amp* NEW!	8-SOIC	2.11	1.89	1.50
TS922AIYDT	497-10255-2-ND	R/R, High Output Current Dual Op Amp* NEW!	8-SOIC	1941.34/2,500		

STMicroelectronics		DigiKey (Cont.)		AMPLIFIERS AND LINEAR		
		RoHS Compliant Parts Available		Price Each*		
Part No.	Digi-Key Part No.	Description	Pkg.	1	10	100
TS922AIYPT	497-10256-1-ND	R/R, High Output Current Dual Op Amp* NEW!	8-TSSOP	2.11	1.89	1.50
TS922AIYPT	497-10256-2-ND	R/R, High Output Current Dual Op Amp* NEW!	8-TSSOP	3106.14/4,000		
TS922IDT	497-6035-1-ND	R/R, High Output Current Dual Op Amp*	8-SOIC	2.44	2.09	1.71
TS922IDT	497-6035-2-ND	R/R, High Output Current Dual Op Amp*	8-SOIC	2348.12/2,500		
TS922IN	497-3049-5-ND	R/R, High Output Current Dual Op Amp*	8-Dip	2.15	1.95	1.57
TS922IPT	497-6619-1-ND	R/R, High Output Current Dual Op Amp*	8-TSSOP	2.11	1.81	1.48
TS922IPT	497-6619-2-ND	R/R, High Output Current Dual Op Amp*	8-TSSOP	3249.74/4,000		
TS922IYDT	497-10257-1-ND	R/R, High Output Current Dual Op Amp* NEW!	8-SOIC	1.66	1.49	1.18
TS922IYDT	497-10257-2-ND	R/R, High Output Current Dual Op Amp* NEW!	8-SOIC	1528.94/2,500		
TS922IYPT	497-10258-1-ND	R/R, High Output Current Dual Op Amp* NEW!	8-TSSOP	1.66	1.49	1.18
TS922IYPT	497-10258-2-ND	R/R, High Output Current Dual Op Amp* NEW!	8-TSSOP	2446.31/4,000		
TS924AID	497-2314-5-ND	R/R, High Output Current Quad Op Amp	14-SOIC	3.40	3.07	2.47
TS924AIPT	497-8138-1-ND	R/R, High Output Current Quad Op Amp*	14-TSSOP	3.47	3.12	2.55
TS924AIPT	497-8138-2-ND	R/R, High Output Current Quad Op Amp*	14-TSSOP	3840.59/2,500		
TS924AIYDT	497-10259-1-ND	R/R, High Output Current Quad Op Amp* NEW!	14-SOIC	2.60	2.23	1.82
TS924AIYDT	497-10259-2-ND	R/R, High Output Current Quad Op Amp* NEW!	14-SOIC	2508.03/2,500		
TS924AIYPT	497-10260-1-ND	R/R, High Output Current Quad Op Amp* NEW!	14-TSSOP	2.60	2.23	1.82
TS924AIYPT	497-10260-2-ND	R/R, High Output Current Quad Op Amp* NEW!	14-TSSOP	2508.03/2,500		
TS924ID	497-6778-5-ND	R/R I/O Quad Op Amp*	14-SOIC	2.82	2.55	2.05
TS924IDT	497-8139-1-ND	R/R, High Output Current Quad Op Amp*	14-SOIC	3.18	2.73	2.23
TS924IDT	497-8139-2-ND	R/R, High Output Current Quad Op Amp*	14-SOIC	3063.50/2,500		
TS924IPT	497-8140-1-ND	R/R, High Output Current Quad Op Amp*	14-TSSOP	3.42	2.94	2.40
TS924IPT	497-8140-2-ND	R/R, High Output Current Quad Op Amp*	14-TSSOP	3301.96/2,500		
TS924IYDT	497-10261-1-ND	R/R, High Output Current Quad Op Amp* NEW!	14-SOIC	2.39	2.05	1.68
TS924IYDT	497-10261-2-ND	R/R, High Output Current Quad Op Amp* NEW!	14-SOIC	2306.04/2,500		
TS924IYPT	497-10262-1-ND	R/R, High Output Current Quad Op Amp* NEW!	14-TSSOP	2.39	2.05	1.68
TS924IYPT	497-10262-2-ND	R/R, High Output Current Quad Op Amp* NEW!	14-TSSOP	2306.04/2,500		
TS925AIP	497-4076-1-ND	R/R, High Output Current Quad Op Amp	16-TSSOP	3.50	3.16	2.57
TS925AIP	497-4076-2-ND	R/R, High Output Current Quad Op Amp	16-TSSOP	3879.87/2,500		
TS925ID	497-3050-5-ND	R/R, High Output Current Quad Op Amp*	16-SOIC	2.52	2.28	1