

STMicroelectronics <b>POWER MANAGEMENT</b> RoHS Compliant Parts Available					
STMicroelectronics Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*	
				1	100
LD39015M18R	497-6977-2-ND	1.8V, 150mA Low Quiescent Current, LN, Voltage Regulator*	SOT-23-5	2.912	01/3,000
LD39015M25R	497-6978-1-ND	2.5V, 150mA Low Quiescent Current, LN, Voltage Regulator*	SOT-23-5	1.12	1.01 .80
LD39015M25R	497-6978-2-ND	2.5V, 150mA Low Quiescent Current, LN, Voltage Regulator*	SOT-23-5	2.912	01/3,000
LD39015M33R	497-6979-1-ND	3.3V, 150mA Low Quiescent Current, LN, Voltage Regulator*	SOT-23-5	1.12	1.01 .80
LD39015M33R	497-6979-2-ND	3.3V, 150mA Low Quiescent Current, LN, Voltage Regulator*	SOT-23-5	1238.86	3,000
LD39015M125R	497-8714-1-ND	1.25V, 150mA Low Quiescent Current, LN, Voltage Regulator*	SOT-23-5	.89	.77 .61
LD39015M125R	497-8714-2-ND	1.25V, 150mA Low Quiescent Current, LN, Voltage Regulator*	SOT-23-5	875.28	3,000
LD39015XG08R	497-6825-1-ND	0.8V, 150mA Low Quiescent Current, LN, Voltage Regulator*	SOT-666	1.02	.88 .70
LD39015XG08R	497-6825-2-ND	0.8V, 150mA Low Quiescent Current, LN, Voltage Regulator*	SOT-666	1006.58	3,000
LD39015XG10R	497-8823-1-ND	1V, 150mA Low Quiescent Current, LN, Voltage Regulator* <b>NEW!</b>	SOT-666	.89	.77 .61
LD39015XG10R	497-8823-2-ND	1V, 150mA Low Quiescent Current, LN, Voltage Regulator* <b>NEW!</b>	SOT-666	875.28	3,000
LD39015XG12R	497-6980-1-ND	1.2V, 150mA Low Quiescent Current, LN, Voltage Regulator*	SOT-666	1.07	.96 .76
LD39015XG12R	497-6980-2-ND	1.2V, 150mA Low Quiescent Current, LN, Voltage Regulator*	SOT-666	1178.27	3,000
LD39015XG33R	497-6826-1-ND	3.3V, 150mA Low Quiescent Current, LN, Voltage Regulator*	SOT-666	1.07	.96 .76
LD39015XG33R	497-6826-2-ND	3.3V, 150mA Low Quiescent Current, LN, Voltage Regulator*	SOT-666	1178.27	3,000
LD39050PU25R	497-8715-1-ND	2.5V, 500mA Low Quiescent Current, LN, Voltage Regulator*	6-DFN	1.35	1.21 .96
LD39050PU25R	497-8715-2-ND	2.5V, 500mA Low Quiescent Current, LN, Voltage Regulator*	6-DFN	1484.62	3,000
LD39050PU33R	497-8716-1-ND	3.3V, 500mA Low Quiescent Current, LN, Voltage Regulator*	6-DFN	1.35	1.21 .96
LD39050PU33R	497-8716-2-ND	3.3V, 500mA Low Quiescent Current, LN, Voltage Regulator*	6-DFN	1484.62	3,000
LD39050PUR	497-8717-1-ND	Adj., 500mA Low Quiescent Current, LN, Voltage Regulator*	6-DFN	1.35	1.21 .96
LD39050PUR	497-8717-2-ND	Adj., 500mA Low Quiescent Current, LN, Voltage Regulator*	6-DFN	1484.62	3,000
LD39080DT12-R	497-6012-1-ND	1.22V, 0.8A Ultra LDO BiCMOS Voltage Regulator*	D-PAK	2.02	1.81 1.44
LD39080DT12-R	497-6012-2-ND	1.22V, 0.8A Ultra LDO BiCMOS Voltage Regulator*	D-PAK	1857.17	2,500
LD39080DT18-R	497-6013-1-ND	1.8V, 0.8A Ultra LDO BiCMOS Voltage Regulator*	D-PAK	2.02	1.81 1.44
LD39080DT18-R	497-6013-2-ND	1.8V, 0.8A Ultra LDO BiCMOS Voltage Regulator*	D-PAK	1857.17	2,500
LD39080DT25-R	497-6014-1-ND	2.5V, 0.8A Ultra LDO BiCMOS Voltage Regulator*	D-PAK	2.02	1.81 1.44
LD39080DT25-R	497-6014-2-ND	2.5V, 0.8A Ultra LDO BiCMOS Voltage Regulator*	D-PAK	1857.17	2,500
LD39080DT33-R	497-6015-1-ND	3.3V, 0.8A Ultra LDO BiCMOS Voltage Regulator*	D-PAK	2.02	1.81 1.44
LD39080DT33-R	497-6015-2-ND	3.3V, 0.8A Ultra LDO BiCMOS Voltage Regulator*	D-PAK	1857.17	2,500
LD39080PT-R	497-6019-1-ND	Adjustable, 0.8A Ultra LDO BiCMOS Voltage Regulator*	P-PAK	2.02	1.81 1.44
LD39080PT-R	497-6019-2-ND	Adjustable, 0.8A Ultra LDO BiCMOS Voltage Regulator*	P-PAK	1857.17	2,500
LD39150DT12-R	497-6141-1-ND	1.22V, 1.5A Ultra LDO BiCMOS Voltage Regulator*	D-PAK	1.92	1.72 1.37
LD39150DT12-R	497-6141-2-ND	1.22V, 1.5A Ultra LDO BiCMOS Voltage Regulator*	D-PAK	1767.40	2,500
LD39150DT18-R	497-7790-1-ND	1.8V, 1.5A Ultra LDO BiCMOS Voltage Regulator*	D-PAK	2.13	1.84 1.50
LD39150DT25-R	497-6143-1-ND	2.5V, 1.5A Ultra LDO BiCMOS Voltage Regulator*	D-PAK	2.13	1.84 1.50
LD39150DT25-R	497-6143-2-ND	2.5V, 1.5A Ultra LDO BiCMOS Voltage Regulator*	D-PAK	2059.16	2,500
LD39150DT33-R	497-6448-1-ND	3.3V, 1.5A Ultra LDO BiCMOS Voltage Regulator*	D-PAK	2.06	1.85 1.47
LD39150DT33-R	497-6448-2-ND	3.3V, 1.5A Ultra LDO BiCMOS Voltage Regulator*	D-PAK	1896.45	2,500
LD39150PT25-R	497-7791-1-ND	2.5V, 1.5A Ultra LDO BiCMOS Voltage Regulator*	P-PAK	2.13	1.84 1.50
LD39150PT25-R	497-7791-2-ND	2.5V, 1.5A Ultra LDO BiCMOS Voltage Regulator*	P-PAK	2059.16	2,500
LD39150PT33-R	497-6144-1-ND	3.3V, 1.5A Ultra LDO BiCMOS Voltage Regulator*	P-PAK-5	2.13	1.84 1.50
LD39150PT33-R	497-6144-2-ND	3.3V, 1.5A Ultra LDO BiCMOS Voltage Regulator*	P-PAK-5	2059.16	2,500
LD39150PT-R	497-7792-1-ND	Adj., 1.5A Ultra LDO BiCMOS Voltage Regulator*	P-PAK	2.13	1.84 1.50
LD39150PT-R	497-7792-2-ND	Adj., 1.5A Ultra LDO BiCMOS Voltage Regulator*	P-PAK	2059.16	2,500
LD39300DT12-R	497-6148-1-ND	1.22V, 3A Ultra LDO BiCMOS Voltage Regulator*	D-PAK	2.06	1.85 1.47
LD39300DT12-R	497-6148-2-ND	1.22V, 3A Ultra LDO BiCMOS Voltage Regulator*	D-PAK	1896.45	2,500
LD39300DT18-R	497-6873-1-ND	1.8V, 3A Ultra LDO BiCMOS Volt. Reg.*	D-PAK	2.06	1.85 1.47
LD39300DT18-R	497-6873-2-ND	1.8V, 3A Ultra LDO BiCMOS Volt. Reg.*	D-PAK	1896.45	2,500
LD39300DT25-R	497-6150-1-ND	2.5V, 3A Ultra LDO BiCMOS Volt. Reg.*	D-PAK	2.06	1.85 1.47
LD39300DT25-R	497-6150-2-ND	2.5V, 3A Ultra LDO BiCMOS Volt. Reg.*	D-PAK	1896.45	2,500
LD39300DT33-R	497-6874-1-ND	3.3V, 3A Ultra LDO BiCMOS Volt. Reg.*	D-PAK	2.06	1.85 1.47
LD39300DT33-R	497-6874-2-ND	3.3V, 3A Ultra LDO BiCMOS Volt. Reg.*	D-PAK	1896.45	2,500
LD39300PT-R	497-5798-1-ND	Adj., 3A Ultra LDO BiCMOS Volt. Reg.*	P-PAK	2.60	2.23 1.82
LD39300PT-R	497-5798-2-ND	Adj., 3A Ultra LDO BiCMOS Volt. Reg.*	P-PAK	2508.03	2,500
LD39300PT25-R	497-6875-1-ND	2.5V, 3A Ultra LDO BiCMOS Volt. Reg.*	P-PAK	2.51	2.16 1.77
LD39300PT25-R	497-6875-2-ND	2.5V, 3A Ultra LDO BiCMOS Volt. Reg.*	P-PAK	2426.67	2,500
LD39300PT33-R	497-6151-1-ND	3.3V, 3A Ultra LDO BiCMOS Volt. Reg.*	P-PAK-5	2.51	2.16 1.77
LD39300PT33-R	497-6151-2-ND	3.3V, 3A Ultra LDO BiCMOS Volt. Reg.*	P-PAK-5	2426.67	2,500
LD49150PT08R	497-7796-1-ND	0.8V, 1.5A VLD0 for Low Output Voltage Regulator*	P-PAK	3.10	2.66 2.17
LD49150PT08R	497-7796-2-ND	0.8V, 1.5A VLD0 for Low Output Voltage Regulator*	P-PAK	2984.95	2,500

STMicroelectronics <b>POWER MANAGEMENT</b> RoHS Compliant Parts Available					
STMicroelectronics Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*	
				1	100
LD49150PT10R	497-6847-1-ND	1.0V, 1.5A VLD0 for Low Output Voltage Regulator*	P-PAK	3.10	2.66 2.17
LD49150PT10R	497-6847-2-ND	1.0V, 1.5A VLD0 for Low Output Voltage Regulator*	P-PAK	2984.95	2,500
LD49150PT12R	497-6848-1-ND	1.2V, 1.5A VLD0 for Low Output Voltage Regulator*	P-PAK	3.10	2.66 2.17
LD49150PT12R	497-6848-2-ND	1.2V, 1.5A VLD0 for Low Output Voltage Regulator*	P-PAK	2984.95	2,500
LD49300PT08-R	497-6155-1-ND	0.8V, 3A VLD0 Voltage Regulator*	P-PAK-5	2.61	2.24 1.83
LD49300PT08-R	497-6155-2-ND	0.8V, 3A VLD0 Voltage Regulator*	P-PAK-5	2519.25	2,500
LD49300PT10R	497-8276-1-ND	1.0V, 3A VLD0 Voltage Regulator*	P-PAK	2.61	2.24 1.83
LD49300PT10R	497-8276-2-ND	1.0V, 3A VLD0 Voltage Regulator*	P-PAK	2519.25	2,500
LD49300PT12R	497-8277-1-ND	1.2V, 3A VLD0 Voltage Regulator*	P-PAK	2.61	2.24 1.83
LD49300PT12R	497-8277-2-ND	1.2V, 3A VLD0 Voltage Regulator*	P-PAK	2519.25	2,500
LD49300PT12R	497-3505-1-ND	2.5V to 3.3V LDO Dual Voltage Reg. *	P-PAK	1.73	1.49 1.22
LD49300PT12R	497-6146-1-ND	1.8V, 300mA ULDO Voltage Regulator*	SOT-23-5	1.19	1.04 82
LD49300PT12R	497-6146-2-ND	1.8V, 300mA ULDO Voltage Regulator*	SOT-23-5	1181.63	3,000
LD49300PT12R	497-6147-1-ND	2.5V, 300mA ULDO Voltage Regulator*	SOT-23-5	1.03	.96 .71
LD49300PT12R	497-6147-2-ND	2.5V, 300mA ULDO Voltage Regulator*	SOT-23-5	1026.78	3,000
LD49300PT12R	497-6849-1-ND	3V, 300mA ULDO Voltage Regulator*	SOT-23-5	1.03	.96 .71
LD49300PT12R	497-6849-2-ND	3V, 300mA ULDO Voltage Regulator*	SOT-23-5	1026.78	3,000
LD49300PT12R	497-4257-1-ND	3.3V, 300mA ULDO Voltage Regulator*	SOT-23-5	1.13	1.02 81
LD49300PT12R	497-4257-2-ND	3.3V, 300mA ULDO Voltage Regulator*	SOT-23-5	1252.33	3,000
LD49300PT12R	497-6850-1-ND	1.5V, 300mA ULDO Voltage Regulator*	6D-DFN	1.23	1.11 .88
LD49300PT12R	497-6850-2-ND	1.5V, 300mA ULDO Voltage Regulator*	6D-DFN	1368.79	3,000
LD49300PT12R	497-6851-1-ND	2.8V, 300mA ULDO Voltage Regulator*	6D-DFN	1.29	1.16 92
LD49300PT12R	497-6851-2-ND	2.8V, 300mA ULDO Voltage Regulator*	6D-DFN	1427.39	3,000
LD49300PT12R	497-6852-1-ND	3.3V, 300mA ULDO Voltage Regulator*	6D-DFN	1.29	1.16 92
LD49300PT12R	497-6852-2-ND	3.3V, 300mA ULDO Voltage Regulator*	6D-DFN	1427.39	3,000
LE30CD-TR	497-8341-1-ND	3V, LDO Voltage Regulator*	8-SOIC	1.48	1.33 1.06
LE30CD-TR	497-8341-2-ND	3V, LDO Voltage Regulator*	8-SOIC	1363.42	2,500
LE30CZ-TR	497-5366-1-ND	3V, LDO Voltage Regulator*	TO-92	.89	.77 61
LE30CZ-TR	497-5366-2-ND	3V, LDO Voltage Regulator*	TO-92	1.35	1.21 96
LE30CZ-TR	497-8342-1-ND	3.3V, LDO Voltage Regulator*	8-SOIC	1.37	1.21 96
LE30CZ-TR	497-8342-2-ND	3.3V, LDO Voltage Regulator*	8-SOIC	1237.18	2,500
LE33CZ-TR	497-4258-1-ND	3.3V, LDO Voltage Regulator*	TO-92	.99	.86 68
LE33CZ-TR	497-4258-2-ND	3.3V, LDO Voltage Regulator*	TO-92	650.85	2,000
LE45ABD-TR	497-1530-1-ND	4.5V, VLD0 Voltage Regulator*	8-SOIC	1.21	1.09 87
LE45CD-TR	497-7797-1-ND	4.5V, VLD0 Voltage Regulator*	8-SOIC	1.48	1.33 1.06
LE45CD-TR	497-7797-2-ND	4.5V, VLD0 Voltage Regulator*	8-SOIC	1363.42	2,500
LE50ABD-TR	497-7798-1-ND	5V, VLD0 Voltage Regulator*	8-SOIC	1.54	1.38 1.10
LE50ABD-TR	497-7798-2-ND	5V, VLD0 Voltage Regulator*	8-SOIC	1413.92	2,500
LE50ABZ-AP	497-1531-1-ND	5V, VLD0 Voltage Regulator*	TO-92	1.18	1.06 84
LE50ABZ-AP	497-1531-3-ND	5V, VLD0 Voltage Regulator*	TO-92	866.31	2,000
LE50CD-TR	497-6431-1-ND	5V, VLD0 Voltage Regulator*	8-SOIC	1.34	1.20 95
LE50CD-TR	497-6431-2-ND	5V, VLD0 Voltage Regulator*	8-SOIC	1228.77	2,500
LE80CD-TR	497-5220-1-ND	8V, LDO Voltage Regulator*	8-SOIC	1.13	1.02 81
LE80CD-TR	497-5220-2-ND	8V, LDO Voltage Regulator*	8-SOIC	1043.61	2,500
LED7706T	497-6879-1-ND	6-Row, 30mA LED Driver*	24-VDFPN	4.80	4.33 3.53
LED7706T	497-6879-2-ND	6-Row, 30mA LED Driver*	24-VDFPN	8523.93	4,000
LED7707T	497-8492-1-ND	6-Row, 85mA LED Driver*	24-VDFPN	4.80	4.33 3.53
LED7707T	497-8492-2-ND	6-Row, 85mA LED Driver*	24-VDFPN	8523.93	4,000
LF15ABDT-TR	497-5221-1-ND	1.5V, LDO Voltage Regulator*	D-PAK	1.23	1.11 88
LF18ABDT-TR	497-5843-1-ND	1.8V, VLD0 Voltage Regulator*	D-PAK	1.62	1.38 1.18
LF18ABPT-TR	497-7799-1-ND	1.8V, VLD0 Voltage Regulator*	P-PAK	2.02	1.74 1.42
LF18ABPT-TR	497-7799-2-ND	1.8V, VLD0 Voltage Regulator*	P-PAK	1948.76	2,500
LF18CDT-TR	497-5222-1-ND	1.8V, VLD0 Voltage Regulator*	D-PAK	1.75	1.57 1.25
LF18CDT-TR	497-5222-2-ND	1.8V, VLD0 Voltage Regulator*	D-PAK	1610.30	2,500
LF18CDT-TRY	497-10194-1-ND	1.8V, VLD0 Voltage Regulator*	D-PAK	1.98	1.70 1.39
LF18CDT-TRY	497-10194-2-ND	1.8V, VLD0 Voltage Regulator*	D-PAK	1907.67	2,500
LF18CPT-TR	497-7800-1-ND	1.8V, VLD0 Voltage Regulator*	P-PAK	1.75	1.57 1.25
LF18CPT-TR	497-7800-2-ND	1.8V, VLD0 Voltage Regulator*	P-PAK	1610.30	2,500
LF25ABDT-TR	497-5223-1-ND	2.5V, VLD0 Voltage Regulator*	D-PAK	1.75	1.57 1.25
LF25ABDT-TRY	497-10195-1-ND	2.5V, VLD0 Voltage Regulator*	D-PAK	2.06	1.77 1.45
LF25ABDT-TRY	497-10195-2-ND	2.5V, VLD0 Voltage Regulator*	D-PAK	1989.03	2,500
LF25CDT-TR	497-6449-1-ND	2.5V, VLD0 Voltage Regulator*	D-PAK	1.98	1.70 1.39
LF25CDT-TRY	497-6449-2-ND	2.5V, VLD0 Voltage Regulator*	D-PAK	1907.67	2,500
LF25CDT-TRY	497-10196-1-ND	2.5V, VLD0 Voltage Regulator*	D-PAK	1.98	1.70 1.39
LF25CDT-TRY	497-10196-2-ND	2.5V, VLD0 Voltage Regulator*	D-PAK	1907.67	2,500
LF33ABDT-TR	497-5225-1-ND				