

LINEAD TECHNOLOGY		DigiKey Reel (Cont.)		POWER MANAGEMENT	
Digi-Key Part No.	Description	Pkg.	Price Each*		
			1	25	100
LT1587C1-3.3PBF-ND	3.3V, 3A, LDO Voltage Regulator*	T0-220	6.88	4.57	3.76
LT1610CMS8PBF-ND	1.7MHz, Single Cell DC/DC Converter*	8-MSP0P	4.63	3.08	2.36
LT1610CS8PBF-ND	1.7MHz, Single Cell DC/DC Converter*	8-SOIC	5.93	2.61	1.97
LT1610IS55FTRMPBFT-ND	1.4MHz, Single Cell DC/DC Converter*	8-SOIC	4.77	3.17	2.53
LT1611CS5FTRMPBFT-ND	1.4MHz, Inverting Switching Regulator*	SOT-23-5	1234.38/500		
LT1611CS5FTRMPBFT-ND	1.4MHz, Single Cell DC/DC Controller*	TSOT-23-5	4.65	4.16	3.74
LT1611CS5FTRMPBFT-ND	1.4MHz, Single Cell DC/DC Controller*	TSOT-23-5	1038.00/500		
LT1614CMS8PBF-ND	600kHz, Inverting Switching Regulator	8-MSP0P	6.17	4.10	3.15
LT1614CMS8PBF-ND	600kHz, Inverting Switching Regulator*	8-MSP0P	6.17	4.10	3.15
LT1614CS8PBF-ND	600kHz, Inverting Switching Regulator*	8-SOIC	5.61	3.73	2.87
LT1615ES5FTRMPBFT-ND	Micropower Step-Up DC/DC Converter*	TSOT-23-5	4.65	4.16	3.74
LT1615ES5FTRMPBFT-ND	Micropower Step-Up DC/DC Converter*	TSOT-23-5	1038.00/500		
LT1615ES5-1FTR-ND	Micropower Step-Up DC/DC Converter	TSOT-23-5	5049.72/2,500		
LT1615ES5-1FTRMPBFT-ND	Micropower Step-Up DC/DC Converter*	TSOT-23-5	4.65	4.16	3.74
LT1615ES5-1FTRMPBFT-ND	Micropower Step-Up DC/DC Converter*	TSOT-23-5	1038.00/500		
LT1615IS5FTRMPBFT-ND	Micropower Step-Up DC/DC Converter*	TSOT-23-5	5.27	4.72	4.25
LT1615IS5FTRMPBFT-ND	Micropower Step-Up DC/DC Converter*	TSOT-23-5	1178.27/500		
LT1616ES6FTRMPBFT-ND	1.4MHz, Step-Down Switching Regulator*	SOT-23-6	5.27	4.72	4.25
LT1616ES6FTRMPBFT-ND	1.4MHz, Step-Down Switching Regulator*	SOT-23-6	1178.27/500		
LT1617ES5FTRMPBFT-ND	Micropower Inverting DC/DC Converter*	TSOT-23-5	4.65	4.16	3.74
LT1617ES5FTRMPBFT-ND	Micropower Inverting DC/DC Converter*	TSOT-23-5	1038.00/500		
LT1618EMS8PBF-ND	1.4MHz, Step-Up DC/DC Converter*	10-MSP0P	5.93	2.61	2.09
LT1619EMS8PBF-ND	300kHz, 2-Cell Current Mode PWM Controller*	8-MSP0P	5.05	3.36	2.53
LT1619EMS8PBF-ND	300kHz, 2-Cell Current Mode PWM Controller	8-MSP0P	662.83/2,500		
LT1619ES8PBF-ND	300kHz, 2-Cell Current Mode PWM Controller*	8-SOIC	4.77	3.17	2.40
LT1619ES8PBF-ND	300kHz, 2-Cell Current Mode PWM Controller	8-SOIC	6327.00/2,500		
LT1619ES8PBF-ND	High Efficiency, Step-Down Switching Regulator*	8-SOIC	6.04	4.01	3.20
LT1619ES8PBF-ND	High Eff., Step-Down Switching Reg., Ind. Temp.*	8-SOIC	7.01	4.66	3.76
LT1680C8PBF-ND	High Power DC/DC Step-Up Controller*	16-DIP	8.98	5.97	4.77
LT1680CSW8PBF-ND	High Power DC/DC Step-Up Controller*	16-SOIC	9.40	6.25	5.00
LT1680CSW8PBF-ND	High Power DC/DC Step-Up Controller*	16-SOIC	11.22	7.46	6.01
LT1681ESW8PBF-ND	Dual Transistor Sync. Forward Controller*	20-SOIC	11.93	7.92	5.97
LT1683ES8PBF-ND	Ultra Low Noise Push-Pull DC/DC Controller*	20-SOIC	10.81	7.18	5.45
LT1725IS8PBF-ND	General Purpose Isolated Flyback Controller*	16-SOIC	7.99	5.22	3.93
LT1737G8PBF-ND	High Power Isolated Flyback Controller*	16-SOIC	8.14	5.41	4.07
LT1738ES8PBF-ND	Ultra Low Noise DC/DC Controller*	20-SOIC	9.68	6.43	4.84
LT1761ES5-BYPFTRMPBFT-ND	Adj., 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	2.67	2.39	2.15
LT1761ES5-BYPFTRMPBFT-ND	Adj., 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	596.15/500		
LT1761ES5-1.5FTRMPBFT-ND	1.5V, 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	2.67	2.39	2.15
LT1761ES5-1.5FTRMPBFT-ND	1.5V, 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	596.15/500		
LT1761ES5-1.8FTRMPBFT-ND	1.8V, 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	2.67	2.39	2.15
LT1761ES5-1.8FTRMPBFT-ND	1.8V, 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	596.15/500		
LT1761ES5-2.5FTRMPBFT-ND	2.5V, 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	2.67	2.39	2.15
LT1761ES5-2.5FTRMPBFT-ND	2.5V, 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	596.15/500		
LT1761ES5-2.8FTRMPBFT-ND	2.8V, 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	2.67	2.39	2.15
LT1761ES5-2.8FTRMPBFT-ND	2.8V, 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	596.15/500		
LT1761ES5-3FTRMPBFT-ND	3V, 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	2.67	2.39	2.15
LT1761ES5-3FTRMPBFT-ND	3V, 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	596.15/500		
LT1761ES5-3.3FTRMPBFT-ND	3.3V, 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	2.67	2.39	2.15
LT1761ES5-3.3FTRMPBFT-ND	3.3V, 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	596.15/500		
LT1761ES5-5FTRMPBFT-ND	5V, 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	2.67	2.39	2.15
LT1761ES5-5FTRMPBFT-ND	5V, 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	596.15/500		
LT1761ES5-SDFTRMPBFT-ND	Adj., 100mA, Low Noise, LDO MPU Regulator*	TSOT-23-5	2.67	2.39	2.15
LT1761ES5-SDFTRMPBFT-ND	Adj., 100mA, Low Noise, LDO MPU Regulator*	TSOT-23-5	596.15/500		
LT1761ES5-1.2FTRMPBFT-ND	1.2V, 100mA, Low Noise LDO MPU Reg.* NEW!	TSOT-23-5	2.92	2.61	2.35
LT1761ES5-1.2FTRMPBFT-ND	1.2V, 100mA, Low Noise LDO MPU Reg.* NEW!	TSOT-23-5	718.18/500		
LT1761ES5-1.5FTRMPBFT-ND	1.5V, 100mA, Low Noise LDO MPU Reg.* NEW!	TSOT-23-5	2.92	2.61	2.35
LT1761ES5-1.5FTRMPBFT-ND	1.5V, 100mA, Low Noise LDO MPU Reg.* NEW!	TSOT-23-5	718.18/500		
LT1761ES5-1.8FTRMPBFT-ND	1.8V, 100mA, Low Noise LDO MPU Reg.* NEW!	TSOT-23-5	2.92	2.61	2.35
LT1761ES5-1.8FTRMPBFT-ND	1.8V, 100mA, Low Noise LDO MPU Reg.* NEW!	TSOT-23-5	718.18/500		
LT1761ES5-2.0FTRMPBFT-ND	2V, 100mA, Low Noise LDO MPU Reg.* NEW!	TSOT-23-5	2.92	2.61	2.35
LT1761ES5-2.0FTRMPBFT-ND	2V, 100mA, Low Noise LDO MPU Reg.* NEW!	TSOT-23-5	718.18/500		
LT1761ES5-2.5FTRMPBFT-ND	2.5V, 100mA, Low Noise LDO MPU Reg.* NEW!	TSOT-23-5	2.92	2.61	2.35
LT1761ES5-2.5FTRMPBFT-ND	2.5V, 100mA, Low Noise LDO MPU Reg.* NEW!	TSOT-23-5	718.18/500		
LT1761ES5-2.8FTRMPBFT-ND	2.8V, 100mA, Low Noise LDO MPU Reg.* NEW!	TSOT-23-5	2.92	2.61	2.35
LT1761ES5-2.8FTRMPBFT-ND	2.8V, 100mA, Low Noise LDO MPU Reg.* NEW!	TSOT-23-5	718.18/500		
LT1761ES5-3FTRMPBFT-ND	3V, 100mA, Low Noise LDO MPU Reg.* NEW!	TSOT-23-5	2.92	2.61	2.35
LT1761ES5-3FTRMPBFT-ND	3V, 100mA, Low Noise LDO MPU Reg.* NEW!	TSOT-23-5	718.18/500		
LT1761ES5-3.3FTRMPBFT-ND	3.3V, 100mA, Low Noise LDO MPU Reg.* NEW!	TSOT-23-5	2.92	2.61	2.35
LT1761ES5-3.3FTRMPBFT-ND	3.3V, 100mA, Low Noise LDO MPU Reg.* NEW!	TSOT-23-5	718.18/500		
LT1761ES5-5FTRMPBFT-ND	5V, 100mA, Low Noise LDO MPU Reg.* NEW!	TSOT-23-5	2.92	2.61	2.35
LT1761ES5-5FTRMPBFT-ND	5V, 100mA, Low Noise LDO MPU Reg.* NEW!	TSOT-23-5	718.18/500		
LT1761ES5-SDFTRMPBFT-ND	Adj., 100mA, Low Noise LDO MPU Reg.* NEW!	TSOT-23-5	2.92	2.61	2.35
LT1761ES5-SDFTRMPBFT-ND	Adj., 100mA, Low Noise LDO MPU Reg.* NEW!	TSOT-23-5	718.18/500		
LT1762EMS8PBF-ND	Adj., 150mA, Low Noise LDO MPU Regulator*	8-MSP0P	2.67	1.77	1.34
LT1762EMS8PBF-ND	Adj., 150mA, Low Noise LDO MPU Regulator*	8-MSP0P	2.67	1.77	1.34
LT1763CS8PBF-ND	Adj., 500mA, Low Noise LDO MPU Regulator*	8-SOIC	4.63	3.08	2.32
LT1763CS8-2.5PBF-ND	2.5V, 500mA, Low Noise LDO MPU Regulator*	8-SOIC	4.63	3.08	2.32
LT1763CS8-3.3PBF-ND	3.3V, 500mA, Low Noise LDO MPU Regulator*	8-SOIC	4.63	3.08	2.32
LT1763CS8-5PBF-ND	5V, 500mA, Low Noise LDO MPU Regulator*	8-SOIC	4.63	3.08	2.32
LT1763D8PBF-ND	Adj., 500mA, Low Noise LDO MPU Reg.* NEW!	12-DFN	5.14	3.45	2.93
LT1763D8-1.8PBF-ND	1.8V, 500mA, Low Noise LDO MPU Reg.* NEW!	12-DFN	5.14	3.45	2.93
LT1763D8-2.5PBF-ND	2.5V, 500mA, Low Noise LDO MPU Reg.* NEW!	12-DFN	5.14	3.45	2.93
LT1763D8-3PBF-ND	3V, 500mA, Low Noise LDO MPU Reg.* NEW!	12-DFN	5.14	3.45	2.93
LT1763D8-3.3PBF-ND	3.3V, 500mA, Low Noise LDO MPU Reg.* NEW!	12-DFN	5.14	3.45	2.93
LT1763D8-5PBF-ND	5V, 500mA, Low Noise LDO MPU Reg.* NEW!	12-DFN	5.14	3.45	2.93
LT1763IS8-1.8PBF-ND	1.8V, 500mA, Low Noise LDO MPU Reg.*	8-SOIC	5.14	3.45	2.93
LT1764AEQ8PBF-ND	Adj., 3A, Fast Transient Response, LDO Reg.*	5-DDPAK	8.28	5.72	4.71
LT1764AEQ-1.5PBF-ND	1.5V, 3A, Fast Transient Response, LDO Reg.*	5-DDPAK	8.28	5.72	4.71
LT1764AEQ-1.5PBF-ND	1.5V, 3A, Fast Transient Response, LDO Reg.*	5-DDPAK	8.28	5.72	4.71
LT1764AEQ-1.8PBF-ND	1.8V, 3A, Fast Transient Response, LDO Reg.*	5-DDPAK	8.28	5.72	4.71
LT1764AEQ-2.5PBF-ND	2.5V, 3A, Fast Transient Response, LDO Reg.*	5-DDPAK	8.28	5.72	4.71
LT1764AEQ-3.3PBF-ND	3.3V, 3A, Fast Transient Response, LDO Reg.*	5-DDPAK	8.28	5.72	4.71
LT1764AET8PBF-ND	Adj., 3A, Fast Transient Response, LDO Reg.*	T0-220-5	8.28	5.72	4.71
LT1764AET-3.3PBF-ND	3.3V, 3A, Fast Transient Response, LDO Reg.*	T0-220-5	8.28	5.72	4.71
LT1764E0PBF-ND	Adj., 3A, Fast Transient Response, LDO Reg.*	5-DDPAK	8.28	5.72	4.71
LT1764E0-2.5PBF-ND	2.5V, 3A, Fast Transient Response, LDO Reg.*	5-DDPAK	8.28	5.72	4.71
LT1764E0-3.3PBF-ND	3.3V, 3A, Fast Transient Response, LDO Reg.*	5-DDPAK	8.28	5.72	4.71
LT1765EFE8PBF-ND	3A Step-Down Switching Regulator*	16-TSSOP	10.83	7.74	6.38
LT1765EFE-1.8PBF-ND	1.8V, 3A Step-Down Switching Regulator	16-TSSOP	10.83	7.74	6.38
LT1765EFE-1.8PBF-ND	1.8V, 3A Step-Down Switching Regulator*	16-TSSOP	10.83	7.74	6.38
LT1765EFE-2.5PBF-ND	2.5V, 3A Step-Down Switching Regulator*	16-TSSOP	10.83	7.74	6.38
LT1765EFE-2.5PBF-ND	2.5V, 3A Step-Down Switching Regulator*	16-TSSOP	10.83	7.74	6.38
LT1765EFE-5PBF-ND	5V, 3A Step-Down Switching Regulator	16-TSSOP	10.83	7.74	6.38

LINEAD TECHNOLOGY		DigiKey Reel (Cont.)		POWER MANAGEMENT	
Digi-Key Part No.	Description	Pkg.	Price Each*		
			1	25	100
LT1765EFE-5PBF-ND	5V, 3A Step-Down Switching Regulator*	16-TSSOP	10.83	7.74	6.38
LT1765ES8PBF-ND	3A-Step-Down Switching Regulator*	8-SOIC	10.75	7.14	5.38
LT1766EFE8PBF-ND	1.5A, 200kHz Step-Down Switching Regulator*	16-TSSOP	8.42	6.02	4.95
LT1766G8PBF-ND	1.5A, 200kHz Step-Down Switching Regulator*	16-TSSOP	8.28	5.50	4.18
LT1766G8-5PBF-ND	1.5A, 200kHz Step-Down Switching Regulator*	16-TSSOP	8.28	5.50	4.18
LT1766G8-5PBF-ND	1.5A, 200kHz Step-Down Switching Regulator*	16-TSSOP	10.10	6.71	5.05
LT1767EMS8PBF-ND	Adj., Mono 1.5A Step-Down Switching Regulator*	8-MSP0P	6.73	4.48	3.48
LT1767EMS8-2.5PBF-ND	2.5V, Mono 1.5A Step-Down Switching Reg.*	8-MSP0P	6.73	4.48	3.48
LT1767EMS8-2.5PBF-ND	2.5V, Mono 1.5A Step-Down Switching Reg.*	8-MSP0P	6.73	4.48	3.48
LT1767EMS8-3.3PBF-ND	3.3V, Mono 1.5A Step-Down Switching Reg.*	8-MSP0P	6.73	4.48	3.48
LT1767EMS8-5PBF-ND	5V, Mono 1.5A Step-Down Switching Regulator*	8-MSP0P	6.73	4.48	3.48
LT1767EMS8PBF-ND	Mono 1.5A Step-Down Switching Reg.*	8-MSP0P	6.73	4.48	3.48
LT1767EMS8-1.8PBF-ND	1.8V, Mono 1.5A Step-Down Switching Reg.*	8-MSP0P	6.85	4.90	4.03
LT1767EMS8E-3.3PBF-ND	3.3V, Mono 1.5A Step-Down Switching Reg.*	8-MSP0P	6.85	4.90	4.03
LT1767EMS8E-5PBF-ND	5V, Mono 1.5A Step-Down Switching Regulator*	8-MSP0P	6.85	4.90	4.03
LT1767G8N8PBF-ND	High Eff., Step-Down Switching Regulator*	8-Dip	5.61	3.73	2.98
LT1767G8S8PBF-ND	High Eff., Step-Down Switching Regulator*	8-SOIC	5.89	3.92	3.09
LT1767G8S8PBF-ND	High Eff., Step-Down Switching Regulator*	8-SOIC	6.73	4.48	3.54
LT1777IS8PBF-ND	Low Noise Step-Down Switching Regulator*	16-SOIC	7.01	4.66	3.76
LT1912E0D8PBF-ND	2A, 500kHz, Step-Down Switching Regulator*	10-DFN	6.02	4.73	3.90
LT1912E0D8PBF-ND	2A, 500kHz, Step-Down Switching Regulator*	10-MSP0P	6.85	4.90	4.03
LT1913E0D8PBF-ND	3.5A, 2.4MHz, Step-Down Switching Regulator*	10-DFN	8.70	5.86	4.98
LT1930AES5FTRMPBFT-ND	2.2MHz, Step-Up DC/DC Converter*	TSOT-23-5	5.27	4.72	4.25
LT1930AES5FTRMPBFT-ND	2.2MHz, Step-Up DC/DC Converter*	TSOT-23-5	1178.27/500		
LT1930AES5FTRMPBFT-ND	1.2MHz, Step-Up DC/DC Converter*	TSOT-23-5	5.27	4.72	4.25
LT1930AES5FTRMPBFT-ND	1.2MHz, Step-Up DC/DC Converter*	TSOT-23-5	1178.27/500		
LT1931AES5FTRMPBFT-ND	2.2MHz, Inverting DC/DC Converter*	TSOT-23-5	5.59	5.00	4.50
LT1931AES5FTRMPBFT-ND	2.2MHz, Inverting DC/DC Converter*	TSOT-23-5	1248.40/500		
LT1931ES5FTRMPBFT-ND	1.2MHz, Inverting DC/DC Converter*	TSOT-23-5	5.59	5.00	4.50