

LINEAD TECHNOLOGY		Digi Reel (Cont.)		POWER MANAGEMENT		
Digi-Key Part No.	Description	Pkg.	Price Each*			
			1	25	100	
LT1965EMS8E-3.3#PBF-ND	3.3V, 1.1A Low Noise LDO Regulator* NEW!	8-MSOP	4.35	3.11	2.65	
LT1965E01-5#PBF-ND	1.5V, 1.1A Low Noise LDO Regulator* NEW!	5-DDPAK	4.92	3.53	3.00	
LT1965E01-8#PBF-ND	1.8V, 1.1A Low Noise LDO Regulator* NEW!	5-DDPAK	4.92	3.53	3.00	
LT1965E02-2.5#PBF-ND	2.5V, 1.1A Low Noise LDO Regulator* NEW!	5-DDPAK	4.92	3.53	3.00	
LT1965E02-3.3#PBF-ND	3.3V, 1.1A Low Noise LDO Regulator* NEW!	5-DDPAK	4.92	3.53	3.00	
LT1965E1-1.5#PBF-ND	1.5V, 1.1A Low Noise LDO Regulator* NEW!	TO-220-5	4.92	3.53	3.00	
LT1965E1-1.8#PBF-ND	1.8V, 1.1A Low Noise LDO Regulator* NEW!	TO-220-5	4.92	3.53	3.00	
LT1965E1-2.5#PBF-ND	2.5V, 1.1A Low Noise LDO Regulator* NEW!	TO-220-5	4.92	3.53	3.00	
LT1965E1-3.3#PBF-ND	3.3V, 1.1A Low Noise LDO Regulator* NEW!	TO-220-5	4.92	3.53	3.00	
LT1965D04#PBF-ND	1.1A, Low Noise LDO Linear Regulator*	8-DFN	4.86	3.47	2.86	
LT1965MS8E#PBF-ND	1.1A, Low Noise LDO Linear Regulator*	8-MSOP	4.99	3.58	2.95	
LT1976FE#PBF-ND	1.5A Step-Down Switching Regulator*	16-TSSOP	10.32	7.38	6.08	
LT1977FE#PBF-ND	1.5A Step-Down Switching Regulator*	16-TSSOP	9.20	6.11	4.79	
LT3008ECD#TRMPBFCF-ND	3µA IQ, 20mA LDO Linear Regulator*	6-DFN	3.33	2.98	2.68	
LT3008EDC#TRMPBFCF-ND	3µA IQ, 20mA LDO Linear Regulator*	6-DFN	819.18/500			
LT3008EDC-1.2#TRMPBFCF-ND	1.2V, 20mA LDO Linear Regulator* NEW!	6-DFN	3.33	2.98	2.68	
LT3008EDC-1.5#TRMPBFCF-ND	1.5V, 20mA LDO Linear Regulator* NEW!	6-DFN	3.33	2.98	2.68	
LT3008EDC-1.8#TRMPBFCF-ND	1.8V, 20mA LDO Linear Regulator* NEW!	6-DFN	3.33	2.98	2.68	
LT3008EDC-1.8#TRMPBFCF-ND	1.8V, 20mA LDO Linear Regulator* NEW!	6-DFN	819.18/500			
LT3008EDC-2.5#TRMPBFCF-ND	2.5V, 20mA LDO Linear Regulator* NEW!	6-DFN	3.33	2.98	2.68	
LT3008EDC-3.3#TRMPBFCF-ND	3.3V, 20mA LDO Linear Regulator* NEW!	6-DFN	3.33	2.98	2.68	
LT3008EDC-3.3#TRMPBFCF-ND	3.3V, 20mA LDO Linear Regulator* NEW!	6-DFN	819.18/500			
LT3008EDC-5#TRMPBFCF-ND	5V, 20mA LDO Linear Regulator* NEW!	6-DFN	3.33	2.98	2.68	
LT3008EDC-5#TRMPBFCF-ND	5V, 20mA LDO Linear Regulator* NEW!	6-DFN	819.18/500			
LT3008ETS#TRMPBFCF-ND	3µA IQ, 20mA LDO Linear Regulator*	TSOT-23-8	3.33	2.98	2.68	
LT3008ETS#TRMPBFCF-ND	3µA IQ, 20mA LDO Linear Regulator*	TSOT-23-8	819.18/500			
LT3008ETS-1.2#TRMPBFCF-ND	1.2V, 20mA LDO Linear Regulator* NEW!	TSOT-23-8	3.33	2.98	2.68	
LT3008ETS-1.5#TRMPBFCF-ND	1.5V, 20mA LDO Linear Regulator* NEW!	TSOT-23-8	3.33	2.98	2.68	
LT3008ETS-1.8#TRMPBFCF-ND	1.8V, 20mA LDO Linear Regulator* NEW!	TSOT-23-8	3.33	2.98	2.68	
LT3008ETS-2.5#TRMPBFCF-ND	2.5V, 20mA LDO Linear Regulator* NEW!	TSOT-23-8	3.33	2.98	2.68	
LT3008ETS-2.5#TRMPBFCF-ND	2.5V, 20mA LDO Linear Regulator* NEW!	TSOT-23-8	819.18/500			
LT3008ETS-3.3#TRMPBFCF-ND	3.3V, 20mA LDO Linear Regulator* NEW!	TSOT-23-8	3.33	2.98	2.68	
LT3008ETS-3.3#TRMPBFCF-ND	3.3V, 20mA LDO Linear Regulator* NEW!	TSOT-23-8	819.18/500			
LT3008ETS-5#TRMPBFCF-ND	5V, 20mA LDO Linear Regulator* NEW!	TSOT-23-8	3.33	2.98	2.68	
LT3008ETS-5#TRMPBFCF-ND	5V, 20mA LDO Linear Regulator* NEW!	TSOT-23-8	819.18/500			
LT3009EDC#TRMPBFCF-ND	3µA IQ, 20mA LDO Linear Regulator*	6-DFN	2.51	2.25	2.02	
LT3009EDC#TRMPBFCF-ND	3µA IQ, 20mA LDO Linear Regulator*	6-DFN	645.24/500			
LT3009ESC8-1.2#TRMPBFCF-ND	1.2V, 20mA LDO Linear Regulator* NEW!	SC70-8	2.67	2.39	2.15	
LT3009ESC8-1.2#TRMPBFCF-ND	1.2V, 20mA LDO Linear Regulator* NEW!	SC70-8	645.24/500			
LT3009ESC8-1.5#TRMPBFCF-ND	1.5V, 20mA LDO Linear Regulator* NEW!	SC70-8	2.67	2.39	2.15	
LT3009ESC8-1.5#TRMPBFCF-ND	1.5V, 20mA LDO Linear Regulator* NEW!	SC70-8	645.24/500			
LT3010EMS8E#PBF-ND	50mA, 3V to 80V LDO µPwr Linear Regulator*	8-MSOP	3.51	2.51	2.07	
LT3010EMS8E-5#PBF-ND	50mA, 3V to 80V LDO µPwr Linear Regulator*	8-MSOP	3.51	2.51	2.07	
LT3010HMS8E-5#PBF-ND	50mA, 3V to 80V LDO µPwr Linear Regulator*	8-MSOP	4.60	3.29	2.71	
LT3011EDD#PBF-ND	50mA, 3V to 80V LDO µPwr Linear Regulator*	10-DFN	4.19	2.81	2.40	
LT3011EMS8E#PBF-ND	50mA, 3V to 80V LDO µPwr Linear Regulator*	10-DFN	4.19	2.81	2.40	
LT3011DD#PBF-ND	50mA, 3V to 80V LDO µPwr Linear Regulator*	10-DFN	4.60	3.10	2.63	
LT3012BEFF#PBF-ND	250mA, 4V to 80V LDO µPwr Linear Regulator*	16-TSSOP	4.94	3.53	2.91	
LT3013EDD#PBF-ND	250mA, 4V to 80V LDO µPwr Linear Regulator*	12-DFN	5.05	3.61	2.98	
LT3013FE#PBF-ND	250mA, 4V to 80V LDO µPwr Linear Regulator*	16-TSSOP	5.39	3.85	3.17	
LT3014EDD#PBF-ND	20mA, 3V to 80V LDO µPwr Linear Regulator*	8-DFN	3.34	2.41	1.99	
LT3014HVEDD#PBF-ND	20mA, 3V to 80V LDO µPwr Linear Regulator*	8-DFN	3.82	2.73	2.25	
LT3020EDD#PBF-ND	100mA, Adj. Low Volt. V LDO Linear Regulator*	8-DFN	3.37	2.24	1.80	
LT3021EDD#PBF-ND	500mA, Adj. Low Volt. V LDO Linear Regulator*	16-DFN	5.05	3.61	2.98	
LT3021ES8#PBF-ND	500mA, Adj. Low Volt. V LDO Linear Regulator*	8-SOIC	5.05	3.61	2.98	
LT3021ES8-1.8#PBF-ND	500mA, 1.8V, LV V LDO Linear Regulator*	8-SOIC	5.93	3.98	3.38	
LT3023EDD-ND	Dual 100mA, LDO Low Noise µPwr Regulator*	10-DFN	3.82	2.73	2.25	
LT3023EDD#PBF-ND	Dual 100mA, LDO Low Noise µPwr Regulator*	10-DFN	3.92	2.73	2.25	
LT3023EMSE#PBF-ND	Dual 100mA, LDO Low Noise µPwr Regulator*	10-DFN	3.59	2.57	2.11	
LT3024EDD#PBF-ND	Dual 100mA/500mA, LDO Low Noise µPwr Reg.*	12-DFN	5.50	3.93	3.24	
LT3024FE#PBF-ND	Dual 100mA/500mA, LDO Low Noise µPwr Reg.*	16-TSSOP	5.50	3.93	3.24	
LT3027EDD#PBF-ND	Dual 100mA, LDO Low Noise MPU Regulator*	10-DFN	3.93	2.61	2.09	
LT3027EMSE#PBF-ND	Dual 100mA, LDO Low Noise MPU Regulator*	10-MSOP	3.70	2.46	1.98	
LT3028EDD#PBF-ND	Dual 100mA/500mA, LDO Low Noise µPwr Reg.*	16-DFN	5.95	3.95	3.17	
LT3028FE#PBF-ND	Dual 100mA/500mA, LDO Low Noise µPwr Reg.*	16-TSSOP	5.72	3.80	3.06	
LT3029EDD#PBF-ND	Dual 0.5A, LDO Linear Regulator* NEW!	16-DFN	6.85	4.61	3.92	
LT3029EMSE#PBF-ND	Dual 0.5A, LDO Linear Regulator* NEW!	16-MSOP	6.85	4.61	3.92	
LT3029MPS#PBF-ND	Dual 0.5A, LDO Linear Regulator* NEW!	16-MSOP	18.46	12.42	10.55	
LT3032EDD#PBF-ND	Dual 150mA Low Noise LDO Linear Reg.* NEW!	14-DFN	5.25	3.53	3.00	
LT3032DE#PBF-ND	Dual 150mA Low Noise LDO Linear Reg.* NEW!	14-DFN	6.06	4.09	3.48	
LT3032DDE#PBF-ND	100mA, Adjustable LDO Linear Regulator* NEW!	12-DFN	4.31	3.85	3.46	
LT3035EDD#TRMPBFCF-ND	100mA, Adjustable LDO Linear Regulator* NEW!	12-DFN	1054.83/500			
LT3035EMSE#PBF-ND	100mA, Adjustable LDO Linear Regulator* NEW!	12-MSOP	3.70	2.50	2.11	
LT3060EDC#TRMPBFCF-ND	100mA Low Noise LDO Linear Regulator* NEW!	8-DFN	3.37	3.01	2.71	
LT3060EDC#TRMPBFCF-ND	100mA Low Noise LDO Linear Regulator* NEW!	8-TSOT	824.79/500			
LT3060ETS#TRMPBFCF-ND	100mA Low Noise LDO Linear Regulator* NEW!	8-TSOT	3.37	3.01	2.71	
LT3060ETS#TRMPBFCF-ND	100mA Low Noise LDO Linear Regulator* NEW!	8-TSOT	824.79/500			
LT3060HTS#TRMPBFCF-ND	100mA Low Noise LDO Linear Regulator* NEW!	8-TSOT	4.59	4.10	3.69	
LT3060HTS#TRMPBFCF-ND	100mA Low Noise LDO Linear Regulator* NEW!	8-TSOT	1138.99/500			
LT3060MPTS#TRMPBFCF-ND	100mA Low Noise LDO Linear Regulator* NEW!	8-TSOT	11.72	10.47	9.42	
LT3060MPTS#TRMPBFCF-ND	100mA Low Noise LDO Linear Regulator* NEW!	8-TSOT	2956.89/500			
LT3070EUD#PBF-ND	5A Low Noise LDO Linear Regulator* NEW!	28-DFN	10.02	6.74	5.73	
LT3080EDD#PBF-ND	Single 1.1A LDO Regulator*	8-DFN	4.21	3.02	2.48	
LT3080EDD#TRMPBFCF-ND	Single 1.1A LDO Regulator*	8-DFN	4.87	4.35	3.92	
LT3080EDD#TRMPBFCF-ND	Single 1.1A LDO Regulator*	8-DFN	6406.58/2,500			
LT3080EMS8E#PBF-ND	Single 1.1A LDO Regulator*	8-MSOP	4.35	3.11	2.56	
LT3080EMS8E#TRMPBFCF-ND	Single 1.1A LDO Regulator*	8-MSOP	5.03	4.49	4.04	
LT3080EMS8E#TRMPBFCF-ND	Single 1.1A LDO Regulator*	8-MSOP	6602.65/2,500			
LT3080E#PBF-ND	Single 1.1A LDO Regulator* NEW!	5-DDPAK	4.92	3.53	3.00	
LT3080EST#PBF-ND	Single 1.1A LDO Regulator*	SOT-223	4.07	2.91	2.40	
LT3080EST#TRMPBFCF-ND	Single 1.1A LDO Regulator*	SOT-223	4.71	4.21	3.79	
LT3080ETS#TRMPBFCF-ND	Single 1.1A LDO Regulator*	SOT-223	4945.26/2,000			
LT3080E#PBF-ND	Single 1.1A LDO Regulator*	TQFN-25	4.92	3.53	2.91	
LT3082EDD#PBF-ND	200mA, Adj. LDO Linear Regulator* NEW!	8-DFN	3.34	2.25	1.91	
LT3082EST#PBF-ND	200mA, Adj. LDO Linear Regulator* NEW!	8-TSOT	3.59	2.41	2.05	
LT3082ETS#TRMPBFCF-ND	200mA, Adj. LDO Linear Regulator* NEW!	TSOT-23-8	3.86	3.46	3.11	
LT3082ETS#TRMPBFCF-ND	200mA, Adj. LDO Linear Regulator* NEW!	TSOT-23-8	953.84/500			
LT3082ETS#TRMPBFCF-ND	200mA, Adj. LDO Linear Regulator* NEW!	6-DFN	4.75	4.24	3.82	
LT3085EDC#TRMPBFCF-ND	Adj., 500mA LDO Regulator*	6-DFN	1178.27/500			
LT3085EMS8E#PBF-ND	Adj., 500mA LDO Regulator*	8-MSOP	4.38	2.94	2.50	
LT3430FE#PBF-ND	High Voltage, 3A Step-Down Switching Reg.*	16-TSSOP	11.11	7.94	6.54	
LT3430FE-1#PBF-ND	High Voltage, 3A Step-Down Switching Reg.*	16-TSSOP	11.11	7.94	6.54	
LT3430FE#PBF-ND	High Voltage, 3A Step-Down Switching Reg.*	16-TSSOP	12.77	9.13	7.51	
LT3430FE-1#PBF-ND	High Voltage, 3A Step-Down Switching Reg.*	16-TSSOP	12.77	9.13	7.51	
LT3431FE#PBF-ND	High Voltage, 3A Step-Down Switching Reg.*	16-TSSOP	11.11	7.94	6.54	
LT3433FE#PBF-ND	High Voltage, Step-Up/Step-Down DC/DC Conv.*	16-TSSOP	7.29	5.21	4.29	

LINEAD TECHNOLOGY		Digi Reel (Cont.)		POWER MANAGEMENT		
Digi-Key Part No.	Description	Pkg.	Price Each*			
			1	25	100	
LT3434FE#PBF-ND	High Voltage, 3A Step-Down Switching Reg.*	16-TSSOP	11.78	8.42	6.94	
LT3435FE#PBF-ND	High Voltage, 3A Step-Down Switching Reg.*	16-TSSOP	11.78	8.42	6.94	
LT3437FE#PBF-ND	High Voltage, 500mA Step-Down Switching Reg.*	16-TSSOP	6.73	4.82	3.97	
LT3438FE#PBF-ND	1A Isolated DC/DC Transformer Driver*	16-TSSOP	7.86	5.62	4.63	
LT3460ES5#TRMPBFCF-ND	1.3MHz Step-Up DC/DC Converter*	TSOT-23-5	4.15	3.71	3.34	
LT3460ES5#TRMPBFCF-ND	1.3MHz Step-Up DC/DC Converter*	TSOT-23-5	1054.83/500			
LT3461AES6#TRMPBFCF-ND	3MHz Step-Up DC/DC Converter*	TSOT-23-6	4.40	3.93	3.54	
LT3461AES6#TRMPBFCF-ND	3MHz Step-Up DC/DC Converter*	TSOT-23-6	1122.16/500			
LT3461ES6#TRMPBFCF-ND	1.3MHz Step-Up DC/DC Converter*	TSOT-23-6	4.40	3.93	3.54	
LT3461ES6#TRMPBFCF-ND	1.3MHz Step-Up DC/DC Converter*	TSOT-23-6	1122.16/500			
LT3463AEDD#PBF-ND	Dual Micropower DC/DC Converter*	10-DFN	4.38	3.14	2.57	
LT3463EDD#PBF-ND	Dual Micropower DC/DC Converter*	10-DFN	4.38	3.14	2.57	
LT3464ETS#TRMPBFCF-ND	Micropower Boost Converter*	TSOT-23-8	4.15	3.71	3.34	
LT3464ETS#TRMPBFCF-ND	Micropower Boost Converter*	TSOT-23-8	1054.83/500			
LT3464ETS#TRMPBFCF-ND	White LED Driver and Dual Step-Up Boost Conv.*	10-DFN	4.38	3.14	2.57	
LT3464ES6#TRMPBFCF-ND	1.1A Step-Up DC/DC Converter*	TSOT-23-6	4.65	4.16	3.74	
LT3464ES6#TRMPBFCF-ND	1.1A Step-Up DC/DC Converter*	TSOT-23-6	1189.49/500			
LT3464ES6#TRMPBFCF-ND	1.1A Step-Up DC/DC Converter*	TSOT-23-6	4.65	4.16	3.74	
LT3464ES6#TRMPBFCF-ND	1.1A Step-Up DC/DC Converter*	TSOT-23-6	1189.49/500			
LT3470ETS#TRMPBFCF-ND	Micropower Buck Regulator*	TSOT-23-8	6.04	5.39	4.85	
LT3470ETS#TRMPBFCF-ND	Micropower Buck Regulator*	TSOT-23-8	1402.70/500			
LT3470TS8#TRMPBFCF-ND	Micropower Buck Regulator*	TSOT-23-8	7.19	6.43	5.79	
LT3470TS8#TRMPBFCF-ND	Micropower Buck Regulator*	TSOT-23-8	1677.63/500			
LT3471EDD#PBF-ND	Dual 1.3A, Switching Regulator Boost/Inverter*	10-DFN	6.28	4.18	3.35	
LT3472EDD#PBF-ND	Dual Boost/Inverting DC/DC Conv. for CCD*	10-DFN	4.28	2.91	2.42	
LT3473AEDD#PBF-ND	Micropower 1A Boost DC/DC Converter*	12-DFN	4.60	3.29	2.71	
LT3473EDD#PBF-ND	Micropower 1A Boost DC/DC Converter*	8-DFN	4.38	3.14	2.57	
LT3479EDD#PBF-ND	3A Full					