

DIGI KEY TECHNOLOGY		Digi Reel® (Cont.)		DATA CONVERSION		
Digi-Key Part No.	Description	Pkg.	Price Each*	1	25	100
LTC1278-5CSW#PBF-ND	12-Bit Sampling ADC with Shutdown*	24-SOIC	28.76	19.19	16.44	
LTC1279CG-ND	12-Bit Sampling ADC with Shutdown	24-SSOP	29.04	19.28	15.94	
LTC1282BCSW-ND	12-Bit 3V, Sampling ADC with Reference	24-SOIC	31.57	21.05	16.56	
LTC1285CN8#PBF-ND	12-Bit 3V, Micropower Sampling ADC*	8-Dip	14.25	9.47	7.30	
LTC1286CN8#PBF-ND	12-Bit 3V, Micropower Sampling ADC*	8-SOIC	15.15	10.06	7.80	
LTC1286CS8#PBF-ND	12-Bit Micropower Sampling ADC*	8-Dip	11.09	7.41	5.90	
LTC1286CS8#PBF-ND	12-Bit Micropower Sampling ADC*	8-SOIC	11.93	7.97	6.35	
LTC1286IS8#PBF-ND	12-Bit Micropower Sampling ADC*	8-SOIC	14.87	9.94	7.92	
LTC1288CN8#PBF-ND	12-Bit 3V, Serial In/Out Sampling ADC*	8-Dip	14.25	9.47	7.30	
LTC1288CS8#PBF-ND	12-Bit 3V, Serial In/Out Sampling ADC*	8-SOIC	15.15	10.06	7.80	
LTC1290CCN#PBF-ND	12-Bit Data Acquisition System*	20-Dip	35.46	23.55	17.90	
LTC1290CCSW#PBF-ND	12-Bit Data Acquisition System*	20-SOIC	42.53	28.24	21.49	
LTC1290CIN#PBF-ND	12-Bit Data Acquisition System*	20-Dip	50.72	33.68	26.21	
LTC1290CISW#PBF-ND	12-Bit Data Acquisition System*	20-SOIC	50.72	33.68	26.21	
LTC1290DCN#PBF-ND	12-Bit Data Acquisition System*	20-Dip	14.81	9.84	7.52	
LTC1290DCSW#PBF-ND	12-Bit Data Acquisition System*	20-SOIC	25.02	16.62	12.74	
LTC1291CCN8-ND	12-Bit Data Acquisition System	8-Dip	31.57	21.05	16.84	
LTC1291CCN8#PBF-ND	12-Bit Data Acquisition System*	8-Dip	31.57	21.05	16.84	
LTC1291CCN8#PBF-ND	12-Bit Data Acquisition System*	8-Dip	20.34	13.58	10.67	
LTC1292CCN8#PBF-ND	12-Bit Data Acquisition System*	8-Dip	31.57	21.05	16.84	
LTC1292CCN8#PBF-ND	12-Bit Data Acquisition System*	8-Dip	20.34	13.58	10.67	
LTC1293CCN#PBF-ND	12-Bit Data Acquisition System*	16-SOIC	50.50	33.67	26.88	
LTC1293CCSW#PBF-ND	12-Bit Data Acquisition System*	16-SOIC	40.40	26.94	21.49	
LTC1293CCN#PBF-ND	12-Bit Data Acquisition System*	16-Dip	33.66	22.45	17.90	
LTC1293DCN#PBF-ND	12-Bit Data Acquisition System*	16-SOIC	20.34	13.58	10.67	
LTC1293DCSW#PBF-ND	12-Bit Data Acquisition System*	16-SOIC	24.41	16.28	12.74	
LTC1294BCSW-ND	12-Bit Data Acquisition System	20-SOIC	50.50	33.67	26.88	
LTC1294CCSW-ND	12-Bit Data Acquisition System*	20-SOIC	40.40	26.94	21.49	
LTC1294DCN#PBF-ND	12-Bit Data Acquisition System*	20-Dip	20.34	13.58	10.67	
LTC1294DCSW-ND	12-Bit Data Acquisition System	20-SOIC	24.41	16.28	12.74	
LTC1294DCSW#PBF-ND	12-Bit Data Acquisition System*	20-SOIC	24.41	16.28	12.74	
LTC1296BCN#PBF-ND	12-Bit Data Acquisition System	20-Dip	27.36	18.24	14.59	
LTC1296BCSW-ND	12-Bit Data Acquisition System	20-SOIC	28.05	18.69	14.99	
LTC1296BCSW#PBF-ND	12-Bit Data Acquisition System*	20-SOIC	28.05	18.69	14.99	
LTC1296CCSW#PBF-ND	12-Bit Data Acquisition System*	20-SOIC	20.06	13.36	10.67	
LTC1296DCN#PBF-ND	12-Bit Data Acquisition System*	20-Dip	17.82	11.90	9.49	
LTC1296DCSW#PBF-ND	12-Bit Data Acquisition System*	20-SOIC	18.24	12.18	9.71	
LTC1297CCN8-ND	12-Bit Data Acquisition System	8-Dip	24.41	16.28	12.80	
LTC1297CCN8#PBF-ND	12-Bit Data Acquisition System*	8-Dip	24.41	16.28	12.80	
LTC1298CN8#PBF-ND	12-Bit Sampling ADC*	8-Dip	11.09	7.41	5.90	
LTC1298CS8#PBF-ND	12-Bit Sampling ADC*	8-SOIC	11.93	7.97	6.35	
LTC1298IS8#PBF-ND	12-Bit Sampling ADC, Ind. Temp*	8-SOIC	14.87	9.94	7.92	
LTC1392CN8#PBF-ND	10-Bit Micropow. Data Acquisition System*	8-Dip	8.42	5.62	4.61	
LTC1400CS8#PBF-ND	12-Bit 400kSPS ADC with Shutdown*	8-SOIC	11.22	7.46	5.90	
LTC1400IS8-ND	12-Bit 400kSPS ADC with Shutdown*	8-SOIC	12.49	8.29	6.57	
LTC1400IS8#PBF-ND	12-Bit 400kSPS ADC with Shutdown*	8-SOIC	12.49	8.29	6.57	
LTC1401IS8#PBF-ND	12-Bit 200kSPS ADC with Shutdown*	8-SOIC	10.70	5.78	4.55	
LTC1403ACMSE#PBF-ND	14-Bit 2.8MSPS Sampling ADC*	10-MSPOP	15.71	11.23	9.25	
LTC1403ACMSE-1#PBF-ND	14-Bit 2.8MSPS Sampling ADC*	10-MSPOP	15.71	11.23	9.25	
LTC1403AIMSE#PBF-ND	14-Bit 2.8MSPS Sampling ADC*	10-MSPOP	17.95	12.83	10.56	
LTC1403AIMSE-1#PBF-ND	14-Bit 2.8MSPS Sampling ADC*	10-MSPOP	17.95	12.83	10.56	
LTC1403CMSE#PBF-ND	12-Bit 2.8MSPS Sampling ADC*	10-MSPOP	8.98	6.41	5.29	
LTC1403CMSE-1#PBF-ND	12-Bit 2.8MSPS Sampling ADC*	10-MSPOP	8.98	6.41	5.29	
LTC1403IMSE#PBF-ND	12-Bit 2.8MSPS Sampling ADC*	10-MSPOP	10.25	7.32	6.03	
LTC1403IMSE-1#PBF-ND	12-Bit 2.8MSPS Sampling ADC*	10-MSPOP	10.25	7.32	6.03	
LTC1404CS8#PBF-ND	12-Bit 600kSPS ADC with Shutdown*	8-SOIC	11.78	7.83	6.18	
LTC1404IS8#PBF-ND	12-Bit 600kSPS ADC with Shutdown*	8-SOIC	12.90	8.57	6.79	
LTC1407AHMSE#PBF-ND	14-Bit 3MSPS Simultaneous Sampling ADC*	10-MSPOP	23.04	15.49	13.17	
LTC1407ACMSE#PBF-ND	14-Bit 3MSPS Simultaneous Sampling ADC*	10-MSPOP	15.71	11.23	9.25	
LTC1407ACMSE-1#PBF-ND	14-Bit 3MSPS Simultaneous Sampling ADC*	10-MSPOP	15.71	11.23	9.25	
LTC1407AIMSE#PBF-ND	14-Bit 3MSPS Simultaneous Sampling ADC*	10-MSPOP	17.95	12.83	10.56	
LTC1407AIMSE-1#PBF-ND	14-Bit 3MSPS Simultaneous Sampling ADC*	10-MSPOP	17.95	12.83	10.56	
LTC1407CMSE#PBF-ND	12-Bit 3MSPS Simultaneous Sampling ADC*	10-MSPOP	8.98	6.41	5.29	
LTC1407CMSE-1#PBF-ND	12-Bit 3MSPS Simultaneous Sampling ADC*	10-MSPOP	8.98	6.41	5.29	
LTC1407IMSE-1#PBF-ND	12-Bit 3MSPS Simultaneous Sampling ADC*	10-MSPOP	10.25	7.32	6.03	
LTC1408CUH#PBF-ND	14-Bit 600kSPS ADC with Shutdown*	32-QFN	20.59	14.72	12.11	
LTC1408CUH-12#PBF-ND	14-Bit 600kSPS ADC with Shutdown*	32-QFN	12.99	9.29	7.65	
LTC1408IUH#PBF-ND	14-Bit 600kSPS ADC w/Shutdown*	32-QFN	24.72	17.66	14.55	
LTC1408IUH-12#PBF-ND	14-Bit 600kSPS ADC w/Shutdown*	32-QFN	15.60	11.15	9.18	
LTC1410CSW#PBF-ND	12-Bit 1.25MSPS Sampling ADC*	28-SSOP	23.85	15.84	11.96	
LTC1412CG#PBF-ND	12-Bit 3MSPS Sampling ADC*	28-SSOP	23.99	15.93	12.00	
LTC1414CG#PBF-ND	12-Bit 2.8MSPS Sampling ADC*	28-SSOP	38.15	25.42	20.37	
LTC1415CSW#PBF-ND	12-Bit 1.25MSPS Sampling ADC*	28-SSOP	24.97	16.58	12.52	
LTC1415CSW#PBF-ND	12-Bit 1.25MSPS Sampling ADC*	28-SOIC	23.85	15.84	11.96	
LTC1415ISG#PBF-ND	12-Bit 1.25MSPS Sampling ADC*	28-SSOP	27.21	18.07	13.64	
LTC1416CG#PBF-ND	14-Bit 400kSPS Sampling ADC, Ind. Temp*	28-SSOP	16.55	11.00	8.31	
LTC1416ISG#PBF-ND	14-Bit 400kSPS Sampling ADC, Ind. Temp*	28-SSOP	17.67	11.74	8.84	
LTC1417ACGN#PBF-ND	14-Bit 400kSPS Sampling ADC*	16-SSOP	22.44	14.91	11.23	
LTC1417CGN#PBF-ND	14-Bit 400kSPS Sampling ADC*	16-SSOP	18.24	12.11	9.15	
LTC1417IGN#PBF-ND	14-Bit 400kSPS Sampling ADC*	16-SSOP	20.06	13.32	10.05	
LTC1418ACG#PBF-ND	14-Bit 200kSPS ADC, Serial/Parallel I/O*	28-SSOP	24.97	16.58	12.52	
LTC1418AIG-ND	14-Bit 200kSPS ADC, S/P I/O, Ind. Temp*	28-SSOP	26.80	17.79	13.41	
LTC1418CG-ND	14-Bit 200kSPS ADC, S/P I/O, Ind. Temp*	28-SSOP	19.36	12.86	9.71	
LTC1418CG#PBF-ND	14-Bit 200kSPS ADC, S/P I/O, Ind. Temp*	28-SSOP	19.36	12.86	9.71	
LTC1418CN-ND	14-Bit 200kSPS ADC, Serial/Parallel I/O*	28-Dip	18.80	12.49	9.43	
LTC1418CN#PBF-ND	14-Bit 200kSPS ADC, Serial/Parallel I/O*	28-Dip	18.80	12.49	9.43	
LTC1419ACSW#PBF-ND	14-Bit 800kSPS Sampling ADC*	28-SOIC	60.04	39.87	30.24	
LTC1419CG-ND	14-Bit 800kSPS Sampling ADC	28-SSOP	36.47	24.22	18.02	
LTC1419CSW#PBF-ND	14-Bit 800kSPS Sampling ADC*	28-SOIC	36.19	24.03	18.10	
LTC1419ISG#PBF-ND	14-Bit 800kSPS Sampling ADC, Ind. Temp*	28-SSOP	40.68	27.02	20.77	
LTC1594CS#PBF-ND	4-Channel, 12-Bit SV, Sampling Serial ADC*	16-SOIC	12.92	8.39	6.74	
LTC1594IS#PBF-ND	4-Channel, 12-Bit SV, Sampling Serial ADC*	16-SOIC	14.59	9.69	8.00	
LTC1598CG-ND	8-Channel, 12-Bit SV, Sampling Serial ADC*	24-SSOP	12.90	8.57	6.96	
LTC1598CG#PBF-ND	8-Channel, 12-Bit SV, Sampling Serial ADC*	24-SSOP	12.90	8.57	6.96	
LTC1598LCG#PBF-ND	8-Channel, 12-Bit SV, Sampling Serial ADC*	24-SSOP	13.05	8.70	7.24	
LTC1603CG#PBF-ND	16-Bit Sampling ADC with Shutdown*	36-SSOP	22.87	15.27	12.69	
LTC1604AIG#PBF-ND	16-Bit Sampling ADC with Shutdown*	36-SSOP	70.84	47.04	35.42	
LTC1604CG#PBF-ND	16-Bit Sampling ADC with Shutdown*	36-SSOP	49.94	33.16	27.49	
LTC1605ACC#PBF-ND	16-Bit, 100kSPS Sampling ADC*	28-SSOP	55.69	36.98	29.87	
LTC1605AISW#PBF-ND	16-Bit, 100kSPS Sampling ADC, Ind. Temp*	28-SOIC	57.23	38.01	28.62	
LTC1605CN#PBF-ND	16-Bit, 100kSPS Sampling ADC*	28-Dip	40.54	26.92	20.27	
LTC1605CSW#PBF-ND	16-Bit, 100kSPS Sampling ADC*	28-SOIC	40.54	26.92	20.27	
LTC1605IN#PBF-ND	16-Bit, 100kSPS Sampling ADC, Ind. Temp*	28-Dip	42.92	28.51	21.49	
LTC1605ISW#PBF-ND	16-Bit, 100kSPS Sampling ADC, Ind. Temp*	28-SOIC	42.92	28.51	21.49	
LTC1605-1CG#PBF-ND	16-Bit, 100kSPS Sampling ADC*	28-SSOP	41.39	27.48	20.99	
LTC1605-2CG#PBF-ND	16-Bit, 100kSPS Sampling ADC*	28-SSOP	41.39	27.48	20.99	

* RoHS Compliant

★ CALL FOR LOWER PRICING ON LARGER QUANTITIES! ★

(Continued)

Free shipping on orders over \$200 CAD! All prices in Canadian dollars and include duty and brokerage fees.

1176 (CA2011)

1-800-344-4539 • www.digikey.ca • 218-681-6674 • Fax: 218-681-3380

DIGI KEY TECHNOLOGY		Digi Reel® (Cont.)		DATA CONVERSION		
Digi-Key Part No.	Description	Pkg.	Price Each*	1	25	100
LTC1606ACG#PBF-ND	16-Bit, 250kSPS Sampling ADC*	28-SSOP	60.74	40.33	30.42	
LTC1606ACSW#PBF-ND	16-Bit, 250kSPS Sampling ADC*	28-SOIC	60.74	40.33	30.42	
LTC1608ACG#PBF-ND	16-Bit, 500kSPS Sampling ADC*	36-SSOP	55.13	36.61	28.28	
LTC1608CG#PBF-ND	16-Bit, 500kSPS Sampling ADC*	36-SSOP	39.28	26.08	19.64	
LTC1609CSW#PBF-ND	16-Bit, 200kSPS Serial Sampling ADC*	20-SOIC	35.63	23.66	17.82	
LTC1609ISG#PBF-ND	16-Bit, 200kSPS Sampling ADC, Ind. Temp*	28-SSOP	39.28	26.08	19.64	
LTC1609ISW#PBF-ND	16-Bit, 200kSPS Serial Sampling ADC*	20-SOIC	39.28	26.08	19.64	
LTC1851CFW-ND	8-Channel, 12-Bit, 1.25MSPS Sampling ADC	48-TSSOP	16.42	10.90	8.81	
LTC1851CFW#PBF-ND	8-Channel, 12-Bit, 1.25MSPS Sampling ADC	48-TSSOP	16.42	10.90	8.81	
LTC1853CFW#PBF-ND	8-Ch., 12-Bit, 400kSPS Low Power ADC*	48-TSSOP	16.42	10.90	8.81	
LTC1856CG#PBF-ND	8-Ch., 16-Bit, 100kSPS, Low Power ADC*	28-SSOP	29.79	21.28	17.53	
LTC1857CG#PBF-ND	8-Ch., 12-Bit, 100kSPS, LP, ADC*	28-TSSOP	20.09	13.39	11.48	
LTC1858CG#PBF-ND	8-Ch., 14-Bit, 100kSPS, LP, ADC*	28-TSSOP	29.06	19.38	16.61	
LTC1859CG#PBF-ND	8-Ch., 16-Bit, 100kSPS, LP, ADC*	28-TSSOP	39.28	26.18	22.45	
LTC1860CMS8#PBF-ND	1-Channel, 12-Bit, 250kSPS ADC*	8-MSPOP	5.48	3.64	2.98	
LTC1860CS8#PBF-ND	1-Channel, 12-Bit, 250kSPS ADC*	8-SOIC	5.33	3.54	2.92	
LTC1861CMS-ND	2-Channel, 12-Bit, 250kSPS ADC*	10-MSPOP	7.01	4.66	3.93	
LTC1861CMS#PBF-ND	2-Channel, 12-Bit, 250kSPS ADC*	10-MSPOP	7.01	4.66	3.93	
LTC1861CS8#PBF-ND	2-Channel, 12-Bit, 250kSPS ADC*	8-SOIC	6.60	4.38	3.65	
LTC1861LCMS#PBF-ND	3V, 2-Channel, 12-Bit, 150kSPS ADC*	10-MSPOP	6.32	4.20	3.43	
LTC1863LCG#PBF-ND	3V, 8-Channel, 12-Bit, 175kSPS ADC*	16-SSOP	8.56	6.12	5.04	
LTC1864ACMS8#PBF-ND	1-Channel, 16-Bit, 250kSPS ADC*	8-MSPOP	16.83	11.18	9.04	
LTC1864ACMS8#PBF-ND	1-Channel, 16-Bit, 250kSPS ADC*	8-SOIC	16.14	10.72	8.65	
LTC1864AIMS8#PBF-ND	1-Channel, 16-Bit, 250kSPS ADC*	8-MSPOP	17.54	11.65	9.43	
LTC1864CMS8#PBF-ND	1-Channel, 16-Bit, 250kSPS ADC*	8-MSPOP	14.45	9.60	7.75	
LTC1864CS8#PBF-ND	1-Channel, 16-Bit, 250kSPS ADC*	8-SOIC	13.89	9.23	7.47	
LTC1865ACMS#PBF-ND	2-Channel, 16-Bit, 250kSPS ADC*	10-MSPOP	17.26	11.46	9.60	
LTC1865ACMS#PBF-ND	2-Channel, 16-Bit, 250kSPS ADC*	8-SOIC	16.55	11.00	9.21	
LTC1865CMS#PBF-ND	2-Channel, 16-Bit, 250kSPS ADC*	10-MSPOP	15.01	9.97	8.37	
LTC1865CS8#PBF-ND	2-Channel, 16-Bit, 250kSPS ADC*	8-SOIC	14.45	9.60	8.03	
LTC1865LAIMS#PBF-ND	2-Channel, 16-Bit, 150kSPS ADC*	10-MSPOP	17.95	11.93	9.99	
LTC1865LAIMS#PBF-ND	2-Channel, 16-Bit, 150kSPS ADC*	10-MSPOP	15.01	9.97	8.37	
LTC1867ACGN#PBF-ND	8-Channel, 16-Bit, 200kSPS ADC*	16-SSOP	20.63	13.75	11.79	
LTC1867CGN#PBF-ND	8-Channel, 16-Bit, 200kSPS ADC*	16-SSOP	17.39	11.62	9.94	
LTC1867LAGN#PBF-ND</						