



Ceramic Conformally Coated Axial Leaded Capacitors "AXIMAX" (Cont.)

Dielectric	Voltage	Capacitance	Cap. Tol. (%)	Size Code	Digi-Key Part No.	Cut Tape Pricing				Digi-Key Part No.	Tape and Reel		Kemet Part No.	
						1	10	25	100		Qty.	Pricing		
COG	50	680pF	±5	410	399-4480-1-ND	.74	5.89	12.43	35.52	399-4480-2-ND	5,000	121.20/M	C410C681J5G5TA7200	
	50	1000pF	±5	410	399-4449-1-ND	.67	5.35	11.29	32.26	399-4449-2-ND	5,000	109.98/M	C410C102J5G5TA7200	
	50	1500pF	±5	412	399-4485-1-ND	.86	7.26	14.90	45.53	399-4485-2-ND	5,000	162.72/M	C412C152J5G5TA7200	
	50	2200pF	±5	412	399-4487-1-ND	.86	7.26	14.90	45.53	399-4487-2-ND	5,000	162.72/M	C412C222J5G5TA7200	
	50	1500pF	±5	420	399-4493-1-ND	.86	7.26	14.90	45.53	399-4493-2-ND	5,000	162.72/M	C420C152J5G5TA7200	
	50	2200pF	±5	420	399-4496-1-ND	.86	7.26	14.90	45.53	399-4496-2-ND	5,000	162.72/M	C420C222J5G5TA7200	
	50	3300pF	±5	430	399-4509-1-ND	1.25	10.60	22.01	72.03	399-4509-2-ND	2,500	299.62/M	C430C332J5G5TA7200	
	50	4700pF	±5	430	399-4511-1-ND	1.25	10.60	22.01	72.03	399-4511-2-ND	2,500	299.62/M	C430C472J5G5TA7200	
	50	6800pF	±5	430	399-4515-1-ND	1.25	10.60	22.01	72.03	399-4515-2-ND	2,500	299.62/M	C430C682J5G5TA7200	
	50	.01µF	±5	440	399-4520-1-ND	1.56	13.04	28.10	95.74	399-4520-2-ND	2,500	402.86/M	C440C103J5G5TA7200	
	50	.015µF	±5	440	399-4523-1-ND	1.71	13.97	31.51	112.43	399-4523-2-ND	2,500	476.92/M	C440C153J5G5TA7200	
	50	.015µF	±5	440	399-1836-1-ND	1.55	12.68	28.62	102.08	399-1836-2-ND	2,500	476.97/M	C440C153J5G5CA7200	
	X7R	100	470pF	±10	410	399-4474-1-ND	.50	3.98	8.39	23.99	—	—	—	C410C471K1R5TA7200
		100	680pF	±10	410	399-4481-1-ND	.56	4.41	9.29	26.54	399-4481-2-ND	5,000	89.78/M	C410C681K1R5TA7200
100		1000pF	±10	410	399-4450-1-ND	.47	3.70	7.81	22.32	—	—	—	C410C102K1R5TA7200	
100		1500pF	±10	410	399-4457-1-ND	.50	3.98	8.39	23.99	—	—	—	C410C152K1R5TA7200	
100		2200pF	±10	410	399-4463-1-ND	.56	4.41	9.29	26.54	399-4463-2-ND	5,000	89.78/M	C410C222K1R5TA7200	
100		3300pF	±10	410	399-4469-1-ND	.50	3.98	8.39	23.99	399-4469-2-ND	5,000	101.00/M	C410C332K1R5TA7200	
100		4700pF	±10	410	399-4475-1-ND	.56	4.41	9.29	26.54	399-4475-2-ND	5,000	89.78/M	C410C472K1R5TA7200	
100		6800pF	±10	410	399-4482-1-ND	.50	3.98	8.39	23.99	—	—	—	C410C682K1R5TA7200	
100		.01µF	±10	410	399-4451-1-ND	.58	4.61	9.45	24.14	399-4451-2-ND	5,000	77.43/M	C410C103K1R5TA7200	
100		.015µF	±10	412	399-4486-1-ND	.58	4.63	9.76	27.90	—	—	—	C412C153K1R5TA7200	
100		.022µF	±10	412	399-4488-1-ND	.63	5.30	10.86	33.18	399-4488-2-ND	5,000	118.95/M	C412C223K1R5TA7200	
100		.015µF	±10	420	399-4494-1-ND	.65	5.13	10.81	30.86	399-4494-2-ND	5,000	105.49/M	C420C153K1R5TA7200	
100		.022µF	±10	420	399-4497-1-ND	.63	5.24	10.75	32.85	—	—	—	C420C223K1R5TA7200	
100		.033µF	±10	420	399-4498-1-ND	.63	5.24	10.75	32.85	—	—	—	C420C333K1R5TA7200	
100		.047µF	±10	430	399-4512-1-ND	.81	6.73	13.83	42.23	—	—	—	C430C473K1R5TA7200	
100		.1µF	±10	430	399-4503-1-ND	.99	8.27	16.98	51.84	399-4503-2-ND	2,500	197.50/M	C430C104K1R5TA7200	
100		.068µF	±10	430	399-4516-1-ND	.95	8.11	16.83	55.10	399-4516-2-ND	2,500	230.05/M	C430C683K1R5TA7200	
100		.15µF	±10	440	399-4524-1-ND	1.28	10.67	22.99	78.36	399-4524-2-ND	2,500	328.80/M	C440C154K1R5TA7200	
50		.01µF	±10	410	399-4452-1-ND	.55	4.34	8.89	22.71	399-4452-2-ND	5,000	72.94/M	C410C103K5R5TA7200	
50		.015µF	±10	410	399-4458-1-ND	.64	5.09	10.74	30.69	—	—	—	C410C153K5R5TA7200	
50		.022µF	±10	410	399-4464-1-ND	.64	5.09	10.74	30.69	—	—	—	C410C223K5R5TA7200	
50		.033µF	±10	410	399-4470-1-ND	.72	5.63	11.88	33.95	399-4470-2-ND	5,000	115.59/M	C410C333K5R5TA7200	
50		.047µF	±10	410	399-4476-1-ND	.77	6.15	12.96	37.03	399-4476-2-ND	5,000	125.69/M	C410C473K5R5TA7200	
50		.068µF	±10	412	399-4490-1-ND	.77	6.15	12.96	37.03	399-4490-2-ND	5,000	125.69/M	C412C683K5R5TA7200	
50		.1µF	±10	412	399-4484-1-ND	.49	3.89	8.21	23.45	399-4484-2-ND	5,000	79.68/M	C412C104K5R5TA7200	
50		.068µF	±10	420	399-4502-1-ND	.77	6.15	12.96	37.03	399-4502-2-ND	5,000	125.69/M	C420C683K5R5TA7200	
50		.1µF	±10	420	399-4491-1-ND	.49	3.89	8.21	23.45	399-4491-2-ND	5,000	79.68/M	C420C104K5R5TA7200	
50		.15µF	±10	430	399-4505-1-ND	.86	7.35	15.25	49.92	—	—	—	C430C154K5R5TA7200	
50		.22µF	±10	430	399-4507-1-ND	1.16	9.68	20.86	71.07	—	—	—	C430C224K5R5TA7200	
50		.33µF	±10	440	399-4526-1-ND	1.27	10.63	22.90	78.02	—	—	—	C440C334K5R5TA7200	
50		.47µF	±10	440	399-4527-1-ND	1.85	15.18	34.26	122.20	399-4527-2-ND	2,500	518.44/M	C440C474K5R5TA7200	
Z5U		100	.01µF	±20	410	399-4453-1-ND	.45	3.53	7.23	18.46	399-4453-2-ND	5,000	59.48/M	C410C103M1U5TA7200
	100	.015µF	±20	410	399-4459-1-ND	.48	3.79	7.99	22.84	399-4459-2-ND	5,000	77.43/M	C410C153M1U5TA7200	
	100	.022µF	±20	410	399-4465-1-ND	.44	3.42	7.23	20.65	—	—	—	C410C223M1U5TA7200	
	100	.033µF	±20	420	399-4499-1-ND	.75	5.95	12.53	35.80	399-4499-2-ND	5,000	121.20/M	C420C333M1U5TA7200	
	100	.047µF	±20	420	399-4501-1-ND	.68	5.38	11.32	32.36	—	—	—	C420C473M1U5TA7200	
	100	.068µF	±20	430	399-4517-1-ND	.90	7.48	15.36	46.92	—	—	—	C430C683M1U5TA7200	
	100	.1µF	±20	430	399-4504-1-ND	.58	4.87	9.99	30.50	—	—	—	C430C104M1U5TA7200	
	100	.15µF	±20	430	399-4506-1-ND	1.09	9.10	18.67	57.03	399-4506-2-ND	2,500	217.70/M	C430C154M1U5TA7200	
	100	.22µF	±20	440	399-4525-1-ND	.99	8.24	16.90	51.61	—	—	—	C440C224M1U5TA7200	
	50	.033µF	±20	410	399-4471-1-ND	.58	4.61	9.45	24.14	399-4471-2-ND	5,000	77.43/M	C410C333M5U5TA7200	
	50	.047µF	±20	410	399-4477-1-ND	.58	4.61	9.45	24.14	399-4477-2-ND	5,000	77.43/M	C410C473M5U5TA7200	
	50	.068µF	±20	410	399-4483-1-ND	.58	4.61	9.45	24.14	399-4483-2-ND	5,000	77.43/M	C410C683M5U5TA7200	
	50	.1µF	±20	410	399-4454-1-ND	.42	3.25	6.67	17.03	399-4454-2-ND	5,000	54.99/M	C410C104M5U5TA7200	
	50	.15µF	±20	410	399-4460-1-ND	.65	5.13	10.81	30.86	399-4460-2-ND	5,000	105.49/M	C410C154M5U5TA7200	
	50	.22µF	±20	410	399-4466-1-ND	.65	5.13	10.81	30.86	399-4466-2-ND	5,000	105.49/M	C410C224M5U5TA7200	
	50	.33µF	±20	412	399-4489-1-ND	.76	6.36	13.07	39.92	399-4489-2-ND	5,000	142.52/M	C412C334M5U5TA7200	
	50	.33µF	±20	420	399-4500-1-ND	.76	6.36	13.07	39.92	399-4500-2-ND	5,000	142.52/M	C420C334M5U5TA7200	
	50	.47µF	±20	430	399-4513-1-ND	.97	8.18	16.98	55.55	399-4513-2-ND	2,500	231.17/M	C430C474M5U5TA7200	
	50	.68µF	±20	430	399-4518-1-ND	.97	8.18	16.98	55.55	399-4518-2-ND	2,500	231.17/M	C430C684M5U5TA7200	
	50	4µF	±20	440	399-4521-1-ND	1.23	10.47	21.73	71.10	399-4521-2-ND	2,500	296.26/M	C440C105M5U5TA7200	

F

Free shipping on orders over \$200 CAD! All prices in Canadian dollars and include duty and brokerage fees.

1-800-344-4539 • www.digikey.ca • 218-681-6674 • Fax: 218-681-3380

(CA2011) 1881