

3M Foil, Electrical, and Specialty Tapes



Please see Digi-Key's website for detailed specifications and diagrams.



Description	Dimensions Width x Length	Digi-Key Part No.	Price Each		3M Part No.
			1	5	
3M Laminating Adhesives					
Adhesive Transfer Tape, 100MP Adhesive, Clear, .005", Dual-lined for Prototyping	8.5" x 8.5"	3M6446-ND	9.12	7.30	F9469PC
Adhesive Transfer Tape, 100MP Adhesive, Clear, .005"	3/8" x 60 yds.	3M9039-ND	26.09	20.88	F9469PC 3/8"X60YD
Adhesive Transfer Tape, 200MP Adhesive, Clear, .005", Dual-lined for Prototyping	8.5" x 8.5"	3M6447-ND	7.44	5.95	468MP
Adhesive Transfer Tape, 200MP Adhesive, Clear, .005"	3/4" x 60 yds.	3M9040-ND	25.45	20.36	468MP 3/4"X60YD
Adhesive Transfer Tape, 300LSE Adhesive, Clear, 6.0 mils	4" x 60 yds.	SCP284-ND	112.79	100.01	9472LE 4"X60YD
Double Coated Tape, 375 Adhesive, Translucent, 7.5 mils	19mm x 50M	3M9042-ND	21.03	16.83	9086 19MMX50M
Double Coated Tape, 375 Adhesive, White, 10.2 mils	19mm x 50M	3M9043-ND	25.22	20.18	9087 19MMX50M
Double Coated Tape, 375 Adhesive, Clear, 8.3 mils	19mm x 50M	3M9044-ND	22.66	18.14	9088 19MMX50M
Double Coated Tape, 200MP Adhesive, Clear, .0057", Dual-lined for Prototyping	8.5" x 8.5"	3M6448-ND	34.37	27.50	9495MP
Double Coated Tape, 300LSE Adhesive, Clear, .0067", Dual-lined for Prototyping	8.5" x 8.5"	3M6449-ND	8.70	6.96	9495LE
Double Coated Tape, 300LSE Adhesive, Clear, .0034"	3/4" x 60 yds.	3M9041-ND	39.93	31.94	9495LE 3/4"X60YD
Double Coated Tape, 300MP Adhesive, Tan, .0055", Dual-lined for Prototyping	8.5" x 8.5"	3M6450-ND	7.01	5.61	9786
Double Coated Tape, 300MP Adhesive, Clear, .0067", Dual-lined for Prototyping	8.5" x 8.5"	3M6451-ND	7.86	6.29	9490LE
Aluminum Foil Tape					
Aluminum Foil Tape, 2.8-mil, Acrylic Adhesive, Thermally Conductive, Heat & Light Reflective	1" x 60 yds.	3M5613-ND	29.79	25.54	425-1"X60YD-BULK
Aluminum Foil Tape, 2.8-mil, Acrylic Adhesive, Thermally Conductive, Heat & Light Reflective	3" x 60 yds.	3M5614-ND	92.06	78.91	425-3"X60YD-BULK
Aluminum Foil Tape, 2.8-mil, Acrylic Adhesive, Thermally Conductive, Heat & Light Reflective	2" x 60 yds.	3M5615-ND	90.70	77.74	427-2"X60YD
Aluminum Foil Tape, 2.0-mil, Silicone Adhesive, Thermally Conductive, Heat & Light Reflective	1" x 60 yds.	3M5617-ND	89.44	76.66	433-1"X60YD
Aluminum Foil Tape, 2.0-mil, Silicone Adhesive, Thermally Conductive, Heat & Light Reflective	2" x 60 yds.	3M5616-ND	178.86	153.31	433-2"X60YD
Aluminum Foil Tape, 2.0-mil, Silicone Adhesive, Thermally Conductive, Heat & Light Reflective, Lined	1" x 60 yds.	3M5632-ND	102.30	87.69	433L-1"X60YD
Aluminum Foil Tape, 2.0-mil, Silicone Adhesive, Thermally Conductive, Heat & Light Reflective, Lined	2" x 60 yds.	3M5631-ND	204.57	175.35	433L-2"X60YD
Aluminum Foil Tape, 5.0-mil, Acrylic Adhesive, Thermally Conductive, Heat and Light Reflective	2" x 60 yds.	3M5633-ND	114.84	98.43	438
Double Coated Tape					
Attachment Tape, .045", Acrylic Plus Adhesive, High Performance, Black, Automotive Grade	1/4" x 20 yds.	3M6411-ND	24.64	—	06386
Attachment Tape, .045", Acrylic Plus Adhesive, High Performance, Black, Automotive Grade	1/2" x 5 yds.	3M6410-ND	13.71	—	06384
Attachment Tape, .045", Acrylic Plus Adhesive, High Performance, Black, Automotive Grade	1/2" x 20 yds.	3M6408-ND	43.05	—	06382
Attachment Tape, .045", Acrylic Plus Adhesive, High Performance, Black, Automotive Grade	7/8" x 20 yds.	3M6409-ND	53.07	—	06383
Attachment Tape, .060", Acrylic Plus Adhesive, High Performance, Black, Automotive Grade	7/8" x 10 yds.	3M6412-ND	38.75	—	06395
Attachment Tape, .090", Acrylic Plus Adhesive, High Performance, Gray, Automotive Grade	1/2" x 10 yds.	3M6413-ND	25.63	—	06394
Double Coated Foam Tape, .125", Pressure Sensitive Acrylic Adhesive, Off-White Urethane Foam	1" x 36 yds.	3M4008-ND	81.38	—	4008 1"
Double Coated Foam Tape, .062", Pressure Sensitive Acrylic Adhesive, Off-White Urethane Foam	1" x 36 yds.	3M40161-ND	54.77	—	4016 1"
Double Coated Foam Tape, .062", Pressure Sensitive Acrylic Adhesive, Neutral Urethane Foam	1" x 36 yds.	3M4026-ND	47.06	—	4026 1"
Double Coated Foam Tape, .125", Pressure Sensitive Acrylic Adhesive, Black Vinyl Foam	1" x 36 yds.	3M44081-ND	113.02	—	4408 1"
Double Coated Foam Tape, .062", Pressure Sensitive Acrylic Adhesive, Black Vinyl Foam	1" x 36 yds.	3M44161B-ND	81.00	—	4416 1" BLACK
Double Coated Foam Tape, .062", Pressure Sensitive Acrylic Adhesive, White Vinyl Foam	1" x 36 yds.	3M44161W-ND	86.82	—	4416 1" WHITE
Double Coated Foam Tape, .045", Pressure Sensitive VHB™ Acrylic Adhesive, Dark Gray	1/2" x 36 yds.	3M462-ND	38.43	32.95	4611 1/2 IN X 36 YD
Double Coated Foam Tape, .020", Pressure Sensitive VHB Acrylic Adhesive, Clear	1" x 72 yds.	3M6463-ND	190.54	163.33	4905-1"X72YD
Double Coated Foam Tape, .020", Pressure Sensitive VHB Acrylic Adhesive, Clear	1/2" x 72 yds.	3M6464-ND	101.85	87.31	4905-1/2"X72YD
Double Coated Foam Tape, .040", Pressure Sensitive VHB Acrylic Adhesive, Clear (small pack)	3/4" x 72 yds.	3M6465-ND	135.82	116.42	4905-3/4"X72YD
Double Coated Foam Tape, .040", Pressure Sensitive VHB Acrylic Adhesive, Clear	1/2" x 36 yds.	3M6466-ND	60.29	51.68	4910-1/2"X36YD
Double Coated Foam Tape, .040", Pressure Sensitive VHB Acrylic Adhesive, Clear	1/2" x 36 yds.	3M6467-ND	53.73	46.06	4910-CLEAR-1/2"X36YD
Double Coated Foam Tape, .040", Pressure Sensitive VHB Acrylic Adhesive, Clear	3/4" x 15 yds.	3M5648-ND	34.33	29.43	4910 3/4"X15YD
Double Coated Foam Tape, .040", Pressure Sensitive VHB Acrylic Adhesive, Clear	1" x 36 yds.	3M5650-ND	89.55	76.76	4910-CLEAR-1"X36YD
Double Coated Foam Tape, .045", Pressure Sensitive VHB Acrylic Adhesive, White Acrylic Foam	1/2" x 36 yds.	3M5625-ND	78.50	67.28	4950-1/2"X36YD-SMPK
Double Coated Foam Tape, .045", Pressure Sensitive VHB Acrylic Adhesive, White Acrylic Foam	3/4" x 36 yds.	3M5626-ND	104.69	89.74	4950-3/4"X36YD-SMPK
Double Coated Foam Tape, .045", Pressure Sensitive VHB Acrylic Adhesive, White Acrylic Foam	1" x 36 yds.	3M5627-ND	130.79	112.11	4950-1"X36YD-SMPK
Double Coated Foam Tape, .045", Pressure Sensitive VHB Modified Acrylic Adhesive, Black	1/2" x 36 yds.	3M6468-ND	64.31	55.13	5952-1/2"X36YD
Double Coated Foam Tape, .045", Pressure Sensitive VHB Modified Acrylic Adhesive, Black	3/4" x 15 yds.	3M5647-ND	34.33	29.43	5952 3/4"X15YD
Double Coated Foam Tape, .045", Pressure Sensitive VHB Modified Acrylic Adhesive, Black	1" x 36 yds.	3M5649-ND	107.20	91.89	5952 1"X36YD
Duct Tape					
Duct Tape Clean Remove, 12.6-mil, Slate Blue Polyethylene Film, Synthetic Rubber Adhesive	1.88" x 60 yds.	3M5630-ND	16.93	14.51	8979-BLUE-48MMX54.8M
Duct Tape Industrial Grade, 10.7-mil, Black Polyethylene Film, Rubber Adhesive	1.88" x 60 yds.	3M6962B-ND	15.97	—	6969 2" BLACK
Duct Tape Industrial Grade, 10.7-mil, Silver Polyethylene Film, Rubber Adhesive	1.88" x 60 yds.	3M6962S-ND	15.97	—	6969 2" SILVER
Electrical Tape - Black					
Vinyl Mastic Pad, All-Weather Grade, 125-mil, Black Vinyl Film, Rubber Mastic	3-1/4" x 4-1/2"	3M11008-ND	4.85	—	2200 (3-1/4"X4-1/2")
Electrical Tape, General Purpose, 7-mil, Black PVC, Flame-Retardant	3/4" x 66'	3M1700-ND	6.80	—	1700 TEM-FLEX
Electrical Tape, Premium Grade, All-Weather, 7-mil, Black PVC, Pressure-Sensitive Adhesive	3/4" x 66'	3M33-A-ND	6.80	—	33- SUPER (3/4"X66')
Electrical Tape, Premium Grade, All-Weather, 8.5-mil, Black PVC, Pressure-Sensitive Adhesive	3/4" x 66'	3M88A-ND	7.63	—	88 SUPER (3/4"X66')
Electrical Color Coding Tape - Colored					
Electrical Color Coding Tape, Red PVC, 7-mil, Pressure-Sensitive Adhesive	3/4" x 66'	3M35-RD-ND	6.31	—	35 RED (3/4"X66')
Electrical Color Coding Tape, Orange PVC, 7-mil, Pressure-Sensitive Adhesive	3/4" x 66'	3M35-OR-ND	6.31	—	35 ORANGE (3/4"X66')
Electrical Color Coding Tape, Yellow PVC, 7-mil, Pressure-Sensitive Adhesive	3/4" x 66'	3M35-YL-ND	6.31	—	35 YELLOW (3/4"X66')
Electrical Color Coding Tape, Green PVC, 7-mil, Pressure-Sensitive Adhesive	3/4" x 66'	3M35-GN-ND	6.31	—	35 GREEN (3/4"X66')
Electrical Color Coding Tape, Blue PVC, 7-mil, Pressure-Sensitive Adhesive	3/4" x 66'	3M35-BL-ND	6.31	—	35 BLUE (3/4"X66')
Electrical Color Coding Tape, Violet PVC, 7-mil, Pressure-Sensitive Adhesive	3/4" x 66'	3M35-VL-ND	6.31	—	35 VIOLET (3/4"X66')
Electrical Color Coding Tape, Gray PVC, 7-mil, Pressure-Sensitive Adhesive	3/4" x 66'	3M35-GY-ND	6.31	—	35 GRAY (3/4"X66')
Electrical Color Coding Tape, White PVC, 7-mil, Pressure-Sensitive Adhesive	3/4" x 66'	3M35-WH-ND	6.31	—	35 WHITE (3/4"X66')
Glass and Aluminum/Glass Cloth Tape					
Glass Cloth Tape, White, 5.4-mil, Silicone Adhesive, High Tensil Strength, General Purpose	1" x 60 yds.	3M5609-ND	86.04	73.75	361-1"X60YD
Glass Cloth Tape, White, 5.4-mil, Silicone Adhesive, High Tensil Strength, General Purpose	2" x 60 yds.	3M5610-ND	172.07	147.49	361-2"X60YD
Aluminum/Glass Cloth Tape, 7.3-mil, Silicone Adhesive, Flame/Tear/Puncture-Resistant	1" x 36 yds.	3M5611-ND	140.57	120.49	363-1"X36YD
Aluminum/Glass Cloth Tape, 7.3-mil, Silicone Adhesive, Flame/Tear/Puncture-Resistant	2" x 36 yds.	3M5612-ND	281.13	240.98	363-2"X36YD
High Temperature Tape					
High Temperature Kapton® Tape, 2.7-mil, Amber Kapton Polyimide Film, Silicone Adhesive	1/2" x 36 yds.	3M541312-ND	29.85	—	5413 1/2"
High Temperature Kapton Tape, 2.7-mil, Amber Kapton Polyimide Film, Silicone Adhesive	3/4" x 36 yds.	3M541334-ND	44.77	—	5413 3/4"
High Temperature Kapton Tape, 2.7-mil, Amber Kapton Polyimide Film, Silicone Adhesive	1" x 36 yds.	3M541310-ND NEW!	64.91	—	5413 AMBER 1 IN X 36 YD
High Temperature Kapton Tape, 2.7-mil, Amber Kapton Polyimide Film, Silicone Adhesive	2" x 36 yds.	3M541320-ND NEW!	129.81	—	5413 AMBER 2 IN X 36 YD
Wave Solder Tape, Low Static, 2.7-mil, Gold Polyimide Film, Silicone Adhesive	1/2" x 36 yds.	3M591912-ND	32.15	—	5419 1/2"
Wave Solder Tape, Low Static, 2.7-mil, Gold Polyimide Film, Silicone Adhesive	3/4" x 36 yds.	3M591934-ND	45.93	—	5419 3/4"
Wave Solder Tape, Low Static, 2.7-mil, Gold Polyimide Film, Silicone Adhesive	1" x 36 yds.	3M541910-ND NEW!	60.02	—	5419 GOLD 1 IN X 36 YD
Wave Solder Tape, Water-Soluble, PVA Film Backing, Water-soluble Synthetic Adhesive	1/2" x 36 yds.	3M541412-ND	30.38	—	5414 1/2"
Wave Solder Tape, Water-Soluble, PVA Film Backing, Water-soluble Synthetic Adhesive	3/4" x 36 yds.	3M541434-ND	52.57	—	5414 3/4"
ScotchCode™ Wire Marker Tape Dispensers					
ScotchCode SDR Wire Marker Tape Dispenser with 0-9 Wire Marker Tapes	—	STD-0-9-ND	47.74	—	STD-0-9
ScotchCode SDR Wire Marker Tape Dispenser with 10 Colored Wire Marker Tapes	—	STD-C-ND	47.74	—	STD-C
ScotchCode SDR Wire Marker Tape Dispenser (no tape included)	—	STD-ND	15.69	—	STD
ScotchCode™ Wire Marker Tape Refills					
"0" ScotchCode SDR Wire Marker Tape, 3-mil, Pressure-Sensitive Adhesive, White with Black #s	0.215" x 96"	SDR-0-ND	3.43	—	SDR-0
"1" ScotchCode SDR Wire Marker Tape, 3-mil, Pressure-Sensitive Adhesive, White with Black #s	0.215" x 96"	SDR-1-ND	3.43	—	SDR-1
"2" ScotchCode SDR Wire Marker Tape, 3-mil, Pressure-Sensitive Adhesive, White with Black #s	0.215" x 96"	SDR-2-ND	3.43	—	SDR-2
"3" ScotchCode SDR Wire Marker Tape, 3-mil, Pressure-Sensitive Adhesive, White with Black #s	0.215" x 96"	SDR-3-ND	3.43	—	SDR-3
"4" ScotchCode SDR Wire Marker Tape, 3-mil, Pressure-Sensitive Adhesive, White with Black #s	0.215" x 96"	SDR-4-ND	3.43	—	SDR-4
"5" ScotchCode SDR Wire Marker Tape, 3-mil, Pressure-Sensitive Adhesive, White with Black #s	0.215" x 96"	SDR-5-ND	3.43	—	SDR-5
"6" ScotchCode SDR Wire Marker Tape, 3-mil, Pressure-Sensitive Adhesive, White with Black #s	0.215" x 96"	SDR-6-ND	3.43	—	SDR-6
"7" ScotchCode SDR Wire Marker Tape, 3-mil, Pressure-Sensitive Adhesive, White with Black #s	0.215" x 96"	SDR-7-ND	3.43	—	SDR-7
"8" ScotchCode SDR Wire Marker Tape, 3-mil, Pressure-Sensitive Adhesive, White with Black #s	0.215" x 96"	SDR-8-ND	3.43	—	SDR-8
"9" ScotchCode SDR Wire Marker Tape, 3-mil, Pressure-Sensitive Adhesive, White with Black #s	0.215" x 96"	SDR-9-ND	3.43	—	SDR-9
Black ScotchCode SDR Wire Marker Tape, 3-mil, Pressure-Sensitive Adhesive	0.215" x 96"	SDR-BK-ND	3.43	—	SDR-BK
Brown ScotchCode SDR Wire Marker Tape, 3-mil, Pressure-Sensitive Adhesive	0.215" x 96"	SDR-BN-ND	3.43	—	SDR-BN
Red ScotchCode SDR Wire Marker Tape, 3-mil, Pressure-Sensitive Adhesive	0.215" x 96"	SDR-RD-ND	3.43	—	SDR-RD
Orange ScotchCode SDR Wire Marker Tape, 3-mil, Pressure-Sensitive Adhesive	0.215" x 96"	SDR-OR-ND	3.43	—	SDR-OR
Yellow ScotchCode SDR Wire Marker Tape, 3-mil, Pressure-Sensitive Adhesive	0.215" x 96"	SDR-YL-ND	3.43	—	SDR-YL
Green ScotchCode SDR Wire Marker Tape, 3-mil, Pressure-Sensitive Adhesive	0.215" x 96"	SDR-GN-ND	3.43	—	SDR-GN
Blue ScotchCode SDR Wire Marker Tape, 3-mil, Pressure-Sensitive Adhesive	0.215" x 96"	SDR-BL-ND	3.43	—	SDR-BL
Violet ScotchCode SDR Wire Marker Tape, 3-mil, Pressure-Sensitive Adhesive	0.215" x 96"	SDR-VL-ND	3.43	—	SDR-VL

† Recommended for wheel floors or other less demanding applications due to a narrower width.

(Continued)

Free shipping on orders over \$200 CAD! All prices in Canadian dollars and include duty and brokerage fees.

1-800-344-4539 • www.digikey.ca • 218-681-6674 • Fax: 218-681-3380

(CA2011) 2493