




**Threaded Standoffs**

- **Brass:** ASTM-B16
- **Plating:** Zinc (ASTM B633)
- **Aluminum:** QQ-A-225/3, Alloy 2011-T3
- **Plating:** Clear Iridite (Mil-C-5541)



Note: Spacers over 1.000 long are tapped .375 deep each end.

Thread	O.D.	"L" Length (Inch)	Hex Thread Part No.	Pricing		Round Thread Part No.	Pricing		
				10	100		10	100	
<b>Aluminum</b>									
2-56	.156	.187	1797AK-ND	8.49	77.32	1801AK-ND	7.52	71.99	
	.156	.250	1797BK-ND	9.12	82.66	1801BK-ND	7.43	71.20	
	.156	.312	1797CK-ND	9.49	86.05	1801CK-ND	8.05	77.32	
	.156	.375	1797DK-ND	9.21	88.65	1801DK-ND	9.88	89.74	
	.187	.250	1891K-ND	4.24	34.90	2025K-ND	4.21	32.48	
4-40	.187	.375	1892K-ND	4.98	40.24	2026K-ND	4.85	38.60	
	.187	.500	1893K-ND	5.48	47.02	2027K-ND	5.34	46.23	
	.187	.625	1894K-ND	5.63	51.69	2028K-ND	5.52	49.39	
	.187	.750	1895K-ND	6.24	57.14	2029K-ND	6.16	53.20	
	.187	.875	1896K-ND	6.87	62.84	2030K-ND	6.76	59.74	
	.187	1.000	1897K-ND	9.15	82.89	2031K-ND	9.15	82.89	
	.250	.250	2201K-ND	4.10	33.58	3478K-ND	3.73	29.75	
	.250	.375	2202K-ND	4.58	37.51	3479K-ND	4.11	33.58	
	.250	.500	2203K-ND	5.08	41.03	3480K-ND	4.61	36.54	
	.250	.625	1808K-ND	5.48	45.69	1839K-ND	5.02	40.66	
	.250	.750	2204K-ND	5.41	49.08	3481K-ND	5.63	45.69	
	.250	.875	1809K-ND	7.04	67.51	1846K-ND	7.37	67.21	
	.250	1.000	2205K-ND	8.35	75.69	3482K-ND	8.15	74.29	
	.250	1.500	2206K-ND	14.22	128.82	3483K-ND	13.76	124.65	
	.250	2.000	2207K-ND	15.44	148.21	3484K-ND	14.99	144.28	
	6-32	.250	.250	2208K-ND	4.10	33.58	3485K-ND	3.73	29.75
		.250	.375	2209K-ND	4.58	37.51	3486K-ND	4.11	33.58
		.250	.500	2210K-ND	5.08	41.03	3487K-ND	4.61	36.54
		.250	.625	1813K-ND	5.78	45.93	1847K-ND	5.49	53.20
		.250	.750	2211K-ND	5.41	49.08	3488K-ND	5.63	45.69
.250		.875	1816K-ND	5.76	53.87	1848K-ND	5.42	49.39	
.250		1.000	2212K-ND	8.35	75.69	3489K-ND	8.15	74.29	
.250		1.250	1818K-ND	12.59	114.83	1853K-ND	12.33	111.92	
.250		1.500	2213K-ND	14.22	128.82	3490K-ND	13.76	124.65	
.250		1.750	1819K-ND	14.85	134.58	1855K-ND	13.74	132.10	
.250		2.000	2214K-ND	15.44	148.21	3491K-ND	14.99	144.28	
.250		2.250	1820K-ND	17.14	165.00	1856K-ND	17.73	161.19	
.250		2.500	1825K-ND	18.74	180.10	1857K-ND	18.29	176.58	
.250		.250	2215K-ND	4.10	33.58	3492K-ND	3.73	29.75	
.250		.375	2216K-ND	4.58	37.51	3493K-ND	4.11	33.58	
.250		.500	2217K-ND	5.08	41.03	3494K-ND	4.61	36.54	
.250		.625	1827K-ND	5.60	53.87	1858K-ND	5.02	40.66	
.250		.750	2218K-ND	6.04	57.93	3495K-ND	5.63	45.69	
.250		.875	1828K-ND	7.51	71.99	1859K-ND	5.45	48.84	
.250		1.000	2219K-ND	8.35	75.69	3496K-ND	8.15	74.29	
.250	1.500	2220K-ND	14.22	128.82	3497K-ND	15.04	142.22		
.250	2.000	2221K-ND	15.44	148.21	3498K-ND	14.99	144.28		
.375	.375	1926AK-ND	7.34	67.21	2315AK-ND	10.86	106.71		
.375	.500	1926BK-ND	7.70	69.81	2315BK-ND	11.49	110.16		
.375	.625	1926CK-ND	9.48	90.84	2315CK-ND	13.14	119.55		
.375	.750	1926DK-ND	11.69	106.47	2315DK-ND	14.11	128.29		
.375	1.000	1926EK-ND	13.35	129.25	2315EK-ND	15.82	152.83		
<b>Brass</b>									
2-56	.156	.187	1798AK-ND	9.74	93.57	1802AK-ND	9.20	88.22	
	.156	.250	1798BK-ND	12.35	112.23	1802BK-ND	10.50	95.74	
	.156	.312	1798CK-ND	13.98	134.58	1802CK-ND	10.90	98.83	
	.156	.375	1798DK-ND	16.00	144.95	1802DK-ND	10.90	98.83	
	.187	.250	1450K-ND	5.88	47.21	1547K-ND	5.91	46.23	
4-40	.187	.375	1803K-ND	6.88	55.75	1864K-ND	6.80	53.33	
	.187	.500	1656K-ND	7.08	65.20	1657K-ND	7.00	63.57	
	.187	.625	1804K-ND	8.61	77.74	1865K-ND	8.57	76.35	
	.187	.750	1656AK-ND	9.72	87.56	1657AK-ND	9.46	86.05	
	.187	.875	1805K-ND	11.93	109.38	1866K-ND	11.91	106.10	
	.187	1.000	1656BK-ND	12.53	114.53	1657BK-ND	12.42	112.65	
	.250	.250	1450AK-ND	5.49	43.93	1547AK-ND	6.33	60.96	
	.250	.375	1450BK-ND	6.88	54.29	1547BK-ND	7.41	71.45	
	.250	.500	1450CK-ND	6.96	64.89	1547CK-ND	9.03	86.71	
	.250	.625	1829K-ND	9.40	86.29	1867K-ND	10.84	98.83	
	.250	.750	1450DK-ND	10.76	100.89	1547DK-ND	12.13	110.71	
	.250	.875	1830K-ND	11.45	105.56	1876K-ND	13.68	123.92	
	.250	1.000	1450EK-ND	27.68	111.08	1547EK-ND	12.56	112.14	
	.250	1.500	1831K-ND	26.19	252.26	1877K-ND	25.59	241.90	
	.250	2.000	1832K-ND	26.84	258.39	1878K-ND	30.99	291.90	
	.250	.250	1451AK-ND	5.49	43.93	1548AK-ND	5.48	43.93	
	.250	.375	1451BK-ND	6.88	54.29	1548BK-ND	6.00	49.39	
	.250	.500	1451CK-ND	6.96	64.89	1548CK-ND	7.00	63.57	
	.250	.625	1451DK-ND	9.40	86.29	1548DK-ND	7.64	71.86	
	.250	.750	1451EK-ND	10.76	100.89	1548EK-ND	9.02	87.81	
.250	.875	1833K-ND	11.45	105.56	1879K-ND	10.73	100.89		
.250	1.000	1635K-ND	12.11	110.29	1548FK-ND	11.15	102.83		
.250	1.250	1636K-ND	18.02	173.00	1881K-ND	18.78	170.46		
.250	1.500	1637K-ND	22.13	200.70	1882K-ND	25.42	244.87		
.250	1.750	1638K-ND	26.53	255.66	1883K-ND	25.74	248.02		
.250	2.000	1639K-ND	26.84	258.39	1884K-ND	25.97	249.23		
.250	2.250	1642K-ND	27.39	264.26	1885K-ND	26.64	256.63		
.250	2.500	1643K-ND	28.18	271.60	1886K-ND	27.39	264.26		
.250	.250	1474AK-ND	5.49	43.93	1692AK-ND	7.57	72.29		
.250	.375	1474BK-ND	6.88	54.29	1692BK-ND	8.44	76.78		
.250	.500	1474CK-ND	6.96	64.89	1692CK-ND	10.74	97.62		
.250	.625	1834K-ND	9.40	86.29	1887K-ND	12.29	111.55		
.250	.750	1474DK-ND	10.76	100.89	1692DK-ND	14.55	132.10		
.250	.875	1836K-ND	12.31	111.37	1888K-ND	13.93	126.52		
.250	1.000	1474EK-ND	12.11	110.29	1692EK-ND	14.12	135.92		

Thread	O.D.	"L" Length (Inch)	Hex Thread Part No.	Pricing		Round Thread Part No.	Pricing	
				10	100		10	100
8-32	.250	1.500	1837K-ND	26.19	252.26	1889K-ND	25.42	244.87
	.250	2.000	1838K-ND	26.84	258.39	1890K-ND	27.30	263.29
	.375	.375	1452AK-ND	14.17	133.74	1549AK-ND	15.81	143.31
	.375	.500	1452BK-ND	14.18	136.34	1549BK-ND	17.06	154.77
	.375	.625	1452CK-ND	21.06	199.36	1549CK-ND	20.49	194.03
	.375	.750	1452DK-ND	19.93	188.15	1549DK-ND	22.47	212.14
	.375	1.000	1452EK-ND	25.51	246.27	1549EK-ND	28.53	269.96

◆ **RoHS Compliant**

**1/4" Hex Threaded Standoff Kit**

Aluminum - Assortment of 1500 pieces in 1/4", 3/8", 1/2", 3/4" and 1" lengths with thread sizes of 4-40, 6-32 and 8-32. 100 pieces of each size complete with cabinet.

STH-22KIT-ND ..... \$930.36

**NEW! 400 Piece Threaded Standoff Kits**


Assortment of 400 total standoffs. Female-Female standoffs and Male-Female standoffs both Aluminum and Nylon, with lengths of .250, .500, .750 and 1.000. 25 pieces of each size. Complete with cabinet and 25 machine screws with matching thread.

STR-440K-ND (STR-440) 4-40 Threaded Standoffs ..... \$207.21  
 STR-632K-ND (STR-632) 6-32 Threaded Standoffs ..... \$207.21  
 STR-832K-ND (STR-832) 8-32 Threaded Standoffs ..... \$207.21

◆ **RoHS Compliant**

**Male/Female .250" Hex Threaded Standoffs**

- **Brass:** ASTM-B16
- **Plating:** Nickel (QQ-N-290)



- **Aluminum:** QQ-C-225/3
- **Plating:** Clear Iridite (Mil-C-5541)

Length (Inch)	4-40 Thread Part No.	Pricing		6-32 Thread Part No.	Pricing		8-32 Thread Part No.	Pricing	
		10	100		10	100		10	100
<b>Aluminum</b>									
.250	8714K-ND	4.75	45.69	8717K-ND	5.27	51.02	—	—	—
.375	8400K-ND	5.40	52.11	8413K-ND	5.59	53.75	8426K-ND	7.40	70.90
.500	8401K-ND	7.52	71.99	8414K-ND	5.66	54.41	8427K-ND	7.52	71.99
.625	8402K-ND	8.09	77.74	8415K-ND	7.14	68.47	8428K-ND	8.09	77.74
.750	8403K-ND	8.23	78.83	8416K-ND	7.64	69.56	8429K-ND	8.61	82.66
.875	8404K-ND	8.93	85.74	8417K-ND	8.33	75.69	8430K-ND	10.17	92.16
1.000	8405K-ND	9.44	90.54	8418K-ND	8.23	78.83	8431K-ND	10.14	97.20
1.125	8406K-ND	11.57	111.25	8419K-ND	8.48	81.56	8432K-ND	14.48	131.44
1.250	8407K-ND	12.42	112.65	8420K-ND	9.06	86.71	8433K-ND	14.99	136.22
1.375	8408K-ND	14.55	131.98	8421K-ND	10.92	99.02	8434K-ND	16.18	147.00
1.500	8409K-ND	14.89	135.13	8422K-ND	11.76	112.89	8435K-ND	16.35	148.21