



Fig.	Dimensions (mm)			Fits Fan Size - mm	Center Dim. - mm	No. of Rings	Material	Digi-Key Part No.	Price Each			Qualtek Part No.
	A	B	Thick						1	10	25	
7	124.46	113.28	5.92	127 Dia.	14 open	9	Metal	CR200-ND	2.65	2.43	2.04	08150
	115.57	104.78	3.75	120 Dia.	14.2 open	8	Metal	Q342-ND	1.03	.95	.79	08129
	115.57	104.78	5.66	120 Dia.	14.2 open	8	Metal	Q357-ND	2.46	2.25	1.89	08130
	76.2	71.37	4.95	80 Dia.	14.2 open	5	Metal	Q358-ND	.86	.79	.66	08132
	115.06	104.65	6.60	120 Sq.	25.4 solid	6	Plastic	CR280-ND	.98	.90	.76	09120-G
9	115.06	104.65	2.54	120 Sq.	32 solid	5	Plastic	CR315-ND	.98	.90	.76	09122-G
10	115.06	104.65	6.60	120 Sq.	45 solid	5	Plastic	CR281-ND	1.11	1.02	.85	09121-G
11	117.35	104.78	5.21	120 Sq.	33 solid	7	Metal	CR210-ND	1.82	1.67	1.40	08141
12	89.41	82.42	4.95	92 Sq.	14 open	6	Metal	CR220-ND	.81	.75	.63	08174
	53.10	50.04	4.95	60 Sq.	14 open	4	Metal	CR221-ND	.71	.66	.55	08147
	222.25	173.99	6.35	254 Dia.	76.2 solid	9	Metal	CR223-ND	4.20	3.85	3.22	08127
	115.6	104.8	5.66	120 Dia.	17.5 open	8	Metal	CR224-ND	.95	.88	.74	08170
	76.20	71.4	4.95	80 Dia.	17.4 open	5	Metal	CR229-ND	.74	.68	.57	08172
	32.00	29.21	4.80	40 Dia.	15.875 open	2	Metal	CR230-ND	.68	.63	.53	08149
	24.00	21.8	4.80	30 Sq.	9 open	2	Metal	CR377-ND	.81	.75	.63	08346
	29.00	27.00	4.00	35 Sq.	14.2 open	2	Metal	CR378-ND	.83	.76	.64	08347
	41.06	40.00	4.80	50 Sq.	14.2 open	3	Metal	CR379-ND	1.08	.99	.83	08248
	42.00	41.00	4.80	52 Sq.	14.2 open	3	Metal	CR388-ND	.74	.68	.57	08148
13	39.88	32.00	4.83	40 Sq.	12 open	3	Plastic	CR285-ND	.45	.41	.35	09150-G
	59.94	50.04	6.35	60 Sq.	5 solid	3	Plastic	CR225-ND	.54	.49	.42	09250-G
14	80.01	71.37	6.35	80 Sq.	15 solid	3	Plastic	CR226-ND	.73	.67	.56	09325-G
	79.76	71.37	3.05	80 Sq.	32 solid	3	Plastic	CR282-ND	.55	.51	.43	09080-G
	91.95	82.55	6.35	92 Sq.	31.5 solid	4	Plastic	CR227-ND	.80	.73	.61	09362-G
	118.11	104.65	7.11	120 Sq.	25 solid	6	Plastic	CR228-ND	1.09	1.00	.84	09450-G
16	24.2	34.2	3.0	25 Sq.	104 open	2	Metal	CR181-ND	.56	.52	.44	08245
18	60.0	50.0	7.0	60 Sq.	21.0 solid	3	Plastic	CR190-ND	.88	.81	.68	09252-G
19	151	172	7.0	151 Sq.	50 solid	8	Plastic	CR191-ND	2.61	2.40	2.01	09651-G
20	162.05	154.43	6.45	150 Dia.	16.31 open	10	Metal	Q341-ND	2.11	1.94	1.62	08126

Fig.	Description	Dimensions (mm)		Fits Fan Size - mm	Digi-Key Part No.	Price Each			Qualtek Part No.
		A	B			1	10	25	
Filters and Filter Accessories									
13	Filter Guard Assembly (30 PPI)	39.88	32.00	40 Sq.	CR286-ND	1.83	1.67	1.40	09150-F/30
13	Filter Guard Assembly (45 PPI)	39.88	32.00	40 Sq.	CR287-ND	1.83	1.67	1.40	09150-F/45
	Replacement Filter Element (30 PPI) - Pkg. of 5	—	—	40 Sq.	CR324-ND	1.53	1.40	1.17	09150-M/30
	Replacement Filter Element (45 PPI) - Pkg. of 5	—	—	40 Sq.	CR325-ND	1.53	1.40	1.17	09150-M/45
13	Filter Guard Assembly (30 PPI)	59.94	50.04	60 Sq.	CR283-ND	1.96	1.80	1.51	09250-F/30
13	Filter Guard Assembly (45 PPI)	59.94	50.04	60 Sq.	CR284-ND	1.96	1.80	1.51	09250-F/45
	Replacement Filter Element (30 PPI) - Pkg. of 5	—	—	60 Sq.	CR326-ND	1.59	1.46	1.23	09250-M/30
	Replacement Filter Element (45 PPI) - Pkg. of 5	—	—	60 Sq.	CR327-ND	1.59	1.46	1.23	09250-M/45
14	Filter Guard Assembly (30 PPI)	83.57	71.37	80 Sq.	CR212-ND	2.08	1.90	1.59	09325-F/30
14	Filter Guard Assembly (45 PPI)	83.57	71.37	80 Sq.	CR214-ND	2.08	1.90	1.59	09325-F/45
	Replacement Filter Element (30 PPI) - Pkg. of 5	—	—	80 Sq.	CR213-ND	1.74	1.60	1.34	09325-M/30
	Replacement Filter Element (45 PPI) - Pkg. of 5	—	—	80 Sq.	CR215-ND	1.74	1.60	1.34	09325-M/45
14	Filter Guard Assembly (30 PPI)	96.52	82.55	92 Sq.	CR328-ND	2.38	2.19	1.83	09362-F/30
14	Filter Guard Assembly (45 PPI)	96.52	82.55	92 Sq.	CR329-ND	2.38	2.19	1.83	09362-F/45
	Replacement Filter Element (30 PPI) - Pkg. of 5	—	—	92 Sq.	CR330-ND	1.84	1.69	1.41	09362-M/30
	Replacement Filter Element (45 PPI) - Pkg. of 5	—	—	92 Sq.	CR331-ND	1.84	1.69	1.41	09362-M/45
14	Filter Guard Assembly (30 PPI)	123.7	104.9	119 & 120 Square	CR216-ND	2.48	2.27	1.90	09450-F/30
14	Filter Guard Assembly (45 PPI)	123.7	104.9	119 & 120 Square	CR218-ND	2.48	2.27	1.90	09450-F/45
	Replacement Filter Element (30 PPI) - Pkg. of 5	—	—	119 & 120 Square	CR217-ND	2.23	2.05	1.71	09450-M/30
	Replacement Filter Element (45 PPI) - Pkg. of 5	—	—	119 & 120 Square	CR219-ND	2.23	2.05	1.71	09450-M/45
15	Filter/Screen, Stainless Steel (Washable)	64.26	49.6	60 Sq.	CR373-ND	3.48	3.19	2.67	06250-SS
	Filter/Screen, Aluminum (Washable)	83.82	71.37	80 Sq.	CR233-ND	2.11	1.93	1.62	06325-M
	Filter/Screen, Stainless Steel (Washable)	83.82	71.37	80 Sq.	CR374-ND	3.95	3.62	3.03	06325-SS
	Filter/Screen, Aluminum (Washable)	91.95	82.42	92 Sq.	CR375-ND	2.27	2.08	1.74	06362-M
	Filter/Screen, Stainless Steel (Washable)	91.95	82.42	92 Sq.	CR375-ND	4.33	3.97	3.32	06362-SS
	Filter/Screen, Aluminum (Washable)	118.87	104.77	120 Sq.	CR235-ND	2.69	2.47	2.07	06450-M
15	Filter/Screen, Stainless Steel (Washable)	118.87	104.77	120 Sq.	CR376-ND	5.53	5.07	4.24	06450-SS
	Filter/Screen, Anodized-Black (Washable)	83.82	71.37	80 Sq.	Q343-ND	2.11	1.93	1.62	06325-B
	Filter/Screen, Anodized-Black (Washable)	118.5	104.77	120 Sq.	Q344-ND	2.69	2.47	2.07	06450-B
17	Finger Guard Assembly, Plastic (30 PPI)	176.0	161.5	150 Sq.	CR183-ND	3.36	3.08	2.58	09650-F/30
	Finger Guard Assembly, Plastic (45 PPI)	176.0	161.5	150 Sq.	CR185-ND	3.36	3.08	2.58	09650-F/45
	Finger Guard Assembly, Plastic (100 PPI)	176.0	161.5	150 Sq.	CR189-ND	3.65	3.35	2.80	09650-F/100
Plug Cord Sets - SPT-1 (18/2)									
21A	Straight On Plug and Cord - 24" (60.96cm)			Fits all Diplomat, Falcon, Maltese, Major, Patriot, Tarzan, Caravel, and Biscuit model fans with Terminal Connections	CR197-ND	1.54	1.41	1.18	07100-24
	Straight On Plug and Cord - 36" (91.44cm)				CR198-ND	1.87	1.72	1.44	07100-36
	Straight On Plug and Cord - 50" (127.00cm)				CR199-ND	2.31	2.12	1.77	07100-50
21B	Straight On Plug and Cord - 24" (60.96cm)			Fits all AC Fans with Terminal Connection Type	CR361-ND	2.39	2.19	1.83	07100-SP024
	Straight On Plug and Cord - 36" (91.44cm)				CR362-ND	2.71	2.49	2.08	07100-SP036
	Straight On Plug and Cord - 72" (182.88cm)				CR363-ND	3.86	3.54	2.96	07100-SP072
22A	45° Angle Plug and Cord - 24" (60.96cm)			Fits all AC Fans with Terminal Connection Type	CR318-ND	1.64	1.50	1.25	07145-24
	45° Angle Plug and Cord - 36" (91.44cm)				CR319-ND	2.00	1.83	1.54	07145-36
	45° Angle Plug and Cord - 72" (182.88cm)				CR365-ND	2.71	2.49	2.08	07145-SP036
22B	45° Angle Plug and Cord - 36" (91.44cm)			Fits all AC Fans with Terminal Connection Type	CR366-ND	3.86	3.54	2.96	07145-SP072
	90° Angle Plug and Cord - 12" (30.48cm)				CR320-ND	1.31	1.21	1.02	07190-12
	90° Angle Plug and Cord - 24" (60.96cm)				CR321-ND	1.64	1.50	1.25	07190-24
23A	90° Angle Plug and Cord - 36" (91.44cm)			Fits all AC Fans with Terminal Connection Type	CR322-ND	2.00	1.83	1.54	07190-36
	90° Angle Plug and Cord - 24" (60.96cm)				CR367-ND	2.39	2.19	1.83	07190-SP024
	90° Angle Plug and Cord - 36" (91.44cm)				CR368-ND	2.71	2.49	2.08	07190-SP036
23B	90° Angle Plug and Cord - 72" (182.88cm)			Fits all AC Fans with Terminal Connection Type	CR369-ND	3.86	3.54	2.96	07190-SP072
	90° Angle T-Style Plug and Cord - 12" (30.48cm)				CR323-ND	1.31	1.21	1.02	07199-12
	90° Angle T-Style Plug and Cord - 24" (60.96cm)				CR170-ND	1.54	1.41	1.18	07199-24
24A	90° Angle T-Style Plug and Cord - 36" (91.44cm)			Fits all AC Fans with Terminal Connection Type	CR175-ND	1.87	1.72	1.44	07199-36
	90° Angle T-Style Plug and Cord - 72" (182.88cm)				CR337-ND	3.19	2.93	2.45	07199-72
	90° Angle T-Style Plug and Cord - 96" (243.84cm)				CR338-ND	3.99	3.65	3.06	07199-96
	90° Angle T-Style Plug and Cord - 36" (91.44cm)				CR371-ND	2.71	2.49	2.08	07199-SP036
24B	90° Angle T-Style Plug and Cord - 72" (182.88cm)				CR372-ND	3.86	3.54	2.96	07199-SP072

Free shipping on orders over \$200 CAD! All prices in Canadian dollars and include duty and brokerage fees.

1-800-344-4539 • www.digikey.ca • 218-681-6674 • Fax: 218-681-3380

(CA2011) 2595