

STMicroelectronics		Digi-Reel® (Cont.)		AMPLIFIERS AND LINEAR RoHS Compliant Parts Available		
STMicroelectronics Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*		
				1	10	100
TS9741YPT	497-10271-2-ND	Output, R/R Low Noise Op Amp*	14-TSSOP	1091.09/2,500		
TS9821YDWT	497-10272-1-ND	Dual Bipolar Op Amp*	8-SOIC	1.63 1.48 1.19		
TS9821YDWT	497-10272-2-ND	Dual Bipolar Op Amp*	8-SOIC	1775.77/2,500		
TS1851AIDT	497-4530-1-ND	1.8V, In/Out, R/R, Low Power Op Amp	8-SOIC	1.35 1.16 .95		
TS1851AIDT	497-4530-2-ND	1.8V, In/Out, R/R, Low Power Op Amp	8-SOIC	1389.39/2,500		
TS1851AILT	497-4531-1-ND	1.8V, In/Out, R/R, Low Power Op Amp	SOT-23-5	1.65 1.42 1.16		
TS1851AILT	497-4531-2-ND	1.8V, In/Out, R/R, Low Power Op Amp	SOT-23-5	1907.51/3,000		
TS1851ID	497-2231-5-ND	1.8V, In/Out, R/R, Low Power Op Amp	8-SOIC	1.17 1.06 .85		
TS1851IDT	497-2231-1-ND	1.8V, In/Out, R/R, Low Power Op Amp	8-SOIC	1.62 1.39 1.14		
TS1851IDT	497-2231-2-ND	1.8V, In/Out, R/R, Low Power Op Amp	8-SOIC	1561.56/2,500		
TS1851ILT	497-5429-2-ND	1.8V, In/Out, R/R, Low Power Op Amp*	SOT-23-5	1.62 1.39 1.14		
TS1851ILT	497-5429-3-ND	1.8V, In/Out, R/R, Low Power Op Amp*	SOT-23-5	1873.87/3,000		
TS1852AIDT	497-4533-1-ND	1.8V, Dual, In/Out, R/R, LP Op Amp	8-MSOP	1.83 1.57 1.28		
TS1852AIDT	497-4533-2-ND	1.8V, Dual, In/Out, R/R, LP Op Amp	8-MSOP	2156.15/2,500		
TS1852AIDT	497-8070-1-ND	1.8V, Dual, In/Out, R/R, LP Op Amp*	8-TSSOP	2.23 1.92 1.57		
TS1852AIDT	497-8070-2-ND	1.8V, Dual, In/Out, R/R, LP Op Amp*	8-TSSOP	3449.85/4,000		
TS1852AIST	497-4443-1-ND	1.8V, Dual, In/Out, R/R, LP Op Amp	8-MSOP	1.83 1.57 1.28		
TS1852AIST	497-4443-2-ND	1.8V, Dual, In/Out, R/R, LP Op Amp	8-MSOP	3017.41/4,000		
TS1852ID	497-2232-5-ND	1.8V, Dual, In/Out, R/R, LP Op Amp	8-MSOP	1.67 1.51 1.22		
TS1852IDT	497-2232-1-ND	1.8V, Dual, In/Out, R/R, LP Op Amp	8-MSOP	1.88 1.62 1.32		
TS1852IDT	497-2232-2-ND	1.8V, Dual, In/Out, R/R, LP Op Amp	8-MSOP	1815.81/2,500		
TS1852IPT	497-8071-1-ND	1.8V, Dual, In/Out, R/R, LP Op Amp*	8-TSSOP	1.36 1.23 .99		
TS1852IPT	497-8071-2-ND	1.8V, Dual, In/Out, R/R, LP Op Amp*	8-TSSOP	2905.30/4,000		
TS1854AIDT	497-4535-1-ND	1.8V, Quad, In/Out, R/R, LP Op Amp	14-SOIC	2.65 2.27 1.86		
TS1854AIDT	497-4535-2-ND	1.8V, Quad, In/Out, R/R, LP Op Amp	14-SOIC	2554.55/2,500		
TS1854ID	497-2234-5-ND	1.8V, Quad, In/Out, R/R, LP Op Amp	14-SOIC	1.91 1.73 1.39		
TS1854IDT	497-2234-1-ND	1.8V, Quad, In/Out, R/R, LP Op Amp	14-SOIC	2.65 2.27 1.86		
TS1854IDT	497-2234-2-ND	1.8V, Quad, In/Out, R/R, LP Op Amp	14-SOIC	2554.55/2,500		
TS1854IPT	497-5430-1-ND	1.8V, Quad, In/Out, R/R, LP Op Amp*	14-TSSOP	2.65 2.27 1.86		
TS1854IPT	497-5430-2-ND	1.8V, Quad, In/Out, R/R, LP Op Amp*	14-TSSOP	2554.55/2,500		
TS1871AIDT	497-4537-1-ND	1.8V, In/Out, R/R, LP Op Amp	8-SOIC	2.16 1.86 1.52		
TS1871AIDT	497-4537-2-ND	1.8V, In/Out, R/R, LP Op Amp	8-SOIC	2232.23/2,500		
TS1871AILT	497-4538-1-ND	1.8V, In/Out, R/R, LP Op Amp	SOT-23-5	2.16 1.86 1.52		
TS1871AILT	497-4538-2-ND	1.8V, In/Out, R/R, LP Op Amp	SOT-23-5	2678.68/3,000		
TS1871AILT	497-10234-1-ND	1.8V, In/Out, R/R, LP Op Amp*	SOT-23-5	1.35 1.20 .95		
TS1871AILT	497-10234-2-ND	1.8V, In/Out, R/R, LP Op Amp*	SOT-23-5	1624.02/3,000		
TS1871ID	497-2236-5-ND	1.8V, In/Out, R/R, LP Op Amp	8-SOIC	1.58 1.43 1.15		
TS1871IDT	497-4539-1-ND	1.8V, In/Out, R/R, LP Op Amp	8-SOIC	1.78 1.53 1.25		
TS1871IDT	497-4539-2-ND	1.8V, In/Out, R/R, LP Op Amp	8-SOIC	1835.83/2,500		
TS1871ILT	497-2237-1-ND	1.8V, In/Out, R/R, LP Op Amp	SOT-23-5	1.78 1.53 1.25		
TS1871ILT	497-2237-2-ND	1.8V, In/Out, R/R, LP Op Amp	SOT-23-5	2520.12/3,000		
TS1871VILT	497-10235-1-ND	1.8V, In/Out, R/R, LP Op Amp*	SOT-23-5	1.21 1.07 .85		
TS1871VILT	497-10235-2-ND	1.8V, In/Out, R/R, LP Op Amp*	SOT-23-5	1448.65/3,000		
TS1872AIDT	497-4540-1-ND	1.8V, Dual, In/Out, R/R, LP Op Amp	8-MSOP	2.35 2.02 1.65		
TS1872AIDT	497-4540-2-ND	1.8V, Dual, In/Out, R/R, LP Op Amp	8-MSOP	2270.27/2,500		
TS1872AIDT	497-10236-1-ND	1.8V, Dual, In/Out, R/R, LP Op Amp*	SOT-23-5	1.35 1.23 .99		
TS1872AIDT	497-10236-2-ND	1.8V, Dual, In/Out, R/R, LP Op Amp*	SOT-23-5	1475.47/2,500		
TS1872ID	497-2238-5-ND	1.8V, Dual, In/Out, R/R, LP Op Amp	8-MSOP	1.58 1.43 1.15		
TS1872IDT	497-2238-1-ND	1.8V, Dual, In/Out, R/R, LP Op Amp	8-MSOP	1.90 1.63 1.33		
TS1872IDT	497-2238-2-ND	1.8V, Dual, In/Out, R/R, LP Op Amp	8-MSOP	1959.96/2,500		
TS1872IPT	497-8072-5-ND	1.8V, Dual, In/Out, R/R, LP Op Amp*	8-Dip	1.60 1.45 1.17		
TS1872IPT	497-8072-1-ND	1.8V, Dual, In/Out, R/R, LP Op Amp*	8-TSSOP	2.33 2.00 1.63		
TS1872IPT	497-8072-2-ND	1.8V, Dual, In/Out, R/R, LP Op Amp*	8-TSSOP	3900.79/4,000		
TS1872IST	497-8073-1-ND	1.8V, Dual, In/Out, R/R, LP Op Amp*	8-MSOP	2.33 2.00 1.63		
TS1872IST	497-8073-2-ND	1.8V, Dual, In/Out, R/R, LP Op Amp*	8-MSOP	3900.79/4,000		
TS1872YDT	497-10237-1-ND	1.8V, Dual, In/Out, R/R, LP Op Amp*	8-SOIC	1.39 1.23 .97		
TS1872YDT	497-10237-2-ND	1.8V, Dual, In/Out, R/R, LP Op Amp*	8-SOIC	1385.38/2,500		
TS1874AIDT	497-4542-1-ND	1.8V, Quad, In/Out, R/R, LP Op Amp	14-SOIC	2.68 2.42 1.97		
TS1874AIDT	497-4542-2-ND	1.8V, Quad, In/Out, R/R, LP Op Amp	14-SOIC	2225.22/2,500		
TS1874AIDT	497-10238-1-ND	1.8V, Quad, In/Out, R/R, LP Op Amp*	14-SOIC	1.51 1.37 1.10		
TS1874AIDT	497-10238-2-ND	1.8V, Quad, In/Out, R/R, LP Op Amp*	14-SOIC	1645.64/2,500		
TS1874AIDT	497-10239-1-ND	1.8V, Quad, In/Out, R/R, LP Op Amp*	14-TSSOP	1.51 1.37 1.10		
TS1874AIDT	497-10239-2-ND	1.8V, Quad, In/Out, R/R, LP Op Amp*	14-TSSOP	1645.64/2,500		
TS1874ID	497-2240-5-ND	1.8V, Quad, In/Out, R/R, LP Op Amp	14-SOIC	1.89 1.69 1.39		
TS1874IDT	497-2240-1-ND	1.8V, Quad, In/Out, R/R, LP Op Amp	14-SOIC	2.03 1.82 1.49		
TS1874IDT	497-2240-2-ND	1.8V, Quad, In/Out, R/R, LP Op Amp	14-SOIC	2304.43/2,500		
TS1874IPT	497-8074-1-ND	1.8V, Quad, In/Out, R/R, LP Op Amp*	14-TSSOP	2.47 2.23 1.82		
TS1874IPT	497-8074-2-ND	1.8V, Quad, In/Out, R/R, LP Op Amp*	14-TSSOP	2740.74/2,500		
TS1874YDT	497-10240-1-ND	1.8V, Quad, In/Out, R/R, LP Op Amp*	14-SOIC	1.30 1.15 .91		
TS1874YDT	497-10240-2-ND	1.8V, Quad, In/Out, R/R, LP Op Amp*	14-SOIC	1295.29/2,500		
TS1874YPT	497-10241-1-ND	1.8V, Quad, In/Out, R/R, LP Op Amp*	14-TSSOP	1.30 1.15 .91		
TS1874YPT	497-10241-2-ND	1.8V, Quad, In/Out, R/R, LP Op Amp*	14-TSSOP	1295.29/2,500		
TS3021ICT	497-5324-1-ND	1.8V, R/R HS Comparator*	SC70-5	1.91 1.65 1.35		
TS3021ICT	497-5324-2-ND	1.8V, R/R HS Comparator*	SC70-5	2215.01/3,000		
TS3021ILT	497-8092-1-ND	1.8V, R/R HS Comparator*	SOT-23-5	1.52 1.31 1.07		
TS3021ILT	497-8092-2-ND	1.8V, R/R HS Comparator*	SOT-23-5	1763.36/3,000		
TS3022IDT	497-5770-1-ND	1.8V, R/R HS Comparator*	8-SOIC	2.65 2.27 1.86		
TS3022IDT	497-5770-2-ND	1.8V, R/R HS Comparator*	8-SOIC	2554.55/2,500		
TS3022IST	497-6103-1-ND	1.8V, R/R HS Comparator*	8-MSOP	1.93 1.66 1.36		
TS3022IST	497-6103-2-ND	1.8V, R/R HS Comparator*	8-MSOP	2978.98/4,000		
TS3702CDT	497-6611-1-ND	Micropower Dual CMOS Voltage Comparator*	8-SOIC	.93 .83 .66		
TS3702CDT	497-6611-2-ND	Micropower Dual CMOS Voltage Comparator*	8-SOIC	854.85/2,500		
TS3702ID	497-3038-5-ND	Micropower Dual CMOS Voltage Comparator	8-SOIC	1.09 .97 .77		
TS3702IDT	497-2267-1-ND	Micropower Dual CMOS Voltage Comparator	8-SOIC	.90 .81 .64		
TS3702IDT	497-2267-2-ND	Micropower Dual CMOS Voltage Comparator	8-SOIC	824.82/2,500		
TS3702IN	497-2268-5-ND	Micropower Dual CMOS Voltage Comparator	8-Dip	.69 .62 .49		
TS3704CDT	497-4063-1-ND	Micropower Quad CMOS Voltage Comparator	14-SOIC	.77 .67 .53		
TS3704CDT	497-4063-2-ND	Micropower Quad CMOS Voltage Comparator	14-SOIC	632.63/2,500		
TS3704IDT	497-2269-1-ND	Micropower Quad CMOS Voltage Comparator	14-SOIC	1.25 1.12 .89		
TS3704IDT	497-2269-2-ND	Micropower Quad CMOS Voltage Comparator	14-SOIC	1149.15/2,500		
TS3704IN	497-2270-5-ND	Micropower Quad CMOS Voltage Comparator	14-Dip	.88 .78 .62		

STMicroelectronics		Digi-Reel® (Cont.)		AMPLIFIERS AND LINEAR RoHS Compliant Parts Available		
STMicroelectronics Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*		
				1	10	100
TS3704IPT	497-4064-1-ND	Micropower Quad CMOS Voltage Comparator	14-TSSOP	1.25 1.12 .89		
TS3704IPT	497-4064-2-ND	Micropower Quad CMOS Voltage Comparator	14-TSSOP	1149.15/2,500		
TS7221AILT	497-3046-1-ND	BiCMOS R/R Micropower Comparator	SOT-23-5	1.15 1.03 .82		
TS7221AILT	497-3047-1-ND	Single BiCMOS R/R Micropower Comparator	SOT-23-5	1.15 1.03 .82		
TS7221AILT	497-3047-2-ND	Single BiCMOS R/R Micropower Comparator	SOT-23-5	1270.87/3,000		
TS7221BILT	497-8122-1-ND	Single BiCMOS R/R Micropower Comparator*	SOT-23-5	1.28 1.15 .91		
TS7221BILT	497-8122-2-ND	Single BiCMOS R/R Micropower Comparator*	SOT-23-5	1412.61/3,000		
TS9222IPT	497-10353-1-ND	Dual R/R I/O Op Amp*	8-TSSOP	1.12 1.00 .79		
TS9222IPT	497-10353-2-ND	Dual R/R I/O Op Amp*	8-TSSOP	1790.59/4,000		
TS9224IPT	497-10156-1-ND	Quad R/R I/O Op Amp*	14-TSSOP	1.67 1.51 1.22		
TS9224IPT	497-10156-2-ND	Quad R/R I/O Op Amp*	14-TSSOP	1815.81/2,500		
TS9511ILT	497-10352-1-ND	Single Precision R/R I/O Op Amp*	SOT23-5	.97 .87 .69		
TS9511ILT	497-10352-2-ND	Single Precision R/R I/O Op Amp*	SOT23-5	1167.57/3,000		
TSC101AILT	497-6945-1-ND	High Side Current Sense Amp*	SOT-23-5	2.35 2.02 1.65		
TSC101AILT	497-6945-2-ND	High Side Current Sense Amp*	SOT-23-5	2724.32/3,000		
TSC101AIVLT	497-10273-1-ND	High Side Current Sense Amp*	SOT-23-5	2.22 2.01 1.61		
TSC101AIVLT	497-10273-2-ND	High Side Current Sense Amp*	SOT-23-5	2897.29/3,000		
TSC101BILT	497-6946-1-ND	High Side Current Sense Amp*	SOT-23-5	2.35 2.02 1.65		
TSC101BILT	497-6946-2-ND	High Side Current Sense Amp*	SOT-23-5	2724.32/3,000		
TSC101BYILT	497-10274-1-ND	High Side Current Sense Amp*	SOT-23-5	2.22 2.01 1.61		
TSC101BYILT	497-10274-2-ND	High Side Current Sense Amp*	SOT-23-5	2897.29/3,000		
TSC101CILT	497-6947-1-ND	High Side Current Sense Amp*	SOT-23-5	2.35 2.02 1.65		
TSC101CILT	497-6947-2-ND	High Side Current Sense Amp*	SOT-23-5	2724.32/3,000		
TSC101CIVLT	497-10275-1-ND	High Side Current Sense Amp*	SOT-23-5	2.22 2.01 1.61		
TSC101CIVLT	497-10275-2-ND	High Side Current Sense Amp*	SOT-23-5	2897.29/3,000		
TSC888AILT	497-8269-1-ND	High Side Current Sense Amp*	SOT-23-5	1.25 1.12 .89		
TSC888AILT	497-8269-2-ND	High Side Current Sense Amp*	SOT-23-5	1378.98/3,000		
TSC888BILT	497-8270-1-ND	High Side Current Sense Amp*	SOT-23-5	1.02 .91 .73		
TSC888BILT	497-8270-2-ND	High Side Current Sense Amp*	SOT-23-5	1378.98/3,000		
TSC888CILT	497-8271-1-ND	High Side Current Sense Amp*	SOT-23-5	1.25 1.12 .89		
TSC888CILT	497-8271-2-ND	High Side Current Sense Amp*	SOT-23-5	1378.98/3,000		
TSH22IDT	497-2320-1-ND	Dual Bipolar Op Amp	8-SOIC	1.06 .95 .76		
TSH22IDT	497-2320-2-ND	Dual Bipolar Op Amp	8-SOIC	972.97/2,500		
TSH22IN	497-7686-5-ND	Dual Bipolar Op Amp*	8-Dip	1.17 1.06 .85		
TSH24IDT	497-2321-1-ND	Quad Bipolar Op Amp	14-SOIC	1.15 1.03 .82		
TSH24IDT	497-2321-2-ND	Quad Bipolar Op Amp	14-SOIC	1059.06/2,500		
TSH62CDT	497-6124-1-ND	Wideband, LP Dual Op Amp*	8-SOIC	1.09 .98 .78		
TSH62CDT	497-6124-2-ND	Wideband, LP Dual Op Amp*	8-SOIC	1235.23/2,500		
TSH70CDT	497-3070-5-ND	Wideband, Low Power Op Amp	8-SOIC	1.07 .97 .78		
TSH70CDT	497-8154-1-ND	Wideband, Low Power Op Amp*	SOT-23-5	1.47 1.27 1.04		
TSH70CDT	497-8154-2-ND	Wideband, Low Power Op Amp*	SOT-23-5	1703.30/3,000		
TSH72CDT	497-2324-5-ND	Wideband, Low Power Dual Op Amp	8-SOIC	1.51 1.37 1.10		
TSH72CDT	497-2324-6-ND	Wideband, Low Power Dual Op Amp	8-SOIC	1.51 1.37 1.10		
TSH72CPT	497-4080-1-ND	Wideband, Low Power Dual Op Amp	8-TSSOP	1.39 1.20 .98		
TSH72CPT	497-4080-2-ND	Wideband, Low Power Dual Op Amp	8-TSSOP	2303.10/4,000		
TSH73CDT	497-8155-1-ND	R/R Wideband Low Power Op Amp*	14-SOIC	1.44 1.29 1.03		
TSH73CDT	497-8155-2-ND	R/R Wideband Low Power Op Amp*	14-SOIC	1325.32/2,500		
TSH73CPT	497-8156-1-ND					