

图	引脚数	尺寸 (mm)		Digi-Key 零件编号	价格		Hirose 零件编号	
		A	B		25	100		
4	10	12.0	8.0	H2853-ND	1.29	23.38	76.50	DF11-10DP-2DSA(01)
	12	14.0	10.0	H2854-ND	1.52	27.50	90.00	DF11-12DP-2DSA(01)
	14	16.0	12.0	H2855-ND	1.71	30.94	101.25	DF11-14DP-2DSA(01)
	16	18.0	14.0	H2856-ND	1.66	31.88	102.00	DF11-16DP-2DSA(01)
	18	20.0	16.0	H2857-ND	1.82	35.00	112.00	DF11-18DP-2DSA(01)
	20	22.0	18.0	H2858-ND	1.98	38.13	122.00	DF11-20DP-2DSA(01)
	22	24.0	20.0	H2859-ND	2.21	42.50	136.00	DF11-22DP-2DSA(01)
	24	26.0	22.0	H2860-ND	2.37	45.63	146.00	DF11-24DP-2DSA(01)
	26	28.0	24.0	H2861-ND	2.54	48.75	156.00	DF11-26DP-2DSA(01)
	28	30.0	26.0	H2862-ND	2.70	51.88	166.00	DF11-28DP-2DSA(01)
	30	32.0	28.0	H2863-ND	2.86	55.00	176.00	DF11-30DP-2DSA(01)
	32	34.0	30.0	H2864-ND	3.02	58.13	186.00	DF11-32DP-2DSA(01)
直角保护式接头, 锡								
5	26	28.0	24.0	H2280-ND	1.44	26.13	85.50	DF11-26DP-2DS(22)
直角保护式接头, 锡 - 符合 RoHS 规范要求								
5	4	6.0	2.0	H10244-ND	.65	9.75	30.55	DF11-4DP-2DS(24)
	6	8.0	4.0	H10245-ND	.61	11.00	36.00	DF11-6DP-2DS(24)
	8	10.0	6.0	H10246-ND	.65	11.69	38.25	DF11-8DP-2DS(24)
	10	12.0	8.0	H10247-ND	.80	14.44	47.25	DF11-10DP-2DS(24)
	12	14.0	10.0	H10248-ND	.91	16.50	54.00	DF11-12DP-2DS(24)
	14	16.0	12.0	H10249-ND	1.06	19.25	63.00	DF11-14DP-2DS(24)
	16	18.0	14.0	H10250-ND	1.25	22.69	74.25	DF11-16DP-2DS(24)
	18	20.0	16.0	H10251-ND	1.25	22.69	74.25	DF11-18DP-2DS(24)
	20	22.0	18.0	H10252-ND	1.41	25.44	83.25	DF11-20DP-2DS(24)
	22	24.0	20.0	H10253-ND	1.56	28.19	92.25	DF11-22DP-2DS(24)
	24	26.0	22.0	H10254-ND	1.71	30.94	101.25	DF11-24DP-2DS(24)
	26	28.0	24.0	H10255-ND	1.71	30.94	101.25	DF11-26DP-2DS(24)
28	30.0	26.0	H10256-ND	1.82	33.00	108.00	DF11-28DP-2DS(24)	
30	32.0	28.0	H10257-ND	1.69	32.50	104.00	DF11-30DP-2DS(24)	
32	34.0	30.0	H10258-ND	1.79	34.38	110.00	DF11-32DP-2DS(24)	
直角保护式接头, 金 - 符合 RoHS 规范要求								
5	4	6.0	2.0	H2865-ND	1.03	18.56	60.75	DF11-4DP-2DS(52)
	6	8.0	4.0	H2866-ND	1.29	23.38	76.50	DF11-6DP-2DS(52)
	8	10.0	6.0	H2867-ND	1.63	29.56	96.75	DF11-8DP-2DS(52)
	10	12.0	8.0	H2868-ND	1.66	31.88	102.00	DF11-10DP-2DS(52)
	12	14.0	10.0	H2869-ND	1.85	35.63	114.00	DF11-12DP-2DS(52)
	14	16.0	12.0	H2870-ND	2.11	40.63	130.00	DF11-14DP-2DS(52)
	16	18.0	14.0	H2871-ND	2.41	46.25	148.00	DF11-16DP-2DS(52)
	18	20.0	16.0	H2872-ND	2.63	50.63	162.00	DF11-18DP-2DS(52)
	20	22.0	18.0	H2873-ND	2.93	56.25	180.00	DF11-20DP-2DS(52)
	22	24.0	20.0	H2874-ND	3.15	60.63	194.00	DF11-22DP-2DS(52)
	24	26.0	22.0	H2875-ND	3.07	59.63	190.80	DF11-24DP-2DS(52)
	26	28.0	24.0	H2876-ND	3.25	63.00	201.60	DF11-26DP-2DS(52)
28	30.0	26.0	H2877-ND	3.48	67.50	216.00	DF11-28DP-2DS(52)	
30	32.0	28.0	H2878-ND	3.68	71.44	228.60	DF11-30DP-2DS(52)	
32	34.0	30.0	H2879-ND	3.94	76.50	244.80	DF11-32DP-2DS(52)	
表面贴装保护式接头, 锡								
6	22	26.5	20.0	H2890-ND	3.22	61.88	198.00	DF11G-22DP-2V(20)
	28	32.5	26.0	H2896-ND	2.11	40.63	130.00	DF11-28DP-2V(20)
	32	36.5	30.0	H2895-ND	2.28	43.75	140.00	DF11G-32DP-2V(20)
表面贴装保护式接头, 锡 - 符合 RoHS 规范要求								
6	4	8.5	2.0	H10259-ND	1.18	21.31	69.75	DF11GZ-4DP-2V(20)
	6	10.5	4.0	H10260-ND	1.25	22.69	74.25	DF11GZ-6DP-2V(20)
	8	12.5	6.0	H10261-ND	1.33	24.06	78.75	DF11GZ-8DP-2V(20)
	10	14.5	8.0	H10262-ND	1.44	26.13	85.50	DF11GZ-10DP-2V(20)
	12	16.5	10.0	H10263-ND	1.56	28.19	92.25	DF11GZ-12DP-2V(20)
	14	18.5	12.0	H10264-ND	1.63	29.56	96.75	DF11GZ-14DP-2V(20)
	16	20.5	14.0	H10265-ND	1.79	32.31	105.75	DF11GZ-16DP-2V(20)
	18	22.5	16.0	H10266-ND	1.86	33.69	110.25	DF11GZ-18DP-2V(20)
	20	24.5	18.0	H10267-ND	1.66	31.88	102.00	DF11GZ-20DP-2V(20)
	22	26.5	20.0	H10268-ND	1.79	34.38	110.00	DF11GZ-22DP-2V(20)
	24	28.5	22.0	H10269-ND	1.89	36.25	116.00	DF11GZ-24DP-2V(20)
	26	30.5	24.0	H10270-ND	2.02	38.75	124.00	DF11GZ-26DP-2V(20)
28	32.5	26.0	H10271-ND	2.21	42.50	136.00	DF11GZ-28DP-2V(20)	
30	34.5	28.0	H10272-ND	2.28	43.75	140.00	DF11GZ-30DP-2V(20)	
32	36.5	30.0	H10273-ND	2.31	44.38	142.00	DF11GZ-32DP-2V(20)	
40	44.5	38.0	H10274-ND	2.80	53.75	172.00	DF11GZ-40DP-2V(20)	
表面贴装保护式接头, 金 - 符合 RoHS 规范要求								
6	4	8.5	2.0	H2897-ND	1.63	29.56	96.75	DF11G-4DP-2V(50)
	6	10.5	4.0	H2898-ND	1.86	33.69	110.25	DF11G-6DP-2V(50)
	8	12.5	6.0	H2899-ND	1.79	34.38	110.00	DF11G-8DP-2V(50)
	10	14.5	8.0	H2900-ND	2.02	38.75	124.00	DF11G-10DP-2V(50)
	12	16.5	10.0	H2901-ND	2.28	43.75	140.00	DF11G-12DP-2V(50)
	14	18.5	12.0	H2902-ND	2.47	47.50	152.00	DF11G-14DP-2V(50)
	16	20.5	14.0	H2903-ND	2.73	52.50	168.00	DF11G-16DP-2V(50)
	18	22.5	16.0	H2904-ND	2.93	56.25	180.00	DF11G-18DP-2V(50)
	20	24.5	18.0	H2905-ND	3.12	60.00	192.00	DF11G-20DP-2V(50)
	22	26.5	20.0	H2906-ND	3.07	59.63	190.80	DF11G-22DP-2V(50)
	24	28.5	22.0	H2907-ND	3.28	63.56	203.40	DF11G-24DP-2V(50)
	26	30.5	24.0	H2908-ND	3.60	69.75	223.20	DF11G-26DP-2V(50)
28	32.5	26.0	H2909-ND	3.83	74.25	237.60	DF11G-28DP-2V(50)	

图	引脚数	尺寸 (mm)		Digi-Key 零件编号	价格			Hirose 零件编号
		A	B		1	25	100	
6	30	34.5	28.0	H2910-ND	4.03	78.19	250.20	DF11G-30DP-2V(50)
	32	36.5	30.0	H2911-ND	4.21	81.56	261.00	DF11G-32DP-2V(50)
	40	44.5	38.0	H2912-ND	5.25	101.81	325.80	DF11G-40DP-2V(50)
连接器插头底座 - 符合 RoHS 规范要求								
7	4	11.0	2.0	H2913-ND	.50	7.50	23.50	DF11-4DEP-2C
	6	13.0	4.0	H2914-ND	.52	7.80	24.44	DF11-6DEP-2C
	8	15.0	6.0	H2915-ND	.54	8.10	25.38	DF11-8DEP-2C
	10	17.0	8.0	H2916-ND	.56	8.40	26.32	DF11-10DEP-2C
	12	19.0	10.0	H2917-ND	.58	8.70	27.26	DF11-12DEP-2C
	14	21.0	12.0	H2918-ND	.61	9.15	28.67	DF11-14DEP-2C
	16	23.0	14.0	H2919-ND	.63	9.45	29.61	DF11-16DEP-2C
	18	25.0	16.0	H2920-ND	.65	9.68	30.32	DF11-18DEP-2C
	20	27.0	18.0	H2921-ND	.67	9.98	31.26	DF11-20DEP-2C
	22	29.0	20.0	H2922-ND	.69	10.35	32.43	DF11-22DEP-2C
	24	31.0	22.0	H2923-ND	.72	10.73	33.61	DF11-24DEP-2C
	26	33.0	24.0	H2924-ND	.74	11.03	34.55	DF11-26DEP-2C
28	35.0	26.0	H2925-ND	.58	10.45	34.20	DF11-28DEP-2C	
30	37.0	28.0	H2926-ND	.59	10.73	35.10	DF11-30DEP-2C	
32	39.0	30.0	H2927-ND	.61	11.00	36.00	DF11-32DEP-2C	
直插式适配器 - 符合 RoHS 规范要求								
8	4	9.2	2.0	H2928-ND	.67	12.10	39.60	DF11-4DEP-2A
	6	11.2	4.0	H2929-ND	.76	13.75	45.00	DF11-6DEP-2A
	8	13.2	6.0	H2930-ND	.87	15.81	51.75	DF11-8DEP-2A
	10	15.2	8.0	H2931-ND	.95	17.19	56.25	DF11-10DEP-2A
	12	17.2	10.0	H2932-ND	1.03	18.56	60.75	DF11-12DEP-2A
	14	19.2	12.0	H2933-ND	1.18	21.31	69.75	DF11-14DEP-2A
	16	21.2	14.0	H2934-ND	1.25	22.69	74.25	DF11-16DEP-2A
	18	23.2	16.0	H2935-ND	1.33	24.06	78.75	DF11-18DEP-2A
	20	25.2	18.0	H2936-ND	1.44	26.13	85.50	DF11-20DEP-2A
	22	27.2	20.0	H2937-ND	1.56	28.19	92.25	DF11-22DEP-2A
	24	29.2	22.0	H2938-ND	1.63	29.56	96.75	DF11-24DEP-2A
	26	31.2	24.0	H2939-ND	1.71	30.94	101.25	DF11-26DEP-2A
28	33.2	26.0	H2940-ND	1.79	32.31	105.75	DF11-28DEP-2A	
30	35.2	28.0	H2941-ND	1.63	31.25	100.00	DF11-30DEP-2A	
32	37.2	30.0	H2942-ND	1.69	32.50	104.00	DF11-32DEP-2A	
连接器短路跳线器 - 符合 RoHS 规范要求								
9A	4	6.6	2.0	H10275-ND	.67	9.98	31.26	DF11-4DP-SP1(05)
	6	8.6	4.0	H10276-ND	.71	10.65	33.37	DF11-6DP-SP1(05)
	8	10.6	6.0	H10277-ND	.58	10.45	34.20	DF11-8DP-SP1(05)
9B	4	6.6	2.0	H10278-ND	.72	13.06	42.75	DF11-4DP-SP2(05)
	6	8.6	4.0	H10279-ND	.80	14.44	47.25	DF11-6DP-SP2(05)
8	10.6	6.0	H10280-ND	.87	15.81	51.75	DF11-8DP-SP2(05)	

压接触点

图	AWG	Digi-Key 零件编号	散装件 价格 100	Hirose 零件编号	Digi-Key 零件编号	带卷 价格 10,000	Hirose 零件编号
插口触点 - 符合 RoHS 规范要求							
镀锡							
10	22	H2950-ND	7.43	DF11-22SC	H2950TR-ND	18.00/M	DF11-22SCF
	24-28	H150					