



Trim Trio 连接系统 (接上页)



坚固耐用圆形反向卡销 - 动态密封 IP68/IP69K UTV 系列

特点: • 反向卡销耦合 • 可与 VG 95234 互安装: MS-5015 反向卡销 • 500 配接 - 断开周期 • 耐盐雾高达 500 小时 技术规格: • 外壳: 铝合金, 镀黑色锌铬 • 工作温度: -55°C - 125°C

图	位置 数量/大小†	说明	Digi-Key 零件编号	单价			Souriau 零件编号
				1	10	25	
13	10 / #16	插口的线缆插头	SOU1275-ND	51.97	49.23	47.87	UTVD18-19SN
14		引脚插座	SOU1273-ND	39.14	37.08	36.05	UTVB18-19PN
13	7 / #12	插口的线缆插头	SOU1276-ND	54.49	51.63	50.19	UTVD20-15SN
14		引脚插座	SOU1274-ND	44.27	41.94	40.78	UTVB20-15PN
13	35 / #12	插口的线缆插头	SOU1278-ND	95.93	90.89	88.36	UTVD40A35PN
14		引脚插座	SOU1277-ND	70.32	66.62	64.77	UTVB40A35PN

† 有关触点, 参见 Trim Trio 触点部分

Trim Trio 附件

图	说明	Digi-Key 零件编号	单价			Souriau 零件编号
			1	10	25	
UTO 和 UTOV 的线缆夹						
15	#10 线缆夹金属	SOU1048-ND	14.42	13.67	13.29	UT010AC
—	#10 线缆夹金属 - IP68	SOU1053-ND†	17.01	16.11	15.67	UT010JCS
15	#12 线缆夹金属	SOU1049-ND	14.99	14.21	13.81	UT012AC
—	#12 线缆夹金属 - IP68	SOU1054-ND†	17.56	16.64	16.17	UT012JCS
15	#14 线缆夹金属	SOU1050-ND	15.64	14.82	14.41	UT014AC
—	#14 线缆夹金属 - IP68	SOU1055-ND†	20.60	19.52	18.97	UT014JCS

图	说明	Digi-Key 零件编号	单价			Souriau 零件编号
			1	10	25	
15	#16 线缆夹金属	SOU1499-ND	11.65	11.04	10.73	UT016AC
—	#16 线缆夹金属 - IP68	SOU1056-ND†	23.79	22.54	21.91	UT016JC
15	#18 线缆夹金属	SOU1051-ND	16.25	15.39	14.97	UT018AC
—	#18 线缆夹金属 - IP68	SOU1057-ND†	25.48	24.14	23.47	UT018JCL
15	#20 线缆夹金属	SOU1500-ND	13.93	13.20	12.83	UT020AC
—	#20 线缆夹金属 - IP68	SOU1502-ND†	20.14	19.08	18.55	UT020JCS
15	#22 线缆夹金属	SOU1501-ND	18.37	17.41	16.93	UT022AC
—	#22 线缆夹金属 - IP68	SOU1503-ND†	24.62	23.33	22.68	UT022JCS
15	#24 线缆夹金属	SOU1052-ND	22.29	21.12	20.53	UT024AC
—	#24 线缆夹金属 - IP68	SOU1504-ND†	31.24	29.60	28.77	UT024JCS
UTG 和 UTP 的线缆夹						
16	#10 线缆夹	SOU1124-ND	7.39	7.01	6.81	UTG10AC
—	#10 线缆夹 - IP65	SOU1131-ND†	9.06	8.59	8.35	UTG10PG
16	#12 线缆夹	SOU1125-ND	8.17	7.74	7.53	UTG12AC
—	#12 线缆夹 - IP65	SOU1132-ND†	10.58	10.03	9.75	UTG12PG
16	#14 线缆夹	SOU1498-ND	9.06	8.59	8.35	UTG14AC
—	#14 线缆夹 - IP65	SOU1133-ND†	10.89	10.32	10.03	UTG14PG
16	#16 线缆夹	SOU1126-ND	8.66	8.21	7.98	UTG16AC
—	#16 线缆夹 - IP65	SOU1134-ND†	11.88	11.25	10.94	UTG16PG
16	#18 线缆夹	SOU1127-ND	9.01	8.54	8.30	UTG18AC
—	#18 线缆夹 - IP65	SOU1135-ND†	12.39	11.74	11.41	UTG18PG
16	#20 线缆夹	SOU1128-ND	10.36	9.81	9.54	UTG20AC
—	#20 线缆夹 - IP65	SOU1136-ND†	13.89	13.16	12.80	UTG20PG
16	#22 线缆夹	SOU1129-ND	10.53	9.98	9.70	UTG22AC
—	#22 线缆夹 - IP65	SOU1137-ND†	14.33	13.58	13.20	UTG22PG
16	#24 线缆夹	SOU1130-ND	12.01	11.38	11.06	UTG24AC
—	#24 线缆夹 - IP65	SOU1138-ND†	12.67	12.01	11.68	UTG24PG
UTO、UTOV、UTG 和 UTP 的密封垫圈						
—	#10 墙壁安装插座的密封	SOU1058-ND	2.56	2.42	2.33	UTFD12B
—	#12 墙壁安装插座的密封	SOU1059-ND	3.76	3.57	3.47	UTFD13B
—	#14 墙壁安装插座的密封	SOU1060-ND	2.17	2.06	1.98	UTFD14B
—	#16 墙壁安装插座的密封	SOU1061-ND	2.07	1.97	1.91	UTFD15B
—	#18 墙壁安装插座的密封	SOU1062-ND	2.34	2.21	2.13	UTFD16B
—	#20 墙壁安装插座的密封	SOU1505-ND	2.01	1.90	1.83	UTFD17B
—	#22 墙壁安装插座的密封	SOU1506-ND	2.01	1.90	1.83	UTFD18B
—	#24 墙壁安装插座的密封	SOU1063-ND	1.87	1.77	1.70	UTFD19B

§ 长式 † 用于防水应用

Trim Trio 触点

类型	AWG	镀层	Digi-Key 零件编号	价格				Souriau 零件编号
				1	10	25	100	
#8 机加工焊接触点								
插口 引脚	12-8	金	SOU1246-ND SOU1245-ND	5.23 5.04	49.50 47.70	120.31 115.94	398.75 384.25	82911684ZX 82911685NZX
#12 机加工焊接触点								
插口 引脚	14-12	金	SOU1244-ND SOU1243-ND	4.56 4.28	43.20 40.50	105.00 98.44	348.00 326.25	RC12Z43D28 RM12Z43D28
#16 机加工焊接触点和同轴								
插口 引脚	20-16	金	SOU1237-ND SOU1238-ND	2.56 1.68	24.18 15.86	58.13 115.90	176.70 159.50	RC16M23D28 RM16M23D28
插口 引脚	22-20	金	SOU1239-ND SOU1240-ND	2.09 2.64	19.80 24.96	48.13 60.00	159.50 182.40	RC20M12D28 RM20M12D28
插口 引脚	同轴套件多件 RG-174U/188U 镀金	同轴套件多件 RG-174U/188U 镀金	SOU1241-ND SOU1242-ND	9.98 9.98	94.50 94.50	229.69 229.69	761.25 761.25	RCDXK1D28 RMDXK1D28

类型	AWG	镀层	Digi-Key 零件编号	散零件 价格		Souriau 零件编号	Digi-Key 零件编号	剪切带 价格		Digi-Key 零件编号	带卷 价格	Souriau 零件编号	
				25	100		10	50	100		3,000		
#16 冲压成型压接触点													
插口 引脚	14	30μ" 金	SOU1247-ND	30.63	93.10	SC14ML1S6	SOU1247CT-ND	11.80	52.21	86.26	SOU1247TR-ND	602.00/M	SC14M1S6
插口 引脚		30μ" 金	SOU1251-ND	25.00	76.00	SM14ML1S6	SOU1251CT-ND	10.50	46.46	76.76	SOU1251TR-ND	490.00/M	SM14M1S6
插口 引脚		锡	SOU1255-ND	11.88	36.10	SC14ML1TK6	SOU1255CT-ND	5.04	22.31	36.86	SOU1255TR-ND	210.00/M	SC14M1TK6
插口 引脚		锡	SOU1259-ND	9.38	28.50	SM14ML1TK6	SOU1259CT-ND	4.00	17.71	29.26	SOU1259TR-ND	182.00/M	SM14M1TK6
插口 引脚	18-16	30μ" 金	SOU1248-ND	28.13	85.50	SC16ML1S6	SOU1248CT-ND	11.80	52.21	86.26	SOU1248TR-ND	602.00/M	SC16M1S6
插口 引脚		30μ" 金	SOU1252-ND	25.00	76.00	SM16ML1S6	SOU1252CT-ND	10.50	46.46	76.76	SOU1252TR-ND	490.00/M	SM16M1S6
插口 引脚		锡	SOU1256-ND	11.88	36.10	SC16ML1TK6	SOU1256CT-ND	5.04	22.31	36.86	SOU1256TR-ND	210.00/M	SC16M1TK6
插口 引脚		锡	SOU1260-ND	9.38	28.50	SM16ML1TK6	SOU1260CT-ND	4.00	17.71	29.26	SOU1260TR-ND	182.00/M	SM16M1TK6
插口 引脚	22-20	30μ" 金	SOU1249-ND	30.63	93.10	SC20ML1S6	SOU1249CT-ND	11.80	52.21	86.26	SOU1249TR-ND	546.00/M	SC20M1S6
插口 引脚		30μ" 金	SOU1253-ND	27.50	83.60	SM20ML1S6	SOU1253CT-ND	10.50	46.46	76.76	SOU1253TR-ND	490.00/M	SM20M1S6
插口 引脚		锡	SOU1257-ND	11.88	36.10	SC20ML1TK6	SOU1257CT-ND	5.04	22.31	36.86	SOU1257TR-ND	210.00/M	SC20M1TK6
插口 引脚		锡	SOU1261-ND	9.38	28.50	SM20ML1TK6	SOU1261CT-ND	4.00	17.71	29.26	SOU1261TR-ND	182.00/M	SM20M1TK6
插口 引脚	26-24	30μ" 金	SOU1250-ND	28.13	85.50	SC24ML1S6	SOU1250CT-ND	11.80	52.21	86.26	SOU1250TR-ND	546.00/M	SC24M1S6
插口 引脚		30μ" 金	SOU1254-ND	25.00	76.00	SM24ML1S6	SOU1254CT-ND	10.50	46.46	76.76	SOU1254TR-ND	490.00/M	SM24M1S6
插口 引脚		锡	SOU1258-ND	11.88	36.10	SC24ML1TK6	SOU1258CT-ND	5.04	22.31	36.86	SOU1258TR-ND	210.00/M	SC24M1TK6
插口 引脚		锡	SOU1262-ND	9.38	28.50	SM24ML1TK6	SOU1262CT-ND	4.00	17.71	29.26	SOU1262TR-ND	168.00/M	SM24M1TK6
#20 冲压成型压接触点													
插口 引脚	22-20	30μ" 金	SOU1265-ND	8.75	26.60	SC20WL3S25	SOU1265CT-ND	3.74	16.56	27.36	SOU1265TR-ND	168.00/M	SC20W3S25
插口 引脚		30μ" 金	SOU1266-ND	9.38	28.50	SM20WL3S26	SOU1266CT-ND	4.00	17.71	29.26	SOU1266TR-ND	168.00/M	SM20W3S26
插口 引脚		锡	SOU1269-ND	7.50	22.80	SC20WL3TK6	—	—	—	—	—	—	
插口 引脚		锡	SOU1271-ND	6.25	19.00	SM20WL3TK6	—	—	—	—	—	—	
插口 引脚	26-24	30μ" 金	SOU1267-ND	9.38	28.50	SC24WL3S25	SOU1267CT-ND	3.74	16.56	27.36	SOU1267TR-ND	168.00/M	SC24W3S25
插口 引脚		30μ" 金	SOU1268-ND	9.38	28.50	SM24WL3S26	SOU1268CT-ND	4.00	17.71	29.26	SOU1268TR-ND	168.00/M	SM24W3S26
插口 引脚		锡	SOU1270-ND	7.50	22.80	SC24WL3TK6	—	—	—	—	—	—	
插口 引脚		锡	SOU1272-ND	6.25	19.00	SM24WL3TK6	—	—	—	—	—	—	

压接工具

说明	Digi-Key 零件编号	单价	Souriau 零件编号
用于对 #16-20 冲压触点 26-14AWG 进行带模具压接全部触点的抽取工具	SOU1263-ND SOU1264-ND	282.15 42.09	Y14MTV RX2025GE1



工具

与 Souriau Trim Trio 机械加工触点一起使用。

616336 压接工具可用于 RC/RM 触点。
615717 和 615708 用于 RC (M) DXK 同轴触点。
需要两种工具, 用于内触点压接和外套圈压接。

说明	Digi-Key 零件编号	单价	Astro 零件编号
#16 机械加工触点的无定位器压接	616336-ND	282.96	616336
616336 工具架的定位器	TGV702-ND	102.41	TGV702
对内压接同轴触点进行无定位器压接	615717-ND	282.96	615717
615717 工具架的定位器	620100-ND	46.62	620100
对外压接同轴触点进行无塔尖压接	615708-ND	282.96	615708
615708 工具架的转接头	620439-ND	74.21	620439

全部产品均以美元计价。 免费电话: 10800-1527031 (China Telecom - 中国电讯) — 10800-8527031 (CNCG - 中国网通)