

3M 兼容电磁干扰的产品

3M EMC 产品可为您提供:

- EMI/RFI 屏蔽与吸收 • 静电中和接地 • 抗静电遮蔽 • 缓冲 • 机械保护 • 导电特性, 适合广泛应用



系列	尺寸	粘接型	总厚度 (密耳/mm)	Digi-Key 零件编号	单价			3M 零件编号
					1	5	10	
铝箔带								
1120	1"x 36 码	导电性 丙烯酸	4.0/0.102	3M1120C-ND	29.75	27.20	25.50	1120 X 1"
	1"x 1 码			3M1120C-1YD-ND	1.65	1.18	1.07	1120 X 1"
	6"x 36 码			3M1120D-ND	163.20	153.00	142.80	1120 X 6"
	6"x 1 英尺			3M1120D-1FT-ND	3.31	2.37	2.13	1120 X 6"
1170	1"x 18 码	导电性 丙烯酸	3.2/0.081	3M1170C-ND	51.29	46.90	43.97	1170 X 1"
	1"x 1 码			3M1170C-1YD-ND	4.48	3.42	3.26	1170 X 1"
	6"x 18 码			3M1170D-ND	260.16	243.90	227.64	1170 X 6"
	6"x 1 英尺			3M1170D-1FT-ND	7.53	6.03	5.42	1170 X 6"
1115	1"x 60 码	导电性 丙烯酸	7.0/0.177	3M1115C-ND	68.14	64.13	60.12	1115 X 1"
	1"x 1 码			3M1115C-1YD-ND	2.34	1.67	1.51	1115 X 1"
	6"x 60 码			3M1115D-ND	372.74	336.68	312.63	1115 X 6"
	6"x 1 英尺			3M1115D-1FT-ND	3.67	2.81	2.68	1115 X 6"
覆有薄膜的铝箔带								
AL-36FR	1"x 54.5 码	导电性 丙烯酸	2.4/0.061	3M3600C-ND	21.00	19.20	18.00	AL-36FR X 1"
	1"x 1 码			3M3600C-1YD-ND	.77	.55	.50	AL-36FR X 1"
	6"x 54.5 码			3M3600D-ND	115.20	108.00	100.80	AL-36FR X 6"
	6"x 1 英尺			3M3600D-1FT-ND	1.54	1.10	1.00	AL-36FR X 6"
AL-36NC	1"x 54.5 码	非导电性 丙烯酸	2.2/0.055	3M3601C-ND	29.75	27.20	25.50	AL-36NC X 1"
	1"x 1 码			3M3601C-1YD-ND	1.09	.78	.71	AL-36NC X 1"
	6"x 54.5 码			3M3601D-ND	163.20	153.00	142.80	AL-36NC X 6"
	6"x 1 英尺			3M3601D-1FT-ND	2.18	1.56	1.41	AL-36NC X 6"
AL-37BLK	1"x 21.8 码	导电性 丙烯酸	2.8/0.071	3M3700C-ND	34.44	31.49	29.52	AL-37BLK X 1"
	1"x 1 码			3M3700C-1YD-ND	3.16	2.26	2.04	AL-37BLK X 1"
	6"x 21.8 码			3M3700D-ND	188.93	177.12	165.32	AL-37BLK X 6"
	6"x 1 英尺			3M3700D-1FT-ND	4.97	3.80	3.62	AL-37BLK X 6"
铜箔带								
1125	1"x 36 码	非导电性 丙烯酸	3.5/0.089	3M1125C-ND	27.04	24.72	23.18	1125 X 1"
	1"x 1 码			3M1125C-1YD-ND	1.50	1.08	.97	1125 X 1"
	6"x 36 码			3M1125D-ND	151.20	141.75	132.30	1125 X 6"
	6"x 1 英尺			3M1125D-1FT-ND	3.06	2.19	1.97	1125 X 6"
1126	1"x 36 码	导电性 丙烯酸	3.5/0.089	3M1126C-ND	51.63	47.20	44.25	1126 X 1"
	1"x 1 码			3M1126C-1YD-ND	2.87	2.05	1.85	1126 X 1"
	6"x 36 码			3M1126D-ND	283.20	265.50	247.80	1126 X 6"
	6"x 1 英尺			3M1126D-1FT-ND	4.51	3.45	3.28	1126 X 6"
1181	1/4"x 18 码	导电性 丙烯酸	2.6/0.066	3M1181A-ND	12.22	10.47	9.08	1181 X 1/4"
	1/2"x 18 码			3M1181B-ND	24.40	20.91	18.13	1181 X 1/2"
	1"x 18 码			3M1181C-ND	48.81	44.63	41.84	1181 X 1"
	1"x 1 码			3M1181C-1YD-ND	4.26	3.26	3.10	1181 X 1"
	6"x 18 码			3M1181D-ND	230.21	215.82	201.44	1181 X 6"
	6"x 1 英尺			3M1181D-1FT-ND	6.66	5.33	4.80	1181 X 6"
1182	1"x 18 码	导电性 丙烯酸, 双面	3.5/0.089	3M1182C-ND	58.50	53.49	50.15	1182 X 1"
	1"x 1 码			3M1182C-1YD-ND	5.11	3.90	3.72	1182 X 1"
	6"x 18 码			3M1182D-ND	276.10	258.84	241.59	1182 X 6"
	6"x 1 英尺			3M1182D-1FT-ND	7.99	6.40	5.76	1182 X 6"
1194	1"x 36 码	非导电性 丙烯酸	2.6/0.066	3M1194C-ND	37.42	34.21	32.07	1194 X 1"
	1"x 1 码			3M1194C-1YD-ND	2.08	1.49	1.34	1194 X 1"
	6"x 36 码			3M1194D-ND	176.54	165.51	154.48	1194 X 6"
	6"x 1 英尺			3M1194D-1FT-ND	3.07	2.30	2.05	1194 X 6"
镀锌铜箔带								
1183	1"x 18 码	导电性 丙烯酸	2.6/0.066	3M1183C-ND	52.19	47.72	44.73	1183 X 1"
	1"x 1 码			3M1183C-1YD-ND	4.56	3.48	3.32	1183 X 1"
	6"x 18 码			3M1183D-ND	246.24	230.85	215.46	1183 X 6"
	6"x 1 英尺			3M1183D-1FT-ND	7.13	5.70	5.13	1183 X 6"
压模铜箔带								
1245	1"x 18 码	非导电性 丙烯酸	4.0/0.102	3M1245C-ND	42.25	38.63	36.21	1245 X 1"
	1"x 1 码			3M1245C-1YD-ND	4.02	3.02	2.69	1245 X 1"
	6"x 18 码			3M1245D-ND	199.39	186.93	174.47	1245 X 6"
	6"x 1 英尺			3M1245D-1FT-ND	5.77	4.62	4.16	1245 X 6"
压模铝箔带								
1267	1"x 18 码	非导电性 丙烯酸	5.0/0.127	3M1267C-ND	44.17	40.39	37.86	1267 X 1"
	1"x 1 码			3M1267C-1YD-ND	3.86	2.95	2.81	1267 X 1"
	6"x 18 码			3M1267D-ND	218.88	205.20	191.52	1267 X 6"
	6"x 1 英尺			3M1267D-1FT-ND	6.33	5.07	4.56	1267 X 6"

系列	尺寸	粘接型	总厚度 (密耳/mm)	Digi-Key 零件编号	单价			3M 零件编号
					1	5	10	
镀锌压模铜箔带								
1345	1"x 18 码	非导电性 丙烯酸	4.0/0.102	3M1345C-ND	47.43	43.36	40.65	1345 X 1"
	1"x 1 码			3M1345C-1YD-ND	4.14	3.17	3.02	1345 X 1"
	6"x 18 码			3M1345D-ND	223.78	209.79	195.81	1345 X 6"
	6"x 1 英尺			3M1345D-1FT-ND	6.48	5.18	4.67	1345 X 6"
镀银聚酯纤维带								
AG-2300	1"x 54.5 码	导电性 丙烯酸	4.3/0.110	3M2300C-ND	142.40	133.50	124.60	AG-2300 X 1"
	1"x 1 英尺			3M2300C-1FT-ND	1.91	1.36	1.23	AG-2300 X 1"
	6"x 54.5 码			3M2300D-ND	774.30	720.90	694.20	AG-2300 X 6"
	6"x 1 英尺			3M2300D-1FT-ND	8.17	6.54	5.88	AG-2300 X 6"
镀金聚酯纤维带								
AU-2190	1"x 54.5 码	导电性 丙烯酸	4.3/0.110	3M2190C-ND	138.59	129.93	121.27	AU-2190 X 1"
	1"x 1 英尺			3M2190C-1FT-ND	1.85	1.33	1.20	AU-2190 X 1"
	6"x 54.5 码			3M2190D-ND	753.59	701.63	675.64	AU-2190 X 6"
	6"x 1 英尺			3M2190D-1FT-ND	7.95	6.36	5.73	AU-2190 X 6"
镀铜防破裂聚酯纤维带								
X-7001	1"x 10.9 码	导电性 丙烯酸, 双面	4.3/0.110	3M7001C-ND	83.73	78.80	73.88	X-7001 X 1"
	1"x 1 英尺			3M7001C-1FT-ND	4.14	3.17	3.02	X-7001 X 1"
	6"x 10.9 码			3M7001D-ND	443.25	413.70	384.15	X-7001 X 6"
	6"x 1 英尺			3M7001D-1FT-ND	18.98	15.82	14.92	X-7001 X 6"
镀铜层再镀镍的防破裂聚酯纤维带								
CN-3190	1"x 54.5 码	导电性 丙烯酸	4.3/0.110	3M3190C-ND	125.57	117.72	109.88	CN 3190 X 1"
	1"x 1 英尺			3M3190C-1FT-ND	1.68	1.20	1.08	CN 3190 X 1"
	6"x 54.5 码			3M3190D-ND	682.78	635.69	612.15	CN 3190 X 6"
	6"x 1 英尺			3M3190D-1FT-ND	7.20	5.76	5.19	CN 3190 X 6"
eCAP 7830N - PET 纤维垫, XYZ-AXIS (导电密封圈)								
7830N	9.45"x 54.5 码	丙烯酸 镀镍 石墨	0.2mm	3M7830A-ND	891.03	827.39	811.48	ECAP 7830N .2
				3M7830A-1FT-ND	9.73	7.79	7.01	ECAP 7830N .2
7830N	9.45"x 54.5 码	丙烯酸 镀镍 石墨	0.3mm	3M7830B-ND	1032.58	958.83	940.39	ECAP 7830N .3
				3M7830B-1FT-ND	11.28	9.03	8.12	ECAP 7830N .3
EMI 吸收垫								
AB-5010	6"x 16.35 码	非导电性 丙烯酸	0.10mm	3M5010D-ND	845.35	784.97	769.88	AB-5010 X 6"
				3M5010D-1FT-ND	24.62	20.93	19.70	AB-5010 X 6"
AB-5020	6"x 16.35 码	非导电性 丙烯酸	0.20mm	3M5020D-ND	886.09	822.80	806.98	AB-5020 X 6"
				3M5020D-1FT-ND	25.81	21.94	20.65	AB-5020 X 6"
AB-5030	6"x 16.35 码	非导电性 丙烯酸	0.30mm	3M5030D-ND	1018.50	945.75	927.57	AB-5030 X 6"
				3M5030D-1FT-ND	29.66	25.22	23.74	AB-5030 X 6"
AB-5050	6"x 16.35 码	非导电性 丙烯酸	0.50mm	3M5050D-ND	1171.27	1087.61	1066.70	AB-5050 X 6"
				3M5050D-1FT-ND	34.11	29.00	27.29	AB-5050 X 6"
AB-5100	6"x 10.9 码	非导电性 丙烯酸	1.00mm	3M5100D-ND	998.13	926.84	909.02	AB-5100 X 6"
				3M5100D-1FT-ND	43.61	37.07	34.89	AB-5100 X 6"
高温聚酯亚胺绝缘带								
92	1/2"x 36 码	硅树脂	180°C	3M92A-ND	23.47	21.46	20.12	92 X 1/2"
				3M92B-ND	46.92	42.90	40.22	92 X 1"
1093	1/2"x 36 码	硅树脂	180°C	3M1093A-ND	23.47	21.46	20.12	1093 X 1/2"
				3M1093B-ND	46.92	42.90	40.22	1093 X 1"
1205	1/2"x 36 码	丙烯酸	155°C	3M1205A-ND	21.25	19.43	18.21	1205 X 1/2"
				3M1205B-ND	42.49	38.85	36.42	1205 X 1"
1206	1/2"x 36 码	丙烯酸	155°C	3M1206A-ND	20.42	18.68	17.51	1206 X 1/2"
				3M1206B-ND	40.86	37.36	35.03	1206 X 1"
1218	1/2"x 36 码	丙烯酸	180°C	3M1218A-ND	21.88	20.00	18.75	1218 X 1/2"
				3M1218B-ND	43.75	40.00	37.50	1218 X 1"
带分配器								
带分配器, 加重底座可容纳 6" 宽 x 6 7/8" 最大直径的带.....				3M56W-ND	76.25	69.72	65.36	P56W
带分配器, 无加重底座, 可容纳 8" 宽 x 7 1/2" 最大直径的带.....				3M448-ND	117.50	106.82	103.26	P448
带分配器, 可容纳 2" 宽 x 6" 最大直径的带 (用于转移带).....				3M712-ND	218.72	204.61	197.56	M712

B

全部产品均以美元计价。 免费电话: 10800-1527031 (China Telecom - 中国电讯) — 10800-8527031 (CNCG - 中国网通)

digikay.com.cn — 电话: (852) 3104 0500 — 传真: (852) 3104 0686

(CN082-09) 489