



陶瓷芯片天线

B

频率 (MHz)	外壳尺寸	增益 (dB) 峰值/平均值	Digi-Key 零件编号	剪切带单价			Digi-Key 零件编号	带卷		Johanson Technology 零件编号
				1	10	100		数量	价格	
2,400 - 2,500, 4,900 - 5,900	46-1	1.0 / -1.5	712-1000-1-ND	1.05	.92	.85	712-1000-2-ND	1,000	422.00	2450AD46A5400E
	50†	-0.7 / -2.6	712-1002-1-ND	2.28	1.98	1.83	712-1002-2-ND	1,000	914.00	0920AT50A080E
	18-4	0.5 / -0.5	712-1005-1-ND	.74	.64	.59	712-1005-2-ND	3,000	294.00/M	2450AT18A100E
	18-4	0.5 / -0.5	712-1006-1-ND	.39	.34	.31	712-1006-2-ND	3,000	155.00/M	2450AT18B100E
2,400 - 2,500	42-1	0 / -1.0	712-1007-1-ND	.78	.68	.63	712-1007-2-ND	2,000	312.00/M	2450AT42A100E
2,400 - 2,500	42-2	0 / -1.5	712-1008-1-ND	.84	.73	.68	712-1008-2-ND	2,000	336.00/M	2450AT42B100E
2,400 - 2,500	43-1	2.0 / 0.5	712-1009-1-ND	.83	.72	.66	712-1009-2-ND	1,000	330.00	2450AT43A100E
2,400 - 2,500	43-2	1.0 / -0.5	712-1010-1-ND	.94	.82	.76	712-1010-2-ND	1,000	377.00	2450AT43B100T
2,400 - 2,500	44-1	1.3 / 0	712-1011-1-ND	.92	.80	.74	712-1011-2-ND	1,000	366.00	2450AT44A100E
2,400 - 2,500	45-1	3.0 / 1.0	712-1012-1-ND	.96	.84	.78	712-1012-2-ND	1,000	386.00	2450AT45A100E
三频段	-†	2.0 / -4.0	712-1013-1-ND	2.28	1.98	1.83	712-1013-2-ND	1,000	913.00	2500AT52M3555E
3,100 - 10,300	-†	1.5 / -3.5	712-1014-1-ND	2.23	1.94	1.79	712-1014-2-ND	1,000	891.00	3100AT51A7200E
5,150 - 5,350	43-1	3.3 / -2.3	712-1015-1-ND	.76	.66	.61	712-1015-2-ND	1,000	304.00	5250AT43A200E
4,900 - 5,900	18-4	2.0 / -2.5	712-1016-1-ND	.66	.58	.53	712-1016-2-ND	3,000	264.00/M	5400AT18A1000E
5,725 - 5,825	43-1	3.9 / -1.5	712-1017-1-ND	1.24	1.08	.99	712-1017-2-ND	1,000	495.00	5775AT43A100E

† 请查看 Digi-Key 网站以获得具体规格。

陶瓷芯片平衡 - 不平衡变压器和平衡 - 不平衡滤波器

频率 (MHz)	外壳尺寸	阻抗 不平衡/平衡 (Ω)	相差	最大 幅度差 (dB)	Digi-Key 零件编号	剪切带单价			Digi-Key 零件编号	带卷		Johanson Technology 零件编号
						1	10	100		数量	价格	
2,300 - 2,700	14-1	50 / 50	180°±15°	1.5	712-1046-1-ND	.76	.66	.61	712-1046-2-ND	4,000	304.00/M	2500BL14M050T
2,300 - 2,700	14-1	50 / 100	180°±15°	1.5	712-1047-1-ND	.76	.66	.61	712-1047-2-ND	4,000	304.00/M	2500BL14M100T
3,300 - 3,900	14-1	50 / 50	180°±15°	1.5	712-1048-1-ND	.76	.66	.61	712-1048-2-ND	4,000	304.00/M	3600BL14M050T
3,300 - 3,900	14-1	50 / 100	180°±15°	1.5	712-1049-1-ND	.76	.66	.61	712-1049-2-ND	4,000	304.00/M	3600BL14M100T
3,400 - 4,000	15-1B	50 / 50	180°±25°	2.0	712-1050-1-ND	.51	.44	.41	712-1050-2-ND	4,000	203.00/M	3700BL15B050E
3,400 - 4,000	15-1B	50 / 100	180°±20°	1.0	712-1051-1-ND	.51	.44	.41	712-1051-2-ND	4,000	203.00/M	3700BL15B100E
3,400 - 4,000	15-1	50 / 200	180°±20°	1.0	712-1052-1-ND	.51	.44	.41	712-1052-2-ND	4,000	203.00/M	3700BL15B200E
3,100 - 4,800	14-1	50 / 100	180°±20°	1.5	712-1053-1-ND	.76	.66	.61	712-1053-2-ND	4,000	304.00/M	4000BL14U100T
5,150 - 5,350	14-1	50 / 100	180°±15°	1.5	712-1054-1-ND	.76	.66	.61	712-1054-2-ND	4,000	304.00/M	5250BL14B100T
5,150 - 5,350	15-1B	50 / 100	180°±10°	2.0	712-1055-1-ND	.51	.44	.41	712-1055-2-ND	4,000	203.00/M	5250BL15B100E
5,150 - 5,500	15-1B	50 / 50	180°±10°	2.0	712-1056-1-ND	.51	.44	.41	712-1056-2-ND	4,000	203.00/M	5325BL15B050E
4,900 - 5,875	14-1	50 / 100	180°±10°	1.5	712-1057-1-ND	.59	.52	.48	712-1057-2-ND	4,000	237.00/M	5400BL14B100T
4,900 - 5,900	15-1B	50 / 50	180°±10°	2.0	712-1058-1-ND	.51	.44	.41	712-1058-2-ND	4,000	203.00/M	5400BL15B050E
4,900 - 5,900	15-1B	50 / 100	180°±10°	2.0	712-1059-1-ND	.51	.44	.41	712-1059-2-ND	4,000	203.00/M	5400BL15B100E
4,900 - 5,875	15-1B	50 / 200	180°±10°	2.0	712-1060-1-ND	.51	.44	.41	712-1060-2-ND	4,000	203.00/M	5400BL15B200E
4,900 - 5,875	15-1A	50 / 50	180°±10°	2.0	712-1061-1-ND	.50	.43	.40	712-1061-2-ND	4,000	198.00/M	5400BL15K050E
5,150 - 5,875	15-1B	50 / 100	180°±10°	2.0	712-1062-1-ND	.36	.31	.29	712-1062-2-ND	4,000	143.00/M	5512BL15B100E
5,725 - 5,875	15-1B	50 / 100	180°±8°	0.75	712-1063-1-ND	.51	.44	.41	712-1063-2-ND	4,000	203.00/M	5800BL15B100E
2,400 - 2,500	18-4	50 / —	180°±10°	2.0 TX, 3.0 RX	712-1064-1-ND†	1.52	1.32	1.22	712-1064-2-ND†	3,000	609.00/M	2450BM18A001E
平衡 - 不平衡滤波器												
2,400 - 2,500	15-1A	50 / 50	180°±10°	1.0	712-1065-1-ND	1.01	.88	.82	712-1065-2-ND	4,000	406.00/M	2450FB15A050E
2,400 - 2,500	15†	50 / —	180°±10°	1.5	712-1066-1-ND	1.02	.89	.82	712-1066-2-ND	4,000	407.00/M	2450FB15K001E
2,400 - 2,500	39†	50 / 22	180°±8°	1.0	712-1114-1-ND	1.55	1.35	1.25	712-1114-2-ND	3,000	621.00/M	2450FB39K001E
2,400 - 2,500	39-2	50 / 50	180°±10°	1.0	712-1067-1-ND	1.04	.90	.83	712-1067-2-ND	3,000	414.00/M	2450FB39A050E
2,400 - 2,500	39-2	50 / 100	180°±10°	1.0	712-1068-1-ND	.84	.73	.68	712-1068-2-ND	3,000	336.00/M	2450FB39B100E
2,400 - 2,500	39†	50 / 100	180±8°	1.0	712-1069-1-ND	1.04	.90	.83	712-1069-2-ND	3,000	414.00/M	2450FB39C100E

† 请查看 Digi-Key 网站以获得具体规格。 ‡ 匹配网络

2.45GHz WiFi/Bluetooth 平衡 - 不平衡变压器

频率 (MHz)	外壳尺寸	阻抗 不平衡/平衡 (Ω)	相差	最大 幅度差 (dB)	Digi-Key 零件编号	剪切带单价			Digi-Key 零件编号	带卷		Johanson Technology 零件编号
						1	10	100		数量	价格	
2,400 - 2,500	14-1	50 / 50	180°±10°	2.0	712-1034-1-ND	.32	.28	.26	712-1034-2-ND	4,000	129.00/M	2450BL14B050T
2,400 - 2,500	14-1	50 / 100	180°±10°	2.0	712-1035-1-ND	.99	.86	.80	712-1035-2-ND	4,000	396.00/M	2450BL14B100T
2,400 - 2,500	14-1	50 / 200	180°±10°	2.0	712-1036-1-ND	.94	.82	.76	712-1036-2-ND	4,000	377.00/M	2450BL14B200T
2,400 - 2,500	14-1	50 / 50	180°±10°	2.0	712-1037-1-ND	.74	.65	.60	712-1037-2-ND	4,000	297.00/M	2450BL14C050T
2,400 - 2,500	14-1	50 / 100	180°±10°	1.5	712-1038-1-ND	.74	.65	.60	712-1038-2-ND	4,000	297.00/M	2450BL14C100T
2,400 - 2,500	14-1	50 / 200	180°±10°	2.0	712-1039-1-ND	.74	.65	.60	712-1039-2-ND	4,000	297.00/M	2450BL14C200T
2,400 - 2,500	15-1B	50 / 50	180°±10°	2.0	712-1040-1-ND	.36	.31	.29	712-1040-2-ND	4,000	143.00/M	2450BL15B050E
2,400 - 2,500	15-1B	50 / 100	180°±10°	2.0	712-1041-1-ND	.28	.25	.23	712-1041-2-ND	4,000	113.00/M	2450BL15B100E
2,400 - 2,500	15-1B	50 / 150	180°±10°	2.0	712-1042-1-ND	.50	.43	.40	712-1042-2-ND	4,000	198.00/M	2450BL15B150E
2,400 - 2,500	15-1B	50 / 200	180°±10°	2.0	712-1043-1-ND	.36	.31	.29	712-1043-2-ND	4,000	143.00/M	2450BL15B200E
2,400 - 2,500	15-1B	50 / 50	180°±10°	2.0	712-1044-1-ND	.36	.31	.29	712-1044-2-ND	4,000	143.00/M	2450BL15K050E
2,400 - 2,500	15-1B	50 / 100	180°±10°	2.0	712-1045-1-ND	.51	.44	.41	712-1045-2-ND	4,000	203.00/M	2450BL15K100E

平衡 - 不平衡变压器, GSM/DCS/PCS/CDMA

频率 (MHz)	外壳尺寸	阻抗 不平衡/平衡 (Ω)	相差	最大 幅度差 (dB)	Digi-Key 零件编号	剪切带单价			Digi-Key 零件编号	带卷		Johanson Technology 零件编号
						1	10	100		数量	价格	
900 - 940	41-2	50 / 50	—	—	712-1018-1-ND	1.17	1.02	.94	712-1018-2-ND	2,000	467.00/M	0918BD41B050E
460 - 470	15-3	— / 100	180°±10°	1.5	712-1019-1-ND	.99	.86	.80	712-1019-2-ND	4,000	396.00/M	0465BL15B100E
800 - 900	15-1D	50 / 200	180°±10°	1.0	712-1020-1-ND	.51	.44	.41	712-1020-2-ND	4,000	203.00/M	0866BL15C200E
851 - 941	14-1	50 / 50	180°±7°	0.7	712-1021-1-ND	1.01	.88	.82	712-1021-2-ND	4,000	406.00/M	0896BL14B050T
800 - 1,000	15-1D	50 / 50	180°±10°	2.0	712-1022-1-ND	.51	.44	.41	712-1022-2-ND	4,000	203.00/M	0900BL15C050E
800 - 1,000	18-1	50 / 100	180°±10°	2.0	712-1023-1-ND	.50	.43	.40	712-1023-2-ND	3,000	198.00/M	0900BL18B100E
800 - 1,000	18-1	50 / 200	180°±10°	2.0	712-1024-1-ND	.40	.35	.32	712-1024-2-ND	3,000	159.00/M	0900BL18B200E
1,700 - 1,900	18-1	50 / 200	180°±10°	2.0	712-1028-1-ND	.51	.44	.41	712-1028-2-ND	3,000	203.00/M	1800BL18B200E
1,700 - 2,000	15-1	50 / 50	180°±10°	2.0	712-1029-1-ND	.51	.44	.41	712-1029-2-ND	4,000	203.00/M	1850BL15A050E
1,700 - 2,000	15-1B	50 / 50	180°±10°	2.0	712-1030-1-ND	.51	.44	.41	712-1030-2-ND	4,000	203.00/M	1850BL15B050E
1,700 - 2,000	15-1B	50 / 100	180°±10°	2.0	712-1031-1-ND	.50	.43	.40	712-1031-2-ND	4,000	198.00/M	1850BL15B100E
1,700 - 2,000	15-1B	50 / 200	180°±10°	2.0	712-1032-1-ND	.50	.43	.40	712-1032-2-ND	4,000	198.00/M	1850BL15B200E

平衡 - 不平衡变压器, WiMAX 和 WCDMA

频率 (MHz)	外壳尺寸	阻抗 不平衡/平衡 (Ω)	相差	最大 幅度差 (dB)	Digi-Key 零件编号	剪切带单价			Digi-Key 零件编号	带卷		Johanson Technology 零件编号
						1						

BandPass 滤波器

频率 (MHz)	外壳尺寸	最大插入损耗 (dB)	最小回程损耗 (dB)	Digi-Key 零件编号	剪切带单价			Digi-Key 零件编号	带卷		Johanson Technology 零件编号
					1	10	100		数量	价格	
1,710 - 1,910	07-1	2.0	9.5	712-1070-1-ND	.39	.34	.32	712-1070-2-ND	10,000	151.00/M	1810BP07B200E
1,710 - 1,910	07-1	2.0	9.5	712-1071-1-ND	.41	.36	.33	712-1071-2-ND	10,000	158.00/M	1810BP07C200E
1,893 - 1,920	18-3B	1.5	9.5	712-1073-1-ND	1.17	1.02	.94	712-1073-2-ND	3,000	467.00/M	1906BP18A027E
1,893 - 1,920	39†	2.8	9.5	712-1075-1-ND	.89	.78	.72	712-1075-2-ND	3,000	357.00/M	1906BP39B027E
1,893 - 1,920	18†	2.0	9.5	712-1074-1-ND	1.17	1.02	.94	712-1074-2-ND	3,000	467.00/M	1906BP18C027E
2,400 - 2,500	07†	2.5	9.5	712-1076-1-ND	1.04	.90	.83	712-1076-2-ND	10,000	400.00/M	2450BP07A100E
2,400 - 2,500	14†	2.0	9.5	712-1077-1-ND	1.04	.90	.83	712-1077-2-ND	4,000	414.00/M	2450BP14C100T
2,400 - 2,500	15-3	2.2	9.5	712-1078-1-ND	.50	.43	.40	712-1078-2-ND	4,000	198.00/M	2450BP15B100E
2,400 - 2,500	15-3B	2.8	9.5	712-1079-1-ND	.74	.65	.60	712-1079-2-ND	4,000	297.00/M	2450BP15C100E
2,400 - 2,500	15-1F	2.6	9.5	712-1080-1-ND	.93	.81	.75	712-1080-2-ND	4,000	372.00/M	2450BP15D100E
2,400 - 2,500	15-3C	1.5	9.5	712-1081-1-ND	1.14	.99	.92	712-1081-2-ND	4,000	456.00/M	2450BP15E100E
2,450 ±50	18-1	2.5	9.5	712-1082-1-ND	1.14	.99	.92	712-1082-2-ND	3,000	455.00/M	2450BP18C100AE
2,450 ±50	18-2	2.0	9.5	712-1083-1-ND	1.14	.99	.92	712-1083-2-ND	3,000	455.00/M	2450BP18C100BE
2,450 ±50	18-3A	2.5	9.5	712-1084-1-ND	.66	.58	.53	712-1084-2-ND	3,000	264.00/M	2450BP18C100CE
2,400 - 2,500	18-3B	2.0	9.5	712-1085-1-ND	1.14	.99	.92	712-1085-2-ND	3,000	455.00/M	2450BP18C100DE
2,400 - 2,500	18-3C	2.3	9.5	712-1086-1-ND	1.14	.99	.92	712-1086-2-ND	3,000	455.00/M	2450BP18D100AE
2,450 ±50	39-1	2.5	9.5	712-1087-1-ND	.47	.41	.38	712-1087-2-ND	3,000	187.00/M	2450BP39C100AE
2,450 ±50	39-1	1.8	9.5	712-1088-1-ND	.50	.43	.40	712-1088-2-ND	3,000	198.00/M	2450BP39C100BE
2,400 - 2,500	39-1	1.5	9.5	712-1089-1-ND	.45	.39	.36	712-1089-2-ND	3,000	179.00/M	2450BP39C100CE
2,400 - 2,500	39-1	2.2	9.5	712-1090-1-ND	.51	.44	.41	712-1090-2-ND	3,000	203.00/M	2450BP39C100DE
2,400 - 2,500	39-1	2.5	9.5	712-1091-1-ND	.52	.45	.42	712-1091-2-ND	3,000	207.00/M	2450BP39D100BE
2,400 - 2,500	39-1	1.2	9.5	712-1092-1-ND	.89	.78	.72	712-1092-2-ND	3,000	357.00/M	2450BP39D100CE
2,400 - 2,500	39-1	2.6	8.9	712-1093-1-ND	.89	.78	.72	712-1093-2-ND	3,000	356.00/M	2450BP39E100AE
2,450 ±50	41-1	2.3	9.5	712-1095-1-ND	1.27	1.10	1.02	712-1095-2-ND	2,000	507.00/M	2450BP41D100AE
2,450 ±50	41-1	1.3	9.5	712-1096-1-ND	1.24	1.08	.99	712-1096-2-ND	2,000	495.00/M	2450BP41D100BE
2,450 ±50	41-1	2.5	9.5	712-1094-1-ND	1.01	.88	.82	712-1094-2-ND	2,000	406.00/M	2450BP41D100E
2,300 - 2,700	15†	2.0	9.5	712-1097-1-ND	1.24	1.08	.99	712-1097-2-ND	4,000	495.00/M	2500BP15M400E
2,500 - 2,686	44-1	2.0	9.5	712-1098-1-ND	1.78	1.54	1.43	712-1098-2-ND	2,000	710.00/M	2500BP44B186E
3,300 - 3,900	15-3B	1.8	9.5	712-1099-1-ND	.89	.78	.72	712-1099-2-ND	4,000	357.00/M	3600BP15M600E
3,100 - 4,900	15-2B	2.3	8.5	712-1100-1-ND	.99	.86	.80	712-1100-2-ND	4,000	396.00/M	4000BP15U1800E
3,100 - 7,160	18-4	1.6	9.5	712-1101-1-ND	1.17	1.02	.94	712-1101-2-ND	3,000	467.00/M	5130BP18U4060E
5,450 ±300	15-3C	2.0	—	712-1102-1-ND	.89	.78	.72	712-1102-2-ND	4,000	356.00/M	5450BP15T600E
5,150 - 5,825	15-1B	1.8	9.5	712-1103-1-ND	.89	.78	.72	712-1103-2-ND	4,000	357.00/M	5487BP15B675E
5,150 - 5,825	15-1B	1.8	9.5	712-1104-1-ND	.89	.78	.72	712-1104-2-ND	4,000	357.00/M	5487BP15C675E
5,150 - 5,875	15-3B	1.5	9.5	712-1105-1-ND	.50	.43	.40	712-1105-2-ND	4,000	198.00/M	5515BP15B725E
5,150 - 5,875	15-3B	2.5	9.5	712-1109-1-ND	.43	.38	.35	712-1109-2-ND	4,000	173.00/M	5515BP15C725E
5,150 - 5,875	15-1B	2.8	9.5	712-1106-1-ND	.89	.78	.72	712-1106-2-ND	4,000	357.00/M	5515BP15B730E
4,900 - 5,875	15-3B	1.5	9.5	712-1107-1-ND	.50	.43	.40	712-1107-2-ND	4,000	198.00/M	5515BP15B975E
4,900 - 5,875	15-3B	2.0	8.5	712-1136-1-ND	.50	.43	.40	712-1136-2-ND	4,000	198.00/M	5515BP15C975E
4,900 - 5,920	15-3B	1.5	9.5	712-1108-1-ND	.50	.43	.40	712-1108-2-ND	4,000	198.00/M	5515BP15C1020E

† 请查看 Digi-Key 网站以获得具体规格。

陶瓷芯片双工器

频率 (MHz)	外壳尺寸	低频带衰减 (dB)	高频带衰减 (dB)	回程损耗 (dB)	Digi-Key 零件编号	剪切带单价			Digi-Key 零件编号	带卷		Johanson Technology 零件编号
						1	10	100		数量	价格	
2,450 - 5,400	15-1D	0.70	19	9.5	712-1110-1-ND	.99	.86	.80	712-1110-2-ND	4,000	396.00/M	2450DP15F5400E

EMI 滤波器

段数	外壳尺寸	截止频率 (MHz)	最小损耗 (dB)	Digi-Key 零件编号	剪切带单价			Digi-Key 零件编号	带卷		Johanson Technology 零件编号
					1	10	100		数量	价格	
4	18-4	200	在 1500 - 3000MHz 时为 10	712-1111-1-ND	.84	.73	.68	712-1111-2-ND	3,000	337.00/M	0200FA18A0200E
4	15†	400	在 800 - 1000MHz 时为 20	712-1112-1-ND	.51	.44	.41	712-1112-2-ND	4,000	203.00/M	0400FA15A0400E
4	18-4	400	在 1500 - 2500MHz 时为 10	712-1113-1-ND	.84	.73	.68	712-1113-2-ND	3,000	337.00/M	0400FA18A0400E

† 请查看 Digi-Key 网站以获得具体规格。

高通和低通滤波器

频率 (MHz)	外壳尺寸	最大插入损耗 (dB)	最小回程损耗 (dB)	Digi-Key 零件编号	剪切带单价			Digi-Key 零件编号	带卷		Johanson Technology 零件编号
					1	10	100		数量	价格	
高通滤波器											
2,450 - 2,500	14-1B	1.3	14	712-1115-1-ND	.78	.68	.63	712-1115-2-ND	4,000	311.00/M	2450HP14A100T
2,450 - 2,500	15†	0.85	9.5	712-1116-1-ND	.86	.75	.69	712-1116-2-ND	4,000	345.00/M	2450HP15A100E
低通滤波器											
0 - 500	15-1A	0.7	9.5	712-1117-1-ND	.91	.80	.74	712-1117-2-ND	4,000	365.00/M	0500LP15A500E
824 - 915	14-1	0.6	10.9	712-1118-1-ND	.91	.80	.74	712-1118-2-ND	4,000	365.00/M	0869LP14A090T
824 - 960	07-1	0.7	9.5	712-1119-1-ND	1.14	.99	.92	712-1119-2-ND	10,000	441.00/M	0892LP07A136E
880 - 915	18-2	0.6	10.9	712-1120-1-ND	1.17	1.02	.94	712-1120-2-ND	3,000	467.00/M	0898LP18A035E
902 - 928	15-2A	0.65	9.5	712-1121-1-ND	.89	.78	.72	712-1121-2-ND	4,000	356.00/M	0915LP15A026E
902 - 928	15-2A	0.5	14.0	712-1122-1-ND	.91	.80	.74	712-1122-2-ND	4,000	365.00/M	0915LP15B026E
1,710 - 1,785	18-2	0.6	10.9	712-1123-1-ND	.96	.84	.78	712-1123-2-ND	3,000	386.00/M	1748LP18A075E
1,710 - 1,910	07-1	0.5	10.9	712-1124-1-ND	.76	.66	.61	712-1124-2-ND	10,000	294.00/M	1810LP07A200E
1,710 - 1,910	07-1	0.6	9.5	712-1125-1-ND	.51	.44	.41	712-1125-2-ND	10,000	196.00/M	1810LP07B200E
1,710 - 1,910	14-1	0.6	11.7	712-1126-1-ND	.91	.80	.74	712-1126-2-ND	4,000	365.00/M	1810LP14A200T
1,850 - 1,910	14-1	0.6	11.7	712-1127-1-ND	.91	.80	.74	712-1127-2-ND	4,000	365.00/M	1880LP14A060T
2,400 - 2,483	18-2	0.6	10.9	712-1128-1-ND	.94	.82	.76	712-1128-2-ND	3,000	376.00/M	2442LP18A083E
2,400 - 2,500	14-1	0.5	14.0	712-1129-1-ND	.91	.80	.74	712-1129-2-ND	4,000	365.00/M	2450LP14A100T
2,400 - 2,500	14-1	0.5	14.0	712-1130-1-ND	.89	.78	.72	712-1130-2-ND	4,000	357.00/M	2450LP14B100T
2,400 - 2,500	14-1	0.6	11.7	712-1131-1-ND	.89	.78	.72	712-1131-2-ND	4,000	356.00/M	2450LP14C100T
2,400 - 2,500	14-1	0.5	10.0	712-1132-1-ND	.46	.40	.37	712-1132-2-ND	4,000	183.00/M	2450LP15A050E
2,400 - 2,500	15†	0.5	10.9	712-1133-1-ND	.93	.81	.75	712-1133-2-ND	4,000	372.00/M	2450LP15B050E
3,400 - 3,700	14-1	0.65	14.0	712-1134-1-ND	.51	.44	.41	712-1134-2-ND	4,000	203.00/M	3550LP14A300T
5,150 - 5,875	15-2A	0.6	10.9	712-1135-1-ND	.46	.40	.37	712-1135-2-ND	4,000	183.00/M	5515LP15A730E

† 请查看 Digi-Key 网站以获得具体规格。

(转下页)

全部产品均以美元计价。 免费电话: 10800-1527031 (China Telecom - 中国电信) — 10800-8527031 (CNCG - 中国网通)

digkey.com.cn — 电话: (852) 3104 0500 — 传真: (852) 3104 0686