



陶瓷芯片天线

B

频率 (MHz)	外壳尺寸	增益 (dB) 峰值/平均值	Digi-Key 零件编号	剪切带单价			Digi-Key 零件编号	带卷		Johanson Technology 零件编号
				1	10	100		数量	价格	
2,400 - 2,500, 4,900 - 5,900	46-1	1.0 / -1.5	712-1000-1-ND	1.05	.92	.85	712-1000-2-ND	1,000	422.00	2450AD46A5400E
	50†	-0.7 / -2.6	712-1002-1-ND	2.28	1.98	1.83	712-1002-2-ND	1,000	914.00	0920AT50A080E
	18-4	0.5 / -0.5	712-1005-1-ND	.74	.64	.59	712-1005-2-ND	3,000	294.00/M	2450AT18A100E
	18-4	0.5 / -0.5	712-1006-1-ND	.39	.34	.31	712-1006-2-ND	3,000	155.00/M	2450AT18B100E
2,400 - 2,500	42-1	0 / -1.0	712-1007-1-ND	.78	.68	.63	712-1007-2-ND	2,000	312.00/M	2450AT42A100E
2,400 - 2,500	42-2	0 / -1.5	712-1008-1-ND	.84	.73	.68	712-1008-2-ND	2,000	336.00/M	2450AT42B100E
2,400 - 2,500	43-1	2.0 / 0.5	712-1009-1-ND	.83	.72	.66	712-1009-2-ND	1,000	330.00	2450AT43A100E
2,400 - 2,500	43-2	1.0 / -0.5	712-1010-1-ND	.94	.82	.76	712-1010-2-ND	1,000	377.00	2450AT43B100T
2,400 - 2,500	44-1	1.3 / 0	712-1011-1-ND	.92	.80	.74	712-1011-2-ND	1,000	366.00	2450AT44A100E
2,400 - 2,500	45-1	3.0 / 1.0	712-1012-1-ND	.96	.84	.78	712-1012-2-ND	1,000	386.00	2450AT45A100E
三频段	-†	2.0 / -4.0	712-1013-1-ND	2.28	1.98	1.83	712-1013-2-ND	1,000	913.00	2500AT52M3555E
3,100 - 10,300	-†	1.5 / -3.5	712-1014-1-ND	2.23	1.94	1.79	712-1014-2-ND	1,000	891.00	3100AT51A7200E
5,150 - 5,350	43-1	3.3 / -2.3	712-1015-1-ND	.76	.66	.61	712-1015-2-ND	1,000	304.00	5250AT43A200E
4,900 - 5,900	18-4	2.0 / -2.5	712-1016-1-ND	.66	.58	.53	712-1016-2-ND	3,000	264.00/M	5400AT18A1000E
5,725 - 5,825	43-1	3.9 / -1.5	712-1017-1-ND	1.24	1.08	.99	712-1017-2-ND	1,000	495.00	5775AT43A100E

† 请查看 Digi-Key 网站以获得具体规格。

陶瓷芯片平衡 - 不平衡变压器和平衡 - 不平衡滤波器

频率 (MHz)	外壳尺寸	阻抗 不平衡/平衡 (Ω)	相差	最大 幅度差 (dB)	Digi-Key 零件编号	剪切带单价			Digi-Key 零件编号	带卷		Johanson Technology 零件编号
						1	10	100		数量	价格	
2,300 - 2,700	14-1	50 / 50	180°±15°	1.5	712-1046-1-ND	.76	.66	.61	712-1046-2-ND	4,000	304.00/M	2500BL14M050T
2,300 - 2,700	14-1	50 / 100	180°±15°	1.5	712-1047-1-ND	.76	.66	.61	712-1047-2-ND	4,000	304.00/M	2500BL14M100T
3,300 - 3,900	14-1	50 / 50	180°±15°	1.5	712-1048-1-ND	.76	.66	.61	712-1048-2-ND	4,000	304.00/M	3600BL14M050T
3,300 - 3,900	14-1	50 / 100	180°±15°	1.5	712-1049-1-ND	.76	.66	.61	712-1049-2-ND	4,000	304.00/M	3600BL14M100T
3,400 - 4,000	15-1B	50 / 50	180°±25°	2.0	712-1050-1-ND	.51	.44	.41	712-1050-2-ND	4,000	203.00/M	3700BL15B050E
3,400 - 4,000	15-1B	50 / 100	180°±20°	1.0	712-1051-1-ND	.51	.44	.41	712-1051-2-ND	4,000	203.00/M	3700BL15B100E
3,400 - 4,000	15-1	50 / 200	180°±20°	1.0	712-1052-1-ND	.51	.44	.41	712-1052-2-ND	4,000	203.00/M	3700BL15B200E
3,100 - 4,800	14-1	50 / 100	180°±20°	1.5	712-1053-1-ND	.76	.66	.61	712-1053-2-ND	4,000	304.00/M	4000BL14U100T
5,150 - 5,350	14-1	50 / 100	180°±15°	1.5	712-1054-1-ND	.76	.66	.61	712-1054-2-ND	4,000	304.00/M	5250BL14B100T
5,150 - 5,350	15-1B	50 / 100	180°±10°	2.0	712-1055-1-ND	.51	.44	.41	712-1055-2-ND	4,000	203.00/M	5250BL15B100E
5,150 - 5,500	15-1B	50 / 50	180°±10°	2.0	712-1056-1-ND	.51	.44	.41	712-1056-2-ND	4,000	203.00/M	5325BL15B050E
4,900 - 5,875	14-1	50 / 100	180°±10°	1.5	712-1057-1-ND	.59	.52	.48	712-1057-2-ND	4,000	237.00/M	5400BL14B100T
4,900 - 5,900	15-1B	50 / 50	180°±10°	2.0	712-1058-1-ND	.51	.44	.41	712-1058-2-ND	4,000	203.00/M	5400BL15B050E
4,900 - 5,900	15-1B	50 / 100	180°±10°	2.0	712-1059-1-ND	.51	.44	.41	712-1059-2-ND	4,000	203.00/M	5400BL15B100E
4,900 - 5,875	15-1B	50 / 200	180°±10°	2.0	712-1060-1-ND	.51	.44	.41	712-1060-2-ND	4,000	203.00/M	5400BL15B200E
4,900 - 5,875	15-1A	50 / 50	180°±10°	2.0	712-1061-1-ND	.50	.43	.40	712-1061-2-ND	4,000	198.00/M	5400BL15K050E
5,150 - 5,875	15-1B	50 / 100	180°±10°	2.0	712-1062-1-ND	.36	.31	.29	712-1062-2-ND	4,000	143.00/M	5512BL15B100E
5,725 - 5,875	15-1B	50 / 100	180°±8°	0.75	712-1063-1-ND	.51	.44	.41	712-1063-2-ND	4,000	203.00/M	5800BL15B100E
2,400 - 2,500	18-4	50 / —	180°±10°	2.0 TX, 3.0 RX	712-1064-1-ND†	1.52	1.32	1.22	712-1064-2-ND†	3,000	609.00/M	2450BM18A001E
平衡 - 不平衡滤波器												
2,400 - 2,500	15-1A	50 / 50	180°±10°	1.0	712-1065-1-ND	1.01	.88	.82	712-1065-2-ND	4,000	406.00/M	2450FB15A050E
2,400 - 2,500	15†	50 / —	180°±10°	1.5	712-1066-1-ND	1.02	.89	.82	712-1066-2-ND	4,000	407.00/M	2450FB15K001E
2,400 - 2,500	39†	50 / 22	180°±8°	1.0	712-1114-1-ND	1.55	1.35	1.25	712-1114-2-ND	3,000	621.00/M	2450FB39K001E
2,400 - 2,500	39-2	50 / 50	180°±10°	1.0	712-1067-1-ND	1.04	.90	.83	712-1067-2-ND	3,000	414.00/M	2450FB39A050E
2,400 - 2,500	39-2	50 / 100	180°±10°	1.0	712-1068-1-ND	.84	.73	.68	712-1068-2-ND	3,000	336.00/M	2450FB39B100E
2,400 - 2,500	39†	50 / 100	180±8°	1.0	712-1069-1-ND	1.04	.90	.83	712-1069-2-ND	3,000	414.00/M	2450FB39C100E

† 请查看 Digi-Key 网站以获得具体规格。 ‡ 匹配网络

2.45GHz WiFi/Bluetooth 平衡 - 不平衡变压器

频率 (MHz)	外壳尺寸	阻抗 不平衡/平衡 (Ω)	相差	最大 幅度差 (dB)	Digi-Key 零件编号	剪切带单价			Digi-Key 零件编号	带卷		Johanson Technology 零件编号
						1	10	100		数量	价格	
2,400 - 2,500	14-1	50 / 50	180°±10°	2.0	712-1034-1-ND	.32	.28	.26	712-1034-2-ND	4,000	129.00/M	2450BL14B050T
2,400 - 2,500	14-1	50 / 100	180°±10°	2.0	712-1035-1-ND	.99	.86	.80	712-1035-2-ND	4,000	396.00/M	2450BL14B100T
2,400 - 2,500	14-1	50 / 200	180°±10°	2.0	712-1036-1-ND	.94	.82	.76	712-1036-2-ND	4,000	377.00/M	2450BL14B200T
2,400 - 2,500	14-1	50 / 50	180°±10°	2.0	712-1037-1-ND	.74	.65	.60	712-1037-2-ND	4,000	297.00/M	2450BL14C050T
2,400 - 2,500	14-1	50 / 100	180°±10°	1.5	712-1038-1-ND	.74	.65	.60	712-1038-2-ND	4,000	297.00/M	2450BL14C100T
2,400 - 2,500	14-1	50 / 200	180°±10°	2.0	712-1039-1-ND	.74	.65	.60	712-1039-2-ND	4,000	297.00/M	2450BL14C200T
2,400 - 2,500	15-1B	50 / 50	180°±10°	2.0	712-1040-1-ND	.36	.31	.29	712-1040-2-ND	4,000	143.00/M	2450BL15B050E
2,400 - 2,500	15-1B	50 / 100	180°±10°	2.0	712-1041-1-ND	.28	.25	.23	712-1041-2-ND	4,000	113.00/M	2450BL15B100E
2,400 - 2,500	15-1B	50 / 150	180°±10°	2.0	712-1042-1-ND	.50	.43	.40	712-1042-2-ND	4,000	198.00/M	2450BL15B150E
2,400 - 2,500	15-1B	50 / 200	180°±10°	2.0	712-1043-1-ND	.36	.31	.29	712-1043-2-ND	4,000	143.00/M	2450BL15B200E
2,400 - 2,500	15-1B	50 / 50	180°±10°	2.0	712-1044-1-ND	.36	.31	.29	712-1044-2-ND	4,000	143.00/M	2450BL15K050E
2,400 - 2,500	15-1B	50 / 100	180°±10°	2.0	712-1045-1-ND	.51	.44	.41	712-1045-2-ND	4,000	203.00/M	2450BL15K100E

平衡 - 不平衡变压器, GSM/DCS/PCS/CDMA

频率 (MHz)	外壳尺寸	阻抗 不平衡/平衡 (Ω)	相差	最大 幅度差 (dB)	Digi-Key 零件编号	剪切带单价			Digi-Key 零件编号	带卷		Johanson Technology 零件编号
						1	10	100		数量	价格	
900 - 940	41-2	50 / 50	—	—	712-1018-1-ND	1.17	1.02	.94	712-1018-2-ND	2,000	467.00/M	0918BD41B050E
460 - 470	15-3	— / 100	180°±10°	1.5	712-1019-1-ND	.99	.86	.80	712-1019-2-ND	4,000	396.00/M	0465BL15B100E
800 - 900	15-1D	50 / 200	180°±10°	1.0	712-1020-1-ND	.51	.44	.41	712-1020-2-ND	4,000	203.00/M	0866BL15C200E
851 - 941	14-1	50 / 50	180°±7°	0.7	712-1021-1-ND	1.01	.88	.82	712-1021-2-ND	4,000	406.00/M	0896BL14B050T
800 - 1,000	15-1D	50 / 50	180°±10°	2.0	712-1022-1-ND	.51	.44	.41	712-1022-2-ND	4,000	203.00/M	0900BL15C050E
800 - 1,000	18-1	50 / 100	180°±10°	2.0	712-1023-1-ND	.50	.43	.40	712-1023-2-ND	3,000	198.00/M	0900BL18B100E
800 - 1,000	18-1	50 / 200	180°±10°	2.0	712-1024-1-ND	.40	.35	.32	712-1024-2-ND	3,000	159.00/M	0900BL18B200E
1,700 - 1,900	18-1	50 / 200	180°±10°	2.0	712-1028-1-ND	.51	.44	.41	712-1028-2-ND	3,000	203.00/M	1800BL18B200E
1,700 - 2,000	15-1	50 / 50	180°±10°	2.0	712-1029-1-ND	.51	.44	.41	712-1029-2-ND	4,000	203.00/M	1850BL15A050E
1,700 - 2,000	15-1B	50 / 50	180°±10°	2.0	712-1030-1-ND	.51	.44	.41	712-1030-2-ND	4,000	203.00/M	1850BL15B050E
1,700 - 2,000	15-1B	50 / 100	180°±10°	2.0	712-1031-1-ND	.50	.43	.40	712-1031-2-ND	4,000	198.00/M	1850BL15B100E
1,700 - 2,000	15-1B	50 / 200	180°±10°	2.0	712-1032-1-ND	.50	.43	.40	712-1032-2-ND	4,000	198.00/M	1850BL15B200E

平衡 - 不平衡变压器, WiMAX 和 WCDMA

频率 (MHz)	外壳尺寸	阻抗 不平衡/平衡 (Ω)	相差	最大 幅度差 (dB)	Digi-Key 零件编号	剪切带单价			Digi-Key 零件编号	带卷		Johanson Technology 零件编号
						1	10	100		数量		