

BandPass 滤波器

| 频率 (MHz) | 外壳尺寸 | 最大插入损耗 (dB) | 最小回程损耗 (dB) | Digi-Key 零件编号 | 剪切带单价 | | | Digi-Key 零件编号 | 带卷 | | Johanson Technology 零件编号 |
|---------------|-------|-------------|-------------|---------------|-------|------|------|---------------|--------|----------|--------------------------|
| | | | | | 1 | 10 | 100 | | 数量 | 价格 | |
| 1,710 - 1,910 | 07-1 | 2.0 | 9.5 | 712-1070-1-ND | .39 | .34 | .32 | 712-1070-2-ND | 10,000 | 151.00/M | 1810BP07B200E |
| 1,710 - 1,910 | 07-1 | 2.0 | 9.5 | 712-1071-1-ND | .41 | .36 | .33 | 712-1071-2-ND | 10,000 | 158.00/M | 1810BP07C200E |
| 1,893 - 1,920 | 18-3B | 1.5 | 9.5 | 712-1073-1-ND | 1.17 | 1.02 | .94 | 712-1073-2-ND | 3,000 | 467.00/M | 1906BP18A027E |
| 1,893 - 1,920 | 39† | 2.8 | 9.5 | 712-1075-1-ND | .89 | .78 | .72 | 712-1075-2-ND | 3,000 | 357.00/M | 1906BP39B027E |
| 1,893 - 1,920 | 18† | 2.0 | 9.5 | 712-1074-1-ND | 1.17 | 1.02 | .94 | 712-1074-2-ND | 3,000 | 467.00/M | 1906BP18C027E |
| 2,400 - 2,500 | 07† | 2.5 | 9.5 | 712-1076-1-ND | 1.04 | .90 | .83 | 712-1076-2-ND | 10,000 | 400.00/M | 2450BP07A100E |
| 2,400 - 2,500 | 14† | 2.0 | 9.5 | 712-1077-1-ND | 1.04 | .90 | .83 | 712-1077-2-ND | 4,000 | 414.00/M | 2450BP14C100T |
| 2,400 - 2,500 | 15-3 | 2.2 | 9.5 | 712-1078-1-ND | .50 | .43 | .40 | 712-1078-2-ND | 4,000 | 198.00/M | 2450BP15B100E |
| 2,400 - 2,500 | 15-3B | 2.8 | 9.5 | 712-1079-1-ND | .74 | .65 | .60 | 712-1079-2-ND | 4,000 | 297.00/M | 2450BP15C100E |
| 2,400 - 2,500 | 15-1F | 2.6 | 9.5 | 712-1080-1-ND | .93 | .81 | .75 | 712-1080-2-ND | 4,000 | 372.00/M | 2450BP15D100E |
| 2,400 - 2,500 | 15-3C | 1.5 | 9.5 | 712-1081-1-ND | 1.14 | .99 | .92 | 712-1081-2-ND | 4,000 | 456.00/M | 2450BP15E100E |
| 2,450 ±50 | 18-1 | 2.5 | 9.5 | 712-1082-1-ND | 1.14 | .99 | .92 | 712-1082-2-ND | 3,000 | 455.00/M | 2450BP18C100AE |
| 2,450 ±50 | 18-2 | 2.0 | 9.5 | 712-1083-1-ND | 1.14 | .99 | .92 | 712-1083-2-ND | 3,000 | 455.00/M | 2450BP18C100BE |
| 2,450 ±50 | 18-3A | 2.5 | 9.5 | 712-1084-1-ND | .66 | .58 | .53 | 712-1084-2-ND | 3,000 | 264.00/M | 2450BP18C100CE |
| 2,400 - 2,500 | 18-3B | 2.0 | 9.5 | 712-1085-1-ND | 1.14 | .99 | .92 | 712-1085-2-ND | 3,000 | 455.00/M | 2450BP18C100DE |
| 2,400 - 2,500 | 18-3C | 2.3 | 9.5 | 712-1086-1-ND | 1.14 | .99 | .92 | 712-1086-2-ND | 3,000 | 455.00/M | 2450BP18D100AE |
| 2,450 ±50 | 39-1 | 2.5 | 9.5 | 712-1087-1-ND | .47 | .41 | .38 | 712-1087-2-ND | 3,000 | 187.00/M | 2450BP39C100AE |
| 2,450 ±50 | 39-1 | 1.8 | 9.5 | 712-1088-1-ND | .50 | .43 | .40 | 712-1088-2-ND | 3,000 | 198.00/M | 2450BP39C100BE |
| 2,400 - 2,500 | 39-1 | 1.5 | 9.5 | 712-1089-1-ND | .45 | .39 | .36 | 712-1089-2-ND | 3,000 | 179.00/M | 2450BP39C100CE |
| 2,400 - 2,500 | 39-1 | 2.2 | 9.5 | 712-1090-1-ND | .51 | .44 | .41 | 712-1090-2-ND | 3,000 | 203.00/M | 2450BP39C100DE |
| 2,400 - 2,500 | 39-1 | 2.5 | 9.5 | 712-1091-1-ND | .52 | .45 | .42 | 712-1091-2-ND | 3,000 | 207.00/M | 2450BP39D100BE |
| 2,400 - 2,500 | 39-1 | 1.2 | 9.5 | 712-1092-1-ND | .89 | .78 | .72 | 712-1092-2-ND | 3,000 | 357.00/M | 2450BP39D100CE |
| 2,400 - 2,500 | 39-1 | 2.6 | 8.9 | 712-1093-1-ND | .89 | .78 | .72 | 712-1093-2-ND | 3,000 | 356.00/M | 2450BP39E100AE |
| 2,450 ±50 | 41-1 | 2.3 | 9.5 | 712-1095-1-ND | 1.27 | 1.10 | 1.02 | 712-1095-2-ND | 2,000 | 507.00/M | 2450BP41D100AE |
| 2,450 ±50 | 41-1 | 1.3 | 9.5 | 712-1096-1-ND | 1.24 | 1.08 | .99 | 712-1096-2-ND | 2,000 | 495.00/M | 2450BP41D100BE |
| 2,450 ±50 | 41-1 | 2.5 | 9.5 | 712-1094-1-ND | 1.01 | .88 | .82 | 712-1094-2-ND | 2,000 | 406.00/M | 2450BP41D100E |
| 2,300 - 2,700 | 15† | 2.0 | 9.5 | 712-1097-1-ND | 1.24 | 1.08 | .99 | 712-1097-2-ND | 4,000 | 495.00/M | 2500BP15M400E |
| 2,500 - 2,686 | 44-1 | 2.0 | 9.5 | 712-1098-1-ND | 1.78 | 1.54 | 1.43 | 712-1098-2-ND | 2,000 | 710.00/M | 2503BP44B186E |
| 3,300 - 3,900 | 15-3B | 1.8 | 9.5 | 712-1099-1-ND | .89 | .78 | .72 | 712-1099-2-ND | 4,000 | 357.00/M | 3600BP15M600E |
| 3,100 - 4,900 | 15-2B | 2.3 | 8.5 | 712-1100-1-ND | .99 | .86 | .80 | 712-1100-2-ND | 4,000 | 396.00/M | 4000BP15U1800E |
| 3,100 - 7,160 | 18-4 | 1.6 | 9.5 | 712-1101-1-ND | 1.17 | 1.02 | .94 | 712-1101-2-ND | 3,000 | 467.00/M | 5130BP18U4060E |
| 5,450 ±300 | 15-3C | 2.0 | — | 712-1102-1-ND | .89 | .78 | .72 | 712-1102-2-ND | 4,000 | 356.00/M | 5450BP15T600E |
| 5,150 - 5,825 | 15-1B | 1.8 | 9.5 | 712-1103-1-ND | .89 | .78 | .72 | 712-1103-2-ND | 4,000 | 357.00/M | 5487BP15B675E |
| 5,150 - 5,825 | 15-1B | 1.8 | 9.5 | 712-1104-1-ND | .89 | .78 | .72 | 712-1104-2-ND | 4,000 | 357.00/M | 5487BP15C675E |
| 5,150 - 5,875 | 15-3B | 1.5 | 9.5 | 712-1105-1-ND | .50 | .43 | .40 | 712-1105-2-ND | 4,000 | 198.00/M | 5515BP15B725E |
| 5,150 - 5,875 | 15-3B | 2.5 | 9.5 | 712-1109-1-ND | .43 | .38 | .35 | 712-1109-2-ND | 4,000 | 173.00/M | 5515BP15C725E |
| 5,150 - 5,875 | 15-1B | 2.8 | 9.5 | 712-1106-1-ND | .89 | .78 | .72 | 712-1106-2-ND | 4,000 | 357.00/M | 5515BP15B730E |
| 4,900 - 5,875 | 15-3B | 1.5 | 9.5 | 712-1107-1-ND | .50 | .43 | .40 | 712-1107-2-ND | 4,000 | 198.00/M | 5515BP15B975E |
| 4,900 - 5,875 | 15-3B | 2.0 | 8.5 | 712-1136-1-ND | .50 | .43 | .40 | 712-1136-2-ND | 4,000 | 198.00/M | 5515BP15C975E |
| 4,900 - 5,920 | 15-3B | 1.5 | 9.5 | 712-1108-1-ND | .50 | .43 | .40 | 712-1108-2-ND | 4,000 | 198.00/M | 5515BP15C1020E |

† 请查看 Digi-Key 网站以获得具体规格。

陶瓷芯片双工器

| 频率 (MHz) | 外壳尺寸 | 低频带衰减 (dB) | 高频带衰减 (dB) | 回程损耗 (dB) | Digi-Key 零件编号 | 剪切带单价 | | | Digi-Key 零件编号 | 带卷 | | Johanson Technology 零件编号 |
|---------------|-------|------------|------------|-----------|---------------|-------|-----|-----|---------------|-------|----------|--------------------------|
| | | | | | | 1 | 10 | 100 | | 数量 | 价格 | |
| 2,450 - 5,400 | 15-1D | 0.70 | 19 | 9.5 | 712-1110-1-ND | .99 | .86 | .80 | 712-1110-2-ND | 4,000 | 396.00/M | 2450DP15F5400E |

EMI 滤波器

| 段数 | 外壳尺寸 | 截止频率 (MHz) | 最小损耗 (dB) | Digi-Key 零件编号 | 剪切带单价 | | | Digi-Key 零件编号 | 带卷 | | Johanson Technology 零件编号 |
|----|------|------------|------------------------|---------------|-------|-----|-----|---------------|-------|----------|--------------------------|
| | | | | | 1 | 10 | 100 | | 数量 | 价格 | |
| 4 | 18-4 | 200 | 在 1500 - 3000MHz 时为 10 | 712-1111-1-ND | .84 | .73 | .68 | 712-1111-2-ND | 3,000 | 337.00/M | 0200FA18A0200E |
| 4 | 15† | 400 | 在 800 - 1000MHz 时为 20 | 712-1112-1-ND | .51 | .44 | .41 | 712-1112-2-ND | 4,000 | 203.00/M | 0400FA15A0400E |
| 4 | 18-4 | 400 | 在 1500 - 2500MHz 时为 10 | 712-1113-1-ND | .84 | .73 | .68 | 712-1113-2-ND | 3,000 | 337.00/M | 0400FA18A0400E |

† 请查看 Digi-Key 网站以获得具体规格。

高通和低通滤波器

| 频率 (MHz) | 外壳尺寸 | 最大插入损耗 (dB) | 最小回程损耗 (dB) | Digi-Key 零件编号 | 剪切带单价 | | | Digi-Key 零件编号 | 带卷 | | Johanson Technology 零件编号 |
|---------------|-------|-------------|-------------|---------------|-------|------|-----|---------------|--------|----------|--------------------------|
| | | | | | 1 | 10 | 100 | | 数量 | 价格 | |
| 高通滤波器 | | | | | | | | | | | |
| 2,450 - 2,500 | 14-1B | 1.3 | 14 | 712-1115-1-ND | .78 | .68 | .63 | 712-1115-2-ND | 4,000 | 311.00/M | 2450HP14A100T |
| 2,450 - 2,500 | 15† | 0.85 | 9.5 | 712-1116-1-ND | .86 | .75 | .69 | 712-1116-2-ND | 4,000 | 345.00/M | 2450HP15A100E |
| 低通滤波器 | | | | | | | | | | | |
| 0 - 500 | 15-1A | 0.7 | 9.5 | 712-1117-1-ND | .91 | .80 | .74 | 712-1117-2-ND | 4,000 | 365.00/M | 0500LP15A500E |
| 824 - 915 | 14-1 | 0.6 | 10.9 | 712-1118-1-ND | .91 | .80 | .74 | 712-1118-2-ND | 4,000 | 365.00/M | 0869LP14A090T |
| 824 - 960 | 07-1 | 0.7 | 9.5 | 712-1119-1-ND | 1.14 | .99 | .92 | 712-1119-2-ND | 10,000 | 441.00/M | 0892LP07A136E |
| 880 - 915 | 18-2 | 0.6 | 10.9 | 712-1120-1-ND | 1.17 | 1.02 | .94 | 712-1120-2-ND | 3,000 | 467.00/M | 0898LP18A035E |
| 902 - 928 | 15-2A | 0.65 | 9.5 | 712-1121-1-ND | .89 | .78 | .72 | 712-1121-2-ND | 4,000 | 356.00/M | 0915LP15A026E |
| 902 - 928 | 15-2A | 0.5 | 14.0 | 712-1122-1-ND | .91 | .80 | .74 | 712-1122-2-ND | 4,000 | 365.00/M | 0915LP15B026E |
| 1,710 - 1,785 | 18-2 | 0.6 | 10.9 | 712-1123-1-ND | .96 | .84 | .78 | 712-1123-2-ND | 3,000 | 386.00/M | 1748LP18A075E |
| 1,710 - 1,910 | 07-1 | 0.5 | 10.9 | 712-1124-1-ND | .76 | .66 | .61 | 712-1124-2-ND | 10,000 | 294.00/M | 1810LP07A200E |
| 1,710 - 1,910 | 07-1 | 0.6 | 9.5 | 712-1125-1-ND | .51 | .44 | .41 | 712-1125-2-ND | 10,000 | 196.00/M | 1810LP07B200E |
| 1,710 - 1,910 | 14-1 | 0.6 | 11.7 | 712-1126-1-ND | .91 | .80 | .74 | 712-1126-2-ND | 4,000 | 365.00/M | 1810LP14A200T |
| 1,850 - 1,910 | 14-1 | 0.6 | 11.7 | 712-1127-1-ND | .91 | .80 | .74 | 712-1127-2-ND | 4,000 | 365.00/M | 1880LP14A060T |
| 2,400 - 2,483 | 18-2 | 0.6 | 10.9 | 712-1128-1-ND | .94 | .82 | .76 | 712-1128-2-ND | 3,000 | 376.00/M | 2442LP18A083E |
| 2,400 - 2,500 | 14-1 | 0.5 | 14.0 | 712-1129-1-ND | .91 | .80 | .74 | 712-1129-2-ND | 4,000 | 365.00/M | 2450LP14A100T |
| 2,400 - 2,500 | 14-1 | 0.5 | 14.0 | 712-1130-1-ND | .89 | .78 | .72 | 712-1130-2-ND | 4,000 | 357.00/M | 2450LP14B100T |
| 2,400 - 2,500 | 14-1 | 0.6 | 11.7 | 712-1131-1-ND | .89 | .78 | .72 | 712-1131-2-ND | 4,000 | 356.00/M | 2450LP14C100T |
| 2,400 - 2,500 | 14-1 | 0.5 | 10.0 | 712-1132-1-ND | .46 | .40 | .37 | 712-1132-2-ND | 4,000 | 183.00/M | 2450LP15A050E |
| 2,400 - 2,500 | 15† | 0.5 | 10.9 | 712-1133-1-ND | .93 | .81 | .75 | 712-1133-2-ND | 4,000 | 372.00/M | 2450LP15B050E |
| 3,400 - 3,700 | 14-1 | 0.65 | 14.0 | 712-1134-1-ND | .51 | .44 | .41 | 712-1134-2-ND | 4,000 | 203.00/M | 3550LP14A300T |
| 5,150 - 5,875 | 15-2A | 0.6 | 10.9 | 712-1135-1-ND | .46 | .40 | .37 | 712-1135-2-ND | 4,000 | 183.00/M | 5515LP15A730E |

† 请查看 Digi-Key 网站以获得具体规格。

(转下页)

全部产品均以美元计价。 免费电话: 10800-1527031 (China Telecom - 中国电信) — 10800-8527031 (CNCG - 中国网通)

digkey.com.cn — 电话: (852) 3104 0500 — 传真: (852) 3104 0686