

T. I. 零件编号	Digi-Key 零件编号	说明	封装	1	25	100	
TLCC34CN	296-10293-5-ND	四路差分比较器	Quad Differential Comparator	14-Dip	1.17	.98	.78
TLCC34CPW	296-10294-5-ND	四路差分比较器	Quad Differential Comparator	14-TSSOP	1.17	.98	.78
TLCC34ID	296-10295-5-ND	四路差分比较器	Quad Differential Comparator	14-SOIC	1.38	1.15	.92
TLV1391CDBVR	296-10492-1-ND	差分比较器	Differential Comparator	SOT-23-5	.75	.63	.50
TLV1391CDBVR	296-10492-2-ND	差分比较器	Differential Comparator	SOT-23-5	975.00/3,000		
TLV2352ID	296-10517-5-ND	双路差分比较器	Dual Differential Comparator	8-SOIC	1.90	1.52	1.14
TLV2352IP	296-10518-5-ND	双路差分比较器	Dual Differential Comparator	8-Dip	1.90	1.52	1.14
TLV2352IPWR	296-10519-1-ND	双路差分比较器	Dual Differential Comparator	8-TSSOP	1.90	1.52	1.14
TLV2352IPWR	296-10519-2-ND	双路差分比较器	Dual Differential Comparator	8-TSSOP	1976.00/2,000		
TLV2354ID	296-10520-5-ND	四路差分比较器	Quad Differential Comparator	14-SOIC	2.68	2.15	1.67
TLV2354IN	296-10521-5-ND	四路差分比较器	Quad Differential Comparator	14-Dip	2.68	2.15	1.67
TLV2354IPWR	296-10522-1-ND	四路差分比较器	Quad Differential Comparator	14-TSSOP	2.68	2.15	1.67
TLV2354IPWR	296-10522-2-ND	四路差分比较器	Quad Differential Comparator	14-TSSOP	3034.00/2,000		

T. I. 零件编号	Digi-Key 零件编号	说明	封装	1	25	100	
音频编解码器							
PCM2900E	296-13034-5-ND	带 USB 接口的立体声音频编解码器	Stereo Audio CODEC w/USB Interface	28-SSOP	8.30	6.64	5.61
PCM2901E	296-12985-5-ND	带 USB 接口、单端模拟输入/输出及 S/PDIF 的立体声音频编解码器	Stereo Audio CODEC w/USB Interface, Single Ended Analog I/O and S/PDIF	28-SSOP	8.30	6.64	5.61
PCM2902E	296-12986-5-ND	带 USB 接口、单端模拟输入/输出及 S/PDIF 的立体声音频编解码器	Stereo Audio CODEC w/USB Interface, Single Ended Analog I/O and S/PDIF	28-SSOP	9.00	7.20	6.08
PCM2903E	296-12987-5-ND	带 USB 接口、单端模拟输入/输出及 S/PDIF 的立体声音频编解码器	Stereo Audio CODEC w/USB Interface, Single Ended Analog I/O and S/PDIF	28-SSOP	9.00	7.20	6.08
PCM29040B	296-13478-5-ND	带 USB 接口、单端模拟输入/输出及 S/PDIF 的立体声音频编解码器	Stereo Audio CODEC w/USB Interface, Single Ended Analog I/O and S/PDIF	28-SSOP	8.30	6.64	5.61
PCM2906DB	296-13479-5-ND	带 USB 接口、单端模拟输入/输出及 S/PDIF 的立体声音频编解码器	Stereo Audio CODEC w/USB Interface, Single Ended Analog I/O and S/PDIF	28-SSOP	9.00	7.20	6.08
PCM3000E	PCM3000E-ND	立体声音频编解码器, 18 位, 3 线路接口	Stereo Audio CODEC 18-Bit, 3-Wire Interface	28-SSOP	6.90	5.52	4.66
PCM3001E	PCM3001E-ND	立体声音频编解码器, 18 位, 可编程引脚	Stereo Audio CODEC 18-Bit, Pin Programmable	28-SSOP	6.90	5.52	4.66
PCM3002E	PCM3002E-ND	20 位立体声音频编解码器, 软件控制	20-Bit, Stereo CODEC, Software Control	24-SOIC	6.90	5.52	4.66
PCM3003E	PCM3003E-ND	20 位立体声音频编解码器, 硬件控制	20-Bit, Stereo CODEC, Hardware Control	24-SOIC	6.90	5.52	4.66
PCM3006T/2K	296-21639-1-ND	16 位单端模拟输入/输出立体声音频编解码器	16-Bit, Single Ended Analog In/Out Stereo Audio CODEC	24-SSOP	6.90	5.52	4.66
PCM3006T/2K	296-21639-2-ND	16 位单端模拟输入/输出立体声音频编解码器	16-Bit, Single Ended Analog In/Out Stereo Audio CODEC	24-SSOP	8626.00/2,000		
PCM3008T	PCM3008T-ND	16 位低功率/电压立体声音频编解码器	16-Bit, Low Power/Voltage Stereo CODEC	16-TSSOP	6.20	4.96	4.19
PCM3010DB	296-14398-5-ND	24 位立体声音频编解码器	24-Bit, Stereo Audio CODEC	24-SSOP	8.00	6.40	5.40
PCM3052ARTF	296-21239-1-ND	24 位 96kHz 立体声音频编解码器	24-Bit, 96kHz Stereo Audio CODEC	32-QFN	5.40	4.32	3.36
PCM3052ARTF	296-21239-2-ND	24 位 96kHz 立体声音频编解码器	24-Bit, 96kHz Stereo Audio CODEC	32-QFN	798.00/250		
PCM3060PW	296-21668-5-ND	24 位 96/192kHz 异步立体声音频编解码器	24-Bit, 96/192kHz Async Stereo Audio CODEC	28-TSSOP	4.39	3.51	2.73
PCM3500E	PCM3500E-ND	语音/调制解调器编解码器	Voice/Modem CODEC	24-SSOP	5.30	4.24	3.58
PCM3501E	PCM3501E-ND	语音/调制解调器编解码器	Voice/Modem CODEC	24-SSOP	5.30	4.24	3.58
PCM3793ARHBR	296-21514-1-ND	16 位低功率立体声音频编解码器	16-Bit, Low Pwr Stereo Audio CODEC	32-QFN	9.00	7.20	6.08
PCM3793ARHBR	296-21514-2-ND	16 位低功率立体声音频编解码器	16-Bit, Low Pwr Stereo Audio CODEC	32-QFN	16740.00/3,000		
PCM3793RHBR	296-21240-1-ND	16 位低功率立体声音频编解码器	16-Bit, Low Pwr Stereo Audio CODEC	32-QFN	9.00	7.20	6.08
PCM3793RHBR	296-21240-2-ND	16 位低功率立体声音频编解码器	16-Bit, Low Pwr Stereo Audio CODEC	32-QFN	16740.00/3,000		
PCM3794ARHBR	296-21538-1-ND	16 位低功率立体声音频编解码器	16-Bit, Low Pwr Stereo Audio CODEC	32-QFN	8.50	6.80	5.74
PCM3794ARHBR	296-21538-2-ND	16 位低功率立体声音频编解码器	16-Bit, Low Pwr Stereo Audio CODEC	32-QFN	15810.00/3,000		
PCM3794ARHBT	296-21786-1-ND	16 位低功率立体声音频编解码器	16-Bit, Low Pwr Stereo Audio CODEC	32-QFN	9.40	7.52	6.35
PCM3794RHBT	296-21786-2-ND	16 位低功率立体声音频编解码器	16-Bit, Low Pwr Stereo Audio CODEC	32-QFN	1527.50/250		
PCM3794RHBR	296-21241-1-ND	16 位低功率立体声音频编解码器	16-Bit, Low Pwr Stereo Audio CODEC	32-QFN	8.50	6.80	5.74
PCM3794RHBR	296-21241-2-ND	16 位低功率立体声音频编解码器	16-Bit, Low Pwr Stereo Audio CODEC	32-QFN	15810.00/3,000		
TLV320AIC22CPT	296-13661-1-ND	双路因特网语音协定 (VoIP) 编解码器	Dual Voice Over Internet Protocol (VoIP) CODEC	48-LQFP	7.04	5.64	4.76
TLV320AIC23BRHDR	296-15121-1-ND	带集成耳机放大器的立体声音频编解码器	Stereo Audio CODEC with Integrated Headphone Amp	28-QFN	6.70	5.36	4.53
TLV320AIC23BRHDR	296-15121-2-ND	带集成耳机放大器的立体声音频编解码器	Stereo Audio CODEC with Integrated Headphone Amp	28-QFN	12462.00/3,000		
TLV320AIC28IRHB	296-18911-ND	低功率立体声音频编解码器	Low Power Stereo Audio CODEC	32-QFN	6.00	4.80	4.05
TLV320AIC1110ZDER	296-21865-1-ND	PCM 编解码器	PCM CODEC	80-BGA	6.60	5.28	4.46
TLV320AIC1110ZDER	296-21865-2-ND	PCM 编解码器	PCM CODEC	80-BGA	10230.00/2,500		
TLV320AIC3101RHBT	296-21969-1-ND	低功率立体声音频编解码器	LP Stereo Audio CODEC	32-QFN	7.50	6.00	5.07
TLV320AIC3101RHBT	296-21969-2-ND	低功率立体声音频编解码器	LP Stereo Audio CODEC	32-QFN	1218.75/250		
TSC2111IRGZT	296-20663-1-ND	音频编解码器	Audio CODEC	48-QFN	9.08	8.18	7.25
TSC2111IRGZT	296-20663-2-ND	音频编解码器	Audio CODEC	48-QFN	1737.25/250		
中心局编解码器							
TP3064BN	296-10792-5-ND	PCM 编解码器/滤波系统 (u 规则)	PCM CODEC/Filtering System (u-law)	20-Dip	2.75	2.20	1.71
TP3067AN	296-10794-5-ND	PCM 编解码器和滤波器 (A 规则)	PCM CODEC and Filter (A-law)	20-Dip	2.75	2.20	1.71
TP3067BDW	296-10795-5-ND	PCM 编解码器和滤波器 (A 规则)	PCM CODEC and Filter (A-law)	20-SOIC	2.75	2.20	1.71
TP3067BN	296-10796-5-ND	PCM 编解码器和滤波器 (A 规则)	PCM CODEC and Filter (A-law)	20-Dip	2.75	2.20	1.71
TP13054ADW	296-10774-5-ND	PCM 编解码器/滤波系统 (u 规则)	PCM CODEC/Filtering System (u-law)	16-SOIC	3.08	2.47	1.92
TP13054BDW	296-10775-5-ND	PCM 编解码器/滤波系统 (u 规则)	PCM CODEC/Filtering System (u-law)	16-SOIC	3.08	2.47	1.92
TP13054BN	296-10776-5-ND	PCM 编解码器/滤波系统 (u 规则)	PCM CODEC/Filtering System (u-law)	16-Dip	3.08	2.47	1.92
TP13057BDW	296-10777-5-ND	PCM 编解码器和滤波器 (A 规则)	PCM CODEC and Filter (A-law)	16-SOIC	3.08	2.47	1.92
TP13057BN	296-10778-5-ND	PCM 编解码器和滤波器 (A 规则)	PCM CODEC and Filter (A-law)	16-Dip	3.08	2.47	1.92
TP13064BDW	296-10779-5-ND	PCM 编解码器/滤波系统 (u 规则)	PCM CODEC/Filtering System (u-law)	20-SOIC	3.08	2.47	1.92
TP13067BN	296-10781-5-ND	PCM 编解码器和滤波器 (A 规则)	PCM CODEC and Filter (A-law)	20-Dip	3.08	2.47	1.92
IrDA							
TIR1000IPWR	296-6574-1-ND	独立 IrDA 编码器/解码器	Standalone IrDA Encoder/Decoder	8-TSSOP	2.59	2.07	1.61
TIR1000IPWR	296-6574-2-ND	独立 IrDA 编码器/解码器	Standalone IrDA Encoder/Decoder	8-TSSOP	2932.00/2,000		
TIR1000PSR	296-6572-1-ND	独立 IrDA 编码器/解码器	Standalone IrDA Encoder/Decoder	8-SOP	2.45	1.96	1.47
TIR1000PSR	296-6572-2-ND	独立 IrDA 编码器/解码器	Standalone IrDA Encoder/Decoder	8-SOP	2548.00/2,000		
TIR1000PWR	296-6573-1-ND	独立 IrDA 编码器/解码器	Standalone IrDA Encoder/Decoder	8-TSSOP	2.45	1.96	1.47
TIR1000PWR	296-6573-2-ND	独立 IrDA 编码器/解码器	Standalone IrDA Encoder/Decoder	8-TSSOP	2548.00/2,000		
铃声信号控制器							
UCC2750DW	296-2602-5-ND	源铃声信号控制器	Source Ringer Controller	28-SOIC	12.41	11.18	9.91
UCC2751D	296-2603-5-ND	单线铃声信号发生器控制器	Single Line Ring Generator Controller	16-SOIC	5.29	4.23	3.29
UCC2752D	296-2604-5-ND	谐振铃声信号发生器控制器	Resonant Ring Generator Controller	16-SOIC	5.29	4.23	3.29
UCC3750N	296-11454-5-ND	源铃声信号控制器	Source Ringer Controller	28-Dip	9.16	8.25	7.32
UCC3750DW	296-2605-5-ND	源铃声信号控制器	Source Ringer Controller	28-SOIC	9.16	8.25	7.32
UCC3751D	296-2606-5-ND	单线铃声信号发生器控制器	Single Line Ring Generator Controller	16-SOIC	4.39	3.51	2.73
UCC3751N	296-11455-5-ND	单线铃声信号发生器控制器	Single Line Ring Generator Controller	16-Dip	4.39	3.51	2.73
UCC3752D	296-2607-5-ND	谐振铃声信号发生器控制器	Resonant Ring Generator Controller	16-SOIC	4.39	3.51	2.73
UCC3752N	296-11456-5-ND	谐振铃声信号发生器控制器	Resonant Ring Generator Controller	16-Dip	4.39	3.51	2.73
SONET 收发器							
SLK2501IPZP	296-12281-ND	OC-48 SONET/SDH 多速率收发器	OC-48 SONET/SDH Multirate Transceiver	100-HTQFP	55.13	51.45	47.78
SLK2511AIPZP	296-16997-ND	SONET/SDH 多速率收发器	SONET/SDH Multirate Transceiver	100-HTQFP	55.13	51.45	47.78
SLK2511BPZP	296-21543-ND	SONET/SDH 多速率收发器	SONET/SDH Multirate Transceiver	100-HTQFP	55.13	51.45	47.78
SLK2511IPZP	296-13035-5-ND	SONET/SDH 多速率收发器	SONET/SDH Multirate Transceiver	100-HTQFP	55.13	51.45	47.78
SLK2701IPZP	296-12543-ND	2.7Gbps SONET/SDH 多速率收发器	2.7Gbps SONET/SDH Multirate Transceiver	100-HTQFP	55.13	51.45	47.78
SLK2721IPZP	296-13036-5-ND	带增强抖动容错的 SONET/SDH 多速率收发器	SONET/SDH Multirate Transceiver with Enhanced Jitter Tolerance	100-HTQFP	55.13	51.45	47.78

(转下页)

★ 欢迎来电查询, 大批量订购, 价格优惠! ★

全部产品均以美元计价。 免费电话: 10800-1527031 (China Telecom - 中国电信) — 10800-8527031 (CNCG - 中国网通)

digikkey.com.cn — 电话: (852) 3104 0500 — 传真: (852) 3104 0686