

T. I. 零件编号	Digi-Key 零件编号	说明	封装	单价★		
				1	25	100
SN75451BDR	296-14960-1-ND	双路高速外设驱动器	Dual High Speed Peripheral Driver	8-SOIC	.55	.44 .33
SN75451BDR	296-14960-2-ND	双路高速外设驱动器	Dual High Speed Peripheral Driver	8-SOIC		372.50/2,500
SN75451BP	296-1746-5-ND	双路高速外设驱动器	Dual High Speed Peripheral Driver	8-Dip	.55	.44 .33
SN75452BDR	296-14961-1-ND	双路高速外设驱动器	Dual High Speed Peripheral Driver	8-SOIC	.55	.44 .33
SN75452BDR	296-14961-2-ND	双路高速外设驱动器	Dual High Speed Peripheral Driver	8-SOIC		372.50/2,500
SN75452BP	296-1747-5-ND	双路高速外设驱动器	Dual High Speed Peripheral Driver	8-Dip	.55	.44 .33
SN75453BD	296-9913-5-ND	双路高速外设驱动器	Dual High Speed Peripheral Driver	8-SOIC	.80	.60 .45
SN75453BDR	296-9913-1-ND	双路高速外设驱动器	Dual High Speed Peripheral Driver	8-SOIC	.55	.44 .33
SN75453BDR	296-9913-2-ND	双路高速外设驱动器	Dual High Speed Peripheral Driver	8-SOIC		372.50/2,500
SN75453BP	296-1748-5-ND	双路高速外设驱动器	Dual High Speed Peripheral Driver	8-Dip	.55	.44 .33
SN75454BP	296-9914-5-ND	双路高速外设驱动器	Dual High Speed Peripheral Driver	8-Dip	.80	.60 .45
SN75462P	296-9915-5-ND	双路外设驱动器	Dual Peripheral Driver	8-Dip	1.14	.95 .76
SN75463P	296-9916-5-ND	双路外设驱动器	Dual Peripheral Driver	8-Dip	1.35	1.13 .90
SN75468N	296-9917-5-ND	高压达林顿晶体管阵列	High Voltage Darlington Transistor Array	16-Dip	.62	.47 .35
SN75469N	296-9918-5-ND	高压达林顿晶体管阵列	High Voltage Darlington Transistor Array	16-Dip	.80	.60 .45
SN75471P	296-9919-5-ND	双路外设驱动器	Dual Peripheral Driver	8-Dip	.80	.60 .45
SN75477DR	296-14962-1-ND	双路外设驱动器	Dual Peripheral Driver	8-SOIC	.80	.60 .45
SN75477DR	296-14962-2-ND	双路外设驱动器	Dual Peripheral Driver	8-SOIC		650.00/2,500
SN75477P	296-9920-5-ND	双路外设驱动器	Dual Peripheral Driver	8-Dip	.66	.50 .38
SN75472P	296-1749-5-ND	双路外设驱动器	Dual Peripheral Driver	8-Dip	.66	.50 .38
TLC5904PZP	296-2378-ND	恒流 LED 驱动器	Constant Current LED Driver	100-HTQFP	7.40	5.92 5.00
TLC5905PAP	296-2379-ND	恒流 LED 驱动器	Constant Current LED Driver	64-HTQFP	5.70	4.56 3.85
TLC5911PZP	296-2381-ND	恒流 LED 驱动器	Constant Current LED Driver	100-HTQFP	9.00	7.20 6.08
TLC5917DR	296-21995-1-ND	8 位恒定电流 LED 汇集驱动器	8-Bit Constant Current LED Sink Driver	16-SOIC	1.50	1.20 .90
TLC5917DR	296-21995-2-ND	8 位恒定电流 LED 汇集驱动器	8-Bit Constant Current LED Sink Driver	16-SOIC		1920.00/2,500
TLC5917IPWR	296-21996-1-ND	8 位恒定电流 LED 汇集驱动器	8-Bit Constant Current LED Sink Driver	16-TSSOP	1.50	1.20 .90
TLC5917IPWR	296-21996-2-ND	8 位恒定电流 LED 汇集驱动器	8-Bit Constant Current LED Sink Driver	16-TSSOP		1560.00/2,000
TLC5920DL	296-10348-5-ND	带移位寄存器的 LED 驱动器	LED Driver with Shift Register	48-SSOP	2.48	1.98 1.54
TLC5921DAP	296-10349-5-ND	带移位寄存器的 LED 驱动器	LED Driver with Shift Register	32-HTSSOP	2.68	2.15 1.67
TLC5922DAP	296-15843-5-ND	16 通道 LED 驱动器	16-Channel LED Driver	32-HTSSOP	3.04	2.43 1.89
TLC5923DAP	296-17731-5-ND	16 通道 LED 驱动器	16-Channel LED Driver	32-HTSSOP	3.15	2.52 1.96
TLC5923RHB	296-19333-ND	16 通道 LED 驱动器	16-Channel LED Driver	32-QFN	3.15	2.52 1.96
TLC5923RHB	296-19334-1-ND	16 通道 LED 驱动器	16-Channel LED Driver	32-QFN	3.49	2.79 2.17
TLC5923RHB	296-19334-2-ND	16 通道 LED 驱动器	16-Channel LED Driver	32-QFN		515.50/250
TLC5924DAP	296-20736-ND	16 通道 LED 驱动器	16-Channel LED Driver	32-HTSSOP	3.38	2.70 2.10
TLC5924RHB	296-20779-1-ND	16 通道 LED 驱动器	16-Channel LED Driver	32-QFN	3.71	2.97 2.31
TLC5924RHB	296-20779-2-ND	16 通道 LED 驱动器	16-Channel LED Driver	32-QFN		548.75/250
TLC5930PWP	296-15631-5-ND	12 通道 LED 驱动器	12-Channel LED Driver	24-HTSSOP	8.30	6.64 5.61
TLC5940PWP	296-17733-5-ND	16 通道 LED 驱动器	16-Channel LED Driver	28-HTSSOP	4.28	3.42 2.66
TLC5940RHB	296-18021-ND	16 通道 LED 驱动器	16-Channel LED Driver	32-QFN	4.28	3.42 2.66
TLC5940RHB	296-21251-1-ND	16 通道 LED 驱动器	16-Channel LED Driver	32-QFN	4.28	3.42 2.66
TLC5940RHB	296-21251-2-ND	16 通道 LED 驱动器	16-Channel LED Driver	32-QFN		7182.00/3,000
TLC5941EVM-156	296-21104-ND	TLC5941 的评估模块	Evaluation Module for TLC5941	—	101.00	—
TLC5941PWP	296-18617-5-ND	16 通道 LED 驱动器	16-Channel LED Driver	28-HTSSOP	3.71	2.97 2.31
TLC5941RHB	296-18618-ND	16 通道 LED 驱动器	16-Channel LED Driver	32-QFN	3.71	2.97 2.31
TLC5941RHB	296-21105-1-ND	16 通道 LED 驱动器	16-Channel LED Driver	32-QFN	4.50	3.60 2.80
TLC5941RHB	296-21105-2-ND	16 通道 LED 驱动器	16-Channel LED Driver	32-QFN		665.00/250
TLC5945PWP	296-21862-1-ND	16 通道 LED 驱动器	16-Channel LED Driver	28-HTSSOP	3.94	3.15 2.45
TLC5945PWP	296-21862-2-ND	16 通道 LED 驱动器	16-Channel LED Driver	28-HTSSOP		4462.00/2,000
TLC5945RHB	296-21863-1-ND	16 通道 LED 驱动器	16-Channel LED Driver	32-QFN	3.94	3.15 2.45
TLC5945RHB	296-21863-2-ND	16 通道 LED 驱动器	16-Channel LED Driver	32-QFN		6615.00/3,000
TPIC2810D	296-13746-5-ND	带 I ² C 接口的 8 位 LED 驱动器	8-Bit LED Driver with I ² C Interface	16-SOIC	2.15	1.72 1.29
TPIC2810DG4	296-21426-5-ND	带 I ² C 接口的 8 位 LED 驱动器	8-Bit LED Driver with I ² C Interface	16-SOIC	2.15	1.72 1.29
TPL9201PWP	296-21442-1-ND	8 通道继电器驱动器	8-Channel Relay Driver	20-HTSSOP	1.44	1.20 .96
TPL9201PWP	296-21442-2-ND	8 通道继电器驱动器	8-Channel Relay Driver	20-HTSSOP		1276.00/2,000
ULN2003AD	296-1368-5-ND	达林顿晶体管阵列	Darlington Transistor Array	16-SOIC	.53	.42 .32
ULN2003ADR	296-1368-1-ND	达林顿晶体管阵列	Darlington Transistor Array	16-SOIC	.50	.40 .30
ULN2003ADR	296-1368-2-ND	达林顿晶体管阵列	Darlington Transistor Array	16-SOIC		335.00/2,500
ULN2003AIDR	296-15407-1-ND	达林顿晶体管阵列	Darlington Transistor Array	16-SOIC	.64	.48 .36
ULN2003AIDR	296-15407-2-ND	达林顿晶体管阵列	Darlington Transistor Array	16-SOIC		520.00/2,500
ULN2003AIN	296-16971-5-ND	达林顿晶体管阵列	Darlington Transistor Array	16-Dip	.64	.48 .36
ULN2003AIPWR	296-17785-1-ND	达林顿晶体管阵列	Darlington Transistor Array	16-TSSOP	.64	.48 .36
ULN2003AIPWR	296-17785-2-ND	达林顿晶体管阵列	Darlington Transistor Array	16-TSSOP		426.00/2,000
ULN2003AN	296-1979-5-ND	达林顿晶体管阵列	Darlington Transistor Array	16-Dip	.55	.44 .33
ULN2004AD	296-12965-5-ND	高压高电流达林顿晶体管阵列	High-Voltage, High-Current Darlington Transistor Array	16-SOIC	.53	.42 .32
ULN2004ADR	296-15067-1-ND	高压高电流达林顿晶体管阵列	High-Voltage, High-Current Darlington Transistor Array	16-SOIC	.53	.42 .32
ULN2004ADR	296-15067-2-ND	高压高电流达林顿晶体管阵列	High-Voltage, High-Current Darlington Transistor Array	16-SOIC		355.00/2,500
ULN2004AIDR	296-17022-1-ND	高压高电流达林顿晶体管阵列	High-Voltage, High-Current Darlington Transistor Array	16-SOIC	.64	.48 .36
ULN2004AIDR	296-17022-2-ND	高压高电流达林顿晶体管阵列	High-Voltage, High-Current Darlington Transistor Array	16-SOIC		520.00/2,500
ULN2004AII	296-17051-5-ND	高压高电流达林顿晶体管阵列	High-Voltage, High-Current Darlington Transistor Array	16-Dip	.64	.48 .36
ULN2004AINSR	296-17023-1-ND	高压高电流达林顿晶体管阵列	High-Voltage, High-Current Darlington Transistor Array	16-SOP	.64	.48 .36
ULN2004AINSR	296-17023-2-ND	高压高电流达林顿晶体管阵列	High-Voltage, High-Current Darlington Transistor Array	16-SOP		426.00/2,000
ULN2004AM	296-1980-5-ND	达林顿晶体管阵列	Darlington Transistor Array	16-Dip	.55	.44 .33
ULN2803AN	296-19046-5-ND	达林顿晶体管阵列	Darlington Transistor Array	18-Dip	1.35	1.13 .90
ULN2803ADWR	296-15777-1-ND	达林顿晶体管阵列	Darlington Transistor Array	18-SOIC	.88	.66 .50
ULN2803ADWR	296-15777-2-ND	达林顿晶体管阵列	Darlington Transistor Array	18-SOIC		586.00/2,000
ULQ2003ADR	296-11570-1-ND	高压高电流达林顿晶体管阵列	High-Voltage, High-Current Darlington Transistor Array	16-SOIC	1.08	.90 .72
ULQ2003ADR	296-11570-2-ND	高压高电流达林顿晶体管阵列	High-Voltage, High-Current Darlington Transistor Array	16-SOIC		1170.00/2,500
ULQ2003AQRQ1	296-21568-1-ND	高压高电流达林顿晶体管阵列	High-Voltage, High-Current Darlington Transistor Array	16-SOIC	2.45	1.97 1.53
ULQ2003AQRQ1	296-21568-2-ND	高压高电流达林顿晶体管阵列	High-Voltage, High-Current Darlington Transistor Array	16-SOIC		3432.50/2,500
ULQ2003ATDQ1	296-14394-5-ND	高压高电流达林顿晶体管阵列	High-Voltage, High-Current Darlington Transistor Array	16-SOIC	2.25	1.80 1.35
ULQ2003ATDQ1	296-14395-1-ND	高压高电流达林顿晶体管阵列	High-Voltage, High-Current Darlington Transistor Array	16-SOIC	2.38	1.90 1.43
ULQ2003ATDQ1	296-14395-2-ND	高压高电流达林顿晶体管阵列	High-Voltage, High-Current Darlington Transistor Array	16-SOIC		3040.00/2,500
ULQ2004ADR	296-13535-1-ND	高压高电流达林顿晶体管阵列	High-Voltage High-Current Darlington Transistor Array	16-SOIC	1.08	.90 .72
ULQ2004ADR	296-13535-2-ND	高压高电流达林顿晶体管阵列	High-Voltage High-Current Darlington Transistor Array	16-SOIC		1170.00/2,500
ULQ2004AN	296-15700-5-ND	高压高电流达林顿晶体管阵列	High-Voltage High-Current Darlington Transistor Array	16-Dip	.74	.56 .42

T. I. 零件编号	Digi-Key 零件编号	说明	封装	单价★		
				1	25	100
<i>模拟多路复用器/乘法器</i>						
MPC506AP	MPC506AP-ND	单端 16 通道/差分 8 通道 CMOS	Single Ended 16-Ch./Diff. 8-Ch. CMOS	28-Dip	9.03	—
MPC506AP	MPC506AU-ND	单端 16 通道/差分 8 通道 CMOS	Single Ended 16-Ch./Diff. 8-Ch. CMOS	28-SOIC	9.03	—
MPC507AP	MPC507AP-ND	单端 16 通道/差分 8 通道 CMOS	Single Ended 16-Ch./Diff. 8-Ch. CMOS	28-Dip	9.03	—
MPC507AP	MPC507AU-ND	单端 16 通道/差分 8 通道 CMOS	Single Ended 16-Ch./Diff. 8-Ch. CMOS	28-SOIC	9.03	—
MPC508AP	MPC508AP-ND	8 通道/4 通道 CMOS 模拟多路复用器	8-Ch./4-Ch. CMOS Analog Multiplexer	16-Dip	5.32	—
MPC508AU	MPC508AU-ND	单端 16 通道/差分 8 通道 CMOS	Single Ended 16-Ch./Diff. 8-Ch. CMOS	16-SOIC	5.32	—
MPC509AP	MPC509AP-ND	单端 8 通道/差分 4 通道 CMOS	Single Ended 8-Ch./Diff. 4-Ch. CMOS	16-Dip	5.32	—
MPC509AU	MPC509AU-ND	单端 8 通道/差分 4 通道 CMOS	Single Ended 8-Ch./Diff. 4-Ch. CMOS	16-SOIC	5.90	—
MPY634KP	MPY634KP-ND	宽带精密模拟乘法器	Wideband Precision Analog Multiplier	14-Dip	17.63	—
MPY634KU	MPY634KU-ND	宽带精密模拟乘法器	Wideband Precision Analog Multiplier	16-SOIC	19.73	—

★ 欢迎来电查询, 大批量订购, 价格优惠! ★

全部产品均以美元计价。 免费电话: 10800-1527031 (China Telecom - 中国电讯) — 10800-8527031 (CNCG - 中国网通)