

T. I. 零件编号	Digi-Key 零件编号	说明	封装	单价★		
				1	25	100
TPIC6A596NE	296-9009-5-ND	电源 8 位移寄存器	Power 8-Bit Shift Register	20-Dip	2.70	2.16 1.68
TPIC6B259DW	296-9010-5-ND	电源 8 位可寻址锁存器	Power 8-Bit Addressable Latch	20-SOIC	1.70	1.36 1.02
TPIC6B259N	296-9011-5-ND	电源 8 位可寻址锁存器	Power 8-Bit Addressable Latch	20-Dip	1.70	1.36 1.02
TPIC6B273DW	296-1350-5-ND	电源八路 D 型开关	Power Octal D-Type Switch	20-SOIC	1.70	1.36 1.02
TPIC6B273DWR	296-1350-1-ND	电源八路 D 型锁存器	Power Octal D-Type Latch	20-SOIC	1.70	1.36 1.02
TPIC6B273DWR	296-1350-2-ND	电源八路 D 型锁存器	Power Octal D-Type Latch	20-SOIC	1768.00/2,000	
TPIC6B273N	296-9012-5-ND	电源八路 D 型锁存器	Power Octal D-Type Latch	20-Dip	1.70	1.36 1.02
TPIC6B595DW	296-1351-5-ND	电源 8 位移寄存器	Power 8-Bit Shift Register	20-SOIC	1.26	1.05 .84
TPIC6B595DWG4	296-1955-5-ND	电源 8 位移寄存器	Power 8-Bit Shift Register	20-SOIC	1.26	1.05 .84
TPIC6B595DWR	296-1351-1-ND	电源 8 位移寄存器	Power 8-Bit Shift Register	20-SOIC	1.41	1.18 .94
TPIC6B595DWR	296-1351-2-ND	电源 8 位移寄存器	Power 8-Bit Shift Register	20-SOIC	1250.00/2,000	
TPIC6B595N	296-1956-5-ND	电源 8 位移寄存器	Power 8-Bit Shift Register	20-Dip	1.41	1.18 .94
TPIC6B596DW	296-9013-5-ND	电源 8 位移寄存器	Power 8-Bit Shift Register	20-SOIC	1.26	1.05 .84
TPIC6C395D	296-2019-5-ND	电源 8 位移寄存器	Power 8-Bit Shift Register	16-SOIC	1.11	.93 .74
TPIC6C395N	296-2020-5-ND	电源 8 位移寄存器	Power 8-Bit Shift Register	16-Dip	1.17	.98 .78
TPIC6C595PW	296-21143-5-ND	电源 8 位移寄存器	Power 8-Bit Shift Register	16-TSSOP	1.11	.93 .74
TPIC6C596D	296-9014-5-ND	电源 8 位移寄存器	Power 8-Bit Shift Register	16-SOIC	.99	.83 .66
TPIC6C596DR	296-19451-1-ND	电源 8 位移寄存器	Power 8-Bit Shift Register	16-SOIC	1.05	.88 .70
TPIC6C596DR	296-19451-2-ND	电源 8 位移寄存器	Power 8-Bit Shift Register	16-SOIC	1137.50/2,500	
TPIC6C596N	296-9015-5-ND	电源 8 位移寄存器	Power 8-Bit Shift Register	16-Dip	1.05	.88 .70
TPIC6C596PW	296-19605-5-ND	电源 8 位移寄存器	Power 8-Bit Shift Register	16-TSSOP	1.02	.85 .68
TPIC43T01DA	296-10866-5-ND	三相无刷电机转速控制器	Three-Phase Brushless Motor RPM Controller	38-TSSOP	5.06	4.05 3.15
TPIC44L01DB	296-10867-5-ND	4 通道串行/并行低端 Pre-FET 驱动器	4-Channel Serial/Parallel Low-Side Pre-FET Driver	24-SSOP	2.00	1.60 1.20
TPIC44L02DB	296-10868-5-ND	4 通道串行/并行低端 Pre-FET 驱动器	4-Channel Serial/Parallel Low-Side Pre-FET Driver	24-SSOP	2.00	1.60 1.20
TPIC46L01DB	296-10869-5-ND	6 通道串行/并行低端 Pre-FET 驱动器	6-Channel Serial/Parallel Low-Side Pre-FET Driver	28-SSOP	2.25	1.80 1.40
TPIC46L02DB	296-10870-5-ND	6 通道串行/并行低端 Pre-FET 驱动器	6-Channel Serial/Parallel Low-Side Pre-FET Driver	28-SSOP	2.25	1.80 1.40
TPIC46L03DB	296-10871-5-ND	6 通道串行/并行低端 Pre-FET 驱动器	6-Channel Serial/Parallel Low-Side Pre-FET Driver	28-SSOP	2.25	1.80 1.40
TPIC1021DR	296-17542-1-ND	LIN 物理接口	LIN Physical Interface	8-SOIC	1.38	1.10 .83
TPIC1021DR	296-17542-2-ND	LIN 物理接口	LIN Physical Interface	8-SOIC	1760.00/2,500	
TPIC2101D	296-10860-5-ND	单相低端 Pre-FET 驱动器	Single Phase Low-Side Pre-FET Driver	14-SOIC	2.48	1.98 1.54
TPIC2101N	296-10861-5-ND	单相低端 Pre-FET 驱动器	Single Phase Low-Side Pre-FET Driver	14-Dip	2.48	1.98 1.54
TPIC2603DW	296-10863-5-ND	6 通道串行接口低端驱动器	6-Ch. Serial Interface Low-Side Driver	24-SOIC	5.29	4.23 3.29
TPIC2603NE	296-10864-5-ND	6 通道串行接口低端驱动器	6-Ch. Serial Interface Low-Side Driver	20-Dip	5.29	4.23 3.29
TPIC6259DW	296-9009-5-ND	电源 8 位可寻址锁存器	Power 8-Bit Addressable Latch	20-SOIC	2.70	2.16 1.68
TPIC6259N	296-9001-5-ND	电源 8 位可寻址锁存器	Power 8-Bit Addressable Latch	20-Dip	2.70	2.16 1.68
TPIC6273DW	296-9002-5-ND	电源八路 D 型锁存器	Power Octal D-Type Latch	20-SOIC	2.70	2.16 1.68
TPIC6273N	296-1953-5-ND	电源八路 D 型锁存器	Power Octal D-Type Latch	20-Dip	2.70	2.16 1.68
TPIC6595DW	296-1349-5-ND	电源 8 位移寄存器	Power 8-Bit Shift Register	20-SOIC	2.41	1.93 1.50
TPIC6595DWR	296-1349-1-ND	电源 8 位移寄存器	Power 8-Bit Shift Register	20-SOIC	2.50	2.00 1.56
TPIC6595DWR	296-1349-2-ND	电源 8 位移寄存器	Power 8-Bit Shift Register	20-SOIC	2830.00/2,000	
TPIC6595N	296-1954-5-ND	电源 8 位移寄存器	Power 8-Bit Shift Register	20-Dip	2.50	2.00 1.56
TPIC6596DW	296-9003-5-ND	电源 8 位移寄存器	Power 8-Bit Shift Register	20-SOIC	2.41	1.93 1.50
TPIC9201N	296-19606-5-ND	微控制器电源和多模低端驱动器	Microcontroller Power Supply and Multiple Low Side Driver	20-Dip	1.44	1.20 .96
TPIC9201PWPR	296-21144-1-ND	微控制器电源和多模低端驱动器	Microcontroller Power Supply and Multiple Low Side Driver	20-HTSSOP	1.44	1.20 .96
TPIC9201PWPR	296-21144-2-ND	微控制器电源和多模低端驱动器	Microcontroller Power Supply and Multiple Low Side Driver	20-HTSSOP	1276.00/2,000	
TPIC9202PWPR	296-21145-1-ND	微控制器电源和多模低端驱动器	Microcontroller Power Supply and Multiple Low Side Driver	20-HTSSOP	1.44	1.20 .96
TPIC9202PWPR	296-21145-2-ND	微控制器电源和多模低端驱动器	Microcontroller Power Supply and Multiple Low Side Driver	20-HTSSOP	1276.00/2,000	



T. I. 零件编号	Digi-Key 零件编号	说明	封装	单价★		
				1	25	100
PGA309AIPWT	296-16726-1-ND	智能可编程传感器	Smart Programmable Sensor	16-TSSOP	6.50	5.20 4.39
PGA309AIPWT	296-16726-2-ND	智能可编程传感器	Smart Programmable Sensor	16-TSSOP	1056.25/250	
PGA309EVM-EU	296-18515-ND	PGA309-EU 的评估模块	Evaluation Module for PGA309-EU	—	203.00	—
PGA309EVM-US	296-18516-ND	PGA309-US 的评估模块	Evaluation Module for PGA309-US	—	203.00	—
TL851CDR	296-18895-1-ND	声纳测距控制	Sonar Ranging Control	16-SOIC	4.32	3.46 2.69
TL851CDR	296-18895-2-ND	声纳测距控制	Sonar Ranging Control	16-SOIC	6047.50/2,500	
TL851CN	296-19329-5-ND	声纳测距控制	Sonar Ranging Control	16-Dip	4.32	3.46 2.69
TL852CDR	296-17139-1-ND	声纳测距接收器	Sonar Ranging Receiver	16-SOIC	4.32	3.46 2.69
TL852CDR	296-17139-2-ND	声纳测距接收器	Sonar Ranging Receiver	16-SOIC	6047.50/2,500	
TL852CN	296-19330-5-ND	声纳测距接收器	Sonar Ranging Receiver	16-Dip	4.32	3.46 2.69
TPIC6101DWR	296-15132-1-ND	震动传感器接口	Knock Sensor Interface	20-SOIC	5.58	4.47 3.48
TPIC6101DWR	296-15132-2-ND	震动传感器接口	Knock Sensor Interface	20-SOIC	6324.00/2,000	
UC2960T	296-13022-5-ND	半桥双极开关	Half-Bridge Bipolar Switch	TO-220-5	5.60	4.48 3.78
UC3717AN	296-11258-5-ND	步进电机驱动电路	Stepper Motor Drive Circuit	16-Dip	6.60	5.28 4.46
UC3770AN	296-11259-5-ND	高功率步进电机驱动电路	HP Stepper Motor Drive Circuit	16-Dip	5.56	4.45 3.46
UC3770BN	296-11260-5-ND	高功率步进电机驱动电路	HP Stepper Motor Drive Circuit	16-Dip	5.04	4.04 3.41
UC3871DW	296-11326-5-ND	谐振荧光灯驱动器	Resonant Fluorescent Lamp Driver	18-SOIC	8.00	6.40 5.40
UC3871N	296-11327-5-ND	谐振荧光灯驱动器	Resonant Fluorescent Lamp Driver	18-Dip	8.00	6.40 5.40
UC3872DW	296-11328-5-ND	谐振荧光灯驱动器	Resonant Lamp Ballast Controller	16-SOIC	6.00	4.80 4.05
UC3872M	296-11329-5-ND	谐振荧光灯驱动器	Resonant Lamp Ballast Controller	16-HTSSOP	6.00	4.80 4.05
UC3872N	296-11330-5-ND	谐振荧光灯驱动器	Resonant Lamp Ballast Controller	20-Dip	6.00	4.80 4.05
UC2305DW	296-13023-5-ND	HID 灯控制器	HID Lamp Controller	28-SOIC	9.83	8.85 7.85
UC2305N	296-13633-5-ND	HID 灯控制器	HID Lamp Controller	28-Dip	11.41	10.28 9.12
UC3974PW	296-12405-5-ND	双路冷阴极荧光灯控制器	Dual Cold Cathode Fluorescent Lamp Controller	16-TSSOP	7.43	5.94 4.62
UC3977PW	296-12615-5-ND	双路变压器控制器	Dual Transformer Controller	8-TSSOP	2.39	1.91 1.49

T. I. 零件编号	Digi-Key 零件编号	说明	封装	单价★		
				1	25	100
音频差分线路驱动器						
DRV134PA	DRV134PA-ND	带差分输出的音频均衡线路驱动器	Audio Balanced Line Driver with Differential Output	8-Dip	4.39	—
DRV134UA	DRV134UA-ND	带差分输出的音频均衡线路驱动器	Audio Balanced Line Driver with Differential Output	16-SOIC	4.39	—
DRV135UA	DRV135UA-ND	带差分输出的音频均衡线路驱动器	Audio Balanced Line Driver with Differential Output	8-SOIC	4.39	—
电池管理						
BQ20Z70PW	296-19864-5-ND	用于 BQ29330 且符合 SBS 1.1 的电池电量检测计	SBS 1.1-Compliant Gas Gauge for use with BQ29330	20-TSSOP	4.94	3.96 3.34
BQ20Z80DBT	296-17638-5-ND	高级电量检测计	Advanced Gas Gauge	38-TSSOP	9.26	7.41 6.26
BQ20Z80DBTR-V102	296-19275-1-ND	符合 SBS 的电量检测计	SBS-Compliant Gas Gauge	38-TSSOP	9.20	7.36 6.21
BQ20Z80DBTR-V102	296-19275-2-ND	符合 SBS 的电量检测计	SBS-Compliant Gas Gauge	38-TSSOP	11500.00/2,000	
BQ20Z80DBTV101	296-18681-1-ND	高级电量检测计	Advanced Gas Gauge	38-TSSOP	9.26	7.41
BQ20Z80DBTV101	296-18681-2-ND	高级电量检测计	Advanced Gas Gauge	38-TSSOP	312.55/50	
BQ20Z80EVM-001	296-20821-ND	BQ20Z80 的评估模块	Evaluation Module for BQ20Z80	—	101.00	—
BQMTMASTER	296-19619-ND	多通道测试和程序板	Multi-Channel Test and Program Board	—	305.00	—
BQ20Z70PWR-V110	296-21216-1-ND	符合 SBS 1.1 的电池电量检测计	SBS 1.1-Compliant Gas Gauge	20-TSSOP	6.30	5.04 4.26
BQ20Z70PWR-V110	296-21216-2-ND	符合 SBS 1.1 的电池电量检测计	SBS 1.1-Compliant Gas Gauge	20-TSSOP	7876.00/2,000	

(转下页)

★ 欢迎来电咨询, 大批量订购, 价格优惠! ★

全部产品均以美元计价。 免费电话: 10800-1527031 (China Telecom - 中国电讯) — 10800-8527031 (CNCG - 中国网通)

digikey.com.cn — 电话: (852) 3104 0500 — 传真: (852) 3104 0686

(CN082-09) 905