



霍尔效应传感器 (续上页)  
- 符合 RoHS 规范要求

Allegro 零件编号	Digi-Key 零件编号	描述	封装	单价★	1	25	100
A3211ELHLT-T	620-1036-2-ND	低功耗超敏感霍尔效应开关	Micropower, Ultra-Sensitive Hall Effect Switch	SOT-23W	1248.00/3,000		
A3212EHLT-T	620-1037-1-ND	低功耗超敏感霍尔效应开关	Micropower, Ultra-Sensitive Hall Effect Switch	2x2-MLPD	.78	.65	.52
A3212EHLT-T	620-1037-2-ND	低功耗超敏感霍尔效应开关	Micropower, Ultra-Sensitive Hall Effect Switch	2x2-MLPD	1014.00/3,000		
A3212EELLT-T	620-1038-1-ND	低功耗超敏感霍尔效应开关	Micropower, Ultra-Sensitive Hall Effect Switch	2x2-MLPD	.96	.72	.54
A3212EELLT-T	620-1038-2-ND	低功耗超敏感霍尔效应开关	Micropower, Ultra-Sensitive Hall Effect Switch	2x2-MLPD	936.00/3,000		
A3212ELHLT-T	620-1039-1-ND	低功耗超敏感霍尔效应开关	Micropower, Ultra-Sensitive Hall Effect Switch	SOT-23W	.78	.65	.52
A3212ELHLT-T	620-1039-2-ND	低功耗超敏感霍尔效应开关	Micropower, Ultra-Sensitive Hall Effect Switch	SOT-23W	1014.00/3,000		
A3212EUA-T	620-1040-ND	低功耗超敏感霍尔效应开关	Micropower, Ultra-Sensitive Hall Effect Switch	3-SIP	.93	.78	.62
A3213ELUA-T	620-1041-1-ND	低功耗超敏感霍尔效应开关	Micropower, Ultra-Sensitive Hall Effect Switch	SOT-23W	1.05	.88	.70
A3213ELUA-T	620-1041-2-ND	低功耗超敏感霍尔效应开关	Micropower, Ultra-Sensitive Hall Effect Switch	SOT-23W	1365.00/3,000		
A3213LHLT-T	620-1042-1-ND	低功耗超敏感霍尔效应开关	Micropower, Ultra-Sensitive Hall Effect Switch	SOT-23W	1.25	1.00	.75
A3213LHLT-T	620-1042-2-ND	低功耗超敏感霍尔效应开关	Micropower, Ultra-Sensitive Hall Effect Switch	SOT-23W	1920.00/3,000		
A3213LUA-T	620-1043-ND	低功耗超敏感霍尔效应开关	Micropower, Ultra-Sensitive Hall Effect Switch	3-SIP	1.25	1.00	.75
A3230LHLT-T	620-1044-1-ND	斩波器稳定霍尔效应双极开关	Chopper Stabilized Hall Effect Bipolar Switch	SOT-23W	1.23	1.03	.82
A3230LHLT-T	620-1044-2-ND	斩波器稳定霍尔效应双极开关	Chopper Stabilized Hall Effect Bipolar Switch	SOT-23W	1599.00/3,000		
A3230LUA-T	620-1045-ND	斩波器稳定霍尔效应双极开关	Chopper Stabilized Hall Effect Bipolar Switch	3-SIP	1.23	1.03	.82
A3240LHLT-T	620-1046-1-ND	斩波器稳定精密霍尔效应开关	Chopper Stabilized, Precision Hall Effect Switch	SOT-23W	1.26	1.05	.84
A3240LHLT-T	620-1046-2-ND	斩波器稳定精密霍尔效应开关	Chopper Stabilized, Precision Hall Effect Switch	SOT-23W	1638.00/3,000		
A3240LUA-T	620-1047-ND	斩波器稳定精密霍尔效应开关	Chopper Stabilized, Precision Hall Effect Switch	3-SIP	1.26	1.05	.84
A3241LHLT-T	620-1048-1-ND	斩波器稳定单极霍尔效应开关	Chopper Stabilized Unipolar Hall Effect Switch	SOT-23W	1.20	1.00	.80
A3241LHLT-T	620-1048-2-ND	斩波器稳定单极霍尔效应开关	Chopper Stabilized Unipolar Hall Effect Switch	SOT-23W	1560.00/3,000		
A3242LHLT-T	620-1049-1-ND	斩波器稳定单极霍尔效应开关	Chopper Stabilized Unipolar Hall Effect Switch	SOT-23W	1.20	1.00	.80
A3242LHLT-T	620-1049-2-ND	斩波器稳定单极霍尔效应开关	Chopper Stabilized Unipolar Hall Effect Switch	SOT-23W	1560.00/3,000		
A3242LUA-T	620-1050-ND	斩波器稳定单极霍尔效应开关	Chopper Stabilized Unipolar Hall Effect Switch	3-SIP	1.20	1.00	.80
A3245LUA-T	620-1213-ND	斩波器稳定单极霍尔效应开关	Chopper Stabilized, Omnipolar Hall Effect Switch	3-SIP	1.26	1.05	.84
A3280LHLT-T	620-1051-1-ND	斩波器稳定精密霍尔效应锁存器	Chopper Stabilized, Precision Hall Effect Latch	SOT-23W	1.26	1.05	.84
A3280LHLT-T	620-1051-2-ND	斩波器稳定精密霍尔效应锁存器	Chopper Stabilized, Precision Hall Effect Latch	SOT-23W	1638.00/3,000		
A3281LHLT-T	620-1053-1-ND	斩波器稳定精密霍尔效应锁存器	Chopper Stabilized, Precision Hall Effect Latch	SOT-23W	1.26	1.05	.84
A3281LHLT-T	620-1053-2-ND	斩波器稳定精密霍尔效应锁存器	Chopper Stabilized, Precision Hall Effect Latch	SOT-23W	1638.00/3,000		
A3281LUA-T	620-1054-ND	斩波器稳定精密霍尔效应锁存器	Chopper Stabilized, Precision Hall Effect Latch	4-SIP	1.26	1.05	.84
A3282LHLT-T	620-1055-1-ND	斩波器稳定霍尔效应锁存器	Chopper Stabilized Hall Effect Latch	SOT-23W	1.20	1.00	.80
A3282LHLT-T	620-1055-2-ND	斩波器稳定霍尔效应锁存器	Chopper Stabilized Hall Effect Latch	SOT-23W	1560.00/3,000		
A3282LUA-T	620-1056-ND	斩波器稳定霍尔效应锁存器	Chopper Stabilized Hall Effect Latch	3-SIP	1.20	1.00	.80
A3340LHLT-T	620-1211-1-ND	斩波器稳定精密霍尔效应开关	Chopper Stabilized, Precision Hall Effect Switch	SOT-23W	1.26	1.05	.84
A3340LHLT-T	620-1211-2-ND	斩波器稳定精密霍尔效应开关	Chopper Stabilized, Precision Hall Effect Switch	SOT-23W	1638.00/3,000		
A3340LUA-T	620-1212-ND	斩波器稳定精密霍尔效应开关	Chopper Stabilized, Precision Hall Effect Switch	3-SIP	1.26	1.05	.84
A3423EK-T	620-1206-ND	双通道霍尔效应方向检测传感器	Dual Channel Hall Effect Direction Detection Sensor	4-SIP	2.35	1.88	1.41
A3423LK-T	620-1207-ND	双通道霍尔效应方向检测传感器	Dual Channel Hall Effect Direction Detection Sensor	4-SIP	2.25	1.80	1.40
ACS712ELCTR-05B-T	620-1189-1-ND	基于霍尔效应的线性电流传感器	Hall Effect-Based Linear Current Sensor	8-SOIC	2.90	2.33	1.81
ACS712ELCTR-05B-T	620-1189-2-ND	基于霍尔效应的线性电流传感器	Hall Effect-Based Linear Current Sensor	8-SOIC	4875.00/3,000		
ACS712ELCTR-20A-T	620-1190-1-ND	基于霍尔效应的线性电流传感器	Hall Effect-Based Linear Current Sensor	8-SOIC	2.90	2.33	1.81
ACS712ELCTR-20A-T	620-1190-2-ND	基于霍尔效应的线性电流传感器	Hall Effect-Based Linear Current Sensor	8-SOIC	4875.00/3,000		
ACS712ELCTR-30A-T	620-1191-1-ND	基于霍尔效应的线性电流传感器	Hall Effect-Based Linear Current Sensor	8-SOIC	2.90	2.33	1.81
ACS712ELCTR-30A-T	620-1191-2-ND	基于霍尔效应的线性电流传感器	Hall Effect-Based Linear Current Sensor	8-SOIC	4875.00/3,000		
ACS713ELCTR-20A-T	620-1192-1-ND	基于霍尔效应的线性电流传感器	Hall Effect-Based Linear Current Sensor	8-SOIC	2.90	2.33	1.81
ACS713ELCTR-20A-T	620-1192-2-ND	基于霍尔效应的线性电流传感器	Hall Effect-Based Linear Current Sensor	8-SOIC	4875.00/3,000		
ACS713ELCTR-30A-T	620-1193-1-ND	基于霍尔效应的线性电流传感器	Hall Effect-Based Linear Current Sensor	8-SOIC	2.90	2.33	1.81
ACS713ELCTR-30A-T	620-1193-2-ND	基于霍尔效应的线性电流传感器	Hall Effect-Based Linear Current Sensor	8-SOIC	4875.00/3,000		
ACS760ELFTR-20B-T	620-1209-1-ND	12V 高端热插拔霍尔效应电流监控器	12V High-Side Hot-Swap Hall Effect Current Monitor	24-GSOP	6.42	5.14	4.30
ACS760ELFTR-20B-T	620-1209-2-ND	12V 高端热插拔霍尔效应电流监控器	12V High-Side Hot-Swap Hall Effect Current Monitor	24-GSOP	9950.00/2,500		

C



电机驱动器  
- 符合 RoHS 规范要求

Allegro 零件编号	Digi-Key 零件编号	描述	封装	单价★	1	25	100
A1441EELLT-T	620-1167-1-ND	低压全桥无刷直流电机驱动器	Low Voltage Full-Bridge Brushless DC Motor Driver	6-MLP	1.41	1.18	.94
A1441EELLT-T	620-1167-2-ND	低压全桥无刷直流电机驱动器	Low Voltage Full-Bridge Brushless DC Motor Driver	6-MLP	1833.00/3,000		
A1442EELWT-P	620-1210-1-ND	低压全桥无刷直流电机驱动器	Low Voltage Full-Bridge Brushless DC Motor Driver	6-MLP	1.23	1.03	.82
A1442EELWT-P	620-1210-2-ND	低压全桥无刷直流电机驱动器	Low Voltage Full-Bridge Brushless DC Motor Driver	6-MLP	1599.00/3,000		
A2919SLBTR-T	620-1125-1-ND	双路全桥 PWM 电机驱动器	Dual Full-Bridge PWM Motor Driver	24-SOIC	4.46	3.57	2.78
A2919SLBTR-T	620-1125-2-ND	双路全桥 PWM 电机驱动器	Dual Full-Bridge PWM Motor Driver	24-SOIC	2525.00/1,000		
A2982ELWTR-T	620-1126-1-ND	8 通道源驱动器	8-Channel Source Driver	20-SOIC	2.03	1.62	1.22
A2982ELWTR-T	620-1126-2-ND	8 通道源驱动器	8-Channel Source Driver	20-SOIC	1053.00/1,000		
A2982SLWTR-T	620-1127-1-ND	8 通道源驱动器	8-Channel Source Driver	20-SOIC	1.98	1.58	1.19
A2982SLWTR-T	620-1127-2-ND	8 通道源驱动器	8-Channel Source Driver	20-SOIC	1027.00/1,000		
A3903EEETR-T	620-1205-1-ND	低压直流电机控制器	Low Voltage DC Motor Driver	8-DFN	1.02	.85	.68
A3903EEETR-T	620-1205-2-ND	低压直流电机控制器	Low Voltage DC Motor Driver	8-DFN	1326.00/3,000		
A3904EETWR-P	620-1216-1-ND	低压音圈电机驱动器	Low Volt. Voice Coil Motor Driver	6-DFN	.96	.80	.64
A3904EETWR-P	620-1216-2-ND	低压音圈电机驱动器	Low Volt. Voice Coil Motor Driver	6-DFN	1248.00/3,000		
A3932SLD-T	620-1220-5-ND	3 相电源 MOSFET 控制器	3-Phase Power MOSFET Controller	38-TSSOP	3.38	2.70	2.10
A3936SED-T	620-1057-ND	DMOS 3 相 PWM 电机驱动器	DMOS 3-Phase PWM Motor Driver	44-PLCC	6.18	4.95	4.18
A3936SEDTR-T	620-1129-1-ND	DMOS 3 相 PWM 电机驱动器	DMOS 3-Phase PWM Motor Driver	44-PLCC	6.18	4.95	4.18
A3936SEDTR-T	620-1129-2-ND	DMOS 3 相 PWM 电机驱动器	DMOS 3-Phase PWM Motor Driver	44-PLCC	1807.65/450		
A3938LDTR-T	620-1130-1-ND	3 相电源 MOSFET 控制器	3-Phase Power MOSFET Controller	38-TSSOP	5.94	4.76	4.01
A3938LDTR-T	620-1130-2-ND	3 相电源 MOSFET 控制器	3-Phase Power MOSFET Controller	38-TSSOP	14732.00/4,000		
A3949SLB-T	620-1062-ND	DMOS 全桥电机驱动器	DMOS Full-Bridge Motor Driver	16-SOIC	3.29	2.63	2.05
A3949SLBTR-T	620-1131-1-ND	DMOS 全桥电机驱动器	DMOS Full-Bridge Motor Driver	16-SOIC	3.29	2.63	2.05
A3949SLBTR-T	620-1131-2-ND	DMOS 全桥电机驱动器	DMOS Full-Bridge Motor Driver	16-SOIC	1862.00/1,000		
A3949SLP-T	620-1063-ND	DMOS 全桥电机驱动器	DMOS Full-Bridge Motor Driver	16-TSSOP	3.49	2.79	2.17
A3949SLPTR-T	620-1132-1-ND	DMOS 全桥电机驱动器	DMOS Full-Bridge Motor Driver	16-TSSOP	3.49	2.79	2.17
A3949SLPTR-T	620-1132-2-ND	DMOS 全桥电机驱动器	DMOS Full-Bridge Motor Driver	16-TSSOP	7812.00/4,000		
A3950SLP-T	620-1064-ND	DMOS 全桥电机驱动器	DMOS Full-Bridge Motor Driver	16-TSSOP	2.90	2.33	1.81
A3953SB-T	620-1065-ND	全桥 PWM 电机驱动器	Full-Bridge PWM Motor Driver	16-Dip	3.02	2.42	1.88
A3953SLB-T	620-1066-ND	全桥 PWM 电机驱动器	Full-Bridge PWM Motor Driver	16-SOIC	3.02	2.42	1.88
A3953SLBTR-T	620-1133-1-ND	全桥 PWM 电机驱动器	Full-Bridge PWM Motor Driver	16-SOIC	3.02	2.42	1.88
A3953SLBTR-T	620-1133-2-ND	全桥 PWM 电机驱动器	Full-Bridge PWM Motor Driver	16-SOIC	1709.00/1,000		
A3955SB-T	620-1067-ND	全桥 PWM 微步进电机控制器	Full-Bridge PWM Microstepping Motor Driver	16-Dip	2.88	2.31	1.80
A3955SLB-T	620-1068-ND	全桥 PWM 微步进电机控制器	Full-Bridge PWM Microstepping Motor Driver	16-SOIC	2.88	2.31	1.80
A3955SLBTR-T	620-1134-1-ND	全桥 PWM 电机驱动器	Full-Bridge PWM Motor Driver	16-SOIC	2.88	2.31	1.80
A3955SLBTR-T	620-1134-2-ND	全桥 PWM 电机驱动器	Full-Bridge PWM Motor Driver	16-SOIC	1632.00/1,000		
A3958SLBTR-T	620-1135-1-ND	DMOS 全桥 PWM 电机驱动器	DMOS Full-Bridge PWM Motor Driver	24-SOIC	4.75	3.80	2.96
A3958SLBTR-T	620-1135-2-ND	DMOS 全桥 PWM 电机驱动器	DMOS Full-Bridge PWM Motor Driver	24-SOIC	2690.00/2,000		
A3959SB-T	620-1069-ND	DMOS 全桥 PWM 电机驱动器	DMOS Full-Bridge PWM Motor Driver	24-Dip	4.75	3.80	2.96
A3959SLB-T	620-1070-ND	DMOS 全桥 PWM 电机驱动器	DMOS Full-Bridge PWM Motor Driver	24-SOIC	4.75	3.80	2.96
A3959SLBTR-T	620-1136-1-ND	DMOS 全桥 PWM 电机驱动器	DMOS Full-Bridge PWM Motor Driver	24-SOIC	4.75	3.80	2.96
A3959SLBTR-T	620-1136-2-ND	DMOS 全桥 PWM 电机驱动器	DMOS Full-Bridge PWM Motor Driver	24-SOIC	2690.00/1,000		
A3959SLP-T	620-1071-ND	DMOS 全桥 PWM 电机驱动器	DMOS Full-Bridge PWM Motor Driver	28-TSSOP	4.86	3.89	3.03
A3959SLPTR-T	620-1137-1-ND	DMOS 全桥 PWM 电机驱动器	DMOS Full-Bridge PWM Motor Driver	28-TSSOP	4.86	3.89	3.03
A3959SLPTR-T	620-1137-2-ND	DMOS 全桥 PWM 电机驱动器	DMOS Full-Bridge PWM Motor Driver	28-TSSOP	10888.00/4,000		
A3964SLBTR-T	620-1138-1-ND	双路全桥 PWM 电机驱动器	Dual Full-Bridge PWM Motor Driver	20-SOIC	4.46	3.57	2.78

(续下页)

★ 欢迎来电查询, 大批量订购, 价格优惠! ★

全部产品均以美元计价。 免费电话: 10800-1527031 (China Telecom - 中国电讯) — 10800-8527031 (CNCG - 中国网通)

digikey.com.cn — 电话: (852) 3104 0500 — 传真: (852) 3104 0686

(CN082-09) 999