



电源管理 (接上页)
- 符合 RoHS 规范要求

| Allegro 零件编号 | Digi-Key 零件编号 | 描述 | 封装 | 1 | 25 | 100 |
|-------------------|---------------|---------------------------|---|---------|---------------|-----------|
| A6280EESTR-T | 620-1179-1-ND | 带 PWM 控制的 3 通道恒流 LED 驱动器 | 3-Channel Constant Current LED Driver with PWM Control | 16-QFN | 1.53 | 1.22 .92 |
| A6280EESTR-T | 620-1179-2-ND | 带 PWM 控制的 3 通道恒流 LED 驱动器 | 3-Channel Constant Current LED Driver with PWM Control | 16-QFN | 1.53 | 1.22 .92 |
| A6281EESTR-T | 620-1218-1-ND | 带 PWM 控制的 3 通道恒流 LED 驱动器 | 3-Channel Constant Current LED Driver with PWM Control | 16-QFN | 1.53 | 1.22 .92 |
| A6281EESTR-T | 620-1218-2-ND | 带 PWM 控制的 3 通道恒流 LED 驱动器 | 3-Channel Constant Current LED Driver with PWM Control | 16-QFN | 1.53 | 1.22 .92 |
| A6800SA-T | 620-1088-ND | DABIC-5 锁存耗散驱动器 | DABIC-5 Latched Sink Drivers | 14-Dip | 1.43 | 1.14 .86 |
| A6800SL-T | 620-1089-ND | DABIC-5 锁存耗散驱动器 | DABIC-5 Latched Sink Drivers | 14-SOIC | 1.58 | 1.26 .95 |
| A6801SA-T | 620-1090-ND | DABIC-5 锁存耗散驱动器 | DABIC-5 Latched Sink Drivers | 22-Dip | 2.10 | 1.68 1.26 |
| A6801SLW-T | 620-1091-ND | DABIC-5 锁存耗散驱动器 | DABIC-5 Latched Sink Drivers | 24-SOIC | 2.10 | 1.68 1.26 |
| A6810SA-T | 620-1092-ND | DABIC-IV, 10 位串行输入锁存源驱动器 | DABIC-IV, 10-Bit Serial Input, Latched Source Driver | 18-Dip | 1.83 | 1.46 1.10 |
| A6812ELW-T | 620-1093-ND | DABIC-IV, 20 位串行输入锁存源驱动器 | DABIC-IV, 20-Bit Serial Input, Latched Source Driver | 28-SOIC | 4.16 | 3.33 2.59 |
| A6818SEP-T | 620-1094-ND | DABIC-IV, 32 位串行输入锁存源驱动器 | DABIC-IV, 32-Bit Serial Input, Latched Source Driver | 44-PLCC | 5.06 | 4.05 3.42 |
| A6821SA-T | 620-1095-ND | DABIC-5 8 位串行输入锁存耗散驱动器 | DABIC-5 8-Bit Serial Input Latched Sink Drivers | 16-Dip | 2.25 | 1.80 1.35 |
| A6821SLW-T | 620-1096-ND | DABIC-5 8 位串行输入锁存耗散驱动器 | DABIC-5 8-Bit Serial Input Latched Sink Drivers | 16-SOIC | 2.38 | 1.90 1.43 |
| A6850KLR-T | 620-1185-1-ND | 双通道开关接口 | Dual Channel Switch Interface | 8-SOIC | 1.53 | 1.22 .92 |
| A6850KLR-T | 620-1185-2-ND | 双通道开关接口 | Dual Channel Switch Interface | 8-SOIC | 2343.00/3,000 | |
| A8285SLBTR-T | 620-1202-1-ND | LNB 电源/控制稳压器 | LNB Supply/Control Voltage Reg. | 16-SOIC | 2.88 | 2.31 1.80 |
| A8285SLBTR-T | 620-1202-2-ND | LNB 电源/控制稳压器 | LNB Supply/Control Voltage Reg. | 16-SOIC | 1632.00/1,000 | |
| A8287SLBTR-T | 620-1200-1-ND | LNB 电源/控制稳压器 | LNB Supply/Control Voltage Reg. | 24-SOIC | 2.95 | 2.36 1.84 |
| A8287SLBTR-T | 620-1200-2-ND | LNB 电源/控制稳压器 | LNB Supply/Control Voltage Reg. | 24-SOIC | 1670.00/1,000 | |
| A8292SETTR-T | 620-1187-1-ND | 双路 LNB 电源/控制稳压器 | Dual LNB Supply/Control Voltage Reg. | 28-MLP | 3.15 | 2.52 1.96 |
| A8430EETR-T | 620-1187-2-ND | 双路 LNB 电源/控制稳压器 | Dual LNB Supply/Control Voltage Reg. | 28-MLP | 2677.50/1,500 | |
| A8430EETR-T | 620-1097-1-ND | 白色 LED 驱动器恒流升转换器 | White LED Driver Constant Current Step-Up Converter | 5-MLPD | .68 | .51 .39 |
| A8430EETR-T | 620-1097-2-ND | 白色 LED 驱动器恒流升转换器 | White LED Driver Constant Current Step-Up Converter | 5-MLPD | 339.00/1,500 | |
| A8431EETR-T | 620-1195-1-ND | 白色 LED 驱动器恒流升转换器 | White LED Driver Constant Current Step-Up Converter | 6-MLPD | .80 | .60 .45 |
| A8431EETR-T | 620-1195-2-ND | 白色 LED 驱动器恒流升转换器 | White LED Driver Constant Current Step-Up Converter | 6-MLPD | 1.20 | 1.00 .80 |
| A8434EESTR-T | 620-1188-1-ND | 6 通道高效充电泵白色 LED 驱动器 | 6 Channel, High Efficiency Charge Pump White LED Driver | 16-MLP | 798.00/1,500 | |
| A8434EESTR-T | 620-1188-2-ND | 6 通道高效充电泵白色 LED 驱动器 | 6 Channel, High Efficiency Charge Pump White LED Driver | 16-MLP | 1.02 | .85 .68 |
| A8435EESTR-T | 620-1124-1-ND | 高效充电泵白色 LED 驱动器 | High Efficiency Charge Pump White LED Driver | 16-MLP | 678.00/1,500 | |
| A8435EESTR-T | 620-1124-2-ND | 高效充电泵白色 LED 驱动器 | High Efficiency Charge Pump White LED Driver | 16-MLP | 1.20 | 1.00 .80 |
| A8436EETR-T | 620-1098-1-ND | 照相闪光灯电容充电器 | Photoflash Capacitor Charger | 10-MLP | 1.29 | 1.08 .86 |
| A8436EETR-T | 620-1098-2-ND | 照相闪光灯电容充电器 | Photoflash Capacitor Charger | 10-MLP | 858.00/1,500 | |
| A8438EETR-T | 620-1099-1-ND | 照相闪光灯电容充电器 | Photoflash Capacitor Charger | 10-MLP | 1.23 | 1.03 .82 |
| A8438EETR-T | 620-1099-2-ND | 照相闪光灯电容充电器 | Photoflash Capacitor Charger | 10-MLP | 817.50/1,500 | |
| A8439EETR-T | 620-1203-1-ND | 照相闪光灯电容充电器, 带 IGBT 驱动器/刷新 | Photoflash Capacitor Charger with IGBT Driver/Refresh | 10-MLP | 4.14 | 3.32 2.58 |
| A8439EETR-T | 620-1203-2-ND | 照相闪光灯电容充电器, 带 IGBT 驱动器/刷新 | Photoflash Capacitor Charger with IGBT Driver/Refresh | 24-SOIC | 1.23 | 1.03 .82 |
| A8450KLB-T | 620-1100-ND | 自动多输出稳压器 | Automotive Multioutput Voltage Reg. | 24-SOIC | 4.14 | 3.32 2.58 |
| A8447SLJTR-T | 620-1174-1-ND | 高压升降稳压器 | High Voltage Step Down Regulator | 8-SOIC | 1.23 | .98 .74 |
| A8447SLJTR-T | 620-1174-2-ND | 高压升降稳压器 | High Voltage Step Down Regulator | 8-SOIC | 1881.00/3,000 | |
| A8480EETR-T | 620-1208-1-ND | 显示器偏置或 LED 驱动器的升压稳压器 | Boost Regulator for Display Bias or LED Driver | 10-MLP | 1.08 | .86 .65 |
| A8480EETR-T | 620-1208-2-ND | 显示器偏置或 LED 驱动器的升压稳压器 | Boost Regulator for Display Bias or LED Driver | 10-MLP | 838.50/1,500 | |
| A8483EETR-T | 620-1101-1-ND | 显示器偏置电源的 1.2MHz 升压转换器 | 1.2MHz Step-Up Converter for Display Bias Supply | 5-MLP | .80 | .60 .45 |
| A8483EETR-T | 620-1101-2-ND | 显示器偏置电源的 1.2MHz 升压转换器 | 1.2MHz Step-Up Converter for Display Bias Supply | 5-MLP | 399.00/1,500 | |
| A8498SLJTR-T | 620-1160-1-ND | 高压升降稳压器 | High Voltage Step Down Regulator | 8-SOIC | 1.30 | 1.04 .78 |
| A8498SLJTR-T | 620-1160-2-ND | 高压升降稳压器 | High Voltage Step Down Regulator | 8-SOIC | 1998.00/3,000 | |
| A8499SLJTR-T | 620-1102-1-ND | 高压升降稳压器 | High Voltage Step Down Regulator | 9-SOIC | 1.47 | 1.23 .98 |
| A8499SLJTR-T | 620-1102-2-ND | 高压升降稳压器 | High Voltage Step Down Regulator | 9-SOIC | 1911.00/3,000 | |
| A8500EETR-T | 620-1204-1-ND | 灵活的 WLED/RGB 背光驱动器 | Flexible WLED/RGB Backlight Driver | 26-QFN | 2.48 | 1.98 1.54 |
| A8500EETR-T | 620-1204-2-ND | 灵活的 WLED/RGB 背光驱动器 | Flexible WLED/RGB Backlight Driver | 26-QFN | 4158.00/3,000 | |
| A8503EESTR-T | 620-1201-1-ND | 超紧凑 6 通道背光和闪光灯白光 LED 驱动器 | Ultracompact 6-Channel Backlight and Flash/Torch White LED Driver | 16-QFN | 1.28 | 1.02 .77 |
| A8503EESTR-T | 620-1201-2-ND | 超紧凑 6 通道背光和闪光灯白光 LED 驱动器 | Ultracompact 6-Channel Backlight and Flash/Torch White LED Driver | 16-QFN | 994.50/1,500 | |
| A8697ELJTR-T | 620-1178-1-ND | 宽输入电压 4.0A 升降稳压器 | Wide Input Voltage 4.0A Step Down Regulator | 8-SOIC | 1.28 | 1.02 .77 |
| A8697ELJTR-T | 620-1178-2-ND | 宽输入电压 4.0A 升降稳压器 | Wide Input Voltage 4.0A Step Down Regulator | 8-SOIC | 1959.00/3,000 | |
| A8698ELJTR-T | 620-1177-1-ND | 宽输入电压 3.0A 升降稳压器 | Wide Input Voltage 3.0A Step Down Regulator | 8-SOIC | 1.38 | 1.15 .92 |
| A8698ELJTR-T | 620-1177-2-ND | 宽输入电压 3.0A 升降稳压器 | Wide Input Voltage 3.0A Step Down Regulator | 8-SOIC | 1794.00/3,000 | |
| ACS754KCB-150-PFF | 620-1105-ND | 电流传感器 | Current Sensor | CB-5 | 5.08 | 4.07 3.43 |
| ACS754LCB-050-PFF | 620-1106-ND | 电流传感器 | Current Sensor | CB-5 | 5.54 | 4.43 3.45 |
| ACS754LCB-100-PFF | 620-1107-ND | 电流传感器 | Current Sensor | CB-5 | 5.54 | 4.43 3.45 |
| ACS754LCB-100-PSF | 620-1108-ND | 电流传感器 | Current Sensor | CB-5 | 5.26 | 4.21 3.56 |
| ACS754LCB-130-PFF | 620-1109-ND | 电流传感器 | Current Sensor | CB-5 | 5.26 | 4.21 3.56 |
| ACS755LCB-050-PFF | 620-1110-ND | 电流传感器 | Current Sensor | CB-5 | 5.54 | 4.43 3.45 |
| ACS755LCB-100-PFF | 620-1111-ND | 电流传感器 | Current Sensor | CB-5 | 5.54 | 4.43 3.45 |
| ACS755SCB-050-PFF | 620-1112-ND | 电流传感器 | Current Sensor | CB-5 | 5.18 | 4.14 3.22 |
| ACS755SCB-100-PFF | 620-1113-ND | 电流传感器 | Current Sensor | CB-5 | 5.18 | 4.14 3.22 |
| ACS755SCB-150-PSF | 620-1114-ND | 电流传感器 | Current Sensor | CB-5 | 5.18 | 4.14 3.22 |
| ACS755SCB-200-PSF | 620-1115-ND | 电流传感器 | Current Sensor | CB-5 | 5.18 | 4.14 3.22 |
| ACS760ELF-20B-T | 620-1168-2-ND | 基于高端热插霍尔效应的 12V 电流监控器 | 12V High Side Hot-Swap Hall Effect Based Current Monitor | 24-QSOP | 5.29 | 4.23 3.29 |
| ACS760ELF-20B-T | 620-1168-1-ND | 基于高端热插霍尔效应的 12V 电流监控器 | 12V High Side Hot-Swap Hall Effect Based Current Monitor | 24-QSOP | 7402.50/2,500 | |
| ATS616LSGNT-T | 620-1116-1-ND | 动态自校准峰值检测差分霍尔效应轮齿传感器 | Dynamic Self-Calibrating Peak Detecting Diff. Hall Effect Gear Tooth Sensor | 4-SIP | 4.32 | 3.46 2.69 |
| ATS616LSGNT-T | 620-1116-2-ND | 动态自校准峰值检测差分霍尔效应轮齿传感器 | Dynamic Self-Calibrating Peak Detecting Diff. Hall Effect Gear Tooth Sensor | 4-SIP | 1996.80/800 | |
| ATS665LSGNT-T | 620-1161-1-ND | 真正零速高精度轮齿传感器 | True Zero Speed, High Accuracy, Gear Tooth Sensor | 4-SIP | 4.91 | 3.93 3.06 |
| ATS665LSGNT-T | 620-1161-2-ND | 真正零速高精度轮齿传感器 | True Zero Speed, High Accuracy, Gear Tooth Sensor | 4-SIP | 2267.20/800 | |
| ATS673LSETN-LT-T | 620-1162-1-ND | 改进型自校准 TPOS 轮齿传感器 | Self-Calibrating TPOS Gear Tooth Sensor Optimized | 4-SIP | 5.60 | 4.48 3.78 |
| ATS673LSETN-LT-T | 620-1162-2-ND | 改进型自校准 TPOS 轮齿传感器 | Self-Calibrating TPOS Gear Tooth Sensor Optimized | 4-SIP | 1638.00/450 | |
| UDN2981A-T | 620-1120-ND | 8 通道源驱动器 | 8-Channel Source Drivers | 18-Dip | 1.78 | 1.42 1.07 |
| UDN2982A-T | 620-1121-ND | 8 通道源驱动器 | 8-Channel Source Drivers | 18-Dip | 1.78 | 1.42 1.07 |

C



74AC/ACT/ALV 系列
提供符合 RoHS 规范要求的零件

| STMicroelectronics 零件编号 | Digi-Key 零件编号 | 描述 | 封装 | 1 | 10 | 100 |
|-------------------------|---------------|------------------|---------------------------------------|----------|--------------|---------|
| 74AC02B | 497-1324-5-ND | 四路 2 输入或非门 | Quad 2-Input NOR Gate | 14-Dip | .51 | .39 .29 |
| 74AC04MTR | 497-1015-1-ND | 六路反相器 | Hex Inverter | 14-SOIC | .62 | .46 .37 |
| 74AC08B | 497-1325-5-ND | 四路 2 输入与门 | Quad 2-Input AND Gate | 14-Dip | .51 | .39 .29 |
| 74AC08MTR | 497-1016-1-ND | 四路 2 输入与门 | Quad 2-Input AND Gate | 14-SOIC | .62 | .46 .37 |
| 74AC08MTR | 497-1016-2-ND | 四路 2 输入与门 | Quad 2-Input AND Gate | 14-SOIC | 508.75/2,500 | |
| 74AC14MTR | 497-1019-1-ND | 六路施密特反相器 | Hex Schmitt Inverter | 14-SOIC | .62 | .46 .37 |
| 74AC14MTR | 497-1019-2-ND | 六路施密特反相器 | Hex Schmitt Inverter | 14-SOIC | 508.75/2,500 | |
| 74AC32MTR | 497-1026-1-ND | 四路 2 输入或门 | Quad 2-Input OR Gate | 14-SOIC | .53 | .39 .32 |
| 74AC32MTR | 497-1026-2-ND | 四路 2 输入或门 | Quad 2-Input OR Gate | 14-SOIC | 439.38/2,500 | |
| 74AC74B | 497-1329-5-ND | 带预设和清除的双路 D 型触发器 | Dual D-Type F/F with Preset and Clear | 14-Dip | .51 | .39 .29 |
| 74AC74MTR | 497-1030-1-ND | 带预设和清除的双路 D 型触发器 | Dual D-Type F/F with Preset and Clear | 14-SOIC | .59 | .44 .35 |
| 74AC125MTR | 497-1017-1-ND | 三态四路总线缓冲器 | Tri-State Quad Bus Buffer | 14-SOIC | .62 | .46 .37 |
| 74AC125MTR | 497-1017-2-ND | 三态四路总线缓冲器 | Tri-State Quad Bus Buffer | 14-SOIC | 508.75/2,500 | |
| 74AC240MTR | 497-2911-1-ND | 三态八路总线缓冲器 | Tri-State Octal Bus Buffer | 20-SOIC | .68 | .53 .45 |
| 74AC240MTR | 497-2911-2-ND | 三态八路总线缓冲器 | Tri-State Octal Bus Buffer | 20-SOIC | 232.50/1,000 | |
| 74AC240TTR | 497-2912-1-ND | 三态八路总线缓冲器 | Tri-State Octal Bus Buffer | 20-TSSOP | .73 | .54 .43 |
| 74AC240TTR | 497-2912-2-ND | 三态八路总线缓冲器 | Tri-State Octal Bus Buffer | 20-TSSOP | 601.25/2,500 | |
| 74AC244MTR | 497-1023-1-ND | 三态八路总线缓冲器 | Tri-State Octal Bus Buffer | 20-SOIC | .73 | .54 .43 |
| 74AC244MTR | 497-1023-2-ND | 三态八路总线缓冲器 | Tri-State Octal Bus Buffer | 20-SOIC | 273.00/1,000 | |
| 74AC244TTR | 497-2913-1-ND | 三态八路总线缓冲器* | Tri-State Octal Bus Buffer* | 20-TSSOP | .73 | .54 .43 |

* 符合 RoHS 规范要求

(转下页)

★ 欢迎来电查询, 大批量订购, 价格优惠! ★

全部产品均以美元计价。

免费电话: 10800-1527031 (China Telecom - 中国电讯) — 10800-8527031 (CNCG - 中国网通)

digikkey.com.cn — 电话: (852) 3104 0500 — 传真: (852) 3104 0686

(CN082-09) 1001