

Digi-Key 零件编号	描述	封装	1	25	100	
FXLH42245MPXCT-ND	低压双源 8 位信号变换器	Low Voltage Dual Supply 8-Bit Signal Translator	24-MLP	1.38	1.15	.92
FXLH42245MPXTR-ND	低压双源 8 位信号变换器	Low Voltage Dual Supply 8-Bit Signal Translator	24-MLP	1794.00	3,000	
FXLP34P5XCT-ND	1 位单向变换器	Single Bit Uni-Directional Translator	SC70-5	.84	.63	.48
FXLP34P5XTR-ND	1 位单向变换器	Single Bit Uni-Directional Translator	SC70-5	819.00	3,000	
GLTP16617MTDXCT-ND	17 位 TTL/GTLP 同步总线收发器	17-Bit TTL/GTLP Sync. Bus Transceiver	56-TSSOP	4.95	3.96	3.08
GLTP16617MTDXTR-ND	17 位 TTL/GTLP 同步总线收发器	17-Bit TTL/GTLP Sync. Bus Transceiver	56-TSSOP	2805.00	1,000	
KA723-ND	精密稳压器	Precision Voltage Regulator	14-Dip	.52	.39	.30
KA7805ETU-ND	3 端子 1A 正稳压器	3-Terminal 1A Positive Voltage Regulator	TO-220	.50	.40	.30
KSC5305DTU-ND	高压高速电源开关	High Voltage High Speed Power Switch	TO-220	.68	.52	.39
LM78L05ACZFS-ND	5V 3 端子 0.1A 正稳压器	5V, 3-Terminal 0.1A Positive Voltage Regulator	TO-92	.32	.26	.18
LM78L12ACZFS-ND	12V 3 端子 0.1A 正稳压器	12V, 3-Terminal 0.1A Positive Voltage Regulator	TO-92	.32	.26	.18
LM78M05CTFS-ND	5V 3 端子 0.5A 正稳压器	5V, 3-Terminal 0.5A Positive Voltage Regulator	TO-220	.50	.40	.30
LM79L05ACZFS-ND	5V 0.1A 3 端子 0.1A 负稳压器	5V, 0.1A 3-Terminal 0.1A Negative Voltage Regulator	TO-92	.40	.32	.22
LM311MFS-ND	0°C 至 70°C 单路比较器	0°C-70°C Single Comparator	8-SOP	.45	.36	.27
LM311NFS-ND	0°C 至 70°C 单路比较器	0°C-70°C Single Comparator	8-Dip	.45	.36	.27
LM317LMFS-ND	0.1A 3 端子正向可调式稳压器	0.1A, 3-Terminal Positive Adjustable Regulator	8-SOP	.40	.32	.24
LM317LZ-ND	0.1A 3 端子正向可调式稳压器	0.1A, 3-Terminal Positive Adjustable Regulator	TO-92	.43	.34	.24
LM317MDTXXFSC-ND	0.5A 3 端子正向可调式稳压器	0.5A, 3-Terminal Positive Adjustable Regulator	D-PAK	.48	.36	.27
LM317MDTXXFSTR-ND	0.5A 3 端子正向可调式稳压器	0.5A, 3-Terminal Positive Adjustable Regulator	D-PAK	320.00	2,000	
LM317TFS-ND	1.5A 3 端子正向可调式稳压器	1.5A, 3-Terminal Positive Adjustable Regulator	TO-220	.48	.36	.27
LM319MXFSC-ND	5V 双路比较器	5V, Dual Comparator	14-SOP	.55	.44	.33
LM319MXFSTR-ND	5V 双路比较器	5V, Dual Comparator	14-SOP	384.00	3,000	
LM336Z25-ND	2.5V 可编程并联稳压器	2.5V, Programmable Shunt Regulator	TO-92	.36	.30	.21
LM336Z5-ND	5V 可编程并联稳压器	5V, Programmable Shunt Regulator	TO-92	.36	.30	.21
LM337TFS-ND	1.5A 3 端子负向可调式稳压器	1.5A, 3-Terminal Negative Adjustable Regulator	TO-220	.60	.45	.34
LM339ANFS-ND	0°C 至 70°C 四路比较器	0°C-70°C Quad Comparator	14-Dip	.45	.36	.27
LM339MFS-ND	0°C 至 70°C 四路比较器	0°C-70°C Quad Comparator	14-SOP	.44	.36	.25
LM339MXFSC-ND	0°C 至 70°C 四路比较器	0°C-70°C Quad Comparator	14-SOP	.44	.36	.25
LM339MXFSTR-ND	0°C 至 70°C 四路比较器	0°C-70°C Quad Comparator	14-SOP	282.00	3,000	
LM339NFS-ND	0°C 至 70°C 四路比较器	0°C-70°C Quad Comparator	14-Dip	.39	.32	.22
LM350TFS-ND	3A 3 端子可调式正稳压器	3A, 3-Terminal Positive Adjustable Voltage Regulator	TO-220	.86	.65	.49
LM393AN-ND	0°C 至 70°C 双路差分比较器	0°C-70°C Dual Differential Comparator	8-Dip	.39	.32	.22
LM393MFS-ND	0°C 至 70°C 双路差分比较器	0°C-70°C Dual Differential Comparator	8-SOP	.43	.34	.24
LM393MXFSC-ND	0°C 至 70°C 双路差分比较器	0°C-70°C Dual Differential Comparator	8-SOP	.43	.34	.24
LM393MXFSTR-ND	0°C 至 70°C 双路差分比较器	0°C-70°C Dual Differential Comparator	8-SOP	258.00	3,000	
LM393NFS-ND	0°C 至 70°C 双路差分比较器	0°C-70°C Dual Differential Comparator	8-Dip	.40	.32	.22
LM431ACZFS-ND	可编程并联稳压器	Programmable Shunt Regulator	TO-92	.27	.21	.15
LM555CMFS-ND	单路计时器	Single Timer	8-SOP	.44	.36	.25
LM555CNFS-ND	单路计时器	Single Timer	8-Dip	.44	.36	.25
LM555CNFS-ND	双路计时器	Dual Timer	14-Dip	.55	.44	.33
LM2901NFS-ND	四路比较器	Quad Comparator	14-Dip	.45	.36	.27
LM2903MFS-ND	双路差分比较器	Dual Differential Comparator	8-SOP	.40	.33	.22
LM2903NFS-ND	双路差分比较器	Dual Differential Comparator	8-Dip	.41	.34	.23
LM7805ACT-ND	0°C 至 125°C 3 端子 1A 正稳压器	0°C to 125°C, 3-Terminal 1A Positive Voltage Regulator	TO-220	.45	.36	.27
LM7805CT-ND	-40°C 至 125°C 3 端子 1A 正稳压器	-40°C to 125°C, 3-Terminal 1A Positive Voltage Regulator	TO-220	.45	.36	.27
LM7905CTFS-ND	-5V 4% 3 端子 1A 负稳压器	-5V, 4% 3-Terminal 1A Negative Voltage Regulator	TO-220	.49	.40	.30
MB2SCT-ND	桥式整流器	Bridge Rectifier	4-SOIC	.44	.36	.25
MB2STR-ND	桥式整流器	Bridge Rectifier	4-SOIC	341.70	3,000	
MB4SCT-ND	桥式整流器	Bridge Rectifier	4-SOIC	.47	.39	.27
MB4STR-ND	桥式整流器	Bridge Rectifier	4-SOIC	372.30	3,000	
MB6SCT-ND	桥式整流器	Bridge Rectifier	4-SOIC	.47	.39	.27
MB6STR-ND	桥式整流器	Bridge Rectifier	4-SOIC	372.30	3,000	
MC78L05ACD-ND	5V 5% 3 端子 0.1A 正稳压器	5V, 5% 3-Terminal 0.1A Positive Voltage Regulator	8-SOP	.40	.33	.23
MC78L05ACPPS-ND	5V 5% 3 端子 0.1A 正稳压器	5V, 5% 3-Terminal 0.1A Positive Voltage Regulator	TO-92	.32	.26	.18
MC78L08ACP-ND	8V 4% 3 端子 0.1A 正稳压器	8V, 4% 3-Terminal 0.1A Positive Voltage Regulator	TO-92	.40	.32	.22
MC78L15ACPPS-ND	15V 5% 3 端子 0.1A 正稳压器	15V, 5% 3-Terminal 0.1A Positive Voltage Regulator	TO-92	.40	.32	.22
MC78M05CDTCT-ND	5V 0.5A 3 端子正稳压器	5V, 0.5A 3-Terminal Positive Voltage Regulator	D-PAK	.50	.40	.30
MC78M05CDTTR-ND	5V 0.5A 3 端子正稳压器	5V, 0.5A 3-Terminal Positive Voltage Regulator	D-PAK	280.00	2,000	
MC78M05CTFS-ND	5V 0.5A 3 端子正稳压器	5V, 0.5A 3-Terminal Positive Voltage Regulator	TO-220	.53	.40	.30
MC78T05CTFS-ND	5V 3A 3 端子正稳压器	5V, 3A 3-Terminal Positive Voltage Regulator	TO-220	1.17	.98	.78
MC78T12CTFS-ND	12V 3A 3 端子正稳压器	12V, 3A 3-Terminal Positive Voltage Regulator	TO-220	1.17	.98	.78
MC78T15CTFS-ND	15V 3A 3 端子正稳压器	15V, 3A 3-Terminal Positive Voltage Regulator	TO-220	1.17	.98	.78
MC7812ECT-ND	12V 1A 3 端子正稳压器	12V, 1A 3-Terminal Positive Voltage Regulator	TO-220	.50	.40	.30
MC7905CTFS-ND	-5V 4% 3 端子 1A 负稳压器	-5V, 4% 3-Terminal 1A Negative Voltage Regulator	TO-220	.53	.40	.30
MC7912CTFS-ND	-12V 4% 3 端子 1A 负稳压器	-12V, 4% 3-Terminal 1A Negative Voltage Regulator	TO-220	.53	.40	.30
MC7915CTFS-ND	-15V 4% 3 端子 1A 负稳压器	-15V, 4% 3-Terminal 1A Negative Voltage Regulator	TO-220	.53	.40	.30
MM74HC04MXCT-ND	六路反相器	Hex Inverter	14-SOIC	.42	.34	.24
MM74HC04MXTR-ND	六路反相器	Hex Inverter	14-SOIC	216.00	2,500	
MMBFJ112CT-ND	N 沟道开关	N-Channel Switch	SOT-23	.39	.31	.22
MMBFJ112TR-ND	N 沟道开关	N-Channel Switch	SOT-23	260.82	3,000	
QRE1113GRCT-ND	反射物体传感器	Reflective Object Sensor	SMD	.69	.52	.39
QRE1113GRTR-ND	反射物体传感器	Reflective Object Sensor	SMD	230.09	1,000	
SCAN18245TSSC-ND	三态非反相收发器	Tri-State Non-Inverting Transceiver	56-SSOP	8.10	6.48	5.47

Digi-Key 零件编号	描述	封装	1	25	100	
FAN1086M-ND	可调式 1.5A 低压降线性稳压器	Adjustable, 1.5A LDO Linear Regulator	TO-263	1.02	.85	.68
FAN1086M33-ND	3.3V 1.5A 固定低压降线性稳压器	3.3V, 1.5A Fixed LDO Linear Regulator	TO-263	1.02	.85	.68
FAN1086M285-ND	2.85V 1.5A 固定低压降线性稳压器	2.85V, 1.5A Fixed LDO Linear Regulator	TO-263	1.02	.85	.68
FAN1539MPXCT-ND	带低静态电流的 3.3V 1A 低压降	3.3V, 1A, LDO with Low Quiescent Current	6-MLP	.96	.80	.64
FAN1539MPXTR-ND	带低静态电流的 3.3V 1A 低压降	3.3V, 1A, LDO with Low Quiescent Current	6-MLP	1248.00	3,000	
FAN1540BMPXCT-ND	带低静态电流的 3.3V 1.3A 低压降	3.3V, 1.3A, LDO with Low Quiescent Current	6-MLP	1.02	.85	.68
FAN1540BMPXTR-ND	带低静态电流的 3.3V 1.3A 低压降	3.3V, 1.3A, LDO with Low Quiescent Current	6-MLP	1326.00	3,000	
FAN2500SXC-ND	可调式 100mA CMOS 低压降稳压器	Adjustable, 100mA, CMOS LDO Regulator	SOT-23-5	.84	.63	.48
FAN2500SXTR-ND	可调式 100mA CMOS 低压降稳压器	Adjustable, 100mA, CMOS LDO Regulator	SOT-23-5	663.00	3,000	
FAN2500S25XCT-ND	2.5V 100mA CMOS 低压降稳压器	2.5V, 100mA, CMOS LDO Regulator	SOT-23-5	.74	.56	.42
FAN2500S25XTR-ND	2.5V 100mA CMOS 低压降稳压器	2.5V, 100mA, CMOS LDO Regulator	SOT-23-5	663.00	3,000	
FAN2500S28XCT-ND	2.8V 100mA CMOS 低压降稳压器	2.8V, 100mA, CMOS LDO Regulator	SOT-23-5	.84	.63	.48
FAN2500S28XTR-ND	2.8V 100mA CMOS 低压降稳压器	2.8V, 100mA, CMOS LDO Regulator	SOT-23-5	663.00	3,000	
FAN2500S30XCT-ND	3.0V 100mA CMOS 低压降稳压器	3.0V, 100mA, CMOS LDO Regulator	SOT-23-5	.84	.63	.48
FAN2500S30XTR-ND	3.0V 100mA CMOS 低压降稳压器	3.0V, 100mA, CMOS LDO Regulator	SOT-23-5	663.00	3,000	
FAN2500S33XCT-ND	3.3V 100mA CMOS 低压降稳压器	3.3V, 100mA, CMOS LDO Regulator	SOT-23-5	.84	.63	.48
FAN2500S33XTR-ND	3.3V 100mA CMOS 低压降稳压器	3.3V, 100mA, CMOS LDO Regulator	SOT-23-5	663.00	3,000	
ILC7083AIM525XCT-ND	2.5V 150mA 低噪声 CMOS RF-LDO™ 稳压器	2.5V, 150mA, Low Noise CMOS RF-LDO™ Regulator	SOT-23-5	.90	.75	.60
ILC7083AIM527XCT-ND	2.7V 150mA 低噪声 CMOS RF-LDO™ 稳压器	2.7V, 150mA, Low Noise CMOS RF-LDO™ Regulator	SOT-23-5	.90	.75	.60
ILC7083AIM536XCT-ND	3.6V 150mA 低噪声 CMOS RF-LDO™ 稳压器	3.6V, 150mA, Low Noise CMOS RF-LDO™ Regulator	SOT-23-5	.90	.75	.60

(转下页)

★ 欢迎来电查询, 大批量订购, 价格优惠! ★

全部产品均以美元计价。 免费电话: 10800-1527031 (China Telecom - 中国电讯) — 10800-8527031 (CNCG - 中国网通)

digikoy.com.cn — 电话: (852) 3104 0500 — 传真: (852) 3104 0686

(CN082-09) 1065