

Digi-Key 零件编号	说明	封装	1	25	100	
LM2686MTC-ND	稳压开关电源电压转换器*	Regulated Switched Capacitor Voltage Converter*	14-TSSOP	2.53	1.92	1.47
LM2687LDCT-ND	低噪声稳压开关电源电压反相器	Low Noise Regulated Switched Capacitor Volt. Inverter	8-LLP	1.83	1.36	1.01
LM2687LDR-ND	低噪声稳压开关电源电压反相器	Low Noise Regulated Switched Capacitor Volt. Inverter	8-LLP	755.20/1,000		
LM2687MMCT-ND	低噪声稳压开关电源电压反相器*	Low Noise Regulated Switched Capacitor Volt. Inverter*	8-MSP	1.71	1.27	0.94
LM2687MMTR-ND	低噪声稳压开关电源电压反相器*	Low Noise Regulated Switched Capacitor Volt. Inverter*	8-MSP	704.00/1,000		
LM2694MT-ND	30V 600mA 降压开关稳压器*	30V, 600mA Buck Switching Regulator*	14-TSSOP	2.95	2.19	1.62
LM2694SDCT-ND	30V 600mA 降压开关稳压器*	30V, 600mA Buck Switching Regulator*	10-LLP	2.95	2.19	1.62
LM2694SDTR-ND	30V 600mA 降压开关稳压器*	30V, 600mA Buck Switching Regulator*	10-LLP	1216.00/1,000		
LM2695MH-ND	30V 1.25A 降压开关稳压器*	30V, 1.25A Buck Switching Regulator*	14-TSSOP	3.33	2.53	1.93
LM2695SDCT-ND	30V 1.25A 降压开关稳压器*	30V, 1.25A Buck Switching Regulator*	10-LLP	3.33	2.53	1.93
LM2695SDTR-ND	30V 1.25A 降压开关稳压器*	30V, 1.25A Buck Switching Regulator*	10-LLP	1675.80/1,000		
LM2696MXA-ND	3A 恒开降压稳压器*	3A Constant On Time Buck Regulator*	16-TSSOP	4.05	3.08	2.35
LM2698MM-ADJCT-ND	可调式 1.35A SIMPLE SWITCHER® 升压稳压器*	Adj. 1.35A SIMPLE SWITCHER® Boost Regulator*	8-MSP	4.35	3.31	2.53
LM2698MM-ADJTR-ND	可调式 1.35A SIMPLE SWITCHER® 升压稳压器*	Adj. 1.35A SIMPLE SWITCHER® Boost Regulator*	8-MSP	2192.40/1,000		
LM2700LD-ADJCT-ND	600kHz/1.25MHz 2.5A 步升 PWM DC-DC 转换器	600kHz/1.25MHz, 2.5A, Step-Up PWM DC-DC Converter	14-LLP	4.08	3.10	2.37
LM2700LD-ADJTR-ND	600kHz/1.25MHz 2.5A 步升 PWM DC-DC 转换器	600kHz/1.25MHz, 2.5A, Step-Up PWM DC-DC Converter	14-LLP	2053.80/1,000		
LM2700MT-ADJ-ND	600kHz/1.25MHz 2.5A 步升 PWM DC-DC 转换器*	600kHz/1.25MHz, 2.5A, Step-Up PWM DC-DC Converter*	14-TSSOP	4.08	3.10	2.37
LM2702MT-ADJ-ND	TFT 面板模块	TFT Panel Module	16-TSSOP	3.28	2.49	1.90
LM2703MF-ADJCT-ND	可调式微功率步升 DC-DC 转换器*	Adj. Micropower Step-Up DC-DC Converter*	SOT-23-5	2.42	1.80	1.33
LM2703MF-ADJTR-ND	可调式微功率步升 DC-DC 转换器*	Adj. Micropower Step-Up DC-DC Converter*	SOT-23-5	998.40/1,000		
LM2703EV-ND	LM2703 的评估板	Evaluation Board for LM2703		49.80	—	
LM2704MF-ADJCT-ND	可调式微功率步升 DC-DC 转换器*	Adj. Micropower Step-Up DC-DC Converter*	SOT-23-5	2.65	1.97	1.46
LM2704MF-ADJTR-ND	可调式微功率步升 DC-DC 转换器*	Adj. Micropower Step-Up DC-DC Converter*	SOT-23-5	1094.40/1,000		
LM2704EV-ND	LM2704 的评估板	Evaluation Board for LM2704		49.80	—	
LM2705MF-ADJCT-ND	步升 DC-DC 转换器, 带 150mA 峰值*	Step-Up DC-DC Converter with 150mA Peak Current*	SOT-23-5	2.41	1.80	1.33
LM2705MF-ADJTR-ND	步升 DC-DC 转换器, 带 150mA 峰值*	Step-Up DC-DC Converter with 150mA Peak Current*	SOT-23-5	997.12/1,000		
LM2715MT-ADJ-ND	TFT 面板模块	TFT Panel Module	16-TSSOP	3.05	2.32	1.77
LM2716MT-ND	双路 PWM DC-DC 转换器*	Dual PWM DC-DC Converter*	24-TSSOP	5.27	4.17	3.34
LM2717MT-ND	双路降压 DC-DC 转换器*	Dual Buck DC-DC Converter*	24-TSSOP	5.40	4.27	3.42
LM2722M-ND	高速同步/异步 MOSFET 驱动器	High Speed Sync./Async. MOSFET Driver	8-SOIC	2.78	2.11	1.61
LM2724ALDCT-ND	高速 3A 同步 MOSFET 驱动器	High Speed 3A Synchronous MOSFET Driver	8-LLP	2.78	2.11	1.61
LM2724ALDTR-ND	高速 3A 同步 MOSFET 驱动器	High Speed 3A Synchronous MOSFET Driver	8-LLP	1398.60/1,000		
LM2724AM-ND	高速 3A 同步 MOSFET 驱动器*	High Speed 3A Synchronous MOSFET Driver*	8-SOIC	2.78	2.11	1.61
LM2724ASDCT-ND	高速 3A 同步 MOSFET 驱动器	High Speed 3A Synchronous MOSFET Driver	8-LLP	2.78	2.11	1.61
LM2724ASDTR-ND	高速 3A 同步 MOSFET 驱动器	High Speed 3A Synchronous MOSFET Driver	8-LLP	1398.60/1,000		
LM2725M-ND	高速同步 MOSFET 驱动器*	High Speed Synchronous MOSFET Driver*	8-SOIC	2.85	2.17	1.66
LM2726M-ND	高速同步 MOSFET 驱动器*	High Speed Synchronous MOSFET Driver*	8-SOIC	3.23	2.46	1.88
LM2727MCT-ND	N 沟道 FET 同步降压稳压器控制器*	N-Channel FET Sync. Buck Regulator Controller*	14-TSSOP	2.98	2.27	1.73
LM2731XMFCF-ND	0.6/1.6MHz 升压转换器, 带 22V 内部 FET 开关*	0.6/1.6MHz Boost Converter w/22V Internal FET Switch*	SOT-23-5	2.58	1.96	1.50
LM2731XMFR-ND	0.6/1.6MHz 升压转换器, 带 22V 内部 FET 开关*	0.6/1.6MHz Boost Converter w/22V Internal FET Switch*	SOT-23-5	1297.80/1,000		
LM2731YMFCF-ND	0.6/1.6MHz 升压转换器, 带 22V 内部 FET 开关*	0.6/1.6MHz Boost Converter w/22V Internal FET Switch*	SOT-23-5	2.58	1.96	1.50
LM2731YMFTR-ND	0.6/1.6MHz 升压转换器, 带 22V 内部 FET 开关*	0.6/1.6MHz Boost Converter w/22V Internal FET Switch*	SOT-23-5	1297.80/1,000		
LM2733XMFCF-ND	0.6/1.6MHz 升压转换器, 带 40V 内部 FET 开关*	0.6/1.6MHz Boost Converter w/40V Internal FET Switch*	SOT-23-5	2.58	1.96	1.50
LM2733XMFR-ND	0.6/1.6MHz 升压转换器, 带 40V 内部 FET 开关*	0.6/1.6MHz Boost Converter w/40V Internal FET Switch*	SOT-23-5	1297.80/1,000		
LM2733YMFCF-ND	0.6/1.6MHz 升压转换器, 带 40V 内部 FET 开关*	0.6/1.6MHz Boost Converter w/40V Internal FET Switch*	SOT-23-5	2.58	1.96	1.50
LM2733YMFTR-ND	0.6/1.6MHz 升压转换器, 带 40V 内部 FET 开关*	0.6/1.6MHz Boost Converter w/40V Internal FET Switch*	SOT-23-5	1297.80/1,000		
LM2734XMKCT-ND	1A 负载降压 DC-DC 稳压器*	1A Load Buck DC-DC Regulator*	TSOT-23-6	3.58	2.72	2.08
LM2734XMKTR-ND	1A 负载降压 DC-DC 稳压器*	1A Load Buck DC-DC Regulator*	TSOT-23-6	1801.80/1,000		
LM2734YMKCT-ND	1A 负载降压 DC-DC 稳压器*	1A Load Buck DC-DC Regulator*	TSOT-23-6	2.98	2.27	1.73
LM2734YMKTR-ND	1A 负载降压 DC-DC 稳压器*	1A Load Buck DC-DC Regulator*	TSOT-23-6	1499.40/1,000		
LM2734ZMKCT-ND	1A 负载降压 DC-DC 稳压器	1A Load Buck DC-DC Regulator	6-TSOT	4.15	3.16	2.41
LM2734ZMKTR-ND	1A 负载降压 DC-DC 稳压器	1A Load Buck DC-DC Regulator	6-TSOT	2091.60/1,000		
LM2734ZSDCT-ND	1A 负载降压 DC-DC 稳压器*	1A Load Buck DC-DC Regulator*	6-LLP	4.15	3.16	2.41
LM2734ZSDTR-ND	1A 负载降压 DC-DC 稳压器*	1A Load Buck DC-DC Regulator*	6-LLP	2091.60/1,000		
LM2735XMFCF-ND	520/1.6MHz 升压 DC-DC 稳压器*	520/1.6MHz Boost DC-DC Regulator*	SOT-23-5	2.98	2.27	1.73
LM2735XMFR-ND	520/1.6MHz 升压 DC-DC 稳压器*	520/1.6MHz Boost DC-DC Regulator*	SOT-23-5	1499.40/1,000		
LM2735MYCT-ND	520/1.6MHz 升压 DC-DC 稳压器*	520/1.6MHz Boost DC-DC Regulator*	8-MSP	2.98	2.27	1.73
LM2735MYTR-ND	520/1.6MHz 升压 DC-DC 稳压器*	520/1.6MHz Boost DC-DC Regulator*	8-MSP	1499.40/1,000		
LM2736XMKCT-ND	750mA 负载降压 DC-DC 稳压器*	750mA Load Buck DC-DC Regulator*	TSOT-23-6	3.33	2.53	1.93
LM2736XMKTR-ND	750mA 负载降压 DC-DC 稳压器*	750mA Load Buck DC-DC Regulator*	TSOT-23-6	1675.80/1,000		
LM2736YMKCT-ND	750mA 负载降压 DC-DC 稳压器*	750mA Load Buck DC-DC Regulator*	TSOT-23-6	2.73	2.08	1.59
LM2736YMKTR-ND	750mA 负载降压 DC-DC 稳压器*	750mA Load Buck DC-DC Regulator*	TSOT-23-6	1373.40/1,000		
LM2737MTC-ND	N 沟道 FET 同步降压稳压器控制器	N-Channel FET Sync. Buck Regulator Controller	14-TSSOP	2.98	2.27	1.73
LM2742MTC-ND	N 沟道 FET 同步降压稳压器控制器*	N-Channel FET Sync. Buck Regulator Controller*	14-TSSOP	2.98	2.27	1.73
LM2743MTC-ND	N 沟道 FET 同步降压稳压器控制器*	N-Channel FET Sync. Buck Regulator Controller*	14-TSSOP	2.73	2.08	1.59
LM2744MTC-ND	低电压 N 沟道 MOSFET 同步降压稳压器控制器	Low Volt. N-Ch. MOSFET Sync. Buck Reg. Controller	14-TSSOP	3.09	2.30	1.70
LM2745MTC-ND	带有预偏压启动的同步降压稳压器控制器	Sync. Buck Controller with Pre-Bias Startup*	14-TSSOP	3.33	2.53	1.93
LM2746MXA-ND	低电压 N 沟道 MOSFET 同步降压稳压器控制器	Low Volt. N-Ch. MOSFET Sync. Buck Reg. Controller	14-TSSOP	3.10	2.36	1.80
LM2747MTC-ND	带有预偏压启动的同步降压稳压器控制器*	Sync. Buck Controller with Pre-Bias Startup*	14-TSSOP	3.45	2.63	2.01
LM2747MTCXCT-ND	带有预偏压启动的同步降压稳压器控制器*	Sync. Buck Controller with Pre-Bias Startup*	14-TSSOP	3.45	2.63	2.01
LM2747MTCXTR-ND	带有预偏压启动的同步降压稳压器控制器*	Sync. Buck Controller with Pre-Bias Startup*	14-TSSOP	4312.50/2,500		
LM2748MTC-ND	带有预偏压启动的同步降压稳压器控制器*	Sync. Buck Controller with Pre-Bias Startup*	14-TSSOP	3.13	2.38	1.82
LM2750LD-5.OCT-ND	低噪声 5.0V 稳压开关电源电压转换器	LN, 5.0V Regulator Switched Capacitor Voltage Converter	10-LLP	2.83	2.15	1.64
LM2750LD-5.0TR-ND	低噪声 5.0V 稳压开关电源电压转换器	LN, 5.0V Regulator Switched Capacitor Voltage Converter	10-LLP	1423.80/1,000		
LM2750LD-ADJCT-ND	低噪声可调稳压开关电源电压转换器	LN, Adj. Regulator Switched Capacitor Voltage Converter	10-LLP	2.83	2.15	1.64
LM2750LD-ADJTR-ND	低噪声可调稳压开关电源电压转换器	LN, Adj. Regulator Switched Capacitor Voltage Converter	10-LLP	1423.80/1,000		
LM2750LD-ADJEV-ND	LM2750LD-ADJ 的评估板*	Evaluation Board for LM2750LD-ADJ*		93.15	—	
LM2750SD-5.OCT-ND	5V 低噪声开关电源升压稳压器*	5V Low Noise Switched Capacitor Boost Regulator*	10-LLP	2.83	2.15	1.64
LM2750SD-5.0TR-ND	5V 低噪声开关电源升压稳压器*	5V Low Noise Switched Capacitor Boost Regulator*	10-LLP	1423.80/1,000		
LM2751SD-ACT-ND	稳压 2X, 1.5X 白色 LED 驱动器*	Regulated 2X, 1.5X White LED Driver*	10-LLP	2.63	2.00	1.53
LM2751SD-ATR-ND	稳压 2X, 1.5X 白色 LED 驱动器*	Regulated 2X, 1.5X White LED Driver*	10-LLP	1323.00/1,000		
LM2751SD-BCT-ND	稳压 2X, 1.5X 白色 LED 驱动器*	Regulated 2X, 1.5X White LED Driver*	10-LLP	2.63	2.00	1.53
LM2751SD-BTR-ND	稳压 2X, 1.5X 白色 LED 驱动器*	Regulated 2X, 1.5X White LED Driver*	10-LLP	1323.00/1,000		
LM2753SDCT-ND	高功率开关电源电压转换器/闪光灯 LED 控制器*	High Power Switched Capacitor Voltage Converter/Flash LED Driver*	10-LLP	3.10	2.36	1.80
LM2753SDTR-ND	高功率开关电源电压转换器/闪光灯 LED 控制器*	High Power Switched Capacitor Voltage Converter/Flash LED Driver*	10-LLP	1562.40/1,000		
LM2754SQCT-ND	800mA 开关电源闪光灯 LED 控制器*	800mA Switched Capacitor Flash LED Driver*	24-LLP	3.10	2.36	1.80
LM2754SQR-ND	800mA 开关电源闪光灯 LED 控制器*	800mA Switched Capacitor Flash LED Driver*	24-LLP	1562.40/1,000		
LM2754SQEV-ND	LM2754SQ 的评估板*	Evaluation Board for LM2754SQ*		123.30	—	
LM2755TMCT-ND	带 I ² C 兼容接口的充电泵 LED 控制器*	Charge Pump LED Controller with I ² C Compatible Interface*	18-microSMD	3.58	2.72	2.08
LM2755TMTR-ND	带 I ² C 兼容接口的充电泵 LED 控制器*	Charge Pump LED Controller with I ² C Compatible Interface*	18-microSMD	475.48/250		
LM2756TMCT-ND	180mA 开关电源多显示无电感 LED 驱动器*	180mA Switched Capacitor Multi-Display Inductorless LED Driver*	20-µSMD	4.28	3.25	2.48
LM2756TMTR-ND	180mA 开关电源多显示无电感 LED 驱动器*	180mA Switched Capacitor Multi-Display Inductorless LED Driver*	20-µSMD	568.58/250		
LM2757TMCT-ND	在关闭模式下带有高阻抗输出的开关电源升压稳压器*	Switched Capacitor Boost Regulator with High Impedance Output in Shutdown*	12-microSMD	3.58	2.72	2.08
LM2757TMTR-ND	在关闭模式下带有高阻抗输出的开关电源升压稳压器*	Switched Capacitor Boost Regulator with High Impedance Output in Shutdown*	12-microSMD	475.48/250		
LM2760M5CT-ND	3.3V 稳压开关电源电压转换器*	3.3V, Regulator Switched Capacitor Voltage Converter*	SOT-23-5	2.89	2.15	1.59
LM2760M5TR-ND	3.3V 稳压开关电源电压转换器	3.3V, Regulator Switched Capacitor Voltage Converter	SOT-23-5	1191.68/1,000		
LM2765M6CT-ND	开关电源电压转换器*	Switched Capacitor Voltage Converter*	SOT-23-6	1.09	0.80	0.58
LM2765M6TR-ND	开关电源电压转换器*	Switched Capacitor Voltage Converter*	SOT-23-6	377.00/1,000		
LM2766M6CT-ND	开关电源电压转换器*	Switched Capacitor Voltage Converter*	SOT-23-6	1.09	0.80	0.58

* 符合 RoHS 规范要求

(转下页)

★ 欢迎来电查询, 大批量订购, 价格优惠! ★

