

Digi-Key 零件编号	说明	封装	1	单价★	100
LM3502ITL-25CT-ND	用于白色 LED 的 25V 升升转换器	25V Step-Up Converter for White LED	10-microSMD	5.08	3.86 2.95
LM3502ITL-25TR-ND	用于白色 LED 的 25V 升升转换器	25V Step-Up Converter for White LED	10-microSMD	6.10	674.98/250
LM3502ITL-44CT-ND	用于白色 LED 的 44V 升升转换器	44V Step-Up Converter for White LED	10-microSMD	6.10	4.64 3.54
LM3502ITL-44TR-ND	用于白色 LED 的 44V 升升转换器	44V Step-Up Converter for White LED	10-microSMD	121.20	811.30/250
LM3502ITL-44EV-ND	LM3502ITL-44 的评估板*	Evaluation Board for LM3502ITL-44*	—	—	—
LM3502SQ-16CT-ND	用于白色 LED 的 16V 升升转换器*	16V Step-Up Converter for White LED*	16-LFP	4.58	3.48 2.66
LM3502SQ-16TR-ND	用于白色 LED 的 16V 升升转换器*	16V Step-Up Converter for White LED*	16-LFP	—	2305.80/1,000
LM3502SQ-25CT-ND	用于白色 LED 的 25V 升升转换器	25V Step-Up Converter for White LED	16-LFP	4.85	3.69 2.82
LM3502SQ-25TR-ND	用于白色 LED 的 25V 升升转换器	25V Step-Up Converter for White LED	16-LFP	—	2444.40/1,000
LM3502SQ-35CT-ND	用于白色 LED 的 35V 升升转换器*	35V Step-Up Converter for White LED*	16-LFP	5.33	4.05 3.09
LM3502SQ-35TR-ND	用于白色 LED 的 35V 升升转换器*	35V Step-Up Converter for White LED*	16-LFP	—	2683.80/1,000
LM3502SQ-44CT-ND	用于白色 LED 的 44V 升升转换器*	44V Step-Up Converter for White LED*	16-LFP	5.83	4.43 3.38
LM3502SQ-44TR-ND	用于白色 LED 的 44V 升升转换器*	44V Step-Up Converter for White LED*	16-LFP	—	2935.80/1,000
LM3503ITL-16CT-ND	16V 双显示器恒流 LED 驱动器*	16V Dual Display Constant Current LED Driver*	10-microSMD	5.00	3.80 2.90
LM3503ITL-16TR-ND	16V 双显示器恒流 LED 驱动器*	16V Dual Display Constant Current LED Driver*	10-microSMD	—	665.00/250
LM3503ITL-25CT-ND	25V 双显示器恒流 LED 驱动器*	25V Dual Display Constant Current LED Driver*	10-microSMD	5.08	3.86 2.95
LM3503ITL-25TR-ND	25V 双显示器恒流 LED 驱动器*	25V Dual Display Constant Current LED Driver*	10-microSMD	—	674.98/250
LM3503ITL-25EV-ND	LM3503ITL-25 的评估板*	Evaluation Board for LM3503ITL-25*	—	121.20	—
LM3503ITL-35CT-ND	35V 双显示器恒流 LED 驱动器*	35V Dual Display Constant Current LED Driver	10-microSMD	5.60	4.26 3.25
LM3503ITL-35TR-ND	35V 双显示器恒流 LED 驱动器*	35V Dual Display Constant Current LED Driver	10-microSMD	—	744.80/250
LM3503ITL-44CT-ND	44V 双显示器恒流 LED 驱动器*	44V Dual Display Constant Current LED Driver	10-microSMD	6.10	4.64 3.54
LM3503ITL-44TR-ND	44V 双显示器恒流 LED 驱动器*	44V Dual Display Constant Current LED Driver	10-microSMD	—	811.30/250
LM3503SQ-16CT-ND	16V 双显示器恒流 LED 驱动器*	16V Dual Display Constant Current LED Driver	16-LFP	4.58	3.48 2.66
LM3503SQ-16TR-ND	16V 双显示器恒流 LED 驱动器*	16V Dual Display Constant Current LED Driver	16-LFP	—	2305.80/1,000
LM3503SQ-25CT-ND	25V 双显示器恒流 LED 驱动器*	25V Dual Display Constant Current LED Driver	16-LFP	4.85	3.69 2.82
LM3503SQ-25TR-ND	25V 双显示器恒流 LED 驱动器*	25V Dual Display Constant Current LED Driver	16-LFP	—	2444.40/1,000
LM3503SQ-35CT-ND	35V 双显示器恒流 LED 驱动器*	35V Dual Display Constant Current LED Driver	16-LFP	5.33	4.05 3.09
LM3503SQ-35TR-ND	35V 双显示器恒流 LED 驱动器*	35V Dual Display Constant Current LED Driver	16-LFP	—	2683.80/1,000
LM3503SQ-44CT-ND	44V 双显示器恒流 LED 驱动器*	44V Dual Display Constant Current LED Driver*	16-LFP	5.83	4.43 3.38
LM3503SQ-44TR-ND	44V 双显示器恒流 LED 驱动器*	44V Dual Display Constant Current LED Driver*	16-LFP	—	2935.80/1,000
LM3508TCT-ND	同步磁性恒流白色 LED 驱动器*	Sync. Magnetic Constant Current White LED Driver*	8-MQOP	2.63	2.00 1.53
LM3508TTR-ND	同步磁性恒流白色 LED 驱动器*	Sync. Magnetic Constant Current White LED Driver*	8-MQOP	—	349.13/250
LM3509SDCT-ND	高效升压白色 LED/OLED*	High Efficiency Boost White LED/OLED*	10-LFP	4.75	3.61 2.76
LM3509SDTR-ND	高效升压白色 LED/OLED*	High Efficiency Boost White LED/OLED*	10-LFP	—	2394.00/1,000
LM3519MK-20CT-ND	20V 高频升压白色 LED 驱动器*	20V High Frequency Boost White LED Driver*	SOT-23-6	2.85	2.17 1.66
LM3519MK-20TR-ND	20V 高频升压白色 LED 驱动器*	20V High Frequency Boost White LED Driver*	SOT-23-6	—	1436.40/1,000
LM3520SDCT-ND	集成式白色 LED 驱动器	Integrated White LED Driver	14-LFP	6.18	4.70 3.59
LM3520SDTR-ND	集成式白色 LED 驱动器	Integrated White LED Driver	14-LFP	—	3112.20/1,000
LM3524DM-ND	稳压型脉宽调制器*	Regulating Pulse Width Modulator*	16-SOIC	1.58	1.18 0.87
LM3524DN-ND	稳压型脉宽调制器*	Regulating Pulse Width Modulator*	16-Dip	1.98	1.48 1.09
LM3525M-H-ND	单端口 USB 电源开关/过电流保护*	Single Port USB Power Switch/Over-Current Protection*	8-SOIC	2.11	1.57 1.16
LM3525M-L-ND	单端口 USB 电源开关/过电流保护*	Single Port USB Power Switch/Over-Current Protection*	8-SOIC	2.11	1.57 1.16
LM3526M-H-ND	双端口 USB 电源开关/过电流保护*	Dual Port USB Power Switch/Over-Current Protection*	8-SOIC	2.39	1.78 1.31
LM3526M-L-ND	双端口 USB 电源开关/过电流保护*	Dual Port USB Power Switch/Over-Current Protection*	8-SOIC	2.39	1.78 1.31
LM3544M-H-ND	四端口 USB 电源开关/过电流保护*	Quad Port USB Power Switch/Over-Current Protection*	16-SOIC	3.83	2.91 2.22
LM3551SDCT-ND	1A 白色 LED 驱动器*	1A White LED Driver*	14-LFP	2.83	2.15 1.64
LM3551SDTR-ND	1A 白色 LED 驱动器*	1A White LED Driver*	14-LFP	—	1423.80/1,000
LM3552SDCT-ND	1A 白色 LED 驱动器*	1A White LED Driver*	14-LFP	2.83	2.15 1.64
LM3552SDTR-ND	1A 白色 LED 驱动器*	1A White LED Driver*	14-LFP	—	1423.80/1,000
LM3552SDEV-ND	LM3552SD 的评估板*	Evaluation Board for LM3552SD*	—	144.15	—
LM3557SD-2CT-ND	用于白色 LED 的升升转换器*	Step-Up Converter for White LED Applications*	8-LFP	3.07	2.28 1.69
LM3557SD-2TR-ND	用于白色 LED 的升升转换器*	Step-Up Converter for White LED Applications*	8-LFP	—	1267.20/1,000
LM3570SDCT-ND	低噪音白色 LED 驱动器系统	Low Noise White LED Driver System	14-LFP	3.33	2.53 1.93
LM3570SDTR-ND	低噪音白色 LED 驱动器系统	Low Noise White LED Driver System	14-LFP	—	1675.80/1,000
LM3578AM-ND	开关稳压器*	Switching Regulator*	8-SOIC	2.11	1.57 1.16
LM3578AMXTR-ND	开关稳压器*	Switching Regulator*	8-SOIC	—	2125.00/2,500
LM3578AN-ND	开关稳压器*	Switching Regulator*	8-Dip	2.11	1.57 1.16
LM3590MFCT-ND	三路白色 LED 驱动器*	Triple White LED Driver*	SOT-23-5	1.54	1.13 0.82
LM3590MFTR-ND	三路白色 LED 驱动器*	Triple White LED Driver*	SOT-23-5	—	533.00/1,000
LM3590MFEV-ND	LM3590MF 的评估板*	Evaluation Board for LM3590MF*	—	93.15	—
LM3595LDCT-ND	四路并联白色 LED 驱动器*	Quad Parallel White LED Driver*	10-LFP	2.65	1.97 1.46
LM3595LDTR-ND	四路并联白色 LED 驱动器*	Quad Parallel White LED Driver*	10-LFP	—	1094.40/1,000
LM3595LDEV-ND	LM3595LD 的评估板*	Evaluation Board for LM3595LD*	—	95.70	—
LM3621M-ND	单节锂离子电池充电控制器	Single Cell Lithium-Ion Battery Charger Controller	16-SOIC	2.98	2.27 1.73
LM3622AM-4.1-ND	4.1V 锂离子电池充电控制器	4.1V, Lithium-Ion Battery Charger Controller	8-SOIC	2.78	2.11 1.61
LM3622AM-4.2-ND	4.2V 锂离子电池充电控制器*	4.2V, Lithium-Ion Battery Charger Controller*	8-SOIC	2.78	2.11 1.61
LM3622AM-8.2-ND	8.2V 锂离子电池充电控制器	8.2V, Lithium-Ion Battery Charger Controller	8-SOIC	2.78	2.11 1.61
LM3622AM-8.4-ND	8.4V 锂离子电池充电控制器*	8.4V, Lithium-Ion Battery Charger Controller*	8-SOIC	2.78	2.11 1.61
LM3622M-4.1-ND	4.1V 锂离子电池充电控制器	4.1V, Lithium-Ion Battery Charger Controller	8-SOIC	2.64	1.96 1.45
LM3622M-4.2-ND	4.2V 锂离子电池充电控制器*	4.2V, Lithium-Ion Battery Charger Controller*	8-SOIC	2.64	1.96 1.45
LM3622M-8.2-ND	8.2V 锂离子电池充电控制器	8.2V, Lithium-Ion Battery Charger Controller	8-SOIC	2.64	1.96 1.45
LM3622M-8.4-ND	8.4V 锂离子电池充电控制器	8.4V, Lithium-Ion Battery Charger Controller	8-SOIC	2.64	1.96 1.45
LM3668SD-ACT-ND	双源 USB/AC 锂化学充电器*	Dual Source USB/AC Li Chemistry Charger*	10-LFP	1.92	1.43 1.06
LM3668SD-ATR-ND	双源 USB/AC 锂化学充电器*	Dual Source USB/AC Li Chemistry Charger*	10-LFP	—	793.60/1,000
LM3668SD-BCT-ND	双源 USB/AC 锂化学充电器, 带低压降模式*	Dual Source USB/AC Li Chemistry Charger w/LDO Mode*	10-LFP	1.92	1.43 1.06
LM3668SD-BTR-ND	双源 USB/AC 锂化学充电器, 带低压降模式*	Dual Source USB/AC Li Chemistry Charger w/LDO Mode*	10-LFP	—	793.60/1,000
LM3668SDCT-ND	双源 USB/AC 锂化学充电器 IC*	Dual Source USB/AC Li Chemistry Charger IC*	10-LFP	1.92	1.43 1.06
LM3668SDTR-ND	双源 USB/AC 锂化学充电器 IC*	Dual Source USB/AC Li Chemistry Charger IC*	10-LFP	—	793.60/1,000
LM3668SD-3.3CT-ND	1A 双路高效 DC/DC 转换器*	1A Dual High Efficiency DC/DC Converter*	12-LFP	5.48	4.34 3.48
LM3668SD-3.3TR-ND	1A 双路高效 DC/DC 转换器*	1A Dual High Efficiency DC/DC Converter*	12-LFP	—	3236.40/1,000
LM3670MF-ADJCT-ND	可调式迷你降压 DC-DC 转换器	Adj., Mini Buck DC-DC Converter	SOT-23-5	3.04	2.26 1.67
LM3670MF-ADJTR-ND	可调式迷你降压 DC-DC 转换器	Adj., Mini Buck DC-DC Converter	SOT-23-5	—	1254.40/1,000
LM3670MF-1.2CT-ND	1.2V 迷你降压 DC-DC 转换器*	1.2V, Mini Buck DC-DC Converter*	SOT-23-5	3.04	2.26 1.67
LM3670MF-1.2TR-ND	1.2V 迷你降压 DC-DC 转换器*	1.2V, Mini Buck DC-DC Converter*	SOT-23-5	—	1254.40/1,000
LM3670MF-1.5CT-ND	1.5V 迷你降压 DC-DC 转换器*	1.5V, Mini Buck DC-DC Converter*	SOT-23-5	3.04	2.26 1.67
LM3670MF-1.5TR-ND	1.5V 迷你降压 DC-DC 转换器*	1.5V, Mini Buck DC-DC Converter*	SOT-23-5	—	1254.40/1,000
LM3670MF-1.6CT-ND	1.6V 迷你降压 DC-DC 转换器*	1.6V, Mini Buck DC-DC Converter*	SOT-23-5	3.04	2.26 1.67
LM3670MF-1.6TR-ND	1.6V 迷你降压 DC-DC 转换器*	1.6V, Mini Buck DC-DC Converter*	SOT-23-5	—	1254.40/1,000
LM3670MF-1.8CT-ND	1.8V 迷你降压 DC-DC 转换器*	1.8V, Mini Buck DC-DC Converter*	SOT-23-5	2.79	2.07 1.53
LM3670MF-1.8TR-ND	1.8V 迷你降压 DC-DC 转换器*	1.8V, Mini Buck DC-DC Converter*	SOT-23-5	—	1254.40/1,000
LM3670MF-1.875CT-ND	1.875V 迷你降压 DC-DC 转换器*	1.875V, Mini Buck DC-DC Converter*	SOT-23-5	3.04	2.26 1.67
LM3670MF-1.875TR-ND	1.875V 迷你降压 DC-DC 转换器*	1.875V, Mini Buck DC-DC Converter*	SOT-23-5	—	1254.40/1,000
LM3670MF-2.5CT-ND	2.5V 迷你降压 DC-DC 转换器*	2.5V, Mini Buck DC-DC Converter*	SOT-23-5	3.04	2.26 1.67
LM3670MF-2.5TR-ND	2.5V 迷你降压 DC-DC 转换器*	2.5V, Mini Buck DC-DC Converter*	SOT-23-5	—	1254.40/1,000
LM3670MF-3.3CT-ND	3.3V 迷你降压 DC-DC 转换器*	3.3V, Mini Buck DC-DC Converter*	SOT-23-5	3.04	2.26 1.67
LM3670MF-3.3TR-ND	3.3V 迷你降压 DC-DC 转换器*	3.3V, Mini Buck DC-DC Converter*	SOT-23-5	—	1254.40/1,000
LM3670MFX-ADJCT-ND	可调式迷你降压 DC-DC 转换器*	Adj., Mini Buck DC-DC Converter*	SOT-23-5	3.04	2.26 1.67
LM3670MFX-ADJTR-ND	可调式迷你降压 DC-DC 转换器*	Adj., Mini Buck DC-DC Converter*	SOT-23-5	—	3675.00/3,000
LM3671MF-ADJCT-ND	可调式 600mA 降压 DC-DC 转换器*	Adj., 600mA Buck DC-DC Converter*	SOT-23-5	2.55	1.94 1.48
LM3671MF-ADJTR-ND	可调式 600mA 降压 DC-DC 转换器*	Adj., 600mA Buck DC-DC Converter*	SOT-23-5	—	1285.20/1,000

* 符合 RoHS 规范要求

(转下页)

★ 欢迎来电查询, 大批量订购, 价格优惠! ★

全部产品均以美元计价。 免费电话: 10800-1527031 (China Telecom - 中国电信) — 10800-8527031 (CNCG - 中国网通)

digikey.com.cn — 电话: (852) 3104 0500 — 传真: (852) 3104 0686

(CN082-09) 1129