

Digi-Key 零件编号	说明	封装	单价★	1	25	100
LM5111-1MYTR-ND	双路 5A 复合栅极驱动器*	Dual 5A Compound Gate Driver*	8-MSOP	912.64	1,000	
LM5111-2M-ND	双路 5A 复合栅极驱动器*	Dual 5A Compound Gate Driver*	8-SOIC	1.92	1.43	1.06
LM5111-2MYCT-ND	双路 5A 复合栅极驱动器*	Dual 5A Compound Gate Driver*	8-MSOP	2.21	1.64	1.22
LM5111-2MYTR-ND	双路 5A 复合栅极驱动器*	Dual 5A Compound Gate Driver*	8-MSOP	912.64	1,000	
LM5111-3M-ND	双路 5A 复合栅极驱动器*	Dual 5A Compound Gate Driver*	8-SOIC	1.92	1.43	1.06
LM5111-3MYCT-ND	双路 5A 复合栅极驱动器*	Dual 5A Compound Gate Driver*	8-MSOP	2.21	1.64	1.22
LM5111-3MYTR-ND	双路 5A 复合栅极驱动器*	Dual 5A Compound Gate Driver*	8-MSOP	912.64	1,000	
LM5112MYCT-ND	微型 7A MOSFET 栅极驱动器*	Tiny 7A MOSFET Gate Driver*	8-MSOP	1.78	1.31	.95
LM5112MYTR-ND	微型 7A MOSFET 栅极驱动器*	Tiny 7A MOSFET Gate Driver*	8-MSOP	617.50	1,000	
LM5112SDCT-ND	微型 7A MOSFET 栅极驱动器*	Tiny 7A MOSFET Gate Driver*	6-LLP	1.78	1.31	.95
LM5112SDTR-ND	微型 7A MOSFET 栅极驱动器*	Tiny 7A MOSFET Gate Driver*	6-LLP	617.50	1,000	
LM5115MTC-ND	二次侧后置稳压器控制器*	Secondary Side Post Regulator Controller*	16-TSSOP	4.28	3.25	2.48
LM5115SDCT-ND	二次侧后置稳压器控制器*	Secondary Side Post Regulator Controller*	16-LLP	4.28	3.25	2.48
LM5115SDTR-ND	二次侧后置稳压器控制器*	Secondary Side Post Regulator Controller*	16-LLP	2154.60	1,000	
LM5116MH-ND	宽范围同步降压控制器*	Wide Range Synchronous Buck Controller*	20-TSSOP	5.88	4.65	3.73
LM5574EVAL-ND	LM5574 评估板	Evaluation Board for LM5574		39.88	—	—
LM5574MT-ND	75V 0.5A 降压开关稳压器*	75V, 0.5A Buck Switching Regulator*	16-TSSOP	3.93	2.99	2.28
LM5575EVAL-ND	LM5575 评估板	Evaluation Board for LM5575		39.88	—	—
LM5575MH-ND	75V 1.5A 降压开关稳压器*	75V, 1.5A Buck Switching Regulator*	16-TSSOP	5.10	3.88	2.96
LM5576EVAL-ND	LM5576 评估板	Evaluation Board for LM5576		39.88	—	—
LM5657MH-ND	75V 3A 降压开关稳压器*	75V, 3A Buck Switching Regulator*	20-TSSOP	5.80	4.59	3.68
LM5642MH-ND	高电压双路同步降压转换器*	High Voltage, Dual Sync. Buck Converter*	20-ETSSOP	4.28	3.25	2.48
LM5642MTC-ND	高电压双路同步降压转换器*	High Voltage, Dual Sync. Buck Converter*	28-TSSOP	4.28	3.25	2.48
LM5642MT-ND	高电压双路同步降压转换器*	High Voltage, Dual Sync. Buck Converter*	28-TSSOP	4.53	3.44	2.63
LM6132AIM-ND	双路高速/低功耗 7MHz 清缓存运算放大器*	Dual High Speed/Low Power 7MHz, Rail-to-Rail Op Amp*	8-SOIC	3.40	2.59	1.98
LM6132BIM-ND	双路高速/低功耗 7MHz 清缓存运算放大器*	Dual High Speed/Low Power 7MHz, Rail-to-Rail Op Amp*	8-SOIC	2.65	2.02	1.54
LM6132BIN-ND	双路高速/低功耗 7MHz 清缓存运算放大器*	Dual High Speed/Low Power 7MHz, Rail-to-Rail Op Amp*	8-Dip	2.65	2.02	1.54
LM6134AIM-ND	四路高速/低功耗 7MHz 清缓存运算放大器*	Quad High Speed/LP 7MHz, Rail-to-Rail Op Amp*	14-SOIC	3.90	2.97	2.27
LM6134BIM-ND	四路高速/低功耗 7MHz 清缓存运算放大器*	Quad High Speed/LP 7MHz, Rail-to-Rail Op Amp*	14-SOIC	3.35	2.55	1.95
LM6134BIMXTR-ND	四路低功率 10MHz 清缓存输入/输出运算放大器*	Quad Low Power 10MHz, Rail-to-Rail, I/O, Op Amp*	14-SOIC	4187.50	2,500	
LM6134BIN-ND	四路高速/低功耗 7MHz 清缓存运算放大器*	Quad High Speed/Low Power, 7MHz, Rail-to-Rail Op Amp*	14-Dip	3.65	2.77	2.11
LM6142AIM-ND	双路高速/低功耗 7MHz 清缓存运算放大器*	Dual High Speed/Low Power Rail-to-Rail Op Amp*	8-SOIC	5.25	3.99	3.05
LM6142BIM-ND	双路高速/低功耗 7MHz 清缓存运算放大器*	Dual High Speed/Low Power Rail-to-Rail Op Amp*	8-SOIC	4.70	3.58	2.73
LM6144BIM-ND	四路高速/低功耗 17MHz 清缓存运算放大器*	Quad High Speed/Low Power 17MHz R-R Op Amp*	14-SOIC	5.25	4.15	3.33
LM6152ACM-ND	双路高速 75MHz 清缓存输入/输出运算放大器, Vos = 4mV*	Dual High Speed 75MHz, R-R, I/O, Op Amp, Vos = 4mV*	8-SOIC	3.93	2.99	2.28
LM6152BCM-ND	双路高速 75MHz 清缓存输入/输出运算放大器, Vos = 4mV*	Dual High Speed 75MHz, R-R, I/O, Op Amp, Vos = 4mV*	8-SOIC	3.18	2.42	1.85
LM6154BCM-ND	四路高速 75MHz 清缓存输入/输出运算放大器, Vos = 7mV*	Quad High Speed 75MHz, R-R, I/O, Op Amp, Vos = 7mV*	14-SOIC	5.71	4.52	3.62
LM6171AIM-ND	电压反馈低失真低功率运算放大器*	Voltage Feedback Low Distortion, Low Power Op Amp*	8-SOIC	3.08	2.34	1.79
LM6171BIM-ND	电压反馈低失真低功率运算放大器*	Voltage Feedback Low Distortion, Low Power Op Amp*	8-SOIC	2.53	1.92	1.47
LM6171BIN-ND	电压反馈低失真低功率运算放大器*	Voltage Feedback Low Distortion, Low Power Op Amp*	8-Dip	2.53	1.92	1.47
LM6172IM-ND	双路高速低功率低失真电压反馈运算放大器*	Dual HS LP, Low Distortion, Voltage Feedback Op Amp*	8-SOIC	3.63	2.76	2.11
LM6172IMXCT-ND	双路高速低功率低失真电压反馈运算放大器*	Dual HS LP, Low Distortion, Voltage Feedback Op Amp*	8-SOIC	3.63	2.76	2.11
LM6172IMXTR-ND	双路高速低功率低失真电压反馈运算放大器*	Dual HS LP, Low Distortion, Voltage Feedback Op Amp*	8-SOIC	4531.25	2,500	
LM6172IN-ND	双路高速低功率低失真电压反馈运算放大器*	Dual HS LP, Low Distortion, Voltage Feedback Op Amp*	8-Dip	3.63	2.76	2.11
LM6181IM-8-ND	100mA 100MHz 电流反馈放大器*	100mA, 100MHz Current Feedback Amp*	8-SOIC	2.65	2.02	1.54
LM6181IN-ND	100MHz 电流反馈放大器*	Current Feedback Amp, 100MHz*	8-Dip	2.65	2.02	1.54
LM6211MFC-ND	低噪声清缓存输出运算放大器*	Low Noise, Rail-to-Rail Out Op Amp*	SOT-23-5	2.58	1.96	1.50
LM6211MFR-ND	低噪声清缓存输出运算放大器*	Low Noise, Rail-to-Rail Out Op Amp*	SOT-23-5	1297.80	1,000	
LM6511IM-ND	180nS 3V 比较器*	180nS, 3V, Comparator*	8-SOIC	2.65	2.02	1.54
LM6588MA-ND	TFT-LCD 四路 16V 清缓存输入/输出高输出电流运算放大器*	TFT-LCD Quad, 16V RRIO High Output Current Op Amp*	14-SOIC	2.73	2.08	1.59
LM6588MT-ND	TFT-LCD 四路 16V 清缓存输入/输出高输出电流运算放大器*	TFT-LCD Quad, 16V RRIO High Output Current Op Amp*	14-TSSOP	2.73	2.08	1.59
LM7121IM-ND	235MHz 微型低功率电压反馈放大器*	235MHz Tiny Low Power Voltage Feedback Amp*	8-SOIC	3.01	2.24	1.65
LM7121IM5CT-ND	235MHz 微型低功率电压反馈放大器*	235MHz Tiny Low Power Voltage Feedback Amp*	SOT-23-5	3.01	2.24	1.65
LM7121IM5TR-ND	235MHz 微型低功率电压反馈放大器*	235MHz Tiny Low Power Voltage Feedback Amp*	SOT-23-5	1241.60	1,000	
LM7171AIM-ND	极高速高输出电压反馈放大器, A 级*	Very High Speed High Out Volt. Feedback Amp, A Grade*	8-SOIC	2.88	2.19	1.67
LM7171AIN-ND	极高速高输出电压反馈放大器, A 级*	Very High Speed High Out Volt. Feedback Amp, A Grade*	8-Dip	2.88	2.19	1.67
LM7171BIM-ND	极高速高输出电压反馈放大器*	Very High Speed High Out Voltage Feedback Amp*	8-SOIC	2.53	1.92	1.47
LM7171BIMXTR-ND	极高速高输出电压反馈放大器*	Very High Speed High Out Voltage Feedback Amp*	8-SOIC	3156.25	2,500	
LM7171BIN-ND	极高速高输出电压反馈放大器*	Very High Speed High Out Voltage Feedback Amp*	8-Dip	2.53	1.92	1.47
LM7301IM-ND	低功率 4MHz GBW 清缓存输入/输出运算放大器*	Low Power, 4MHz GBW, Rail-to-Rail, In/Out Op Amp*	8-SOIC	2.26	1.68	1.25
LM7301IM5CT-ND	低功率 4MHz GBW 清缓存输入/输出运算放大器*	Low Power, 4MHz GBW, Rail-to-Rail, In/Out Op Amp*	SOT-23-5	2.26	1.68	1.25
LM7301IM5TR-ND	低功率 4MHz GBW 清缓存输入/输出运算放大器*	Low Power, 4MHz GBW, Rail-to-Rail, In/Out Op Amp*	SOT-23-5	934.40	1,000	
LM7372LDC-ND	双路高速高输出电流运算放大器*	Dual High Speed, High Output Current Op Amp	8-LLP	4.70	3.58	2.73
LM7372LDR-ND	双路高速高输出电流运算放大器*	Dual High Speed, High Output Current Op Amp	8-LLP	2368.80	1,000	
LM7372IMA-ND	双路高速高输出电流运算放大器*	Dual High Speed, High Output Current Op Amp*	16-SOIC	4.70	3.58	2.73
LM7372MR-ND	双路高速高输出电流运算放大器*	Dual High Speed, High Output Current Op Amp*	8-PSOP	4.70	3.58	2.73
LM7808CT-ND	8V 1.0A 正稳压器*	8V, 1.0A Positive Voltage Regulator*	TO-220	1.67	1.25	.92
LM7905CTNS-ND	5V 1.5A 负稳压器*	5V, 1.5A Negative Voltage Regulator*	TO-220	1.67	1.25	.92
LM7912CT-ND	12V 1.5A 负稳压器*	12V, 1.5A Negative Voltage Regulator*	TO-220	1.67	1.25	.92
LM7915CT-ND	15V 1.5A 负稳压器*	15V, 1.5A Negative Voltage Regulator*	TO-220	1.67	1.25	.92
LM8207MT-ND	TFT 18 Gamma 缓冲器 + VCOM 驱动器 + 电压基准*	TFT 18 Gamma Buffer + VCOM Driver + Volt. Reference*	48-TSSOP	4.58	3.48	2.66
LM8261M5CT-ND	清缓存输入/输出高输出电流和无限电容负载运算放大器*	RRIO, High Op Current, Unlimited Cap Load Op Amp*	SOT-23-5	2.82	2.10	1.55
LM8261M5TR-ND	清缓存输入/输出高输出电流和无限电容负载运算放大器*	RRIO, High Op Current, Unlimited Cap Load Op Amp*	SOT-23-5	1164.80	1,000	
LM8262MMCT-ND	清缓存输入/输出高输出电流和无限电容负载运算放大器*	RRIO, High Op Current, Unlimited Cap Load Op Amp*	8-MSOP	2.50	1.90	1.45
LM8262MMTR-ND	清缓存输入/输出高输出电流和无限电容负载运算放大器*	RRIO, High Op Current, Unlimited Cap Load Op Amp*	8-MSOP	1204.48	1,000	
LM8272MMCT-ND	清缓存输入/输出高输出无限电容负载运算放大器*	RRIO, High Output, Unlimited Cap Load Op Amp*	8-MSOP	3.10	2.36	1.80
LM8272MMTR-ND	清缓存输入/输出高输出无限电容负载运算放大器*	RRIO, High Output, Unlimited Cap Load Op Amp*	8-MSOP	1562.40	1,000	
LM8322JGR8CT-ND	移动输入/输出配件*	Mobile I/O Companion*	36-microArray	5.29	4.19	3.36
LM8322JGR8TR-ND	移动输入/输出配件*	Mobile I/O Companion*	36-microArray	3124.80	1,000	
LM8333FLQ8YCT-ND	移动输入/输出配件*	Mobile I/O Companion*	32-LLP	3.89	3.08	2.47
LM8333FLQ8YTR-ND	移动输入/输出配件*	Mobile I/O Companion*	32-LLP	587.38	250	
LM8333GGR8CT-ND	带扩展输入/输出的键盘控制器*	Keypad Controller with I/O Expansion*	49-microArray	4.88	3.71	2.83
LM8333GGR8TR-ND	带扩展输入/输出的键盘控制器*	Keypad Controller with I/O Expansion*	49-microArray	2457.00	1,000	
LM8342SDCT-ND	可编程 TFT Vcom 校准器*	Programmable TFT Vcom Calibrator*	10-LLP	1.95	1.45	1.08
LM8342SDTR-ND	可编程 TFT Vcom 校准器*	Programmable TFT Vcom Calibrator*	10-LLP	806.40	1,000	
LM8364BALMF20CT-ND	微功率欠电压检测电路	Micropower Undervoltage Sensing Circuit	SOT-23-5	1.08	.78	.57
LM8364BALMF20TR-ND	微功率欠电压检测电路	Micropower Undervoltage Sensing Circuit	SOT-23-5	336.00	1,000	
LM8364BALMF30CT-ND	微功率欠电压检测电路	Micropower Undervoltage Sensing Circuit*	SOT-23-5	1.08	.78	.57
LM8364BALMF30TR-ND	微功率欠电压检测电路	Micropower Undervoltage Sensing Circuit*	SOT-23-5	336.00	1,000	
LM8364BALMF32CT-ND	微功率欠电压检测电路	Micropower Undervoltage Sensing Circuit*	SOT-23-5	1.08	.78	.57
LM8364BALMF32TR-ND	微功率欠电压检测电路	Micropower Undervoltage Sensing Circuit*	SOT-23-5	336.00	1,000	
LM8364BALMF45CT-ND	微功率欠电压检测电路	Micropower Undervoltage Sensing Circuit*	SOT-23-5	.95	.69	.50
LM8364BALMF45TR-ND	微功率欠电压检测电路	Micropower Undervoltage Sensing Circuit*	SOT-23-5	296.80	1,000	
LM8365BALMF22CT-ND	微功率欠电压检测电路	Micropower Undervoltage Sensing Circuit	SOT-23-5	1.08	.78	.57
LM8365BALMF22TR-ND	微功率欠电压检测电路	Micropower Undervoltage Sensing Circuit	SOT-23-5	336.00	1,000	
LM8365BALMF27CT-ND	微功率欠电压检测电路	Micropower Undervoltage Sensing Circuit*	SOT-23-5	1.08	.78	.57
LM8365BALMF27TR-ND	微功率欠电压检测电路	Micropower Undervoltage Sensing Circuit*	SOT-23-5	336.00	1,000	
LM8365BALMF45CT-ND	微功率欠电压检测电路	Micropower Undervoltage Sensing Circuit*	SOT-23-5	1.08	.78	.57
LM8365BALMF45TR-ND	微功率欠电压检测电路	Micropower Undervoltage Sensing Circuit*	SOT-23-5	336.00	1,000	
LM8365BCLMF30CT-ND	微功率欠电压检测电路	Micropower Undervoltage Sensing Circuit	SOT-23-5	1.08	.78	.57

\* 符合 RoHS 规范要求

(转下页)

★ 欢迎来电查询, 大批量订购, 价格优惠! ★

全部产品均以美元计价。 免费电话: 10800-1527031 (China Telecom - 中国电讯) — 10800-8527031 (CNCG - 中国网通)

digikey.com.cn — 电话: (852) 3104 0500 — 传真: (852) 3104 0686

(CN082-09) 1141