

Digi-Key 零件编号	说明	封装	1	25	100	
LTC1515IS8-3/5-ND	3V/5V 步升/步降开关电容 DC/DC 转换器	3V/5V, Step-Up/Down Switch-Capacitor DC/DC Converter	8-SOIC	7.88	5.25	4.55
LTC1516CS8-ND	稳压 5V 充电泵 DC/DC 转换器	Regulated 5V Charge Pump DC/DC Converter	8-SOIC	6.25	4.15	3.60
LTC1516CS8#PBF-ND	稳压 5V 充电泵 DC/DC 转换器*	Regulated 5V Charge Pump DC/DC Converter*	8-SOIC	6.25	4.15	3.60
LTC1517CS5-5#TRMCT-ND	稳压 5V 充电泵 DC/DC 转换器	Regulated 5V Charge Pump DC/DC Converter	SOT-23-5	4.42	3.95	3.56
LTC1517CS5-5#TRMPBFCT-ND	稳压 5V 充电泵 DC/DC 转换器*	Regulated 5V Charge Pump DC/DC Converter*	SOT-23-5	4.42	3.95	3.56
LTC1517CS5-5#TRMPBFTR-ND	稳压 5V 充电泵 DC/DC 转换器*	Regulated 5V Charge Pump DC/DC Converter*	SOT-23-5	4.70	4.20	3.78
LTC1517ES5-3.3#TRMCT-ND	稳压 3.3V 充电泵 DC/DC 转换器	Regulated 3.3V Charge Pump DC/DC Converter	SOT-23-5	4.70	4.20	3.78
LTC1517ES5-3.3#TRMPBFCT-ND	稳压 3.3V 充电泵 DC/DC 转换器*	Regulated 3.3V Charge Pump DC/DC Converter*	SOT-23-5	4.70	4.20	3.78
LTC1517ES5-5#TRMCT-ND	稳压 5V 充电泵 DC/DC 转换器	Regulated 5V Charge Pump DC/DC Converter	SOT-23-5	4.70	4.20	3.78
LTC1517ES5-5#TRMPBFCT-ND	稳压 5V 充电泵 DC/DC 转换器*	Regulated 5V Charge Pump DC/DC Converter*	SOT-23-5	4.70	4.20	3.78
LTC1517ES5-5#TRMPBFTR-ND	稳压 5V 充电泵 DC/DC 转换器*	Regulated 5V Charge Pump DC/DC Converter*	SOT-23-5	4.70	4.20	3.78
LTC1522CMS8-ND	稳压 5V 充电泵 DC/DC 转换器	Regulated 5V Charge Pump DC/DC Converter	8-MSOP	3.75	2.50	2.20
LTC1522CMS8#PBF-ND	稳压 5V 充电泵 DC/DC 转换器*	Regulated 5V Charge Pump DC/DC Converter*	8-MSOP	3.75	2.50	2.20
LTC1550CGN-ND	开关电容稳压反相器	Switched Capacitor-Regulated Voltage Inverter	16-SSOP	5.25	3.49	2.85
LTC1550LCGN-ND	开关电容稳压反相器	Switched Capacitor-Regulated Voltage Inverter	16-SSOP	4.00	2.66	2.05
LTC1550LCS8-ND	开关电容稳压反相器	Switched Capacitor-Regulated Voltage Inverter	8-SOIC	3.63	2.41	1.85
LTC1682CS8-5-ND	5V 倍增器充电泵, 带低噪声线性稳压器	5V, Doubler Charge Pump with Low Noise Linear Regulator	8-SOIC	3.50	2.33	1.85
LTC1682CS8-5#PBF-ND	5V 倍增器充电泵, 带低噪声线性稳压器*	5V, Doubler Charge Pump with Low Noise Linear Regulator*	8-SOIC	3.50	2.33	1.85
LTC1682IS8-5#PBF-ND	5V 倍增器充电泵, 带低噪声线性稳压器*	5V, Doubler Charge Pump with Low Noise Linear Regulator*	8-SOIC	4.13	2.74	2.20
LTC1751EMS8#PBF-ND	MPU 稳压充电泵 DC/DC 转换器*	MPU Regulated Charge Pump DC/DC Converter*	8-MSOP	4.63	3.08	2.35
LTC1751EMS8-3.3-ND	MPU 稳压充电泵 DC/DC 转换器	MPU Regulated Charge Pump DC/DC Converter	8-MSOP	4.63	3.08	2.35
LTC1751EMS8-3.3#PBF-ND	MPU 稳压充电泵 DC/DC 转换器*	MPU Regulated Charge Pump DC/DC Converter*	8-MSOP	4.63	3.08	2.35
LTC1751EMS8-5#PBF-ND	MPU 稳压充电泵 DC/DC 转换器*	MPU Regulated Charge Pump DC/DC Converter*	8-MSOP	4.63	3.08	2.35
LTC1754ES6-5#TRMPBFCT-ND	MPU 稳压充电泵, 带关闭模式*	MPU Regulated Charge Pump with Shutdown*	SOT-23-6	3.44	3.08	2.77
LTC1754ES6-5#TRMPBFTR-ND	MPU 稳压充电泵, 带关闭模式*	MPU Regulated Charge Pump with Shutdown*	SOT-23-6	3.44	3.08	2.77
LTC1911EMS8-1.5-ND	1.5V 低噪声步降 DC/DC 转换器	1.5V Low Noise Step-Down DC/DC Converter	8-MSOP	4.80	3.19	2.44
LTC1911EMS8-1.8-ND	1.8V 低噪声步降 DC/DC 转换器	1.8V Low Noise Step-Down DC/DC Converter	8-MSOP	4.80	3.19	2.44
LTC1911EMS8-1.8#PBF-ND	1.8V 低噪声步降 DC/DC 转换器*	1.8V Low Noise Step-Down DC/DC Converter*	8-MSOP	4.80	3.19	2.44
LTC1983ES6-3#TRMPBFCT-ND	3V, 100mA 稳压充电泵反相器*	3V, 100mA Regulated Charge Pump Inverter*	SOT-23-6	4.26	3.80	3.42
LTC1983ES6-3#TRMPBFTR-ND	3V, 100mA 稳压充电泵反相器*	3V, 100mA Regulated Charge Pump Inverter*	SOT-23-6	4.26	3.80	3.42
LTC1983ES6-5#TRMCT-ND	5V, 100mA 稳压充电泵反相器	5V, 100mA, Regulated Charge Pump Inverter	SOT-23-6	4.26	3.80	3.42
LTC1983ES6-5#TRMTR-ND	5V, 100mA 稳压充电泵反相器	5V, 100mA, Regulated Charge Pump Inverter	SOT-23-6	4.26	3.80	3.42
LTC1983ES6-5#TRMPBFCT-ND	5V, 100mA 稳压充电泵反相器*	5V, 100mA, Regulated Charge Pump Inverter*	SOT-23-6	4.26	3.80	3.42
LTC1983ES6-5#TRMPBFTR-ND	5V, 100mA 稳压充电泵反相器*	5V, 100mA, Regulated Charge Pump Inverter*	SOT-23-6	4.26	3.80	3.42
LTC3200ES6-5#TRMPBFCT-ND	低噪声稳压充电泵 DC/DC 转换器*	Low Noise, Regulated Charge Pump DC/DC Converter*	TSOT-23-6	3.75	3.55	3.02
LTC3200ES6-5#TRMPBFTR-ND	低噪声稳压充电泵 DC/DC 转换器*	Low Noise, Regulated Charge Pump DC/DC Converter*	TSOT-23-6	3.75	3.55	3.02
LTC3202EEDD-ND	低噪声高效充电泵	Low Noise, High Efficiency Charge Pump	10-DFN	4.10	2.93	2.46
LTC3202EEDD#PBF-ND	低噪声高效充电泵*	Low Noise, High Efficiency Charge Pump*	10-DFN	4.10	2.93	2.46
LTC3202EMS-ND	低噪声高效充电泵	Low Noise, High Efficiency Charge Pump	10-MSOP	3.75	2.49	1.99
LTC3204BEDC-3.3#TRMPBFCT-ND	3.3V 低噪声稳压充电泵*	3.3V, Low Noise Regulated Charge Pump*	6-DFN	3.70	3.30	2.97
LTC3204BEDC-3.3#TRMPBFTR-ND	3.3V 低噪声稳压充电泵*	3.3V, Low Noise Regulated Charge Pump*	6-DFN	3.70	3.30	2.97
LTC3204BEDC-5#TRMPBFCT-ND	5V 低噪声稳压充电泵*	5V, Low Noise Regulated Charge Pump*	6-DFN	3.70	3.30	2.97
LTC3204BEDC-5#TRMPBFTR-ND	5V 低噪声稳压充电泵*	5V, Low Noise Regulated Charge Pump*	6-DFN	3.70	3.30	2.97
LTC3214EEDD#PBF-ND	500mA 照相 LED 充电泵*	500mA Camera LED Charge Pump*	10-DFN	3.30	2.36	1.99
LTC3215EEDD#PBF-ND	700mA 低噪声大电流 LED 充电泵*	700mA LN High Current LED Charge Pump*	10-DFN	3.50	2.50	2.11
LTC3250ES6-1.5#TRMCT-ND	1.5V 高效低噪声无电感步降 DC/DC 转换器	1.5V, High Efficiency, Low Noise, Inductorless, Step-Down DC/DC Converter	SOT-23-6	3.44	3.08	2.77
LTC3250ES6-1.5#TRMPBFCT-ND	1.5V 高效低噪声无电感步降 DC/DC 转换器*	1.5V, High Efficiency, Low Noise, Inductorless, Step-Down DC/DC Converter*	SOT-23-6	3.44	3.08	2.77
LTC3251EMSE-ND	高效低噪声无电感步降 DC/DC 转换器	High Efficiency, Low Noise, Inductorless, Step-Down DC/DC Converter	10-MSOP	3.90	2.79	2.34
LTC3251EMSE#PBF-ND	高效低噪声无电感步降 DC/DC 转换器*	High Efficiency, Low Noise, Inductorless, Step-Down DC/DC Converter*	10-MSOP	3.90	2.79	2.34

**CPU 内核电源**

LTC1703IG-ND	双路 550kHz 同步开关稳压控制器	Dual 550kHz, Sync. Switch Regulator Controller	28-SSOP	12.50	8.93	7.35
LTC1705EGN-ND	双路 5 位同步开关稳压控制器	Dual 5-Bit, Sync. Switching Regulator Controller	28-SSOP	11.25	7.47	5.68
LTC1705EGN#PBF-ND	双路 5 位同步开关稳压控制器*	Dual 5-Bit, Sync. Switching Reg. Controller*	28-SSOP	11.25	7.47	5.68
LTC1706EMS-85-ND	用于 Intel VRM 8.5 的 VID 电压编程器	VID Voltage Programmer for Intel VRM 8.5	10-MSOP	4.25	2.83	2.20
LTC1709EG-7-ND	5 位 2 相同步步降开关稳压器	5-Bit, 2-Phase, Sync., Step-Down Switching Reg.	36-SSOP	9.75	6.48	5.05
LTC1709EG-85-ND	5 位 2 相同步步降开关稳压器	5-Bit, 2-Phase, Sync., Step-Down Switching Reg.	36-SSOP	9.75	6.48	5.05
LTC1753CG-ND	用于 Pentium II 处理器的 5 位可编程同步开关稳压控制器	5-Bit, Programmable Synchronous Switching Regulator Controller for Pentium II Processor	20-SSOP	6.50	4.32	3.30
LTC1753CG#PBF-ND	用于 Pentium II 处理器的 5 位可编程同步开关稳压控制器*	5-Bit, Programmable Synchronous Switching Regulator Controller for Pentium II Processor*	20-SSOP	6.50	4.32	3.30
LTC1753CSW-ND	用于 Pentium II 处理器的 5 位可编程同步开关稳压控制器	5-Bit, Programmable Synchronous Switching Regulator Controller for Pentium II Processor	20-SOIC	6.00	3.99	3.05
LTC1909-8EG-ND	步降 DC/DC 稳压控制器	Step-Down DC/DC Regulator Controller	28-SSOP	10.38	6.89	5.20
LTC3703EG#PBF-ND	步降 DC/DC 稳压控制器*	Step-Down DC/DC Regulator Controller*	28-SSOP	7.00	4.65	3.67
LTC3703EGN#PBF-ND	100V 同步开关稳压控制器*	100V Sync. Switching Regulator Controller*	16-SSOP	6.38	4.24	3.35
LTC3714EG#PBF-ND	Intel 兼容型宽工作范围步降控制器, 带内部运算放大器*	Intel Compatible, Wide Operating Range, Step-Down Controller with Internal Op Amp*	28-SSOP	6.50	4.32	3.30
LTC3720EGN#PBF-ND	1 相 VRM8.5 电流模式步降控制器*	1-Phase VRM8.5 Current Mode Step-Down Controller*	28-SSOP	6.50	4.64	3.87
LTC3733CG-ND	用于 AMD CPU 的 3 相降压控制器	3-Phase, Buck Controller for AMD CPU's	36-SSOP	8.75	6.25	5.20
LTC3733CG#PBF-ND	用于 AMD CPU 的 3 相降压控制器*	3-Phase, Buck Controller for AMD CPU's*	36-SSOP	8.75	6.25	5.20

**LED 驱动器**

LTC3478IFE#PBF-ND	4.5A 单片 LED 驱动器, 带真彩色 PWM 调光*	4.5A Mono LED Driver with True Color PWM Dimming*	16-TSSOP	8.65	6.17	5.13
LTC3478IFE-1#PBF-ND	4.5A 单片 LED 驱动器, 带真彩色 PWM 调光*	4.5A Mono LED Driver with True Color PWM Dimming*	16-TSSOP	8.65	6.17	5.13
LTC3496IUD#PBF-ND	三路输出 LED 驱动器*	Triple Output LED Driver*	28-DFN	8.40	6.00	4.99
LTC3498EDB#TRMPBFCT-ND	20mA LED 驱动器和 OLED 驱动器*	20mA LED Driver and OLED Driver*	12-DFN	4.48	4.00	3.60
LTC3498EDB#TRMPBFTR-ND	20mA LED 驱动器和 OLED 驱动器*	20mA LED Driver and OLED Driver*	12-DFN	4.48	4.00	3.60
LTC3518EUF#PBF-ND	2.3A LED 驱动器*	2.3A, LED Driver*	16-QFN	5.90	4.21	3.52
LTC3518IUF#PBF-ND	2.3A LED 驱动器*	2.3A, LED Driver*	16-QFN	7.08	5.06	4.22
LTC3591EDB#TRMPBFCT-ND	带集成肖特基的白色 LED 驱动器*	White LED Driver with Integrated Schottky*	8-DFN	3.25	2.90	2.61
LTC3591EDB#TRMPBFTR-ND	带集成肖特基的白色 LED 驱动器*	White LED Driver with Integrated Schottky*	8-DFN	3.25	2.90	2.61
LTC3595EUIH#PBF-ND	16 通道降压模式 LED 驱动器*	16-Channel Buck Mode LED Driver*	56-QFN	14.25	9.93	8.22
LTC3230EUD#PBF-ND	5-LED 显示驱动器, 带双路低电压降*	5-LED Display Driver with Dual LDO*	20-QFN	3.10	2.21	1.87

**电池充电器**

LT1505CG-ND	恒定电流/电压高效电池充电器	Constant-Current/Voltage, High Efficiency Battery Charger	28-SSOP	9.88	6.56	5.15
LT1505CG-1-ND	恒定电流/电压高效电池充电器	Constant-Current/Voltage, High Efficiency Battery Charger	28-SSOP	9.38	5.15	4.90
LT1505CG-1#PBF-ND	恒定电流/电压高效电池充电器*	Constant-Current/Volt., High Efficiency Battery Charger*	28-SSOP	9.38	6.23	4.95
LT1510-SCGN#PBF-ND	500kHz 1.5A 恒定电压/电流电池充电器*	500kHz, 1.5A Constant Voltage/Current Battery Charger*	16-SSOP	8.13	5.40	4.40
LT1510CGN-ND	200kHz 1.5A 恒定电压/电流电池充电器	200kHz, 1.5A Constant Voltage/Current Battery Charger	16-SSOP	8.13	5.40	4.40
LT1510CGN#PBF-ND	200kHz 1.5A 恒定电压/电流电池充电器*	200kHz, 1.5A Constant Voltage/Current Battery Charger*	16-SSOP	8.13	5.40	4.40
LT1510CN-ND	200kHz 1.5A 恒定电压/电流电池充电器	200kHz, 1.5A Constant Voltage/Current Battery Charger	16-Dip	7.50	4.60	4.00
LT1510CN#PBF-ND	200kHz 1.5A 恒定电压/电流电池充电器*	200kHz, 1.5A Constant Voltage/Current Battery Charger*	16-Dip	7.50	4.98	4.05
LT1510CS-ND	200kHz 1.5A 恒定电压/电流电池充电器	200kHz, 1.5A Constant Voltage/Current Battery Charger	16-SOIC	7.88	5.23	4.25
LT1510CS#PBF-ND	200kHz 1.5A 恒定电压/电流电池充电器*	200kHz, 1.5A Constant Voltage/Current Battery Charger*	16-SOIC	7.88	5.23	4.25
LT1510CS8#PBF-ND	200kHz 1.5A 恒定电压/电流电池充电器*	200kHz, 1.5A Constant Voltage/Current Battery Charger*	8-SOIC	6.00	3.99	3.25
LT1510IS#PBF-ND	200kHz 1.5A 恒定电压/电流电池充电器*	200kHz, 1.5A Constant Voltage/Current Battery Charger*	16-SOIC	9.00	5.98	4.85
LT1510IS8-ND	200kHz 1.5A 恒定电压/电流电池充电器	200kHz, 1.5A Constant Voltage/Current Battery Charger	8-SOIC	6.88	4.57	3.70
LT1511CSW#PBF-ND	3A 恒定电流/电压电池充电器*	3A Constant Current/Voltage Battery Charger*	24-SOIC	13.00	8.64	7.00
LT1511SW-ND	3A 恒定电流/电压电池充电器, 工业级温度	3A Constant Current/Voltage Battery Charger, Ind. Temp.	24-SOIC	15.00	10.00	8.65

\* 符合 RoHS 规范要求

(转下页)

★ 欢迎来电查询, 大批量订购, 价格优惠! ★

全部产品均以美元计价。

免费电话: 10800-1527031 (China Telecom - 中国电讯) — 10800-8527031 (CNCG - 中国网通)

1190 (CN082-09)

digikey.com.cn — 电话: (852) 3104 0500 — 传真: (852) 3104 0686

