

**JRC / NJR Corporation**

放大器 (接上页)

Digi-Key 零件编号	说明	封装	单价★			
			1	25	100	
NJU7096M-ND	低功率低偏压电压双路 CMOS 运算放大器	Low Power/Low Offset Voltage Dual CMOS Op Amp	8-DMP	.96	.80	.64
NJU7096R-TE1CT-ND	低功率低偏压电压双路 CMOS 运算放大器*	Low Power/Low Offset Voltage Dual CMOS Op Amp*	8-VSP	2.73	2.28	1.82
NJU7096R-TE1TR-ND	低功率低偏压电压双路 CMOS 运算放大器*	Low Power/Low Offset Voltage Dual CMOS Op Amp*	8-VSP		3256.00/2,000	
NJU7096R1-TE1CT-ND	低功率低偏压电压双路 CMOS 运算放大器	Low Power/Low Offset Voltage Dual CMOS Op Amp	8-TVSP	2.73	2.28	1.82
NJU7096R1-TE1TR-ND	低功率低偏压电压双路 CMOS 运算放大器	Low Power/Low Offset Voltage Dual CMOS Op Amp	8-TVSP		3185.00/2,000	
NJU7096V-TE2CT-ND	低功率低偏压电压双路 CMOS 运算放大器	Low Power/Low Offset Voltage Dual CMOS Op Amp	8-SSOP	2.73	2.28	1.82
NJU7096V-TE2TR-ND	低功率低偏压电压双路 CMOS 运算放大器	Low Power/Low Offset Voltage Dual CMOS Op Amp	8-SSOP		3185.00/2,000	
NJU7102AD-ND	带 CMOS 输出的 CMOS 比较器	CMOS Comparator with CMOS Output	8-Dip	3.15	2.63	2.10
NJU7102AM-ND	带 CMOS 输出的 CMOS 比较器	CMOS Comparator with CMOS Output	8-DMP	3.15	2.63	2.10
NJU8721V-TE1CT-ND	D 类耳机放大器, 用于数字音频设备	Class-D Headphone Amplifier for Digital Audio	20-SSOP	4.20	3.50	2.80
NJU8721V-TE1TR-ND	D 类耳机放大器, 用于数字音频设备	Class-D Headphone Amplifier for Digital Audio	20-SSOP		4900.00/2,000	
NJU8725V-TE1CT-ND	D 类放大器, 用于数字音频设备	Class-D Amp for Digital Audio	24-SSOP	6.30	5.25	4.20
NJU8725V-TE1TR-ND	D 类放大器, 用于数字音频设备	Class-D Amp for Digital Audio	24-SSOP		7350.00/2,000	
NJU8752V-TE1CT-ND	模拟信号输入 D 类放大器, 用于压电式扬声器*	Analog Signal Input Class-D Amp for Piezo Speaker*	14-SSOP	5.46	4.55	3.64
NJU8752V-TE1TR-ND	模拟信号输入 D 类放大器, 用于压电式扬声器*	Analog Signal Input Class-D Amp for Piezo Speaker*	14-SSOP		4236.00/2,000	
NJU8754V-TE2CT-ND	模拟信号输入单通道输出 D 类功率放大器*	Analog Signal Input Monaural Class-D Power Amp*	10-SSOP	2.19	1.83	1.46
NJU8755V-TE1CT-ND	模拟信号输入立体声 D 类功率放大器*	Analog Signal Input Stereo Class-D Power Amp*	20-SSOP	3.42	2.85	2.28
NJU8755V-TE1TR-ND	模拟信号输入立体声 D 类功率放大器*	Analog Signal Input Stereo Class-D Power Amp*	20-SSOP		3990.00/2,000	

\* 符合 RoHS 规范要求

**JRC / NJR Corporation**

驱动器

Digi-Key 零件编号	说明	封装	单价★			
			1	25	100	
NJM#2577M-TE2CT-ND	四路视频驱动器*	Quad Video Driver*	20-DMP	3.00	2.50	2.00
NJM#2577M-TE2TR-ND	四路视频驱动器*	Quad Video Driver*	20-DMP		3500.00/2,000	
NJM#3517D2-ND	步进电机控制器/驱动器*	Stepper Motor Controller/Driver*	16-Dip	5.58	4.65	3.72
NJM#3517E2-ND	步进电机控制器/驱动器*	Stepper Motor Controller/Driver*	16-EMP	5.58	4.65	3.72
NJM#3717D2-ND	步进电机驱动器*	Stepper Motor Driver*	16-Dip	2.13	1.78	1.42
NJM#3770AD3-ND	步进电机驱动器*	Stepper Motor Driver*	16-Dip (Batwing)	4.50	3.75	3.00
NJM#3771D2-ND	双路步进电机驱动器*	Dual Stepper Motor Driver*	22-Dip	6.00	5.00	4.00
NJM#3771FM2-ND	双路步进电机驱动器*	Dual Stepper Motor Driver*	28-PLCC	6.00	5.00	4.00
NJM#3772D2-ND	双路步进电机驱动器	Dual Stepper Motor Driver	22-Dip	5.46	4.55	3.64
NJM#3772D2-ND	双路步进电机驱动器*	Dual Stepper Motor Driver*	22-Dip	5.58	4.65	3.72
NJM#3773D2-ND	双路步进电机驱动器	Dual Stepper Motor Driver	22-Dip	5.04	4.20	3.36
NJM#3773D2-ND	双路步进电机驱动器*	Dual Stepper Motor Driver*	22-Dip	5.13	4.28	3.42
NJM#3774FM2-ND	双路步进电机驱动器	Dual Stepper Motor Driver	28-PLCC	5.46	4.55	3.64
NJM#3775D2-ND	双路步进电机驱动器*	Dual Stepper Motor Driver*	22-Dip	5.13	4.28	3.42
NJM#3775FM2-ND	双路步进电机驱动器	Dual Stepper Motor Driver	28-PLCC	5.04	4.20	3.36
NJM#3777E3-ND	双路步进电机驱动器*	Dual Stepper Motor Driver*	24-EMP	5.13	4.28	3.42
NJM#37717E3-ND	步进电机驱动器	Stepper Motor Driver	24-EMP	5.04	4.20	3.36
NJU6048F-TE1CT-ND	高效白色 LED 驱动器	High Efficiency White LED Driver	SOT-23-5	1.68	1.40	1.12
NJU6048F-TE1TR-ND	高效白色 LED 驱动器	High Efficiency White LED Driver	SOT-23-5		2940.00/3,000	
NJU6050F-TE2CT-ND	高效白色 LED 驱动器*	High Efficiency White LED Driver*	SOT-23-5	1.50	1.25	1.00
NJU6050F-TE2TR-ND	高效白色 LED 驱动器*	High Efficiency White LED Driver*	SOT-23-5		2625.00/3,000	
NJU6060V-TE1CT-ND	带 PWM 控制的全色 LED 控制器驱动器*	Full Color LED Controller Driver with PWM Control*	10-SSOP	1.47	1.23	.98
NJU6060V-TE1TR-ND	带 PWM 控制的全色 LED 控制器驱动器*	Full Color LED Controller Driver with PWM Control*	10-SSOP		1750.00/2,000	
NJU7325R-TE1CT-ND	单相 DC 无刷电机驱动器	Single-Phase DC Brushless Motor Driver	8-VSP	1.05	.88	.70
NJU7325R-TE1TR-ND	单相 DC 无刷电机驱动器	Single-Phase DC Brushless Motor Driver	8-VSP		1225.00/2,000	
NJU8711V-TE2CT-ND	用于 D 类放大器的 3V 工作开关驱动器*	3V Operation Switching Driver for Class D Amp*	10-SSOP	2.52	2.10	1.68
NJU8711V-TE2TR-ND	用于 D 类放大器的 3V 工作开关驱动器*	3V Operation Switching Driver for Class D Amp*	10-SSOP		3256.00/2,000	
NJU8713V-TE1CT-ND	用于 D 类放大器的 2V 工作开关驱动器*	2V Operation Switching Driver for Class D Amp*	14-SSOP	2.73	2.28	1.82
NJU8713V-TE1TR-ND	用于 D 类放大器的 2V 工作开关驱动器*	2V Operation Switching Driver for Class D Amp*	14-SSOP		2766.00/2,000	
NJU4301D-ND	2 通道桥路驱动器	2-Channel Bridge Driver	16-Dip	3.48	2.90	2.32
NJU4301M-ND	2 通道桥路驱动器	2-Channel Bridge Driver	30-SDMP	3.48	2.90	2.32

\* 符合 RoHS 规范要求

**JRC / NJR Corporation**

多路复用器

Digi-Key 零件编号	说明	封装	单价★			
			1	25	100	
NJU4051BM-ND	单路 8 通道多路复用器	Single 8-Channel Mux	16-DMP	.93	.78	.62
NJU4053BD-ND	三路 2 通道多路复用器	Triple 2-Channel Mux	16-Dip	.96	.80	.64

**JRC / NJR Corporation**

电源管理

Digi-Key 零件编号	说明	封装	单价★			
			1	25	100	
NJM#78L08L2A-ND	8V 100mA 正稳压器*	8V, 100mA, Positive Voltage Regulator*	TO-92	.36	.30	.24
NJM#78L12L2A-ND	12V 100mA 正稳压器*	12V, 100mA, Positive Voltage Regulator*	TO-92	.36	.30	.24
NJM#78L05BD-ND	带复位功能的串联稳压器	Series Regulator with Reset Function	8-Dip	.72	.60	.48
NJM#78L05BM-ND	带复位功能的串联稳压器	Series Regulator with Reset Function	8-DMP	.45	.38	.30
NJM#78L05UA-ND	5V 100mA 正稳压器*	5V, 100mA, Positive Voltage Regulator*	SOT-89	.39	.33	.26
NJM#78L06UA-ND	6V 100mA 正稳压器*	6V, 100mA, Positive Voltage Regulator*	SOT-89	.39	.33	.26
NJM#78L08UA-ND	8V 100mA 正稳压器*	8V, 100mA, Positive Voltage Regulator*	SOT-89	.39	.33	.26
NJM#78L09UA-ND	9V 100mA 正稳压器*	9V, 100mA, Positive Voltage Regulator*	SOT-89	.39	.33	.26
NJM#78L12UA-ND	12V 100mA 正稳压器*	12V, 100mA, Positive Voltage Regulator*	SOT-89	.39	.33	.26
NJM#78L15UA-ND	15V 100mA 正稳压器*	15V, 100mA, Positive Voltage Regulator*	SOT-89	.39	.33	.26
NJM#78L20UA-ND	20V 100mA 正稳压器	20V, 100mA, Positive Voltage Regulator	SOT-89	.39	.33	.26
NJM#78L05BUTE1CT-ND	带复位功能的串联稳压器*	Series Regulator with Reset Function*	SOT-89-5	.63	.53	.42
NJM#78L05BUTE1TR-ND	带复位功能的串联稳压器*	Series Regulator with Reset Function*	SOT-89-5		367.50/1,000	
NJM#78LR05DD-ND	带复位功能的串联稳压器	Series Regulator with Reset Function	8-Dip	.72	.60	.48
NJM#78LR05DU-TE1CT-ND	带复位功能的串联稳压器	Series Regulator with Reset Function	SOT-89-5	.60	.50	.40
NJM#78LR05DU-TE1TR-ND	带复位功能的串联稳压器	Series Regulator with Reset Function	SOT-89-5		350.00/1,000	
NJM#78M05FA-ND	5V 500mA 正稳压器, 带隔离片*	5V, 500mA, Positive Voltage Reg. with Isolated Tab*	TO-220F	.57	.48	.38
NJM#78M06FA-ND	6V 500mA 正稳压器, 带隔离片*	6V, 500mA, Positive Voltage Reg. with Isolated Tab*	TO-220F	.57	.48	.38
NJM#78M09FA-ND	9V 500mA 正稳压器, 带隔离片*	9V, 500mA, Positive Voltage Reg. with Isolated Tab*	TO-220F	.57	.48	.38
NJM#78M12FA-ND	12V 500mA 正稳压器, 带隔离片*	12V, 500mA, Positive Voltage Reg. with Isolated Tab*	TO-220F	.57	.48	.38
NJM#78M15FA-ND	15V 500mA 正稳压器, 带隔离片*	15V, 500mA, Positive Voltage Reg. with Isolated Tab*	TO-220F	.57	.48	.38
NJM#78M18FA-ND	18V 500mA 正稳压器, 带隔离片	18V, 500mA, Positive Voltage Reg. with Isolated Tab	TO-220F	.54	.45	.36
NJM#78M24FA-ND	24V 500mA 正稳压器, 带隔离片*	24V, 500mA, Positive Voltage Reg. with Isolated Tab*	TO-220F	.57	.48	.38
NJM#79L05L2A-ND	5V 100mA 负稳压器*	5V, 100mA, Negative Voltage Regulator*	TO-92	.42	.35	.28
NJM#79L05UA-ND	5V 100mA 负稳压器*	5V, 100mA, Negative Voltage Regulator*	SOT-89	.45	.38	.30
NJM#79L08L2A-ND	8V 100mA 负稳压器*	8V, 100mA, Negative Voltage Regulator*	TO-92	.42	.35	.28
NJM#79L08UA-ND	8V 100mA 负稳压器*	8V, 100mA, Negative Voltage Regulator*	SOT-89	.45	.38	.30
NJM#79L09L2A-ND	9V 100mA 负稳压器*	9V, 100mA, Negative Voltage Regulator*	TO-92	.42	.35	.28
NJM#79L09UA-ND	9V 100mA 负稳压器*	9V, 100mA, Negative Voltage Regulator*	SOT-89	.45	.38	.30
NJM#79L09UA-TE1CT-ND	9V 100mA 负稳压器*	9V, 100mA, Negative Voltage Regulator*	SOT-89		45.38.30	

\* 符合 RoHS 规范要求

(转下页)

★ 欢迎来电查询, 大批量订购, 价格优惠! ★

全部产品均以美元计价。 免费电话: 10800-1527031 (China Telecom - 中国电讯) — 10800-8527031 (CNCG - 中国网通)

digikkey.com.cn — 电话: (852) 3104 0500 — 传真: (852) 3104 0686

(CN082-09) 1215

