

Digi-Key 零件编号	说明	封装	单价★		
			1	25	100
NJM2240D-ND	视频副载波信号四倍频器	Video Sub-Carrier Signal Quadrupler	8-Dip	1.89	1.58 1.26
NJM2240M-ND	视频副载波信号四倍频器	Video Sub-Carrier Signal Quadrupler	8-DMP	1.89	1.58 1.26
NJM2248D-ND	3输入视频叠加器	3-Input Video Superimposer	8-Dip	1.05	.88 .70
NJM2255M-ND	色度信号色控制器	Chroma Signal Hue Tint Controller	8-DMP	1.68	1.40 1.12
NJM2257D-ND	带 AFC 的同步分离器	Sync. Separator with AFC	16-Dip	2.85	2.38 1.90
NJM2259M-ND	用于 UHF 波段的射频调制器	RF Modulator for UHF Band	16-DMP	1.89	1.58 1.26
NJM2292V-TE1CT-ND	窄波段 FM IF IC	Narrow Band FM IF IC	20-SSOP	1.47	1.23 .98
NJM2292V-TE1TR-ND	窄波段 FM IF IC	Narrow Band FM IF IC	20-SSOP		1715.00/2,000
NJM2294V-TE1CT-ND	用于寻呼机的 FM IF IC	FM IF IC for Pager	16-SSOP	3.99	3.33 2.66
NJM2294V-TE1TR-ND	用于寻呼机的 FM IF IC	FM IF IC for Pager	16-SSOP		3675.00/2,000
NJM#2509V-TE1CT-ND	带 Y-C 混频器的视频叠加器*	Video Superimposer with Y-C Mixer*	8-SSOP	1.68	1.40 1.12
NJM#2509V-TE1TR-ND	带 Y-C 混频器的视频叠加器*	Video Superimposer with Y-C Mixer*	8-SSOP		1995.00/2,000
NJM2519AM-ND	用于 VHF 波段的射频调制器	RF Modulator for VHF Band	8-DMP	1.26	1.05 .84
NJM2590V-TE1CT-ND	455kHz 输入 FM IF 解调器	455kHz Input FM IF Demodulator	14-SSOP	2.10	1.75 1.40
NJM2592V-TE1CT-ND	470MHz 输入混频器 455kHz FM IF 解调器	470MHz Input Mixer 455kHz FM IF Demodulator	20-SSOP	3.15	2.63 2.10
NJM2592V-TE1TR-ND	470MHz 输入混频器 455kHz FM IF 解调器	470MHz Input Mixer 455kHz FM IF Demodulator	20-SSOP		3675.00/2,000
NJM2594V-TE1CT-ND	双路平衡调制/解调	Double Balanced Modulation/Demodulation	8-SSOP	2.94	2.45 1.96
NJM2594V-TE1TR-ND	双路平衡调制/解调	Double Balanced Modulation/Demodulation	8-SSOP		3430.00/2,000
NJM2611M-ND	伺服电机控制器	Servo Motor Controller	16-DIP	2.10	1.75 1.40
NJM2624AD-ND	无刷直流电机前级驱动器	Brushless DC Motor Pre-Driver	16-Dip	1.77	1.48 1.18
NJM2624AM-ND	无刷直流电机前级驱动器	Brushless DC Motor Pre-Driver	16-DMP	1.77	1.48 1.18
NJM2761R82-TE1CT-ND	用于扬声器保护的音频限幅器	Audio Limiter for Speaker Protection	10-TVSP	1.50	1.25 1.00
NJM3524D-ND	开关稳压器控制电路	Switching Regulator Control Circuit	16-Dip	1.17	.98 .78
NJM3524M-ND	开关稳压器控制电路	Switching Regulator Control Circuit	16-DMP	1.17	.98 .78
NJM#4151D-ND	电压至频率/频率至电压转换器*	Voltage-to-Frequency/Frequency-to-Voltage Converter*	8-Dip	2.37	1.98 1.58
NJM#7805FA-ND	5V 1A 正稳压器, 带隔离片*	5V, 1A Positive Voltage Regulator with Isolated Tab*	TO-220F	.60	.50 .40
NJM#7806FA-ND	6V 1A 正稳压器, 带隔离片*	6V, 1A Positive Voltage Regulator with Isolated Tab*	TO-220F	.60	.50 .40
NJM#7808FA-ND	8V 1A 正稳压器, 带隔离片*	8V, 1A Positive Voltage Regulator with Isolated Tab*	TO-220F	.60	.50 .40
NJM#7809FA-ND	9V 1A 正稳压器, 带隔离片*	9V, 1A Positive Voltage Regulator with Isolated Tab*	TO-220F	.60	.50 .40
NJM#7812FA-ND	12V 1A 正稳压器, 带隔离片*	12V, 1A Positive Voltage Regulator with Isolated Tab*	TO-220F	.60	.50 .40
NJM#7815FA-ND	15V 1A 正稳压器, 带隔离片*	15V, 1A Positive Voltage Regulator with Isolated Tab*	TO-220F	.60	.50 .40
NJM#7818FA-ND	18V 1A 正稳压器, 带隔离片*	18V, 1A Positive Voltage Regulator with Isolated Tab*	TO-220F	.60	.50 .40
NJM#7820FA-ND	20V 1A 正稳压器, 带隔离片*	20V, 1A Positive Voltage Regulator with Isolated Tab*	TO-220F	.60	.50 .40
NJM#7824FA-ND	24V 1A 正稳压器, 带隔离片*	24V, 1A Positive Voltage Regulator with Isolated Tab*	TO-220F	.60	.50 .40
NJU3711D-ND	8位串行至并行转换器	8-Bit Serial to Parallel Converter	14-Dip	1.17	.98 .78
NJU3712D-ND	8位 25mA 串行至并行输出扩展器	8-Bit, 25mA, Serial to Parallel Output Expander	16-Dip	1.80	1.50 1.20
NJU#3712M-ND	8位 25mA 串行至并行输出扩展器*	8-Bit, 25mA, Serial to Parallel Output Expander*	16-SOIC	1.83	1.53 1.22
NJU#3716M-ND	16位 25mA 串行至并行输出扩展器*	16-Bit, 25mA, Serial to Parallel Output Expander*	24-SOIC	2.28	1.90 1.52
NJU#6355ED-ND	串行输入/输出实时时钟*	Serial In/Out Real Time Clock*	8-Dip	1.71	1.43 1.14
NJU#39610D2-ND	带双路数模转换器的微步进电机控制器*	Microstepping Motor Controller with Dual DAC*	22-Dip	8.58	7.15 5.72
NJU#39610FM2-ND	带双路数模转换器的微步进电机控制器*	Microstepping Motor Controller with Dual DAC*	28-PLCC	8.58	7.15 5.72
NJW1150M-ND	6通道电子音量	6-Channel Electronic Volume	30-SDMP	5.88	4.90 3.92
NJW1151M-ND	6通道电子音量	6-Channel Electronic Volume	30-SDMP	8.40	7.00 5.60
NJW1503AV-TE1CT-ND	PLL 合成器, 带 3 线总线, 用于电视调谐器	PLL Synthesizer with 3-Wire Bus for TV Tuner	16-SSOP	2.52	2.10 1.68
NJW1503AV-TE1TR-ND	PLL 合成器, 带 3 线总线, 用于电视调谐器	PLL Synthesizer with 3-Wire Bus for TV Tuner	16-SSOP		2940.00/2,000
NJW1504V-TE1CT-ND	PLL 合成器, 带 I <sup>2</sup> C 总线, 用于电视调谐器	PLL Synthesizer with I <sup>2</sup> C Bus for TV Tuner	16-SSOP	2.52	2.10 1.68
NJW1508V-TE1CT-ND	PLL 合成器, 带 I <sup>2</sup> C 总线, 用于电视调谐器	PLL Synthesizer with I <sup>2</sup> C Bus for TV Tuner	16-SSOP	1.77	1.48 1.18
NJW1508V-TE1TR-ND	PLL 合成器, 带 I <sup>2</sup> C 总线, 用于电视调谐器	PLL Synthesizer with I <sup>2</sup> C Bus for TV Tuner	16-SSOP		2065.00/2,000

Digi-Key 零件编号	说明	封装	单价★		
			1	25	100
NJG1505R-TE1CT-ND	SPDT 开关, 砷化镓 MMIC	SPDT Switch, GaAs MMIC	8-VSP	1.89	1.58 1.26
NJG1505R-TE1TR-ND	SPDT 开关, 砷化镓 MMIC	SPDT Switch, GaAs MMIC	8-VSP		2205.00/2,000
NJG#1505R-TE1CT-ND	SPDT 开关, 砷化镓 MMIC*	SPDT Switch, GaAs MMIC*	8-VSP	1.89	1.58 1.26
NJG#1505R-TE1TR-ND	SPDT 开关, 砷化镓 MMIC*	SPDT Switch, GaAs MMIC*	8-VSP		2240.00/2,000
NJG1506R-TE2CT-ND	SPDT 开关, 砷化镓 MMIC	SPDT Switch, GaAs MMIC	8-VSP	1.47	1.23 .98
NJG1506R-TE2TR-ND	SPDT 开关, 砷化镓 MMIC	SPDT Switch, GaAs MMIC	8-VSP		1715.00/2,000
NJG1512V-TE1CT-ND	SPDT 开关, 砷化镓 MMIC	SPDT Switch, GaAs MMIC	14-SSOP	2.28	1.90 1.52
NJG1512V-TE1TR-ND	SPDT 开关, 砷化镓 MMIC	SPDT Switch, GaAs MMIC	14-SSOP		2660.00/2,000
NJG1516R-TE1CT-ND	SPDT 开关, 砷化镓 MMIC	SPDT Switch, GaAs MMIC	8-VSP	2.10	1.75 1.40
NJG1516R-TE1TR-ND	SPDT 开关, 砷化镓 MMIC	SPDT Switch, GaAs MMIC	8-VSP		2450.00/2,000
NJG1519KC1-TE3CT-ND	SP4T 开关, 砷化镓 MMIC	SP4T Switch, GaAs MMIC	10-FLP	2.73	2.28 1.82
NJG1519KC1-TE3TR-ND	SP4T 开关, 砷化镓 MMIC	SP4T Switch, GaAs MMIC	10-FLP		4777.50/3,000
NJG1522KB2-TE1CT-ND	SPDT 开关, 砷化镓 MMIC	SPDT Switch, GaAs MMIC	6-FLP	1.26	1.05 .84
NJG1522KB2-TE1TR-ND	SPDT 开关, 砷化镓 MMIC	SPDT Switch, GaAs MMIC	6-FLP		2205.00/3,000
NJG1524APC1-TE1CT-ND	DPDT 开关, 砷化镓 MMIC	DPDT Switch, GaAs MMIC	16-FFP	2.94	2.45 1.96
NJG1524APC1-TE1TR-ND	DPDT 开关, 砷化镓 MMIC	DPDT Switch, GaAs MMIC	16-FFP		6860.00/4,000
NJG1528KC1-TE3CT-ND	DPDT 开关, 砷化镓 MMIC	DPDT Switch, GaAs MMIC	10-FLP	3.48	2.90 2.32
NJG1528KC1-TE3TR-ND	DPDT 开关, 砷化镓 MMIC	DPDT Switch, GaAs MMIC	10-FLP		6090.00/3,000
NJG#1532KB2-TE2CT-ND	SPDT 开关, 砷化镓 MMIC*	SPDT Switch, GaAs MMIC*	6-FLP	1.26	1.05 .84
NJG#1532KB2-TE2TR-ND	SPDT 开关, 砷化镓 MMIC*	SPDT Switch, GaAs MMIC*	6-FLP		2259.00/3,000
NJG1544HC3-TE1CT-ND	2x2 天线开关, 砷化镓 MMIC	2x2 Antenna Switch GaAs MMIC	10-USB	1.47	1.23 .98
NJG1544HC3-TE1TR-ND	2x2 天线开关, 砷化镓 MMIC	2x2 Antenna Switch GaAs MMIC	10-USB		2572.50/3,000
NJG1602HE3-TE1CT-ND	DPDT 开关, 砷化镓 MMIC	DPDT Switch, GaAs MMIC	12-USB	2.31	1.93 1.54
NJG1602HE3-TE1TR-ND	DPDT 开关, 砷化镓 MMIC	DPDT Switch, GaAs MMIC	12-USB		4042.50/3,000
NJG1617K1-TE1CT-ND	无线局域网 DPDT 砷化镓 MMIC 开关	Wireless LAN DPDT GaAs MMIC Switch	12-QFN	1.38	1.15 .92
NJM2233BD-ND	2输入单路视频开关	2-Input Single Video Switch	8-Dip	.42	.35 .28
NJM2234D-ND	3输入视频开关	3-Input Video Switch	8-Dip	.51	.43 .34
NJM#2234M-ND	3输入视频开关*	3-Input Video Switch*	8-DMP	.51	.43 .34
NJM#2244M-ND	3输入视频开关*	3-Input Video Switch*	8-DMP	.57	.48 .38
NJM2249D-ND	3输入视频开关	3-Input Video Switch	8-Dip	1.05	.88 .70
NJM2249M-ND	3输入视频开关	3-Input Video Switch	8-DMP	1.05	.88 .70
NJM#2279D-ND	3输入, 2输出视频开关, 用于音频视频装置*	3-Input, 2-Output Video Switch for AV-Set*	14-Dip	1.50	1.25 1.00
NJM2283D-ND	2输入, 3通道视频开关	2-Input, 3-Channel Video Switch	16-Dip	1.50	1.25 1.00
NJM2283M-ND	2输入, 3通道视频开关	2-Input, 3-Channel Video Switch	16-DMP	1.35	1.13 .90
NJM2284V-TE1CT-ND	2输入, 3通道视频开关	2-Input, 3-Channel Video Switch	16-SSOP	1.14	.95 .76
NJM2284V-TE1TR-ND	2输入, 3通道视频开关	2-Input, 3-Channel Video Switch	16-SSOP		1330.00/2,000
NJM2285M-ND	2输入, 3通道视频开关	2-Input, 3-Channel Video Switch	16-DMP	1.17	.98 .78
NJM2285V-TE2CT-ND	2输入, 3通道视频开关	2-Input, 3-Channel Video Switch	16-SSOP	1.17	.98 .78
NJM2285V-TE2TR-ND	2输入, 3通道视频开关	2-Input, 3-Channel Video Switch	16-SSOP		1365.00/2,000
NJM2286D-ND	2输入, 3通道视频开关	2-Input, 3-Channel Video Switch	16-Dip	1.50	1.25 1.00
NJM#2286V-TE1CT-ND	2输入, 3通道视频开关*	2-Input, 3-Channel Video Switch*	16-SSOP	1.29	1.08 .86
NJM#2286V-TE1TR-ND	2输入, 3通道视频开关*	2-Input, 3-Channel Video Switch*	16-SSOP		1506.00/2,000
NJM2296D-ND	5输入, 3输出视频开关	5-Input, 3-Output Video Switch	16-Dip	2.19	1.83 1.46
NJM2296M-ND	5输入, 3输出视频开关	5-Input, 3-Output Video Switch	16-DMP	1.98	1.65 1.32
NJM2506M-ND	3输入, 2输出视频开关	3-Input, 2-Output Video Switch	16-DMP	1.08	.90 .72

\* 符合 RoHS 规范要求

(转下页)

★ 欢迎来电查询, 大批量订购, 价格优惠! ★

全部产品均以美元计价。

免费电话: 10800-1527031 (China Telecom - 中国电讯) — 10800-8527031 (CNCG - 中国网通)

1218 (CN082-09)

digkey.com.cn — 电话: (852) 3104 0500 — 传真: (852) 3104 0686